

Technical Documentation Local Languages (TDLL)

Documentation List
July 2017

Issued by Nordson Engineering, Lüneburg

Documentation List

Introduction

The Documentation List is updated and distributed monthly. It details translated manuals, instructions and operator's cards created, updated, and/or formatted in Nordson Engineering in Lüneburg.

The Documentation List is available to all, on request, as a **.pdf file**. This file contains *all* of the Product Line sections mentioned below in *one* file - enabling an easier and faster search for P/Ns or product titles etc.

Contents

The Documentation List is divided as follows:

Part A Nordson Engineering Hot Melt Products
(former Meltex), refer to page 2 for details

Part B Nordson US Hot Melt Products
refer to page 2 for details

Part C Nordson Finishing Products
refer to page 2 for details

Part D Nordson UV (U.K. and U.S.) Products

Part E Paper and Paperboard Converting
Nordson Benelux Products (former Walcom)

Part F

1. Asymtek
2. EFD
3. JM Laboratories
4. March Plasma
5. Mountaingate
6. MSDS
7. PICODOSTEC
8. Nordson Puffe Hot Melt
9. Slautterback
10. Watlow

Contents *(contd.)*

Part A Nordson Engineering Hot Melt Products

1. Blue Series Melters
 - DuraBlue
 - VersaBlue
2. Bulk Melters
 - BM 20, BM 200 Series
 - BM 5xxx Lueneburg Rebuilt Units
 - DG / DuraDrum / DuraPail
3. MC Units
4. MX Units
5. Auxiliary Systems, e.g. Pattern Ctrl, Refill, Temperature Ctrl, Timer, Verification
6. Applicators/ Guns
7. Systems -
 - Automotive, Bookbinding, Gasketing, Moulding
8. Coating Units
9. Other Hot Melt Units
10. Drives
11. Mechanical & Hydraulic Components
12. Pneumatic Components
13. Electrical & Electronic Components
14. Level Controls
15. Miscellaneous

Part B Nordson US Hot Melt Products

1. Blue Series Melters
2. Series 3000V (Vista)
3. Series 2000 / Series 3000 / Series 5000 / Series 6000
4. Other Melters and
 - Diverse Equipment, Hoses
5. Auxiliary Systems, e.g. Pattern Ctrl, Refill, Temperature Ctrl, Timer, Verification
6. Applicators/ Guns
7. FoamMelt & FoamMix
8. Bulk Melters, older BM 5xxx Series

Part C Nordson Finishing Products

1. Automotive / Container / Electronics / Liquid / NSE
2. U.S. Powder
3. U.K. Powder

Abbreviations and Header Line

Document Type:

- IN	Instructions
- MA	Manual
- OP	Operator's Card
- PA	Parts List
- PI	Product Information Sheet
- SA	Safety Section
- SU	Supplement

Languages:

- BU	Bulgarian
- CH	Chinese
- CR	Croatian
- CZ	Czech
- DA	Danish
- DU	Dutch
- EN	English
- ES	Estonian
- FI	Finnish
- FR	French
- GE	German
- GR	Greek
- HU	Hungarian
- IT	Italian
- JA	Japanese
- KO	Korean
- LA	Latvian
- LI	Lithuanian
- NO	Norwegian
- PL	Polish
- PO	Portuguese
- RO	Romanian
- RU	Russian
- SE	Serbian
- SK	Slovak
- SL	Slovenian
- SP	Spanish
- SW	Swedish
- TU	Turkish

The header line is made up of the following:

- Model	Specific Model name
- Product Title	Full title of document
- Langs.	Languages available (see abbreviations above)
- P/N	Part Number of document
- Type	Document type (see abbreviations above)
- Price Category	Number denoting price per copy
- Notes	Any additional useful information

NOTES: All documents within each section are sorted alphabetically according to *Model*. **Exceptions** - Nordson Finishing, JM Laboratories, Nordson UV (Spectral) and Nordson UK/ Europe are sorted according to *Product Title*.

Ordering Documents

When ordering manual/documentation copies please follow these guidelines. Please note the different product line procedures.

ALL Product Lines EXCEPT Nordson Engineering

These manuals are to be ordered at EDC, Maastricht. When creating an order in SAP, use the manual-specific P/N, **not** the Category P/N.

Nordson Engineering GmbH (MELTEX) Product Line

For ordering manuals or system documentation from Nordson Engineering the Category P/Ns should be used as listed below.

In order to allow documentation orders to be properly selected and served, the categories distinguish between media CD-ROM and conventional paper copy in blue binder.

Also AFTER-SALES and ADDITIONAL needs to be distinguished for both of the documentation media.

ADDITIONAL			
P/N	€	Documentation Type	Required Information
7156797	18	Configured Manual on CD-ROM Melter WITHOUT system components	Language
7156798	30	Configured Manual on CD-ROM Melter WITH system components (Hose, Applicator, etc.) or for numerous Systems	Language
AFTER-SALES			
P/N	€	Documentation Type	Required Information
7165316	18	Configured Manual on CD-ROM Melter WITHOUT system components	Language and Serial Number (of the main component)
7165317	30	Configured Manual on CD-ROM Melter WITH system components (Hose, Applicator, etc.) or for numerous Systems	Language and Serial Number (of the main component)

ADDITIONAL			
P/N	€	Documentation Type	Required Information
317102	18	Medium Manual typically Applicator, Timer	Language
317103	30	Configured Manual Melter WITHOUT system components	Language
317104	100	Configured Manual Melter WITH system components (Hose, Applicator, etc.)	Language
AFTER-SALES			
P/N	€	Documentation Type	Required Information
317107	18	Medium Manual typically Applicator, Timer	Language and Serial Number (or P/N)
317106	30	Configured Manual Melter WITHOUT system components	Language and Serial Number (of the main component)
317105	100	Configured System Manual Melter WITH system components (Hose, Applicator, etc.)	Language and Serial Number (of the main component)

NOTES:

ADDITIONAL means: Within a Nordson Engineering GmbH equipment order more copies are requested additional to the ONE documentation CD, which is automatically included in the equipment delivery.

AFTER-SALES means: Documentation items which refer to equipment sales orders delivered earlier (typically the need arises because the documentation originally being delivered got lost at the customer site).

For all **AFTER-SALES** orders, regardless whether on CD-ROM or in the conventional form of paper in blue binder, the product/system for which the documentation is requested must be identified (Serial number, P/N, UI, or - if applicable- the original SO#, the language request).

Please write the required information as Position Text into the SAP "Text" field. If that identification is missing the Lue PDE group cannot restore the requested order-specific document compilation.

In both cases, **ADDITIONAL** and **AFTER-SALES**, be careful to request language versions which may not yet exist. Casewise significant translation costs may result and should be clarified **PRIOR** to an order.

Do **NOT** use the category P/Ns for requesting translations which do not yet exist, but contact TS dept. at Lueneburg first in order to get a time & cost quote.

Information & Support

For translation enquiries (all product lines), information or feedback regarding **Nordson Engineering GmbH** documentation, please contact:

Nordson Engineering GmbH
Bettina Rösnick (Translation Support)
Lilienthalstr. 6
21337 Lüneburg / Germany

Phone: 49-4131-894-260
Email: bettina.roesnick@de.nordson.com

For **all other Product Lines** please contact:

Nordson European Distribution Centre B.V.
Cindy Kenzeler
Bergerstraat 10
6226 BD Maastricht / Netherlands

Phone: 31-43-3526-023
Fax: 31-43-3626-230
Email: cindy.kenzeler@nl.nordson.com

NOTES: If you cannot order directly in SAP, please send orders for documentation in writing (fax/email). Please include the following information:

Product Title, Language, P/N and Quantity required.

NOTES: The listed costs for documentation (on page 4 and 5) are valid for additional copies of existing material. If you order and pay for the translation of a manual etc., you will receive one soft-copy free of charge.

Central Archive in Lüneburg

The central archive for translated documents is in Lüneburg. Therefore, we ask you to give us any information regarding manuals e.g. translation needs, planned products, product changes etc.

In the Technical Documentation Local Languages department (TS) we assign Part Numbers for all translated documents, format them in accordance with the Nordson corporate design and style, archive all documents electronically, coordinate projects with experienced translators, and ensure that all documents are made available for everyone within the Nordson network.

We appreciate any comments and feedback which you may have to offer, so that we can enhance the cooperation between Local Language Support in Lüneburg, and Nordson worldwide.

All details correct at time of release. Liable to future corrections.

A-1 - 1

Nordson Engineering Hot Melt Products (sorted by Model)

Blue Series Melters - DuraBlue (for PURBlue EC melter see MC Units)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
DuraBlue	Kit-SVC conv. 7186936 (Motor Controller i550 in DuraBlue Melters)	EN GE	7560838_01 7560837_01	IN	(317103) or (317106)	
DuraBlue	DuraBlue Adhesive Melters - Models D25, D25H, D50, D100	CH CR CZ DA DU EN FI FR GE HU IT JA LA NO PL PO RO RU SK SP SW	397882A_1 7580141_11* 7119873_11 7105604_11 7105103_11 397056_11 7105105_11 397237_11 397063_11 7105410_11 397238_11 397276C 7146749_11 7105104_11 7119878_11 7105070_11 7580029_11 7105895_11 7192860_11 397247_11 7105068_11	MA	(317103) or (317106)	* = not yet released
DuraBlue	DuraBlue Adhesive Melters - Models D25, D25H, D50, D100 - Parts List -	EN	7146820_06	PA	(317102) or (317107)	
DuraBlue	DuraBlue Adhesive Melters - Models D25, D25H, D50, D100 - User's Guide	EN/ FR/ GE/ IT/ SP	7119964B	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
DuraBlue	DuraBlue Adhesive Melters - Models D25, D25H, D50, D100 - User's Guide	EN/ DA/ FI/ NO/ SW	7135110B	OP	(317102) or (317107)	Multilingual document, therefore one P/N only

A-1 - 2

Nordson Engineering Hot Melt Products (sorted by Model)

Blue Series Melters - DuraBlue (for PURBlue EC melter see MC Units)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
DuraBlue	DuraBlue Adhesive Melters - Models D25, D25H, D50, D100 - User's Guide	EN/ CZ/ HU/ PL/ RU	7135111B	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
DuraBlue	DuraBlue Adhesive Melters - Models D25, D25H, D50, D100 - User's Guide	EN/ DU/ PO/ SL/ SK	7135112B	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
DuraBlue	DuraBlue Adhesive Melters - Models D25, D25H, D50, D100 - User's Guide	EN/GE/ RO	7580030B	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
DuraBlue	DuraBlue Adhesive Melters - Models DK25, DK25H, DK50, DK100	DU EN FR GE IT NO SP SW	7119056_09 7105986_09 7119055_09 7105926_09 7119041_09 7119080_09 7119050_09 7119061D	MA	(317103) or (317106)	
DuraBlue	DuraBlue Adhesive Melters - Models DK25, DK25H, DK50, DK100 - Parts List -	EN	7146844_06	PA	(317102) or (317107)	
DuraBlue	DuraBlue Adhesive Melter D25H, D50	EN GE	7119512B 7119419B	MA	(317103) or (317106)	
DuraBlue	DuraBlue Adhesive Melters N-Series - Parts List -	EN	7156101_03	PA	(317102) or (317107)	
DuraBlue	Control Panel Service Kit - P/N 394734	EN/ FR/ GE/ IT/ SP	397411B	IN	(317102) or (317107)	Multilingual document, therefore one P/N only

A-1 - 3

Nordson Engineering Hot Melt Products (sorted by Model)

Blue Series Melters - DuraBlue (for PURBlue EC melter see MC Units)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
DuraBlue	Pneumatic Pressure Control Valve Service Kit - P/N 729055	EN/ FR/ GE/ IT/ SP	397871C	IN	(317102) or (317107)	<i>Multilingual document, therefore one P/N only</i>
DuraBlue	Pressure Control Valve (5-90 bar Manual) Accessory Kit - P/N 394795	EN/ FR/ GE/ IT/ SP	397671A	IN	(317102) or (317107)	<i>Multilingual document, therefore one P/N only</i>
DuraBlue	Shaft Seal Service Kits Gerotor Pump - P/N 394768 Shaft Seal Service Kits Gear Pump - P/Ns Diverse	EN/ FR/ GE/ IT/ SP	397325G	IN	(317102) or (317107)	<i>Multilingual document, therefore one P/N only</i>
DuraBlue/ DuraPail/ DuraDrum	Interface Cable - P/N 7109800, 7144759, 7148723, 7149085	CZ EN ES GE HU	7146015E 7119092E 7146245D 7105852E 7146217E	IN	(317102) or (317107)	
DuraBlue/ DuraPail/ DuraDrum	Interface Cable - P/N 7128700, 7144869, 7148912	EN GE	7135374F 7135356F	IN	(317102) or (317107)	
DuraBlue/ DuraPail/ DuraDrum	Service Kit Contactors P/N 251790, P/N 251791, P/N 251797, P/N 414100, P/N 256703, P/N 291187	EN/ FR/ GE/ IT/ SP	7119470A	IN	(317102) or (317107)	<i>Multilingual document, therefore one P/N only</i>

A-1 - 4

Nordson Engineering Hot Melt Products (sorted by Model) *Blue Series Melters - VersaBlue*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
VBCM	Electrical Cabinet VBCM	CZ DA DU EN FI FR GE HU IT PL PO RU SK SL SP SW TU	7580143_05 7580092_05 7119277_05 7105553_05 7119434_05 7146259_05 7105524_05 7560552_05 7105529_05 7119095_05 7560381_05 7560553_05 7105596_05 7146492_05 7135299_05 7105534_05 7192925_05	MA	(317102) or (317107)	
VBCM	VBCM with IPC Operator Panel	EN GE	7146063A 7135999A	MA	(317102) or (317107)	
VBCM	VBCM with Siemens PLC	FR GE IT JA	7156716A 7156699A 7179739A 7156706A	MA	(317102) or (317107)	
Versa	Engineering Update for Versa Adhesive Melters, Bulk Melters and VBCM	EN GE	7560962_02 7560938_02	MA	(317102) or (317107)	

A-1 - 6

Nordson Engineering Hot Melt Products (sorted by Model)

Blue Series Melters - VersaBlue

VersaBlue	VersaBlue Adhesive Melters Model VA and VT	BU CH CZ DA DU EN FI FR GE GR HU IT JA LA LI NO PL PO RO RU SL SP SW	7135678_11 397881A_4 7105310_11 397599_11 397537_11 213828_11 7105054_11 397049_11 213807_12 7105434_11 7105166_11 397051_11 397277_11 7179489_11 7169612_11 397803_11 7105203_11 397514_11 7169182_11 7105167_11 7105671_11 397023_11 397552_11	MA	(317103) or (317106)	
VersaBlue	VersaBlue Adhesive Melters Model VA and VT - Parts List -	EN	7135025_07	PA	(317102) or (317107)	
VersaBlue	Motor Controller i550	EN	7560839_01	IN	(317102) or (317107)	
VersaBlue	Kit-SVC conv. 7578171 (Motor Controller i550 in Versa Melters)	EN GE	7580110_01 7580105_01	IN	(317103) or (317106)	
VersaBlue	Kit-SVC conv. 7561537 (Motor Controller i550 in Versa Melters or Bulk Melters)	EN GE	7560961_02 7560943_02	IN	(317103) or (317106)	

A-1 - 7

Nordson Engineering Hot Melt Products (sorted by Model)

Blue Series Melters - VersaBlue

VersaBlue/ VersaBlue Plus	VersaBlue and VersaBlue Plus Melters in the Series N Types VB, VC, VD, VE, VW, VX, VY, VZ	CZ DA DU EN FI FR GE GR HU IT JA KO NO PL PO RU SK SL SP SW TU	7119645_09 7105811_09 7105446_09 7105144_09 7105557G 7105190_09 7105011_09 7119982_09 7105619_09 7105157_09 7105964G 7135197F 7105859_09 7119136_09 7105830_09 7119132_09 7105389_09 7146490_09 7105257_09 7105216_09 7119674_09	MA	(317103) or (317106)	
VersaBlue Plus	Engineering Update for Melter Type VersaBlue Plus with TruFlow Capability	EN GE	7192909_01 7192901_01	MA	(317103) or (317106)	
VersaBlue	VersaBlue Adhesive Melters Serie N, Model VB, VC, VD, VE, VW, VX, VY, VZ - Parts List -	EN	7119994_05	PA	(317102) or (317107)	
VersaBlue	VersaBlue Adhesive Melters Serie N, Model VB, VC, VD, VE, VW, VX, VY, VZ with Siemens Controller	DU EN FR GE PL	7146505A 7146181A 7146228A 7146149A 7146425A	MA	(317103) or (317106)	
VersaBlue	VersaBlue Adhesive Melters Serie N, Model VB, VC, VD, VE, VW, VX, VY, VZ with Siemens Controller - Parts List	EN	7146314C	PA	(317103) or (317106)	

A-1 - 8

Nordson Engineering Hot Melt Products (sorted by Model)

Blue Series Melters - VersaBlue

VersaBlue	VersaBlue Adhesive Melters Serie N, Model VD, VE, VY, VZ with Allen Bradley Control System	CZ EN GE IT PO RU SP SW	7169873_04 7105491_04 7105436_04 7156913_04 7169323_04 7146695_04 7135483_04 7179533_04	MA	(317103) or (317106)	
VersaBlue	VersaBlue Adhesive Melters Serie N, Model VD, VE, VY, VZ with Allen Bradley Control System - Parts List -	EN	7135190AC	PA	(317102) or (317107)	
VersaBlue	VersaBlue Melter Series N without IPC (Title version A: VersaBlue Adhesive Melters N, Model VW 012)	DU EN FR GE IT RU	7156671C 7135916C 7135139A 7135101C 7135934C 7156040C	MA	(317103) or (317106)	
VersaBlue	VersaBlue Melter Series N without IPC - Parts List -	EN	7156021B	PA	(317103) or (317106)	
VersaBlue	VersaBlue Adhesive Melters VB C - Model SC	DA DU EN GE FR IT NO PO SP TU	7169347B 7135148B 7135193_03 7135066_03 7135556B 7135161_03 7192876_03 7192887_03 7146385_03 7560655_03	MA	(317103) or (317106)	
VersaBlue	VersaBlue Adhesive Melters VB C - Model SC - Parts List -	EN	7169235_02	PA	(317102) or (317107)	

A-1 - 9

Nordson Engineering Hot Melt Products (sorted by Model)

Blue Series Melters - VersaBlue

VersaBlue	VersaBlue Adhesive Melters VBC with Allen Bradley Controller	CZ EN GE IT	7169874A 7135475A 7135315A 7560955A	MA	(317103) or (317106)	
VersaBlue	VersaBlue Adhesive Melters Model VB C with Industrial PC	CH DU EN FI GE IT SP SW	7560881_04 7169289C 7135228_04 7146402B 7119461_04 7135980B 7135358B 7169165C	MA	(317103) or (317106)	
VersaBlue	VersaBlue Adhesive Melters VB C with Industrial PC - Parts List -	EN	7135002_03	PA	(317102) or (317107)	
VersaBlue	VersaBlue Adhesive Melters VB C with Siemens Controller	EN FR GE IT RU SW	7135049A 7146344A 7135000A 7146665A 7146675A 7146279A	MA	(317103) or (317106)	
VersaBlue	VersaBlue Adhesive Melters VB C with Siemens Controller - Parts List -	EN	7135001A	PA	(317102) or (317107)	
VersaBlue	VersaBlue Adhesive Melters VBN with Allen Bradley Controller	EN GE IT RU SP	7119549D* 7119415C 7169324D* 7146694C 7119580D*	MA	(317103) or (317106)	* = New Sec. 4 OP from 1098104A !
VersaBlue	VersaBlue Adhesive Melters VBN with Allen Bradley Controller - Parts List -	EN	7146018A	PA	(317102) or (317107)	

A-1 - 10

Nordson Engineering Hot Melt Products (sorted by Model)

Blue Series Melters - VersaBlue

VersaBlue	VersaBlue Adhesive Melters VBN with Siemens Controller	DU EN FR GE IT PL SW	7146650A 7135528A 7156290A 7135044A 7146661A 7146426A 7135683A	MA	(317103) or (317106)	
VersaBlue	VersaBlue Adhesive Melters VBN with Siemens Controller - Parts List -	EN	7135135A	PA	(317102) or (317107)	
VersaBlue	VersaBlue Adhesive Melters VBN without Control System	EN FR GE	7146386A 7146639A 7146349A	MA	(317103) or (317106)	
VersaBlue	VersaBlue Adhesive Melters VBN without Control System - Parts List -	EN	7146350A	PA	(317102) or (317107)	
VersaBlue	VersaBlue Adhesive Melters VW050 Lotion	EN GE IT	7169157B 7156589B 7156651A	MA	(317102) or (317107)	
VersaBlue	VersaBlue LOTION Melters Serie N - Parts List -	EN	7156205_05	PA	(317102) or (317107)	
VersaBlue	VersaBlue Adhesive Melters VZ025 E with Siemens Controller	CH EN GE RU	7156663A 7156662A 7156498A 7156659A	MA	(317102) or (317107)	
VersaBlue	VersaBlue Adhesive Melters Twin Tank	EN GE IT	7169240A 7169151A 7169234A	MA	(317102) or (317107)	
VersaBlue	VersaBlue Melters Safety	EN/BU/ GE/RO/ TU	7156010C	OP	(317102) or (317107)	Multilingual document, therefore one P/N only

A-1 - 11

Nordson Engineering Hot Melt Products (sorted by Model) Blue Series Melters - VersaBlue

VersaBlue	VersaBlue Melters Safety	EN/ CH/JA	7119555B	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	VersaBlue Melters Safety	EN/CR/ ES/LA/ LI	7179537C	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	VersaBlue Melters Safety	EN/CZ/ HU/PL/ RU	7119556C	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	VersaBlue Melters Safety	EN/DA/ FI/NO/ SW	7119564C	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	VersaBlue Melters Safety	EN/DU/ PO/SL/ SK	7119565C	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	VersaBlue Melters Safety	EN/FR/ GE/IT/ SP	7105468C	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	VersaBlue Melters User's Guide	EN/BU/ GE/RO/ TU	7156009B	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	VersaBlue Melters User's Guide	EN/ CH/JA	7105978C	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	VersaBlue Melters User's Guide	EN/CR/ ES/LA/ LI	7179536C	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	VersaBlue Melters User's Guide	EN/CZ/ HU/PL/ RU	7119200C	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	VersaBlue Melters User's Guide	EN/DA/ FI/NO/ SW	7119199C	OP	(317102) or (317107)	Multilingual document, therefore one P/N only

A-1 - 12

Nordson Engineering Hot Melt Products (sorted by Model)

Blue Series Melters - VersaBlue

VersaBlue	VersaBlue Melters User's Guide	EN/DU/ PO/SL/ SK	7119566C	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	VersaBlue Melters User's Guide	EN/FR/ GE/IT/ SP	7105284C	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	VersaBlue Adhesive Melters - Safety and User's Guide	GE GR	7560164_01 7560845_01	OP	(317102) or (317107)	
VersaBlue	Accessory Kit, Lid VB/DB Feed System - P/N 7116463	EN/ FR/ GE/ IT/ SP	7119696A	IN	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	Adapter cable - P/N 398681B, 7137287, 7153276, 7165446, 7170178	EN/ GE	7105339H	IN	(317102) or (317107)	Bilingual document, therefore one P/N only
VersaBlue	Adapter cable - P/N 7137425, ..., 7197447	EN/ GE	7135376_09	IN	(317102) or (317107)	Bilingual document, therefore one P/N only
VersaBlue	Adapter Cable for Handgun Operation - P/N 398564	EN/ FR/ GE/ IT/ SP	7105022A	IN	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	Bypass Plate Service Kit - P/N 394594 or 394595 (HT)	EN/ FR/ GE/ IT/ SP	397160A	IN	(317102) or (317107)	Multilingual document, therefore one P/N only
Versablue	Bypass Plate Service Kit - P/N 7104646	EN/ FR/ GE/ IT/ SP	7105134A	IN	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	Filter Service Kit - P/N 394590, 7109691 or P/N 394591 (HT)	EN/ FR/ GE/ IT/ SP	397158B	IN	Non-Saleable	Multilingual document, therefore one P/N only -> Cross-reference to manual !
VersaBlue	Heat Exchanger Parts Kit - P/N 7116737	EN/ FR/ GE/ IT/ SP	7119462A	IN	(317102) or (317107)	Multilingual document, therefore one P/N only

A-1 - 13

Nordson Engineering Hot Melt Products (sorted by Model) Blue Series Melters - VersaBlue

VersaBlue	Inert Gas Kit - P/N 394770	EN/ FR/ GE/ IT/ SP	7105050_02	IN	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	IPC Console Service Kit - P/N 729865	EN/ FR/ GE/ IT/ SP	397972A	IN	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	Level Kits for VersaBlue	EN/FR/ GE	7105320_05	IN	(317102) or (317107)	Trilingual document, therefore one P/N only
VersaBlue	Light Tower Service Kit - P/N 394794	EN/ FR/ GE/ IT/ SP	397313A	IN	Non- Saleable	Multilingual document, therefore one P/N only -> Cross-reference to manual !
VersaBlue	Pressure Control Valve (pneu.) Service Kit - P/N 394602 or 394603 (HT)	EN/ FR/ GE/ IT/ SP	397163A	IN	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	Pressure Control Valve Service Kit - P/N 394600 or P/N 394601 (HT)	EN/ FR/ GE/ IT/ SP	397162A	IN	Non- Saleable	Multilingual document, therefore one P/N only -> Cross-reference to manual !
VersaBlue	Pump Service Kit - P/N 394589 or P/N 394596	EN/ FR/ GE/ IT/ SP	397157A	IN	Non- Saleable	Multilingual document, therefore one P/N only -> Cross-reference to manual !
VersaBlue	Retrofit Kit Coupling Monitoring - P/N 7104102	EN/ FR/ GE/ IT/ SP	7105936B	IN	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	RTD Sensor (Ni 120) Service Kit - P/N 394597	EN/ FR/ GE/ IT/ SP	397312A	IN	Non- Saleable	Multilingual document, therefore one P/N only -> Cross-reference to manual !
VersaBlue	Safety Valve Service Kit - P/N 394592 or P/N 394593 (HT)	EN/ FR/ GE/ IT/ SP	397159A	IN	Non- Saleable	Multilingual document, therefore one P/N only -> Cross-reference to manual !
VersaBlue	Software Upgrade Kit Vers. ≤ 1.00.000 to > 1.00.000 - P/N 7104397	EN/ FR/ GE/ IT/ SP	7105044A	IN	(317102) or (317107)	Multilingual document, therefore one P/N only

A-1 - 14

Nordson Engineering Hot Melt Products (sorted by Model)

Blue Series Melters - VersaBlue

VersaBlue	Spare Parts Kit - High Temperature (HT) Thermostat - P/N 1035766	EN/ FR/ GE/ IT/ SP	7105958A	IN	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	Tank Isolation Valve Service Kit - P/N 394598 or P/N 394599 (HT)	EN/ FR/ GE/ IT/ SP	397161A	IN	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaBlue	Upgrade Instructions (Upgrade to Software Version 3.22.014)	EN	7105948E	IN	(317102) or (317107)	
VersaBlue	Engineering Update IPC III (Industrial PC Generation III, Software Version 6.00.000)	EN GE	7169185A 7169172A	MA	(317102) or (317107)	
VersaBlue	Installation and Operation via the IPC Webserver	EN GE	7192668_02 7192664_02	IN	(317102) or (317107)	
VTC	Electrical Cabinet VTC	CZ EN FI GE IT SW	7169993_02 7169994_02 7169996_02 7169462_02 7179217_02 7192640_02	MA	(317102) or (317107)	

A-2 - 1

Nordson Engineering Hot Melt Products (sorted by Model)

Bulk Melters - BM 20 Series

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
BM 20	Bulk Melters BM 20 with Gear/Gerotor Pump for 20l Drums	DA DU EN FR GE IT JA NO PO SP SW	458448D 458421D 458372D 458397D 458327D 458423D 464856C* 458471D 464859D 458407D 458464D	MA	(317102) or (317107)	* available at Nordson K.K.
BM 20	BM 20 with Gear/Gerotor Pump - Parts List -	EN	464845D	PA	(317102) or (317107)	
BM 20 EASY	Bulk Melters BM 20 with Gear Pump / Gerotor Pump - EASY Pneumatics -	CZ DA DU EN FI FR GE IT NO PL PO RU SK SP SW	7105856E 397267E 397165E 397166E 7119862E 397173E 397086E 397184E 397227E 7105209E 397177E 7135765E 7119037E 397222E 397230E	MA	(317102) or (317107)	
BM 20 EASY	Bulk Melters BM 20 with Gear/Gerotor Pump - EASY pneumatic - - Parts List -	EN	213959K	PA	(317102) or (317107)	

A-2 - 2

Nordson Engineering Hot Melt Products (sorted by Model)

Bulk Melters - BM 20 Series

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
BM 20	Bulk Melters BM 20 with Piston Pump for 20l Drums	DA DU EN FR GE IT JA NO PO SP SW	447688E 458499E 458478E 458493E 458284E 458494E 464862C* 464723E 213165E 447603E 447651E	MA	(317102) or (317107)	* available at Nordson K.K.
BM 20	BM 20 with Piston Pump - Parts List -	EN	464846A	PA	(317102) or (317107)	
BM 20 EASY	Bulk Melters BM 20 with Piston Pump - EASY Pneumatics -	DA DU EN FI FR GE IT NO PO SP SW	397538A* 397539E 397540E 7135230E 397541E 397087E 397542E 397543E 397544E 397545E 397546E	MA	(317102) or (317107)	* = not yet translated
BM 20 EASY	Bulk Melter Series BM 20 with Piston Pump - EASY pneumatic - -Parts List -	EN	397436H	MA	(317102) or (317107)	
BM 20 / BM 200	Bulk Melters BM 20 / BM 200	EN GE FR IT SL SP	7119313B 7119275B 7119314B 7119315B 7135026B 7119316B	OP	(317102) or (317107)	

A-2 - 3

Nordson Engineering Hot Melt Products (sorted by Model)

Bulk Melters - BM 20 Series

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
BM 20 / BM 200	Control Unit Change-Over for Bulk Melters in the Series BM 20/BM 200	DA DU EN FI FR GE IT JA NO PO SP SW	458475C 458454C 458442C 447748C 458439C 458282C 458469C 464864C* 458459C 213198C 458457C 458450C	MA	(317102) or (317107)	* available at Nordson K.K.
BM 20 / BM 200	Control Unit Change-Over II for Bulk Melters BM 20/BM 200	DU EN FR GE IT NO PO SP SW	397910A 397891A 397886A 397875A 397904A 397929A 397906A 397884A 397912A	MA	(317102) or (317107)	
BM 20 / BM 200	Pressure Control for Bulk Melters Series BM 20 / BM200	DU EN FR GE IT JA PO SP SW	458455A 458356A 458406A 458283A 458474A 464863A* 213171A 447711A 458466A	MA	(317102) or (317107)	* available at Nordson K.K.

A-2 - 4

Nordson Engineering Hot Melt Products (sorted by Model)

Bulk Melters - BM 20 Series

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
BM 20 / BM 200	Aeration, Pneumatic Assembly P/N 394049 for Bulk Melters BM 20 with Gear/Gerotor Pump Assembly P/N 729174 for Bulk Melters BM 20 / BM 200 with Piston Pump Assembly P/N 394575 for Bulk Melters BM 200 with Gear/Gerotor Pump	EN GE	397039C	IN	(317102) or (317107)	<i>Bilingual</i> document, therefore one P/N only
BM 20 / BM 200	Retrofit Kit Bulk Melters BM 20 / BM 200	EN/GE/ FR/SP	213146A	IN	(317102) or (317107)	<i>Multilingual</i> document, therefore one P/N only
BM 20 / BM 200	Replacing Aeration Valve on Bulk Melters BM 20, BM 200	EN	213774A	IN	(317102) or (317107)	
BM 20 / BM 200 EASY	Instructions for retrofit Kit 729121	EN/GE/ FR/IT/ SP	397598A	IN	(317102) or (317107)	<i>Multilingual</i> document, therefore one P/N only

A-2 - 5

Nordson Engineering Hot Melt Products (sorted by Model)

Bulk Melters - BM 200 Series

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
BM 200	Bulk Melters BM 200 with Gear/Gerotor Pump for 200 l Drums	DA DU EN FR GE IT NO PO SP SW	213403C 213030C 464958C 213027C 447681C 464956C 213033C 213166C 213032C 213031C	MA	(317102) or (317107)	
BM 200	BM 200 with Gear Pump - Parts List -	EN	213003_06	PA	(317102) or (317107)	
BM 200 EASY	Bulk Melters BM 200 with Gear Pump - EASY Pneumatics -	CZ DA DU EN FI FR GE IT NO PL PO RU SP SW	7119700E 397268E 397212E 397189E 397858E 397220E 397084E 397195E 397248E 7146329E 397244E 7135691E 397233E 397260E	MA	(317102) or (317107)	
BM 200 EASY	Bulk Melters BM 200 with Gear Pump - EASY-pneumatic - - Parts List -	EN	397176J	PA	(317102) or (317107)	

A-2 - 6

Nordson Engineering Hot Melt Products (sorted by Model)

Bulk Melters - BM 200 Series

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
BM 200	Bulk Melter BM 200 with Piston Pump for 200l Drums	DA DU EN FR GE IT NO PO SP SW	213058B 464952B 464937B 464936B 447682B 464931B 464964B 213164B 464940B 213006B	MA	(317102) or (317107)	
BM 200	BM 200 with Piston Pump - Parts List -	EN	213004B	PA	(317102) or (317107)	
BM 200 EASY	Bulk Melters BM 200 with Piston Pump - EASY Pneumatics -	CZ DA DU EN FR GE IT NO PL PO SP SW	7105110E 397440E 397270E 397249E 397271E 397085E 397299E 397300E 7119248E 397269E 397273E 397275E	MA	(317102) or (317107)	
BM 200 EASY	Bulk Melters BM 200 with Piston Pump - EASY-pneumatic - - Parts List -	EN	397437I	PA	(317102) or (317107)	

A-2 - 7

Nordson Engineering Hot Melt Products (sorted by Model)

Bulk Melters - BM 5xxx Lueneburg Rebuilt Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
BM 505 PC	Bulk Melter BM 505 PC	EN GE	284119 284067	MA	(317104) or (317105)	Meltex
BM 505 PC/ BM 506 PC/ BM 5506 PC/ BM 5530 PC/ BM 5540 PC/ BM 551 PC/ BM 5550 PC/ BM 5551 PC	Drum Melter BM 505 PC / BM 506 PC BM 5506 PC / BM 5530 PC BM 5540 PC / BM 551 PC BM 5550 PC / BM 5551 PC	DA DU FI FR IT PO SP SW	290860A 290861A 290863A 290864A 290865A 290866A 290867A 290868A	IN	(317102) or (317107)	Meltex
BM 506 PC	Bulk Melter BM 506 PC	EN GE	269809 267962	MA	(317104) or (317105)	Meltex, when ordering, please state Unit Type and Serial Number
BM 506 PC/ BM 5506 PC/ BM 551 PC/ BM 5551 PC	Bulk Melters BM 506 PC / BM 5506 PC/ BM 551 PC / BM 5551 PC	EN GE PL	269826 269825 213255	OP	(317102) or (317107)	Meltex
BM 551 PC	Bulk Melter BM 551 PC	EN GE	284120 267964	MA	(317104) or (317105)	Meltex, when ordering, please state Unit Type and Serial Number
BM 5506 PC	Bulk Melter BM 5506 PC	EN GE	284043 284113	MA	(317104) or (317105)	Meltex, when ordering, please state Unit Type and Serial Number
BM 5530 PC/ BM 5540 PC	BM 5530 PC / BM 5540 PC - Parts List -	EN	317124A	PA	(317102) or (317107)	Meltex, only to be ordered with Instructions and Supplement

Issued by Technical Documentation Local Languages (TDLL) Department, Nordson Engineering, Lüneburg
Status : July 2017

A-2 - 8

Nordson Engineering Hot Melt Products (sorted by Model) ***Bulk Melters - BM 5xxx Lueneburg Rebuilt Units***

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
BM 5550 PC	BM 5550 PC - Parts List -	EN	317125	PA	(317102) or (317107)	Meltex, only to be ordered with Instructions and Supplement
BM 5551 PC	Bulk Melter BM 5551 PC	EN GE SP	284118 267965 403035	MA	(317104) or (317105)	Meltex, when ordering, please state <i>Unit Type and Serial Number</i>

A-2 - 9

Nordson Engineering Hot Melt Products (sorted by Model)

Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
AltaPail	AltaPail Bulk Melters DP020	EN GE	7169000B 7156963B	MA	(317102) or (317107)	
AltaPail	AltaPail Bulk Melters DP020 - Parts List	EN	7156964A	PA	(317102) or (317107)	
DG 21 / DG 201	Drum Melters DG 21 / DG 201	DU EN FR GE IT SP	464849A 464839A 213094A 464764A 464842A 464848A	MA	(317104) or (317105)	
DG 22 / DG 25 / DG 26 DG 202 / DG 207 / DG 251	Drum Melters DG 22 / DG 25 / DG 26 DG 202 / DG 207 / DG 251	DA DU EN FR GE IT SP	458221A 412873A 412976A 412874A 412854A 413013A 458020A	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
DG 25	Drum Melters DG 25	FR GE SP	458387A 458128A 458388A	MA	(317104) or (317105)	

A-2 - 10

Nordson Engineering Hot Melt Products (sorted by Model)

Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
DuraDrum	DuraDrum Bulk Melters DD200	CZ DA DU EN FI FR GE GR IT JA NO PL PO RU SP SW	7119475J 7105975J 7105868J 7105731J 7119378J 7105821J 7105721K 7135232K 7105820J 7105881A 7105878J 7119472J 7105873J 7156582K 7105765J 7105872J	MA	(317102) or (317107)	
DuraDrum	DuraDrum Bulk Melters DD200 - Parts List -	EN	7135705B	PA	(317102) or (317107)	
DuraDrum	DuraDrum Bulk Melters DK200	BU CZ DU EN ES FI FR GE HU IT NO PO RU SP SW	7135427H 7135271H 7119505H 7119506I 7146242H 7135052H 7119507H 7119423I 7146214H 7119508H 7119509H 7146399H 7146219H 7119510H 7119511H*	MA	(317103) or (317106)	* = not yet translated

A-2 - 11

Nordson Engineering Hot Melt Products (sorted by Model)

Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
DuraDrum	DuraDrum Bulk Melters DK200 - Parts List -	EN	7135706B	PA	(317102) or (317107)	
DuraDrum	DuraDrum Bulk Melter (P/N 8051763)	GE	7105533A	IN	(317102) or (317107)	
DuraDrum	DuraDrum Bulk Melter (P/N 8055277)	EN GE	7105625A 7105623A	IN	(317102) or (317107)	
DuraDrum/ DuraPail	DuraDrum/ DuraPail Bulk Melters User's Guide	EN/ CH/JA	7119560_02	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
DuraDrum/ DuraPail	DuraDrum/ DuraPail Bulk Melters User's Guide	EN/CR/ ES/LA/ LI	7192166B	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
DuraDrum/ DuraPail	DuraDrum/ DuraPail Bulk Melters User's Guide	EN/CZ/ HU/PL/ RU	7119558B	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
DuraDrum/ DuraPail	DuraDrum/ DuraPail Bulk Melters User's Guide	EN/DA/ FI/NO/ SW	7119567B	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
DuraDrum/ DuraPail	DuraDrum/ DuraPail Bulk Melters User's Guide	EN/DU/ PO/SL/ SK	7119568B	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
DuraDrum/ DuraPail	DuraDrum/ DuraPail Bulk Melters User's Guide	EN/ FR/ GE/ IT/ SP	7119276B	OP	(317102) or (317107)	Multilingual document, therefore one P/N only

A-2 - 12

Nordson Engineering Hot Melt Products (sorted by Model)

Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
DuraPail	DuraPail Bulk Melters DP020	CZ DA DU EN FI FR GE GR IT JA NO PL PO SP SW	7119437K 7105976K 7105367K 397983K 7119377K 397981K 397493L 7146489L 397995K 7105122A 7105406K 7119337K 7105346K 7105018K 7105355K	MA	(317103) or (317106)	
DuraPail	DuraPail Bulk Melters DP020 - Parts List -	EN	7135694E	PA	(317102) or (317107)	
DuraPail	DuraPail Bulk Melters DK020	BU CZ DU EN FR GE IT JA NO PL PO RO RU SK SP SW	7135426G 7146014G 7119489G 7119488G 7119490H 7119422H 7119491G 7156095G* 7119492G 7119504G 7146576H 7156845H 7146856H 7146164G 7119493G 7119494G	MA	(317103) or (317106)	* available at Nordson K.K.

A-2 - 13

Nordson Engineering Hot Melt Products (sorted by Model)

Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
DuraPail	DuraPail Bulk Melters DK020 - Parts List -	EN	7135693E	PA	(317102) or (317107)	
DuraPail/ DuraDrum	DuraPail DP020 / DuraDrum DD200 Bulk Melters Generation II	CZ DA DU EN ES FI FR GE GR HU IT JA LI NO PL PO RO RU SP SW	7156450_07 7156384_07 7156211_09 7156106_09 7179784_07 7156361_07 7156148_09 7146728_09 7156368_07 7156648_09 7156109_09 7156277B* 7560747_09 7156587_07 7156654_09 7156152_07 7560546_08 7169170_07 7156107_09 7156360_09	MA	(317103) or (317106)	* available at Nordson K.K.
DuraPail/ DuraDrum	DuraPail DP020 Bulk Melters with Gear Pump Generation II - Parts List -	EN	7146729_10	PA	(317102) or (317107)	
DuraPail/ DuraDrum	DuraDrum DD200 Bulk Melters with Gear Pump Generation II - Parts List -	EN	7146730_10	PA	(317102) or (317107)	
DuraPail/ DuraDrum/ VersaPail/ VersaDrum	DuraPail/ DuraDrum VersaPail/ VersaDrum Bulk Melters Safety	EN/ CH/JA	7119561_02	OP	(317102) or (317107)	Multilingual document, therefore one P/N only

A-2 - 14

Nordson Engineering Hot Melt Products (sorted by Model)

Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
DuraPail/ DuraDrum/ VersaPail/ VersaDrum	DuraPail/ DuraDrum VersaPail/ VersaDrum Bulk Melters Safety	EN/CR/ ES/LA/ LI	7192168C	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
DuraPail/ DuraDrum/ VersaPail/ VersaDrum	DuraPail/ DuraDrum VersaPail/ VersaDrum Bulk Melters Safety	EN/CZ/ HU/PL/ RU	7119559C	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
DuraPail/ DuraDrum/ VersaPail/ VersaDrum	DuraPail/ DuraDrum VersaPail/ VersaDrum Bulk Melters Safety	EN/DA/ FI/NO/ SW	7119569C	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
DuraPail/ DuraDrum/ VersaPail/ VersaDrum	DuraPail/ DuraDrum VersaPail/ VersaDrum Bulk Melters Safety	EN/DU/ PO/SL/ SK	7119570C	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
DuraPail/ DuraDrum/ VersaPail/ VersaDrum	DuraPail/ DuraDrum VersaPail/ VersaDrum Bulk Melters Safety	EN/ FR/ GE/ IT/ SP	7119305C	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
VersaDrum	VersaDrum VD200 Bulk Melters with Gear Pump - Parts List -	EN	7146281_13	PA	(317102) or (317107)	
VersaDrum	VersaDrum VD200 Bulk Melters with Piston Pump - Parts List -	CH EN RU	7169270_08 7146280_11 7169001E	PA	((317102) or (317107)	
VersaDrum	Bulk Melters VersaDrum VD200 with Allen-Bradley Controller (P/N 7155289,....,7570976)	EN GE	7156136_02 7156128_02	MA	(317103) or (317106)	
VersaDrum	Bulk Melters VersaDrum VD200 with Allen-Bradley Controller (P/N 7161294,....,7564594)	EN GE	7156761_07 7156754_07	MA	(317103) or (317106)	

A-2 - 15

Nordson Engineering Hot Melt Products (sorted by Model)

Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
VersaDrum	Bulk Melters VersaDrum VD200 with Allen-Bradley Controller (P/N 7573575)	EN GE IT	7560923_01 7560922_01 7560924_01	MA	(317103) or (317106)	
VersaDrum	Bulk Melters VersaDrum VD200 with Gear Pump - Model SC	DA EN FR GE IT RO SP TU	7169313A 7169427A 7179450A 7169277_02 7192762A 7560801_02 7169627A 7560656A	MA	(317103) or (317106)	
VersaDrum	Bulk Melters VersaDrum VD200 with Gear Pump - Model SC - Parts List -	GE	7169278_02	PA	(317103) or (317106)	
VersaDrum	Bulk Melters VersaDrum VD200 (P/N 7184467) with Gear Pump and Siemens Controller	EN GE PL	7179961_01 7179771_01 7179989_01	MA	(317103) or (317106)	
VersaDrum	Bulk Melters VersaDrum VD200 (P/N 7184467) with Gear Pump and Siemens Controller - Parts List -	EN PL	7179981_01 7179997_01	PA	(317103) or (317106)	
VersaDrum	Interface Cable P/N 7153985, 7177902	EN GE	7156286_02 7156155_02	IN	(317102) or (317107)	
VersaDrum	Kit-SVC conv. 7186935 (Motor Controller i550 in VersaDrum Melters)	EN GE	7560960_03 7560944_03	IN	(317103) or (317106)	
VersaDrum/ VersaPail	ACO System with Bulk Melters VersaPail/ VersaDrum	EN/ GE	7156074_05	IN	(317102) or (317107)	<i>Bilingual document, therefore one P/N only</i>
VersaDrum/ VersaPail	VersaDrum/ VersaPail Bulk Melters User's Guide	EN/CH/ JA	7169763_02	OP	(317102) or (317107)	<i>Multilingual document, therefore one P/N only</i>

A-2 - 16

Nordson Engineering Hot Melt Products (sorted by Model)

Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
VersaDrum/ VersaPail	VersaDrum/ VersaPail Bulk Melters User's Guide	EN/CR/ ES/LA/ LI	7192167B	OP	(317102) or (317107)	<i>Multilingual document, therefore one P/N only</i>
VersaDrum/ VersaPail	VersaDrum/ VersaPail Bulk Melters User's Guide	EN/CZ/ HU/PL/ RU	7146791B	OP	(317102) or (317107)	<i>Multilingual document, therefore one P/N only</i>
VersaDrum/ VersaPail	VersaDrum/ VersaPail Bulk Melters User's Guide	EN/DA/ FI/NO/ SW	7146790B	OP	(317102) or (317107)	<i>Multilingual document, therefore one P/N only</i>
VersaDrum/ VersaPail	VersaDrum/ VersaPail Bulk Melters User's Guide	EN/DU/ PO/SL/ SK	7146789B	OP	(317102) or (317107)	<i>Multilingual document, therefore one P/N only</i>
VersaDrum/ VersaPail	VersaDrum/ VersaPail Bulk Melters User's Guide	EN/FR/ GE/IT/ SP	7146751B	OP	(317102) or (317107)	<i>Multilingual document, therefore one P/N only</i>
VersaPail/ VersaDrum	VersaPail/ VersaDrum Safety and User' s Guide	GE GR RO TU	7560799_01 7560824_01 7560813_01 7560828_01	OP	(317102) or (317107)	

A-2 - 17

Nordson Engineering Hot Melt Products (sorted by Model)

Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
VersaPail/ VersaDrum	VersaPail VP020 / VersaDrum VD200 Bulk Melters with Gear Pump and IPC Control Unit	CH CR CZ DA DU EN FI FR GE GR HU IT JA NO PL PO RO RU SK SP SW TU	7146594_10 7580036_10 7156944_10 7146982_08 7146172_10 7135406_10 7146496_09 7146126_10 7135377_10 7169304_08 7156458_08 7146591_10 7146328A** 7146715_08 7156468_10 7146745_10 7192769_10 7146389_08 7179505_08 7146485_10 7146499_09 7560789_10	MA	(317103) or (317106)	** available at Nordson K.K.

A-2 - 18

Nordson Engineering Hot Melt Products (sorted by Model)

Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
VersaPail/ VersaDrum	VersaPail VP020 / VersaDrum VD200 Bulk Melters with Piston Pump and IPC Control Unit	CH CZ DU EN FR GE GR JA NO PL PO RU SP SW TU	7156532_04 7146677_04 7192915_05 7146640_06 7179440_06 7146084_06 7179560_06 7156467_04 7169848_04 7156814_05 7156558_04 7156850_04 7146423_04 7146707_04 7560079_05	MA	(317103) or (317106)	
VersaPail/ VersaDrum	Engineering Update with Bookbinding System Configurations (VP/VD with IPC)	CR CZ DU EN FR GE PL PO RU SP SW	7580046_01 7192735_01 7192736_01 7192665_01 7192678_01 7192646_01 7192733_01 7192675_01 7192737_01 7192666_01 7192739_01	MA	(317103) or (317106)	
VersaPail	VersaPail VP020 Bulk Melters with Gear Pump - Parts List -	EN	7146098_11	PA	(317103) or (317106)	
VersaPail	VersaPail VP020 Bulk Melters with Piston Pump - Parts List -	EN	7146178_10	PA	(317102) or (317107)	

A-3 - 1

Nordson Engineering Hot Melt Products (sorted by Model)

MC/ (PUR) Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
MC 4	Hot Melt Material Applicator MC 4	DU EN GE IT	7105567A 213746A 464771B 213747B	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
MC 6	Hot Melt Material Applicator MC 6	DU EN FR GE IT PO SP SW	403109D 403022D 403142D 317230D 403043D 405042D 405011D 403126D	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
MC 7	Hot Melt Material Applicator MC 7	DU EN FI FR GE HU IT NO PL PO RU SK SP SW	7105970C 412892C 458161C 397885C 412855C 7146612C 458170C 458320C 7135116C 213660C 7135995C 7135452C 412910C 397265C	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
MC 7	Hot Melt Material Applicator MC 7 - Parts List -	EN	7135003A	PA	(317102) or (317107)	

A-3 - 2

Nordson Engineering Hot Melt Products (sorted by Model)

MC/ (PUR) Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
MC 12/ MC 24	Hot Melt Material Applicator MC 12 / MC 24	CZ DA DU EN FI FR GE GR IT NO PL PO RU SP SW	7105701D 405207D 403119D 403076D 413008D 403102D 317291D 7119832D 403077D 409452D 7105796D 7119416D 7105352D 403112D 403243D	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number Obolete! Replaced by PURBlue 4 and PURBlue EC
MC 12/ MC 24	Hot Melt Material Applicator MC 12 / MC 24 - Parts List -	EN	7135004A	PA	(317102) or (317107)	
MC 20/ MC 21	Melter MC 20 / MC21 with Foil Bag (Title Rev. A - E: Melter MC 20 with Foil Bag)	CZ DU EN FI FR GE HU IT JA PL PO RO RU SK SP SW	7105250F 7119673F 397155F 7105430E 397491F 213642F 7156911F 397480F 7105965D 7119266F 7169394F 7135621F 7135298F 7119924F 7105697F 7105431E	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number

A-3 - 3

Nordson Engineering Hot Melt Products (sorted by Model)

MC/ (PUR) Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
MC21 MOD	Adhesive Melters MC21 MOD for Foil-encased PUR Slugs	CZ DU EN FR GE IT PO SK SP	7169890_02 7179389_02 7169901_03 7179356_02 7169563_03 7179757_03 7179905_03 7179530_02 7179064_03	MA	(317102) or (317107)	
MC21 MOD	Adhesive Melters MC21 MOD for Foil-encased PUR Slugs - Parts List	EN	7179606_01	PA	(317102) or (317107)	
MC 106	MC 106 Hot Melt Material Applicator	DA DU EN FR GE IT NO SW	315709A 292738A 283043A 292793A 269876A 290702A 292854A 284184A	MA	(317103) or (317106)	When ordering, please state Unit Type and Serial Number
MC 201/ MC 203/ MC 204/ MC 210	Hot Melt Material Applicators MC 201 / MC 203 / MC 204 / MC 210	EN GE	412628A 409066A	MA	(317102) or (317107)	When ordering, please state Unit Type and Serial Number
MC 405	Hot Melt Applicator MC 405 for Foil Bags	CZ DU EN FR GE HU IT PL SK SP	7146593G 7105658G 213668G 7105667G 213066G 7119805G 7146647G 7135320G 7119349G 7119033G	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number

A-3 - 4

Nordson Engineering Hot Melt Products (sorted by Model)

MC/ (PUR) Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
MC 4020	MC 4020 Hot Melt Material Applicator	DU EN FR GE IT SW	292716A 284124A 290714A 284125A 290715A 292715A	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
MC 4420	Hot Melt Material Applicator MC 4420	DA DU EN FI FR GE IT PO RU SP SW	409195E 317079E 315915E 405210E 403113E 315858E 315911E 213098E 7119635E 317042E 403248E	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number Obsolete! Replaced by PURBlue EC and MC21 MOD
MC 4420	Hot Melt Material Applicator MC 4420 - Parts List -	EN	7135164A	PA	(317102) or (317107)	
PURBlue EC	Adhesive Melters PURBlue EC for Reactive Materials	EN FI FR GE IT JA LI PL PO RO SP SW	7135268_05 7146601B 7135321A 7135055_06 7135322_05 7135449B 7179996_06 7135661A 7146680B 7156680C 7135262C 7156791_06	MA	(317102) or (317107)	

A-3 - 5

Nordson Engineering Hot Melt Products (sorted by Model)

MC/ (PUR) Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
PURBlue EC	PURBlue EC Melters - Safety	EN/ FR/ GE/ IT/ SP	7135243A	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
PURBlue EC	PURBlue EC Melters - Safety	EN/ DA/ RO / SW/ LI	7156682_02	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
PURBlue EC	PURBlue EC Melters - User's Guide	EN/ FR/ GE/ IT/ SP	7135242A	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
PURBlue EC	PURBlue EC Melters - User's Guide	EN/ DA/ RO / SW/ LI	7156681_02	OP	(317102) or (317107)	Multilingual document, therefore one P/N only
PURBlue RP	Slug Melter PURBlue RP	EN GE IT	7179025D 7156483_05 7169016B	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
VersaPUR S	Adhesive Melters VersaPUR S for Slugs	CH CZ DA DU EN FI FR GE IT JA PL PO SK SP	7560945_03 7179896_03 7580148_03 7192583_03 7179482_03 7580218_03* 7192742_03 7179000_03 7192120_02 7179651_02 7179722_02 7192368_02 7560762_03 7179483_03	MA	(317104) or (317105)	

A-3 - 6

Nordson Engineering Hot Melt Products (sorted by Model)

MC/ (PUR) Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
VersaPUR S	VersaPUR S Adhesive Melters - Safety and User's Guide	CZ DA DU EN FI FR GE IT JA PL PO SK SP	7192951_01 7580149_01 7192956_01 7192871_01 7580219_01* 7192950_01 7192869_01 7192933_01 7192958_01 7192957_01 7192948_01 7560763_01 7192936_01	OP	(317102) or (317107)	
VersaPUR T	Adhesive Melters VersaPUR-T Tank Melter for Reactive Materials	BU DU EN GE IT JA PO RU SP SW	7560755_03 7560978_03 7192212_04 7179011_04 7192592_04 7192934_02 7580196_04* 7192347_03 7192370_03 7192596_03	MA	(317104) or (317105)	* = not yet released

A-3 - 7 **Nordson Engineering Hot Melt Products (sorted by Model)**
MC/ (PUR) Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
VersaPUR T	VersaPUR T Adhesive Melters - Safety and User's Guide	BU DU EN GE IT JA PO RU SP SW	7560756_01 7560979_01 7192870_01 7192868_01 7192932_01 7560072_01 7580197_01* 7192955_01 7192935_01 7192937_01	OP	(317102) or (317107)	* = not yet released
VersaPUR S/T	Adhesive Melters VersaPUR-S, VersaPUR-T - Parts List -	EN	7192178_03	PA	(317104) or (317105)	

A-4 - 1

Nordson Engineering Hot Melt Products (sorted by Model)

MX Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Kit-SVC conv. 7577674 (Motor Controller i550 in MX 3106 and M 4003)	EN GE	7580099_01 7580096_01	IN	(317103) or (317106)	
	Pressure Control for Applicators MX / MC	DU EN FR GE IT JA PO SP	397211A 213020A 397371A 464861A 213087A 7119723A 213110A 7105221A	MA	(317102) or (317107)	
MX 1500	Lotion Applicators MX 1500	EN FR GE IT SP TU	412990B 447750B 412866B 213224B 413039B 7119675B	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
MX 2001/ MX 2001 S/ MX 2001 SD	Hot Melt Material Applicators MX 2001 / MX 2001 S / MX 2001 SD	DU EN FI GE IT SP SW	403233A 403134A 7146251A 403133A 403242A 403249A 405050A	MA	(317103) or (317106)	When ordering, please state Unit Type and Serial Number
MX 3000/ MX 4000	SERIES MX 3000 / MX 4000 Hot Melt Applicators with DC Drives	DU EN FR GE HU IT SP SW	269830 267808 267809 267810 7119546A 269821 269820 269819	OP	(317102) or (317107)	When ordering, please state Unit Type and Serial Number

A-4 - 2

Nordson Engineering Hot Melt Products (sorted by Model)

MX Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
MX 3006	Hot Melt Material Applicators MX 3006	DU EN FI GE PO	317030C 317090C 405003C 269879C 317070C	MA	(317103) or (317106)	When ordering, please state Unit Type and Serial Number
MX 3106/ MX 3106 N MX 3106 IG	Hot Melt Material Applicators MX 3106 / MX 3106 N MX 3106 IG	DU EN FR GE HU IT PO JA SK SP	464957_04 464780_04 464779_04 412915_05 7105475B 458319_04 7560506_04 464987B* 7105458_04 213173_04	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number * available at Nordson K.K.
MX 3400/ MX 4400	Hot Melt Material Applicators MX 3400 / MX 4400	DA DU EN FI FR GE GR IT NO PL PO RU SP SW TU	292850C 290847C 290842C 292851C 290843C 290841C 213836C 290845C 412707C 458269C 403061C 397386C 290846C 290848C 397109C	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number

A-4 - 3

Nordson Engineering Hot Melt Products (sorted by Model)

MX Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
MX 3400/ MX 4400	Hot Melt Material Applicators MX 3400 / MX 4400	CH DA DU EN FI FR GE GR IT JA NO PL PO RU SP SW TU	412695B 409273B 409202B 409203B 409274B 409204B 409205B 213837B 409206B 447744B 409275B 458262B 409491B 213203B 409207B 409208B 397110B	OP	(317102) or (317107)	
MX 4003/ MX 4003 N/ MX 4003 IG	Hot Melt Material Applicator MX 4003 / MX 4003 N / MX 4003 IG	DU EN FI FR GE HU IT PL SK SP SW	447611C 409434C 412614C 412823C 409433C 7156855C 409459C 7105301C 7119810C 458250C 458145C	MA	(317104) or (317105)	
MX 4003 NV	Adhesive Melters Series MX4003NV	DA EN FR GE PL	7169177C 7156020_04 7156015_04 7146334_05 7560625_04	MA	(317104) or (317105)	

A-4 - 4

Nordson Engineering Hot Melt Products (sorted by Model)

MX Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
MX 4003 NV	Adhesive Melter Series MX 4003 NV - Parts List	EN	7146357_04	PA	(317104) or (317105)	
MX 4003 N/ MX 3106 N	Hot Melt Material Applicators MX 4003 N / MX3106 N - Parts List -	EN	7135192_03	PA	(317102) or (317107)	
MX 4460	Hot Melt Material Applicators MX 4460 with Rockwell PLC-5 System	EN GE IT SP	409293B 407475B 409390B 458063B	MA	(317103) or (317106)	
MX 4460	Electrical Cabinet for Melt Material Applicators MX 4460 with Rockwell PLC-5 System	EN GE IT SP	409240B 409222B 409470B 458064B	MA	(317103) or (317106)	
MX 4460	Electrical Cabinet for Hot Melt Material Applicators MX4460 with Rockwell PLC-5 System - <i>Appendix</i>	EN GE IT SP	409242B 409241B 409471B 458065B	MA	(317102) or (317107)	
MX 4460/ MX 44110	Hot Melt Material Applicators MX 4460 / MX 44110	EN	412887A	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
MX 5100/ MX 5200	Hot Melt Material Applicators MX 5100 / MX 5200	DU EN FR GE IT SP SW	213524B 213547B 397948B 213422B 213457B 7119543B 213435B	MA	(317103) or (317106)	

A-4 - 5 **Nordson Engineering Hot Melt Products (sorted by Model)**
MX Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
MX 5100/ MX 5200	Hot Melt Material Applicators MX 5100 / MX 5200 with Control System CS 20	EN FR GE IT SP SW	458353C 213077C 458235C 213333C 458354C 213429C	MA	(317103) or (317106)	When ordering, please state Unit Type and Serial Number
MX 5100/ MX 5200	Hot Melt Material Applicators MX 5100 / MX 5200 with Siemens PLC (Version A: Hot Melt Material Applicators MX 5124 / MX 51110 / 5224 with Siemens PLC)	EN FR GE	458130A 213129B 458067B	MA	(317103) or (317106)	
MX 5100/ MX 5200	Operator Panel OP 27 for Hot Melt Applicators MX 5100 / MX 5200	DU EN FR GE IT	213521A 458099A 213130A 413078A 7105162A	MA	(317102) or (317107)	
MX 5160	Hot Melt Material Applicators MX 5160 with Control System CS 20	EN GE	458301A 458267A	MA	(317103) or (317106)	
MX 51110/ MX 5224	Hot Melt Material Applicators MX 51110 / MX 5224 with Siemens PLC	GE	413067A	MA	(317103) or (317106)	When ordering, please state Unit Type and Serial Number

A-5 - 1

Nordson Engineering Hot Melt Products (sorted by Model)

Auxiliary Systems

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Analog Pressure Display	EN GE	397141A 458447A	MA	(317102) or (317107)	
	Communication Data List for Drum Melters DG 202 with Rockwell PLC	EN	458183A	MA	(317102) or (317107)	
	Communication Data List for Application Units MX 5160 with Rockwell PLC	EN	458185A	MA	(317102) or (317107)	
	Communication Data List for PROFIBUS Interface on Drum Melters BM 20 / BM 200	DA DU EN FR GE PO	458432A 458433A 458434A 458435A 458429A 213183A	MA	(317102) or (317107)	
	Communication Data List for PROFIBUS Interface on Drum Melters DG	DA DU EN FR GE	458273B 413036B 412926B 412944B 412876B	MA	(317102) or (317107)	
	Communication Data List for PROFIBUS Interface on Hot Melt Application Units MX / MC	DA DU EN FI FR GE IT NO PL PO SP SW	458402C 413037C 412925C 447745C 412943C 412845C 458403C 458476C 7119269C 213182C 458420C 458445C	MA	(317102) or (317107)	

A-5 - 2 **Nordson Engineering Hot Melt Products (sorted by Model)**
Auxiliary Systems

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Field Bus Interface PROFIBUS DP for Control System CS 20	DA DU EN FI FR GE IT NO PL PO SP SW	458272B 413038B 412886B 447746B 412940B 412861B 458426B 447623B 7119270B 213181B 458419B 458446B	MA	(317102) or (317107)	
	Field Bus Interface PROFIBUS DP for Siemens PLC	DU EN FR GE IT	213527A 458098A 213134A 458015A 7105161A	MA	(317102) or (317107)	
	Interbus Interface	EN FR GE	458171A 458172A 458167A	MA	(317102) or (317107)	
	PROFIBUS-DP Interface	EN GE	458103B 458072B	PI	(317102) or (317107)	
	Single-Channel Temperature Controller	EN FR GE IT JA SP	409009B 409287B 407452B 409480B 464985B* 409041B	MA	(317102) or (317107)	* = available at Nordson K.K.

A-5 - 3 **Nordson Engineering Hot Melt Products (sorted by Model)**
Auxiliary Systems

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Single-Channel Temperature Controller	DU EN FR GE HU IT JA SK SP SW	269827 267950 269818 267951 7105476A 269828 464981* 7105459A 269817 269829	OP	(317102) or (317107)	* = available at Norson K.K.
BA 9624	Luminous Band Display BA 9624	EN GE IT SW	283019B 283018B 7105057B 7105037B	MA	(317102) or (317107)	
CS 20	Control System CS 20	DA DU EN FI FR GE GR IT NO PO RU SP SW	409186A 409187A 409188A 409332A 409189A 409181A 7119548A 409190A 409479A 409371A 7179611A 409191A 409192A	MA " " " " " OP MA " " " "	(317102) or (317107)	

A-5 - 4

Nordson Engineering Hot Melt Products (sorted by Model) *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
CS 20_ BM 20 / BM 200	Control System CS 20 for Bulk Melters BM 20 / BM 200	CZ DA DU EN FI FR GE IT JA NO PL PO RU SP SW	7105111C 458438C 458408C 458374C 213410C 458399C 458280C 458412C 464865A* 447602C 7105210C 213180C 7135722C 458428C 447606C	MA	(317103) or (317106)	* = available at K.K.
CS 20_DG	Control System CS 20 for Drum Melters DG	DA DU EN FR GE IT NO PO SP SW	458223D 412862D 412811D 412863D 407280D 458082D 458296D 458297D 458062D 458298D	MA	(317103) or (317106)	

A-5 - 5

Nordson Engineering Hot Melt Products (sorted by Model) *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
CS 20_MX/MC	Control System CS 20 for MX / MC Hot Melt Material Applicators	CZ DA DU EN FI FR GE GR HU IT JA NO PL PO RO RU SK SP SW TU	7105251D 458485D 458449D 412960D 213352D 412962D 412908D 213838D 7119806D 458462D 464866D 458495D 213141D 213095D 7135625D 397387D 7119350D 458453D 447625D 397113D	MA	(317103) or (317106)	
DD 77	Pressure Difference Measuring Instrument for Filter Monitoring DD 77	EN GE	315804A 315790A	MA	(317102) or (317107)	
DG 202	Control Device PanelMate for DG 202	EN GE	458231B 458212B	MA	(317102) or (317107)	
E5CN	Single Channel Temperature Controller E5CN	DU EN FI FR GE HU PL SP SW	7119590A 7119283A 7119606A 7119608A 7119053B 7156854B 7119308A 7119589A 7119591A	IN		

A-5 - 6

Nordson Engineering Hot Melt Products (sorted by Model) *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
E 75	Electric Gun Driver E 75	EN GE IT	412834B 409398B 447686B	MA	(317102) or (317107)	
E 75	Electric Gun Driver E 75	EN GE	412859A 412858A	PI	(317102) or (317107)	
E 750	Switching Amplifier E 750	EN FR GE SP	292869A 412966A 292792A 405049A	MA	(317102) or (317107)	
ES 10	Coating Weight Control ES 10	EN GE	412739A 412730A	PI	(317102) or (317107)	
ES 10-I	Coating Weight Control ES 10-I	DU EN FR GE	412893B 412727B 412907B 409294B	MA	(317102) or (317107)	
ES 10-II	Coating Weight Control ES 10-II	DU EN FR GE IT SP SW	458017A 458018A 213034A 413049A 213049A 464949A 458141A	MA	(317102) or (317107)	

A-5 - 7

Nordson Engineering Hot Melt Products (sorted by Model) *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
ES 10-III	Coating Weight Control ES 10-III	DU EN FR GE HU IT PL RU SP SW	213372G 213356J 213375G 213225J 7156460H 213363G 7105869G 397389G 213436G 213365G	MA	(317102) or (317107)	
ES 23-xxx	Pressure Monitoring Device ES 23-xxx	DU EN FI FR GE IT SP SW	213395C 213387C 213441C 213389C 213309C 213398C 213408C 213402C	MA	(317102) or (317107)	
ES 64	Pressure Control Unit ES 64	DU EN FR GE IT PO SP SW	447783C 284111C 317207C 284110C 458000C 213269C 409094C 317160C	MA	(317102) or (317107)	
ES 80 / ES 90 / ES 90 P	Replacement of Central Unit for ES 80 / ES 90 / ES 90 P	EN	213083A	MA	(317102) or (317107)	

A-5 - 8

Nordson Engineering Hot Melt Products (sorted by Model)

Auxiliary Systems

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
ES 80	Pressure Control Unit ES 80	DU EN FR GE IT PO RU SP SW	403268E 284132E 292717E 284150E 458380E 315820B 7179777E 458392E 317019B	MA	(317102) or (317107)	
ES 90	Control Box for ES 90	FR GE	412659A 412615A	MA	(317102) or (317107)	
ES 90	Pattern Control Unit ES 90	DA DU EN FI FR GE GR IT PL SK SP SW	412711E 405059E 284144E 412959E 292718E 284138E 7119983E 407012E 7105417E 7105392E 405095E 317276E	MA	(317103) or (317106)	

A-5 - 9

Nordson Engineering Hot Melt Products (sorted by Model) *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
ES 90 P	Pattern / Pressure Control Unit ES 90 P	DA DU EN FI FR GE IT PO RU SP SW	405208E 317217E 284126E 412888E 292719E 284127E 407138E 292960A 7179778E 405068E 464810E	MA	(317103) or (317106)	
ETR 104 / ETR 108	Temperature Controller ETR 104 / ETR 108	DU EN FR GE IT PO SP	413076A 413058A 413063A 413029A 413075A 213380A 447638A	OP	(317102) or (317107)	
FP13	Temperature Controller	EN FR GE IT LI PO SL SP	7169635_01 7179307_01 7169611_01 7169850_01 7560768_01 7169639_01 7560666_01 7179769_01	MA	(317102) or (317107)	
OptiStroke	Optical Needle Stroke Detection System OptiStroke	EN FR GE IT SP	213958B 7105038B 213748B 7105008B 7105009B	MA	(317102) or (317107)	

A-5 - 10

Nordson Engineering Hot Melt Products (sorted by Model)

Auxiliary Systems

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
OptiStroke	Optical Needle Stroke Detection System OptiStroke Generation II	CH DU EN GE IT JA PL SK SP	7560332_04 7560709_04 7192332_04 7192103_04 7192843_04 7560897_03* 7560054_02 7580146_04 7560331_04	MA	(317102) or (317107)	* available at Nordson K.K.
OptiStroke	Adapter Bushing for OptiStroke-Sensors	EN/ GE	7105403A	IN	(317102) or (317107)	<i>Bilingual</i> document, therefore one P/N only
PC 6/ PC 9/ PC 12	Temperature Controllers PC 6 / PC 9 / PC 12	DA DU EN FI FR GE IT NO PO SP SW	290921A 290922A 290938A 290923A 290940A 290939A 290924A 290925A 290926A 290920A 290927A	IN	(317102) or (317107)	

A-5 - 11

Nordson Engineering Hot Melt Products (sorted by Model)

Auxiliary Systems

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
PC 6/ PC 9/ PC 12	Temperature Controllers PC 6 / PC 9 / PC 12	CH CZ DA DU EN FI FR GE HU IT NO PL PO RU SK SP SW	412917B 464928B 447666B 317051B 317050B 403069B 317052B 317032B 7146613B 317053B 317054B 7146010B 317055B 7135996B 7135453B 317056B 317057B	MA	(317102) or (317107)	
TR 35... / TR 36... / TR 36...Z	Temperature Control Boxes TR 35 ... / TR 36 ... / TR 36 ... Z	DU EN FR GE	403232B 213504B 464917B 403144B	MA	(317102) or (317107)	
TR 37... / TR 38... / TR 38...Z	Temperature Control Boxes TR 37 ... / TR 38 ... / TR 38 ... Z	EN FI GE	213505B 7146252B 403146B	MA	(317102) or (317107)	
	Bead Gap Detector II Item Nos. 1160.0443 1160.0449	EN FR GE SW	317199A 403247A 317120A 315786A	MA	(317102) or (317107)	

A-5 - 12

Nordson Engineering Hot Melt Products (sorted by Model) *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Digital Display with Limit Monitoring	CZ DU EN FR GE IT SP SW	464926C 464744C 407455C 409413C 407454C 409004C 458417C 413073C	MA	(317102) or (317107)	
	Digital Display with Limit Monitoring (Type 2300)	CZ DU EN FI FR GE IT PL SP SW	7105113C 213396C 213388C 213442C 213390C 213308C 213397C 7119265C 213407C 213401C	MA	(317102) or (317107)	
	Feed System for Hot Melt Material Applicators FILLMASTER I	DU EN FR GE IT PO SP SW	458328B 458264B 458316B 413083B 458329B 464939B 458330B 458467B	MA	(317102) or (317107)	

A-6 - 1

Nordson Engineering Hot Melt Products (sorted by Model) Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Field Bus on Nordson Applicators	EN FR GE IT PL	7169718_08 7560479_08 7169180_08 7169515_08 7179215_08	MA	(317102) or (317107)	
	Inside Coating Nozzle	EN FR GE	213759C 412708C 412617D	MA	(317102) or (317107)	
	Material Guide for Applicators (Titel version B: Material Guide for Hot Melt Application Head PF...V)	DU EN FI FR GE	397927B 397964B 397980B 7560659_03 397888_03	IN	(317102) or (317107)	
	Outside Coating Nozzle	EN GE SP	397481B 458302B 458383A	MA	(317102) or (317107)	
	Recirculation Control Module RV45, CC, MG	EN GE	7135366A 7135337A	MA	(317101)	
	Retrofitting Kit Spinner Roll	EN/FR/ GE	409427A	MA	(317102) or (317107)	Multilingual document, therefore one P/N only
AD 24	Hot Melt Application Head AD 24	EN GE	412762A 405111A	MA	(317102) or (317107)	
AG 900	Control Modules Series AG 900	CZ EN GE	7105114B 397773B 458114B	MA	(317102) or (317107)	
AltaSlot-c	Hot Melt Adhesive Applicator AltaSlot-c	EN GE	7146313_03 7146404_03	MA	(317102) or (317107)	

A-6 - 2

Nordson Engineering Hot Melt Products (sorted by Model) Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
AltaSlot-i	Hot Melt Adhesive Applicator AltaSlot-i	EN GE	7119466_04 7119456_04	MA	(317102) or (317107)	
AN240	AN240 Applicators	EN GE	7192572_02 7560691_02	MA	(317102) or (317107)	
BC	Trolley for Application Heads BC	FR GE	458209A 458196A	MA	(317102) or (317107)	
BC 31	Surface Coating Applicator BC 31 (Title version H: Surface Coating Head BC 31)	CH DU EN FR GE IT JA PO SP	7560882_09 447704G 317096H 405005H 317080_09 317110G 464853H 7119273G 317200G	MA	(317102) or (317107)	
BC 35	Surface Coating Head BC 35	DU EN FR GE IT JA	464923F 458451F 464934F 317098F 7135176F 464854D*	MA	(317102) or (317107)	* available at Nordson K.K.
BC 40	Surface Coating Application Head BC 40	EN FR GE PO SP	317015C 458142B 315879C 7105106B 7135819B	MA	(317102) or (317107)	
BC 40-1620	Surface Application Head BC 40-1620	EN GE	7156122A 7156091A	MA	(317102) or (317107)	

A-6 - 3

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
BC 60	Surface Coating Head BC 60	EN FR GE IT SP	412827E 7119987E 409387E 7105181E 409140C	MA	(317102) or (317107)	
BC 62	Surface Coating Head BC 62	CH DU EN FR GE IT PO RU SP TU	7119922F 317297F 403044F 403040F 317209F 409289F 7105130F 7156510F 7119550F 7560657F	MA	(317102) or (317107)	
BC 70	Surface Coating Head BC 70	FR GE JA	397190G 447604G 7119627D*	MA	(317102) or (317107)	* available at Nordson K.K.
BC 70	Surface Coating Head BC 70 with Gear Pumps	GE	7105789A	MA	(317102) or (317107)	
CA 410/ 420	Cable Applicators	EN FR GE GR PL SP SW	7560254_01 7179883_01 7169990_01 7560815_01 7560624_01 7560509_01 7192989_01	MA	(317102) or (317107)	
CA 410/ 420	Cable Applicators - Parts List -	EN	7179185_01	PA	(317102) or (317107)	

A-6 - 4 **Nordson Engineering Hot Melt Products (sorted by Model)**
Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
CC ../ ..C	Hot Melt Material Application Heads for continuous surface coating Control Coat CC ../ ..C	DU EN GE IT SP	409213D 315788D 292963D 213453D 317097D	MA	(317102) or (317107)	
CC ../ ..I	Hot Melt Material Application Heads for intermittent surface coating Control Coat CC ../ ..I	DA DU EN FR GE IT SP SW	409142D 403031D 292930D 405206D 292878D 213310D 317109D 403054D	MA	(317102) or (317107)	
CC ../ ..I GP	Hot Melt Material Application Heads with gear pump for intermittent surface coating Control Coat CC ../ ..I GP	EN GE	292856E 292861E	MA	(317102) or (317107)	
CC	Hot Melt Applicators Control Coat CCQE	DU EN FR GE IT PL SK SL SP SW TU	7105513_03 397986_04 7135446_04 397836_04 7105014_04 7169616_04 7192986_03 7560866_04 7560088_03 397985_03 7192924_04	MA	(317102) or (317107)	
CC	Hot Melt Applicator Control Coat CC MF	EN GE IT	7156197_02 7156183_02 7560077_02	MA	(317102) or (317107)	

A-6 - 5

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
CC 10	Hot Melt Application Head CC 10	EN GE	458131B 458093B	MA	(317102) or (317107)	
CC 18 / 322 I	Hot Melt Application Head CC 18 / 322 I	EN GE	458342B 458326B	MA	(317102) or (317107)	
CC 201	Hot Melt Application Head CC 201	FR GE	213135B 458373B	MA	(317102) or (317107)	
CF 04	Application Head CF 04	EN GE	458168A 458126A	MA	(317102) or (317107)	
CF 04	Retrofitting Kit Application Head CF 04	EN GE	458422A 458398A	MA	(317102) or (317107)	
CF 04	Retrofitting Kit Application Head CF 04	EN GE	447620A 458498A	MA	(317102) or (317107)	
CF 200	Hot Melt Application Heads CF 200	DA DU EN FI FR GE IT PL PO SP SW	213188A 213105A 213125A 213359A 213108A 213014A 213097A 213434A 213167A 213197A 213322A	OP	(317102) or (317107)	
CF 200	Hot Melt Material Application Head CF 200	DA EN GE	7105996C 447653B 458236C	MA	(317102) or (317107)	

A-6 - 6

Nordson Engineering Hot Melt Products (sorted by Model) Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
CF 216	Hot Melt Application Head CF 216	EN GE	213213A 213186A	MA	(317102) or (317107)	
CH26	Application Head Precision Holder CH26	EN FR GE IT	317034A 317131A 317033A 403033A	MA	(317102) or (317107)	
COBRA	Application Nozzle COBRA	EN FR GE IT SP SW	464995A 464994A 464919A 464996A 464992A 464993A	MA	(317102) or (317107)	
CONTOUR COAT	Contour Coat Applicator	EN GE	7105874B 7105345B	MA	(317102) or (317107)	
CURTAIN COAT BC 70	Curtain Coat BC 70 Surface Coating Applicator (Title version H: Application Head Curtain Coat BC 70)	EN GE IT JA PL	7135511_09 7119301_09 7135179H 7119628A* 7146513_09	MA	(317102) or (317107)	* available at Nordson K.K.
DA 34	Application Head Series DA 34	EN GE	403030B 317282B	MA	(317102) or (317107)	
DN 50	Metering Application Head DN 50	EN FR GE SP SW	413054B 407494B 403003B 403052B 413051B	MA	(317102) or (317107)	

A-6 - 7

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
DPW	Application Heads DPW, DPW-J	CZ DU EN FR GE IT JA PL PO SP SW	7179897J 7119613I 7105670J 7156799J 7105661J 7119417I 7135450F* 7146415J 7119646G 7119071J 7135780I	MA	(317102) or (317107)	* available at Nordson K.K.
DPW-HC	Application Heads DPW-HC	EN GE IT SP SW	7119754C 7119704C 7135143C 7119748B 7156321C	MA	(317102) or (317107)	
e-slot	e-slot Applicator	GE IT	7146358A0 7146398A0	MA	(317102) or (317107)	Preliminary Version!
Easy PW	Application Heads Easy PW ... with Swivel Device	CZ EN FR GE IT PL SW	7146540E 7105109E 7156910E 397532E 7179785E 7119261E 7156626E	MA	(317102) or (317107)	
EB	Hot Melt Application Heads Series EB	EN GE IT NO SP SW	409496E 409401E 409497E 412624E 464976E 412623E	MA	(317102) or (317107)	

A-6 - 8

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
EB Flex	Hot Melt Applicators EB Flex (Title - version_05: EB60 Flex)	DU EN FI FR GE IT JA PL PO SP	7560040_05 7179567_06 7580161_06 7560041_03 7179534_06 7179566_03 7560766_04* 7179587_03 7560516_05 7192845_06	MA	(317102) or (317107)	* available at Nordson K.K.
EB Flex	Hot Melt Applicators EB Flex- Parts List -	EN	7192555_04	PA	(317102) or (317107)	
EB Flex	EB Flex OEM Integration Handout	EN	7560692_01	IN	(317102) or (317107)	Created by Application Development, Andrea Poggi
EB ... V EB ... V-M	Hot Melt Application Heads EB ... V EB ... V-M	DA EN FI FR GE HU IT JA NO PL RO RU SP SW	458243I 458009I 458244I 447671I 413074I 7192546I 458245I 464969F 458246I 7560537I 7169225I 7135317I 447724I 458247I	MA	(317102) or (317107)	
EF60 V	Applicator with Diamant Nozzle	EN GE	7179900_01 7179811_01	MA	(317102) or (317107)	

A-6 - 9

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
EF60 V	Applicator with Diamant Nozzle - Parts List -	EN	7179656_01	PA	(317102) or (317107)	
EP 10 / EP 10 FL / EP 10 D / EP 10D-FL	Suction Stem Control Module EP 10 / EP 10 FL EP 10 D / EP 10 D-FL	BU CZ DA DU EN FI FR GE HU IT NO PL PO SP SW TU	7135432D 464741D 464747D 412767D 412768D 464841D 458012D 412747D 7105615D 412769D 464761D 7156350D 464890D 458010D 412905D 397127B	MA	(317102) or (317107)	
EP 10	Repair Kit Control Module EP 10	EN GE	447730_06 447729_06	MA	(317102) or (317107)	
EP 11	Application Head	EN GE	7156157A 7156151A	MA	(317102) or (317107)	Only available for special EP 11 P/N 7153753

A-6 - 10

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
EP 11/ EP 11 N/ EP 12 V/ EP 12 L/ EP 12 RV	Hot Melt Applicators EP 11 / EP 11 N EP 12 V / EP 12 L / EP 12 RV	BU CZ DA DU EN FI FR GE HU IT NO RU PL PO SP SW TU	7135431G 7560289G 464762G 403265G 317091G 213076G 403082G 317092G 7105613G 407470G 464796G 7146738G 7156349G 405051G 403251G 447755G 397126G	MA	(317102) or (317107)	
EP 11 N	Hot Melt Application Heads EP 11 N	GE	7105599A	MA	(317102) or (317107)	
EP 15	Lotion Application Head EP 15	CZ EN FR GE IT SK SP	464740A 412935A 458011A 412867A 213007A 7105624A 413040A	MA	(317102) or (317107)	
EP 23/ EP 23T	Electropneumatic Hot Melt Application Heads EP 23 / EP 23T	GE	405018A	MA	(317102) or (317107)	

A-6 - 11

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
EP 25/ EP 25 S/ EP 25 SD	Electropneumatic Hot Melt Application Heads EP 25 / EP 25 S / EP 25 SD	CZ DA DU EN FI FR GE GR HU IT JA PL PO SK SL SP SW	7105253A 409141A 409174A 409017A 409069A 409122A 405019A 7105439A 7105485A 409134A 213124A* 7156365A 464782A 7105467A 7560665A 409217A 397037A	MA	(317102) or (317107)	* available at Nordson K.K.
EP 26 SD	Electropneumatic Hot Melt Application Head EP 26 SD	DU EN FR GE IT PL SP SW	213466A 409097A 409098A 405020A 409099A 7119260A 213285A 7105556A	MA	(317102) or (317107)	
EP 26-8 SD	Electropneumatic Hot Melt Application Head EP 26-8 SD	GE IT	7135166A 7135177A	MA	(317102) or (317107)	
EP 30	Hot Melt Application Head EP 30	EN GE IT	397191B 397140B 397219B	MA	(317102) or (317107)	

A-6 - 12

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
EP 34/ EP 34 S/ EP 34 SD	Electropneumatic Hot Melt Application Heads EP 34 / EP 34 S / EP 34 SD	DU EN FI FR GE IT PL RU SP SW	213212A 409090A 7146327A 409091A 405021A 409092A 7156143A 7580166A 7146085A 7179316A	MA	(317102) or (317107)	
EP 45	Electropneumatic Hot Melt Application Head EP 45	CZ DU EN FI FR GE GR HU IT JA PL PO RU SP TU	7119713B 409013B 403228C 397523B 409121C 315705C 213840B 7105411B 315808C 464868B* 458270B 315706A 7105351B 213386C 397124B	MA	(317102) or (317107)	* available at Nordson K.K.
EP 45	Control Module EP 45	DU EN FR GE IT SP	7105704A 7105703A 7105705A 7105702A 7105706A 7105707A	MA	(317102) or (317107)	
EP 45	Feed Valve EP 45	DU FR GE	409170A 409185A 409105A	MA	(317102) or (317107)	

A-6 - 13

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
EP 48-BoD	Hot Melt Applicators Series EP 48-BoD	EN FR GE	7169856_02 7169862_02 7169838_04	MA	(317102) or (317107)	
EP 48-BoD	Hot Melt Applicators Series EP 48-BoD - Parts List -	EN	7179006_03	PA	(317102) or (317107)	
EP 48 Pro	Hot Melt Applicators Series EP48 Pro	EN FR GE	7560606_02 7560773_02 7560542_02	MA	(317102) or (317107)	
EP 48 Pro	Hot Melt Applicators Series EP48 Pro - Parts List -	EN	7560880_01	PA	(317102) or (317107)	
EP 48 Pro	Instructions for EP 48 Pro Transport Frame (P/N 7561630 „EP48 Pro-angled“, P/N 7561631 „EP48-Pro-straight“)	EN GE	7560871_02 7560827_02	IN	(317102) or (317107)	
EP 48-V	Hot Melt Applicators Series EP 48-V (UL Models)	CZ DU EN FR GE JA PO	7156476_06 7156402_06 7156473_08 7156569_08 7156348_08 7169423D* 7560804_08	MA	(317102) or (317107)	* available at Nordson K.K.
EP 48-V	Hot Melt Application Head EP 48-V (UL Design) - Parts List -	EN JA	7156338_07 7169424C*	PA	(317102) or (317107)	* available at Nordson K.K.

A-6 - 14

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
EP 48-V	Trolleys for EP 48-V/ EP48 Pro (Title Version G: Trolleys for EP 48-V)	BU DU EN FR GE HU IT PL SP	7135435E 7179231G 7119707G 7135152_08 7119703_08 7156649E 7156202G 7179802G 7135045G	IN	(317102) or (317107)	
EP 48-V EP 48-VL	Hot Melt Application Head EP 48-V/ EP 48-VL	BU CZ DA DU EN FI FR GE IT JA NO PL PO SK SP	7135429M 7135525M 213399M 213362M 458361M 7135150M 213364M 407307M 213373M 464869I* 213355M 213254M 213109M 7146165M 213315M	MA	(317102) or (317107)	* available at Nordson K.K.
EP 48-VM	Hot Melt Application Head EP 48-VM	DU EN GE	7156806C 7146651D 7146083D	MA	(317102) or (317107)	
EP 48-VSB	Hot Melt Application Head EP 48-VSB	EN FR GE IT JA SP	7135899B 7135898B 7135820B 7146535B 7146681B* 7146732B	MA	(317102) or (317107)	* available at Nordson K.K.

A-6 - 15

Nordson Engineering Hot Melt Products (sorted by Model) Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
EP 48-VSB	Extension Side Gluing for EP 48-VSB (P/N 7133305 for EP48-VSB, P/N 7173132 for EP48-BoD)	GE	7156055_03	IN	(317102) or (317107)	Bilingual document, therefore one P/N only
EP 51	Electropneumatic Hot Melt Application Head EP 51	DA DU EN FR GE IT JA PO SP SW	7105709B 409283B 409282B 409284B 315703B 315753B 464870B* 315704B 409285B 409286B	MA	(317102) or (317107)	* available at Nordson K.K.
EP 51	Electro-pneumatic Unheated Coating Head	EN GE SP	713555A 7135522A 7135620A	MA	(317102) or (317107)	
EP51-01	Application Heads EP51-01 for Edge Banding	GE	397823B	MA	(317102) or (317107)	
EP 51 PW	Electropneumatic Hot Melt Application Head EP 51 PW	EN FR GE SP SW	412734A 397428A 412712A 412743A 413043A	MA	(317102) or (317107)	
EP 52	Hot Melt Application Head Series EP 52	EN FR GE IT JA SP SW	403021B 407468B 317212B 397255B 464871A* 464783B 397264B	MA	(317102) or (317107)	* available at Nordson K.K.

A-6 - 16

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
EP 310 / EP 310P	Small Metering Unit for PUR Cartridges EP 310 / EP 310 P	EN GE SP	409042A 407453A 409065A	MA	(317102) or (317107)	
GMG	Volume Metering Head GMG	CH CZ DA DU EN FI FR GE IT NO PL PO RU SK SL SP SW	7560946J 464929J 7156422H 7146227J 405103J 213376J 405027J 405025J 407043J 7146534H 7119267J 7119420J 7179543J 7119351E 7135027E 458414J 413047E	MA	(317102) or (317107)	Former product title VDK
GMG	Electrical Cabinet for Volume Metering Head GMG	CZ EN FI FR GE IT PL SP SW	7105112F 405065F 213377F 405028F 405026F 407499F 7119268F 458415F 413048F	MA	(317102) or (317107)	Former product title VDK

A-6 - 17

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
GMG	Electrical Cabinet for Volume Metering Head GMG - Model with PLC -	CZ EN FI FR GE PL PO SK SL	7119289D 7105929D 7135194D 7119192D 7105669D 7135257D 7119421B 7119352B 7135028C	MA	(317102) or (317107)	
GMG	Electrical Cabinet for Volume Metering Head GMG - Model with Volume Display -	CZ EN FR GE	7135648F 7135818F 7135605E 7135147F	MA	(317102) or (317107)	
GMG	Electrical Cabinet for Volume Metering Head GMG - Model April 2008 and later -	CZ DA DU EN FI FR GE NO PL PO SP	7146282E 7156423D 7146397E 7146393D 7146607D 7146904E 7146204E 7146537D 7156789E 7156557E 7146267D	MA	(317102) or (317107)	

A-6 - 18

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
GMS	Electrical Cabinet GMS - Generation II for Volume Metering Head GMG	CH CZ DU EN FI FR GE IT PL PO RU SP	7560947_05 7179344_05 7192426_05 7179354_03 7192787_03 7179368_05 7179325_05 7560372_04 7192676_03 7560604_03 7179544_03 7560371_05	MA	(317102) or (317107)	
H 200	Application Modules H 200	GE	213385A	IN	(317102) or (317107)	
LabelCoat	LabelCoat Slot Gun	EN FR GE IT	7105502B 7135061B 7105449B 7135476B	MA	(317102) or (317107)	
LabelCoat MB II	LabelCoat MB II Horizontal Slot Applicator	GE	7560661_01	MA	(317102) or (317107)	
LabelCoat MB II	LabelCoat MB II Horizontal Slot Applicator - Parts List -	GE	7560662_01	PA	(317102) or (317107)	
LPW	Application Heads LPW	GE	7119868A_01	MA	(317102) or (317107)	Prerliminary version !
MG 11	Hot Melt Application Head MG 11	DU EN GE IT SW	412784B 412785B 412715B 412786B 412901B	MA	(317102) or (317107)	

A-6 - 19

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
MG 11	Electrical Cabinet	DU EN GE IT SW	412736B 412735B 412716B 412737B 412902B	MA	(317102) or (317107)	
MG 95	Applicator	FR GE	7192573_01 7192493_01	MA	(317102) or (317107)	
MMG	Melt Metering Gun MMG	GE	7135153D	MA	(317102) or (317107)	
MP 16 / MP 16S / MP 16 SD	Assembly Handgun MP 16 / MP 16 S / MP 16 SD	EN FR GE	409143A 409173A 405014A	MA	(317102) or (317107)	
MP 17 / MP 17 S/ MP 17 SD	Assembly Handgun MP 17 / MP 17 S / MP 17 SD	EN FR GE	412608A 7119339A 405015A	MA	(317102) or (317107)	
MP 18 / MP 18S / MP 18 SD	Assembly Handgun MP 18 / MP 18 S / MP 18 SD	GE	405016A	MA	(317102) or (317107)	
MP 300, MP 300 S, MP 300 P, MP 350, MP 350 S	Assembly Handguns MP 300, MP 300 S, MP 300 P MP 350, MP 350 S	EN FR GE SP	213151C 464918C 405017C 7105695C	MA	(317102) or (317107)	
PatternCoat	Applicators Series PatternCoat (PCT)	DU EN FR GE IT PL SP	7560302_09 7135308_08 7135590_08 7135247_09 7560967_09 7192361_08 7560708_09	MA	(317102) or (317107)	

A-6 - 20

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
PF...V PV...V-HT	Hot Melt Application Head PF...V/ PF...V-HT	DU EN FI GE IT JA	397926D 397949_05 397979D 397889_05 7135324D 7119307A*	MA	(317102) or (317107)	
PN 18	Electropneumatic Hot Melt Application Heads PN 18	EN FR GE	213558A no P/N 213541A	MA	(317102) or (317107)	
PU...	Application Heads PU...	EN GE PL RU	7135888A 7135460A 7135946A 7146646A	MA	(317102) or (317107)	
PW ...	Hot Melt Application Head Series PW...	CZ DA DU EN FI FR GE IT PL RU SP SW	7156142I 458437I 458016I 458013I 458022I 213008I 412882I 464909I 397231I 397388I 464811I 458014I	MA	(317103) or (317106)	
PW ...	Retrofitting Right/Left of Hot Melt Application Heads PW 200 PW 350 PW 500 PW 800	EN GE	213048A 213041A	MA	(317102) or (317107)	

A-6 - 21

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
PWII-...	PWII... Applicators	CH EN FR GE HU IT LI PL RO RU SP	7179319_10 7135328_10 7135704_10 7119937_10 7156459B 7135788B 7560769_10 7135747B 7169224C 7135677B 7135676_10	MA	(317102) or (317107)	
PWII-...	PWII... Applicators P/N 7407037, 7407038 - Parts List -	EN	7179725_01	PA	(317102) or (317107)	
PWII...HC	PWII...HC Applicator P/N 7165538	EN GE	7169267A 7169266A	MA	(317102) or (317107)	
PWIII	PWIII Applicator P/N 7161049	GE	7156456A	MA	(317102) or (317107)	
PWIII	PWIII Applicator - Model with Adjustable Application Width	DA EN GE IT	7169356C 7169355C 7156701_04 7169514C	MA	(317102) or (317107)	
PWIII	PWIII Applicator - Model with Shim Plate (P/N 7165227)	GE SW	7169127_03 7169171_03	MA	(317102) or (317107)	
PWIII	PWIII Applicator - Parts List -	EN	7156755A	PA	(317102) or (317107)	

A-6 - 22

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
PW-S	PW-S Applicators	EN GE GR PO	7169663A1 7169245_03 7169262A0 7169403A1	MA	(317102) or (317107)	
PW-S	PW-S Parts List	EN	7169987_01	PA	(317102) or (317107)	
RA 80	Coating Wheel RA 80	GE	213378A	MA	(317102) or (317107)	
RA 80	Coating Whee RA 80 Double-sided Bearing	DU EN GE IT PL SW	403266C 403108C 315826C 405041C 7119870C 409079C	MA	(317102) or (317107)	
RA 80	Coating Wheel RA 80 Single-sided Bearing	CZ DA DU EN FR GE SW	7135156C 7105506C 407461C 405054C 405105C 317165C 405006C	MA	(317102) or (317107)	
RA 80	Coating Wheel RA 80 Single-sided Bearing With Spinner Rotating Bar	EN GE IT SP	409281C 409234C 7135154C 447708C	MA	(317102) or (317107)	
RA 80	RA 80 Wheel Applicator Station with Additional Tank for Bag Application	EN GE	407042A 407041A	MA	(317102) or (317107)	
RA 80	Maintenance of Wheel Applicator RA 80	GE SW	409199A 409201A	OP	(317102) or (317107)	

A-6 - 23

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
ROC	Applicator ROC	GE	7179980_01	MA	(317102) or (317107)	
SB60 - BoD	Hot Melt Applicators SB60 - BoD	EN FR GE JA NO SP SW	7179925_05 7179982_05 7179789_05 7192216_05 7192232_05 7192205_05 7192206_05	MA	(317102) or (317107)	
SB60 - BoD	Hot Melt Applicators SB 60 - BoD - Parts List -	EN	7179970_06	PA	(317102) or (317107)	
SN 30	Screen Printer Application Head SN 30	EN GE	412978A 412932A	MA	(317102) or (317107)	

A-6 - 24

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
SPEED-COAT	Hot Melt Applicators SPEED-COAT	CZ DA DU EN FR GE GR HU IT JA NO PL PO RU SK SL SP SW TU	7169875_07 7560510_07 397351_07 213980_07 7105287_07 213470_07 7146142_06 7560797_07 7105074_07 7156733_05* 7560388_07 7105416_07 7560397_07 7135948_07 7105391_07 7146515C 213978_07 7135227_07 7192922_07	MA	(317102) or (317107)	* available at Nordson K.K.
SPEED-COAT	Suction Stem Control Module Speed-Coat	DA DU EN FI FR GE IT JA NO PL PO SP SW	213689_05 213680D 213686_05 213896A 213685D 213482_05 213693_05 7179147_05* 213667D 7169617D 213661D 213674D 213699D	MA	(317102) or (317107)	* available at Nordson K.K.
SPEED-COAT	Speed-Coat - Parts List -	EN JA	7156778_03 7179148_02*	PA	(317102) or (317107)	* available at Nordson K.K.

A-6 - 25

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
SPEED-COAT	Installation Notes Speed-Coat Solenoid Valves	EN/ FR/ GE/ IT/ SP	397072_03	IN	(317102) or (317107)	Multilingual document, therefore one P/N only
TRANSFER DISK	Transfer Disk	EN GE SP	7119617D 7119123D 7135134C	IN	(317102) or (317107)	
TRANSFER DISK	System Description Application System with Transfer Disk	EN GE SP	7119616F 7119124F 7135133F	MA	(317102) or (317107)	
TRIO	Trio Hot Melt Applicators	DA DU EN FR GE IT PL PO RU SK SP	7560412_03 7560846_02 7560027_03 7560809_03 7192645_03 7192969_03 7560963_03 7560823_03 7560676_01 7560874_03 7560089_03	MA	(317102) or (317107)	

A-6 - 26

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
TRUECOAT	Hot Melt Applicators TrueCoat	CZ DA DU EN FI FR GE GR IT JA NO PL PO RU SK SL SP TU	7560291_10 7156826_10 7135075_10 7119681_10 7146799_10 7119680_10 7105415_10 7146143_10 7119688_10 7135031A* 7192249_10 7146903_10 7156376_10 7135949_10 7135501_10 7146516_10 7119682_10 7192923_10	MA	(317102) or (317107)	* available at Nordson K.K.
TRUECOAT	Hot Melt Applicators TrueCoat HP	CH EN FI GE PO SP	7560898_02 7179962_02 7580045_02 7179781_02 7192891_02 7192285_02	MA	(317102) or (317107)	
TRUECOAT	Hot Melt Applicators TrueCoat HP with Adjustable Application Width	EN GE IT PL PO	7169655_05 7169607_05 7179195_05 7179213_05 7192830_05	MA	(317102) or (317107)	
TRUECOAT	Hot Melt Adhesive Applicators TrueCoat - Parts List -	EN	7146948_08	MA	(317102) or (317107)	

A-6 - 27

Nordson Engineering Hot Melt Products (sorted by Model) Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
TRUECOAT	Hot Melt Applicator TrueCoat (7144549, 7153564)	EN FR GE IT	7146787A 7146766B 7146762B 7146905B	MA	(317102) or (317107)	
TRUECOAT	Hot Melt Applicator TrueCoat with Throttle Screw	EN GE	7156487B 7156373B	MA	(317102) or (317107)	
TRUECOAT	Applicators in the Series TC-FS Applicators	GE	7169281_02	MA	(317102) or (317107)	
TRUECOAT	Applicators in the Series TC-FS - Parts List -	EN	7179219_01	PA	(317102) or (317107)	Preliminary Version!
TRUECOAT	Applicators in the Series TC-FS Generation II with Motor-driven Application Width Adjustment and Grammage Control (Option) (Title version_02+03: Applicators in the Series TC-FS Generation II with Grammage Control (Option) (Title version_01: Models RET, EVA/PO, PUR)	DU EN FR GE IT SP SW	7179881_01 7179884_07 7560478_07 7179813_07 7179885_07 7560242_07 7192861_03	MA	(317102) or (317107)	
TRUECOAT	Applicators in the Series TC-FS Generation II with Grammage Control (Option) - Parts List -	EN	7192556_04	PA	(317102) or (317107)	
TRUECOAT	Applicators in the Series TC-FS Generation II with Hand Wheel	DU EN FR GE IT PL SP	7192875_01 7192854_03 7560990_03 7192851_03 7560988_03 7560008_01 7560989_03	MA	(317102) or (317107)	

A-6 - 28

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
TRUECOAT	Applicators in the Series TC-FS Generation II with Hand Wheel - Parts List -	EN	7560667_01	PA	(317102) or (317107)	
TRUECOAT	Truecoat FS-PW OEM Integration Handout	EN	7580160_01	IN	(317102) or (317107)	Created by Application Development, Ralf Dittmann
TRUFLOW	TruFlow Applikator UTA... Flow Divider and Flow Meter (Title version A: TruFlow Applikator UTA...)	CZ DA DU EN FR GE IT NO PL PO RU SK SP SW TU	7146854_02 7156643_02 7169106_02 7146808_02 7169545_02 7146417_02 7169377_02 7560512_02 7156499_02 7179697_02 7560674_02 7179350_02 7169133_02 7560930_02 7560259_02	MA	(317102) or (317107)	
TRUFLOW	TruFlow Flow Detection System	DA DU EN FR GE IT NO PO RU SK SP SW	7560273_02 7560336_02 7179720_02 7192260_02 7179933_02 7192290_02 7560513_02 7580169_02 7560899_02 7192987_02 7192104_02 7560931_02	MA	(317102) or (317107)	

A-6 - 29

Nordson Engineering Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
TRUFLOW	Electrical Cabinet for TruFlow Application System	CZ EN GE	7146855A_1 7146809A_1 7146416A_1	MA	(317102) or (317107)	
TRUFLOW	Electrical Cabinet for TruFlow Application System Generation II	CZ DA DU EN FR GE IT PL PO SK SP	7169350_03 7156642_03 7169076_03 7156170_03 7169546_03 7156096_03 7179234_03 7156500_03 7179698_03 7192130_03 7169882_03	MA	(317102) or (317107)	
UM	Universal Application Head UME... and UMU...	EN FR GE RU	7105687A 7119381A 7105558A 7192814A	MA	(317102) or (317107)	
VDK	VDK-MAXI Applicator	GE PL	7560229_01 7560237_01	MA	(317102) or (317107)	
VDK	VDK-MIDI Applicator	EN FI GE IT	7179780_01 7192333_01 7179773_01 7560411_01	MA	(317102) or (317107)	
VDK	VDK-MIDI Applicator (P/N 7185070)	CH EN	7179496_01 7179506_01	MA	(317102) or (317107)	
VDK	VDK-MIDI Volume Metering Head (P/N 7552265)	JA	7169614_01	MA	(317102) or (317107)	

A-7 - 1

Nordson Engineering Hot Melt Products (sorted by Model) Systems - Automotive

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Heated Pro-Meter IV System	CH EN	412919A 413041A	MA	(317102) or (317107)	
	Heated Pro-Meter IV System - System Description	EN	412849A	MA	(317102) or (317107)	
	FlowCoat Pressure Controller	GE	213090E	IN	(317102) or (317107)	
Pro-Flo	Pro-Flo Controller	DU FR GE IT SP SW	292873A 292875A 292872A 292877A 292874A 292896A	OP	(317102) or (317107)	EDB 25-11
Pro-Flo	Pro-Flo Controller (European Version)	DU FR GE SP SW	315859A 315830A 315831A 315861A 315833A	MA	(317102) or (317107)	EDB 25-13
Pro-Flo	Pro-Flo System	DU	292870	IN	(317102) or (317107)	
Pro-Flo	Pro-Flo System	EN FR GE IT SP SW	269847 269848 269849 269850 269852 269851	OP	(317102) or (317107)	
Pro-Flo	Pro-Flo System Dispensing Gun	FR SP	315860B 403062C	MA	(317102) or (317107)	EDB 26-9

A-7 - 2 **Nordson Engineering Hot Melt Products (sorted by Model)**
Systems - Bookbinding

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Instructions for Kit-EP48-V light barrier P/N 7147780	EN/ GE	7156332B	IN	(317102) or (317107)	Bilingual document, therefore one P/N only
	Spine Gluing with Application Head EP 48-V and PUR Hot Melt Adhesive	BU CZ DA DU EN FI FR GE IT JA NO PL PO SK SP	7135428C 7146013C 213873B 213813B 213574C 7135151C 213787B 213671C 213801B 397987C* 213898B 397213C 213811C 7135408C 213825C	IN	(317102) or (317107)	* available at Nordson K.K.
	Bookbinding System with Bulk Melter BM 20 / BM 200 - Initial Startup -	EN GE JA SP	213416B 213337B 397988A* 7105562B	IN	(317102) or (317107)	* available at Nordson K.K.
	Bookbinding System with Bulk Melter BM 20 / BM200 - System Description -	EN GE JA SP	213417B 213338B 397989B* 7105563B	OP	(317102) or (317107)	* available at Nordson K.K.

A-7 - 3 **Nordson Engineering Hot Melt Products (sorted by Model)**
Systems - Bookbinding

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Bookbinding System with Bulk Melter DuraPail / DuraDrum - Initial Startup -	BU CZ DU EN ES FI FR GE HU IT NO PL PO SK SP	7135424B 7146011D 7146111D 7119592D 7146244D 7135053D 7119988D 7119824D 7146216D 7119985D 7156607D 7135345D 7146400D 7146166D 7119968D	IN	(317102) or (317107)	
	Book Spine Gluing with Bulk Melter DuraPail / DuraDrum - System Description -	BU CZ DU EN ES FI FR GE HU IT NO PL PO SK SP	7135425B 7146012B 7146112B 7119593B 7146243B 7135054B 7119989B 7119823B 7146215B 7119986B 7156606B 7135346B 7146401B 7135407B 7119969B	OP	(317102) or (317107)	

A-7 - 4

Nordson Engineering Hot Melt Products (sorted by Model) Systems - Bookbinding

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Book Binding System with Melter MC 20 or MC 4420 - Initial Startup -	DA DU EN FR GE IT JA NO PO SP	213512F 213431F 458358F 213424F 458195F 213405F 7119721F 213426F 213112F 213313F	IN	(317102) or (317107)	
	Book Binding System with Melter MC 20 or MC 4420 - System Description -	DA DU EN FR GE IT JA NO PO SP	213513F 213432F 447764F 213425F 447664F 213406F 7119722F 213427F 213113F 213314F	OP	(317102) or (317107)	
	Book Binding System with ProBlue - Initial Startup -	EN GE NO	7146019A 7135931A 7146099A	IN	(317102) or (317107)	
EP 48 PRO	EP 48 PRO Spine Gluing Applicator - System operation card -	EN	7560864_01	OP	(317102) or (317107)	
EP 48 PRO	EP 48 PRO Spine Gluing Applicator (KM200) - System operation card -	EN	7560865_01	OP	(317102) or (317107)	
PB 90	Book Binding System PB 90 - System Description -	EN GE	317187A 315924A	MA	(317102) or (317107)	When ordering, please state Unit Type and Serial Number

A-7 - 5

Nordson Engineering Hot Melt Products (sorted by Model) Systems - Bookbinding

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
PB 90	PB 90 - Operating Console	EN GE	317188A 315925A	MA	(317102) or (317107)	When ordering, please state <i>Unit Type and Serial Number</i>
PB 90	Bulk Melter BM 506 for PB 90	EN GE	317189A 315926A	MA	(317103) or (317106)	When ordering, please state <i>Unit Type and Serial Number</i>
PB 90	Bulk Melter BM 5506 for PB 90	EN	407324A	MA	(317103) or (317106)	When ordering, please state <i>Unit Type and Serial Number</i>
PB 90	Wheel Applicator Station	EN GE	317190B 315927B	MA	(317102) or (317107)	When ordering, please state <i>Unit Type and Serial Number</i>
PB 90	Microset® MultiScan Control System	EN GE	317191A 315928A	MA	(317102) or (317107)	When ordering, please state <i>Unit Type and Serial Number</i>
PB 90	PB 90 Trolley Starbinder	EN FR GE	317157A 317174A 315936A	MA	(317102) or (317107)	When ordering, please state <i>Unit Type and Serial Number</i>
PB 90	PB 90 Trolley Normbinder	EN FR GE	317158A 317175A 315937A	MA	(317102) or (317107)	When ordering, please state <i>Unit Type and Serial Number</i>
PB 90	PB 90 Trolley Universal	EN FR GE	403100A 403101A 403099A	MA	(317102) or (317107)	When ordering, please state <i>Unit Type and Serial Number</i>
PB 90	PB 90 Trolley Universal with Eccentric Vertical Adjustment	EN FR GE	317159A 317176A 315938A	MA	(317102) or (317107)	When ordering, please state <i>Unit Type and Serial Number</i>

Issued by Technical Documentation Local Languages (TDLL) Department, Nordson Engineering, Lüneburg
Status : July 2017

A-7 - 6

Nordson Engineering Hot Melt Products (sorted by Model) *Systems - Bookbinding*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
SDS	Spindle Metering Device Series SDS	EN FL GE	412911C 412912A 412846C	MA	(317102) or (317107)	
SDS	Spindle Metering System SDS - System Description -	EN FL GE	412913B 412914A 412847B	MA	(317102) or (317107)	

A-7 - 7

Nordson Engineering Hot Melt Products (sorted by Model) Systems - Gasketing

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Foam Mix	System Description FoamMix / BM Gasketing System AGT Standard System	EN FR GE IT SP	317253B 315931B 315836B 315923B 403053B	MA	(317103) or (317106)	
Foam Mix	FoamMix / BM Gasketing Unit	GE	458219A	SU	(317102) or (317107)	Addition to P/N 315836B
Foam Mix	System Description FoamMix / BM-Gasketing Unit Tandem System	FR GE IT	315710A 292948A 315922A	MA	(317103) or (317106)	
Foam Mix	Foam Mix System	IT	292789A	IN	(317102) or (317107)	
Foam Mix	FoamMix / Gasketing Unit - Cold - System Description	GE IT	407230A 407231A	MA	(317103) or (317106)	
Foam Mix	FoamMix / BM Gasketing Unit - System Description	GE	458211A	MA	(317102) or (317107)	
Foam Mix 9400 Series	Foam Mix 9400 Systems	EN GE	284066 284065	OP	(317102) or (317107)	

A-7 - 8 **Nordson Engineering Hot Melt Products (sorted by Model)**
Systems - Moulding

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
WS 100 Series WS 101/ WS 102/ WS 103/ WS 104	Casting System Series WS 100 with Control Module easy	DU EN FR GE IT JA PL PO SP	464812 I 315853 I 317099 I 317017 I 409475 I 213265 I* 7105308I 464813 I 464798 I	MA	(317102) or (317107)	When ordering, please state Unit Type and Serial Number * available at Nordson K.K.
WS 200 Series WS 201/ WS 202	Casting System Series WS 200	EN FR GE IT PO SP	317290B 403042B 317179B 412975B 464781B 317246B	MA	(317102) or (317107)	When ordering, please state Unit Type and Serial Number

A-8 - 1

Nordson Engineering (Meltex) Product Line (sorted by Model) Coating Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Roll Coater	EN FR GE	412709A 407451A 458325A	MA	(317102) or (317107)	Italian source - P/N 290936
	Self-carrying Swivel Inlet Deublin	DU EN FR GE IT SW	409333A 409318A 409334A 409179A 409319A 409346A	MA	(317102) or (317107)	
	Self-carrying Swivel Inlet Maier	DU EN FR GE IT JA PL PO SP SW	409335C 409320C 409336C 409180C 409321C 7119929C 7146581C 7105198C 464977C 409345C	MA	(317102) or (317107)	
CL 2018/ CL 2018S	Hot Melt Laboratory Coater CL 2018 / CL 2018 S	EN FR GE IT PL SW	317184D 317195D 317172D 403058D 7105714D 458041D	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
CLG 05	Electrical Cabinet CLG 05	EN GE	407449A 407448A	MA	(317102) or (317107)	When ordering, please state Unit Type and Serial Number
CLG 05/ CLG 05P	Electrical Cabinet CLG 05 / CLG 05 P	GE	458382A	MA	(317102) or (317107)	When ordering, please state Unit Type and Serial Number

A-8 - 2

Nordson Engineering (Meltex) Product Line (sorted by Model) Coating Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
CLG 05/ CLG 05P	Lab Melter CLG 05 / CLG 05 P	DU EN GE	317211A 407473B 315771B	MA	(317102) or (317107)	When ordering, please state Unit Type and Serial Number
CLG 05P	Laboratory Coater CLG 05 P	GE	458335A	MA	(317102) or (317107)	When ordering, please state Unit Type and Serial Number
CLG 05	Laboratory Melter CLG 05	EN FR GE SP	7146638A 7119822A 7119799A 7135940A	MA	(317102) or (317107)	When ordering, please state Unit Type and Serial Number
NT 1027	Hot Melt Coating Module NT 1027	FR GE	409048A 409119A	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
NT 1035	Hot Melt Coating Module NT 1035	EN GE	7119612B 7119540B	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
NT 1041	Hot Melt Coating Module NT 1041	FR GE	464935A 464772A	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
NT 1045	Hot Melt Coating Modules NT 1045	EN GE	7105823A 7105686A	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
NT 1050	Hot Melt Coating Module NT 1050	FR GE	7135445A 7135340A	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
NT 1050	Hot Melt Coating Module NT 1050	GE	405193A	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
NT 1050	Hot Melt Coating Module NT 1050	EN GE	458027A 413086A	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number

A-8 - 3

Nordson Engineering (Meltex) Product Line (sorted by Model)

Coating Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
NT 1050	Hot Melt Coating Module NT 1050	EN GE	213750B 213698B	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
NT 1050	Hot Melt Coating Module NT 1050	GE PO	397424A 397516A	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
NT 1050	Hot Melt Coating Module NT 1050	EN GE	397550B 397534B	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
NT 1050	Hot Melt Coating Module NT 1050	EN GE	7119358A 7119300A	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
NT 1055	Hot Melt Coating Module NT 1055	EN GE PL	7146510A 7146467A 7146579A	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
NT 1070	Hot Melt Coating Module NT 1070	EN GE	397367A 397078A	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
NT 1075	Hot Melt Coating Module NT 1075	EN GE	7192177_01 7192149_01	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
NT 1085	Hot Melt Coating Module NT 1085	GE	447645A	MA	(317104) or (317105)	When ordering, please state Unit Type and Serial Number
NT 4035	Hot Melt Coating Module NT 4035	GE	7119090A	MA	(317104)	When ordering, please state Unit Type and Serial Number
SD01	Swivel Device	EN FR GE SP SW	405092B 405093B 405094B 447624B 405124B	MA	(317102) or (317107)	

A-8 - 4

Nordson Engineering (Meltex) Product Line (sorted by Model) Coating Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
SD02	Swivel Device	EN FR GE IT RU SP SW	317186B 407469B 317185B 397347B 7179744B 7135631B 458042B	MA	(317102) or (317107)	
SD03	Swivel Device with horizontal swivel path for surface coating heads	DU EN FR GE IT PO SP	405229C 405190C 405191C 405192C 458001C 7119274C 7119551C	MA	(317102) or (317107)	
SD04	Swivel Device with possibility for 3D adjustment	GE	317229A	MA	(317102) or (317107)	
SD05	Swivel Device with horizontal adjustment for application heads EP...	FR GE	464803A 464794A	MA	(317102) or (317107)	
SD06	Swivel Device for surface coating heads BC 40 with application widths up to 350mm	GE	412797A	MA	(317102) or (317107)	
SD08	Swivel Device for Hot Melt Application Head Control Coat	DU GE	409232A 409221A	MA	(317102) or (317107)	
SD09	Swivel Device for CT 4000 and CL 2018	EN GE	409474A 409454A	MA	(317102) or (317107)	
SD10	Swivel Device with two mounting positions	GE	409473A	MA	(317102) or (317107)	

A-8 - 5

Nordson Engineering (Meltex) Product Line (sorted by Model) Coating Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
SD11	Swivel Device with Height Adjustment for Hot Melt Application Head Control Coat	EN GE	412704A 412687A	MA	(317102) or (317107)	
SD12	Swivel Device for three Hot Melt Application Heads EP	GE	412701A	MA	(317102) or (317107)	
SD13	Swivel Device for Hot Melt Application Heads EP 51	GE	412722A	MA	(317102) or (317107)	
SD14	Swivel Device for Application Head BC 40 with Adapter for Application Head EP	EN GE	458032B 458004B	MA	(317102) or (317107)	
SD15	Swivel Device with Horizontal Swivel Path for Application Heads EP	EN GE	458102A 458095A	MA	(317102) or (317107)	
SD16	Swivel Device on Coating System CT 4400 for Application Heads EP...	EN GE	447794A 447731A	MA	(317102) or (317107)	
SD17	Swivel Device CT / SB	EN GE SP	447799A 447782A 464777A	MA	(317102) or (317107)	
SD18	Swivel Device	FR GE	7119184A 213028A	MA	(317102) or (317107)	
SD19	Swivel Device with Maintenance Position	FR GE	213086A 213065A	MA	(317102) or (317107)	
SD20	Swivel Device with Coating Roll for Application Heads EP...	EN FR GE	213752B 213733B 213713B	MA	(317 101)	

A-8 - 6

Nordson Engineering (Meltex) Product Line (sorted by Model) Coating Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
SD21	Swivel Device with Sensor for Druckmarkenerkennung	FR GE	397045A 213974A	MA	(317102) or (317107)	
SD22	Swivel Device on CT 4435 for Application Head EP 51	FR GE	397239A 397196A	MA	(317102) or (317107)	
SD23	Swivel Device on CT 4400	EN FR GE	7105769A 397263A 397223A	MA	(317102) or (317107)	
SD24	Adjusting Device for Applicator (Title Version C: Adjusting Device for Application Head)	DA DU EN FR GE IT PL PO RU SP SW	7156827C 7105951C 397672_04 7105944_04 397453_04 7146698C 7146582C 397475A 7146690C 7146163C 7135757C	MA	(317102) or (317107)	
SD25	Swivel Device for Vertical Coating Position	CH EN GE RU	7156633A 397937A 397892A 7156511A	MA	(317102) or (317107)	
SD26	Adjusting Device for Application Heads EP 51	FR GE	7105867A 7105307A	MA	(317102) or (317107)	
SD27	Adjusting Device for Surface Coating Head	EN FR GE JA	7119821A 7135482A 7119749A 7119932A	MA	(317102) or (317107)	

A-8 - 7

Nordson Engineering (Meltex) Product Line (sorted by Model) Coating Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
SD28	Adjusting Device for Application Head Curtain Coat BC70	EN GE IT PL	7135512A 7135326A 7135332A 7146514A	MA	(317102) or (317107)	
SD29	Adjusting Device for Application Head	FR GE	7146071A 7146056A	MA	(317102) or (317107)	
SD30	Adjusting Device	DA EN FR GE IT PL PO SP	7169283D 7146763_05 7146673C 7146659_05 7179196_05 7179214D 7192829_05 7169629_05	MA	(317102) or (317107)	
SD31	Adjusting Device Cart for BC40	EN GE	7156212B 7156207B	MA	(317102) or (317107)	
SD32	Adjusting Device with Motor-driven Angle Adjustment	EN FI GE	7169154A 7169167A 7169103A	MA	(317102) or (317107)	
SD33	Adjusting Device for Applicator EP11	GE	7560337_01	MA	(317102) or (317107)	

A-9 - 1

Nordson Engineering Hot Melt Products (sorted by Model)

Other Hot Melt Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
EEX	Extruder Economic Series	EN FR GE IT LI PL PO SL SP	7169667_04 7179306_05 7169615_05 7169849_05 7560767_04 7179198_01 7169666_03 7560664_04 7179768_02	MA	(317102) or (317107)	
EX/ EX...UFM	Extruder	CZ EN FR GE PL	7179814_03 7179048_03 7179136_03 7169915_03 7560821_03	MA	(317102) or (317107)	
GR 22	Retrofitting Kit GR 22	GE	409068A	MA	(317102) or (317107)	
HM 4500/ HM 4200	SERIES HM 4500 / HM 4200 Hot Melt Applicator	DU EN FR GE IT SP SW	290820A 264236B 264238B 264240B 264242B 290822A 264244B 290823A 290821A	SA MA MA MA MA SA MA SA SA	(317104) or (317105)	
HM 4500/ HM 4200	SERIES HM 4500 / HM 4200 Hot Melt Applicator	DU EN FR GE IT SP SW	269823 264237 264239 264241 264243 264245 269824	OP	(317102) or (317107)	

A-9 - 2

Nordson Engineering Hot Melt Products (sorted by Model)

Other Hot Melt Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
KBV 400	Cartridge Filling Device KBV 400	FR GE	213499A 213336A	MA	(317102) or (317107)	
PH	PH and PH.. UFM Adhesive Melters	EN GE SW	7179598_01 7179431_02 7179615_01	MA	(317103) or (317106)	
PM 350	Hot Melt Material Premelter PM-350	EN	315789B	MA	(317103) or (317106)	When ordering, please state Unit Type and Serial Number
PS 352/ PS 752	Hot Melt Metering Unit PS 352 / PS 752 with Siemens Controller	EN GE	7146788A 7146717A	MA	(317103) or (317106)	
PS 352/ PS 752/ PS 1502	Hot Melt Metering Unit PS 352 / PS 752 / PS 1502	CH EN FI FR GE IT PL SP SW TU	7119920 B 458207 B 7135508 B 458149 B 409130 B 458050 B 7135518 B 7105518A 7105033A 7135926 B	MA	(317103) or (317106)	
PS 352/ PS 752/ PS 1502	Hot Melt Metering Unit PS 352 / PS 752 / PS 1502 with Control System CS 20	EN FI FR GE GR IT PL RU SP SW TU	397021A 7135509A 213571A 213485A 213522A 213767A 7135519A 7119694A 7105519A 7105034A 7135927A	OP	(317102) or (317107)	

A-9 - 3

Nordson Engineering Hot Melt Products (sorted by Model)

Other Hot Melt Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
PS 352-1S/ PS 352-4S	Hot Melt Metering Unit with Agitator PS 352-1S / PS352-4S	GE IT	7105067A 7105136A	MA	(317103) or (317106)	
PS 752	Hot Melt Metering Unit PS 752-1	GE	409026A	MA	(317103) or (317106)	
UFM	Ultra Foam Mix Cube C4_Type 10	EN	7169638_02	MA	(317102) or (317107)	
UFM	Foam Units Ultra Foam Mix Cube	CZ EN FI GE IT JA PL SP SW	7179964_01 7179183_04 7192580_03 7169660_04 7179772_03 7560390_03 7179988_04 7179499_04 7179145_01	MA	(317102) or (317107)	
UFM	Touchpanel on Foam Units Ultra Foam Mix Cube	CZ FI EN GE IT JA PL SP	7179653_02 7192581_03 7179572_05 7179131_05 7560529_03 7560505_03 7179699_05 7192976_05	MA	(317102) or (317107)	
XP 5 / XP 10	Extruder XP 5 XP 10	FR GE IT	213696B 213244B 213656B	MA	(317102) or (317107)	
XP 5 / XP 10	Extruder XP 5 XP 10	FR GE	213946A 213922A	MA	(317102) or (317107)	

A-9 - 4 **Nordson Engineering Hot Melt Products (sorted by Model)**
Other Hot Melt Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
XP 10	Extruder XP 10	GE	458306B	MA	(317102) or (317107)	
XP 22	Extruder XP 22	EN GE PO SP	409107E 409106E 213382E 409108A	MA	(317103) or (317106)	When ordering, please state Unit Type and Serial Number
XP 22	Extruder XP 22	FR GE	409391A 409027A	MA	(317103) or (317106)	When ordering, please state Unit Type and Serial Number
XP 41	Extruder XP 41	EN GE	413097A 413093A	MA	(317103) or (317106)	When ordering, please state Unit Type and Serial Number
XP 81	Extruder XP 81	EN GE	458477A 458436A	MA	(317102) or (317107)	
XP 81	Extruder Item No. 8018770	DU GE	213277A 213258A	MA	(317102) or (317107)	
XP 81	Extruder XP 81	FR GE IT	412802A 412744A 412806A	MA	(317102) or (317107)	
XP 225	Extruder XP 225	EN GE	407127A 405296A	MA	(317104) or (317105)	

A-10 - 1

Nordson Engineering Hot Melt Products (sorted by Model)

Drives

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Air Motor with Piston Pump for Bulk Melters BM	CZ DA DU EN FI FR GE IT JA NO PO SP SW	464960C 447698C 447601C 458479C 397982C 458488C 458127C 447654C 464855A* 397879C 213168C 458489C 447650C	MA	(317102) or (317107)	* available at Nordson K.K.
	Servo Converter	GE	458024A	MA	(317102) or (317107)	
	Motor Controller and Servomotor	DU EN GE IT SW	412775B 412776B 412746B 412777B 412903B	MA	(317102) or (317107)	

A-10 - 2

Nordson Engineering Hot Melt Products (sorted by Model)

Drives

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Speed Compiler (RPM)	DA DU EN FI FR GE GR IT JA NO PL PO RU SP SW TU	409374B 405117B 405066B 405204B 405067B 405008B 213845B 405126B 7146027B 409451B 7105755B 405230B 397394B 405292B 405106B 397117B	MA	(317102) or (317107)	(PS03)
	Speed Compiler (RPM)	DA DU EN FI FR GE IT NO PO SP SW	407271A 407272A 407273A 407274A 407275A 409437A 407276A 412686A 407277A 407278A 407279A	MA	(317102) or (317107)	(PS04)
	Three-phase AC Motor with Worm Gear	EN GE SW	412961B 409123B 458046B	MA	(317102) or (317107)	(DR05)

A-10 - 3

Nordson Engineering Hot Melt Products (sorted by Model) *Drives*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
BG	Gear Motor BG	CH EN GE JA PL PO	7135018A 7119597B 7119585B 7146026B 7156351B 7192889B	MA	(317102) or (317107)	
DM 200	Gear Torque Motor DM 200	DU EN FR GE IT PO SP SW	405194A 405195A 405196A 405116A 405197A 412705A 405289A 405198A	MA	(317102) or (317107)	
ECC	Overload Coupling Series ECC	CZ DU EN FR GE IT PO SP	464721D 213465E 403039E 403048E 317263E 403047E 7105193E 213251E	MA	(317102) or (317107)	(CL02)
GL 02	D.C. Gear Motor Series GL ...02	EN GE IT	409425A 409422A 409426A	MA	(317102) or (317107)	

A-10 - 4

Nordson Engineering Hot Melt Products (sorted by Model) *Drives*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
GL 03	D.C. Gear Motor Series GL ...03	DA DU EN FI FR GE IT NO PO SP SW	317288A 317219A 317220A 403057A 317245A 317206A 317226A 317228A 317223A 317221A 317227A	MA	(317102) or (317107)	
GL 550	D.C. Gear Motor GL 550	EN GE IT	409444A 409421A 409445A	MA	(317102) or (317107)	(DR06)

A-10 - 5

Nordson Engineering Hot Melt Products (sorted by Model) *Drives*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LM 20/ LM 40	Air Gear Motors LM 20 / LM 40	DU EN GE	409343A 409405A 403103A	MA	(317102) or (317107)	
WS Series	A.C. Gear Motors Series WS ...	CZ DA DU EN FI FR GE GR HU IT JA NO PL PO RU SK SP SW TU	447775C 405231C 407051C 317277D 407410C 407040C 317271D 407153C 7105480C 407039C 405172C 407329C 7105212C 407317C 407018D 7105463C 317278C 405202C 397116C	MA	(317102) or (317107)	(DR03)

A-11 - 1

Nordson Engineering Hot Melt Products (sorted by Model) *Mechanical & Hydraulic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Bypass Plate with Safety Valve	DA DU EN FR GE IT NO PO SP SW	317299A 403014A 403027A 403041A 317284A 403006A 403001A 403011A 403005A 403019A	MA	(317102) or (317107)	(SV07)
	Cascade Filter	EN GE IT PL	7105511B 7105510B 7156576B 7156354B	MA	(317102) or (317107)	(FC07)
	Feed Valve	CZ EN GE	464725A 464724A 464714A	MA	(317102) or (317107)	
	Feed Valve	EN GE	397497A 397464A	MA	(317102) or (317107)	
	Feed Valve	EN GE	213970A 213954A	MA	(317102) or (317107)	
	Filter Block with Safety Valve	EN GE IT	409464A 409457A 409465A	MA	(317102) or (317107)	

A-11 - 2

Nordson Engineering Hot Melt Products (sorted by Model)

Mechanical & Hydraulic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Filter Cartridge	CZ DA DU EN FI FR GE GR HU IT JA NO PL PO RU SK SP SW TU	447778C 407252D 407253D 407254D 407255D 407256D 405297D 407291C 7105482C 407257D 405174A* 407258D 7105304C 407259D 407294A 7105465C 407260D 407261D 397121C	MA	(317102) or (317107)	(FC02) * = available at Nordson K.K.
	Filter Cartridge	DU EN GE IT SW	412778A 412779A 412745A 412780A 412904A	MA	(317102) or (317107)	(FC05)
	Filter Cartridge with Bayonet Fastener	DA DU EN FI FR GE IT NO PO SP SW	213690C 213681C 213687C 213894C 213678C 213477C 213694C 213666C 213662C 213675C 213700C	MA	(317102) or (317107)	(FC06)

A-11 - 3

Nordson Engineering Hot Melt Products (sorted by Model) Mechanical & Hydraulic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Filter Unit in Hot Melt Metering Units PS...	CH EN FR GE IT SP SW	7135019B 458234C 458156A 409389C 458151A 7105521A 7105036A	MA	(317102) or (317107)	(FC04)
	Gear Pumps Series Mahr / Feinprüf	CZ DA DU EN FI FR GE GR IT JA NO PO RU SP SW	447774A 407289D 407327D 403038E 409016D 407297D 317247E 407152A 403245E 405171A* 407320D 407316D 407017A 407171D 407172D	MA	(317102) or (317107)	(GP07) * = available at K.K.
	Gerotor Pump	DA DU EN FR GE IT NO PO SP SW	464746A 464750A 447795A 464709A 458456A 447793A 464703A 213169A 464704A 464705A	MA	(317102) or (317107)	
	Gerotor Pump with Manifold Block	EN FR GE	412936A 412937A 409277A	MA	(317102) or (317107)	

A-11 - 4

Nordson Engineering Hot Melt Products (sorted by Model)

Mechanical & Hydraulic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Mechanical Safety Valve	DA DU EN FI FR GE IT JA NO PL PO RO RU SP SW TU	409160A 409161A 409162A 409163A 409164A 405298A 409165A 464880A* 409166A 7105211A 409167A 7135548A 397391A 409168A 409169A 397118A	MA	(317102) or (317107)	(SV04) * = available at Nordson K.K.
	Mechanical Safety Valve with Pressure Display	EN FR GE	409363A 409372A 409364A	MA	(317102) or (317107)	(SV02)

A-11 - 5

Nordson Engineering Hot Melt Products (sorted by Model)

Mechanical & Hydraulic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Pneumatic Safety Valve	CZ DA DU EN FI FR GE GR HU IT JA NO PL PO SK SP SW	447776G 409151G 409152G 405189G 409153G 409154G 317222G 213842F 7105481G 409155G 464986G 409156G 7105303G 409157G 7105464G 409158G 409159G	MA	(317102) or (317107)	(SV05)
	Pneumatic Safety Valve with Reed Switch	DA DU EN FI FR GE GR IT JA NO PO RU SP SW TU	403012H 317269H 317268_09 409015H 317294H 317135_09 407154B 317281H 405173B* 317270H 317266H 407019B 317256H 403016H 397119F	MA	(317102) or (317107)	(SV06) * = available at Nordson K.K.

A-11 - 6

Nordson Engineering Hot Melt Products (sorted by Model)

Mechanical & Hydraulic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Sevice Kit 7109870: Pneumatic Safety Valve and Pressure Restrictor Valve (3 bar) Sevice Kit 7109871: Pneumatic Safety Valve and Pressure Restrictor Valve (5 bar)	EN/FR/ GE/IT/ SP	7105860A	IN	(317102) or (317107)	Multilingual document, therefore one P/N only
	Retrofitting Kit PR Pump - Feinprüf Pump	EN GE	412819A 412665A	MA	(317102) or (317107)	
DR 145	Constant Pressure Controller DR 145	EN FR GE IT SW	317181C 409369B 317173C 7135226C 7135224C	MA	(317102) or (317107)	
DR 330	Constant Pressure Controller DR 330	EN GE PL RU SW	317170C 315835C 7146008C 7146003C 447722C	MA	(317102) or (317107)	
DR 900/1300	Constant Pressure Controller DR 900 / DR 1300	GE EN SP	315832B 315946B 403056B	MA	(317102) or (317107)	
GB 04	Pressure Compensating Module	EN GE	407478A 407408A	MA	(317102) or (317107)	

A-11 - 7

Nordson Engineering Hot Melt Products (sorted by Model)

Mechanical & Hydraulic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
KF 25	Nozzle Filter KF 25	BU CZ DA DU EN FI FR GE GR HU IT NO PL PO RU SP SW TU	7135433F 464722D 409136F 409019F 403023F 447691F 413021F 403024F 213843D 7105614F 409018F 464804F 7119263F 464805F 397392F 464806F 403059F 397125D	MA	(317102) or (317107)	When ordering, please state Product Part Number
KF 25	Filter Cartridge KF 25	EN GE	409220A 407487A	MA	(317102) or (317107)	(FC03)
PF...	Active Pressure Accumulator Series PF	EN FR GE SP	403074D 403256D 317296D 403037D	MA	(317102) or (317107)	

A-11 - 8

Nordson Engineering Hot Melt Products (sorted by Model)

Mechanical & Hydraulic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
PR Series	Gear Pumps Series PR ...	CZ DA DU EN FI FR GE GR HU IT JA NO PL PO RO RU SK SP SW TU	464930A 405071A 405072A 403130A 405073A 405074A 403131A 213844A 7105479A 405075A 464879A* 407284A 7105214A 405076A 7135546A 397393A 7105462A 405131A 405077A 397115A	MA	(317102) or (317107)	(GP08) * = available at Nordson K.K.
	Pump Feed Capacity PR 2 Module 1	EN	407026A			
	Pump Feed Capacity PR 2 Module 2	EN	407027A			
	Pump Feed Capacity PR 3 Module 1	EN	407028A			
	Pump Feed Capacity PR 3 Module 2	EN	407029A			
	Pump Feed Capacity PR 4 Module 1	EN	407030A			
	Pump Feed Capacity PR 6 Module 1	EN	407031A			

A-11 - 9

Nordson Engineering Hot Melt Products (sorted by Model)

Mechanical & Hydraulic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Pump Feed Capacity PR 6 Module 2	EN	407032A			
	Pump Feed Capacity PR 12 Module1	EN	407023A			
	Pump Feed Capacity PR 12 Module 2	EN	407024A			
	Pump Feed Capacity PR 18 Module 2	EN	409064A			
	Pump Feed Capacity PR 25 Module 2	EN	407025A			
	Pump Feed Capacity PR 100 Module 3	EN	407022A			
PU Series	Multiple Current Gear Pump Series PU □-□m□	DA DU EN FI FR GE IT NO PO SP SW	405078B 405079B 403220B 405080B 405081B 403132B 405082B 407285B 405083B 405130B 405084B	MA	(317102) or (317107)	(GP09)

A-11 - 10

Nordson Engineering Hot Melt Products (sorted by Model)

Mechanical & Hydraulic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
PU Series	Single Stream Gear Pump Series PU □/85 and PU 700	CH CZ DA DU EN FI FR GE IT JA NO PO SP SW	7135016C 464743B 405085C 405086C 403221E 405087C 405088C 403222E 405089C 7146025E 407286C 405090C 405129C 405091C	MA	(317102) or (317107)	(GP10)
PUR_PR_EP48	Pressure Regulator CPR	EN GE IT	7179678_03 7179677_03 7560105_02			
	Pump Feed Capacity PU 2-2 Module 1	EN	409239A			
	Pump Feed Capacity PU 2-4 Module 1	EN	397130A			
	Pump Feed Capacity PU 2-6 Module 1	EN	397131A			
	Pump Feed Capacity PU 2-8 Module 1	EN	213286A			
	Pump Feed Capacity PU 3-2 Module 1	EN	407048A			
	Pump Feed Capacity PU 3-4 Module 1	EN	397314A			
	Pump Feed Capacity PU 4-2 Module 1	EN	407049A			

A-11 - 11

Nordson Engineering Hot Melt Products (sorted by Model)

Mechanical & Hydraulic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Pump Feed Capacity PU 4-4 Module 1	EN	397132A			
	Pump Feed Capacity PU 4-6 Module 1	EN	409145A			
	Pump Feed Capacity PU 6-2 Module 1	EN	409243A			
	Pump Feed Capacity PU 6-4 Module 1	EN	407036A			
	Pump Feed Capacity PU 12-2 Module 1	EN	407050A			
	Pump Feed Capacity PU 12-2 Module 2	EN	412758A			
	Pump Feed Capacity PU 12-4 Module 1	EN	458106A			
	Pump Feed Capacity PU 15/85 Module 2.5	EN	464948A			
	Pump Feed Capacity PU 18-2 Module 1	EN	407438A			
	Pump Feed Capacity PU 25/85 Module 2.5	EN	407033A			
	Pump Feed Capacity PU 25-2 Module 2	EN	213298A			
	Pump Feed Capacity PU 35/85 Module 2.5	EN	407034A			
	Pump Feed Capacity PU 50/85 Module 2.5	EN	407035A			
	Pump Feed Capacity PU 700	EN	407037A			

A-12 - 1

Nordson Engineering Hot Melt Products (sorted by Model)

Pneumatic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Air Heater LH03, LH04, LH05	EN GE PL	7156284A 7156279A 7179170A	MA	(317102) or (317107)	
	Air Manifold Bar	DA EN GE IT PO SP SW	464915A 405052A 405053A 405127A 213022A 213057A 464954A	MA	(317102) or (317107)	
	Air Manifold Bar with Pressure Accumulator for Hot Melt Application Heads	DU EN FR GE HU IT PO SP	458355B 458351B 458343B 458315B 7105616B 458393B 213023B 458491B	MA	(317102) or (317107)	
	Air Manifold Bar	EN GE	7105657A 7105626A	MA	(317102) or (317107)	
	Clean Air Flow Kit	DA EN	409139A 403261A	MA	(317102) or (317107)	
	Clean Air Flow Kit (Compact)	EN SW	405109B 405203B	MA	(317102) or (317107)	

A-12 - 2

Nordson Engineering Hot Melt Products (sorted by Model)

Pneumatic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Control Units for Pneumatic Safety Valves	CZ DA DU EN FI FR GE GR IT JA NO PO RU SP SW TU	447777F 403018G 317250G 317255G 409014G 317275G 317028G 407292F 317280G 405175A* 317251G 317267G 407295A 317252G 403004G 397120F	MA	(317102) or (317107)	(SVC01) * = available at Nordson K.K.
	Control Unit for Pneumatic Safety Valves	DA DU EN FI FR GE IT NO PO SP SW	458323A 458344A 403269A 458345A 458346A 315732A 458347A 458348A 405012A 458349A 458350A	MA	(317102) or (317107)	(SVC02)

A-12 - 3

Nordson Engineering Hot Melt Products (sorted by Model)

Pneumatic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Control Unit for Pneumatic Safety Valves	CZ DU EN FI FR GE IT SP SW	7105414B 213764B 213312B 7105722B 213757B 213301B 213317B 213763B 213709B	MA	(317102) or (317107)	(SVC03)
HI 10	Heated Air Assembly HI 10	EN FR GE	409184A 213821A 409085A	MA	(317102) or (317107)	
HI 11	Heated Air Assembly HI 11	EN FR GE	403262A 403263A 403264A	MA	(317102) or (317107)	
HI 14	Heated Air Assembly HI 14	CZ DA DU EN FR GE IT PL RU SP	7580194B* 213736B 7179026B 292943B 292944B 292879B 407303B 7179169B 7192815B 213917B	MA	(317102) or (317107)	* not yet released
HI 15	Heated Air Assembly HI 15	DA DU EN FR GE IT PL SP SW	409137C 317295C 315944C 315947C 315824C 317289C 7146658C 407328C 403055C	MA	(317102) or (317107)	

A-12 - 4

Nordson Engineering Hot Melt Products (sorted by Model)

Pneumatic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
HI 16	Heated Air Assembly HI 16	EN FR GE IT PL SP SW	315945B 315948B 315827B 213420B 7156355B 213340B 464801B	MA	(317102) or (317107)	
HI 17	Heated Air Assembly HI 17	EN FR GE	407006A 407007A 407005A	MA	(317102) or (317107)	
IG 24	Inert Gas Equipment IG 24	DU EN FI FR GE HU IT JA NO PO SK SP SW	292797E 292796E 292798E 292799E 292778E 7105477E 292909E 464983D* 292910E 292911E 7105460E 292912E 292800E	MA	(317102) or (317107)	When ordering, please state Product Part Number * available at Nordson K.K.
IG 24 V	Inert Gas Equipment IG 24 with Vacuum Pump	DA DU EN FI FR GE IT NO PO SP SW	407232A 407233A 407234A 407235A 407236A 407125A 407237A 407238A 407239A 407240A 407241A	MA	(317102) or (317107)	

A-12 - 5

Nordson Engineering Hot Melt Products (sorted by Model)

Pneumatic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
IG 25	Inert Gas Equipment IG 25	DA DU EN FI FR GE IT NO PL PO RU SP SW	407242B 407243B 407244B 407245B 407246B 407126B 407247B 407248B 7105737B 407249B 7135997B 407250B 407251B	IN	(317102) or (317107)	
IG 25 V	Inert Gas Equipment IG 25 with Vacuum Pump	DA DU EN FI FR GE IT NO PL PO SP SW	409362B 407263B 407262B 407264B 407265B 409329B 407266B 407267B 7119892B 407268B 407269B 407270B	IN	(317102) or (317107)	
IG 25 / IG 25 V	Notes on Inert Gas Equipment IG 25 / IG 25V	EN/ FR/ GE/ IT/ SP	397853A	IN	(317102) or (317107)	Multilingual document, therefore one P/N only

A-12 - 6

Nordson Engineering Hot Melt Products (sorted by Model)

Pneumatic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
MBT	Membrane Compressed Air Dryer	DU EN GE IT NO PO RU SP	397857B 458252B 412860B 447707B 458321B 213111B 7105349B 213235B	MA	(317102) or (317107)	
OR ...	Air Conditioning Unit	DU EN FR GE IT SP SW	317060A 317061A 317059A 315918A 317062A 317065A 317074A	MA	(317102) or (317107)	

A-13 - 1

Nordson Engineering Hot Melt Products (sorted by Model)

Electrical & Electronic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Capacitive Evaluation Unit - Data Sheet (LC 24)	EN	407399D	MA	(317102) or (317107)	
	Capacitive Evaluation Unit - Data Sheet (LC 25)	EN	458277B	MA	(317102) or (317107)	
	Capacitive Level Sensor - Data Sheet (IP 68)	EN	407400C	MA	(317102) or (317107)	
	Capacitive Level Sensor - Data Sheet (IP 68)	EN	458278B	MA	(317102) or (317107)	
	Connection Box with Indicator Signal Distributor 2:1	DU EN GE SP	315916A 315910A 315862A 317043A	MA	(317102) or (317107)	
	Encoder	DU EN FI FR GE IT PL PO SK SP SW	317254C 292785C 412889C 292786C 290719C 317279C 7105418C 315701C 7105393C 405048C 317285C	MA	(317102) or (317107)	

A-13 - 2

Nordson Engineering Hot Melt Products (sorted by Model)

Electrical & Electronic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Frequency Converters Series 82xx E and 8200 vector	CH DA DU EN FI FR GE IT JA NO PL PO RO RU SP SW	7135020A 7119060A 7119006A 7119002A 7119195A 7119005A 7105653A 7105998A 7146030A 7119079A 7146007A 7119007A 7135547A 7146000A 7119034A 7119035A	MA	(317102) or (317107)	
	Heat Exchanger for Electrical Cabinets (RITTAL_SK)	CZ DA DU EN FR GE IT NO SP SW	447732A 464884C 405255C 405264C 464840C 405265C 409044C 464814C 213128C 405266C	SU MA	(317102) or (317107)	CZ = Supplement (Title: Rittal_SK_CZ_A-0396)
	Inductive Proximity Switch	DU EN FR GE IT SW	317248B 292787B 292788B 290819B 317292B 317286B	MA	(317102) or (317107)	(PS01)

A-13 - 3

Nordson Engineering Hot Melt Products (sorted by Model) Electrical & Electronic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Inductive Proximity Switch Item No. 2614.0387	DA DU EN FI FR GE IT PL PO SK SP SW	413014A 413015A 403105A 412890A 413016A 403104A 413017A 7105419A 413018A 7105394A 413019A 405200A	MA	(317102) or (317107)	(PS02)
	Inductive Proximity Switch	CZ EN FR GE IT PO SP	464706B 464700B 213243B 447798B 213248B 7105194B 213252B	MA	(317102) or (317107)	(PS05)
	BANNER OMNI-BEAM Sensor Heads	EN GE	213072A 213071A	IN	(317102) or (317107)	
	Pressure Sensor	DU EN FR GE IT	409326C 403110C 409327C 403111C 409328C	MA	(317102) or (317107)	(SP83)

A-13 - 4

Nordson Engineering Hot Melt Products (sorted by Model) Electrical & Electronic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Pressure Sensor	DA DU EN FI FR GE IT JA NO PO SP SW	407443_08 403065_08 317258_08 407444_08 405046_08 317257_08 405097_08 409379G 407445_08 407446_08 407447_08 405201_08	MA	(317102) or (317107)	(SP85)
	Pressure Sensor	EN FR GE	292781A 292782A 290717A	MAN	(317102) or (317107)	
	Pressure Sensor EPXO-...	EN/FR/ GE/SP EN/CH EN/CZ EN/RU	447785E 7169274E 7169290E 7156956E	IN	(317102) or (317107)	Multilingual documents, therefore one P/N only
	Pressure Sensor Series W	CZ DU EN FR GE JA PL PO RU	7169876_11 7156672_11 7119609_11 7156598G 7119581_11 7146028C 7156353_11 7192888_11 7169147G	MA	(317102) or (317107)	
	Retrofit Kit Solid State Relais	EN/ FR/ GE/ SP	7105876A	IN		Multilingual document, therefore one P/N only

A-13 - 5

Nordson Engineering Hot Melt Products (sorted by Model)

Electrical & Electronic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Retrofitting Kit Encoder	EN/FR/ GE	409428B	MA	(317102) or (317107)	Multilingual document, therefore one P/N only
DMU 04	Pressure Transducer DMU 04	EN/FR/ GE	458037B 458038B 458030B	MA	(317102) or (317107)	
DR 130	Retrofitting Instructions RPM Monitoring DR 130	EN FR GE	403114C	IN	(317102) or (317107)	Multilingual document, therefore one P/N only
GDS 200	Pressure Sensors with Limiting Value Switch Function GDS 200	DU EN FR GE IT	315828B 292783B 292784B 290718B 409300B	MA	(317102) or (317107)	
KTD 3	Tach Generator KTD 3	EN GE SP	464820A 464786A 464860A	MA	(317102) or (317107)	
LG 9	Tach Generator LG 9	DA DU EN FI FR GE IT NO PO SP SW	292903A 292802A 292801A 292803A 292804A 292726A 292904A 292905A 292906A 292907A 292805A	MA	(317102) or (317107)	
NV 01	Level Adaptation Amplifier NV 01	EN GE IT	397153A 458043A 458047A	MA	(317102) or (317107)	

A-13 - 6

Nordson Engineering Hot Melt Products (sorted by Model) Electrical & Electronic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
P605	Pressure Switch P605	EN GE	7105578A 7105577A	MA	(317102) or (317107)	
PDM 03	Torque Controller for Torque Motors PDM 03	DA DU EN FR GE IT NO PO SP SW	317298B 403015B 403026B 403049B 317287B 403007B 403000B 403010B 403032B 403020B	MA	(317102) or (317107)	
PY 9450/ PY 9451/ PY 9452/ PY 9453	Pressure Sensors with Limit Value Switch Function PY 9450 PY 9451 PY 9452 PY 9453	DU EN FR GE IT SP SW	409233A 317260A 403299A 317259B 409295A 407282A 409231A	MA	(317102) or (317107)	
TLB-KSR	Signal Amplifier TLB-KSR with Level Sensor	EN GE SP	413022A 412998A 413023A	MA	(317102) or (317107)	
TT 61	Isolating Amplifier TT 61	DU EN FR GE IT JA PO SP SW	412673A 409383A 412631A 409382A 458023A 7146029A 7105107A 447637A 447727A	MA	(317102) or (317107)	

A-13 - 7

Nordson Engineering Hot Melt Products (sorted by Model)

Electrical & Electronic Components

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
WZ 201/ WZ 202	Week Timer WZ 201, WZ 202	CZ DA DU EN FI FR GE IT JA NO PO SP SW	213044A 403238B 403244B 403117B 405205B 403235B 403107B 403250B 464883A* 403225B 403227B 403241B 403237B	MA	(317102) or (317107)	* available at Nordson K.K.
WZ 202	WZ 202 Programmable Week Timer	DU EN FI FR GE IT NO PO SP SW	292892A 292893A 292894A 292895A 292777A 292900A 292897A 292898A 292901A 292902A	MA	(317102) or (317107)	

A-14 - 1

Nordson Engineering Hot Melt Products (sorted by Model) Level Controls

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Connector Bracket P/N 447 197	EN	464784A	IN	(317102) or (317107)	
	Evaluation unit for capacitive proximity switch	EN GE	409197A 409196A	MA	(317102) or (317107)	
	Level Control Drexelbrook	CZ EN GE	447733A 458190A 458186A	MA	(317102) or (317107)	
	Plotting Unit KFA-1-... for Rod Probe KFS-1-...	DU EN FI FR GE IT PO SP SW	213019A 458430A 447689A 458440A 458379A 447749A 7105108A 458431A 213701A	MA	(317102) or (317107)	
	Plotting Unit KFA-4-... for 3-Point Rod Probe KFS-4-...	DU EN FR GE IT NO SP SW	447762A 447763A 447779A 447673A 213321A 447769A 213127A 447725A	MA	(317102) or (317107)	
	Plotting Unit KFA-5-... for 3-Point Rod Probe KFS-5-...	CH DU EN FR GE PO SP	7135021C 213509C 464795C 458233C 458204C 7105199C 7119552C	MA	(317102) or (317107)	

A-14 - 2

Nordson Engineering Hot Melt Products (sorted by Model) Level Controls

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Evaluator KFA-5-/ 1-5... for 5-point Level Sensors KFS-5-5... in VersaBlue Melters	EN GE	7119855A 7119820A	MA	(317102) or (317107)	
	Evaluator KFA-5-... for Overfill Sensor	EN GE	7146741B 7146733B	MA	(317102) or (317107)	
	Evaluator KFA for Capacitive Level Sensor KFS-5-4 (in MX 4003 NV Melters)	EN FR GE	7560647_02 7560653_02 7169867_02	MA	(317102) or (317107)	
	Switching Amplifier CSV with Level Sensor	DA DU EN FI FR GE IT JA NO PO SP SW	409093B 409055B 407498B 409078B 409056B 407465B 409057B 409378B* 409063B 409237B 409046B 409045B	MA	(317102) or (317107)	* available at Nordson K.K.
Captron CCT	Captron Rod Probe CCT and Probe Amplifier VC 11-A	EN FR GE	317078A 403137A 317076A	MA	(317102) or (317107)	
LC 18	Weighing Cells LC 18 / LC18-2 / LC18-2 PS	EN GE	283017A 283016A	MA	(317102) or (317107)	

A-14 - 3

Nordson Engineering Hot Melt Products (sorted by Model) Level Controls

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LC 19	Weighing Cell LC 19-1 / LC 19-2 / LC 19-2 PS	CH DA DU EN FI FR GE IT NO PO SP SW	7135022C 403017C 292932C 292933C 292934C 292935C 292795C 292936C 292937C 292938C 292939C 292940C	MA	(317102) or (317107)	
LC 20	Level Controller LC 20	EN GE	317020A 315940A	MA	(317102) or (317107)	
LC 22	Changing Level Control Sensitivity	EN/FR/ GE	405023A	--	(317102) or (317107)	Multilingual document, therefore one P/N only
LC 23	Electronic Level Control LC 23	DA DU EN FI FR GE IT NO PO SP SW	317164E 315758E 292949E 315759E 315760E 292950E 315761E 315762E 315763E 315764E 315731E	MA	(317102) or (317107)	

A-14 - 4

Nordson Engineering Hot Melt Products (sorted by Model) *Level Controls*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LC 24	Electronic Level Control LC 24	DU EN FR GE IT SP SW	409053F 409043F 409054F 407288F 409080F 409212F 409047F	MA	(317102) or (317107)	
LC 24	LC 24 Calibration	EN	397406A	OP	(317102) or (317107)	
LC 25	Electronic Level Control LC 25, LC 25-2	DA DU EN FR GE IT NO SP SW	7105505D 458287D 458288G 458289D 458276G 458290E 458291D 458292D 458293G	MA	(317102) or (317107)	

A-14 - 5

Nordson Engineering Hot Melt Products (sorted by Model) Level Controls

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LC 26	Electronic Level Control LC 26	DA DU EN FR GE IT NO SP SW	213311A 213296A 213288A 213294A 213263A 213297A 213292A 213328A 213289A	MA	(317102) or (317107)	
LC_201458	Level Monitoring with Rod Probe	EN FI FR GE IT SP SW	213669 B 213895A 213688 B 213639 B 213708 B 397038 B 213702 B	IN	(317102) or (317107)	

A-15 - 1

Nordson Engineering Hot Melt Products (sorted by Model)

Miscellaneous

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Cartridge Preheater for Hot Melt Cartridges	FR GE SP	213084A 405022A 7105696A	MA	(317102) or (317107)	
	Constant Pressure Controller 7183101	EN GE	7560365_01 7560303_01	MA	(317102) or (317107)	
	Elastics Positioning Unit	DA EN FR GE IT	213754C 213556C 213572C 213497C 213552C	MA	(317102) or (317107)	
	Glossary	CH CR CZ DA DU EN FI FR GE GR HU IT JA NO PL PO RO RU SK SP SW TU	7119980B 7580039B 447718B 407128B 407129B 407130B 407131B 407132B 407020B 213835B* 7105473B 407133B 409386B 407134B 7105207B 407135B 7135552B 7156949B 7105456B 407136B 407137B 397107B	MA	(317102) or (317107)	* = SAP P/N 231835!

A-15 - 2

Nordson Engineering Hot Melt Products (sorted by Model)

Miscellaneous

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	General Application Materials Processing Instructions	CZ DA DU EN FI FR GE GR HU IT JA NO PL PO RU SK SP SW TU	464718A 405144A 405145A 405146A 405147A 405148A 405149A 407300A 7105470A 405150A 405167A* 405151A 7105299A 405152A 407301A 7105453A 405153A 405154A 397104A	MA	(317102) or (317107)	* available at Nordson K.K.

A-15 - 3

Nordson Engineering Hot Melt Products (sorted by Model)

Miscellaneous

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	General Application Materials Processing Instructions (With instructions regarding PUR application materials)	CH CR CZ DA DU EN FI FR GE GR IT JA NO PL PO RO RU SP SW	7119977B 7580043_03 447716B 405155B 405156B 405157_03 405158B 405159B 405160_03 407290B 405161B 7146140B 405162B 7105205B 405163B 7135551B 407293B 405164B 405165B	MA	(317102) or (317107)	

A-15 - 4

Nordson Engineering Hot Melt Products (sorted by Model)

Miscellaneous

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Safety Instructions (for Hot Melt Application Systems)	BU CH CR CZ DA DU EN ES FI FR GE GR HU IT JA LI NO PL PO RO RU SK SL SP SW TU	7560793_02 7119981_02 7580044_02 7105758_02 7105749_02 7105750_02 7105744_02 7146248A 7105752_02 7105745_02 7105743_02 7105759_02 7105760_02 7105746_02 7146141_02 7560792_02 7105751_02 7105761_02 7105748_02 7135615_02 7105762_02 7105763_02 7105792_02 7105747_02 7105753_02 7119676_02	MA	(317102) or (317107)	
	Safety Instructions for Adhesive and Sealing Material Application Systems	DU EN FR GE IT PO SP SW	407382A 407383A 407384A 407385A 407386A 407387A 407388A 407389A	MA	(317102) or (317107)	

A-15 - 5

Nordson Engineering Hot Melt Products (sorted by Model)

Miscellaneous

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Safety Instructions for Adhesive and Sealing Material Application Systems (PUR)	CH DU EN FR GE IT PO SK SP SW	412918A 407390A 407391A 407392A 407393A 407394A 407395A 213601A 407396A 407397A	MA	(317102) or (317107)	
	Test Bench (P) and Test Bench Classic (P)	EN GE HU IT PL	7146589D 7146406D 7179990D 7156745D 7560085D	MA	(317102) or (317107)	
508	Water Recooler 508	EN FI FR GE IT JA PO SP	403063D 409020D 403071D 403036D 464844D 464984D* 464788D 403070D	MA	(317102) or (317107)	* available at Nordson K.K.
GF 200	Metering Pump Flange Station GF 200	EN FR GE IT PO SP	409087D 409351D 315739E 397218E 213381D 409088D	MA	(317102) or (317107)	
GP ...	Metering Pump Station GP...	FR GE IT	412804A 412770A 412808A	MA	(317103) or (317106)	

A-15 - 6

Nordson Engineering Hot Melt Products (sorted by Model)

Miscellaneous

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
GP 200	Metering Pump Station GP 200	CH DU EN FR GE IT PO SP TU	7119921E 213498E 405125_07 403298F 403116_07 409230_07 7105135D 213234F 7560658_07	MA	(317103) or (317106)	When ordering, please state Unit Type and Serial Number
GP 200 (Mini)	Gear Metering Pump Station GP 200 (Mini)	CZ DA DU EN FR GE HU IT JA PL PO RU SK SL SP SW TU	7580142_04 7580093_04 7119286_04 7105523_04 7146258_04 7105509_04 7560685_04 7105526_04 7169359C** 7119094_04 7560380_04 7560675_04 7105595_04 7146610_04 7119599_04 7105525_04 7192926_04	MA	(317102) or (317107)	** available at Nordson K.K.
GP 200 BC 62	SERIES GP 200 / BC 62 Hot Melt Metering and Application System	EN GE	267966 267953	OP	(317102) or (317107)	When ordering, please state Unit Type and Serial Number
P 103	Metering Pump Station P 103	EN GE IT	403050A 403051A 403064A	MA	(317102) or (317107)	When ordering, please state Unit Type and Serial Number

A-15 - 7

Nordson Engineering Hot Melt Products (sorted by Model)

Miscellaneous

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
PS Midi	Pump Station	CZ DU EN GE IT PL	7179965_04 7179882_01 7179718_03 7169754_04 7179774_01 7179989_04	MA	(317103) or (317106)	
PG...	Heated Hoses PG ...	EN GE	317163B 315825B	MA	(317102) or (317107)	
TC..	Heated Hoses TC ...	CH CZ DA DU EN FI FR GE GR HU IT JA NO PL PO RU SK SL SP SW TU	7119853H 464742H 405232H 317046G01 317044H 403072G01 317045H 267969H 213839H 7105484G01 315909G01 7119930G 317058H 7105306H 317047H 7146001H 7105390H 7146517G01 317075H 317048H 397123H	MA	(317102) or (317107)	

B-1 - 1

Nordson US Hot Melt Products (sorted by Model) *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Fulfill Retrofit Kits - for Non-ProBlue Melters	GE PL	7560726_02 7560712_02	MA	(317102) or (317107)	EN - 1124683_02 - Issued 12/15
	ATS Retrofit Kit for Hot Melt Adhesive Systems	FR GE IT SP	7580114_01 7580115_01 7580116_01 7580117_01	MA	(317102) or (317107)	EN - 1125511_01 - Issued 05/17
AltaBlue	AltaBlue Adhesive Melters - Models 15, 30, 50, and 100	CH DU FR GE HU IT JA PO RU SP	7401317_04 7179004A07 7135269A03 7135253A07 7135270A03 7135306A03 7135385A 7135266A03 7146335A03 7135331A03	MA	(317103) or (317106)	EN - 1072086A07 - Issued 03/14
AltaBlue PLC	AltaBlue PLC Series Adhesive Melters - Safety	EN/FR/ GE/IT/ PO/SP/ CH/JA	1125535_01	OP	(317102) or (317107)	Multilingual document, therefore one P/N only Issued 12/16
AltaBlue Touch	AltaBlue Touch Adhesive Melters	CH FR GE IT JA PL PO SK SP	7403725A_01 7179029_04 7179017_04 7179022_04 7179015_01 7192767_04 7179024_04 7580168_04* 7179023_04	MA	(317103) or (317106)	EN - 1120350_04 - Issued 03/14 * = not yet released

B-1 - 2

Nordson US Hot Melt Products (sorted by Model) *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
AltaBlue Touch	AltaBlue Touch Series Quick Reference Card	FR GE IT JA PO SP	7169920_01 7169928_01 7169945_01 7169953_01 7169961_01 7169936_01	OP	(317102) or (317107)	EN - 1120352_01 - Issued 02/12
AltaBlue Touch	External Pressure Transducer Kit	FR GE IT JA PO SP	7169925_01 7169933_01 7169950_01 7169958_01 7169966_01 7169941_01	IN	(317102) or (317107)	EN - 1120582_01 - Issued 04/12
AltaBlue Touch	Flow Meter and Encoder Kits	FR GE IT JA PO SP	7169923_01 7169931_01 7169948_01 7169956_01 7169964_01 7169939_01	IN	(317102) or (317107)	EN - 1120580_01 - Issued 04/12
AltaBlue Touch	Flow/Pressure Control and Monitoring	CH GE JA PO SP	7403723_01 7169934_02 7169960_02 7169969_01 7169944_02	MA	(317102) or (317107)	EN - 1120351_02 - Issued 05/12
AltaBlue Touch	Flow/Pressure Option Board for Control and/or Monitoring - P/Ns 7403137 and 7403138	FR GE IT JA PO SP	7169924_01 7169932_01 7169949_01 7169957_01 7169965_01 7169940_01	IN	(317102) or (317107)	EN - 1120581_01 - Issued 04/12

B-1 - 3

Nordson US Hot Melt Products (sorted by Model) *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
AltaBlue Touch	Remote Visual System for 1 AltaTouch Melter - P/N 7403151 (24 ft cable)	FR GE IT JA PO SP	7169921_01 7169929_01 7169946_01 7169954_01 7169962_01 7169937_01	IN	(317102) or (317107)	EN - 1120586_01 - Issued 04/12
AltaBlue Touch	Remote Visual System for 1-5 AltaTouch Melter - P/N 7403152 (50 ft cable) and P/N 7403153 (100 ft cable)	FR GE IT JA PO SP	7169922_01 7169930_01 7169947_01 7169955_01 7169963_01 7169938_01	IN	(317102) or (317107)	EN - 1120393_01 - Issued 04/12
AltaBlue TT	AltaBlue TT Adhesive Melters - Models A4, A10, and A16	CH CZ DU FR GE HU IT JA PL RU SP	7401336 7156544A04 7156545A 7156546A 7156474A04 7156540A 7156547A04 7156552A 7156541A 7156542A 7156543A04	MA	(317103) or (317106)	EN - 1095085A04 - Issued 03/14
AltaBlue TT QR	AltaBlue TT Quick Reference Guide	EN/CZ DUI/FR/ /GE/HU /IT/PL/ RU/SP/ CH/JA	1124571_01	OP	(317102) or (317107)	Multilingual document, therefore one P/N only Issued 07/15
AltaBlue/ DuraBlue	Fulfill Retrofit Kit for AltaBlue TT and DuraBlue D10/ D16 Melters	FR GE IT JA SP	7156839A 7156837A 7156843A 7169644A* 7156841A	MA	(317102) or (317107)	EN - 1102240A - Issued 01/13 -> Replaced by P/N 1121940_01 * available at Nordson K.K.

B-1 - 4

Nordson US Hot Melt Products (sorted by Model) *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
AltaBlue/ DuraBlue	Fulfill Retrofit Kit for AltaBlue TT and DuraBlue D10/ D16 Melters	FR GE IT SP	7179753_01 7179754_01 7179755_01 7179756_01	MA	(317102) or (317107)	EN - 1121940_02 - Issued 5/13
DuraBlue	DuraBlue Adhesive Melters - Models D10 and D16	CH DA DU FI FR GE IT JA NO PL PO SP SW	7119827A 397774B 397778B 397509B 213729B 213717B 213727B 7119828A 397869B 7105855B 397482B 213715B 397674B	MA	(317103) or (317106)	EN - 1028347B - Issued 07/03
DuraBlue	DuraBlue Adhesive Melters - Models D4L, D10L, and D16L (Gerotor)	CH CZ DA DU FI FR GE HU IT JA NO PL PO RO RU SP SW	7401350 397994B 397775B 397779B 397510B 213730B 213718B 7146346A02 213728B 7105883A 397870B 7105969_05 397483B 7560786A05 7105350A 213716B 397675B	MA	(317103) or (317106)	EN - 1032059B -> Replaced by P/N 1073401A05 Issued 03/14

B-1 - 5

Nordson US Hot Melt Products (sorted by Model) *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
DuraBlue	DuraBlue Adhesive Melters D4F	GE SP	7119864A03 7119865A03	MA	(317103) or (317106)	EN - 1065648A09 - Issued 03/14
DuraBlue	Pedestal for DuraBlue™ 4F	EN GE	7146384A 7146383A	MA	(317102) or (317107)	N - Benelux BV Issued 01/08
DuraBlue/ VersaBlue	Fulfill Retrofit Kit - DuraBlue/VersaBlue 25L and 50L Melters	FR GE IT SP	7169241A 7169246A 7169252A 7169257A	MA	(317102) or (317107)	EN - 1105309A - Issued 02/11
DuraBlue/ VersaBlue	Fulfill Retrofit Kit for 100-Liter DuraBlue and VersaBlue Adhesive Melters	FR GE IT SP	7169201A 7169220A 7169214A 7169218A	MA	(317102) or (317107)	EN - 1106395A - Issued 02/11
DuraBlue/ VersaBlue	DB/VB 25 and 50 Fulfill- Lid Replacement - P/N 1123139 and 1123140	PL	7560539_01	IN	(317102) or (317107)	EN - 1123432_01 - Issued 02/14
DeviceNet	Profibus-DP, DeviceNet, and ControlNet Fieldbus Interface Cards	FR GE IT JA PO SP	7169926_04 7119831_04 7169951_04 7119808_04 7169967_04 7169942_04	MA	(317102) or (317107)	EN - 1052255_04 - Issued 05/12
Ethernet	Ethernet/IP Fieldbus Interface Card	FR GE IT JA PO SP	7169927_04 7119340_04 7119739_04 7119807_04 7169968_04 7169943_04	MA	(317102) or (317107)	EN - 1054600_07 - Issued 05/16

B-1 - 6

Nordson US Hot Melt Products (sorted by Model) *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
ProBlue	ProBlue Fulfill Integrated Fill System (Generation III)	CZ DU FI FR GE IT RU SP	7179580_02 7179586_02 7179595_02 7179603_02 7179578_02 7179588_02 7179590_02 7179593_02	MA	(317102) or (317107)	EN - 1121787_02 - Issued 5/13
ProBlue	ProBlue Fulfill Integrated Fill System (Generation IV)	CH FR GE IT JA SP	7192528_01 7192483_01 7192446_01 7192451_01 7192427_01 7192442_01	MA	(317102) or (317107)	EN - 1123107_01 - Issued 4/15 Issue date of translations 03/14
ProBlue	FulFill Retrofit Kit ProBlue Melters	FR GE IT SP SW	7560636_02 7560637_02 7560638_02 7560639_02 7580084_03	MA	(317102) or (317107)	EN - 1124682_03 - Issued 11/16
ProBlue	ProBlue Adhesive Melter Pump Replacement Kit P/N 1028303, 1058305, and 1058306 (Title version A: Pump Service Kit - P/N 1028303)	DA DU FI FR GE IT NO PO SL SP SW	397600A 397581A 397806A 397780A 397562A 397683A 397654A 397617A 7105834A 397700A 397636A	IN	(317102) or (317107)	EN - 1029711B - Issued 02/05

B-1 - 7

Nordson US Hot Melt Products (sorted by Model) *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
ProBlue	ProBlue Pneumatic Panel Assembly Service Kit - P/N 1028307, 1058380, 1058383, or 1058385 (Title version A : Pneumatic Panel Assembly Service Kit - P/N 1028307)	DA DU FI FR GE IT NO PO SL SP SW	397601A 397582A 397807A 397781A 397563A 397684A 397655A 397618A 7105835A 397701A 397637A	IN	(317102) or (317107)	EN - 1029713B - Issued 02/05
ProBlue	ProBlue Pressure Discharge Valve Service Kit - P/N 1028308	DA DU FI FR GE IT NO PO SL SP SW	397602A 397583A 397808A 397782A 397564A 397685A 397656A 397619A 7105836A 397702A 397638A	IN	(317102) or (317107)	EN - 1029714B02 - Issued 07/10
ProBlue	Manifold Service Kit P/Ns 1064651, 1064652, 1064653, 1064654, 1125302, 1125303, 1125308, 1125309 (Title Version B: Manifold Replacement Kit - P/Ns 1064651, 1064652, 1064653, and 1064654)	JA	7135023B	IN	(317102) or (317107)	EN - 1049668_04 - Issued 09/16

B-1 - 8

Nordson US Hot Melt Products (sorted by Model) *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
ProBlue	ProBlue Manifold Service Kit - P/N 1028309	DA DU FI FR GE IT NO PO SL SP SW	397603A 397584A 397809A 397783A 397565A 397686A 397657A 397620A 7105837A 397703A 397639A	IN	(317102) or (317107)	EN - 1029715_02 - Issued 08/11
ProBlue	RTD Service Kit - P/N 1028320	DA DU FI FR GE IT NO PO SL SP SW	397604A 397585A 397810A 397784A 397566A 397687A 397658A 397621A 7105838A 397704A 397640A	IN	(317102) or (317107)	EN - 1029716B02 - Issued 02/08
ProBlue	ProBlue Melter Main Circuit Board Service Kit - P/N 1028322	DA DU FI FR GE IT NO PO SL SP SW	397606A 397587A 397812A 397786A 397568A 397689A 397660A 397623A 7105840A 397706A 397642A	IN	(317102) or (317107)	EN - 1029718A - Issued 2002

B-1 - 9

Nordson US Hot Melt Products (sorted by Model) *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
ProBlue	ProBlue 10 Main Circuit Board Service Kit - P/N 1028323	DA DU FI FR GE IT NO PO SL SP SW	397607A 397588A 397813A 397787A 397569A 397690A 397661A 397624A 7105841A 397707A 397643A	IN	(317102) or (317107)	EN - 1029719A - Issued 2002
ProBlue	6-Hose Extension Board Kit - P/N 1028324	DA DU FI FR GE IT NO PO SL SP SW	397608A 397589A 397814A 397788A 397570A 397691A 397662A 397625A 7105842A 397708A 397644A	IN	(317102) or (317107)	EN - 1029720A - Issued 2002
ProBlue	Operator's Panel/Enclosure Service Kit - P/N 1028326	DA DU FI FR GE IT NO PO SL SP SW	397610A 397591A 397816A 397790A 397572A 397693A 397664A 397627A 7105844A 397710A 397646A	IN	(317102) or (317107)	EN - 1029722A - Issued 2002

B-1 - 10

Nordson US Hot Melt Products (sorted by Model) *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
ProBlue	ProBlue P10/P15/P30 and P50 Operator's Panel Service Kit - P/N 1028327 (Title version A: Operator's Panel/Enclosure Service Kit - P/N 1028327)	DA DU FI FR GE IT NO PO SL SP SW	397611A 397592A 397817A 397791A 397573A 397694A 397665A 397628A 7105845A 397711A 397647A	IN	(317102) or (317107)	EN - 1029723B - Issued 02/05
ProBlue	Hose/Gun Module Service Kit - P/N 1028328	DA DU FI FR GE IT NO PO SL SP SW	397612A 397593A 397818A 397792A 397574A 397695A 397666A 397629A 7105846A 397712A 397648A	IN	(317102) or (317107)	EN - 1029724A - Issued 2002
ProBlue	Level Switch Service Kit, ProBlue - P/N 1038971, 1038972, 1060329, 1059911, 1060362, 1097366, and 1099690 (Title version A: Level Switch Service Kit, ProBlue - P/N 1038971 and 1038972)	DA DU FI FR GE IT NO PO SL SP SW	397615A 397596A 397821A 397795A 397577A 397698A 397669A 397632A 7105849A 397715A 397651A	IN	(317102) or (317107)	EN - 1038989B02 - Issued 01/10

B-1 - 11

Nordson US Hot Melt Products (sorted by Model) *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
ProBlue	6-Hose Manifold Guard Kit - P/N 1031871	DA DU FI FR GE IT NO PO SL SP SW	397616A 397597A 397822A 397796A 397578A 397699A 397670A 397633A 7105850A 397716A 397652A	IN	(317102) or (317107)	EN - 1055774A - Issued 2003
ProBlue P4/ P7/ P10	ProBlue Adhesive Melters Model P4, P7, and P10	CH CR/SE CZ DA DU FI FR GE GR HU IT JA LA LI NO PL PO RO RU SK SL SP SW	7119829_05 7179355_05 7119036_05 397262_05 397022_05 213918_05 213533_07 213544_07 397183B 7105608A** 213548_07 7119830_05 7192984_06 7560036_06 397281_05 397443_06 397257_05 7135063_05 7105117B 7146687_05 7105833_05 213570_07 397258_07	MA	(317103) or (317106)	EN - 1024496_07 - Issued 02/16 ** = Abridged edition, document and translation is NOT issued by TDLL !

B-1 - 12

Nordson US Hot Melt Products (sorted by Model) *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Pro Blue P4 /P7/ P10	FulFill Retrofit Kit ProBlue 4/7/10 Melters (Generation II)	CZ FI FR GE IT JA PL RU SP	7169405A 7169301A 7156550A 7156537A 7156538A 7169175A* 7169244A 7169711A 7156539A	MA	(317102) or (317107)	EN - 1098477A - Issued 1/10 * available at Nordson K.K.
ProBlue P10/ P15	ProBlue P10 and P15 8-Hose/Gun Expansion Base	FR GE JA SP	7119691A 7119698A 7119715A* 7119695A	MA	(317102) or (317107)	EN - 1063727B - Issued 04/06 * available at Nordson K.K
ProBlue P15/ 30/ 50	ProBlue Adhesive Melter Model P15, P30, and P50	CZ DA DU FI FR GE IT JA LA LI NO PL PO RO RU SK SP SW	7146688B02 7105904B 7105903B 7105988B 7105899B 7105913_07 7105901B 7105882_05 7192746_06 7169829_05 7105908B 7156734_05 7105914B 7169842_06 7169365_05 7156929_05 7105922B 7105905B	MA	(317103) or (317106)	EN - 1058683_07 - Issued 01/17

B-1 - 13

Nordson US Hot Melt Products (sorted by Model) *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
ProBlue P15/ 30/ 50	Fulfill Retrofit ProBlue 15 and 30/50 Melters (Generation II)	CZ FR GE IT JA SP	7169406A 7156838A 7156836A 7156842A 7169643A* 7156840A	MA	(317103) or (317106)	EN - 1102228A - Issued 01/13 Issue date of translations 08/10 * available at Nordson K.K
ProBlue ATS	ProBlue ATS and ProBlue Liberty ATS Hot Melt Adhesive Systems	FR GE IT JA PL RO SP	7560847_03 7560848_03 7560849_03 7580167_03* 7580102_03 7560941_03 7560850_03	MA	(317103) or (317106)	EN - 1125291_03 - Issued 10/16 * available at Nordson K.K
ProBlue/ DuraBlue	Software Service Kit - P/N 1018817	DA DU FI FR GE IT NO PO SL SP SW	397613A 397594A 397819A 397793A 397575A 397696A 397667A 397630A 7105847A 397713A 397649A	IN	(317102) or (317107)	EN - 1029725A - Issued 2002

B-1 - 14

Nordson US Hot Melt Products (sorted by Model) *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
ProBlue/ DuraBlue/ AltaBlue/ DuraPail/Drum /Mesa/ AltaTouch	Input/Output Expansion Card Kit - P/N 1036607	DA DU FI FR GE IT JA NO PO SL SP SW	397614A 397595A 397820A 397794_05 397576_05 397697_05 7169959_05 397668A 397631_05 7105848A 397714_05 397650A	IN	(317102) or (317107)	EN - 1036221_05 - Issued 05/12
ProBlue/ DuraBlue/ DuraPail/ Mesa	Display/CPU Board Service Kit - P/Ns 1028325 and 1104492 (Title version B: CPU Board Service Kit - P/N 1028325)	DA DU FI FR GE IT NO PO SL SP SW	397609B 397590B 397815B 397789B 397571B 397692B 397663B 397626B 7105843B 397709B 397645B	IN	(317102) or (317107)	EN - 1029721C03 - Issued 10/10
ProBlue/ ProBlue Liberty/ DuraBlue Mesa	ProBlue, ProBlue Liberty, DuraBlue, or Mesa Thermostat Service Kit - P/N 1028321 (Title version B: ProBlue and DuraBlue Thermostat Service Kit - P/N 1028321)	DA DU FI FR GE IT NO PO SL SP SW	397605B 397586B 397811B 397785B 397567B 397688B 397659B 397622B 7105839B 397705B 397641B	IN	(317102) or (317107)	EN - 1029717_06 - Issued 05/14

B-1 - 15

Nordson US Hot Melt Products (sorted by Model) *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
ProBlue/ DuraBlue/ DuraDrum/ DuraPail	Instructions for adapter cable (P/N 7114262)	EN/ FR/ GE/ IT	7119096G	IN	(317102) or (317107)	Multilingual document, therefore one P/N only Issued 10/09
ProBlue/ DuraBlue/	ProBlue DuraBlue Adhesive Melters - User's Guide	CH/DA/ EN/FI/ FR/GE/ IT/JA/ NO/SP/ SW	1024497B02	OP	(317102) or (317107)	Multilingual document, therefore one P/N only Issued 10/08
ProBlue/ DuraBlue/ AltaBlue TT	ProBlue DuraBlue AltaBlue TT Adhesive Melters - User's Guide	BU/CZ/ EN/GE/ GR/HU/ PL/RO/ RU/TU/ CR	1091164_03	OP	(317102) or (317107)	Multilingual document, therefore one P/N only Issued 12/12
ProBlue QR	ProBlue Series Quick Reference Guide	EN/DA/ FI/FR// GE/IT/ NO/PO/ SP/SW/ CH/JA	1124526_02	-	(317102) or (317107)	Multilingual document, therefore one P/N only Issued 02/16
ProBlue Liberty	ProBlue Liberty Hot Melt Adhesive System	CH CZ DU FR GE IT JA PL RU SP SW	7192585_01 7192899_01 7560094_01 7192593_01 7192589_01 7192588_01 7192586_01 7192833_01 7560029_01 7192636_01 7560605_01	MA	(317102) or (317107)	EN - 1123388_01 - Issued 07/15 Issue date of translations 05/14 Obsolete! Replaced by P/N 1124685_02

B-1 - 16

Nordson US Hot Melt Products (sorted by Model) *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
ProBlue Liberty	ProBlue Liberty Hot Melt Adhesive System	RO	7580120_02	MA	(317102) or (317107)	EN - 1124685_02 - Issued 12/15
ProBlue Liberty	ProBlue Liberty System Calibration Warning	EN/CZ DU/FR/ GE/IT/ PL/SP/ CH/JA	1124822_01	-	(317102) or (317107)	<i>Multilingual</i> document, therefore one P/N only Issued 12/15
ProBlue Liberty QR	ProBlue Liberty System Quick Reference	EN/CZ DU/FR/ GE/IT/ PL/RU/ SP/CH/ JA	1124779_01	-	(317102) or (317107)	<i>Multilingual</i> document, therefore one P/N only Issued 12/15
ProBlue Liberty QR	ProBlue Liberty System Quick Reference	EN/CR/ HU/SE/ SL	7560985_01	-	(317102) or (317107)	EN - 1124779_01 <i>Multilingual</i> document, therefore one P/N only Issued 12/15
PURBlue	PURBlue 4 Adhesive Melter	CZ DA DU FR GE IT PL PO RU SL SP SW	7169674_03 7169746_03 7156412_04 7156403A 7156404_04 7156401_04 7156708A03 7156421A 7179571_03 7169631_03 7156408A 7156405A	MA	(317102) or (317107)	EN - 1098452_04 - Issued 11/13

B-1 - 17

Nordson US Hot Melt Products (sorted by Model) *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
PURBlue	PURBlue 4 Adhesive Melter Upgrade Kit - P/N 1120270	CZ FR GE IT PL PO SP	7169879_01 7169881_01 7169872_01 7169870_01 7169886_01 7169861_01 7169859_01	IN	(317102) or (317107)	EN - 1120277_01 - Issued 03/12
PURBlue	PURBlue 4 High-Output Adhesive Melter	CZ FR GE IT PL PO SP	7169878_01 7169880_01 7169871_01 7169869_01 7169885_01 7169860_01 7169858_01	MA	(317102) or (317107)	EN - 1120255_01 - Issued 01/13 Issue date of translations 02/12

B-2 - 1

Nordson US Hot Melt Products (sorted by Model) Series 3000V (Vista)

Model	Product Title	CE	Langs.	P/N	Type	Price Category	Notes
Series 3000V	Series 3000V Low Level Indicator		GE	213634A	IN	(317102) or (317107)	Source: EN: 237473A
Series 3000V	Series 3000 V Input/Output Board		GE	405199K	IN	(317102) or (317107)	Source EN: 229823K
Series 3000V	Pressure Dump Valve Service Kit for Series 3000 Vista Units		GE	409325A	IN	(317102) or (317107)	Source EN: 237479A
Series 3000V	Vista Control Guide		FR	458162B	OP	(317102) or (317107)	Source EN: 321213B
Series 3000V	Vista Profibus Gateway Interface User's Guide		GE	397917A_02	MAN	(317102) or (317107)	Source EN: 321288A_02 - Issued 03/02

B-2 - 2

Nordson US Hot Melt Products (sorted by Model) Series 3000V (Vista)

Model	Product Title	CE	Langs.	P/N	Type	Price Category	Notes
Series 3100V-PC	SERIES 3100V Hot Melt Material Applicator with 6:1 / 14:1 SP30 Piston Pump and Pattern Controller	Y	DA DU FI FR GE IT NO PL PO SP SW	403170E 403171E 403172A 403173E 403174E 403175E 403176E 458299E 403177A 403178E 403179E	MA Part O and Part A	(317103) or (317106)	Source <i>Manual Config. Codes</i> EN: 248449 3100V-XEAPXX/X EN: 248450 3100V-XGAPXX/X Appropriate OP card included
Series 3100V-TC (Tetra)	SERIES 3100V Hot Melt Material Applicator with 14:1 SP Piston Pump and VistaTemperature Controller	Y	DA DU FI FR GE GR IT NO PL PO SP SW	409264E 403127E 409265E 409266E 409267E 213450G02 409268E 409269E 7119851H 409270E 409271E 409272E	MA Part O and Part A	(317103) or (317106)	Source <i>Manual Config. Codes</i> EN: 272381H 3100V-XEATXX/4 Appropriate OP card included

B-2 - 3

Nordson US Hot Melt Products (sorted by Model) Series 3000V (Vista)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Series 3100V-VC	SERIES 3100V Hot Melt Material Applicator with 6:1 / 14:1 SP30 Piston Pump and Vista Controller	DA DU FI FR GE IT NO PL PO SP SW	403160E 403169E 403161E 403162E 403163E 403164E 403165E 412793E 403166A 403167E 403168E	MA Part O and Part A	(317103) or (317106)	Source <i>Manual Config. Codes</i> EN: 237346 3100V-XEAVXX/X EN: 244943 3100V-XGAVXX/X Appropriate OP card included
Series 3100V-PC / 3400V-PC	Series 3100V/3400V Hot Melt Material Applicator with AC Constant-Speed Gear Pump, Standard Filter, Pattern Control	DA DU FI FR GE IT NO PO SP SW	407352A 407353A 407354A 407355A 407356A 407357A 407358A 407359A 407360A 407361A	OP	(317102) or (317107)	Source EN: 237532A
Series 3100V-VC / 3400V-VC	Series 3100V/3400V Hot Melt Material Applicator with AC Constant-Speed Gear Pump, Standard Filter, Standard Control	DA DU FI FR GE IT NO PO SP SW	407342A 407343A 407344A 407345A 407346A 407347A 407348A 407349A 407350A 407351A	OP	(317102) or (317107)	Source EN: 237531A

B-2 - 4

Nordson US Hot Melt Products (sorted by Model) Series 3000V (Vista)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Series 3100V-TC / 3400V-TC / 3500V-TC	Series 3100V/3400V/3500V Hot Melt Material Applicator with Piston Pump, Standard Filter, Temperature Control (TC)	DA DU FI FR GE GR IT NO PL PO SP SW	407075B 407076B 407077B 407078B 407079B 213451B 407080B 407081B 458341B 407082B 407083B 407084B	OP	(317102) or (317107)	Source EN: 237518B
Series 3100V-TC / 3400V-TC / 3500V-TC (TCGM)	SERIES 3100V, 3400V, 3500V Hot Melt Material Applicator with 6:1 / 14:1 SP30 Piston Pump and Temperature Controller	DA DU FI FR GE IT NO PO SP SW	409254E 409255E 409256E 409257E 409258E 409259E 409260E 409261E 409262E 409263E	MA Part O and Part A	(317103) or (317106)	Source <i>Manual Config. Codes</i> EN: 309734 3100V-XEATXX/X EN: 310647 3400V-XEATXX/X EN: 310713 3500V-XEATXX/X EN: 273193 3100V-XGATXX/X EN: 248451 3400V-XGATXX/X EN: 309662 3500V-XGATXX/X Appropriate OP card included
Series 3100V-PC / 3400V-PC / 3500V-PC / 3700V-PC	Series 3100V/3400V/3500V/3700V Hot Melt Material Applicator with Piston Pump, Standard Filter, Pattern Control	DA DU FI FR GE IT NO PL PO SP SW	403151C 403224C 403152C 403153C 403154C 403155C 403156C 412787C 403157C 403158C 403159C	OP	(317102) or (317107)	Source EN: 237379C

B-2 - 5

Nordson US Hot Melt Products (sorted by Model) Series 3000V (Vista)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Series 3100V-VC / 3400V-VC / 3500V-VC / 3700V-VC	Series 3100V/3400V/3500V/3700V Hot Melt Material Applicator with Piston Pump, Standard Filter, Standard Control	DA DU FI FR GE GR IT NO PL PO RU SP SW	403147C 403223C 403148C 403124C 403118C 213419C 403136C 403149C 412788C 403129C 409176C 403121C 403150C	OP	(317102) or (317107)	Source EN: 229777C
Series 3400V-PC	SERIES 3400V Hot Melt Material Applicator with 6:1 / 14:1 SP30 Piston Pump and Pattern Controller	DA DU FI FR GE IT NO PO SP SW	403190E 403191E 403192A 403193E 403194E 403195E 403196E 403197A 403198E 403199E	MA Part O and Part A	(317103) or (317106)	Source <i>Manual Config. Codes</i> EN: 248446 3400V-XEAPXX/X EN: 248447 3400V-XGAPXX/X Appropriate OP card included
Series 3400V-VC	SERIES 3400V Hot Melt Material Applicator - with AC Constant-Speed Gear Pump and Vista Controller	GE	447639E	MA Part O and Part A	(317103) or (317106)	Source <i>Manual Config. Codes</i> EN: 237681E 3400V-XKJVXX/X EN: 273280E 3400V-XLJVXX/X

B-2 - 6

Nordson US Hot Melt Products (sorted by Model) Series 3000V (Vista)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Series 3400V-VC	SERIES 3400V Hot Melt Material Applicator with 6:1 / 14:1 SP30 Piston Pump and Vista Controller	DA DU FI FR GE IT NO PL PO SP SW	403180E 403181E 403182A 403183E 403184E 403185E 403186E 458338E 403187A 403188E 403189E	MA Part O and Part A	(317103) or (317106)	Source <i>Manual Config. Codes</i> EN: 237347 3400V-XEAVXX/X EN: 243590 3400V-XGAVXX/X Appropriate OP card included
Series 3500V-PC	SERIES 3500V Hot Melt Material Applicator with 6:1 / 10:1 / 14:1 / 21:1 SP30 Piston Pump and Pattern Controller	DA DU FI FR GE IT NO PO SP SW	403210E 403211E 403212A 403213E 403214E 403215E 403216E 403217A 403218E 403219E	MA Part O and Part A	(317103) or (317106)	Source <i>Manual Config. Codes</i> EN: 331237 3500V-XDAPXX/X EN: 272412 3500V-XEAPXX/X EN: 276140 3500V-XFAPXX/X EN: 288000 3500V-XGAPXX/X Appropriate OP card included
Series 3500V-VC	SERIES 3500V Hot Melt Material Applicator with 6:1 / 10:1 / 14:1 / 21:1 SP30 Piston Pump and Vista Controller	GE PL	213566E 464809E	MA Part O and Part A	(317103) or (317106)	Source <i>Manual Config. Codes</i> EN: 331245E 3500V-XDBVXX/X EN: 331203E 3500V-XEBVXX/X EN: 331206E 3500V-XFBVXX/X EN: 331208E 3500V-XGBVXX/X Appropriate OP card included

B-2 - 7

Nordson US Hot Melt Products (sorted by Model) Series 3000V (Vista)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Series 3500V-VC	SERIES 3500V Hot Melt Material Applicator with 6:1 / 10:1 / 14:1 / 21:1 SP30 Piston Pump and Vista Controller	DA DU FI FR GE IT NO PL PO SP SW	403200E 403201E 403202A 403203E 403204E 403205E 403206E 458339E 403207A 403208E 403209E	MA Part O and Part A	(317103) or (317106)	Source <i>Manual Config. Codes</i> EN: 331236 3500V-XDAVXX/X EN: 237348 3500V-XEAVXX/X EN: 240813 3500V-XFAVXX/X EN: 248432 3500V-XGAVXX/X Appropriate OP card included
Series 3500V-PC / 3700V-PC	Series 3500V/3700V Hot Melt Material Applicator with Piston Pump, Reverse-Flush Filter, Pattern Control	DA DU FI FR GE IT NO PO SP SW	407065B 407066B 407067B 407068B 407069B 407070B 407071B 407072B 407073B 407074B	OP	(317102) or (317107)	Source EN: 237506B
Series 3500V-VC / 3700V-VC	Series 3500V/3700V Hot Melt Material Applicator with Piston Pump, Reverse-Flush Filter, Standard Control	DA DU FI FR GE IT NO PO SP SW	407055B 407056B 407057B 407058B 407059B 407060B 407061B 407062B 407063B 407064B	OP	(317102) or (317107)	Source EN: 237505B

B-2 - 8

Nordson US Hot Melt Products (sorted by Model) Series 3000V (Vista)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Series 3700V-VC	SERIES 3700V Hot Melt Material Applicator with 6:1 / 10:1 / 14:1 / 21:1 SP30 Piston Pump and Vista Controller	DA DU FI FR GE IT NO PO SP SW	409244E 409245E 409246E 409247E 409248E 409249E 409250E 409251E 409252E 409253E	MA Part O and Part A	(317103) or (317106)	Source <i>Manual Config. Codes</i> EN: 331260 3700V-XDBVXX/X EN: 304985G02 3700V-XEBVXX/X EN: 309663 3700V-XFBVXX/X EN: 237634 3700V-XGBVXX/X Appropriate OP card included
Series 3800V-VC	SERIES 3800V Hot Melt Material Applicator with AC Constant-Speed Gear Pump and Vista Controller	GE IT	213449E 213347E	MA Part O and Part A	(317103) or (317106)	Source <i>Manual Config. Codes</i> EN: 237655E 3830V-XKJVXX/X EN: 237653E 3830V-XLJVXX/X
Series 3800V-PC / 3900V-PC	Series 3800V/3900V Hot Melt Material Applicator with AC Constant-Speed Gear Pump, Standard Filter, Pattern Control	DA DU FI FR GE IT NO PO SP SW	407372A 407373A 407374A 407375A 407376A 407377A 407378A 407379A 407380A 407381A	OP	(317102) or (317107)	Source EN: 237534A
Series 3800V-PC / 3900V-PC	Series 3800V/3900V Hot Melt Material Applicator with Piston Pump, Reverse-Flush Filter, Pattern Control	DA DU FI FR GE IT NO PO SP SW	407115B 407116B 407117B 407118B 407119B 407120B 407121B 407122B 407123B 407124B	OP	(317102) or (317107)	Source EN: 237528B

B-2 - 9

Nordson US Hot Melt Products (sorted by Model) Series 3000V (Vista)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Series 3800V-PC / 3900V-PC	Series 3800V/3900V Hot Melt Material Applicator with Piston Pump, Standard Filter, Pattern Control	DA DU FI FR GE IT NO PO SP SW	407095B 407096B 407097B 407098B 407099B 407100B 407101B 407102B 407103B 407104B	OP	(317102) or (317107)	Source EN: 237526B
Series 3800V-VC / 3900V-VC	Series 3800V/3900V Hot Melt Material Applicator with AC Constant-Speed Gear Pump, Standard Filter, Standard Control	DA DU FI FR GE IT NO PO SP SW	407362A 407363A 407364A 407365A 407366A 407367A 407368A 407369A 407370A 407371A	OP	(317102) or (317107)	Source EN: 237533A
Series 3800V-VC / 3900V-VC	Series 3800V/3900V Hot Melt Material Applicator with Piston Pump, Reverse-Flush Filter, Standard Control	DA DU FI FR GE IT NO PO SP SW	407105B 407106B 407107B 407108B 407109B 407110B 407111B 407112B 407113B 407114B	OP	(317102) or (317107)	Source EN: 237527B

B-2 - 10

Nordson US Hot Melt Products (sorted by Model) Series 3000V (Vista)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Series 3800V-VC / 3900V-VC	Series 3800V/3900V Hot Melt Material Applicator with Piston Pump, Standard Filter, Standard Control	DA DU FI FR GE IT NO PO SP SW	407085B 407086B 407087B 407088B 407089B 407090B 407091B 407092B 407093B 407094B	OP	(317102) or (317107)	Source EN: 237525B
Series 3860V-VC / 3890V-VC	SERIES 3800V Hot Melt Material Applicator with AC Constant-Speed Gear Pump and Vista Controller	FI GE IT SP	464903E 413035E 464778E 458191E	MA Part O and Part A	(317103) or (317106)	Source <i>Manual Config. Codes</i> EN: 237663E 3860V-XKJVXX/X EN: 237661E 3860V-XLJVXX/X EN: 237671E 3890V-XKJVXX/X EN: 237669E 3890V-XLJVXX/X Appropriate OP card included
Series 3860V-VC / 3890V-VC	SERIES 3800V Hot Melt Material Applicator with 21:1 SP30 Piston Pump and Vista Controller	DU FI FR GE	213519E 213302E 458200E 213064E	MA Part O and Part A	(317103) or (317106)	Source <i>Manual Config. Codes</i> EN: 309856E 3860V-XFAVXX/X EN: 310299E 3890V-XFAVXX/X Appropriate OP card included
Series 3860V-VC / 3890V-VC	SERIES 3800V Hot Melt Material Applicator with 21:1 SP30 Piston Pump and Vista Controller	FI FR SW	213229E 458169E 213304E	MA Part O and Part A	(317103) or (317106)	Source <i>Manual Config. Codes</i> EN: 237519E 3860V-XFBVXX/X EN: 323994E 3890V-XFBVXX/X Appropriate OP card included
Series 3900V-VC	SERIES 3900V Hot Melt Material Applicator with 21:1 SP30 Piston Pump and Vista Controller	FI FR GE	213303E 447770E 213184E	MA	(317103) or (317106)	Source <i>Manual Config. Codes</i> EN: 310301E 3960V-XFBVXX/X Appropriate OP card included

B-3 - 1

Nordson US Hot Melt Products (sorted by Model)

Series 2000 / Series 3000 / Series 5000 / Series 6000

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Series 2300	SERIES 2300 Hot Melt Applicators	DU EN FI FR GE IT SP SW	292732A 292731A 292735A 292733A 292734A 292736A 292737A 292776A	IN	(317102) or (317107)	
Series 2300	Fulfill Retrofit Kit Series 2300 Melters	FR GE IT SP	7169243A 7169248A 7169254A 7169259A	MA	(317102) or (317107)	EN - 1104162A - Issued 01/13 Obsolete!
Series 3000	Pressure Dump Valve Service Kit for Series 3000 Units	GE	409324B	IN	(317102) or (317107)	EN - 108838B
Series 3000	Fulfill Retrofit 3000 Series Melters	FR GE IT PL SP	7179622_01 7179623_01 7179624_01 7179626_01 7179628_01	MA	(317102) or (317107)	EN - 1121935_01 - Issued 04/13 Obsolete!
Series 3000 ACMs	Series 3000 ACMs	FR GE	447713A 447685A	MA	(317104) or (317105)	EN - 1001762A
Series 3100	SERIES 3100 Hot Melt Applicator with Gear Pump Each manual (MA) is composed of several parts, these have been listed under Notes.	DU FR GE IT SP	290956 290957 290958 290959 290960	MA	(317103) or (317106)	DU = 269831 OP, 284173 IN, RTD, H200 FR = 106531 OP, 284175 IN, RTD, H200 GE = 106532 OP, 284176 IN, RTD; H200 IT = 106533 OP, 284177 IN, RTD, H200 SP = 106534 OP, 284180 IN, RTD, H200
Series 3100	SERIES 3100 Hot Melt Applicator with Piston Pump / MultiScan	DU GE IT SP	269895 269894 269898 269899	MA	(317103) or (317106)	

B-3 - 2

Nordson US Hot Melt Products (sorted by Model)

Series 2000 / Series 3000 / Series 5000 / Series 6000

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Series 3100	SERIES 3100 Hot Melt Material Applicator with 14:1 SP Piston Pump, A Manifold, and MultiScan Controller	DU FR GE IT PL SP	284092 269897 284091 284094 412765C 284095	MA	(317103) or (317106)	EN - 106687C
Series 3100	SERIES 3100 Hot Melt Applicator with Piston Pump SP 30 14:1 / MultiScan Each manual (MA) is composed of several parts, these have been listed under Notes.	DU FR GE IT SP	290946 290947 290948 290949 290950	MA	(317103) or (317106)	DU = 269831 OP, 284173 IN, 284092 MA, RTD, H200 FR = 106531 OP, 284175 IN, 269897 MA, RTD, H200 GE = 106532 OP, 284176 IN, 284091 MA, RTD; H200 IT = 106533 OP, 284177 IN, 284094 MA, RTD, H200 SP = 106534 OP, 284180 IN, 284095 MA, RTD, H200
Series 3100	SERIES 3100 Hot Melt Applicator with Piston Pump SP 30 14:1 / UniScan	DU FR GE IT	283009 283011 283008 283012	MA	(317103) or (317106)	
Series 3100	SERIES 3100 Hot Melt Applicator with Piston Pump SP 30 14:1 / UniScan Each manual (MA) is composed of several parts, these have been listed under Notes.	DU FR GE IT SP	290951 290952 290953 290954 290955	MA	(317103) or (317106)	DU = 269831 OP, 284173 IN, 283009 MA, RTD, H200 FR = 106531 OP, 284175 IN, 283011 MA, RTD, H200 GE = 106532 OP, 284176 IN, 283008 MA, RTD; H200 IT = 106533 OP, 284177 IN, 283012 MA, RTD, H200 SP = 106534 OP, 284180 IN, RTD, H200

B-3 - 3

Nordson US Hot Melt Products (sorted by Model)

Series 2000 / Series 3000 / Series 5000 / Series 6000

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Series 3100 Series 3400 Series 3500 Series 3700	SERIES 3100/ 3400/ 3500/ 3700 Hot Melt Material Applicators	DA DU EN FI FR GE GR IT NO PO SP SW	284172A 284173A 284171A 284174A 284175A 284176A 292868A 284177A 284178A 284179A 284180A 284181A	IN	(317102) or (317107)	
Series 3100 Series 3400 Series 3500 Series 3700	SERIES 3100/3400/3500/3700 Hot Melt Material Applicator with Piston Pump, MultiScan Controller and Manifolds A, B, or S	CZ DA DU EN FI FR GE HU IT PL PO SP SW	458258A* 269816 269831 106530A 269815 106531 106532 7119545A 106533 413034A 269814 106534 269832	OP	(317102) or (317107)	* = Document and translation is NOT issued by TDLL !
Series 3400	SERIES 3400 Hot Melt Applicator with Gear Pump Each manual (MA) is composed of several parts, these have been listed under Notes.	DU FR GE IT SP	290971 290972 290973 290974 290975	MA	(317103) or (317106)	DU = 269831 OP, 284173 IN, RTD, H200 FR = 106531 OP, 284175 IN, RTD, H200 GE = 106532 OP, 284176 IN, RTD; H200 IT = 106533 OP, 284177 IN, RTD, H200 SP = 106534 OP, 284180 IN, RTD, H200

B-3 - 4

Nordson US Hot Melt Products (sorted by Model)

Series 2000 / Series 3000 / Series 5000 / Series 6000

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Series 3400	SERIES 3400 Hot Melt Applicator with Piston Pump / MultiScan	CZ DU EN FR GE IT SP	7135296A* 269841 106689E 283006 269842 269840 269810	MA	(317103) or (317106)	* = Document and translation is NOT issued by TDLL !
Series 3400	SERIES 3400 Hot Melt Applicator with Piston Pump SP 30 14:1 / MultiScan	DU FR GE IT SP	284104 284105 284103 284106 284107	MA	(317103) or (317106)	
Series 3400	SERIES 3400 Hot Melt Applicator with Piston Pump SP 30 14:1 / MultiScan Each manual (MA) is composed of several parts, these have been listed under Notes.	DU FR GE IT SP SW	290961 290962 290963 290964 290965 290391	MA	(317103) or (317106)	DU = 269831 OP, 284173 IN, 284104 MA, RTD, H200 FR = 106531 OP, 284175 IN, 284105 MA, RTD, H200 GE = 106532 OP, 284176 IN, 284103 MA, RTD, H200 IT = 106533 OP, 284177 IN, 284106 MA, RTD, H200 SP = 106534 OP, 284180 IN, 284107 MA, RTD, H200
Series 3400	SERIES 3400 Hot Melt Applicator with Piston Pump / UniScan	DU GE IT SP	283001 283000 283004 283005	MA	(317103) or (317106)	
Series 3400	SERIES 3400 Hot Melt Applicator with Piston Pump SP 30 14:1 / UniScan	DU FR GE IT SP	284098 283003 284097 284100 284101	MA	(317103) or (317106)	

B-3 - 5

Nordson US Hot Melt Products (sorted by Model)

Series 2000 / Series 3000 / Series 5000 / Series 6000

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Series 3400	SERIES 3400 Hot Melt Applicator with Piston Pump SP 30 14:1 / UniScan Each manual (MA) is composed of several parts, these have been listed under Notes.	DU FR GE IT SP	290966 290967 290968 290969 290970	MA	(317103) or (317106)	DU = 269831 OP, 284173 IN, 284098 MA, RTD, H200 FR = 106531 OP, 284175 IN, 283003 MA, RTD, H200 GE = 106532 OP, 284176 IN, 284097 MA, RTD; H200 IT = 106533 OP, 284177 IN, 284100 MA, RTD, H200 SP = 106534 OP, 284101 MA, RTD, H200
Series 3500	SERIES 3500 Hot Melt Applicator with Gear Pump Each manual (MA) is composed of several parts, these have been listed under Notes.	DU FR GE IT SP	290986 290987 290988 290989 290990	MA	(317103) or (317106)	DU = 269831 OP, 284173 IN, RTD, H200 FR = 106531 OP, 284175 IN, RTD, H200 GE = 106532 OP, 284176 IN, RTD; H200 IT = 106533 OP, 284177 IN, RTD, H200 SP = 106534 OP, 284180 IN, RTD, H200
Series 3500	SERIES 3500 Hot Melt Applicator with Piston Pump SP 30 14:1 / MultiScan / UniScan Each manual (MA) is composed of several parts, these have been listed under Notes.	DU FR GE IT SP	290976 290977 290978 290979 290980	MA	(317103) or (317106)	DU = 269831 OP, 284173 IN, 284038 MA, RTD, H200 FR = 106531 OP, 284175 IN, 284039 MA, RTD, H200 GE = 106532 OP, 284176 IN, 284037 MA, RTD; H200 IT = 106533 OP, 284177 IN, 284040 MA, RTD, H200 SP = 106534 OP, 284180 IN, 284041 MA, RTD, H200
Series 3500	SERIES 3500 Hot Melt Applicator with Piston Pump SP 30 21:1/ MultiScan / UniScan Each manual (MA) is composed of several parts, these have been listed under Notes.	DU FR GE IT SP	290981 290982 290983 290984 290985	MA	(317103) or (317106)	DU = 269831 OP, 284173 IN, 284050 MA, RTD, H200 FR = 106531 OP, 284175 IN, 284051 MA, RTD, H200 GE = 106532 OP, 284176 IN, 284049 MA, RTD; H200 IT = 106533 OP, 284177 IN, 284052 MA, RTD, H200 SP = 106534 OP, 284180 IN, 284053 MA, RTD, H200
Series 3700	SERIES 3700 Hot Melt Applicator with Gear Pump Each manual (MA) is composed of several parts, these have been listed under Notes.	DU FR GE IT SP	292701 292702 292703 292704 292705	MA	(317103) or (317106)	DU = 269831 OP, 284173 IN, RTD, H200 FR = 106531 OP, 284175 IN, RTD, H200 GE = 106532 OP, 284176 IN, RTD; H200 IT = 106533 OP, 284177 IN, RTD, H200 SP = 106534 OP, 284180 IN, RTD, H200

B-3 - 6

Nordson US Hot Melt Products (sorted by Model)

Series 2000 / Series 3000 / Series 5000 / Series 6000

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Series 3700	SERIES 3700 Hot Melt Applicator with Piston Pump SP 30 14:1 / MultiScan Each manual (MA) is composed of several parts, these have been listed under Notes.	DU FR GE IT SP	290991 290992 290993 290994 290995	MA	(317103) or (317106)	DU = 269831 OP, 284173 IN, 284038 MA, RTD, H200 FR = 106531 OP, 284175 IN, 284039 MA, RTD, H200 GE = 106532 OP, 284176 IN, 284037 MA, RTD; H200 IT = 106533 OP, 284177 IN, 284040 MA, RTD, H200 SP = 106534 OP, 284180 IN, 284041 MA, RTD, H200
Series 3700	SERIES 3700 Hot Melt Applicator with Piston Pump SP 30 21:1 / MultiScan Each manual (MA) is composed of several parts, these have been listed under Notes.	DU FR GE IT SP	290996 290997 290998 290999 292700	MA	(317103) or (317106)	DU = 269831 OP, 284173 IN, 284050 MA, RTD, H200 FR = 106531 OP, 284175 IN, 284051 MA, RTD, H200 GE = 106532 OP, 284176 IN, 284049 MA, RTD; H200 IT = 106533 OP, 284177 IN, 284052 MA, RTD, H200 SP = 106534 OP, 284180 IN, 284053 MA, RTD, H200
Series 3800 Series 3900	SERIES 3800/ 3900 Hot Melt Material Applicators	DA DU EN FI FR GE IT SP	290740A 290741A 290739A 290742A 290743A 290744A 290745A 290747A	IN	(317102) or (317107)	
Series 3800 Series 3900	SERIES 3800/ 3900 Hot Melt Applicator SP 21:1 Each manual (MA) is composed of several parts, these have been listed under Notes.	DU FR GE IT SP	292706 292707 292708 292709 292710	MA	(317103) or (317106)	DU = 290741 IN, 284050 MA, RTD, H200 FR = 290743 IN, 284051 MA, RTD H200 GE = 290744 IN, 284049 MA, RTD, H200 IT = 290745 IN, 284052 MA, RTD, H200 SP = 290747 IN, 284053 MA, RTD, H200
Series 3860	SERIES 3860 Hot Melt Material Applicator with DC Pump, K or L Manifold, M.P.C. and Multiscan Controller	PO	397530B	MA	(317103) or (317106)	EN - 334583B

B-3 - 7

Nordson US Hot Melt Products (sorted by Model)

Series 2000 / Series 3000 / Series 5000 / Series 6000

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Series 3860/ 3960	Fulfill Retrofit Series 3860 and 3960 Melters	FR GE IT SP	7179749_01 7179750_01 7179751_01 7179752_01	MA	(317103) or (317106)	EN - 1121936_01 - Issued 04/13
Series 5625P	Series 5625P Melt-On-Demand Application System	FR	405294C	OP	(317102) or (317107)	
Series 5625P	Series 5625P Melt-On-Demand Application System Precision Control Reference Guide	FR	405295C	IN	(317102) or (317107)	
Series 5625P	Series 5625P Melt-On-Demand Application System Single-Drive Dispensing System with Transfer Pump	FR	405293A	MA	(317103) or (317106)	
Series 6000	SERIES 6000	SP	458049A	MA	(317104) or (317105)	Section: Models covered: 1 - 6 6120C 7 6120A + 6065C 8 6120A + 6120C 9 6120C 10 6065C
Series 6000 6065	SERIES 6000 Model 6065	GE	269883	MA	(317104) or (317105)	
Series 6000 (6065, 6120, 6220)	SERIES 6000 (6065, 6120, 6220) Hot Melt Material Applicator	DU EN FR GE IT SP	269863 269862 269864 269865 269866 269868	OP	(317102) or (317107)	
Series 6000 6120A	SERIES 6000 Model 6120A	GE IT	104767A 269843	MA	(317104) or (317105)	

B-3 - 8

Nordson US Hot Melt Products (sorted by Model)

Series 2000 / Series 3000 / Series 5000 / Series 6000

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Series 6000 6120C	SERIES 6000 Model 6120C	IT	269844	MA	(317104) or (317105)	
Series OS6000	SERIES OS6000 Hot Melt Material Applicators	DU EN SP	292947A 292855A 292871A	IN	(317102) or (317107)	
SP30 6:1	SP30 6:1 Piston Pump Installation and Maintenance	GE	284185	MA	(317102) or (317107)	
SP30 14:1	SP30 14:1 Piston Pump Installation and Maintenance Instructions	DU EN FI FR GE IT SP	284038 108715B 397419B 284039 284037 284040 284041	MA	(317102) or (317107)	Issued 10/95
SP30 21:1	SP30 21:1 Piston Pump Installation and Maintenance Instructions	DU EN FR GE IT SP	284050 108720D 284051 284049 284052 284053	MA	(317102) or (317107)	Issued 02/01
UMI	UNIVERSAL MACHINE INTERFACE FOR SERIES 6000 APPLICATORS	GE	267968	MA	(317102) or (317107)	

B-4 - 1

Nordson US Hot Melt Products (sorted by Model) Other Melters and Diverse Equipment, Hoses

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Best Hose Routing Practices	CR DU FR GE HU IT LI PL PO SP	7580034_04 7560752_04 7192982_04 7192993_04 7580013_04 7192686_04 7560771_04 7192996_04 7192997_04 7192992_04	IN	(317102) or (317107)	EN - 1078079_04 - Issued 09/13
	Elastic Attachement Applications - Quick Reference -	SP	7119155B	IN	(317102) or (317107)	EN - 1046122B - Issued 06/04
	Electrical Cabinet for Label Adhesive System	IT	7560968_01	MA	(317102) or (317107)	EN - 1124934_01 - Issued 03/16
	Melter Flushing Kit - P/N 1072368 Melter Flushing Kit - P/N 1126060	EN FR	1054223A03 7119607_03	IN	(317102) or (317107)	Issued 09/06 Issued 07/17
	Three-Way Dispensing Modules	GE	7119611B	IN	(317102) or (317107)	EN - 321551B - Issued 11/02
	Remote Metering Station	IT	7146833B03	MA	(317102) or (317107)	EN - 1041397B03 - Issued 08/06
	Stand-alone Level Sensor (User's Guide)	FR GE IT SP	7560906_01 7560904_01 7560907_01 7560905_01	MA	(317102) or (317107)	EN - 1125417_01 - Issued 12/16

B-4 - 2

Nordson US Hot Melt Products (sorted by Model) Other Melters and Diverse Equipment, Hoses

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Blue Series	Blue Series Hot Melt Hose with RediFlex II Hanger System	CZ DA DU FI FR GE HU IT JA KO PL PO RU SP SW	7560212_01 7560222_01 7560213_01 7560219_01 7560223_01 7560214_01 7560220_01 7560285_01 7560215_01 7560216_01 7560218_01 7560225_01 7560221_01 7560224_01 7560217_01	IN	(317102) or (317107)	EN - 1124594_01 - Issued 06/15
Bravura	Bravura Adhesive Melters	DA DU FR GE IT EN/PL SP	7135103D02* 7119435D02 7105580D02 7105598D02 7105585D02 7119074C** 7105592D02	MA	(317103) or (317106)	EN - 1052743D03 - Issued 02/10 * = Only section 2-5 ! ** = only section INS in Polish ! - OBSOLETE -
Bravura	Bravura Adhesive Melters	DA DU FR GE IT PL SP	7135104A 7119436A 7105559A 7105571A 7105535A 7119054A 7105566A	OP	(317102) or (317107)	EN - 1053810A02 - Issued 08/04 - OBSOLETE -
C9/ C15	C9 and C15 Adhesive Melters	DU FR GE PO SP	7179527_02 7179525_02 7179526_02 7179529_02 7179528_02	MA	(317102) or (317107)	EN - 1121010_02 - Issued 01/13

B-4 - 3

Nordson US Hot Melt Products (sorted by Model) Other Melters and Diverse Equipment, Hoses

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Classic Series	Classic Series Melters	FR SP	7169314_02 7169319_02	MA	(317102) or (317107)	EN - 1108226_02 - Issued 02/12
EZ	EZ Adhesive Melters Models 20 and 45	CH	7560918_01	MA	(317102) or (317107)	EN - 1125336_01 - Issued 08/16
Freedom	Freedom Hot Melt Adhesive System	DU FR GE IT JA PL PO SP SW	7179694_02 7179648_02 7179995_02 7179649_02 7179994_02 7192323_02 7179670_02 7179654_02 7179668_02	MA	(317102) or (317107)	EN - 1121631_02 - Issued 7/13 OLD!
Freedom	Freedom Hot Melt Adhesive System	CZ	7192494_02	MA	(317102) or (317107)	EN - 1123087_02 - Issued 3/14 OLD!
Freedom	Freedom Hot Melt Adhesive System	-	-	MA	(317102) or (317107)	EN - 1125366_01 - Issued 10/16 NEW!

B-4 - 4

Nordson US Hot Melt Products (sorted by Model) Other Melters and Diverse Equipment, Hoses

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Freedom	Freedom Hot Melt Adhesive System - Quick Reference -	CZ DA DU FI FR GE HU IT JA KO NO PL PO RU SP SW	7179809_01 7179931_01 7179550_01 7179864_01 7179547_01 7179501_01 7179903_01 7179553_01 7179532_01 7179861_01 7560119_01 7179830_01 7179575_01 7179828_01 7179549_01 7179608_01	IN	(317102) or (317107)	EN - 1121655_02 - Issued 10/16
Freedom	Freedom Hot Melt Hose	CZ DA DU FI FR GE HU IT JA KO PL PO RU SP SW	7179810_01 7179932_01 7179551_01 7179865_01 7179546_01 7179500_01 7179904_01 7179552_01 7179531_01 7179862_01 7179831_01 7179576_01 7179829_01 7179548_01 7179609_01	IN	(317102) or (317107)	EN - 1121628_01 - Issued 02/13

B-4 - 5

Nordson US Hot Melt Products (sorted by Model) Other Melters and Diverse Equipment, Hoses

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Freedom	Freedom Hot Melt Hose with RediFlex II Hanger System	CZ DA DU FI FR GE HU IT JA KO PL PO RU SP SW	7560206_01 7560203_01 7560207_01 7560198_01 7560204_01 7560208_01 7560199_01 7560200_01 7560209_01 7560210_01 7560197_01 7560202_01 7560201_01 7560205_01 7560211_01	IN	(317102) or (317107)	EN - 1124593_01 - Issued 06/15
GD-200	GD-200S and GD-200F Sensors Customer Product Manual (Title version A: GD-200 Sensor)	CH CZ DU FI FR GE IT JA PL SP SW	7135382_04 7192557_04 7135526_04 7135524_04 7135443_04 7135423_04 7135462_04 7156371_04 7135420_04 7135527_04 7135417_04	MA	(317102) or (317107)	EN - 1074512_04 - Issued 07/14
GD-500	Bead Detection System	IT PL	7156046A 7192155A	MA	(317102) or (317107)	EN - 1085946A - Issued 04/08

B-4 - 6

Nordson US Hot Melt Products (sorted by Model) Other Melters and Diverse Equipment, Hoses

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
GD-500	Smart Sensor	CH CZ DU FI FR GE IT PL SP SW	7156123A 7192558A 7156127A 7156137A 7156124A 7156111A 7156140A 7156130A 7156139A 7156103A	MA	(317102) or (317107)	EN - 1094263A - Issued 06/09
GP 200	GP 200 Metering Station	GE IT JA RU SP SW	7146133A04 7135881_07 7169360A03* 7146739A04 7135136A 7179508A06	MA	(317102) or (317107)	EN - 1072082_07 - Issued 02/16 * = available at Nordson K.K.
GP 200	GP 200 Metering Station Equipment Part Number 1075167	SP	7135137A	MA	(317102) or (317107)	EN - 1075820A - Issued 01/07
GP 200	GP 200 Metering Station	DU RU	7156667A 7169136A	MA	(317102) or (317107)	EN - 1083573A - Issued 03/08
HD-70	Hot Melt Sensor	GE	7179353A	MA	(317102) or (317107)	EN - 1091995A - Issued 10/08
HD-100	Hot Melt Sensor	CH DU FR GE IT JA SP	7192128_01 7192165_01 7192160_01 7192139_01 7192140_01 7192129_01 7192150_01	MA	(317102) or (317107)	EN - 1122177_01 - Issued 08/13

B-4 - 7

Nordson US Hot Melt Products (sorted by Model) Other Melters and Diverse Equipment, Hoses

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LP90	LP90 Fluid Application System	CZ DU GE IT PL PO RU SK SP	7192781B03 7192499_04 7179542B03 7105675_04 7192858B03 397405A 7560669_04 7105699_04 397420_04	MA	(317102) or (317107)	EN - 1041182_04 - Issued 06/12
LP 100	LP100 Fluid Application System	FR GE IT	464962B 458405B 458391B	MA	(317102) or (317107)	EN - 1002288B - Issued 03/01
Mesa	Mesa Adhesive Melters Model M4, M6, M9, and M14	CZ DU FI FR GE IT PL RU SP	7169300A03 7192369_04 7156188_04 7156166_04 7156146_04 7156156_04 7156556_04 7156158_04 7156141_04	MA	(317102) or (317107)	EN - 1089887_05 - Issued 10/15
Mesa	FulFill Retrofit for Mesa Melters	FR GE IT SP	7169200A 7169219A 7169213A 7169217A	MA	(317102) or (317107)	EN - 1103525A - Issued 01/13 Issue date of translations 09/10 OLD! - > Replaced by P/N 1121938_01
Mesa	FulFill Retrofit for Mesa Melters	FR GE IT SP	7179745_01 7179746_01 7179747_01 7179748_01	MA	(317102) or (317107)	EN - 1121938_02 - Issued 05/13 Obsolete!

B-4 - 8

Nordson US Hot Melt Products (sorted by Model) Other Melters and Diverse Equipment, Hoses

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Mesa	Mesa Adhesive Melters - User' s Guide	EN/CH/ DA/FI/ FR/GE/ IT/JA/ NO/SP/ SW	1096980A	OP	(317102) or (317107)	Issued 06/09
Mesa	Mesa Adhesive Melters - User' s Guide	EN/DU	7192313_01	OP	(317102) or (317107)	Issued 01/14
MiniPUR	MiniPUR Adhesive Melter	FR	7179658A03	MA	(317102) or (317107)	EN - 1093491A03 - Issued 01/13
MiniPUR Plus	MiniPUR Plus Adhesive Melter	CZ FR GE JA NO SP SW	7560723_02 7192214_02 7192176_02 7192211_02 7192162_02 7192172_02 7192215_02	MA	(317102) or (317107)	EN - 1122803_02 - Issued 06/14
PM-150/250	PM-150/250 Premelter Manual	DU FR GE IT	413071A 413060A 413059A 413061A	MA	(317102) or (317107)	EN - 321224A (EDB 41-710)
Pro-Meter	Pro-Meter VDK Dispensing System	DA GE IT JA SP	7119346C 397893C 7105096C 7119302C* 7119630C	MA	(317102) or (317107)	EN - 321208C - Issued 3/05 OLD! * = available at Nordson K.K
Pro-Meter	Pro-Meter VDK Dispensing System	IT JA PL	7560679_07 7169753_07* 7192994_07	MA	(317102) or (317107)	EN - 10692041_07 - Issued 01/12 * = available at Nordson K.K OLD!

B-4 - 9

Nordson US Hot Melt Products (sorted by Model) Other Melters and Diverse Equipment, Hoses

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Pro-Meter	Pro-Meter VDK Dispensing System	CZ	7560836_01	MA	(317102) or (317107)	EN - 1123462_01 - Issued 10/14 NEW!
PS40	PS40 Power Supply	DU GE GR HU PL	7179193B02 213009B02 7119834B 7156462B02 7169216B02	IN	(317102) or (317107)	EN - 1011339_04 - Issued 08/11 Obsolete!
RTD	RTD-Style Hot Melt Hose	BU CH CZ DA DU ES FI FR GE HU IT NO PL PO RO RU SK SP SW	7135437E 7169269E 7105115E 447643E 284190E 7146247E 458480E 284191E 284192E 7146218E 284193E 447631E 7105754E 403296E 7192771E 7135330E 7156926E 284194E 284195E	MA	(317102) or (317107)	EN - 108232E - Issued 01/00

B-4 - 10

Nordson US Hot Melt Products (sorted by Model) Other Melters and Diverse Equipment, Hoses

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
RTD	RTD-Style Hot Melt Hoses User' s Guide	BU CH CR CZ DU FR GE HU IT JA LI PL PO RO RU SK SP	7135438D 7560948D05 7580035D05 7119714D05 7560751D05 7560007D05 7135144D 7580012D05 7560091D05 7146031D 7560770D05 7135347D 7560933D05 7135549D 7119637D 7146167D 7560087D05	IN	(317102) or (317107)	EN - 321346D05 - Issued 11/10
RTD	RTD-Style Hot Melt FoamMix Hoses for Bulk Melter Systems	CH FR GE IT	7179630_01 7560231_01 7560032_01 7560507_01	OP	(317102) or (317107)	EN - 1121861_01 - Issued 06/13
RTD	RTD-Style e. dot Hot Melt Hoses	GE PL SW	7560808B03 7560298B03 7179032B03	IN	(317102) or (317107)	EN - 1032556B03 - Issued 11/07
RTD	RTD Style High Temperature Hot Melt Hoses	GE IT	7146506B03 7192685B04	IN	(317102) or (317107)	EN - 1044182B04 - Issued 10/08
Select Series	Select Series Advanced Technology RTD Style Hoses	GE IT	213478D 213445D	OP	(317102) or (317107)	EN - 321197F04 - Issued 07/09

B-4 - 11

Nordson US Hot Melt Products (sorted by Model) *Other Melters and Diverse Equipment, Hoses*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
TruFlow	TruFlow Meter	CZ GE IT PL SK	7560890_03 7580156_03 7560006_03 7560538_03 7560875_03	IN	(317102) or (317107)	EN - 1121840_03 - Issued 07/14
VL200	VL200 Melter	IT	7105607B	MA	(317103) or (317106)	EN - 779639C - Issued 08/05 Obsolete!
VL300	VL300 Melters	GE IT	213123B 213050B	MA	(317103) or (317106)	EN - 1004923D - Issued 10/02 Obsolete!
VL300	VL300 Melters	FR GE	397368C 213080A	OP	(317103) or (317106)	EN - 1004924C - Issued 01/02 Obsolete!
VL400	VL400 Melters	GE IT	7105530A 7105503A	MA	(317103) or (317106)	EN - 1052643B - Issued 08/05 Obsolete!

B-5 - 1

Nordson US Hot Melt Products (sorted by Model) Auxiliary Systems

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Accubar	Accubar Bar Code Verifier	FR IT PL	7119993D02 7119631D 7119154D	MA	(317102) or (317107)	EN - 321356D02 - Issued 02/10
Braille	Braille Pattern Controller	EN IT	7135662A 7135781A	MA	(317102) or (317107)	Application Development Word .doc
Concert	Concert Series Basic Standalone Temperature Controller	FR GE IT	7192853_01 7192883_01 7560048_01	MA	(317102) or (317107)	EN - 1123727_01 - Issued 06/14
Concert	Concert Series Basic Standalone Temperature Controller with Flow Monitor and Control	CZ PL SK	7580068_01 7580075_01 7580069_01	MA	(317102) or (317107)	EN - 1121717_01 - Issued 06/14
Concert	Concert Series Expanded Standalone Temperature Controller	PO	7560394_01	MA	(317102) or (317107)	EN - 1123728_01 - Issued 09/14
Concert	Concert Series Expanded Standalone Temperature Controller with Flow Monitor and Control	CZ PL SK	7580070_01 7580076_01 7580071_01	MA	(317102) or (317107)	EN - 11263730_01 - Issued 09/14
Concert	Concert Series Standalone Temperature Controller - User's Guide -	IT	7560049_01	OP	(317102) or (317107)	EN - 1122802_01 - Issued 06/14
EcoBead	EcoBead Inline Pattern Generator	CH CZ FR GE IT JA PL SP	7179204_01 7179314_01 7179205_01 7179206_01 7179207_01 7179208_01 7560170_01 7179209_01	MA	(317102) or (317107)	EN - 1120911_01 - Issued 09/12

B-5 - 2

Nordson US Hot Melt Products (sorted by Model) Auxiliary Systems

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
EPC-15	Eclipse Series EPC-15 Pattern Control	DU FI FR GE IT JA PL SP SW	464999A 213249A 447759D02 447760D02 464990D02 447781A* 7119513D 464726D02 213115A	MA	(317103) or (317106)	EN - 321352D02 -Issued 02/10 available at Nordson K.K OBSOLETE!
EPC-15	Eclipse Series EPC-15 User's Guide	DA HU JA RU SL	213117C 7146262A** 464873A* 7156923C 7146407C	OP	(317102) or (317107)	EN - 321287C * available at Nordson K.K ** = Abridged edition, document and translation is NOT issued by TDLL ! OBSOLETE!
EPC-30	Eclipse Series EPC-30 Pattern Control	CZ DA DU FI FR GE IT NO PL PO RU SP SW	7119051C* 412851B 412985B 412852B 412853B 412680D 412842B 412850B 458274B 458424B 7179129D 412718B 412719C	MA	(317103) or (317106)	EN - 237514D - Issued 02/10 * = Abridged edition, document and translation is NOT issued by TDLL ! OBSOLETE!
EPC-30	Series EPC-30 Current-to-Pressure (I/P) Transducer	GE	213026A	IN	(317102) or (317107)	EN - 331276B02 -Issued 08/10

B-5 - 3

Nordson US Hot Melt Products (sorted by Model) *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
EPC-30	Eclipse Series EPC-30 User's Guide	FR GE GR HU PL RU SK	447709A 447703A 7119833C 7146265C02 7169183C02 213201A 7119229A	OP	(317102) or (317107)	EN - 331180C02 - Issued 2007 OBSOLETE!
FillEasy II	FillEasy II Adhesive Feed System	FR GE IT JA PO SP SW	7119961A 7146580A 7135604A 7146260A 7119974A 7119996A 7119992A	MA	(317102) or (317107)	EN - 1073536A - Issued 10/06 OBSOLETE!
FillEasy II	FillEasy II Cone and Level Sensor Assembly Installation - P/N 1071613	FR	7135149A	IN	(317102) or (317107)	EN - 1071702A - Issued 1006 OBSOLETE!
Fillmaster	Fillmaster Adhesive Feed System	DU FI FR GE IT NO PO SP SW	213650B 397002B 213677B 213663B 213648B 397047B 213645B 213673B 213719B	MA	(317102) or (317107)	EN - 1030629C - Issued 07/04 OBSOLETE!

B-5 - 4

Nordson US Hot Melt Products (sorted by Model) Auxiliary Systems

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Fillmaster	Level Sensor	DU FI FR GE IT NO PO SP SW	213651A 397003A 213679A 213664A 213649A 397048A 213646A 213676A 213720A	IN	(317102) or (317107)	EN - 1029200A - Issued 07/02 OBSOLETE!
LogiCOMM	LogiCOMM Control System Control Module Manual	CH CZ DU FI FR GE HU IT JA PL PO RU SK SP SW	7135046A** 7146512A 7105862A 7135071B 7105822A 7105812A 7135654A 7105794A 7135341A* 7119148B 7146465A 7146502A 7156930A 7105808A 7105791A	MA	(317102) or (317107)	EN - 1049054A02 - Issued 2010 * available at Nordson K.K ** = Document and translation is NOT issued by TDLL!
LogiComm	LogiComm Control System with Combination Configuration	CH CZ DU FR GE IT PL PO SP SW	7169758_01 7169152_01 7169723_01 7169693_01 7169682_01 7169701_01 7169816_01 7169707_01 7169679_01 7169698_01	MA	(317102) or (317107)	EN - 1105135_01 - Issued 11/11

B-5 - 5

Nordson US Hot Melt Products (sorted by Model) *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LogiComm	LogiComm Control System for Pattern Generation	CH DU FR GE IT PL PO SP SW	7169756_01 7169721_01 7169691_01 7169680_01 7169699_01 7169814_01 7169705_01 7169677_01 7169696_01	MA	(317102) or (317107)	EN - 1120173_01 - Issued 12/11 Issue date of translations 11/11
LogiComm	LogiComm Control System for Product Verification	CH DU FR GE IT PL PO SP SW	7169757_01 7169722_01 7169692_01 7169681_01 7169700_01 7169815_01 7169706_01 7169678_01 7169697_01	MA	(317102) or (317107)	EN - 1120174_01 - Issued 12/11 Issue date of translations 11/11
LogiComm	LogiComm Control System User's Guide	DA DU FI FR GE HU IT NO PL PO RU SP SW	7169470 7169471 7169472 7169473 7169474 7169475 7169476 7169477 7169478 7169479 7169480 7169481 7169482	OP	(317102) or (317107)	EN - 1105134 - Issued 04/11

B-5 - 6

Nordson US Hot Melt Products (sorted by Model) *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LogiComm	LogiComm Gun Driver	CZ DU FI FR GE HU IT JA PL RU SP SW	7156951 A02 7146391A 7146369A 7146340A 7146360 A02 7146375A 7146396 A02 7146355A 7146605 A02 7560672 A02 7146368 A02 7146577A	MA	(317102) or (317107)	EN - 1087837A02 - Issued 03/10
LogiComm	LogiComm Gun Driver User's Guide	CZ DA DU FR GE HU IT NO PL PO RU SK SP SW	7192775A 7146316A 7146317A 7146318A 7146319A 7146320A 7146321A 7146322A 7146323A 7146324A 7560673A 7580000A 7146325A 7146326A	OP	(317102) or (317107)	EN - 1087838A - Issued 05/08
LogiComm	LogiComm OEM Applicator Driver Board	CH DU FR GE IT SP SW	7156173A02 7156189A02 7156195A02 7156206A02 7156182A02 7156222A02 7179030A02	MA	(317102) or (317107)	EN - 1097242A02 - Issued 04/10

B-5 - 7

Nordson US Hot Melt Products (sorted by Model) Auxiliary Systems

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LogiComm	LogiComm OEM Applicator Driver Board Wiring Diagram	CH DU FR GE IT SP	7156664A02 7156683A02 7156684A02 7156678A02 7156677A02 7156679A02	IN	(317102) or (317107)	EN - 1098142A02 - Issued 04/10
LogiComm	Trigger I/O Board for the LogiComm Gun Driver	DU FI FR GE HU IT JA PL SP SW	7146409A 7146539A 7146411A 7146412A 7146419A 7146464A 7146424A 7146606A 7146413A 7146578A	IN	(317102) or (317107)	EN - 1084488A - Issued 02/06
LogiComm	LogiComm Touch-screen Panel Installation for Basic and Expanded Systems	DA DU FR GE HU IT JA NO PL PO SP SW	7105924A 7105953A 7105916A 7105985A 7135879B 7105921A 7135375A 7105947A 7119150A 7105938A 7105934A 7105918A	IN	(317102) or (317107)	EN - 1060849B - Issued 03/06
LogiComm	LogiComm: Change Encoder from Quadrature to Single Phase	EN/ GE	7169790_01	IN	(317102) or (317107)	Bilingual document, therefore one P/N only Created by Nordson Engineering GmbH

B-5 - 8

Nordson US Hot Melt Products (sorted by Model) Auxiliary Systems

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Nitrogen	Generation System	FR PL	7179660_02 7179423A	MA	(317102) or (317107)	EN - 1107704_02 - Issued 06/13
PACK	Pattern Air Control Kit (PACK)	DU PL RU	7156669B02 7156358B02 7169143B02	IN	(317102) or (317107)	EN - 1044445B02 - Issued 01/08 OBSOLETE!
Seal Sentry	Seal Sentry Series 10 Bead Detection System	FR GE NO SP SW	464910A 213015A 213418B 7119137C02 213412B	MA	(317103) or (317106)	EN - 321289D02 - Issued 02/10 Obsolete!
Spectra 30	Pattern Controller -OLD!-	CH CZ DU FR GE IT JA PL PO RU SP	7192744_01 7560062_01 7192788_01 7192786_01 7192782_01 7192779_01 7192745_01 7560146_01 7192774_01 7560339_01 7192800_01	MA	(317103) or (317106)	EN - 1123406_01 - Issued 8/14
Spectra 30	Pattern Controller -NEW!-	CH DU FR GE IT JA PL PO SP	7560423_01 7560421_01 7560418_01 7560417_01 7560419_01 7560424_01 7560425_01 7560422_01 7560420_01	MA	(317103) or (317106)	EN - 1124631_01 - Issued 10/15

B-5 - 9

Nordson US Hot Melt Products (sorted by Model) *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Spectra 30	Pattern Controller -Installation Guide- -OLD!-	CH DU FR GE IT JA PL PO SP	7192703_01 7192704_01 7192705_01 7192706_01 7192707_01 7192708_01 7560256_01 7192709_01 7192710_01	OP	(317102) or (317107)	EN - 1123405_01 - Issued 07/14
Spectra 30	Control System -Installation Guide- -NEW!-	CH CR DU FR GE HU IT JA PO RO SE SL SP	1124780_01 7560973_01 1124781_01 1124782_01 1124783_01 7560974_01 1124784_01 1124785_01 1124786_01 7560745_01 7560975_01 7560976_01 1124787_01	OP	(317102) or (317107)	EN - 1124634_01 - Issued 09/15
Spectra 30	Pattern Controller -Quick Reference Guide- -OLD!-	CH DU FR GE IT JA PL PO SP	7192699_01 7192700_01 7192562_01 7192563_01 7192564_01 7192701_01 7560257_01 7192702_01 7192565_01	OP	(317102) or (317107)	EN - 1122901_01 - Issued 2014

B-5 - 10

Nordson US Hot Melt Products (sorted by Model) Auxiliary Systems

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Spectra 30	Control System -Quick Reference Guide- -NEW!-	CH CR CZ DU FR GE HU IT JA PO RO SE SL SP	1124727_01 7560969_01 7560781_01 1124728_01 1124729_01 1124730_01 7560970_01 1124731_01 1124732_01 1124733_01 7560746_01 7560971_01 7560972_01 1124734_01	OP	(317102) or (317107)	EN - 1124633_01 - Issued 2015
Spectra 30	Control System -Safety Instructions-	CH CR DU FR GE HU IT JA PL PO RO SE SL SP	7192711_01 7560981_01 7192712_01 7192713_01 7192714_01 7560982_01 7192715_01 7192716_01 1124796_01* 7560143_01 7192717_01 7560764_01 7560983_01 7560984_01 7192718_01	IN	(317102) or (317107)	EN - 1123841_01 - Issued 08/14 * PL = US P/N !
Unity	Unity IC30/ IC300 Dispensing System	JA	7156685A*	MA	(317102) or (317107)	EN - 1092353_05 - Issued 06/16 * available at Nordson K.K
Unity	Unity IC30/ IC300 PLUS Dispensing System	CH	7580118_01	MA	(317102) or (317107)	EN - 1126102_01 - Issued 06/17

Issued by Technical Documentation Local Languages (TDLL) Department, Nordson Engineering, Lüneburg
Status : July 2017

B-5 - 11

Nordson US Hot Melt Products (sorted by Model) ***Auxiliary Systems***

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Unity	Unity PURJet 30 Dispensing System	HU	7169794A	MA	(317102) or (317107)	EN - 1104545_06 - Issued 12/13
Unity	Unity-C Controller	CH	7580059_01	MA	(317102) or (317107)	EN - 1125640_01 - Issued 03/17
Unity	Unity Touch Controller	CH	7580060_01	MA	(317102) or (317107)	EN - 1125641_01 - Issued 03/17

B-6 - 1

Nordson US Hot Melt Products (sorted by Model) Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Cleaning Nozzles	JA	7156562B*	IN	(317102) or (317107)	EN - 1053027 - Issued 2004 * available at Nordson K.K
AD 31	Series AD-31 Swirl and Wide-Pattern Swirl Hand-held Applicators	RO	7560814_03	MA	(317102) or (317107)	EN - 107111_03 - Issued 10/15
AD 31	Series AD-31 and Series L4 Hand-held Applicators (Title version B: Series AD-31 Extrusion Handgun) (Title version C: Series AD-31 and Series L4 Extrusion Handguns)	FR GE	409229B 397245C	MA	(317102) or (317107)	EN - 107105_05 - Issued 08/15
AD 41	Series AD-41, L5, and L7 Extrusion Handguns (Title version B: AD-41 Handgun)	CZ FI FR GE IT JA PL RO	7105254B 7135231G 7135474G 412629G02 7135472G 464852B** 7560455G02 7560785G02	MA	(317102) or (317107)	EN - 237567G02 - Issued 06/10 ** available at Nordson K.K
AltaSpray	AltaSpray Applicators	FR GE IT JA SP	7135777A04 7135769A04 7135836A04 7169646A05* 7135778A02	MA	(317102) or (317107)	EN - 1081984A05 - Issued 11/10 * available at Nordson K.K
AltaSpray	AltaSpray Applicator Insulating Jacket Installation	JA	7169645A*	IN	(317102) or (317107)	EN/CH - 1097095A - Issued 09/09 * available at Nordson K.K

B-6 - 2

Nordson US Hot Melt Products (sorted by Model) Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
AltaSpray Plus	AltaSpray Plus Applicators	FR GE IT JA PO SP	7192161_01 7192164_01 7192171_01 7192210_01 7192170_01 7192163_01	MA	(317102) or (317107)	EN - 1121844_01 - Issued 05/13
Blue Series	Blue Series Pneumatic Applicators	CZ DA DU FI FR GE IT JA NO PL PO RU SK SP SW	7105736_08 7105733A 7105729A 7105732A 7105831A 7105735_07 7105829_08 7105793A 7105734A 7105897_07 7105809A 7146767A04 7156927A04 7105851A 7105727A	MA	(317102) or (317107)	EN - 1054960_08 - Issued 01/17
Blue Series	Blue Series Low Profile Pneumatic Guns	RU	7146768A03	MA	(317102) or (317107)	EN - 1074086A03 - Issued 09/08
CC 200	Control Coat (CC200) Applicators	CZ DA DU FR GE IT PL SP SW	213853B 213932B 213905B 213940B 213892B 213914B 213996B 213965B 213885B	OP	(317102) or (317107)	EN - 237562C - Issued 12/04

B-6 - 3

Nordson US Hot Melt Products (sorted by Model) Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
CF 200	HMS Applicators (CF200) (Title version A: Controlled Fiberization (CF200) Applicators)	CZ DA DU FR HU GE IT PL SK SP SW	213848A 213927A 213900A 213935A 7105617A 213887A 213909A 213991A 7105676A 213960A 213880A	OP	(317102) or (317107)	EN - 1029961C02 - Issued 01/07
CF 200	Universal Applicators (CF200)	IT JA	7135835_04 7119451A*	OP	(317102) or (317107)	EN - 1063322_04 - Issued 08/11 *available at Nordson K.K
CF 400	Controlled Fiberization (CF400) Applicators	CZ DA DU FR GE IT PL SP SW	213852A 213931A 213904A 213939A 213891A 213913A 213995A 213964A 213884A	OP	(317102) or (317107)	EN - 1029965B - Issued 12/04
Control Coat	Control Coat Applicators Base applicator parts 1066085 and 1065853, grade plate 1065814, and return plate 753367	SP	7119579A	MAN	(317102) or (317107)	EN - 1066099A - Issued 02/06

B-6 - 4

Nordson US Hot Melt Products (sorted by Model) Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
CW 200	Control Weave (CW200) Applicators	CZ DA DU FR GE IT PL SP SW	213854B 213933B 213906B 213941B 213893B 213915B 213997B 213966B 213886B	OP	(317102) or (317107)	EN - 303861C - Issued 12/04
e.dot	e.dot Gun	FR GE IT JA	7119109D 7105139B 7119697D 7105119B*	MA	(317102) or (317107)	EN - 1041250E02 - Issued 09/06 * available at Nordson K.K
e.dot+	e.dot+ Electric Applicator (Title A02: e.dot+ Electric Gun)	CZ FR GE IT JA PL SK SW	7156952A02 7169434A02 7156425_03 7156520A02 7156451A02 7560299_03 7580147_03 7179031A02	MA	(317102) or (317107)	EN - 1079033_03 - Issued 11/16 PL translation issued 09/12
e.dot+	e.dot+ Module Replacement Kit - P/N 7301602, 7301603, and 7301604	GE	7156427A	IN	(317102) or (317107)	EN - 1082903A - Issued 06/07
e.dot+	e.dot+ Module Seal Service Kit - P/N 7302201	GE	7156426_01	IN	(317102) or (317107)	EN - 1079052_01 - Issued 07/17
e.dot+	e.dot+ Armature-Spring-Nozzle Replacement Kit - P/N 7302202 (.25 mm), 7302203 (.3 mm), and 7302204 (.35 mm)	GE	7156428A	IN	(317102) or (317107)	EN - 1079051A - issued 06/07

B-6 - 5

Nordson US Hot Melt Products (sorted by Model) Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
e driver	e driver	FR GE IT JA SK	7119119B 7105140A 7146341B 7105121A* 7146723B	MA	(317102) or (317107)	EN - 1044198B - Issued 05/05 * available at Nordson K.K
e driver 2, 3, 4	e driver2, e driver3, e driver4	FR JA	7119120C 7105120A*	MA	(317102) or (317107)	EN - 1032560C - Issued 05/05 * available at Nordson K.K
E400	E400 Driver	GE IT PL	7105712B 7119990B 7105296B	MA	(317102) or (317107)	EN - 1037528B02 - Issued 02/10
E400	E400 Hot Melt Electric Gun	GE IT SP	7105764A 7119991B 7105672A	MA	(317102) or (317107)	EN - 1048256B - Issued 12/05
E400B	E400B Rebuildable Hot Melt Electric Applicator	DU	7560271A02	MA	(317102) or (317107)	EN - 1085353A02 - Issued 05/15
E400NP	E400NP Driver	DU GE IT PL SK	7192497C 7146748C 7146351C 7560084C 7146734C	MA	317102) or (317107))	EN - 1038035C02 - Issued 02/10
E401	E401 Electric Applicator	GE SK	7105711C 7146735C	MA	(317102) or (317107)	EN - 1045491C - Issued 07/05
ES400	ES400 Driver	GE SP	397054B 7105832B	MA	(317102) or (317107)	EN - 1015800B - Issued 06/02
ES400	ES400 Electric Applicator	IT PL SK	7146342B 7105297B 7146722B	MA	(317102) or (317107))	EN - 1007312B - issued 06/02

B-6 - 6

Nordson US Hot Melt Products (sorted by Model) Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
FP-200	FP-200 Multi-Swirl Hand-Held Applicator (Title version C: FP-200 Gun System)	IT	413042C	MA	(317102) or (317107)	EN - 108391_04 - Issued 02/16
FP-200	FP-200 Guns	JA PL	464876C* 7179577_03	MA	(317102) or (317107)	EN - 237478_03 - Issued 10/12 * available at Nordson K.K
H-20	Series H-20 Automatic Applicators	CZ FR GE IT PL RO RU	7105866G02 7560042G02 213575G02 7580198G02* 7156917G02 7192770G02 7146208G02	MA	(317102) or (317107)	EN - 104449G02 - Issued 04/15 Issue date of translation FR: 01/15 Issue date of translations CZ, PL, RO, RU: 07/04 * = not yet released
H-200	Series H-200 Guns	CZ DA DU FI FR GE IT NO PL SP SW	7135297D* 412828G 284196K 412670G 284197G 284198J 284199G 409302G 458144G 284200G 290700G	MA	(317102) or (317107)	EN - 104457K - Issued 08/05 * = Document and translation is NOT issued by TDLL ! Obsolete!
H-200	Series H-200 Mini-Bead Guns	JA RU	7119718B 7146979B	MA	(317102) or (317107)	EN - 107075B - Issued 09/15 Issue date of translations 04/04 Obsolete!

B-6 - 7

Nordson US Hot Melt Products (sorted by Model) Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
H-400	Series H-400 Guns	DU FI FR GE IT JA PL SP SW	213013C 213394C 458060C 412635C 458074C 213264C* 458279C 458239C 213116C	MA	(317102) or (317107)	EN - 331170D - Issued 08/05 Obsolete! * available at Nordson K.K
H-440	Series H-440 Guns	DU FI FR GE IT JA PL SP SW	213016C 213404C 458061C 412993C 458029C 213460C* 213323C 458240C 458217C	MA	(317102) or (317107)	EN - 237564C02 - Issued 03/02 Obsolete! * available at Nordson K.K
HMS	HMS Series Applicators (Titel version C: Spray Applicators)	DU SP	7156688F 213501C	MA	(317103) or (317106)	EN -106926F - Issued 09/05 Obsolete!
HMS	Section 10 Filter	DU	7156696E02	MA	(317102) or (317107)	EN - 106935E02 - Issued 01/07 Section applies to applicators with an in-out filter Obsolete!
HMS	Section 11 Electrical System	DU	7156697D	MA	(317102) or (317107)	EN - 106938D - Issued 12/04 Section applies to applicators with M-style cordsets Obsolete!

B-6 - 8

Nordson US Hot Melt Products (sorted by Model) Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
MB 200	Meltblown (MB200) Applicators	CZ DA DU FR GE IT PL SP SW	213849A 213928A 213901A 213936A 213888A 213910A 213992A 213961A 213881A	OP	(317102) or (317107)	EN - 1029962B - Issued 12/04 Obsolete!
MiniBlue	MiniBlue	FR GE IT JA RU SP	7105639A 7105630A 7105673A 7105813A* 7135976A 7105651A	MA	(317102) or (317107)	EN - 1013124A02 - Issued 01/08 * available at Nordson K.K
MiniBlue II	MiniBlue II Pneumatic Applicators	CZ DA DU FI FR GE HU IT JA KO LA PL PO RU SK SP SW	7169407_06 7179930_06 7156902_06 7179863_06 7156666_06 7156674_06 7179902_06 7156673_06 7156656_06 7179860_06 7192985_06 7156735_06 7179574_06 7156665_06 7156928_06 7156670_06 7179607_06	MA	(317102) or (317107)	EN - 1096215_07 - Issued 01/17
MiniBlue II	MiniBlue II Pneumatic Applicators	-	-	MA	(317102) or (317107)	EN - 1124393_02 - Issued 04/16 New!

B-6 - 9

Nordson US Hot Melt Products (sorted by Model) Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
MiniBlue II	MiniBlue II Low Profile Ball and Seat Pneumatic Applicators	FR	7192723_02	MA	(317102) or (317107)	EN - 1120707_02 - Issued 06/14
MiniBlue II	Plastic Cover Kit P/N 1103018	FR GE IT PL RU SP	7156969A 7156975A 7156972A 7156970A 7169101A 7156976A	IN	(317102) or (317107)	EN - 1104548A - Issued 11/10
PatternJet	PatternJet Adhesive Dispensing Gun	JA	7119716A	MA	(317102) or (317107)	EN - 1063110A - Issued 03/10
PatternJet	PatternJet Applicators (Title version A02: PatternJet Adhesive Dispensing Gun)	IT	7135799A02	MA	(317102) or (317107)	EN - 1071823_05 - Issued 04/15
PatternJet	Cordset Replacement Kit	JA	7119717A	IN	(317102) or (317107)	EN - 1068356A02 - Issued 06/06
PatternJet Plus	PatternJet Plus Applicators	GE IT PL	7169501_02 7169496_02 7192362_02	MA	(317102) or (317107)	EN - 1095295_03 - Issued 04/16
PatternPro	PatternPro Variable Pitch Guns	FR GE IT JA SP	7119471B 7119467B 7119468B 7105877B 7119469B	MA	(317102) or (317107)	EN - 1048257B - Issued 11/05

B-6 - 10

Nordson US Hot Melt Products (sorted by Model) Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
SD Series	SD Series Electric Gun Driver	CZ DU FR GE IT SP SW	7156026D 458181B 458036A 412632A 409359A 412927A 412723A	MA	(317102) or (317107)	EN - 229766D - Issued 05/05 Replaces E26 Electric Gun Driver (see Section G - Walcom)
Speed-Coat	Universal Applicators (Speed-Coat)	CZ DA DU FR GE IT JA PL PO RU SK SP TU	7169877_06 7560413_06 7560230_06 7192293_06 7135300_06 7119464_06 7119450A** 7156357_06 7560396_06 7169142_06 7560876_06 7560086_06 7192919_06	OP	(317102) or (317107)	EN - 1063324_06 - Issued 04/15 ** available at Nordson K.K
Speed-Coat	Section 9 Module	DU IT PL PO RU	7156695B04 7560694_07 7169499B04 7560695B04 7169139B04	MAN	(317102) or (317107)	EN - 1050064_07 - Issued 2015 Section applies to applicators with Universal Speed-Coat modules
SureSeal	SureSeal Applicator System (Title version B: SureSeal Gun System)	FR GE IT JA SP	7105640B 7105638B 7105674B 7119303B* 7105652B	MA	(317102) or (317107)	EN - 1041226_04 - Issued 09/16 * available at Nordson K.K
SureBead	SureBead Module Replacement	PL	7119288A	IN	(317102) or (317107)	EN - 1041616A - Issued 09/03

B-6 - 11

Nordson US Hot Melt Products (sorted by Model) Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
UM22/ UM25	Universal Applicators (UM22/UM25)	CH CZ DA DU FR GE GR HU IT JA PL PO RU SK SL SP TU	7580078A04 7135696A04 7135200A04 7119425A04 7119624A04 7119473A04 7146144A02 7156461A02 7119443A04 7119452A** 7146021A04 7560395A04 7146740A04 7580222A04* 7146611A02 7146134A04 7119678A04	OP	(317102) or (317107)	EN - 1063323A04 - Issued 03/10 ** available at Nordson K.K * not yet released
UM22/ UM25/ UM50	UM22/UM25/ UM50 Module Rebuild Kit - P/Ns 1049909 (Minor) = and 1049908 (Major) (Title version A: UM22/UM25 Module Rebuild)	FR GE	7119625A 7119114A	IN	(317102) or (317107)	EN - 1050983_04 - Issued 0715
UM25	Section 9 Module	CZ DU GE IT JA PO PL RU	7146719_07 7156694C06 7169431_07 7560696_07 7119454B* 7560697_07 7156897_07 7169138C06	MAN	(317102) or (317107)	EN - 1049772_07 - Issued 05/15 Section applies to applicators with UM25 modules * available at Nordson K.K
UM50	Universal Applicators (UM50)	FR GE GR IT RU SP	7560075_04 7135530_04 7146145A 7135531_04 7560916_04 7169467_04	OP	(317102) or (317107)	EN - 1072064_04 - Issued 08/11

B-6 - 12

Nordson US Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
UM50	Section 9 Module	SP	7169464_06	MAN	(317102) or (317107)	EN - 1069046_06 - Issued 07/11 Section applies to applicators with UM50 modules
Universal	Universal Series Spray Applicators	CZ GE IT JA PL PO RU SP	7146718_05 7169430_05 7192974_05 7119449C** 7156896_05 7560693_05 7169137_05 7169463_05	MA	(317103) or (317106)	EN - 1050063_05 - Issued 07/11 ** = available at Nordson K.K
Universal	Section 10 Filter (in-out)	CZ GE IT JA PL PO RU SP	7146720 A02 7169432 A02 7560698 A02 7119457A** 7156898 A02 7560699 A02 7169140 A02 7169465 A02	MA	(317102) or (317107)	EN - 1050065A02 - Issued 01/07 Section applies to applicators with a Universal in-out filter ** available at Nordson K.K
Universal	Section 10 Filter (Threaded)	CZ	7560681_03	MA	(317102) or (317107)	EN - 1096214_03 - Issued 07/11 Section applies to applicators with a threaded filter
Universal	Section 11 Electrical System (M-style)	CZ DU GE IT PL PO RU SP	7146721B03 7156698B03 7169433B03 7560700_04 7156899_04 7560701_04 7169141_04 7169466_04	MA	(317102) or (317107)	EN - 1050067_04 - Issued 07/11 Section applies to applicators with Universal M-style cordsets
Universal	Section 11 Electrical System (T-style)	CZ	7560682B03	MA	(317102) or (317107)	EN - 1050066B03 - Issued 01/08 Section applies to applicators with Universal T-style cordsets

B-6 - 13

Nordson US Hot Melt Products (sorted by Model) Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Universal	High-Speed Universal Series Applicators	FR GE PL	7169156A03 7169161A03 7560053A03	MA	(317103) or (317106)	EN - 1079832_04 - Issued 04/15
Universal	Universal Applicators (Bead /Slot)	IT RU SP	7135951_02 7146980A 7560477_02	OP	(317102) or (317107)	EN - 1084530_02 - Issued 08/11
Universal	Universal Slice Applicator	GE	7119610B	MA	(317103) or (317106)	EN - 1031709B02 - Issued 03/11
Universal	Universal Slice Applicator	IT SW	7179422A02 7156527A02	MA	(317103) or (317106)	EN - 1072085A02 - Issued 03/09
Universal	Universal Controlled Fiberization (CF) Spray Nozzles (Title version A: Controlled Fiberization (CF) Lamination Application)	GE SP	7169575_02 7156218A	MA IN	(317103) or (317106)	EN - 1072379_02 - Issued 07/11
Universal	Universal Signature Spray Nozzles (Continuous Applications) (Title version A02: Signature Lamination Applications)	GE SP	7169576_03 7156216A02	MA IN	(317103) or (317106)	EN - 1076139_04 - Issued 10/11
Universal	Universal Signature Spray Nozzles (Intermittend Applications) (Title version A: Signature Lamination Applications (Intermittend))	GE SP	7169577_02 7156217A	MA IN	(317103) or (317106)	EN - 1090174_02 - Issued 07/11
Universal	Universal SureWrap Spray Nozzles	GE	7169578_01	MA	(317103) or (317106)	EN - 1103674_01 - Issued 07/11

B-6 - 14

Nordson US Hot Melt Products (sorted by Model) *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Universal	Universal Summit Spray Nozzles	CZ GE SP	7560683_02 7169579_02 7156215_02	MA IN	(317103) or (317106)	EN - 1072400_02 - Issued 07/11
World Gun Series	World Gun Series	CZ DA DU FI FR GE IT NO PL PO SP SW	213788A 213908A 213869A 397147A 213830A 213819A 213899A 213897A 213916A 213824A 213818A 213826A	MA	(317103) or (317106)	EN - 1027562C - Issued 11/03

B-7 - 1

Nordson US Hot Melt Products (sorted by Model)

Foam

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
FM 200	FoamMelt 200 Processor	DU FR GE IT PL RU SP	213492B 213503B 213474D02 7135744D 7119786D 7560775_06 213981C	MA	(317102) or (317107)	EN - 321222_06 - Issued 04/15
FM 200	FoamMelt 200 Processor	DA DU FI FR GE IT JA NO PL PO SP SW	447735A 447752A 464748A 447771A 447761B 447751A 447697A* 464702A 7119290A 464787A 447773A 447792A	OP	(317102) or (317107)	EN - 321380B - Issued 03/01 * available at Nordson K.K
Foam Mix AG-900 Series	Foam Mix AG-900 Series Dispensing Gun	FR GE IT PL SP	292876A 292728A 292729A 7119198B 317283A	MA	(317102) or (317107)	EN - 108168A - Issued 09/91 108168B - Issued 01/97
Foam Mix AG-900 Series	AG900+ Applicators	JA	7169251A*	MA	(317102) or (317107)	EN - 1063320A - Issued 04/07 * available at Nordson K.K

Issued by Technical Documentation Local Languages (TDLL) Department, Nordson Engineering, Lüneburg
 Status : July 2017

B-7 - 2

Nordson US Hot Melt Products (sorted by Model) *Foam*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Foam Mix AG-900+ Series	AG900+ and AG900+ S Applicators	GE	7156452A	MA	(317102) or (317107)	EN - 1098464A - Issued 09/09
SureFoam	SureFoam Foam Dispensing System	FR GE IT PO SP	7146091A 7146092A 7146130A 7146082A 7146068A	MA	(317102) or (317107)	EN - 1079037A05 - Issued 03/14

Nordson Finishing Products (sorted by Product Title)

Automotive / Container / Electronics / Liquid / NSE

C-1 - 1

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	0-8 CC Accu-Drop Ejector Gun	GE IT	7192283A_03 7192224A_03	MA	(317102) or (317107)	EN - 1090618A_03 - Issued 02/10
--	0-900 psi Pressure Reducing Diaphragm Regulator (Title - version_06: 0-900 psi Diaphragm Regulator)	FR IT PL RU SE SP	7146597D03 7192760_05 7146481D02 7169037D03 7560382_06 7146631D03	IN	(317102) or (317107)	EN - 1009506_07 - Issued 01/16
--	0-1000 PSI Pressure Transducer and Amplifier	FI FR GE IT PL PO RU SE SP	7560489_01* 7560185_01 7560184_01 7560186_01 7560187_01 7560188_01 7580090_01 7560780_01 7560189_01	IN	(317102) or (317107)	EN - 1602989_01- Issued 02/13 * = not yet translated
--	2-8 CC Ejector Gun	CZ FR GE IT PL RU SP TU	7179948B_02 7179866B_02 7179816B_02 7179833B_02 7179681B_02 7179909B_02 7179845B_02 7179632B_02	MA	(317102) or (317107)	EN - 1040029_03 - 03/14
--	2-8 CC Ejector Gun Fluid Cartridge Kit	CZ FR GE IT PL RU SP TU	7179949B 7179867B 7179817B 7179834B 7179682B 7179910B 7179846B 7179633B	IN	(317102) or (317107)	EN - 1040851B02 - Issued 11/04

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 2

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
23-17	7- and 10-Inch Air Motors with Air Valve	CZ FR GE IT SP	7192248 C 7105583B 458463 C 7119928 C 7146254 C	MA	(317102) or (317107)	EN - 334607C - Issued 03/05
1-8	25B 2:1 Plated Steel Pump (Title version E-H: 25B Pumps - Obsolete!)	DU FR GE IT PL PO SP SW	292973E 292974E 292975E 292976 P02 412606E 317162E 317177E 458109H	MA	(317102) or (317107)	EN - 104330P02 - Issued 05/07
--	24B 4:1 Plated Steel Pump	IT	7192749F02	MA	(317102) or (317107)	EN - 1044131F02 - Issued 05/07
--	25B 16:1 Aluminium Pump	FR IT RU	7105396B 7192747 E02 7169036 E02	MA	(317102) or (317107)	EN - 1044132E02 - Issued 05/07
--	25B 16:1 Stainless Steel Pump	FR GE IT	7105397B 7580158_03 7192748_03	MA	(317102) or (317107)	EN - 1044133_03 - Issued 11/12
--	25B 27:1 Aluminium Pump	FR	7105398B	MA	(317102) or (317107)	EN - 1044134_03 - Issued 11/12
--	25B 27:1 Stainless Steel Pump	FR	7105399B	MA	(317102) or (317107)	EN - 1044135_03 - Issued 11/12
--	55-Gallon Powder Drum Truck for Bulk-Feed Powder Transfer Systems	FR RU	7169980A03 7156610A03	IN	(317102) or (317107)	EN - 1062573_04 - Issued 04/15

Nordson Finishing Products (sorted by Product Title)

Automotive / Container / Electronics / Liquid / NSE

C-1 - 3

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
1-5	64B Pump 15:1 Aluminium	DU GE IT SP	7179360L04 7179298L04 458241L04 458331L04	MA	(317102) or (317107)	EN - 104321L04 - Issued 01/09
1-5A	Pressure Housing Retainer Service Kit 64B Stainless Steel Pumps (Title version B: 64B Housing Retainer Service Kit)	FR GE IT	292811B 292812B 292813B	IN	(317102) or (317107)	EN - 108695C - Issued 01/96
--	90 Degree Cable Routing Fitting Kit	GE	7560779_01	IN	(317102) or (317107)	EN - 1609315_01 - Issued 05/16
--	2200-245-Series Kiss Valves (NSE)	PL	7580065_01	MAN	(317102) or (317107)	EN - 7439854_01 - Issued 08/16
4-2	A4B Airless Manual Spray Gun (Title version E: A4B Airless Handgun)	GE PL	107973E 409482E*	MA	(317102) or (317107)	EN - 107973J02 - Issued 05/08 * = not yet translated
--	A7A Lancing Spray Guns	PL SP	7560852_02 7192793_02	MA	(317102) or (317107)	EN - 107009_02 - Issued 12/13
4-6	A7A Single and Dual Automatic Airless Spray Guns (Title version D - J: A7A Airless Spray Gun)	FR GE IT PL RU SP	7105283J 317117D 292915D 409484D 397506L 458333E	MA	(317102) or (317107)	EN - 107966L - Issued 03/06 OLD!
--	A7A Single and Dual Automatic Airless Spray Guns	GE	7169042A	MA	(317102) or (317107)	EN - 1072640A - Issued 08/06 NEW!

Nordson Finishing Products (sorted by Product Title)

Automotive / Container / Electronics / Liquid / NSE

C-1 - 4

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	A7A Single and Dual Modular Automatic Airless Spray Guns	CZ GE IT RU SP SW	7146615A 7169669A 7192753A 7169035A 7560446A 7169231A	MA	(317102) or (317107)	EN - 1072609A - Issued 08/06
--	A7A Application Head for Liquid Foil	GE	213274C	IN	(317102) or (317107)	Created by Nordson Engineering GmbH Issued 01/03
4-22	A20A Electric Airless Spray Gun (Title version E: A20A Electric Spray Gun)	FR GE IT PO RU SP	292916E 292917E 292918E 317143E 403096E 317140E	MA	(317102) or (317107)	EN - 108182G02 - Issued 06/08
4-13	A11A Compound Gun	GE	317197D	MA	(317102) or (317107)	EN - 107977E - Issued 09/03
--	Adjustable Mounting Assembly for Automatic Guns	GE	7169557B	IN	(317102) or (317107)	EN - 104618B - Issued 03/98
19-6	Air Lubricator Adjustments and Oils (Title version D: Adjusting Air Line Lubricators)	DU FR GE IT PL PO SP SW TU	292985D 292986E 292987D 292808E 412601E 317114D 317152D 458112D 7560858E	IN	(317102) or (317107)	EN - 108152E - Issued 01/04
--	Air Operated Color Change Valve	PL	7179705A	IN	(317102) or (317107)	EN - 334619A - Issued 10/99

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 5

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
-	Airless Material Pressure Controller	GE	213236D	IN	(317102) or (317107)	Created by Nordson Engineering GmbH Issued 11/02
26-21	Auto-Flo Automatic Dispensing Valve	GE	405069E	MA	(317102) or (317107)	EN - 229798E - Issued 03/06
--	Auto-Flo Zero-Cavity Automatic Dispensing Valve	FR	7179171D02	MA	(317102) or (317107)	EN - 303796D02 - Issued 06/03
--	Auto-Flo II Anti-Drool Dispense Valves	CZ FR GE IT RU PL SP TU	7179950_01 7179868_01 7179818_01 7179835_01 7179911_01 7179683_01 7179847_01 7179634_01	MA	(317102) or (317107)	EN - 1104014_01 - Issued 05/12
--	Auto-Flo II Automatic Dispense Valves	CZ FR GE IT PL RU SP TU	7179951_01 7179869_01 7179819_01 7179836_01 7179684_01 7179912_01 7179848_01 7179635_01	MA	(317102) or (317107)	EN - 1104010_01 - Issued 05/12
--	Auto-Flo II CP Dispense Valves	CZ FR GE IT PL RU SP TU	7179952_01 7179870_01 7179820_01 7179837_01 7179685_01 7179913_01 7179849_01 7179636_01	MA	(317102) or (317107)	EN - 1104015_01 - Issued 05/12

Nordson Finishing Products (sorted by Product Title)

Automotive / Container / Electronics / Liquid / NSE

C-1 - 6

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Auto-Flo II Dispense Valves for Pro-Meter-S and -S2K Applications	CZ FR GE IT PL RU SP TU	7179953_01 7179871_01 7179821_01 7179838_01 7179686_01 7179914_01 7179850_01 7179637_01	MA	(317102) or (317107)	EN - 1104225_01 - Issued 01/13
--	Auto-Flo II Spring-Close Standalone Dispense Valve Cleaning	CZ FR GE IT PL RO RU SP TU	7179954A 7179872A 7169209A 7179839A 7179687A 7169197A 7179915A 7179851A 7179638A	IN	(317102) or (317107)	EN - 1105175A - Issued 02/11
--	Auto-Flo II Zero Cavity Dispense Valves	CH CZ FR GE IT PL PO RO RU SP TU	7560456_03 7179955_02 7179873_02 7156914_02 7179840_02 7179266_02 7179138_03 7156922A 7179916_03 7169534_02 7179639_02	MA	(317102) or (317107)	EN - 1103506_03 - Issued 03/14
--	Automatic Iso-Flo Voltage-Block System	PL	7179700C	MA	(317102) or (317107)	EN - 106589C - Issued 10/96

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 7

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
10-21	Automatic Iso-Flo HD Voltage-Block System	DU FR GE IT PL SP	7156396G02 7119161F 213475G02 409117G02 7179701G02 447670G02	MA	(317102) or (317107)	EN - 107158G02 - Issued 05/08
10-22	Automatic Iso-Flo HD Automatic Voltage Block System	DU FR GE IT PL SP	7156397B 7119163B 7156383B 7156387B 7179702B02 213282B	OP	(317102) or (317107)	EN - 107159B02 - Issued 10/03
--	Back Pressure Diaphragm Regulator	FI GE PO SP	7560490A* 7119940A 7135812A 7146632A	IN	(317102) or (317107)	EN - 1060626A - Issued 03/05 * = not yet translated
--	BR-1 Induction Temperature Controller	DU GE SP	7169789_02 7179573_02 7169745_02	MA	(317102) or (317107)	EN - 1106132_04 - Issued 01/16
--	Bubble Detect Calibration Kit	GE IT	7192278B 7192222B	IN	(317102) or (317107)	EN - 1055813B - Issued 11/04
--	Bubble Detection System for the Pro-Meter Controller with Process Sentry	GE IT	7192241B 7192187B	IN	(317102) or (317107)	EN - 1010995B - Issued 02/01
14-5	CanWorks Display Module	GE	315747A	MA	(317102) or (317107)	EN - 106697B - Issued 09/03
--	CanWorks SM-1 Spray Monitor	GE	7105092B	MA	(317102) or (317107)	EN - 106698B - Issued 09/03

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 8

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	CE20 Gun Air Injector Manifold Assembly Kit	GE IT	7192277C 7192193C	IN	(317102) or (317107)	EN - 1055812C - Issued 12/04
--	CE20 Gun	GE IT	7135986A03 7135975A03	MA	(317102) or (317107)	EN - 334678A03 - Issued 07/12
--	CE20 2K Large Cycle Dispense Gun	GE IT	7192287 7192198	MA	(317102) or (317107)	EN - 1107352 - Issued 09/11
12-48	Century C-708 and C-718 Workcell	DU FR GE	409005A 409006A 409003A	OP	(317102) or (317107)	EN - 303847A - Issued 05/98
-	Circulation Kit for 180D / 360D Pumps	RU	397508B	IN	(317102) or (317107)	EN - 1006454B - Issued 09/02
6-15	Circulation Kits for CP Pumps (Title version B: Circulation Valve Kit)	DU FR GE SP	292970B 292971B 292972B 409315B	IN	(317102) or (317107)	EN - 108000C - Issued 11/02
--	Clean and Black Primer Five-Gallon Pressure Pot	GE IT	7192279A02 7192194A02	IN	(317102) or (317107)	EN - 1066149A02 - Issued 10/07
12-40	Clean Coat Workcell	SP	403257A	MA	(317102) or (317107)	EN - 229801A - 02/97
17-22	CleanSpray Controller	GE PO SP	403143B 317141B 317137B	MA	(317102) or (317107)	EN - 108330E - Issued 05/04
4-46	CleanSpray II Extension Assembly	SP	213620B	IN	(317102) or (317107)	EN - 331286C - Issued 06/03

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 9

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
14-2	CleanSpray System Operation	PO SP	317168C 317155C	OP	(317102) or (317107)	EN - 108684C - Issued 10/03 Date of translations 10/96
--	CleanSpray XT Spray Gun	GE	7119997A02	MA	(317102) or (317107)	EN - 1067500A02 - Issued 07/06
--	Compact Manual Iso-Flo Voltage Block System	PL	7179704B	MA	(317102) or (317107)	EN - 108390B - Issued 07/96
26-26	Controlled Pressure (CP) Gun	GE	409394C	MA	(317102) or (317107)	EN - 303788C - Issued 04/02
12-43	Conveyorized Century Workcell	FR GE IT	412941A 412942A 413052A	MA	(317102) or (317107)	EN - 303778A - Issued 06/99
1-9	CP Pump	DU FR GE PL SP	292964E 292965E 292966E 7560822_03 409312H	MA	(317102) or (317107)	EN - 104373_03 - Issued 10/15
--	CP II Inline Regulator	CZ FR GE IT PL RU SP TU	7179956A 7179874A 7179823A 7179841A 7179688A 7179917A 7179853A 7179640A	MA	(317102) or (317107)	EN - 1097151_02 - Issued 06/13

Nordson Finishing Products (sorted by Product Title)

Automotive / Container / Electronics / Liquid / NSE

C-1 - 10

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	CP II Regulator	CZ FR GE IT PL RU SP TU	7179957A_04 7179875A_04 7179824A_04 7179842A_04 7179689A_04 7179918A_04 7179854A_04 7179641A_04	MA	(317102) or (317107)	EN - 1075654A_05 - Issued 06/13
--	CWS 100 - Cable Wet Coating System	EN GE	213391A 464925A	MA	(317102) or (317107)	Created by Nordson Engineering GmbH Issued 08/01
--	DR-1676 Pump	CZ FR TU	7560093_03 7580074_07 7560856_05	MA	(317102) or (317107)	EN - 237432_07 - Issued 04/17
28-13	Drip and Drag Applicator Tool with Felt Wick Dispenser	GE	447610A	MA	(317102) or (317107)	EN - 331287A - Issued 12/99
--	Dual-Pump Primer Delivery Stand	FR GE IT PL SP	7146710A-02 7192286A-02 7156056A-02 7560449A-02 7560561A-02	MA	(317102) or (317107)	EN - 1065659A-02 - Issued 11/05
--	Dual Pro-Meter S-Series PCI Controller	CH GE IT PO RO RU SP	7560457A 7156921A 7146277A 7146949A 7156940A 7560262A 7169522A	MA	(317102) or (317107)	EN - 1083956A - Issued 01/08
--	Dual-Zone Temperature Control Unit	FR PL	7192896A 7169280A	MA	(317102) or (317107)	EN - 1107681_04 - Issued 05/16

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 11

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	EcoLiner Compound Gun	FR GE	7146114A 7179517A	MA	(317102) or (317107)	EN - 1069243A - Issued 03/06
0-9	Electrostatic Cable Care and Installation	GE IT SW	409102C 412636C 458120C	MA	(317102) or (317107)	EN - 107913C - Issued 02/04
0-8	Electrostatic System Checks	GE IT SW	409101B 412630B 458119B	IN	(317102) or (317107)	EN - 107964B - Issued 04/96
--	EP2 Pump System	FI PL PO RU	7560491A02* 7146478 A02 7135806A 7169039 A02	MA	(317102) or (317107)	EN - 1072608A02 - Issued 05/08 = not yet translated
--	EP-2 Three-Piston Pump	FI GE PL PO RU SP	7560492_03* 7119183A 7560190_03 7135807A 7169040A 7119201A	MA	(317102) or (317107)	EN - 1049229_03 - Issued 04/15 * = not yet translated
--	EP-2 Three Piston Pump (QRG)	PL	7560191_01	IN	(317102) or (317107)	1607026_01 - Issued 2015
9-15	EPS6 Electrostatic Power Supply	CZ DU GE IT PL SP SW	7156774 D 7179418 D 397478 D 409385 D 7192509 D 7119066 D 458122 C	MA	(317102) or (317107)	EN - 237381D - Issued 11/01
9-13	EPS-8 and EPS-9 Electrostatic Power Supplies	IT	409384B	MA	(317102) or (317107)	EN - 107068C - Issued 11/01

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 12

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
17-23	Extended Watchdog Pulse Timer	GE PO SP	403145A 317142A 317138A	IN	(317102) or (317107)	EN - 108821B - Issued 02/01
--	Felt Installation for Flow-Through-Felt Applicators	GE IT SP	7192234A 7192192A 7560562A	IN	(317102) or (317107)	EN - 1043852A - Issued 04/04
--	Five-Gallon Black Primer T-Handle Assemblies	GE IT	7192226B 7192186B	MA	(317102) or (317107)	EN - 343559B - Issued 05/04
--	Flo-Brush PDMP Applicator Tool	GE IT PL	7192284A 7192217A 7560448A	MA	(317102) or (317107)	EN 1091853A - Issued 04/09
--	Flowmeter with Encoder Assembly	GE IT SP TU	7192242E 7192188E 7560722E 7560014E	MA	(317102) or (317107)	EN - 1016731E - Issued 03/05
--	Flowmeter Service Kits	GE IT SP TU	7192225C02 7192219C02 7560721_04 7560013_03	IN	(317102) or (317107)	EN - 334679_04 - Issued 2015
--	Flow-Through-Felt Gravity Feed Applicator Tool	GE IT	7192288_01 7192218_01	MA	(317102) or (317107)	EN - 1108200_01 - Issued 10/11
--	Flow-Through-Felt PDMP Applicator Tool	FR GE IT SP	7146709B02 7192356_04 7156057_04 7560563_05	MA	(317102) or (317107)	EN - 1065657_05 - Issued 11/15
--	Flow-Through-Felt Primer Dispensing System	SP	7560565A	MA	(317102) or (317107)	EN - 1009200A - Issued 02/02

Nordson Finishing Products (sorted by Product Title)

Automotive / Container / Electronics / Liquid / NSE

C-1 - 13

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Flow-Through-Felt Rub Block Maintenance	FR GE IT SP	7146711B 7192233B 7156058B 7560566B	IN	(317102) or (317107)	EN - 1045635B - Issued 06/05
--	Flow-Through-Felt System Operator's Card	GE IT SP	7192275A 7192220A 7560567A	OP	(317102) or (317107)	EN - 1045721A - Issued 03/04
--	Flow-Through-Felt Troubleshooting Guide	FR IT SP	7156084A 7156083_02 7560568_02	IN	(317102) or (317107)	EN - 1063663_02 - Issued 09/13
6-16	Hard Seat Fluid Pressure Regulator	GE RU SP	458158E 7119602H 412726H	IN	(317102) or (317107)	EN - 104742H - Issued 11/03
--	HD Cable and Retrofit Cable Care and Installation	PL	7192510B	IN	(317102) or (317107)	EN - 229802B - Issued 01/06
--	Helical Flowmeter	GE IT	7192276B 7192221B	IN	(317102) or (317107)	EN - 1050114B - Issued 02/05
5-2	High Pressure Fluid Hoses	IT SW	458242C 458113C	IN	(317102) or (317107)	EN - 108145_04 - Issued 08/13
26-14	HIVISC Gun Manual	SP	409408A	MA	(317102) or (317107)	EN - 107001B - Issued 10/98
--	Ink-Dot Controller	FI GE PL PO SP	7560493C02* 7560398C02 7156529C02 7135802C02 7146636C02	MA	(317102) or (317107)	EN - 106605C02 - Issued 09/03 * = not yet translated

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 14

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
4-33	Ink-Dot Electric Spray Gun	PL PO SP	7156528D 7135803D 7146635D	MA	(317102) or (317107)	EN - 229727D - Issued 01/01
--	Ink-Dot Electric Spray Gun	FI FR GE	75604934_02* 7169600A 7560399_02	MA	(317102) or (317107)	EN - 1103065_02 - Issued 10/11 * = not yet translated
--	Ink-Dot Hydraulic System	PL PO SP	7156530 A02 7135804 B 7146633 B	MA	(317102) or (317107)	EN - 237436B and EN - 237436A02, both Issued 09/03
--	Ink-Dot Hydraulic System	FI GE	7560495A* 7560400A	MA	(317102) or (317107)	EN - 1103066A - Issued 7/10 * = not yet translated
--	Ink-Dot Hydraulic System with Reservoir Manifold	FR GE	7169601A 7560476A	MA	(317102) or (317107)	EN - 1103067A - Issued 07/10
	Ink-Dot System with Reservoir Manifold	FR	7169602A	OP	(317102) or (317107)	EN - 1100472A - Issued 06/12
14-18	Ink-Dot System	DU GE IT PO SP	397055B 447720B 407433A 317169A 317156A	OP	(317102) or (317107)	EN - 229726B02 - Issued 10/03
--	Ink-Dot Series II Driver	PO SP	7135808B02 7146634B02	IN	(317102) or (317107)	EN - 237466B02 - Issued 09/03

Nordson Finishing Products (sorted by Product Title)

Automotive / Container / Electronics / Liquid / NSE

C-1 - 15

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
3-54	Inverted Dual High Pressure Fluid Filters Assemblies (Title Versions A-C: Inverted Dual High Pressure Fluid Filters)	CZ DU FR GE IT PL PO RU SP	7146617C02 7179361C03 7156879C03 7179299C03 464946C03 7146480C02 7135810C 7119603C 7146627C03	IN	(317102) or (317107)	EN - 334621C03 - Issued 02/09
3-53	Inverted High Pressure Fluid Filters	DU GE IT PL RU SE SP SW	7179362B 213100_03 464891B 7146479B 397505B 7560378B 213148B 7169233B	IN	(317102) or (317107)	EN - 331290_03 - Issued 01/17 (B version issued 04/04)
--	IPS-20 Automatic Electrostatic System Controller	DU FR GE IT SP	7179373A 7156465A 7169413A 7179376A 7179332A	MA	(317102) or (317107)	EN - 1084168A - Issued 06/08
--	IPS-20 Manual Electrostatic System Controller	DU FR GE IT SP	7179372A 7156466A 7169414A 7179375A 7179331A	MA	(317102) or (317107)	EN - 1084167A - Issued 06/08
10-26	Iso-Flo Coupling Repair	IT	213735C	IN	(317102) or (317107)	EN- 229782C - Issued 01/02
10-24	Dump Shuttle Kit for the HD Manual Iso-Flo	IT	213734B	IN	(317102) or (317107)	EN - 229771B - Issued 11/97

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 16

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
10-25	Dump Shuttle Kit for the HD Automatic Iso-Flo	GE	7119447C	IN	(317102) or (317107)	EN - 229772C - Issued 02/01
10-5	Iso-Flo Supply Pump	FR	269873	IN	(317102) or (317107)	EN - 108621B - Issued 12/96
--	ITRAX Electronic Pressure Regulator	FI GE	7560499_03* 7560401_03	MA	(317102) or (317107)	EN - 1604922_03 - Issued 01/16 * = not yet translated
--	iTRAX PRx Module	SP	7169511A04	MA	(317102) or (317107)	EN - 1078355_08 - Issued 04/15
--	ITRAX PRx II Module	FI GE	7560498_02* 7560402_02	MA	(317102) or (317107)	EN - 1604923_02 - Issued 03/15 * = not yet translated
--	iTRAX Spray Controller	FI GE SP	7560497_06* 7560286_06 7169512A04	MA	(317102) or (317107)	EN - 1079459_06 - Issued 08/15 * = not yet translated
--	iTRAX Spray Monitor with Can-in-Pocket Feature	FI GE PL SP	7560496_04* 7560287_04 7146477A02 7169513A03	MA	(317102) or (317107)	EN - 1066206_06 - Issued 06/16 * = not yet translated
--	ITRAX System Operator Interface User' s Guide	FI	7560500_01*	OP	(317102) or (317107)	EN - 1604854_01 - Issued 02/14 * = not yet translated
21-56	Kinetix Electrostatic Spray Gun Automatic Version 60kV Airspray and KVLP Waterborne	FR GE IT	7105187F 213172C 464885B	MA	(317102) or (317107)	EN - 334609H04 - Issued 08/08

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 17

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
8-8	Kinetix Electrostatic Spray Gun Automatic Air-Assisted Airless	FR GE IT SP	7105239E 213160B 464739A 213284B	MA	(317102) or (317107)	EN - 334593F03 - Issued 08/08
8-13	Kinetix Electrostatic Spray Gun Manual Air-Assisted Airless	FR GE IT	7105041E 213161D 447784C	MA	(317102) or (317107)	EN - 334591F03 - Issued 08/08
8-7	Kinetix Electrostatic Spray Gun Automatic Airless	FR GE IT	7105238E 213191B 464765A	MA	(317102) or (317107)	EN - 334592F03 - Issued 08/08
8-11	Kinetix Electrostatic Spray Gun Manual Version Airless	FR GE IT PL	7105242C 213192D 464749C 7105817G	MA	(317102) or (317107)	EN - 334598G03 - Issued 08/08
17-24	Level Detector	PO SP	317132A 317139A	MA	(317102) or (317107)	EN - 106988A - Issued 07/95
6-31	Low-Pressure Color Change Manifold	GE	397528B	MA	(317102) or (317107)	EN - 331151C - Issued 10/03
1-34	Low-Pressure Diaphragm Pump	GE	7156308A	IN	(317102) or (317107)	EN - 1013754A - Issued 11/01
5-3	Low Pressure Hoses and Connectors	IT	412661B	IN	(317102) or (317107)	EN - 104598B - Issued 07/97
-	Magnetic Separator Adjustments	FR GE	7105715A 7119858A	IN	(317102) or (317107)	EN - 1040053A Issued 03/03
28-7	Manual Black Primer Application System	GE IT SP	7192208C 7192174C 409410A	MA	(317102) or (317107)	EN - 107003C - Issued 04/02

Nordson Finishing Products (sorted by Product Title) ***Automotive / Container / Electronics / Liquid / NSE***

C-1 - 18

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
28-6	Manual Clear Primer Application System	GE IT SP	7192207B 7192173B 409409A	MA	(317102) or (317107)	EN - 107002B - Issued 02/06
10-20	Manual Iso-Flo HD Voltage Block System	CZ DU FR GE IT PL SP SW	7119876G 7179370G02 7119160G 458193G02 407427G02 7179703_03 7179320G02 458117C	MA	(317102) or (317107)	EN - 107157_03 - Issued 0713
10-19	Manual Iso-Flo HD Voltage Block System	DU FR GE IT SP	7179371B 7119162B 458194B 407432B 7179321B	OP	(317102) or (317107)	EN - 187695B02 - Issued 10/03
-	Manual Pressure Regulator - Stainless Seat	GE	213237D	IN	(317102) or (317107)	Created by Nordson Engineering GmbH Issued 11/02
--	Mastic Gun	GE IT	7192236A 7192191A	MA	(317102) or (317107)	EN - 1040769A - Issued 02/04
17-26	MEG Driver	GE PL SP	7105093B 7146475B 458322A	MA	(317102) or (317107)	EN - 229776B - Issued 10/14
--	MEG Inside Stripe Applicator	GE IT SP	7179352_04 7192754_04 7192839_04	MA	(317102) or (317107)	EN - 1084632_04 - Issued 07/16

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 19

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	MEG II Airless Spray Guns (Reduced Cavity and Extended Tip)	FR GE IT PL PO SP	7192971_09 7105094_09 7192755_09 7146476_09 7135805_09 7146622_09	MA	(317102) or (317107)	EN - 334669_09 - Issued 07/16
--	MEG II Airless Spray Guns with 10 ft Cable	FI FR GE IT PL PO RU SE SP	7560501_02* 7560174_04 7560173_04 7560175_04 7560176_04 7560177_04 7580088_04 7560384_04 7560178_04	MA	(317102) or (317107)	EN - 1602990_04 - Issued 07/16 * = not yet translated
--	MEG II Armature Spring Kit	PO SP	7135815B 7146623B	IN	(317102) or (317107)	EN - 1046764_02 - Issued 09/14
--	MEG II Spray Gun (QRG)	FR GE IT PL PO RU SE SP	7192995_01 7560179_01 7560180_01 7560181_01 7560182_01 7580089_01 7560389_01 7560183_01	IN	(317102) or (317107)	EN - 1606179_01 - Issued 09/14
--	Mini Regenerative Air Dryer	GE IT	7192281A03 7192196A03	IN	(317102) or (317107)	EN - 1066461A_03 - Issued 01/07
--	MSP3 Filter Element Change	PO RU	7560472_02 7560263_02	IN	(317102) or (317107)	EN - 1083734_02 - Issued 11/14

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 20

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	NC-1 Spray Gun Driver	GE IT SE SP	7169624A 7192759A 7560385A 7560660A	IN	(317102) or (317107)	EN - 1101142A - Issued 04/10
--	NH-4 Heaters	DA GE	7560111_01 7580159_02	MA	(317102) or (317107)	EN - 1602369_02 - Issued 03/17
--	Nine-Station Valve Pack	GE IT SP	7192280A 7192195A 7560569A	IN	(317102) or (317107)	EN - 1066460A - Issued 2005
--	Nordson Airless Nozzle Tester	FR	7192972A	OP	(317102) or (317107)	EN - 187681A -Issued 11/95
--	Nordson Mastic Regulator	GE IT	7192238B 7192189B	IN	(317102) or (317107)	EN - 1017656B - Issued 04/03
2-0	Paint Heater Calculations	PL	7119197A	IN	(317102) or (317107)	EN - 334624A - Issued 11/99
--	Pattern Control Kit	PL	7192511A	IN	(317102) or (317107)	EN - 1023432A - Issued 02/02
--	PDMP Purge Gland Greasing	GE IT SP	7192289_01 7192199_01 7560564_01	IN	(317102) or (317107)	EN - 1601202_01 - Issued 02/12
PermaFlo	Circulation Kit for PermaFlo Pumps	CZ GE IT	7156051A 7105191A 7192752A	IN	(317102) or (317107)	EN - 1029315A - Issued 11/02

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 21

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
PermaFlo	PermaFlo 815 Pump NEW!	GE IT PL RU SP SW TU	7179202_02 7192750_02 7560853_02 7179421_02 7560308_02 7169260A 7169518A	MA	(317102) or (317107)	EN - 1102698_02 - Issued 07/12
PermaFlo	PermaFlo 815 Pump Service Kits Quick Reference Guide	FR	7156480 -QR02	IN	(317102) or (317107)	EN - 1085470-QR03 - Issued 2008
PermaFlo	PermaFlo 830 Pump New!	DA FR GE IT TU	7560110_03 7156481A02 7179203_03 7192751_03 7169519A02	MA	(317102) or (317107)	EN - 1085458_03 - Issued 07/12
PermaFlo	PermaFlo 830 Pump Service Kits Quick Reference Guide	FR	7156481 -QR02	IN	(317102) or (317107)	EN - 1085458-QR03 - Issued 2008
Permaflo	PermaFlo Pump Packing Kits	FR	7156491A02	IN	317102) or (317107)	EN - 1087851A02 - Issued 09/08
-	Pressure Transducer and Amplifier Assembly	GE	7105095D	IN	(317102) or (317107)	EN - 331233D - Issued 12/03
21-51	Prism Automatic Low-Pressure Spray Guns (Airspray and HVLP)	GE IT SP	7105010C 458188C 397832C	MA	(317102) or (317107)	EN - 303869C02 - Issued 08/08
25-18	Process Sentry Controller (Body Shop Version)	GE	412809A	MA	(317102) or (317107)	EN - 331162C - Issued 07/02
--	Pro-Meter Controller with Process Sentry (AC Motor Version)	GE IT	7192209A 7192175A	MA	(317102) or (317107)	EN - 334623A - Issued 04/00

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 22

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Pro-Meter Controller with Process Sentry (DC Motor Version)	GE IT	7192239B 7192231B	MA	(317102) or (317107)	EN - 1007773B - Issued 11/03
--	Pro-Meter Gear Metering Pump	CH GE IT	7580058E03 7135988E03 7135913E03	MA	(317102) or (317107)	EN - 303808E03 - Issued 04/16
--	Pro-Meter S-Series Dispensers	CH CZ FR GE IT PL PO RO RU SP TU	7560458_08 7179959_06 7179173_06 7156932_07 7146276_07 7179691_06 7146946_09 7156924A04 7179920_07 7169521A05 7179643_06	MA	(317102) or (317107)	EN - 1075653_09 - Issued 07/16
--	Pro-Meter S2K-Series Dispensers	CZ FR GE IT PL RU SP TU	7179958_07 7179876_07 7179825_07 7179843_07 7179690_07 7179919_07 7179855_07 7179642_07	MA	(317102) or (317107)	EN - 1089138_07 - Issued 06/13
--	Pro-Meter II 14-Zone Heated Controller with PROFIBUS	IT	7146461A	MA	(317102) or (317107)	EN - 1086500A - Issued 04/08
--	Pro-Swirl Applicator and Controller	GE IT	7192240C02 7192223C02	MA	(317102) or (317107)	EN - 1009910_03 - Issued 08/15

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 23

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Pro-Swirl Motor Rotor Replacement	GE IT	7192235B 7192200B	IN	(317102) or (317107)	EN - 1041592B - Issued 06/05
--	Pro-Swirl Teach Tip Installation	GE IT	7192237A 7192190A	IN	(317102) or (317107)	EN - 1024900A - Issued 02/02
--	PS3 Controller General Operation Guide with Optional Controller Configurations	CZ FR GE IT PL RU SP TU	7179960_01 7179877_01 7179826_01 7179844_01 7179692_01 7179921_01 7179856_01 7179644_01	MA	(317102) or (317107)	EN - 1602964_01 - Issued 12/12
--	RA-20 Paint/ Solvent/ Dump Valve	PL PO	7192515B02 7179696B02	IN	(317102) or (317107)	EN - 237431B02 - Issued 09/07
21-47	RA-20 Rotary Atomizer	CZ IT PL SP	7156772 J02 409468C 7192512 J02 412897F	MA	(317102) or (317107)	EN - 237366J02 - Issued 10/07
21-48	RA-20 Rotary Atomizer	CZ DU PL SP	7156773 B02 213950B 7192513 B02 412974B	OP	(317102) or (317107)	EN - 237367B02 - Issued 10/03
--	RA-20 Rotary Atomizer Nozzle Kit	PL	7192514A	IN	(317102) or (317107)	EN - 1065516A - Issued 10/05
--	RPM Indicator	PL	7192516_03	MA	(317102) or (317107)	EN - 108103_03 - Issued 07/13

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 24

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
Rhino	Standard A- and B-Unit Rhino Bulk Unloader Controls	CZ FR GE IT JA PL RU SP	7192244C 405004C 409416C 407283C 7135342C* 7119370C 7179555C 405007B	MA	(317103) or (317106)	EN - 187688_02 - Issued 06/15 Version C Issued 02/03 * available at Nordson K.K.
27-53	Rhino Bulk Unloader Container Change	CZ FR GE NO PL RU SP SW	7146645C 7146834C 7146871C 7146536C 7119371C 7179554C 7146256C 213120C	OP	(317102) or (317107)	EN - 107172C - Issued 12/00
23-18	Rhino Bulk Unloader Frames	CZ FR GE IT	7192245B 7105582B 447609B 7119927B	MA	(317102) or (317107)	EN - 334608B - Issued 10/00
--	Rhino Heated Bulk Unloader Drum Position Sensor	IT	7146454A	IN	(317102) or (317107)	EN - 1085713A-02 - Issued 09/08
--	Rhino Power Train Cell Pail Hold Down	GE RO	7169202A 7169190A	IN	(317102) or (317107)	EN - 1105525A - Issued 01/11
--	Rhino Power Train Cell Drum Position Switch	GE RO	7169203A 7169191A	IN	(317102) or (317107)	EN - 1105526A - Issued 01/11
--	Rhino Power Train Cell Ram Control and Blow-Off Module	GE RO	7169204A 7169192A	IN	(317102) or (317107)	EN - 1105544A - Issued 01/11

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 25

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino Power Train Cell Follower Module	GE RO	7169205A 7169193A	IN	(317102) or (317107)	EN - 1105591A - Issued 01/11
--	Rhino Power Train Cell Pail Change	GE RO	7169206A 7169194A	IN	(317102) or (317107)	EN - 1106431A - Issued 01/11
--	Rhino Power Train Cell Pail Level Detect Module	GE RO	7169207A 7169195A	IN	(317102) or (317107)	EN - 1106360A - Issued 01/11
--	Rhino Power Train Cell Pneumatic Crossover Control Module	GE RO	7169208A 7169196A	IN	(317102) or (317107)	EN - 1106561A - Issued 01/11
27-64	Rhino Pump Service Kits	CZ SW	7192246B 213118B	IN	(317102) or (317107)	EN - 303801B - Issued 04/00
23-16	Rhino Screw Together 24:1 / 48:1 & 32:1 / 65:1 Pumps	CZ FR GE IT	7192247C 7105584C 458461C 7119926C	MA	(317102) or (317107)	EN - 334606C - Issued 09/01
--	Rhino SD/SD2/XD/XD2 ¾- and 1¼ -Inch Ball Check Valves	CH CZ FR GE IT JA PO RO SP	7560459_03 7580127_03 7179177A02 7156918A02 7192259_02 7119724A** 7146965_03 7156939A02 7169529A02	IN	(317102) or (317107)	EN - 1043115_03 - Issued 2003 ** available at Nordson K.K

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 26

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino SD Bleed Valves	CH GE IT JA PO RO SP	7560460 A03 7156919 A03 7179888 A03 7119725 A* 7146966 A03 7156938 A03 7169530 A03	IN	(317102) or (317107)	EN - 1047087A03 - Issued 07/08 * available at Nordson K.K
--	Rhino SD Interconnect Hose Modules	JA	7119727 A*	IN	(317102) or (317107)	EN - 1047086A - Issued 02/04 * available at Nordson K.K
--	Rhino SD Packing Gland Replacement	JA	7119728 A*	IN	(317102) or (317107)	EN - 1033035A - Issued 11/03 * available at Nordson K.K
--	Rhino SD Switch for Glass Application	JA	7119730 A*	IN	(317102) or (317107)	EN - 1047117A - Issued 03/04 * available at Nordson K.K
--	Rhino SD Purge Buttons for Electric Changeover Controls	CH JA PO	7560461 A02 7119732 A* 7146967 A02	IN	(317102) or (317107)	EN - 1047104A02 - Issued 10/06 * available at Nordson K.K
--	Rhino SD Runaway Sensors	JA	7119733 A*	IN	(317102) or (317107)	EN - 1047108B - Issued 03/06 * available at Nordson K.K
--	Rhino SD Single Red Lens 24 VDCLight Towers for Electric Changeover Controls	JA	7119734 A*	IN	(317102) or (317107)	EN - 1047115A - Issued 02/04 * available at Nordson K.K
--	Rhino SD Single Amber Lens 24 VDCLight Tower for Electric Changeover Controls	JA	7119735 A*	IN	(317102) or (317107)	EN - 1047114A - Issued 02/04 * available at Nordson K.K
--	Rhino SD/XD 125- or 160-mm Frames	PO	7560956_01	MA	(317102) or (317107)	EN - 1607593_01 - Issued 08/15

Nordson Finishing Products (sorted by Product Title) **Automotive / Container / Electronics / Liquid / NSE**

C-1 - 27

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino SD / XD Container Change	FR JA PL PO SP	7179178B 7119726A* 7179264B 7146962B 7169533B	OP	(317102) or (317107)	EN - 1045988B - Issued 02/06 * available at Nordson K.K
--	Rhino SD / XD PCI and PLC/DeviceNet Filter Stand Cable Module	CH PO	7560462A 7560957A	IN	(317102) or (317107)	EN - 1047120A - Issued 04/06
--	Rhino SD / XD Pressure Switches for PCI/PLC and DeviceNet Applications	JA PO RU	7119731A 7560473B 7560264B	IN	(317102) or (317107)	EN - 1047116B - Issued 02/05
--	Rhino SD / XD Pump Air Valve Rebuild Kit	JA	7119737A*	IN	(317102) or (317107)	EN - 1062535A - Issued 05/05 * available at Nordson K.K
--	Rhino SD / XD Type-F Electric Control Module Pneumatic Purge Button (Title version A: Rhino SD Ford Electrical ChangeOver Control)	JA	7119729A*	IN	(317102) or (317107)	EN - 1047105B-01 - Issued 07/06 * available at Nordson K.K
--	Rhino SD / XD Type-G/D 24 Vdc ISO Electric Control Module	CH PO	7560463A02 7146968A02	IN	(317102) or (317107)	EN - 1047125A02 - Issued 08/06
--	Rhino SD / XD Type-G/D Pneumatic Control Module	SP	7169524A02	IN	(317102) or (317107)	EN - 1047102A02 - Issued 08/06
--	Rhino SD2 / XD2 and VE Hose Support Module	CH CZ FR GE IT PL PO SP	7560468_02 7179414_02 7179404_02 7192311_02 7146453_02 7179395_02 7179141_02 7169528A	IN	(317102) or (317107)	EN - 1085711_02 - Issued 12/12

Nordson Finishing Products (sorted by Product Title) Automotive / Container / Electronics / Liquid / NSE

C-1 - 28

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino SD2 / XD2 and VE Interconnect Hose Modules	CH CZ FR GE IT PL PO SP	7560467A_03 7179415A_03 7179405A_03 7192282A_03 7192197A_03 7179396A_03 7146970A_03 7169527A02	IN	(317102) or (317107)	EN - 1077748A_03 - Issued 12/12
--	Rhino SD2 / XD2 ARW Air Circuit Module	GE IT	7192309A 7192269A	IN	(317102) or (317107)	EN - 1077884A - Issued 08/07
--	Rhino SD2 / XD2 Container Change for Two-Hand Controls with Blow-Off Circuit	TU	7560023A	IN	(317102) or (317107)	EN - 1094288A - Issued 06/09
--	Rhino SD2 / XD2 DeciceNet I/O Modules	GE IT PO	7192306A 7192266A 7146971A	IN	(317102) or (317107)	EN - 1077749A - Issued 08/07
--	Rhino SD2 / XD2 Drive Train Shroud	CZ	7580128A	IN	(317102) or (317107)	EN - 1087764A - Issued 2008
--	Rhino SD2 / XD2 Drum-Centering Shoes	CZ	7580129A	IN	(317102) or (317107)	EN - 1096813A - Issued 06/09
--	Rhino SD2 / XD2 Electric Drum/Pail Level Indicators	CH GE IT PO	7560464A 7192304A 7192263A 7146969A	IN	(317102) or (317107)	EN - 1077746A - Issued 07/07
--	Rhino SD2 / XD2 Follower Modules	CH GE IT PO SP TU	7560466A04 7192308A03 7192268A03 7146972A04 7169525A03 7560016A04	IN	(317102) or (317107)	EN - 1077883A04- Issued 06/09

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 29

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino SD2 / XD2 Frames	CH CZ GE IT PO RO SP	7560465A05 7179020A05 7156920A05 7146447A05 7146964A05 7156933A05 7169531A05	MA	(317102) or (317107)	EN - 1073086A05 - Issued 06/09
--	Rhino SD2 / XD2 NAP Frames	CZ FR GE IT PL RU	7179021A02 7179176A02 7192312A02 7192271A02 7179262A02 7560265A02	MA	(317102) or (317107)	EN - 1077149A02 - Issued 06/09
--	Rhino SD2/XD2 NPN Runaway Sensor	PO	7560958A	IN	(317102) or (317107)	EN - 1096335A - Issued 06/09
--	Rhino SD2 / XD2 Packing Gland Replacement	CH GE IT PO RO SP TU	7560469A 7156916A 7192261A 7146963_02 7156937A 7169532A 7560015A	OP	(317102) or (317107)	EN - 1075674_02 - Issued 2016
--	Rhino SD2 / XD2 Pneumatic Drum/Pail Level Indicators	GE IT SP	7192305A02 7192264A02 7169526A02	IN	(317102) or (317107)	EN - 1077747A02 - Issued 06/09
--	Rhino SD2 / XD2 Pressure Relief Valves	GE IT PO	7192307A 7192267A 7560474A	IN	(317102) or (317107)	EN - 1077882A - Issued 07/07

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 30

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino SD2 / XD2 Pumps (Title -A08 :Rhino SD2 / XD2 / XD2H Pumps)	CH CZ FI FR GE IT PL PO RO SP	7560470_13 7179019_14 7192795_12 7179179A11 7135989A11 7146275A11 7179261A11 7146959_14 7156931A10 7169523A11	MA	(317102) or (317107)	EN - 1073520_14 - Issued 08/16
--	Rhino SD2 / XD2 Runaway Sensors	CH FR GE IT PO	7560471A02 7179180A02 7192303A02 7192262A02 7179140A02	IN	(317102) or (317107)	EN - 1075675A02 - Issued 01/10
--	Rhino SD2 / XD2 CE Two-Hand Operation Control Module	TU	7560021A	IN	(317102) or (317107)	EN - 1087765A - Issued 05/08
--	Rhino SD2 / XD2 / XD2H Customer-Specific Pumps	IT TU	7179889A03 7560024A03	MA	(317102) or (317107)	EN - 1096339A03 - Issued 11/10
--	Rhino SD2CE / XD2H Drum Level Detect Module	IT TU	7146448A 7560017A	MA	(317102) or (317107)	EN - 1085716A - Issued 02/08
23-15	Rhino Stainless Steel 24:1 / 48:1 Single-Acting Bolt Together Pumps	GE	447613A	MA	(317102) or (317107)	EN - 334605B - Issued 01/04
27-49	Rhino Unloader Packing Gland Replacement	CZ FR GE PL RU SP	7192243A 7146835A 7146872A 7119372A 7179556A 7146255A	OP	(317102) or (317107)	EN - 187674A - Issued 09/96

Nordson Finishing Products (sorted by Product Title)

Automotive / Container / Electronics / Liquid / NSE

C-1 - 31

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
27-59	GMT Rhino Unloader Packing Gland Replacement - Updated Pump Design (Title version B: Rhino Unloader Packing Gland Replacement - Updated Pump Design)	SW	213119B	OP	(317102) or (317107)	EN - 229760C - Issued 07/03
--	Rhino VE Bulk Unloaders	CZ FR GE IT PL RU	7179408_01 7179399_01 7179947_01 7192250_01 7179390_01 7560268_01	MA	(317102) or (317107)	EN - 1600109_01 - Issued 11/12 Obsolete! -> Replaced by 1608271_01
--	Rhino VE Bulk Unloaders, 125-mm Frame	CZ	7580130_01	MA	(317102) or (317107)	EN - 1608271_01 - Issued 06/16
--	Rhino VE Bleed Valve	CZ FR GE IT PL RU	7179018A 7179174A 7192295A 7146455A 7179265A 7560267A	IN	(317102) or (317107)	EN - 1080105A - Issued 07/07 Obsolete! -> Replaced by 1608273_01
--	Rhino VE/CE 24 Vdc Light Tower for Pneumatic Control Modules	CZ GE IT	7580132_01 7192298_01 7192253_01	IN	(317102) or (317107)	EN - 1602148_01 - Issued 2013
--	Rhino VE/CE Bulk Unloader OP Card	CZ FR GE PL RU	7179410_01 7179401_01 7192302_01 7179392_01 7560269_01	OP	(317102) or (317107)	EN - 1602948_01 - Issued 12/12
--	Rhino VE/CE Pneumatic Level Detect Modules	CZ FR GE IT PL RU	7179413_01 7179403_01 7192299_01 7192254_01 7179394_01 7560270_01	IN	(317102) or (317107)	EN - 1603025_01 - Issued 12/12

Nordson Finishing Products (sorted by Product Title)

Automotive / Container / Electronics / Liquid / NSE

C-1 - 32

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino VE Follower Modules	CZ FR GE IT PL RU	7179411_02 7179175_02 7192297_02 7192252_02 7179263_02 7560266_02	IN	(317102) or (317107)	EN - 1079490A_02 - Issued 12/12 Obsolete! -> Replaced by 1608275_01
--	Rhino VE Follower Modules	CZ	7580131_01	IN	(317102) or (317107)	EN - 1608275_01 - Issued 11/15
--	Rhino VE Pneumatic Drum Level Modules	CZ FR GE IT PL	7179412_01 7179402_01 7192296_01 7192251_01 7179393_01	IN	(317102) or (317107)	EN - 1602963_01 - Issued 12/12
--	Rhino VE Pop-Off Valve	CZ FR GE IT PL	7179417_01 7179407_01 7192300_01 7192255_01 7179398_01	IN	(317102) or (317107)	EN - 1097674_01 - Issued 12/12
--	Rhino VE Relief Valves	CZ FR GE IT PL	7179416_01 7179406_01 7192301_01 7192256_01 7179397_01	IN	(317102) or (317107)	EN - 1098016_01 - Issued 03/12
--	Rhino VE Standard Bulk Unloader OP Card	CZ FR GE IT PL	7179409_01 7179400_01 7192294_01 7192258_01 7179391_01	OP	(317102) or (317107)	EN - 1600110_01 - Issued 12/12
--	Rhino XD2 Stainless Steel Packing Gland Replacement	GE IT	7192310A 7192270A	IN	(317102) or (317107)	EN - 1081653A - Issued 10/07

Nordson Finishing Products (sorted by Product Title) ***Automotive / Container / Electronics / Liquid / NSE***

C-1 - 33

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino XD2H Container Change for Two-Hand Control Urethane Systems	IT	7179890A	OP	(317102) or (317107)	EN - 1087958A - Issued 06/09
--	Rhino XD2H Heated Control Modules	IT TU	7146450A 7560019A02	MA	(317102) or (317107)	EN - 1087552A_02 - Issued 09/08
--	Rhino XD2H Heated Follower Module with Steel Ring	IT TU	7146451A 7560018A	MA	(317102) or (317107)	EN - 1085717_02 - Issued 11/15
--	Rhino XD2H Interconnect Hose Module	IT TU	7146452A 7560020A	MA	(317102) or (317107)	EN - 1087763A - Issued 05/08
--	Rhino XD2H Platen/ J-Box Harness Assembly	IT TU	7146449A 7560022A	MA	(317102) or (317107)	EN - 1087784A - Issued 05/08
--	Saturn Solenoid Valves	JA	7119801A*	IN	(317102) or (317107)	EN - 1059638B - Issued 05/05 * available at Nordson K.K
--	Small Cv Saturn Solenoid Valves	JA	7119802A*	IN	(317102) or (317107)	EN - 1069640A -Issued 04/06 * available at Nordson K.K
--	SDS Single-PCI Controller	FR PO	7179172A02 7179139A02	MA	(317102) or (317107)	EN - 1062961A_02 - Issued 11/07
--	Self-Venting Pressure Regulator	IT	7192756A	IN	(317102) or (317107)	EN - 1105708A - Issued 08/13
3-5	Siphon Strainer Assemblies	GE	7156307D	IN	(317102) or (317107)	EN - 108466D - Issued 07/99

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 34

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
6-14	Soft Seat Fluid Pressure Regulator	GE IT PO SP	447767E 213870E 317178C 317154C	IN	(317102) or (317107)	EN - 104622F - Issued 11/03
19-5	Pump Packing and Solvent Chamber Fluid Guide (Title version F: Solvent Chamber Fluids)	DU FR GE IT NO PL PO SP SW TU	292981F 292982G 292983F 292984G 292962F 412603G 317113F 317151F 458111F 7560857G	IN	(317102) or (317107)	EN - 108044G - Issued 10/03
26-15	Spray Automatic Dispensing Valves	GE SP	405070A 403013A	MA	(317102) or (317107)	EN - 107023A -. Issued 06/95
6-13	Spray Pressure Control Manifold	DU FI FR GE IT PO RU SE SP	7179363G02 7560502_03* 7156881G02 317161G02 7179317G02 7135811G 7169038G02 7560383_03 7146629G02	IN	(317102) or (317107)	EN - 108730_03 - Issued 04/15 * = not yet translated
22-1	Standard and Conical AN Series Air Spray Nozzles) (Title version D: Standard and Conical Air Spray Nozzles)	GE IT SW	409103D 412640D 458116D	IN	(317102) or (317107)	EN - 107967E - Issued 08/01
--	Standard and Stainless Steel Circulation Valves	IT	7192758A	IN	(317102) or (317107)	EN - 1033690A - Issued 11/02

Nordson Finishing Products (sorted by Product Title) ***Automotive / Container / Electronics / Liquid / NSE***

C-1 - 35

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
---	Standard and Stainless Steel Single and Dual Circulation Kits	GE IT RU	397903D 7192757D 7119604D	IN	(317102) or (317107)	EN - 104625D - Issued 11/02
StediFlo	StediFlow 3:1 and 6:1 Low Pressure Pumps	CZ PL	7179519_01 7179510_01	MA	(317102) or (317107)	EN - 1601877_01 - Issued 07/12
StediFlo	StediFlow 8:1 Low Pressure Pump	CZ PL RO	7179520_01 7179511_01 7560045_01	MA	(317102) or (317107)	EN - 1601878_01 - Issued 07/12
StediFlo	StediFlow 10:1 Pump	CZ PL	7179521_01 7179512_01	MA	(317102) or (317107)	EN - 1601879_01 - Issued 07/12
StediFlo	StediFlow 12:1 Pump	CZ PL	7179522_01 7179513_01	MA	(317102) or (317107)	EN - 1601880_01 - Issued 07/12
StediFlo	StediFlow 18:1/ 32:1Pumps	CZ PL SP	7179523_01 7179514_01 7560447_01	MA	(317102) or (317107)	EN - 1601881_01 - Issued 07/12
StediFlo	StediFlow High Pressure 57:1 Pump	CZ PL	7179524_01 7179515_01	MA	(317102) or (317107)	EN - 1601882_01 - Issued 07/12
--	T-Filters	PO SP	7135809A 7146628 A04	IN	(317102) or (317107)	EN - 303843A04 - Issued 05/08
--	Temperature Control System	CZ FI FR GE	7560196_02 7560503_02* 7580073_04 7135536A	MA	(317102) or (317107)	EN - 1075456_04 - Issued 05/16 * = not yet translated

Nordson Finishing Products (sorted by Product Title) ***Automotive / Container / Electronics / Liquid / NSE***

C-1 - 36

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Trilogy Air Assisted Airless Manual Spray Gun	CH CZ DA FR GE IT JA KO PL SP SW	7179056_01 7179467_01 7560112_01 7179057_01 7179058_01 7179059_01 7179060_01 7179061_01 7179458_01 7179062_01 7179063_01	MA	(317102) or (317107)	EN - 1601051_02 - Issued 12/15
--	Trilogy Air Assisted Airless LT Manual Spray Gun	CH CZ FR GE IT JA KO PL SP SW	7179065_01 7179468_01 7179066_01 7179067_01 7179068_01 7179069_01 7179070_01 7179459_01 7179071_01 7179072_01	MA	(317102) or (317107)	EN - 1601052_03 - Issued 02/16
--	Trilogy GP Air Spray and LVLP Gravity Fed Manual Spray Guns	CH CZ FR GE IT JA KO PL SP SW	7179073_01 7179469_01 7179074_01 7179075_01 7179076_01 7179077_01 7179078_01 7179460_01 7179079_01 7179080_01	MA	(317102) or (317107)	EN - 1601053_02 - Issued 07/13

Nordson Finishing Products (sorted by Product Title) Automotive / Container / Electronics / Liquid / NSE

C-1 - 37

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Trilogy AC Air Spray and LVLP Gravity Fed Manual Spray Guns	CH CZ FR GE IT JA KO PL SP SW	7179081_01 7179470_01 7179082_01 7179083_01 7179084_01 7179085_01 7179086_01 7179461_01 7179087_01 7179088_01	MA	(317102) or (317107)	EN - 1601054_02 - Issued 07/13
	Trilogy Air Spray and LVLP Gravity Fed Manual Spray Guns	CH CZ FR GE IT JA KO PL SP SW	7179089_01 7179471_01 7179090_01 7179091_01 7179092_01 7179093_01 7179094_01 7179462_01 7179095_01 7179096_01	MA	(317102) or (317107)	EN - 1601055_03 - Issued 02/16
--	Trilogy Air Spray and LVLP Siphon Fed Manual Spray Guns	CH CZ FR GE IT JA KO PL SP SW	7179097_01 7179472_01 7179098_01 7179099_01 7179100_01 7179101_01 7179102_01 7179463_01 7179103_01 7179104_01	MA	(317102) or (317107)	EN - 1601056_03 - Issued 02/16

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 38

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Trilogy Air-Assisted Airless Automatic Spray Guns	CH CZ FR GE IT JA KO PL SP SW	7179105_01 7179473_01 7179106_01 7179107_01 7179108_01 7179109_01 7179110_01 7179464_01 7179111_01 7179112_01	MA	(317102) or (317107)	EN - 1601057_01 - Issued 06/12
--	Trilogy Air Spray and LVLP Automatic Spray Guns (Title version _01: Trilogy Automatic AS and LP Guns)	CH CZ FR GE IT JA KO PL PO SP SW	7179113_01 7179474_01 7179114_01 7179115_01 7179168_01 7179117_01 7179118_01 7179465_01 7179695_01 7179119_01 7179120_01	MA	(317102) or (317107)	EN - 1601058_03 - Issued 03/14
--	Trilogy LP Quick Change Automatic Spray Guns	CH CZ FR GE IT JA KO PL SP SW	7179121_01 7179475_01 7179122_01 7179123_01 7179124_01 7179125_01 7179126_01 7179466_01 7179127_01 7179128_01	MA	(317102) or (317107)	EN - 1601059_01 - Issued 06/12
--	Trilogy Manual Electrostatic Air Spray/HVLP Solventborne Spray Gun	DU FR GE IT SP	7179425A 7156877A 7169317A 7179433A 7169293A	MA	(317102) or (317107)	EN - 1093591A - Issued 06/09

Nordson Finishing Products (sorted by Product Title) *Automotive / Container / Electronics / Liquid / NSE*

C-1 - 39

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Trilogy Manual Electrostatic Air Spray/HVLP Waterborne Spray Gun	DU GE IT SP	7179428A 7179313A 7179436A 7179327A	MA	(317102) or (317107)	EN - 1093558A - Issued 06/09
--	Trilogy Solventborne Electrostatic HVLP and Air Spray Automatic Gun	DU FR GE IT SP	7179427A 7156878A 7179303A 7179435A 7179326A	MA	(317102) or (317107)	EN - 1093593A - Issued 04/09
--	Trilogy Waterborne Electrostatic HVLP and Air Spray Automatic Gun	DU GE IT SP	7179426A 7179312A 7179434A 7169250A	MA	(317102) or (317107)	EN - 1093592A - Issued 04/09
26-19	Two Component Dispensing Gun	GE	409393A	MA	(317102) or (317107)	EN - 107063C_04 - Issued 08/10
28-12	Two Component Meter	GE	412794A	MA	(317102) or (317107)	EN - 331161A - Issued 04/99
--	Two-Way Ball Valves and Ball Valve Manifolds	DU FR GE IT PO SP	7179364D02 7156880D02 7179300D02 7179318D02 7135813D02 7146625D02	IN	(317102) or (317107)	EN - 104667D02 - Issued 03/07
--	Universal Automatic Non-Conductive Fluid Regulator	GE PL SP	397902 F03 7179706 F03 7169249A	MA	(317102) or (317107)	EN - 1017527F03 - Issued 04/08

Nordson Finishing Products (sorted by Product Title)
Automotive / Container / Electronics / Liquid / NSE

C-1 - 40

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Welded Can Coating System (System Training Guide)	PL	7119962A	MA	(317102) or (317107)	EN - C0057 - Issued 11/06
--	XPS 60 Power Supply	DU	7580011_02	MA	(317102) or (317107)	EN - 1606291_02 - Issued 07/16

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 1

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Antistatic Powder Feed Tubing	DU	7135922A	IN	(317102) or (317107)	EN - 1070652A - Issued 06/06
--	ColorMax 2 Powder Coating System with Encore Feed Center) (Title version_01: ColorMax 2 E/Cubed Powder Coating System with Encore Feed Center)	SP	7192606_01	MA	(317102) or (317107)	EN - 1605397_04 - Issued 10/15
--	ColorMax 2 Powder Coating System with Encore® Venturi Feed Center - Color Change Procedure .ppt	SP	7560076_02	IN	(317102) or (317107)	EN - 1605545_03 - Issued 06/15
--	ColorMax Powder Coating System	PO SP	7169279C02 7169354C02	MA	(317102) or (317107)	EN - 1012899C02 - Issued 06/09 Title on emanuals: ColorMax Powder Coating System with Spectrum Feed Center and Sure-Max Transfer System
--	ColorMax Powder Coating Booth Installation Guide	PO SP	7169285A 7169353A	MA	(317102) or (317107)	EN - 1099290A - Issued 02/10
--	Container Inside Powder Coating Equipment	GE	7156409A	IN	(317102) or (317107)	EN - 1092529A - Issued 12/08
38-10	Econo-Coat Series II Powder Coating System	SP	412692B	MA	(317102) or (317107)	EN - 106712C02 - Issued 1010
31-0	Electrostatic System Installation, Checks and Troubleshooting	SP	213353A	MA	(317102) or (317107)	EN - 334632A - Issued 04/03 Issue date of SP translation : 02/00
--	Encore 50-lb Feed Hopper	FR LI SP	7169730A 7179383A 7169687A	IN	(317102) or (317107)	EN - 1107950-02 - Issued 02/16 Obsolete! Replaced by P/N 1609826

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 2

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Encore Angled Spray Extensions	FR	7580122_02	IN	(317102) or (317107)	EN - 1605615 - Issued 02/16
--	Encore Automatic Powder Spray Guns	CZ DA DU FI FR GE IT LI PL PO RO RU SP SW TU	7169910A03 7179583A03 7169784A02 7169443A02 7169771A02 7169338A02 7169807A02 7179380A04 7169555A03 7169767A02 7169452A02 7169777A02 7169436A02 7169819A02 7192597_07	MA	(317102) or (317107)	EN - 1098185_13 - Issued 10/16
--	Encore Generation II Powder Feed Pumps	CZ DA DU ES FI FR GE IT LI PL PO RU SP SW TU	7169911A 7179584A 7169783A 7179618A 7169188A 7169734A 7169199A 7169806A 7179386A 7156808A 7156968A 7156613A 7169107A 7156818A 7192598_02	IN	(317102) or (317107)	EN - 1095927_02 - Issued 01/14

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 3

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Encore Inline Powder Feed Pump	DU FI FR GE IT LI PL PO RO RU SP SW	7169785A 7169801A 7169772A 7169798A 7169808A 7179385A 7169553A 7169768A 7169455A 7169778A 7169437A 7169820A	IN	(317102) or (317107)	EN - 1095928_02 - Issued 01/14
--	Encore Manual Powder Spray System	CH CZ CR DA DU FI FR GE HU IT LI PL PO RU SP SW	7156064A* 7146813A 7146726A 7146899A 7146841A 7146891A 7146837A 7146851A 7146868A 7146826A 7192126A02 7146847A 7156967A02 7146822A 7146930A 7146830A	OP	(317102) or (317107)	EN - 1088668A02 - Issued 04/09 * = Document and translation is NOT issued by TDLL !
--	Encore Pattern Adjuster Kit	FR SP	7169733A 7169690A	IN	(317102) or (317107)	EN - 1098440A - Issued 11/09
--	Encore Powder Feed Center	SP	7192607_01	MA	(317102) or (317107)	EN - 1602966_05 - Issued 10/15

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 4

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Ion Collector Kit for Encore Automatic Guns	CZ DA DU FI FR GE IT PO RO RU SP SW TU	7169912A02 7179275A02 7179311A02 7179245A02 7169919A02 7179223A02 7179248A02 7179343A02 7179367A02 7169907A02 7169896A02 7179324A02 7179379A02	IN	(317102) or (317107)	EN - 1098186_06 - Issued 09/16
Encore HD	Encore HD Automatic Powder Spray Guns	CZ DA DU GE FI FR IT PL PO RO RU SL SP SW TU	7192398_02 7192432_02 7192105_02 7192132_08 7192410_02 7192503_08 7192404_02 7192470_02 7192538_02 7192142_02 7192229_08 7192463_02 7192121_02 7192420_07 7192476_02	MA	(317102) or (317107)	EN - 1602018_08 - Issued 09/16

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 5

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
Encore HD	Encore HD Manual Powder Spray Gun	CH CR CZ DA DU FI FR GE IT JA PL PO RO RU SL SP SW TU	7560450_07 7580008_09 7192399_07 7192433_07 7192458_07 7192411_07 7192504_07 7192377_07 7192405_07 7560451_09 7192471_07 7192539_07 7192382_07 7192371_07 7192464_07 7192387_07 7192421_08 7192477_01	MA	(317102) or (317107)	EN - 1604869_09 - Issued 09/16
Encore HD	Encore HD Mobile Powder Spray System	CH CZ DA DU FI FR GE IT JA PL PO RO RU SL SP SW	7560431_01 7560544_01 7560586_01 7560587_01 7560588_01 7560589_01 7560429_01 7560547_01 7560432_01 7560428_01 7560594_01 7560590_01 7560591_01 7560592_01 7560430_01 7560593_01	MA	(317102) or (317107)	EN - 1605707_01 - Issued 10/15 New issue date: 01/16 Title: Encore HD <u>Manual</u> Powder Spray System

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 6

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
Encore HD	Encore HD and XT Manual Powder Spray System Controller (Titel version_01: Encore HD Manual Powder Spray System Controller)	CH CR CZ DA DU FI FR GE IT JA PL PO RO RU SL SP SW TU	7560452_04 7580009_04 7192400_04 7192434_04 7192459_04 7192412_04 7192505_04 7192378_04 7192406_04 7560453_04 7192472_04 7192540_04 7192383_04 7192372_04 7192465_04 7192388_04 7192422_04 7192478_01	MA	(317102) or (317107)	EN - 1604870_04 - Issued 10/15 New Issue date: 01/16
Encore HD	Encore HD Mobile Powder Coating System - Quick Start Guide -	CH CZ DA DU FI FR GE IT JA PL PO RO RU SL SP SW	7560441_01 7560731_02 7560732_02 7560733_02 7560734_02 7560735_02 7560439_02 7560736_02 7560442_01 7560438_02 7560737_02 7560738_02 7560739_02 7560740_02 7560440_02 7560741_02	OP	(317102) or (317107)	EN - 1608259_02 - Issued 02/16

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 7

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
Encore HD	Encore HD Powder Spray System with Prodigy Color-on-Demand	CZ DA DU FI FR GE IT PL PO RO RU SL SP SW TU	7192614_01 7192615_01 7192616_01 7192617_01 7192668_01 7192618_01 7192695_01 7192619_01 7192620_01 7192621_01 7192622_01 7192623_01 7192659_01 7192634_01 7192656_01	MA	(317102) or (317107)	EN - 1605396_02 - Issued 06/14
Encore HD	Encore HD Powder Spray System with Prodigy Color-on-Demand - OP Card	CZ DA DU FI FR GE IT PL PO RO RU SL SP SW TU	7192624_01 7192625_01 7192626_01 7192627_01 7192639_01 7192628_01 7192696_01 7192629_01 7192630_01 7192631_01 7192632_01 7192633_01 7192660_01 7192635_01 7192657_01	OP	(317102) or (317107)	EN - 1605548_01 - Issued 03/14

Nordson Finishing Products (sorted by Product Title) *U.S. Powder*

C-2 - 8

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
Encore HD	Encore HD Powder Spray System with Prodigy Pump Cabinet	CZ DA DU FI FR GE IT PL PO RO RU SL SP SW TU	7192401_02 7192435_02 7192460_02 7192413_02 7192506_02 7192379_02 7192407_02 7192473_02 7192541_02 7192384_02 7192373_02 7192466_02 7192389_02 7192423_02 7192479_02	MA	(317102) or (317107)	EN - 1604979_02 - Issued 02/14
Encore HD	Encore HD Powder Spray System with Prodigy Pump Cabinet - OP Card	CZ DA DU FI FR GE IT PL PO RO RU SL SP SW TU	7192402_01 7192436_01 7192461_01 7192414_01 7192507_01 7192380_01 7192408_01 7192474_01 7192542_01 7192385_01 7192374_01 7192467_01 7192390_01 7192424_01 7192480_01	OP	(317102) or (317107)	EN - 1604871_01 - Issued 01/14

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 9

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
Encore HD	Encore HD Pump Control Unit and Power Supply	CH CZ DA DU FI FR GE IT JA PL PO RO RU SL SP SW TU	7560436_01 7560545_01 7560595_01 7560577_01 7560596_01 7560578_01 7560434_01 7560548_01 7560437_02 7560433_01 7560599_01 7560579_01 7560580_01 7560597_01 7560435_01 7560598_01 7560581_01	MA	(317102) or (317107)	EN - 1606783_02 - Issued 03/16
Encore HD	External Diffuser for Encore HD Automatic Spray Guns	IT SW	7560550_01 7560678_01	IN	(317102) or (317107)	EN - 1606973_01 - Issued 02/15
Encore HD/ iControl	Encore HD iControl System Hardware Manual (Installation, Troubleshooting, Repair, Parts)	CZ DA DU FI FR GE IT PL PO RO RU SP SW TU	7192649_02 7560403_02 7179665_02 7560405_02 7560404_02 7192133_02 7560171_02 7560406_02 7560407_02 7192143_02 7192228_02 7192122_02 7560408_02 7560409_02	MA	(317102) or (317107)	EN - 1603054_02 - Issued 04/15

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 10

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
Encore/ iControl	Standard Encore iControl Console Hardware Manual	CZ DA DU FI FR GE IT PL PO RO RU SP SW	7169909A02 7179582A02 7179798A02 7179937A02 7169973A02 7179488A02 7179942A02 7169554A02 7179341A02 7169520A02 7169795A02 7169435A02 7179807A02	MA	(317102) or (317107)	EN - 1105821_04 - Issued 05/15
Encore/ iControl	Encore iControl 2 Integrated Control System (Installation, Troubleshooting, Repair)	CZ DU FR GE IT PL RO RU SP	7560321_05 7560324_05 7560326_05 7560322_05 7560320_05 7560325_05 7192946_04 7192953_05 7560323_05	MA	(317102) or (317107)	EN - 1603638_07 - Issued 05/16
Encore LT	Encore LT Air Filter Kit	FR SP	7169728_01 7169685_01	IN	(317102) or (317107)	EN - 1600565_01 - Issued 09/11
Encore LT	Encore LT Automatic Powder Spray Controllers	FI FR GE RU TU	7560940_01 7192689_01 7192852_01 7580091_01* 7192599_01	MA	(317102) or (317107)	EN - 1604858_01 - Issued 11/13 * = not yet released
Encore LT	Encore LT Automatic Powder Spray Systems	TU	7192600_01	OP	(317102) or (317107)	EN - 1604860_01 - Issued 11/13

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 11

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
Encore LT	Encore LT Main Control Board Replacement	FR PL SP	7169729 7169865 7169686	IN	(317102) or (317107)	EN - 1108327 - Issued 06/11
Encore LT	Encore LT Manual Powder Spray Systems	CZ DA DU ES FI FR GE IT LI PL PO RO RU SL SP SW TU	7580171_11* 7580172_11* 7580173_11* 7580174_11* 7580175_11* 7580176_11* 7580177_11* 7580178_11* 7580179_11* 7580180_11* 7580181_11* 7580182_11* 7580183_11* 7192801_04 7580184_11* 7580185_11* 7192601_02	MA	(317102) or (317107)	EN - 1604857_11 - Issued 09/16 * = not yet released
Encore LT	Encore LT Manual Powder Spray Systems	SL TU	7192802_01 7192602_01	OP	(317102) or (317107)	EN - 1604859_01 - Issued 11/13

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 12

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
Encore LT	Encore LT Manual Powder Spray Systems Quick Start Guide	CZ	7580199_03*	OP	(317102) or (317107)	EN - 1601161_03 - Issued 05/17 * = not yet released
		DA	7580200_03*			
		DU	7580201_03*			
		ES	7580202_03*			
		FI	7580203_03*			
		FR	7580204_03*			
		GE	7580205_03*			
		IT	7580206_03*			
		LI	7580207_03*			
		PL	7580208_03*			
		PO	7580209_03*			
		RO	7580210_03*			
		RU	7580211_03*			
		SL	7192820_02			
		SP	7580212_03*			
SW	7580213_03*					
TU	7580214_03*					
Encore PE	Encore Automatic Porcelain Enamel Powder Spray Gun	CZ	7179893_04	MA	(317102) or (317107)	EN - 1601753_05 - Issued 08/16
		DA	7179985_01			
		DU	7179795_01			
		FI	7179934_05			
		FR	7192692_04			
		GE	7179485_05			
		IT	7179939_01			
		PL	7179792_01			
		RO	7560341_04			
		RU	7179799_04			
		SL	7179735_01			
		SP	7179822_04			
		SW	7179804_01			
		TU	7560340_04			

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 13

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
Encore PE	Encore Automatic Porcelain Enamel Powder Spray Gun - Parts Poster	CZ FR GE RO RU SP TU	7560349_03 7560350_03 7560351_03 7560355_03 7560352_03 7560353_03 7560354_03	IN	(317102) or (317107)	EN - 1602223_04 - Issued 08/16
Encore PE	Encore Manual Porcelain Enamel Powder Spray Gun and Controller	GE	7192349_01	MA	(317102) or (317107)	EN - 1602221_01 - Issued 10/12
Encore PE	Encore Porcelain Enamel Powder Pump	CZ DA DU FI FR GE IT PL RU SP SW	7179894_01 7179986_01 7179796_01 7179935_01 7192691_01 7179486_01 7179940_01 7179793_01 7179800_01 7179852_01 7179805_01	IN	(317102) or (317107)	EN - 1602273_01 - Issued 09/12
Encore PE	Ion Collector Kit - Encore Automatic PE Gun	CZ DA DU FI GE IT PL RU SP SW	7179895_01 7179987_01 7179797_01 7179936_01 7179487_01 7179941_01 7179794_01 7179801_01 7179879_01 7179806_01	IN	(317102) or (317107)	EN - 1602228_01 - Issued 09/12

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 14

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
Encore PE/HD	Encore Automatic Porcelain Enamel HD Powder Spray Gun	CZ FR GE RO RU SP TU	7560342_03 7560343_03 7560344_03 7560348_03 7560345_03 7560346_03 7560347_03	MA	(317102) or (317107)	EN - 1605438_04 - Issued 08/16
Encore PE/HD	Encore Automatic Porcelain Enamel HD Powder Spray Gun - Parts Poster	CZ FR GE RO RU SP TU	7560356_02 7560357_02 7560358_02 7560362_02 7560359_02 7560360_02 7560361_02	IN	(317102) or (317107)	EN - 1605678_03 - Issued 08/16
Encore XT	Encore XT Manual Powder Spray Systems	CZ DU DA FI FR GE IT PL PO RU SP SW TU	7192319_03 7192327_03 7192330_03 7192325_03 7192334_03 7179731_01 7192326_03 7192351_03 7192324_03 7192265_03 7192328_03 7192329_03 7192355_03	MA	(317102) or (317107)	EN - 1603227_012 - Issued 09/16

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 15

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	ESD Grounding Block Kit Installation	CZ DU FI FR GE IT PL PO RU SP SW TU	7560530A 7169780A 7169802A 7169773A 7146573A 7169809A 7169813A 7169769A 7169776A 7169748A 7169821A 7560787A	IN	(317102) or (317107)	EN - 1069022A - Issued 03/06
38-4	Excel 2000 Series Powder Coating System	SP	317133G	MA	(317102) or (317107)	EN - 106641H03 - Issued 04/09
33-13	EXP-100 Electrostatic Power Unit	CZ GE HU	7179599E 405118C 7119741E	MA	(317102) or (317107)	EN - 108242_03 - Issued 05/16
--	External Gun Blow Off Kit	TU	7560788_02	IN	(317102) or (317107)	EN - 1603264_02 - Issued 04/15
--	Global Oscillator	CZ DA DU FI FR GE IT PL PO RO RU SP SW	7169694_01 7169764_01 7169738_01 7169708_01 7169740_01 7169688_01 7169714_01 7169761_03 7169715_01 7169703_01 7169702_01 7169710_03 7169720_01		(317102) or (317107)	EN - 1106313_03 - Issued 04/12

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 16

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	HDLV 55-Gallon Powder Drum Unloader (Title version A02: HDLV 55-Gallon Powder Drum Dolly)	CZ DU FI FR GE IT PL PO RU SP SW TU	7156725A04 7169781A04 7169803A04 7169223A04 7169230A04 7169810A04 7146996A02 7169770A04 7135937A02 7169747A04 7169822A04 7192825A04	IN	(317102) or (317107)	EN - 1073133_05 - Issued 04/15
32-15	High Flow and 100 PLUS FB Powder Pumps	GE HU	464817C 7119743C	IN	(317102) or (317107)	EN - 107987C - Issued 02/97
38-11	Horizon 200/400 Powder Coating System	IT PO RU	407426A 213357D 403 246A	MA	(317102) or (317107)	EN - 106913E03 - Issued 04/09

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 17

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
iControl	iControl Integrated Control System OP	BU CZ DA DU FI FR GE GR HU IT LI PL PO RO RU SE SP SW TU	7105628D 7105145_04 7105146_04 7105147_04 7156521_04 7105148_04 7105149_04 7105627D 7119642E 7105150_04 7156873F 7105512_04 7179330_04 7179707_04 7105154_04 7146583F 397851_04 7105151_04 7560410_04	OP	(317102) or (317107)	EN - 1024758_04 - Issued 04/13
iControl	iControl Standard Console Hardware Manual (Installation, Troubleshooting, Repair, Parts)	GE PO SP	7580157_04 7169298A 7169367A	MA	317103) or (317106)	EN - 1105779_04 - Issued 09/14
iControl	iControl Operator Interface (Configuration, Preset Setup, Operation)	CZ DA DU FI GE IT LI PL RO RU SP SW	7146203C03 7135495C02 7135463C02 7156522C03 7146674C02 7119519C03 7156872C05 7146656C02 7146054C02 7135801_06 7135484C02 7146315C02	MA	(317102) or (317107)	EN - 1056418_06 - Issued 04/13

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 18

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
iControl	iControl Configuration Guide	CZ FI GE IT LI SP SW	7146203-CG 7156522-CG 7146674-CG 7119519-CG 7156872-CG 7135484-CG 7146315-CG	MA	(317102) or (317107)	EN - 1056418-CG06 - Issued 04/13
iControl	Standard iControl Power Supply Kit	CZ GE RU SP	7192834A 7192823A 7192827A 7192842A	IN	(317102) or (317107)	EN - 1107150A - Issued 06/11
iControl/ Prodigy	iControl Prodigy Console Hardware Manual (Installation, Troubleshooting, Repair, Parts)	PO	7179437A02	MA	(317103) or (317106)	EN - 1105820A02 - Issued 09/14
31-31B	Ion Collector Kits for Automatic Guns (Versa-Spray + Versa-Spray II)	IT	407430A	IN	(317102) or (317107)	EN - 108887B - Issued 03/03
--	Manual Horizontal In/Out Positioner	CZ DA DU FI FR GE IT PL PO RO RU SP SW	7169441A 7169509A 7169458A 7169589A 7169491A 7169488A 7169461A 7169348A 7169451A 7169506A 7169411A 7169448A 7169446A	IN	(317102) or (317107)	EN - 1104688A - Issued 01/11

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 19

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
32-35	Metric Porcelain Enamel Powder Pump	FR GE IT NO PL RU SP SW TU	7119815 D 412613 B 409116 B 458006 D 458401 D 7135185 D 412647 B 7105132 D 7135713 D	IN	(317102) or (317107)	EN - 106813D - Issued 04/99
32-14	Metric Powder Transfer Pump	CZ DA DU FI FR GE IT LI PL PO RO RU SP SW TU	7560033 C 7105421 C 7179664 C 7156584 C 7169905 C 412612 A 407425 C 7169113 C 7156196 C 213241 C 7169453 C 7105363 C 412646 B 7146531 C 7192944 C	IN	(317102) or (317107)	EN - 106702C - Issued 03/03
32-12	Metric Standard and Low-Flow Powder Feed Pumps	DA FI FR GE IT GR PO RU SK SP SW	7192783 E 7156604 E 7135613 E 412717 B 409298 A 7146761 E 7105994 D 7105364 E 7156506 E 412690 E 7146253 E	IN	(317102) or (317107)	EN - 106699E - Issued 08/05

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 20

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
32-38	Modular Powder Feed Pumps	DA DU FI FR GE IT PL PO SP SW	409115B 213596E 213630H 213025H 409010H 409341H 409435H 7105806H 458324H 213617E	IN MA IN IN IN IN IN IN IN MA	(317102) or (317107)	EN - 107128H - Issued 05/04 Rev. E = Manual Rev. H = Instructions
--	NHR-X-X Encore Feed Hoppers	GE	7580221_01*	IN	(317102) or (317107)	EN - 1609826_01 - Issued 10/16 * = not yet released
--	NHR-X-X Feed Hoppers	CZ FI FR GE IT PL PO RO RU SP SW	7135751A 7156605A 7169979A 7135882A 7146562A 7156807A 7135489A 7192144A 7146866A 7135494A 7146530A	IN	(317102) or (317107)	EN - 1062942_04 - Issued 10/16
--	NHR-18-150 Powder Feed Hopper	FR HU SP TU	7192690A03 7156524A03 7560618A03 7192603A03	IN	(317102) or (317107)	EN - 1080413A03 - Issued 02/09
--	NHR-25 Feed Hopper with Agitator	GE	7156410A	IN	(317102) or (317107)	EN - 1092140_02 - Issued 02/16
34-36	Non-Loading kV Meter Kit	IT SP	315751A 7135910E02	IN	(317102) or (317107)	EN - 107004E02 - Issued 07/07

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 21

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Nordson Automatic Spray Gun Support Kits	GE	7169344A02	MA	(317102) or (317107)	EN - 1104183A02 - Issued 01/11
--	Nordson Belt-Drive Horizontal In/Out Positioner	CZ DA DU FI FR GE IT PL PO RO RU SP SW	7169440_02 7169508_02 7169457_02 7169588_02 7169490_02 7169345_02 7169460_02 7169418_02 7169450_02 7169502_02 7169484_02 7169447_02 7169445_02	MA	(317102) or (317107)	EN - 7750171_03 - Issued 10/12
--	Nordson Extruded Automatic Spray Gun Support Kits	SP	7192608_01	MA	(317102) or (317107)	EN - 1604216_02 - Issued 08/14
--	Nordson NIO2 In/Out Positioner	SP	7192609_01	MA	(317102) or (317107)	EN - 1603770_02 - Issued 05/16
31-29D	Nozzle Extension Installation for Versa-Spray and Versa-Spray II Manual Guns used with Versa-Spray II Control Units	GE IT	315757B 315752B	IN	(317102) or (317107)	EN - 108861B - Issued 10/95
31-18	NPE-LF10 and NPE-HF10 Powder Spray Guns	CZ FR GE HU	7179600C 213814C 317196C 7119742C	MA	(317102) or (317107)	EN - 108191C - Issued 06/03
--	NV02 Oscillator	SP	7192610_01	MA	(317102) or (317107)	EN - 1602413_01 - Issued 08/13

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 22

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	NVR-Series Vertical Reciprocators	CZ DA DU FI FR GE IT PL PO RO RU SP SW	7169337_02 7169507_02 7169456_02 7169613_02 7169332_02 7169343_02 7169459_02 7169318_02 7169449_02 7169469_02 7169331_02 7169330_02 7169444_02	MA	(317102) or (317107)	EN - 1098602_02 - Issued 06/11
--	Optional Nozzles for Versa-Spray and Versa-Spray II Guns	FI HU IT PO RO RU SK	7156740A 7105816A 397936A 7560912A 7119573A 7105508A 7156512A	IN	(317102) or (317107)	EN - 1037936A - Issued 03/03
--	Pattern Adjuster for Encore Lance Assemblies	FR SP	7169732A 7169689A	IN	(317102) or (317107)	EN - 1100013A - Issued 01/10
32-39	Porcelain Powder Transfer Pump with Stainless Steel Tube Adapter	FR GE IT NO RU SW TU	7119816E 409299A 458473C 458005C 7135184E 7105133E 7135714E	IN	(317102) or (317107)	EN - 229784E - Issued 05/02

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 23

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
32-17	Powder Transfer Pump	CZ DA DU FR GE IT PL PO RU SP SW	397341B 315934B 213591B 290839B 397008B 409485B 412604B 458045B 7105362 C 397676 C 213879B	IN	(317102) or (317107)	EN - 108117C - Issued 03/03
34-25	Powder Tubings, Fittings and Miscellaneous Accessories	SP	213344D	IN	(317102) or (317107)	EN - 108662D - Issued 10/99
--	Prodigy Automatic Tube-Mount Gun Clap	FI	7156776A02	IN	(317102) or (317107)	EN - 1054549A02 - Issued 06/10
--	Prodigy Automatic Powder Spray Guns	CZ DA DU FI FR GE IT LI PL PO RO RU SP SW	7146755B05 7135497B04 7135467B04 7156777B05 7135795B04 7146004B04 7146569B04 7169115B05 7146642B05 7179349 B07 7146055B04 7135889B04 7135642B04 7146468B04	MA	(317102) or (317107)	EN - 1054075B07 - Issued 09/10

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 24

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Prodigy Powder Port Feed Center (Title version A: Prodigy Powder Port)	CZ DA DU GE IT PL RU SP SW	7146753A03 7135498A 7135379A 7146776A03 7146563A03 7146655A03 7135891A03 7146170A03 7146456A03	MA	(317102) or (317107)	EN - 1056625_07 - Issued 12/11 (US-Version) (European version: see U. K. Powder)
--	Prodigy Nozzle Disassembly and Cleaning	DU FI FR GE IT PL PO RU SL SP SW	7135469A01 7169029A01 7156988A01 7146783A01 7146570A01 7169095A01 7169007A01 7169072A01 7135671A01 7169086A01 7146528A01	IN	(317102) or (317107)	EN - 1073708A01 - Issued 11/06
--	Prodigy Spray Gun Nozzles (Parts Poster)	GE	7156593A	IN	(317102) or (317107)	EN - 1079431A - Issued 05/07

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 25

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Prodigy to Encore HD Manual Powder Spray System Upgrade Kit	CZ DA DU FI FR GE IT PL PO RO RU SL SP SW TU	7192403_01 7192437_01 7192462_01 7192415_01 7192508_01 7192381_01 7192409_01 7192475_01 7192543_01 7192386_01 7192375_01 7192468_01 7192391_01 7192425_01 7192481_01	IN	(317102) or (317107)	EN - 1604780_03 - Issued 07/15
--	Prodigy Mobile Manual Powder Spray System	GE	7156971A	IN	(317102) or (317107)	EN - 1081310A- Issued 03/08
--	Prodigy Lance Assembly	CZ DU GE FI FR IT LI PL PO RU SL SP SW TU	7146754A 7169063A 7146781A 7156781A 7146772A 7146564A 7169120A 7169093A 7169005A 7169070A 7179734A 7169085A 7146524A 7192826A	IN	(317102) or (317107)	EN - 1084294A - Issued 05/08

Nordson Finishing Products (sorted by Product Title) *U.S. Powder*

C-2 - 26

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Prodigy Mobile Box Unloader System	FR GE PL RU SP	7169981A 7156411A 7169650A 7169796A 7192611A	IN	(317102) or (317107)	EN - 1091202A - Issued 10/08
--	Prodigy Porcelain Enamel Manual Powder Spray Gun	SL	7169642A	MA	(317102) or (317107)	EN - 1093482_02 - Issued 04/12
--	Prodigy/ Sure Coat Nozzle Extension	LI	7169117A02	IN	(317102) or (317107)	EN - 1097315A02 - Issued 01/10
--	Prodigy Robot Gun	GE	7169315A	MA	(317102) or (317107)	EN - 1105518_02 - Issued 03/14
--	Prodigy Generation II Manual Powder Spray Gun	CZ DU FI FR GE IT LI PL PO RO RU SP SW	7135764A 7169054A04 7156779A04 7156979A04 7146779A02 7146994A02 7169116A04 7146471A02 7156993_06 7146060A02 7135893A 7156341A04 7146459A02	MA	(317102) or (317107)	EN - 1077434_09 - Issued 06/15

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 27

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Prodigy Generation II Manual Powder Spray Gun - Resistor Replacement Kit -	DU FI FR GE IT PL PO RU SP SW	7169055A 7169018A 7156980A 7156857A 7156890A 7169087A 7156994A 7135903A 7169078A 7146523A	IN	(317102) or (317107)	EN - 1081072A - Issued 09/07
--	Prodigy Generation II Manual Powder Spray Gun - Lance Extensions -	RO	7192148_01	IN	(317102) or (317107)	EN - 1603191_01 - Issued 02/13
--	Prodigy Generation III Color-on-Demand System	GE	7169382A02	MA	(317102) or (317107)	EN - 1102101_04 - Issued 05/13
--	Prodigy Generation III Color-on-Demand System OP Card	GE	7169383A04	OP	(317102) or (317107)	EN - 1081751_06 - Issued 05/13
--	Prodigy HDLV Pump Fluidizing Tube Replacement	DA DU FI FR GE HU IT PL PO RU SL SP SW	7135595A 7169059 A02 7169022 A02 7119047A 7119106A 7119321A 7119086A 7169089 A02 7169012 A02 7135900A 7135665 A02 7119213A 7146526A02	IN	(317102) or (317107)	EN - 1058016A02 - Issued 09/07

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 28

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Prodigy HDLV Pump Pinch Valve Replacement	DA FR GE HU IT RU SL SP SW	7135596A 7119048A 7119107A 7119322A 7119087A02 7135901A 7135666A03 7119214A 7146527A02	IN	(317102) or (317107)	EN - 1053279A03 - Issued 08/09
--	Prodigy HDLV Pump Circuit Board Replacement	DA DU FI FR GE IT PO RU SL SP SW	7135597B 7169058B02 7169021B02 7156983B02 7156859B02 7156885B02 7156997B02 7135909B 7135664B 7169081B02 7169046B02	IN	(317102) or (317107)	EN - 1058046B02 - Issued 11/08
--	Prodigy High-Capacity HDLV Pump Fluidizing Tube Replacement	CZ DA DU FI FR GE GR IT LI PL PO RU SP SW TU	7156724A02 7135598A 7135924A 7169026A02 7156986A02 7146784A02 7146760A02 7146567A02 7169123A02 7169091A02 7169003A02 7135908A 7169083A02 7146525A02 7192674A02	IN	(317102) or (317107)	EN - 1063413_03 - Issued 09/16

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 29

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Prodigy High-Capacity HDLV Pump Pinch Valve Replacement	CZ DA DU FI FR GE GR IT LI PL PO RU SP SW TU	7156723 A02 7135599A 7135923A 7169027 A02 7156987 A02 7146785A 7146759A 7146568A 7169124 A02 7169092 A02 7169004 A02 7135907A 7169084 A02 7146529A 7192673 A02	IN	(317102) or (317107)	EN - 1063437A02 - Issued 08/09
--	Prodigy HDLV Pump Lance Powder Tube Fitting Kit	CZ DU FI FR GE IT PL PO RU SP SW	7156087A 7169060A 7169023A 7156984A 7156860A 7156886A 7169090A 7156998A 7169069A 7169082A 7169047A	IN	(317102) or (317107)	EN - 1071378A - Issued 06/06
--	Prodigy HDLV Transfer Pump Station	GE IT TU	7192134A03 7560172A03 7192671A03	IN	(317102) or (317107)	EN - 1073134A03 - Issued 08/09

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 30

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Prodigy Generation II HDLV Manual System Installation Instructions	CZ DU FI FR GE IT PL PO RU SP SW	7135762A 7169056A 7169019A 7156981A 7156858A 7156894A 7169088A 7156995A 7135904A 7169079A 7169044A	IN	(317102) or (317107)	EN - 1081707A - Issued 09/07
--	Prodigy Generation II High-Capacity HDLV Powder Transfer Pump	CH CZ DA DU FI FR GE HU IT LI PL PO RO RU SL SP SW TU	7169398A04 7156722A03 7560536A04 7179661A04 7156586A03 7169904A04 7169346A04 7169537A04 7560576A04 7169122A03 7156775A03 7156846A04 7169454A04 7169075A03 7179732A04 7156340A03 7156809A04 7192672A04	MA	(317102) or (317107)	EN - 1092270A04 - Issued 10/10

Nordson Finishing Products (sorted by Product Title) *U.S. Powder*

C-2 - 31

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Prodigy HDLV System Troubleshooting - Generation III (Rev. A - A03: Generation II)	CZ DU FI FR GE IT PL PO RU SP SW	7135776A 7156847A03 7156848A03 7156864A03 7146672A 7146671A 7146621A 7156865A04 7156863A04 7156849A03 7146519A	IN	(317102) or (317107)	EN - 1081071_05 - Issued 03/16
--	Prodigy Generation III HDLV Pump, Pump Manifold and Circuit Board (Title - A06: Prodigy HDLV Pump Generation 2, Pump Manifold and Circuit Board (Title A - A04: Prodigy HDLV Pump Generation 2)	CR CZ DA DU FI FR GE IT LI PL PO RO RU SL SP SW TU	7580007_10 7135752_08 7192438_08 7169061_08 7169024_08 7135797_10 7146158_08 7146566_08 7169119A06 7146998_08 7156999_08 7146062_08 7135894_10 7169641_08 7156342_08 7146458_08 7192482_08	MA	(317102) or (317107)	EN - 1081195_10 - Issued 03/16

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 32

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Prodigy Generation III Manual Powder Spray System (Title version A: Prodigy HDLV Manual System Generation III)	CZ DU FI FR GE PL PO RO RU SL SP SW	7179154_02 7179042_02 7179187_02 7179164_02 7179035_02 7179052_02 7179049_02 7192145_03 7179151_02 7169640A 7179161_02 7179157_02	MA	(317102) or (317107)	EN - 1102106_03 - Issued 11/12
--	Prodigy PLC Gateway Generation III	GE IT	7169606A 7560870_02	MA	(317102) or (317107)	EN - 1102107_02 - Issued 12/14
--	Prodigy Generation III HDLV Manual System Operator's Card	CZ DU FI FR GE PL PO RO RU SP SW	7179155A 7179043A 7179188A 71791655A 7179036A 7179053A 7179050A 7192146A 7179152A 7179162A 7179158A	OP	(317102) or (317107)	EN - 1102109A - Issued 07/10

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 33

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Prodigy Generation III Automatic System HDLV Pump Panel	CZ DU FI FR GE PL PO RO RU SL SP SW TU	7179156A 7179044A 7179189A 7179166A 7179037A 7179054A 7179051A 7192147A 7179153A 7179733A 7179163A 7179159A 7192824A	MAN	(317102) or (317107)	EN - 1102110A - Issued 11/10
--	Pulse Valve Diaphragm Kit	PL	7105782A	IN	(317102) or (317107)	EN - 1038550_02 - Issued 02/13
--	Spectrum Powder Feed Center	PL PO RO RU SP	7169552A 7169287A 7169505A 7192392_03 7169363A	MA	(317102) or (317107)	EN - 1103292_04 - Issued 04/15
--	Standard Powder Transfer Pump Kit	RU	7156611C	IN	317102) or (317107)	EN - 108655C - Issued 09/02

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 34

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
31-46	Sure Coat Automatic Powder Spray Gun	CH CZ DA DU FI FR GE GR HU IT PL PO RU SP SW	7169399J03 397423F 397334F 397343F 213798D 397282F 464967J 7105865G 7119643J 464922J 7105249F 397357J03 7105343F 213067J03 213691D	MA	(317102) or (317107)	EN - 334627_05 - Issued 04/16
--	Sure Coat and Prodigy Manual Gun Cable Replacement (Title Rev. B: Sure Coat Manual Gun Cable Replacement)	DU FI FR GE IT PL PO RU SL SP SW	7169066C03 7169031C03 7156990C03 7146786C03 7156892C03 7169097C03 7169009C03 7135906C03 7135670C03 213342B 7146522C03	IN	(317102) or (317107)	EN - 237393C03 - Issued 09/07
34-40	Sure Coat Manual Gun Lance Extensions	DU FI FR GE IT PL PO RU SP SW	7169067B 7169032B 7156991B 7156862B 7156893B 7169098B 7169010B 7169074B 213343B 7169052B	IN	(317102) or (317107)	EN - 303814B - Issued 03/13

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 35

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
37-31	Tribomatic 500 Manual Powder Spray Gun	FI GE IT NO PL SP SW	458101B 412611B 7119782D 409029B 7169215D02 412645B 7105192C	MA	(317102) or (317107)	EN - 237467D02 - Issued 11/07
--	Tribomatic Optional Sprayheads and Nozzles	DA FR IT PL PO SP	7105405A 7135682A 7105730A 7169222A 7105807A 397992A	IN	(317102) or (317107)	EN - 1040999A - Issued 04/03
37-20	Tribomatic II Automatic Powder Spray Gun	CZ FR GE IT PL PO RU SP	7156721F 213339F 412651D 407422C 409483C* 407492E 7105974F 213327E	MA	(317102) or (317107)	EN - 106571F - Issued 10/02
--	Tribomatic II Manual Powder Spray Gun	IT	7560141A	MA	(317102) or (317107)	EN - 1098020A - Issued 06/09
37-19	Tribomatic II Powder Pump	CZ DA DU GE IT PO RU SP	7146162B 7105422B 7135925B 7119145B 412843A 458048A 7119849B 458334A	IN IN IN IN MA MA IN MA	(317102) or (317107)	EN - 106570B - Issued 05/01 Rev. A = Manual Rev. B = Instructions

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 36

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
37-34	Tribomatic II Extended Automatic Powder Spray Gun	DA FI GE IT SP	7105404B 7105427B 213866B 7105717B 7146156 B03	MA	(317102) or (317107)	EN - 334691B03 - Issued 07/06
37-38	Tribomatic II Purgeable Automatic Powder Spray Gun	FR GE IT PL PO SP	7135681 A02 213856A 7105718 A02 7169221 A02 7105805 A02 397991 A02	MA	(317102) or (317107)	EN - 1014255A02 - Issued 04/03
--	Vantage FCM Booth	SP	7179973A	MA	(317102) or (317107)	EN - 1102582A - Issued 05/11
--	Vantage Individual Powder Spray Gun Controller	CH CZ DA DU ES FI FR GE IT PL PO RO RU SK SP SW	7169400C 7105341A 7105267C 7105288A 7169375C 7105516C 7105356C 7105269C 7105265C 7105575A 7105262C 7135708C 7105488A 7156505C 7105294C 7105291C	MA	(317102) or (317107)	EN - 1044199_04 - Issued 04/15
--	Vantage Manual Electrostatic Porcelain Enamel Powder Spray Gun	RU	7146865A	MA	(317102) or (317107)	EN - 1075735_02 - Issued 04/16

Nordson Finishing Products (sorted by Product Title)

U.S. Powder

C-2 - 37

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Vantage Manual Powder Spray Gun	CZ FI FR IT PO RU SP	7135981A 7135760A 7135611A 7135600A 7156433A02 7135826A 7135534A	MA	(317102) or (317107)	EN - 1070278_04 - Issued 04/16
--	Vantage Manual Spray Gun Control Unit	CZ FI FR GE IT PO RU SP	7135982A02 7135761A02 7135612A02 7135539A02 7135601A02 7156434A02 7135827A02 7135535A02	MA	(317102) or (317107)	EN - 1066850_03 - Issued 04/16
--	Vantage Modular Gun Control System	CZ DA DU FI FR GE GR HU IT PL PO RO RU SP SW	7105342A 7105268A 7105289A 7105517A 7105357A 7105270C 7105950C 7105814B 7105266A 7105576A 7105263A 7119576C 7105489A 7105295C 7105292A	MA	(317102) or (317107)	EN - 1046736_05 - Issued 04/15
--	Vantage RCM Powder Coating Booth	SP	7179974A	MA	(317102) or (317107)	EN - 1030157A - Issued 10/02

Nordson Finishing Products (sorted by Product Title) *U.S. Powder*

C-2 - 38

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Vantage RCM Powder Coating Booth Installation Instructions	SP	7179975A	In	(317102) or (317107)	EN - 1032841A - Issued 10/02
35-11	Versa-Coat Batch and Conveyor Booths	SP	412817B	MA	(317102) or (317107)	EN - 106535E - Issued 06/01
31-23	Versa-Spray IPS Automatic Electrostatic Porcelain Enamel Powder Spray Gun	DA ES FR GE IT NO PL RU SP SW TU	7192784F02 7169372F02 292920C 292919F02 407479C 413003C 7560641F02 7135182F02 7560144F02 7105131F02 7135690F02	MA	(317102) or (317107)	EN - 106584_03 - Issued 05/16
31-26	Versa-Spray II IPS Automatic Powder Spray Gun	DA DU FI FR GE HU IT PL PO RO RU SK SP SW	315766D 412820E 397970H 213010G 292925D 7105815G 292926G 7119240G 7135505_02 7119572H 7105490H 7156507H 397868G 213618E	MA	(317102) or (317107)	EN - 107016_02 - Issued 05/16

Nordson Finishing Products (sorted by Product Title) *U.S. Powder*

C-2 - 39

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
33-19	Versa-Spray II IPS 2-Gauge Control Unit	DU FI FR GE IT NO PL PO SP SW	213633C 397968D 292834C 292835A 292836C 413001B 7119239D 7119165D 397860C 213587C	MA	(317102) or (317107)	EN - 106991D - Issued 07/05
--	Vibratory Deck Sieves - 15 in. (380 mm)	RO RU SP	7192947_01 7192954_01 7192291_01	IN	(317102) or (317107)	EN - 1604433_01 - Issued 07/13
--	VO618N Belt-Drive Horizontal In/Out Positioner	PO SP	7169276A 7169342A	IN	(317102) or (317107)	EN - 1058080A - Issued 02/05

Nordson Finishing Products (sorted by Product Title) *U.K. / Europe Powder*

C-3 - 1

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Afterfilter Generation 5	CZ DA DU EN FI FR GE IT LI PL PO RO RU SP SW TU	7146918A 7560532C 7179662C 7146911C 7156577C 7156513A 7146914C 7146912A 7169110A 7146915A 7179347C 7169504C 7146916A 7146917A 7146913C 7192942C	MA	(317102) or (317107)	Issued 11/10
	Afterfilter Generation 5 - Total Control Board	CR CZ DA DU EN FI FR GE IT LI PL PO RO RU SP SW TU	7580010C 7146926A 7560533C 7179663C 7146919C 7156583C 7156514A 7146922C 7146920A 7169111A 7146923A 7179348C 7169503C 7146924A 7146925A 7146921A 7192943C	MA	(317102) or (317107)	Issued 06/10
	Big Bag Unloader	EN	7580188_01	MA	(317102) or (317107)	Is currently beeing created by Nordson (U.K.) Ltd.

Nordson Finishing Products (sorted by Product Title)

U.K. / Europe Powder

C-3 - 2

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	ColorMax Engineered Booth	CZ EN FR GE PO RO RU	7192648B 7156925B 7169906B 7169226B 7179340B 7192141B 7169826B	MA	(317102) or (317107)	Issued 10/15
	ColorMax ³	CH CR CZ DA DU EN FI FR GE IT LI PL PO RO RU SP SW TU	7156424A 7580006D 7135647A 7135632C 7146574C 7135457D 7135603C 7169977C 7146708C 7146746C 7169109A 7146575A 7179345C 7135943A 7135646A 7135672C 7146333C 7192941C	MA	(317102) or (317107)	Issued 02/16
	ColorMax ³ Colour Change Procedure - Prodigy	EN FI FR GE PO RU SP	7169100A 7169442A 7169983A 7179296A 7179346A 7192230A 7179452A	OP	(317102) or (317107)	Issued 11/10
	Detecting Module MRT 116	EN RU	7156271A 7156272A	MA	(317102) or (317107)	Issued 2008 (Word .docs)

Nordson Finishing Products (sorted by Product Title)

U.K. / Europe Powder

C-3 - 3

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
--	ECC 701 Electrostatic Cable Coater	CZ DA EN ES FI FR GE IT PL PO RU SK SP SW	7146388C 7192768_04 7146059_06 7169371C 7146175C 7146202_05 7135786_06 7146157_05 7169587_05 7156763_06 7179269_04 7156503B 7146999_04 7146159_04	MA	(317102) or (317107)	Issued 08/16 Created by Nordson Engineering GmbH
--	ECC 701 Electrostatic Cable Coater - Parts List-	EN	7135883_06	PA	(317102) or (317107)	Issued 12/16 Created by Nordson Engineering GmbH
--	ECC 701 Operator's Card	CZ DA DU EN ES FI FR GE IT NO PL PO RU SK SP SW	7146881A 7146882A 7146880A 7146860A 7169374A 7146883A 7146884A 7146859A 7146885A 7146886A 7146887A 7146879A 7146888A 7156504A 7146878A 7146889A	OP	(317102) or (317107)	Issued 02/09 Created by Nordson Engineering GmbH

Nordson Finishing Products (sorted by Product Title) U.K. / Europe Powder

C-3 - 4

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
--	ECC 702 Electrostatic Cable Coater	GE	7560959_01	MA	(317102) or (317107)	Is currently beeing created by Nordson Engineering GmbH
--	ECC 702 Electrostatic Cable Coater - Parts List-	EN	7580107_01	PA	(317102) or (317107)	Is currently beeing created by Nordson Engineering GmbH
--	ECC 702 Operator's Card	EN GE	7580101_01 7580100_01	OP	(317102) or (317107)	Is currently beeing created by Nordson Engineering GmbH
--	ECC-Compact Electrostatic Cable Coater	GE LA RU	7192931_02 7580135_02 7560807_02	MA	(317102) or (317107)	Issued 05/17 Created by Nordson Engineering GmbH
	Motorized Base Control HQ-612	EN SP	7156273A 7156274A	MA	(317102) or (317107)	Issued 2009 - Word .docs
	Nordson MicroMax Booth (Manual Spray Booth)	CZ CR DA DU EN FI FR GE HU IT PO RU SL SP SW	7156050J ** 7146769_11 7135592_11 213114D 768635_11 213291E 7119293_11 458238A 7119323_11 458261E 7105023_11 447739C 716955_11 464767D 213967I	MA	(317102) or (317107)	** = Document and translation is NOT issued by TDLL ! Issued 12/13

Nordson Finishing Products (sorted by Product Title)

U.K. / Europe Powder

C-3 - 5

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	NQCB / NCB Booth Systems	CZ DA EN FR GE IT LI PL PO RU SP TU	7156186C 7135593C 768636E 7119814C 7146685E 7156193E 7192127E 7119196C 7105992C 7105586C 7135674C 7135716C	MA	(317102) or (317107)	Issued 01/13
	Oscillator HOF/50	CZ DA DU EN FI FR GE PL RU SP SW TU	7560034_02 7560277_02 7560282_02 7192822_02 7560275_02 7560278_02 7560281_02 7560276_02 7560280_02 7560279_02 7560283_02 7560284_02	MA	(317102) or (317107)	Issued 05/16
	PowderPilot ^{HD} System Manual	CZ DA EN FI FR GE RO RU SP SW TU	7192740_01 7560535_01 7192721_01 7192863_01 7560152_01 7192776_01 7560261_01 7192777_01 7192743_01 7560877_01 7192938_01	MA	(317102) or (317107)	Issued 08/14

Nordson Finishing Products (sorted by Product Title)

U.K. / Europe Powder

C-3 - 6

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Reciprocator HF30 V4 / HF80 V4	CZ DA DU EN FI FR GE PL RO RU SP SW TU	7179858_02 7192111_02 7192100_02 7179770_02 7179719_02 7192116_02 7192101_04 7192135_02 7192967_02 7179788_02 7179999_02 7192110_02 7192109_02	MA	(317102) or (317107)	Issued 04/16
	Reciprocator Control HQF-02	CZ DU EN FR GE PL RO RU SP	7179859_01 7192272_01 7179783_01 7192227_01 7192315_01 7192322_01 7192318_01 7192316_01 7179657_01	OP	(317102) or (317107)	Issued 06/13
	Spectrum HD Powder Feed Center - Generation II -	CZ DA DU EN FI FR GE RO RU SP SW TU	7192917_01 7560534_01 7192914_01 7192568_01 7192898_01 7560151_01 7192913_01 7560260_01 7192912_01 7192910_01 7560878_01 7192940_01	MA	(317102) or (317107)	Issued 10/14

Nordson Finishing Products (sorted by Product Title) *U.K. / Europe Powder*

C-3 - 7

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Tilt Table	EN	7560626_01	MA	(317102) or (317107)	Is currently beeing created by Nordson (U.K.) Ltd.
	Twin Cyclones	CZ DA DU EN FI FR GE IT LI PO RU SP SW TU	397894F 7135349D 213812D 768641F 7156533E 213987D 464727E 464738D 7169112D 213975E 7105590D 397006E 213920E 7192939E	MA	(317102) or (317107)	Issued 10/15
	Venturi & HDLV - 150L Powder Feed Hopper	EN	7560761_01	MA	(317102) or (317107)	Is currently beeing created by Nordson (U.K.) Ltd.

Nordson Finishing Products (sorted by Product Title)

U.K. / Europe Powder

C-3 - 8

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Z-Axis Gun Mover Positioner (Incl. Ext. Gun Blow Off)	CZ EN FR GE PL SW	397899D 768648D 397096D 464901D 7105016D 213985D	MA	(317102) or (317107)	Issued 03/02 Obsolete !
	Z-Axis HBF	CZ DA DU EN FI FR GE PL RO RU SP SW TU	7192548_01 7192519_01 7192525_01 7179832_01 7192532_01 7192526_01 7192492_01 7192522_01 7192968_01 7192450_01 7179629_01 7192521_01 7192524_01	MA	(317102) or (317107)	Issued 05/16

D-1-1

Nordson UV Products (sorted by Product Title)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
U.K. Products						
--	6kW Mini Cooler	FR EN GE	7156813A 7119934A 7135790A	IN	(317102) or (317107)	
--	Accelerated Drying System (Sheetcure)	DU	no P/N	MA	(317102) or (317107)	
--	Digital Power Supply DPS 5-U	EN	7135100A	MA	(317102) or (317107)	
--	DropCure UV Lamp Head	FR EN GE	7156812C 7119747C 7135789C	MA	(317102) or (317107)	
--	e-Series	EN FR GE	7146507A 7146771A 7156622A	MA	(317102) or (317107)	
--	ew-Series System	EN GE	7156018A 7156208A	MA	(317102) or (317107)	
--	Ink Mist Extraction Hood	DU NO	no P/N no P/N	MA	(317102) or (317107)	EN source - IM-C01-A
--	MiniCure	EN NO SW	7119745C 7135932C 7135638C	MA	(317102) or (317107)	
--	MaxiCure	EN	7119746A	MA	(317102) or (317107)	

D-1-2

Nordson UV Products (sorted by Product Title)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Nordson Cooler Unit	EN GE IT FR PO SP	213000D 213001D 397908C 213711C 397859C 7105487D	MA	(317102) or (317107)	
--	Nordson Drying System	CH DU EN FI FR GE GR IT JA PL PO RO RU SP SW TU	7119406G 7105939G 464978G 7146271G 213710G 464979G 7135272G 397909G 7119401G 7146987G 397855G 7119947G 7119886G 7105486G 7146088G 7105824G	MA	(317102) or (317107)	
Parts Drawings	LS29 I/C	EN	7156414A	PA	(317102) or (317107)	
Parts Drawings	LSX29 I/C	EN	7156415A	PA	(317102) or (317107)	
Parts Drawings	LSX29 EOP-DU	EN	7156416A	PA	(317102) or (317107)	
Parts Drawings	LSX40 I/C	EN	7156417A	PA	(317102) or (317107)	

D-1-3

Nordson UV Products (sorted by Product Title)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Parts Drawings	LS40 EOP (Upsweep)	EN	7156418A	PA	(317102) or (317107)	
Parts Drawings	LS40 DU-EOP	EN	7156419A	PA	(317102) or (317107)	
Parts Drawings	LS40 I/C	EN	7156420A	PA	(317102) or (317107)	
--	PU System	EN FR GE	7135102A 7156811A 7135791A	MA	(317102) or (317107)	
--	Spectral Drying Systems - Operating Manual	SP	no P/N	MA	(317102) or (317107)	EN source - Manual 2.1
--	Spectronic NT20 Monochrome Display	DU FR GE SP	no P/N no P/N no P/N no P/N	MA	(317102) or (317107)	EN source - D 122135D
--	Spectronic NT 31 Colour Display	DU FR GE SW	no P/N no P/N no P/N no P/N	MA	(317102) or (317107)	EN source - 12NT31 C
--	Spectronic Operating / Alarm Instructions	FR GE	no P/N no P/N	MA	(317102) or (317107)	EN source - D 0600000
--	Spectronic Operating / Alarm Instructions	FR	no P/N	MA	(317102) or (317107)	EN source - D 122135A

D-1-4

Nordson UV Products (sorted by Product Title)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Spectronic 3 Operating Manual for Nordson Dryer	CH DU EN FR GE GR IT JA PO RO RU SP TU	7119407B 7105940B 397431B 397553B 397677B 7135273B 397933B 7119402B 397801B 7119948B 7119887B 7105445B 7105825B	MA	(317102) or (317107)	
--	Spectronic 4 Manual	CH DU EN FI FR GE GR IT JA PL PO RO RU SP SW TU	7135844F 7135845F 7135629F 7146272E 7135846E 7135847E 7135630E 7135842E 7146874C 7146988F 7135848E 7135849E 7135850E 7135851E 7135843E 7135852E	MA	(317102) or (317107)	
--	Ultra-Violet Curing System	PO SP	no P/N 409030A	MA	(317102) or (317107)	EN source - 407467A (av. in EDC)
--	UVED UV Light Emitting Diode	EN	7156629A	MA	(317102) or (317107)	

D-1-5

Nordson UV Products (sorted by Product Title)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
U.S. Products						
--	CoolWave Ultraviolet Microwave Applied Curing System with Six-Inch Lamphead	SW	7105076B	MA	(317102) or (317107)	EN - 775361B - Issued 6/03
--	CW306 Lamphead with Unicable	FR GE IT	7119952B 7105088A 7119398B	MA	(317102) or (317107)	EN - 775567B - Issued 5/05
--	Coolwave 306 Lamphead with Unicable	PL PO SP	7179927A03 7169131A03 7169370A03	MA	(317102) or (317107)	EN - 1074167A03 - Issued 11/10
--	CW410 Lamphead with Unicable	FR	7119954A	MA	(317102) or (317107)	EN - 775555A - Issued 5/05
--	Coolwave 2 410 UV Curing System	JA	7192643_01	MA	(317102) or (317107)	EN - 1105121_01 - Issued 4/13
--	CW610 Lamphead	GE	7105087A	MA	(317102) or (317107)	EN - 775560A - Issued 2/04
--	CW610 Lamphead with Unicable	FR GE PL SW	7119480B 7119347A 7119482B 7119356A	MA	(317102) or (317107)	EN - 1061255B - Issued 1/06
--	CW610 Lamphead with Unicable	FR	7560724A02	MA	(317102) or (317107)	EN - 1074165A02 - Issued 11/10
--	CoolWave 2 610-Inch UV Curing System	GE IT SK	7156495A06 7146697A03 7179268A06	MA	(317102) or (317107)	EN - 1085684A06 - Issued 06/10
--	Coolwave 2 610 UV Curing System	JA	7192644_01	MA	(317102) or (317107)	EN - 1105120_03 - Issued 4/13

D-1-6 Nordson UV Products (sorted by Product Title)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
--	MPS306F Power Supply with Unicable	FR GE IT	7119953C 7105086A 7119399C	MA	(3171012)	EN - 775569C - Issued 7/05
--	MPS306F Power Supply with Unicable	PL PO SP	7179926A 7169132A 7169369A	MA	(3171012)	EN - 1074166A - Issued 06/07
--	MPS610D Power Supply with Dual Cables	GE	7105085A	MA	(317102) or (317107)	EN - 775564B - Issued 02/04
--	MPS610V Power Supply with Unicable	FR GE PL SW	7119481B 7119348B 7119483B 7119357A	MA	(317102) or (317107)	EN - 1061254B - Issued 1/06
--	MPS610V Power Supply with Unicable	FR	7560725A	MA	(317102) or (317107)	EN - 1074164A - Issued 1/07
--	MPS610V Power Supply with Dual Cables	GE	7105084A	MA	(317102) or (317107)	EN - 775562B - Issued 2/04

E-1-1

Paper and Paperboard Converting Nordson Benelux Products (former Walcom) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
BRACKETS	Brackets	EN GE	213017A 464847A	MA	(317102) or (317107)	For Nordson internal use ONLY
BRACKETS	Core Winding Bracket 120	EN GE	7179249_01 7179182_01	MA	(317102) or (317107)	
BC 5100	BC 5100 Bar Code Scanner	HU PL	7560488A 7156844A	MA	(317102) or (317107)	EN - 1076483A
CBC 5100	Color Barcode Scanner CBC 5100	CZ DU EN FR GE IT PL SP	7169309D 7135444D 7135357D 7135418D 7135024D 7135360D 7169306D 7135368D	MA	(317102) or (317107)	
CHAMELEON	Application Head System	CZ DU EN FI FR GE IT JA SP SW	7560663C 458076C 409216C 213177C 447630C 409215C 213233C 7119846C* 213231C 213238C	MA	(317102) or (317107)	* available at Nordson K.K
E 26	Electric Gun Driver	DU FR GE IT SP SW	317127A 317128A 317129A 317134A 317144A 317130A	MA	(317102) or (317107)	EN - 187728A (EDB 42-81) No longer valid - replaced by SD Series Electric Gun Driver (see Section B - Hot Melt)

E-1-2

Paper and Paperboard Converting Nordson Benelux Products (former Walcom) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
EP48	Spine Gluing with EP 48 and LogiComm - OPERATION	EN GE	7192179_01 7192180_01	IN	(317102) or (317107)	
EP48	Spine Gluing with EP 48 and LogiComm - SETTINGS	EN GE	7192181_01 7192182_01	IN	(317102) or (317107)	
EP48	Spine Gluing with EP 48 (Integrated Systems) - OPERATION	EN GE IT	7192201_01 7192202_01 7560107_01	IN	(317102) or (317107)	
EP48	Spine Gluing with EP 48 (Integrated Systems) - SETTINGS	EN GE IT	7192203_01 7192204_01 7560108_01	IN	(317102) or (317107)	
G-NET	G-NET Verification System	DA DU FI FR GE IT NO SP SW	464728A 464729A 464730A 464731A 464732A 464733A 464734A 464736A 464737A	MA	(317102) or (317107)	EN - 321226D (56-GNET-MA-01)
LA 22/ LA 44	Glue Guns	GE	397019A	MA	(317102) or (317107)	EN - 321344A
LA 100	Level Monitor	CZ EN FR GE IT SP	7169320A 7156393A 7156388A 7156078A 7156389A 7156382A	MA	(317102) or (317107)	

E-1-3

Paper and Paperboard Converting Nordson Benelux Products (former Walcom) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LA 100-C	Level Detection	EN FR GE IT PL SP	7169652_02 7169742_01 7169595_03 7169735_01 7192340_02 7169675_01	MA	(317102) or (317107)	
LA105	Pressurized Adhesive Container	EN	7119459A	MA	(317102) or (317107)	
LA120	Pressurized Adhesive Container	EN	7119460A	MA	(317102) or (317107)	
LA 105/ LA 120/ LA 140	Pressurized Adhesive Container	CZ DU	7169321B 213270A	MA	(317102) or (317107)	Obsolete!
LA 105/ LA 120/	Pressurized Adhesive Container	EN FR GE IT PL SP	213261_03 213647_03 213207_03 213627_03 7179438_03 213652_03	MA	(317102) or (317107)	New!

E-1-4

Paper and Paperboard Converting Nordson Benelux Products (former Walcom) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LA 300	Piston Pump	CZ DA DU EN FI FR GE GR HU IT JA NO PL PO RU SP SW	7105336_05 7105329_05 7105327_06 7105256_06 7105330_05 7105324_06 7105255_06 7105334_05 7105335_05 7105326_06 7105963A* 7105333_05 7105331_06 7105332_05 7146365_06 7105325_06 7105328_06	MA	(317102) or (317107)	* available at Nordson K.K
LA 302	Pressure Controller	EN GE FI FR	7119797A 7119689A 7135479A 7169376A	MA	(317102) or (317107)	

E-1-5

Paper and Paperboard Converting Nordson Benelux Products (former Walcom) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LA 310	Piston Pump	CZ DA DU EN FI FR GE GR HU IT NO PL PO RU SP SW	7156309_04 7156336_04 7156312_05 7156289_05 7156318_04 7156331_05 7156068_05 7156322_04 7156323_04 7156311_05 7156324_04 7156317_05 7156315_04 7156314_05 7156310_05 7156316_05	MA	(317102) or (317107)	
LA 320/ LA 320M	Pneumatic Diaphragm Pump (see also WM320 / WM320M - revision A)	CZ DU EN FI GE JA PL	7105797B 409147B 407442B 7135478B 407441B 7119455B* 7146764B	MA	(317102) or (317107)	Issued 12/ 2000 * available at Nordson K.K
LA 320/ LA 320M	Pneumatic Diaphragm Pump	CZ DU FI FR EN GE HU PL	7156758_02 7156756_02 7156782_02 719235_02 7156751_02 7156689_02 7192545_02 7156771_02	MA	(317102) or (317107)	Issued 03/ 2010

E-1-6

Paper and Paperboard Converting Nordson Benelux Products (former Walcom) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LA 330	Constant Pressure Controller	DA DU EN FR GE IT NO PO SP	213400A 213360A 213329A 213371A 213306A 213383A 213354A 213346A 213324A	MA	(317102) or (317107)	
LA 330-II	Constant Pressure Controller	BU DU EN GE PO SP	7135430C 7156805C 7105264C 397831C 7146392C 7105564C	MA	(317102) or (317107)	
LA 380	Pressure Regulators	CZ DU EN FR GE IT JA PL RU SP SW	7146498 C 397470 C 397377 C 397467 C 397376 C 397468 C 7105962A* 7119151 C 7146366 C 397469 C 397471 C	MA	(317102) or (317107)	* available at Nordson K.K
LA 404	Pattern Control System	CZ DU FR GE IT JA SP	7105819A 397441A 397401A 397463A 397400A 7119847 B 397484A	MA	(317102) or (317107)	EN - 1037527B

E-1-7

Paper and Paperboard Converting Nordson Benelux Products (former Walcom) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LA 404-2	Pattern Controller	BU CZ DA DU EN FI FR GE GR HU IT JA NO PL PO RU SK SL SP SW TU	7135434A 7146017A 7146132A 7135120A 7119995A 7146072A 7135076A 7119877A 7146155A 7146080A 7135125A 7135155A 7146100A 7135344A 7146169A 7146131A 7146168A 7146073A 7135128A 7135130A 7146032A	MA	(317102) or (317107)	
LA 600PE	Product Ejection System	CZ DU EN FR GE IT PL SP	7169310A 213816A 213433A 213796A 213443A 213804A 7119152A 213820A	MA	(317102) or (317107)	

E-1-8

Paper and Paperboard Converting Nordson Benelux Products (former Walcom) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LA 725/ LA 725-S	Applicators	DU EN FR GE IT JA PL SP	7192844_02 7179424_02 7179490_02 7179276_02 7179491_02 7192416_01* 7192698_02 7179448_02	MA	(317102) or (317107)	* available at Nordson K.K
LA 820/ LA 820 RC	Liquid Adhesive Guns	CZ DU EN FR GE IT PL SP	7105766B 7105977B 7105681B 7105927B 7105680B 7105931B 7119153B 7105928B	MA	(317102) or (317107)	
LA 825/ LA 825 RC	Applicators (Version A: Liquid Adhesive Guns)	CZ DU EN FR GE IT PL RU SP	7156031_02 7156032_02 7156011_02 7156027_02 7156001_02 7156029_02 7156033_02 7156028_02 7156030_02	MA	317102) or (317107)	
LA 844M	LA 844M Electric Applicator	CZ DU GE IT PL RU SK SP	7192780A 7192498A 7179541A 7146352A02 7192857A02 7560671A02 7560998A02 7192790A02	MA	(317102) or (317107)	EN - 1062950A02

E-1-9

Paper and Paperboard Converting Nordson Benelux Products (former Walcom) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LA 901	Hot Melt Application Head	EN GE	7135939B 7135721B	MA	(317102) or (317107)	
LA 4100	User Interface Specification	DU FR GE IT SP SW	213530A 213605A 213529A 213531A 213528A 213532A	MA	(317102) or (317107)	EN source no P/N (Rev. F 4/02/01)
LA 4100	Pattern Control System	DU FR GE IT SP	213573A 213604A 213584A 213553A 213817A	MA	(317102) or (317107)	EN-1006817A
LA 4400	Pattern Control System	DU FR GE IT SP	213805A 213773A 213770A 213858A 213971A	MA	(317102) or (317107)	EN - 321232D
LA 5091	Hot Melt Glue Sensor	-	-	OP	(317102) or (317107)	EN - 377023A
Labeling	Multi e. dot+ Gun	EN GE	7169558B 7146700B	MA	(317102) or (317107)	
Labeling	Bracket for Multi e. dot+ Guns	GE	7146703A	MA	(317102) or (317107)	
Labeling	Electrical Cabinet Label Application System for Multi e. dot+ or MiniBlue II Guns	EN GE	7169559B 7146701B	MA	(317102) or (317107)	

E-1-10

Paper and Paperboard Converting Nordson Benelux Products (former Walcom) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Labeling	Electrical Cabinet Label Gluing System	DU EN FR GE IT PL SP	7156330A 7146179A 7156559A 7135653A 7135775A 7192213A 7156329A	MA	(317102) or (317107)	
Labeling	Electrical Cabinet Label Gluing System without Pneumatics	EN GE	7156012A 7156006A	MA	(317102) or (317107)	
Labeling	System Manual e.dot+ Roll Fed Labeling (RFL)	EN GE	7169564B 7146705B	MA	(317102) or (317107)	
LB 101	Pressurized Adhesive Container	DU EN FI FR GE IT NO PO SP SW	292759D 292758D 315717D 292761D 292760D 292762D 315740D 315718D 292763D 315719D	MA	(317102) or (317107)	
LB 120	Pressurized Adhesive Container	DU EN FR GE IT SP	292765D 292764_05 292767D 292766_05 292768D 292769D	MA	(317102) or (317107)	

E-1-11

Paper and Paperboard Converting Nordson Benelux Products (former Walcom) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LB 140	Pressurized Adhesive Container	DU EN FR GE IT SP	292771D 292770_06 292773_05 292772_06 292774_05 292775_05	MA	(317102) or (317107)	
LEP 34 S	Electropneumatic Hot Melt Applicators LEP 34 S	DU EN FR GE IT PL	7560307_03 397963_03 7135060B 397416_03 7135477B 7156144B	MA	(317102) or (317107)	
LS 373	Liquid Adhesive Gun	DU EN FI FR GE HU IT NO PL PO SP	292753E 292752E 315729E 292755E 292754E 7192547E 292756E 315743E 7146960E 315730E 292757E	MA	(317102) or (317107)	
LS-T 373	Liquid Adhesive Gun	EN FR GE IT SP	7135973B 7135977B 7135929B 7135983B 7135985B	MA	(317102) or (317107)	

E-1-12

Paper and Paperboard Converting Nordson Benelux Products (former Walcom) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LV 227	Applicator (Title version B + C: Liquid Adhesive Gun)	CZ DU EN FI FR GE IT JA NO PL PO SP SW	7169322B 405029C 405030_05 405031C 405032_05 405033_05 405034_05 464878B* 405035C 7135115C 405036C 405037_05 405038C	MA	(317102) or (317107)	* available at Nordson K.K
VarioCoat-S/ VarioCoat-M	Applicators	EN FR GE IT PL SP	7560317_02 7560327_02 7179993_02 7560328_02 7560330_02 7560329_02	MA	(317102) or (317107)	
WM 100 CS	Pattern Control Unit for Corrugated Cardboard	DU EN FI FR GE IT PL SP SW	317202C 317149C 7119343C 317205C 7135361C 317166C 7119975C 317167C 405211C	MA	(317102) or (317107)	Obsolete!
WM 302	Pressure Control Unit	DU EN FR GE IT SP	317145B 317146B 317147B 317108B 317171B 317148B	MA	(317102) or (317107)	

E-1-13

Paper and Paperboard Converting Nordson Benelux Products (former Walcom) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
WM 315& WM 315M & WM 325	Pneumatic Diaphragm Pump	DU EN FR GE IT SP	315855B 315814B 315856B 315837B 315857B 317087B	MA	(317102) or (317107)	Replaced by WM320/320M!
WM 315 H	High Pressure Pneumatic Diaphragm Pump	DU EN FR GE IT SP	317272A 317218A 403086A 317210A 403002A 317273A	MA	(317102) or (317107)	Obsolete!
WM 320/ WM 320M	Pneumatic Diaphragm Pump (see also LA320 / LA320M - revision B)	DU EN FR GE IT SP	409147B 407442B 409148A 407441B 409149A 409150A	MA	(317102) or (317107)	
WM 325	Pneumatic Membrane Pump	EN GE	458285A 458286A	MA	(317102) or (317107)	
WM 351/352	Pressure Regulator for Liquid Adhesives - Pump Mounted	DU EN FI FR GE IT SW	315905A 315841A 315906A 315907A 315842A 317182A 315908A	MA	(317102) or (317107)	
WM 353/354	Pressure Regulators for Liquid Adhesives - Wall Mounted	DU EN FR GE IT	315913A 315843A 315914A 315844A 317183A	MA	(317102) or (317107)	Replaced by LA38x series!

E-1-14

Paper and Paperboard Converting Nordson Benelux Products (former Walcom) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
WM 360	Pneumatic Piston Pump for Liquid Adhesives - Lid Mounted	CZ DA DU EN FI FR GE HU IT PL SP SW	7105365C* 315888C* 315889C* 315819C* 315890C* 315891C* 315838C* 403078B* 315892C* 397000C* 317049C* 315893C*	MA	(317102) or (317107)	* = supplement included - correction to parts list, page 8-7
WM 360 WM	Pneumatic Piston Pump for Liquid Adhesives - Wall Mounted	DU EN FI FR GE IT SP	403125A 403081A 213626A 409182A 403080A 409183A 403236A	MA	(317102) or (317107)	
WM 370	Pressure Regulators for Liquid Adhesives	DA DU EN FI FR GE IT SP	315896A 315897A 315839A 315898A 315899A 315840A 317180A 315917A	MA	(317102) or (317107)	
WM 408	OP - special corrugated	EN FR	213704A 213706A	OP	(317102) or (317107)	

E-1-15

Paper and Paperboard Converting Nordson Benelux Products (former Walcom) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
WM 408	Pattern Control Unit	DA DU EN FI FR GE IT PL RU SP SW	413009E 317068E 317063E 403085E 317069E 315866E 317111E 464774E 7135172E 317071E 405212E	MA	(317102) or (317107)	
WM 408	Pattern Control Unit	CH DA DU EN FI FR GE IT NO PL SW	213876A 458225A 213988A 374360A 458314A 375364A 458386A 458094A 458226A 458378A 458227A	OP	(317102) or (317107)	
WM 408	PCA 408 Electric Gun Driver Board (7 languages: DU / EN / FR / GE / IT / SP / SW)	--	331182B	IN	(317102) or (317107)	EDB No. 4-44
WM 416	Pattern Control Unit	DU EN FR GE IT SP SW	405043A 317262A 407054A 317261A 405044A 403045A 407287A	MA	(317102) or (317107)	

E-1-16

Paper and Paperboard Converting Nordson Benelux Products (former Walcom) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
WM 500	Liquid Adhesive Detection System	DA DU EN FR GE IT RU SP SW	447663B 315864B 315815B 315865B 315816B 317225B 7135173B 317064B 407011B	MA	(317102) or (317107)	
WM 500	Liquid Adhesive Detection System	CH DA EN FI FR GE NO SW	213877A 458311A 374361A 458313A 375425A 464953A 458312A 458310A	OP	(317102) or (317107)	
WM 500	OP - special corrugated	EN FR	213705A 213707A	OP	(317102) or (317107)	
WM 710	Liquid Adhesive Gun	DU EN FI FR GE IT JA PL SP	405062B 403270B 213208B 407008B 403271B 407009B 464881B* 7179439B 407010B	MA	(317102) or (317107)	* available at Nordson K.K

E-1-17

Paper and Paperboard Converting Nordson Benelux Products (former Walcom) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
WM 801 P/Q	Liquid Adhesive Gun	CZ DU EN FI FR GE IT JA PL SP SW	7105366B 403229B 403123B 213502B 409096B 403122B 409104B 464882B* 397001B 403230B 409493B	MA	(317102) or (317107)	* available at Nordson K.K
WM 801 S/Q	Liquid Adhesive Gun	DU EN FI FR GE IT SP SW	7105725A 7105606A 7105799A 7105716A 7105605A 7105726A 7105728A 7105724A	MA	(317102) or (317107)	
WM 83X & WM 88X	Liquid Adhesive Guns	DA DU EN FI FR GE IT SP SW	315845A 315846A 315812A 315847A 315848A 315813A 315849A 317037A 315850A	MA	(317102) or (317107)	

Issued by Technical Documentation Local Languages (TDLL) Department, Nordson Engineering, Lüneburg
Status : July 2017

F-1 -1

Asymtek (sorted by Product Title)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Free-Standing Loaders	IT	409323A	MA		EN source - 76-UYO3-0C (Obsolete !!!)
	Millenium Series	FI FR GE	409342A 409449A 409322A	MA		EN source - 76-UML1-0C (Obsolete !!!)

Other translated Asymtek manuals are available on <<http://www.asymtek.com>> by clicking on Tech Support, then Manuals.

F-2 -1

EFD (sorted by Product Title)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
EFD	740V Series Dispense Valve Operating Manual	FR GE PL SK	7105999A 7105879A 7105800A 7119226A	MAN	(317102) or (317107)	EN - 7105955A
EFD	741V Series Dispense Valve Installation Guide	DU FR GE PL SP	7179190A 7135455A 7135058A 7119879A 7135117A	IN	(317102) or (317107)	EN - No P/N
EFD	741V Series Dispense Valve Maintenance and Parts Guide	DU FR GE PL SP	7179191A 7135456A 7135059A 7119880A 7135118A	IN	(317102) or (317107)	EN - No P/N
EFD	Float Level Switch Installation for 600D5 Series Tank Reservoirs	DU FR GE PL SK	7179192A 7119000A 7105880A 7105801A 7119227A	IN	(317102) or (317107)	EN - 7105956A

F-3 -1

JM Laboratories (sorted by Product Title)

Model/Edition	Product Title	Langs.	P/N	Type	Price Category	Notes
	<i>ORDER DIRECTLY VIA JML !</i>					
	Durafiber II Modular Application System	GE SP SW	412857A 458317A 412878A	MA	(317102) or (317107)	EN source - no P/N
	Durafiber III Modular Adhesive Applicator	FR GE IT SP SW	412970B 412971A 458300B 458265B 458205B	MA	(317102) or (317107)	EN source - no P/N
	Duraheater Modular Air Heating System	FR GE IT SP SW	458034A 412856A 458303A 458318A 412877A	MA	(317102) or (317107)	EN source - no P/N
	Duramelt DX-902 Expansion Melt Delivery System	IT	458305A	MA	(317102) or (317107)	EN source - no P/N (10171)
	Duramelt DX-902 Expansion Melt Delivery System	IT	447626A	MA	(317102) or (317107)	EN source - no P/N (11399)
	Duramelt DX-902 Melt Delivery System	PL SP	458371A 413050A	MA	(317102) or (317107)	EN source - no P/N
	Duramelt DX-902 Melt Delivery Unit - Ply Bonding System plus comprehensive Training material as .ppt file	IT	464908A	MA	(317102) or (317107)	EN source - no P/N
	Duramelt DX-2002 Melt Delivery System	GE IT SP	413066A 213012A 458039A	MA	(317102) or (317107)	EN source - no P/N
	Duramelt DX-2002 Melt Delivery System - HMI texts complete .xls file only, including screen .bmp files	EN/GE	-	-	-	

F-3 -2

JM Laboratories (sorted by Product Title)

Model/Edition	Product Title	Langs.	P/N	Type	Price Category	Notes
	Duraremove Metering Unit DRM 448	FR SP	458201A 458266A	MA	(317102) or (317107)	EN source - no P/N
	DX Remote HMI texts complete .xls file only (by Keith Mulkey)	EN/IT	-	-	-	
	MeltBlown Fiber System comprehensive manual (sections 1 - 6) (JM Job # 18685)	GE	-	MA	(317103) or (317106)	EN source - no P/N
	MonoComponent MeltBlown HMI texts complete .xls file only (JM Job # 18685)	EN/GE/ PO	-	-	-	
	MonoComponent MeltBlown Installation, Operation, Maintenance, Operation Fitesa	PO	-	-	-	EN source - no P/N
	Ply Bonding Applicator (Rev. 0005, Jan 2000)	IT	458304A	MA	(317102) or (317107)	EN source - no P/N
	Ply Bonding Applicator (Dec 99), incl. Charts	FR	458071A	MA	(317102) or (317107)	EN source - no P/N
	Ply Bonding Applicator (JM Job # 398834), including Warranty document	SW	-	MA	(317102) or (317107)	EN source - no P/N
	Polymer Meltblown (JM Job # 8996), plus System Screens, .ppt files	IT	458123A	MA	(317102) or (317107)	EN source - no P/N
	Remote Metering Station (Ref. D12340)	SP	447607A	MA	(317102) or (317107)	EN source - no P/N
	Spunbond Fiber System comprehensive manual (sections 1 - 9)	TU	-	MA	(317103) or (317106)	EN source - no P/N

Issued by Technical Documentation Local Languages (TDLL) Department, Nordson Engineering, Lüneburg
Status : July 2017

F-3 -3

JM Laboratories (sorted by Product Title)

Model/Edition	Product Title	Langs.	P/N	Type	Price Category	Notes
	Universal Slice Applicator	SP	213483A	MA	(317102) or (317107)	EN source - no P/N
	Universal Slice Applicator, Betrieb u Wartung, .ppt	GE	-	MA	(317102) or (317107)	EN source - no P/N

Issued by Technical Documentation Local Languages (TDLL) Department, Nordson Engineering, Lüneburg
Status : July 2017

F-4 -1

March Plasma (sorted by Product Title)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
AP-1000	AP-1000 Plasma System - Operation and Maintenance Manual	GE	397378A	MA	(317103) or (317106)	EN - 021-000137
XTRAK	XTRAK System - Operation and Maintenance Manual	GE	213749A	MA	(317103) or (317106)	EN - 021-000140 rev.1.0

F-5 -1

Mountaingate (sorted by Product Title)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Mountaingate Heat and Hold Induction System	EN PL	1041928A 7105857A	MA	(317102) or (317107)	
ICD	Series Induction Dryer	EN GE SP	75-3000-02 292958A 317216A	MA	(317102) or (317107)	
ICD	Series Induction Dryers	EN FR PO	1018438A 397091A 397088A	MA	(317102) or (317107)	
ISC2	Series Induction Dryers	EN FR SP	1606739_01 7192945_01 7560607_01	MA	(317102) or (317107)	
EcoDry	Series Induction Dryers	DU EN FR GE SP	7146532A02 1045354A02 7105554A 7119856A 7105560A	MA	(317102) or (317107)	Issued 02/04
EcoDry	Nordson EcoDry Series Induction Dryers with Touch Screen Controls	DU EN FR GE IT SP	7169793_02 1601306_02 7192654_02 7169824_02 7560078_02 7179714_02	MA	(317102) or (317107)	Issued 3/14

F-5 -2

Mountaingate (sorted by Product Title)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
EcoDry	Series Induction Dryers	EN FR GE SP	1045825A 7105555A 7119857A 7105561A	OP	(317102) or (317107)	
iDry	Nordson iDry Series Induction Dryers	DU EN FR GE HU IT PL PO RU SP	7179374A02 1075452_04 7135912_04 7179419A02 7560774_04 7179441A02 7192961A02 7580145_04 7179645A02 7135884_04	MA	(317102) or (317107)	

F-6 -1

Material Safety Data Sheets (sorted by Product Title)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
MSDS	Type R Fluid	EN/ FR/ GE/ IT/ SP/ SW	7156299C*	-	(317102) or (317107)	Multilingual document, therefore one P/N only * OLD! Replaced by version 08/12/2014 (Single documents)
MSDS	Type S Fluid	DU\EN/ FR/ GE/ IT/ SP/ SW	7156303D*	-	(317102) or (317107)	Multilingual document, therefore one P/N only * OLD! Replaced by version 06/03/2015 (Single documents)
MSDS	Type T Fluid	DU\EN/ FR/ GE/ IT/ SP/ SW	7156304D*	-	(317102) or (317107)	Multilingual document, therefore one P/N only * OLD! Replaced by version 08/28/2015 (Single documents)
MSDS	Vitalizer Oil	DU\EN/ FR/ GE/ IT/ SP/ SW	7156305D*	-	(317102) or (317107)	Multilingual document, therefore one P/N only * OLD! Replaced by version 08/28/2015 (Single documents)

PICODOSTEC (sorted by Product Title)

F-7 -1

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Micrometering System PICODOSTEC SV 60 Piezoelectric Metering Valve with Slide Technology, Type SV with Control Unit Type CON SV	EN GE	7135378A 7135350A	MA	(317102) or (317107)	
	Micrometering System PICODOSTEC DS100/DS200 Micrometering Valve Type DV with Control Unit Type CON	FR GE	7156293A 7156292A	MA	(317102) or (317107)	
	DCON Aixtron	EN GE	7156295A 7156294A	MA	(317102) or (317107)	
	Cleaning Instructions How to Clean PICO Piezoelectric Metering Valves	EN FR GE	7156297A 7156298A 7156296A	MA	(317102) or (317107)	
	Manual for Pressure Tank DT-FP	EN GE	7156502A 7156501A	MA	(317102) or (317107)	
	Operating Manual Pulse Generator DPA2 ⁺² for Triggering the Control Unit Type CON/DCON	EN GE	7156508A 7156509A	MA	(317102) or (317107)	

F-8 -1

Nordson Puffe Hot Melt (sorted by Product Title)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Extruder EX 03-PS01	CZ	7119187A	MA	(317102) or (317107)	GE source - no P/N
	Heated Hoses Serie PC	CZ	7119188A	MA	(317102) or (317107)	GE source - no P/N
	Pressure Sensor	CZ	7119189A	MA	(317102) or (317107)	GE source - no P/N
	Bead Application Head AN 26 T	CZ	7119190A	MA	(317102) or (317107)	GE source - no P/N

F-9 -1

Slautterback (sorted by Product Title)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Autotech AT 8	Hotmelt Unit	DU FR GE	458376A 447615A 458377A	MA	(317102) or (317107)	EN - 19600-221D
Autotech AT 15	Hotmelt Unit	DU FR GE IT PL PO SP	412898C 412674C 412681C 412761C 397251C 464838C 412728C	MA	(317102) or (317107)	EN - 19600-184H (US-version) EN - 19600-216C (European)
Autotech AT 30 / 40 / 60	Melt Unit Series with T500 Temperature Controller	DU FR	458069B 458070B	MA	(317102) or (317107)	EN - 19600-146C
CH22-TR	Pattern Controller	FR	315933A	MA	(317102) or (317107)	EN - 19600-113B
Data Beam Sensor	Controller	DU FR GE IT SP	290904A 290905A 290906A 290907A 290908A	MA	(317102) or (317107)	EN - 19600 124A
DC Driver	DC Driver - Single Output	FR GE IT SP	405047F 405010F 405104F 405057F	MA	(317102) or (317107)	EN - 19600-76F
DX5 / DX3A	Temperature Controllers	JA	464867A	MA	(317102) or (317107)	EN - 19600-210A
E100XT	Applicator	DU FR GE IT SP	290713G 292890G 292891G 290808G 290809G	MA	(317102) or (317107)	EN - 19600-17XTH

F-9 -2

Slautterback (sorted by Product Title)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
E900	Modular Applicators 3-Pin Coil	FR GE IT	405055A 405009A 405096A	MA	(317102) or (317107)	EN - 19600-154A
ET2-TR	Pattern Controller	DU FR GE IT SP	290886B 290887B 290817B 290888B 290889B	MA	(317102) or (317107)	EN - 19600-131B
ET4	Pattern Controller	DU GE IT SP	290855A 290857A 290858A 290859A	MA	(317102) or (317107)	EN - 19600-129A (latest EN revision - 19600-129C)
ET4-T	Pattern Controller	DU GE IT SP	315799B 315796B 315800B 290885B	MA	(317102) or (317107)	EN - 19600-130B (latest EN revision -19600-130C)
HC/HS/OP/ 501 Style	Heated Supply Hoses (Automatic Application)	DU FR GE IT SP	290712 I 290767 I 290768 I 290769 I 290770 I	MA	(317102) or (317107)	EN - 19600-24I (latest EN revision - 19600-24K)
HD2	Head Driver	DU FR GE IT SP	290890A* 292841A 290891A* 292842A 290892A* 292843A 290893A 290894A	MA	(317102) or (317107)	EN - 19600-126A * = old version
HD2A	Head Driver	DU FR GE IT SP	290895A 290896A 292844A 290897A 290898A	MA	(317102) or (317107)	EN - 19600-127A

F-9 -3

Slautterback (sorted by Product Title)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
HD4A	Head Driver	DU FR GE IT SP	290899A 290900A 290901A* 292845A 290902A 290903A	MA	(317102) or (317107)	EN - 19600-128A * = old version
JR1	Hotmelt System	DU FR SP	413089B 413090B 464965B	MA	(317102) or (317107)	EN - 19600-191B
JR5	Hot Melt Applicator	DA DU FI FR GE NO SP SW	407416D 407491D 407440D 407417D 407421D 407419D 407450D 407439D	OP	(317102) or (317107)	EN - 19600-195D
JR5 / JR6 / JR7 / JR8	JR Series Hotmelt System Product Manual	DA DU FI FR GE IT NO SP SW	409070A* 409071A 409072B 409073A 409074A 413070A 409075A* 409076A 409077A*	MA	(317102) or (317107)	EN - 19600-190-2A * = not yet translated
KB 10/20E/ T150	Melt Unit	DU FR GE IT SP	315781C 315782C 315783C 315784C 315785C	MA	(317102) or (317107)	EN - 19600-144A

F-9 -4

Slautterback (sorted by Product Title)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
KB 10/20E/ Thermostat	Melt Unit	DU FR GE IT SP	315776A 315778A 315779A 315780A 315777A	MA	(317102) or (317107)	EN - 19600-143A
KS 10/20E/ T150	Melt Unit	DA DU FI FR GE IT NO SP SW	317066C 315770C 315821C 315772C 315773C 315774C 315809C 315775C 315794C	MA	(317102) or (317107)	EN - 19600-145A
L4	Handgun	DA DU FI FR GE IT NO SP SW	315943C 292951C 292952C 292953C 292954C 292955C 315810C 292956C 292957C	MA	(317102) or (317107)	EN - 19600-110B
L5	Handgun - Manual Extrusion and Swirl Applicator	DU FR GE IT SP	458059E 403073C 403079C 403089C 403091C	MA	(317102) or (317107)	EN - 19600-147E
LR 10	Low Profile Hot Melt Unit	JA	464877B*	MA	(317102) or (317107)	EN - 19600-158B * = available at Nordson K.K.

F-9 -5

Slautterback (sorted by Product Title)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LS 10/20E	Melt Unit	DU FI FR GE IT SP SW	292880A 292945A 292881A 292882A 292883A 292884A 292946A	MA	(317102) or (317107)	EN - 19600-137A No longer distributed
Mini Squirt II	Hot Melt Adhesive Applicator	FR IT SP	403087F 403088F 403090F	MA	(317102) or (317107)	EN - 19600-03MSII - revision F
MiniSquirt III	MiniSquirt III Hand-held Applicator	PL PO	7179518D02 7135170D	MA	(317102) or (317107)	EN - 1018551D02 - Issued 12/15 Date of Polish translation 01/09 Obsolete!
SW4	Swirl Handgun	FR GE	407493A 315930A	MA	(317102) or (317107)	EN - 19600-125A
T150	Temperature Controller	DU FR GE IT SP	290824C 290721C 290722C 290723C 290724C	MA	(317102) or (317107)	EN - 19600-116C
T500	Temperature Controller	DU FR GE IT SP	290916B 283048B 290917B 283050B 283049B	MA	(317102) or (317107)	
T1000	Temperature Controller	DU FR GE IT SP	290918 I 283045 I 290919 I 283047 I 283046 I	MA	(317102) or (317107)	No longer marketed in EU

Issued by Technical Documentation Local Languages (TDLL) Department, Nordson Engineering, Lüneburg
Status : July 2017

F-10 -1

Watlow (sorted by Product Title)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
TDM4	Thermo-Ducer	EN GE	no P/N 292959	MA	(317102) or (317107)	

