

*Technical Documentation Local Languages (TDLL)*

---

***Documentation List  
December 2019***

*Issued by Nordson Engineering, Lüneburg*

---



# Table of Contents

<b>Introduction</b> .....	<b>1</b>
<b>Contents</b> .....	<b>1</b>
<b>Abbreviations and Header Line</b> .....	<b>3</b>
<b>Ordering Documents</b> .....	<b>4</b>
<b>Information &amp; Support</b> .....	<b>6</b>
<b>Central Archive in Lüneburg</b> .....	<b>7</b>
<b>Nordson Engineering Hot Melt Products (sorted by Model)</b>	<b>A-1 - 1</b>
Blue Series Melters - DuraBlue .....	A-1 - 1
Blue Series Melters - VersaBlue .....	A-1 - 4
Bulk Melters - BM 20 Series .....	A-2 - 1
Bulk Melters - BM 200 Series .....	A-2 - 5
Bulk Melters - BM 5xxx Lueneburg Rebuilt Units .....	A-2 - 7
Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum	A-2 - 9
MC/ (PUR) Units .....	A-3 - 5
MX Units .....	A-4 - 1
Auxiliary Systems .....	A-5 - 1
Applicators (Guns) .....	A-6 - 1
Systems - Automotive .....	A-7 - 1
Systems - Bookbinding .....	A-7 - 2
Systems - Gasketing .....	A-7 - 7
Systems - Moulding .....	A-7 - 8
Coating Units .....	A-8 - 1
Other Hot Melt Units .....	A-9 - 1
Drives .....	A-10 - 1
Mechanical & Hydraulic Components .....	A-11 - 1
Pneumatic Components .....	A-12 - 1
Electrical & Electronic Components .....	A-13 - 1
Level Controls .....	A-14 - 1
Miscellaneous .....	A-15 - 1

<b>Nordson US Hot Melt Products (sorted by Model) .....</b>	<b>B-1 - 1</b>
Blue Series Melters .....	B-1 - 1
Series 3000V (Vista) .....	B-2 - 1
Series 2000 / Series 3000 / Series 5000 / Series 6000 .....	B-3 - 8
Other Melters and Diverse Equipment, Hoses .....	B-4 - 1
Auxiliary Systems .....	B-5 - 1
Applicators (Guns) .....	B-6 - 1
Foam .....	B-7 - 1
<b>Nordson Finishing Products (sorted by Product Title) .....</b>	<b>C-1 - 1</b>
Automotive / Container / Electronics / Liquid .....	C-1 - 1
U.S. Powder .....	C-2 - 1
U.K. / Europe Powder .....	C-3 - 9
<b>Nordson UV Products (sorted by Product Title) .....</b>	<b>D-1-1</b>
<b>Nordson Benelux Products ( former Walcom ) (sorted by Model) .....</b>	<b>E-1-1</b>
<b>Paper and Paperboard Converting .....</b>	<b>E-1-1</b>
<b>Asymtek (sorted by Product Title) .....</b>	<b>F-1 -1</b>
<b>EFD (sorted by Product Title) .....</b>	<b>F-2 -1</b>
<b>JM Laboratories (sorted by Product Title) .....</b>	<b>F-3 -1</b>
<b>March Plasma (sorted by Product Title) .....</b>	<b>F-4 -1</b>
<b>Mountaingate (sorted by Product Title) .....</b>	<b>F-5 -1</b>
<b>Nordson Sealant Equipment (sorted by Product Title) .....</b>	<b>F-6 -1</b>
<b>PICODOSTEC (sorted by Product Title) .....</b>	<b>F-7-1</b>
<b>Nordson Puffe Hot Melt (sorted by Product Title) .....</b>	<b>F-8 -1</b>
<b>Slautterback (sorted by Product Title) .....</b>	<b>F-9 -1</b>
<b>Watlow (sorted by Product Title) .....</b>	<b>F-10 -1</b>

---

# Documentation List

## Introduction

The Documentation List is updated and distributed monthly. It details translated manuals, instructions and operator's cards created, updated, and/or formatted in Nordson Engineering in Lüneburg.

## Contents

The Documentation List is divided as follows:

**Part A** Nordson Engineering Hot Melt Products  
(former Meltex), refer to page 2 for details

**Part B** Nordson US Hot Melt Products  
refer to page 2 for details

**Part C** Nordson Finishing Products  
refer to page 2 for details

**Part D** Nordson UV (U.K. and U.S.) Products

**Part E** Paper and Paperboard Converting  
Nordson Benelux Products (former Walcom)

**Part F**

1. Asymtek
2. EFD
3. JM Laboratories
4. March Plasma
5. Mountaingate
6. NSE
7. PICODOSTEC
8. Nordson Puffe Hot Melt
9. Slutterback
10. Watlow

## Contents *(contd.)*

### **Part A** Nordson Engineering Hot Melt Products

1. Blue Series Melters
  - DuraBlue
  - VersaBlue
2. Bulk Melters
  - BM 20, BM 200 Series
  - BM 5xxx Lueneburg Rebuilt Units
  - DG / DuraDrum / DuraPail
3. MC Units
4. MX Units
5. Auxiliary Systems, e.g. Pattern Ctrl, Refill, Temperature Ctrl, Timer, Verification
6. Applicators/ Guns
7. Systems -
  - Automotive, Bookbinding, Gasketing, Moulding
8. Coating Units
9. Other Hot Melt Units
10. Drives
11. Mechanical & Hydraulic Components
12. Pneumatic Components
13. Electrical & Electronic Components
14. Level Controls
15. Miscellaneous

### **Part B** Nordson US Hot Melt Products

1. Blue Series Melters
2. Series 3000V (Vista)
3. Series 2000 / Series 3000 / Series 5000 / Series 6000
4. Other Melters and
  - Diverse Equipment, Hoses
5. Auxiliary Systems, e.g. Pattern Ctrl, Refill, Temperature Ctrl, Timer, Verification
6. Applicators/ Guns
7. FoamMelt & FoamMix
8. Bulk Melters, older BM 5xxx Series

### **Part C** Nordson Finishing Products

1. Automotive / Container / Electronics / Liquid
2. U.S. Powder
3. U.K. Powder

## Abbreviations and Header Line

### Document Type:

- IN	Instructions
- MA	Manual
- OP	Operator's Card
- PA	Parts List
- PI	Product Information Sheet
- SA	Safety Section
- SU	Supplement

### Languages:

- BU	Bulgarian
- CH	Chinese
- CR	Croatian
- CZ	Czech
- DA	Danish
- DU	Dutch
- EN	English
- ES	Estonian
- FI	Finnish
- FR	French
- GE	German
- GR	Greek
- HU	Hungarian
- IT	Italian
- JA	Japanese
- KO	Korean
- LA	Latvian
- LI	Lithuanian
- NO	Norwegian
- PL	Polish
- PO	Portuguese
- RO	Romanian
- RU	Russian
- SE	Serbian
- SK	Slovak
- SL	Slovenian
- SP	Spanish
- SW	Swedish
- TU	Turkish

### The header line is made up of the following:

- Model	Specific Model name
- Product Title	Full title of document
- Langs.	Languages available (see abbreviations above)
- P/N	Part Number of document
- Type	Document type (see abbreviations above)
- Price Category	Number denoting price per copy
- Notes	Any additional useful information

**NOTES:** All documents within each section are sorted alphabetically according to *Model*. **Exceptions** - Nordson Finishing, JM Laboratories, Nordson UV (Spectral) and Nordson UK/ Europe are sorted according to *Product Title*.

## Ordering Documents

When ordering manual/documentation copies please follow these guidelines. Please note the different product line procedures.

### **ALL Product Lines EXCEPT Nordson Engineering**

These manuals are to be ordered at EDC, Maastricht. When creating an order in SAP, use the manual-specific P/N, **not** the Category P/N.

### **Nordson Engineering GmbH (MELTEX) Product Line**

For ordering manuals or system documentation from Nordson Engineering the Category P/Ns should be used as listed below.

In order to allow documentation orders to be properly selected and served, the categories distinguish between media CD-ROM and conventional paper copy in blue binder.

Also AFTER-SALES and ADDITIONAL needs to be distinguished for both of the documentation media.

<b>ADDITIONAL</b>			
<b>P/N</b>	<b>€</b>	<b>Documentation Type</b>	<b>Required Information</b>
7156797	18	Configured Manual on CD-ROM Melter WITHOUT system components	Language
7156798	30	Configured Manual on CD-ROM Melter WITH system components (Hose, Applicator, etc.) or for numerous Systems	Language
<b>AFTER-SALES</b>			
<b>P/N</b>	<b>€</b>	<b>Documentation Type</b>	<b>Required Information</b>
7165316	18	Configured Manual on CD-ROM Melter WITHOUT system components	Language and Serial Number and P/N (of the main component)
7165317	30	Configured Manual on CD-ROM Melter WITH system components (Hose, Applicator, etc.) or for numerous Systems	Language and Serial Number and P/N (of the main component)



<b>ADDITIONAL</b>			
<b>P/N</b>	<b>€</b>	<b>Documentation Type</b>	<b>Required Information</b>
317102	18	Medium Manual typically Applicator, Timer	Language
317103	30	Configured Manual Melter WITHOUT system components	Language
317104	100	Configured Manual Melter WITH system components (Hose, Applicator, etc.)	Language
<b>AFTER-SALES</b>			
<b>P/N</b>	<b>€</b>	<b>Documentation Type</b>	<b>Required Information</b>
317107	18	Medium Manual typically Applicator, Timer	Language and Serial Number and P/N
317106	30	Configured Manual Melter WITHOUT system components	Language and Serial Number and P/N (of the main component)
317105	100	Configured System Manual Melter WITH system components (Hose, Applicator, etc.)	Language and Serial Number and P/N (of the main component)

**NOTES:**

**ADDITIONAL** means: Within a Nordson Engineering GmbH equipment order more copies are requested additional to the ONE documentation CD, which is automatically included in the equipment delivery.

**AFTER-SALES** means: Documentation items which refer to equipment sales orders delivered earlier (typically the need arises because the documentation originally being delivered got lost at the customer site).

For all **AFTER-SALES** orders, regardless whether on CD-ROM or in the conventional form of paper in blue binder, the product/system for which the documentation is requested must be identified (Serial number, P/N, UI, or - if applicable- the original SO#, the language request).

Please write the required information as Position Text into the SAP "Text" field. If that identification is missing the Lue PDE group cannot restore the requested order-specific document compilation.

In both cases, **ADDITIONAL** and **AFTER-SALES**, be careful to request language versions which may not yet exist. Casewise significant translation costs may result and should be clarified **PRIOR** to an order. Do **NOT** use the category P/Ns for requesting translations which do not yet exist, but contact TS dpt. at Lueneburg first in order to get a time & cost quote.

## Information & Support

For translation enquiries (all product lines), information or feedback regarding **Nordson Engineering GmbH** documentation, please contact:

Nordson Engineering GmbH  
Bettina Rösnick (Translation Support)  
Lilienthalstr. 6  
21337 Lüneburg / Germany

Phone: 49-4131-894-260  
Email: [bettina.roesnick@de.nordson.com](mailto:bettina.roesnick@de.nordson.com)

For **all other Product Lines** please contact:

Nordson European Distribution Centre B.V.  
Cindy Kenzeler  
Bergerstraat 10  
6226 BD Maastricht / Netherlands

Phone: 31-43-3526-023  
Fax: 31-43-3626-230  
Email: [cindy.kenzeler@nl.nordson.com](mailto:cindy.kenzeler@nl.nordson.com)

**NOTES:** If you cannot order directly in SAP, please send orders for documentation in writing (fax/email). Please include the following information:

**Product Title, Language, P/N and Quantity required.**

**NOTES:** The listed costs for documentation (on page 4 and 5) are valid for additional copies of existing material. If you order and pay for the translation of a manual etc., you will receive one soft-copy free of charge.

---

## Central Archive in Lüneburg

The central archive for translated documents is in Lüneburg. Therefore, we ask you to give us any information regarding manuals e.g. translation needs, planned products, product changes etc.

In the Technical Documentation Local Languages department (TS) we assign Part Numbers for all translated documents, format them in accordance with the Nordson corporate design and style, archive all documents electronically, coordinate projects with experienced translators, and ensure that all documents are made available for everyone within the Nordson network.

We appreciate any comments and feedback which you may have to offer, so that we can enhance the cooperation between Local Language Support in Lüneburg, and Nordson worldwide.

All details correct at time of release. Liable to future corrections.



# Nordson Engineering Hot Melt Products (sorted by Model)

A-1 - 1

## Blue Series Melters - DuraBlue

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
DuraBlue	Kit-SVC conv. 7186936 (Motor Controller i550 in DuraBlue Melters)	EN GE	7560838_01 7560837_01	IN	(317103) or (317106)	
DuraBlue	DuraBlue Adhesive Melters - Models D25, D25H, D50, D100	CH CR CZ DA DU EN FI FR GE HU IT JA LA NO PL PO RO RU SK SP SW	397882A_1 7580141_11 7119873_11 7105604_11 7105103_11 397056_11 7105105_11 397237_11 397063_11 7105410_11 397238_11 397276C 7146749_11 7105104_11 7119878_11 7105070_11 7580029_11 7105895_11 7192860_11 397247_11 7105068_11	MA	(317103) or (317106)	<b>Product Obsolescence 31.10. 2019</b>  <b>Recommended Replacement Products: Duralue II Adhesive Melters and VersaBlue Melters.</b>
DuraBlue	DuraBlue Adhesive Melters - Models D25, D25H, D50, D100 - Parts List -	EN	7146820_07	PA	(317102) or (317107)	<b>Product Obsolescence 31.10. 2019</b>
DuraBlue	DuraBlue Adhesive Melters - Models D25, D25H, D50, D100 - User's Guide	EN/ FR/ GE/ IT/ SP	7119964B	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>  <b>Product Obsolescence 31.10. 2019</b>

# Nordson Engineering Hot Melt Products (sorted by Model)

A-1 - 2

## Blue Series Melters - DuraBlue

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
DuraBlue	DuraBlue Adhesive Melters - Models D25, D25H, D50, D100 - User's Guide	EN/ DA/ FI/ NO/ SW	7135110B	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b> <b>Product Obsolescence 31.10. 2019</b>
DuraBlue	DuraBlue Adhesive Melters - Models D25, D25H, D50, D100 - User's Guide	EN/ CZ/ HU/ PL/ RU	7135111B	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b> <b>Product Obsolescence 31.10. 2019</b>
DuraBlue	DuraBlue Adhesive Melters - Models D25, D25H, D50, D100 - User's Guide	EN/ DU/ PO/ SL/ SK	7135112B	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b> <b>Product Obsolescence 31.10. 2019</b>
DuraBlue	DuraBlue Adhesive Melters - Models D25, D25H, D50, D100 - User's Guide	EN/CR/ GE/RO	7580030B	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b> <b>Product Obsolescence 31.10. 2019</b>
DuraBlue	DuraBlue Adhesive Melters - Models DK25, DK25H, DK50, DK100	DU EN FR GE IT NO SP SW	7119056_09 7105986_09 7119055_09 7105926_09 7119041_09 7119080_09 7119050_09 7119061D	MA	(317103) or (317106)	<b>Product Obsolescence 31.10 2019</b>
DuraBlue	DuraBlue Adhesive Melters - Models DK25, DK25H, DK50, DK100 - Parts List -	EN	7146844_07	PA	(317102) or (317107)	<b>Product Obsolescence 31.10. 2019</b>
DuraBlue	DuraBlue Adhesive Melter D25H, D50	EN GE	7119512B 7119419B	MA	(317103) or (317106)	<b>Product Obsolescence 31.10. 2019</b>

## Nordson Engineering Hot Melt Products (sorted by Model)

A-1 - 3

### *Blue Series Melters - DuraBlue*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
DuraBlue	DuraBlue Adhesive Melters N-Series - Parts List -	EN	7156101_04	PA	(317102) or (317107)	
DuraBlue	Control Panel Service Kit - P/N 394734	EN/ FR/ GE/ IT/ SP	397411B	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
DuraBlue	Pneumatic Pressure Control Valve Service Kit - P/N 729055	EN/ FR/ GE/ IT/ SP	397871C	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
DuraBlue	Pressure Control Valve ( 5-90 bar Manual ) Accessory Kit - P/N 394795	EN/ FR/ GE/ IT/ SP	397671A	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
DuraBlue	Shaft Seal Service Kits Gerotor Pump - P/N 394768 Shaft Seal Service Kits Gear Pump - P/Ns Diverse	EN/ FR/ GE/ IT/ SP	397325G	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
DuraBlue/ DuraPail/ DuraDrum	Interface Cable - P/N 7109800, 7144759, 7148723, 7149085	CZ EN ES FR GE HU	7146015E 7119092E 7146245D 7593118E 7105852E 7146217E	IN	(317102) or (317107)	
DuraBlue/ DuraPail/ DuraDrum	Interface Cable - P/N 7128700, 7144869, 7148912	EN GE	7135374F 7135356F	IN	(317102) or (317107)	
DuraBlue/ DuraPail/ DuraDrum	Service Kit Contactors P/N 251790, P/N 251791, P/N 251797, P/N 414100, P/N 256703, P/N 291187	EN/ FR/ GE/ IT/ SP	7119470A	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>

A-1 - 4

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Blue Series Melters - VersaBlue*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>VBCM</b>	Electrical Cabinet VBCM	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SK</b> <b>SL</b> <b>SP</b> <b>SW</b> <b>TU</b>	7580143_06 7580092_05 7119277_06 7105553_06 7119434_05 7146259_06 7105524_06 7560552_05 7105529_06 7119095_06 7560381_06 7560553_05 7105596_05 7146492_05 7135299_06 7105534_05 7192925_05	MA	(317102) or (317107)	
<b>VBCM</b>	Kit-SVC conv. 7561998 (Motor Controller i550 in VBCM)	<b>EN</b> <b>GE</b>	7593380_01 7593379_01	IN	(317103) or (317106)	
<b>VBCM</b>	VBCM with IPC Operator Panel	<b>EN</b> <b>GE</b>	7146063A 7135999A	MA	(317102) or (317107)	
<b>VBCM</b>	VBCM with Siemens PLC	<b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b>	7156716A 7156699A 7179739A 7156706A	MA	(317102) or (317107)	
<b>Versa</b>	Engineering Update for Versa Adhesive Melters, Bulk Melters and VBCM	<b>EN</b> <b>GE</b>	7560962_02 7560938_02	MA	(317102) or (317107)	
<b>Versa</b>	Engineering Update IPC4 for Versa Adhesive Melters, Bulk Melters and VTC	<b>EN</b> <b>GE</b>	7580605_01 7580601_01	MA	(317102) or (317107)	



A-1 - 5

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Blue Series Melters - VersaBlue*

<b>Versa</b>	Field Bus on Nordson Melters with IPC	<b>BU</b> <b>CH</b> <b>CR</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SK</b> <b>SL</b> <b>SP</b> <b>SW</b>	7146212_12 7146595_12 7580037_12 7146209_12 7146363_12 7146173_12 7135952_12 7146497_12 7146127_12 7135837_12 7146211_12 7146213_12 7146205_12 7156359F* 7146378_12 7146347_12 7146348_12 7146390_12 7146410_12 7146491_12 7146210_12 7146359_12	MA	(317102) or (317107)	<b>* available at Nordson K.K.</b>
<b>Versa</b>	Kit-SVC conv. 7578171 (Motor Controller i550 in Versa Melters)	<b>EN</b> <b>GE</b>	7580110_01 7580105_01	IN	(317103) or (317106)	
<b>Versa</b>	Kit-SVC conv. 7561537 (Motor Controller i550 in Versa Melters or Bulk Melters)	<b>EN</b> <b>GE</b>	7560961_03 7560943_03	IN	(317103) or (317106)	
<b>Versa</b>	Motor Controller i550	<b>EN</b>	7560839_01	IN	(317102) or (317107)	

A-1 - 6 **Nordson Engineering Hot Melt Products (sorted by Model)**

**Blue Series Melters - VersaBlue**

<b>VersaBlue</b>	VersaBlue Adhesive Melters Model VA and VT	<b>BU</b> <b>CH</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>LA</b> <b>LI</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SL</b> <b>SP</b> <b>SW</b>	7135678_11 397881_14 7105310_14 397599_14 397537_14 213828_14 7105054_13 397049_14 213807_14 7105434_14 7105166_14 397051_14 397277_12 7179489_11 7169612_12 397803_11 7105203_14 397514_14 7169182_11 7105167_12 7105671_11 397023_14 397552_14	MA	(317103) or (317106)	
<b>VersaBlue</b>	VersaBlue Adhesive Melters Model VA and VT - Parts List -	<b>EN</b>	7135025_10	PA	(317102) or (317107)	

A-1 - 7

## Nordson Engineering Hot Melt Products (sorted by Model)

### Blue Series Melters - VersaBlue

<b>VersaBlue/ VersaBlue Plus</b>	VersaBlue and VersaBlue Plus Melters in the Series N Types VB, VC, VD, VE, VW, VX, VY, VZ	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>KO</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SK</b> <b>SL</b> <b>SP</b> <b>SW</b> <b>TU</b>	7119645_09 7105811_09 7105446_09 7105144_09 7105557G 7105190_09 7105011_09 7119982_09 7105619_09 7105157_09 7105964G 7135197F 7105859_09 7119136_09 7105830_09 7119132_09 7105389_09 7146490_09 7105257_09 7105216_09 7119674_09	MA	(317103) or (317106)	
<b>VersaBlue/ VersaBlue Plus</b>	VersaBlue and VersaBlue Plus Adhesive Melters Serie N Model VB, VC, VD, VE, VW, VX, VY, VZ - Parts List -	<b>EN</b>	7119994_09	PA	(317102) or (317107)	
<b>VersaBlue Plus</b>	Engineering Update for Melter Type VersaBlue Plus with TruFlow Capability	<b>EN</b> <b>GE</b>	7192909_01 7192901_01	MA	(317103) or (317106)	
<b>VersaBlue</b>	VersaBlue Adhesive Melters Serie N Model VD, VE, VY, VZ with Siemens Controller	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b>	7146505A 7146181A 7146228A 7146149A 7580559A 7146425A	MA	(317103) or (317106)	
<b>VersaBlue</b>	VersaBlue Adhesive Melters Serie N Model VD, VE, VY, VZ with Siemens Controller - Parts List -	<b>EN</b>	7146314_07	PA	(317103) or (317106)	

A-1 - 8

## Nordson Engineering Hot Melt Products (sorted by Model)

### Blue Series Melters - VersaBlue

<b>VersaBlue</b>	VersaBlue Adhesive Melters Serie N Model VD, VE, VY, VZ with Allen Bradley Control System	<b>CZ</b> <b>EN</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7169873_04 7105491_04 7105436_04 7156913_04 7169323_04 7146695_04 7135483_04 7179533_04	MA	(317103) or (317106)	
<b>VersaBlue</b>	VersaBlue Adhesive Melters Serie N Model VD, VE, VY, VZ with Allen Bradley Control System - Parts List -	<b>EN</b>	7135190_08	PA	(317102) or (317107)	
<b>VersaBlue</b>	VersaBlue Melter Series N without IPC (Title version A: VersaBlue Adhesive Melters N, Model VW 012)	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>RU</b>	7156671C 7135916C 7135139A 7135101C 7135934C 7156040C	MA	(317103) or (317106)	
<b>VersaBlue</b>	VersaBlue Melter Series N without IPC - Parts List -	<b>EN</b>	7156021_04	PA	(317103) or (317106)	
<b>VersaBlue</b>	VersaBlue Adhesive Melters VB C - Model SC	<b>DA</b> <b>DU</b> <b>EN</b> <b>GE</b> <b>FR</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>TU</b>	7169347B 7135148B 7135193_04 7135066_04 7135556B 7135161_03 7192876_03 7192887_03 7146385_03 7560655_04	MA	(317103) or (317106)	
<b>VersaBlue</b>	VersaBlue Adhesive Melters VB C - Model SC - Parts List -	<b>EN</b>	7169235_03	PA	(317102) or (317107)	

A-1 - 9

## Nordson Engineering Hot Melt Products (sorted by Model)

### Blue Series Melters - VersaBlue

<b>VersaBlue</b>	VersaBlue Adhesive Melters VBC with Allen Bradley Controller	<b>CZ</b> <b>EN</b> <b>GE</b> <b>IT</b>	7169874A 7135475A 7135315A 7560955A	MA	(317103) or (317106)	
<b>VersaBlue</b>	VersaBlue Adhesive Melters Model VB C with Industrial PC	<b>CH</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>GE</b> <b>IT</b> <b>SP</b> <b>SW</b>	7560881_04 7169289C 7135228_04 7146402B 7119461_04 7135980B 7135358B 7169165C	MA	(317103) or (317106)	
<b>VersaBlue</b>	VersaBlue Adhesive Melters VB C with Industrial PC - Parts List -	<b>EN</b>	7135002_05	PA	(317102) or (317107)	
<b>VersaBlue</b>	VersaBlue Adhesive Melters VB C with Siemens Controller	<b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>RU</b> <b>SW</b>	7135049_02 7146344A 7135000_02 7146665A 7146675A 7146279A	MA	(317103) or (317106)	
<b>VersaBlue</b>	VersaBlue Adhesive Melters VBC with Siemens Controller - Parts List -	<b>EN</b>	7135001A	PA	(317102) or (317107)	
<b>VersaBlue</b>	Field Bus on VB-C Melters with IFC	<b>GE</b>	7580665_01	MA	(317102) or (317107)	
<b>VersaBlue</b>	VersaBlue Adhesive Melters VBN with Allen Bradley Controller	<b>EN</b> <b>GE</b> <b>IT</b> <b>RU</b> <b>SP</b>	7119549D* 7119415C 7169324D* 7146694C 7119580D*	MA	(317103) or (317106)	<b>* = New Sec. 4 OP from 1098104A !</b>
<b>VersaBlue</b>	VersaBlue Adhesive Melters VBN with Allen Bradley Controller - Parts List -	<b>EN</b>	7146018A	PA	(317102) or (317107)	

A-1 - 10

## Nordson Engineering Hot Melt Products (sorted by Model)

### Blue Series Melters - VersaBlue

<b>VersaBlue</b>	VersaBlue Adhesive Melters VBN with Siemens Controller	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>SW</b>	7146650A 7135528A 7156290A 7135044A 7146661A 7146426A 7135683A	MA	(317103) or (317106)	
<b>VersaBlue</b>	VersaBlue Adhesive Melters VBN with Siemens Controller - Parts List -	<b>EN</b>	7135135A	PA	(317102) or (317107)	
<b>VersaBlue</b>	VersaBlue Adhesive Melters VBN without Control System	<b>EN</b> <b>FR</b> <b>GE</b>	7146386A 7146639A 7146349A	MA	(317103) or (317106)	
<b>VersaBlue</b>	VersaBlue Adhesive Melters VBN without Control System - Parts List -	<b>EN</b>	7146350A	PA	(317102) or (317107)	
<b>VersaBlue</b>	VersaBlue Adhesive Melters VW050 Lotion	<b>EN</b> <b>GE</b> <b>IT</b>	7169157B 7156589B 7156651A	MA	(317102) or (317107)	
<b>VersaBlue</b>	VersaBlue LOTION Melters Serie N - Parts List -	<b>EN</b>	7156205_10	PA	(317102) or (317107)	
<b>VersaBlue</b>	VersaBlue Adhesive Melters VZ025 E with Siemens Controller	<b>CH</b> <b>EN</b> <b>GE</b> <b>RU</b>	7156663A 7156662A 7156498A 7156659A	MA	(317102) or (317107)	
<b>VersaBlue</b>	VersaBlue Adhesive Melters Twin Tank	<b>EN</b> <b>GE</b> <b>IT</b>	7169240A 7169151A 7169234A	MA	(317102) or (317107)	
<b>VersaBlue</b>	VersaBlue Melters Safety	<b>EN/BU/</b> <b>GE/RO/</b> <b>TU</b>	7156010C	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>

A-1 - 11

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Blue Series Melters - VersaBlue*

<b>VersaBlue</b>	VersaBlue Melters Safety	<b>EN/ CH/JA</b>	7119555C	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	VersaBlue Melters Safety	<b>EN/CR/ ES/LA/ LI</b>	7179537C	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	VersaBlue Melters Safety	<b>EN/CZ/ HU/PL/ RU</b>	7119556C	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	VersaBlue Melters Safety	<b>EN/DA/ FI/NO/ SW</b>	7119564C	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	VersaBlue Melters Safety	<b>EN/DU/ PO/SL/ SK</b>	7119565C	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	VersaBlue Melters Safety	<b>EN/FR/ GE/IT/ SP</b>	7105468C	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	VersaBlue Melters User's Guide	<b>EN/BU/ GE/RO/ TU</b>	7156009C	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	VersaBlue Melters User's Guide	<b>EN/ CH/JA</b>	7105978C	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	VersaBlue Melters User's Guide	<b>EN/CR/ ES/LA/ LI</b>	7179536C	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	VersaBlue Melters User's Guide	<b>EN/CZ/ HU/PL/ RU</b>	7119200C	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	VersaBlue Melters User's Guide	<b>EN/DA/ FI/NO/ SW</b>	7119199C	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>

A-1 - 12

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Blue Series Melters - VersaBlue*

<b>VersaBlue</b>	VersaBlue Melters User's Guide	<b>EN/DU/ PO/SL/ SK</b>	7119566C	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	VersaBlue Melters User's Guide	<b>EN/FR/ GE/IT/ SP</b>	7105284C	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	VersaBlue Adhesive Melters - Safety and User's Guide	<b>GE GR</b>	7560164_01 7560845_01	OP	(317102) or (317107)	
<b>VersaBlue</b>	Accessory Kit, Lid VB/DB Feed System - P/N 7116463	<b>EN/ FR/ GE/ IT/ SP</b>	7119696A	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	Adapter cable - P/N 398681B, 7137287, 7153276, 7165446, 7170178	<b>EN/ GE</b>	7105339H	IN	(317102) or (317107)	<b>Bilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	Adapter cable - P/N 7137425, ..., 7197447	<b>EN/ GE</b>	7135376_10	IN	(317102) or (317107)	<b>Bilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	Adapter Cable for Handgun Operation - P/N 398564	<b>EN/ FR/ GE/ IT/ SP</b>	7105022A	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	Bypass Plate Service Kit - P/N 394594 or 394595 (HT)	<b>EN/ FR/ GE/ IT/ SP</b>	397160A	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>Versablue</b>	Bypass Plate Service Kit - P/N 7104646	<b>EN/ FR/ GE/ IT/ SP</b>	7105134A	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	Filter Service Kits - (HT: High Temperature)	<b>EN/ GE</b>	397158_03	IN	(317102) or (317107)	<b>Bilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	Heat Exchanger Parts Kit - P/N 7116737	<b>EN/ FR/ GE/ IT/ SP</b>	7119462A	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>



A-1 - 13

## Nordson Engineering Hot Melt Products (sorted by Model)

### Blue Series Melters - VersaBlue

<b>VersaBlue</b>	Inert Gas Kit - P/N 394770	<b>EN/ FR/ GE/ IT/ SP</b>	7105050_02	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	IPC Console Service Kit - P/N 729865	<b>EN/ FR/ GE/ IT/ SP</b>	397972A	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	Level Kits for VersaBlue	<b>EN/FR/ GE</b>	7105320_07	IN	(317102) or (317107)	<b>Trilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	Light Tower Service Kit - P/N 394794	<b>EN/ FR/ GE/ IT/ SP</b>	397313A	IN	Non- Saleable	<b>Multilingual document, therefore one P/N only -&gt; Cross-reference to manual !</b>
<b>VersaBlue</b>	Pressure Control Valve (pneu.) Service Kit - P/N 394602 or 394603 (HT)	<b>EN/ FR/ GE/ IT/ SP</b>	397163A	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	Pressure Control Valve Service Kit - P/N 394600 or P/N 394601 (HT)	<b>EN/ FR/ GE/ IT/ SP</b>	397162A	IN	Non- Saleable	<b>Multilingual document, therefore one P/N only -&gt; Cross-reference to manual !</b>
<b>VersaBlue</b>	Pump Service Kit - P/N 394589 or P/N 394596	<b>EN/ FR/ GE/ IT/ SP</b>	397157A	IN	Non- Saleable	<b>Multilingual document, therefore one P/N only -&gt; Cross-reference to manual !</b>
<b>VersaBlue</b>	Retrofit Kit Coupling Monitoring - P/N 7104102	<b>EN/ FR/ GE/ IT/ SP</b>	7105936B	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	RTD Sensor (Ni 120) Service Kit - P/N 394597	<b>EN/ FR/ GE/ IT/ SP</b>	397312A	IN	Non- Saleable	<b>Multilingual document, therefore one P/N only -&gt; Cross-reference to manual !</b>
<b>VersaBlue</b>	Safety Valve Service Kit - P/N 394592 or P/N 394593 (HT)	<b>EN/ FR/ GE/ IT/ SP</b>	397159A	IN	Non- Saleable	<b>Multilingual document, therefore one P/N only -&gt; Cross-reference to manual !</b>
<b>VersaBlue</b>	Software Upgrade Kit Vers. ≤ 1.00.000 to > 1.00.000 - P/N 7104397	<b>EN/ FR/ GE/ IT/ SP</b>	7105044A	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>

A-1 - 14

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Blue Series Melters - VersaBlue*

<b>VersaBlue</b>	Spare Parts Kit - High Temperature (HT) Thermostat - P/N 1035766	<b>EN/ FR/ GE/ IT/ SP</b>	7105958A	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	Tank Isolation Valve Service Kit - P/N 394598 or P/N 394599 (HT)	<b>EN/ FR/ GE/ IT/ SP</b>	397161A	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaBlue</b>	Upgrade Instructions (Upgrade to Software Version 3.22.014)	<b>EN</b>	7105948E	IN	(317102) or (317107)	
<b>VersaBlue</b>	Engineering Update IPC III (Industrial PC Generation III, Software Version 6.00.000)	<b>EN GE</b>	7169185A 7169172A	MA	(317102) or (317107)	
<b>VersaBlue</b>	Installation and Operation via the IPC Webserver	<b>EN GE</b>	7192668_02 7192664_02	IN	(317102) or (317107)	
<b>VersaBlue Connect</b>	VersaBlue Connect Adhesive Melters	<b>EN GE</b>	7580624_01 7580614_01	MA	(317103) or (317106)	<b>Preliminary Version !</b>
<b>VTC</b>	Electrical Cabinet VTC	<b>CZ EN FI GE IT SW</b>	7169993_02 7169994_02 7169996_02 7169462_02 7179217_02 7192640_02	MA	(317102) or (317107)	

A-2 - 1

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Bulk Melters - BM 20 Series*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>BM 20</b>	Bulk Melters BM 20 with Gear/Gerotor Pump for 20l Drums	<b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	458448D 458421D 458372D 458397D 458327D 458423D 464856C* 458471D 464859D 458407D 458464D	MA	(317102) or (317107)	<b>End of Support 10/2016</b>          <b>* available at Nordson K.K.</b>
<b>BM 20</b>	BM 20 with Gear/Gerotor Pump - Parts List -	<b>EN</b>	464845D	PA	(317102) or (317107)	<b>End of Support 10/2016</b>
<b>BM 20 EASY</b>	Bulk Melters BM 20 with Gear Pump / Gerotor Pump - EASY Pneumatics -	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SK</b> <b>SP</b> <b>SW</b>	7105856E 397267E 397165E 397166E 7119862E 397173E 397086E 397184E 397227E 7105209E 397177E 7135765E 7119037E 397222E 397230E	MA	(317102) or (317107)	<b>End of Support 10/2016</b>
<b>BM 20 EASY</b>	Bulk Melters BM 20 with Gear/Gerotor Pump - EASY pneumatic - - Parts List -	<b>EN</b>	213959K	PA	(317102) or (317107)	<b>End of Support 10/2016</b>

A-2 - 2

## Nordson Engineering Hot Melt Products (sorted by Model)

### Bulk Melters - BM 20 Series

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>BM 20</b>	Bulk Melters BM 20 with Piston Pump for 20l Drums	<b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	447688E 458499E 458478E 458493E 458284E 458494E 464862C* 464723E 213165E 447603E 447651E	MA	(317102) or (317107)	<b>End of Support 10/2016</b>          <b>* available at Nordson K.K.</b>
<b>BM 20</b>	BM 20 with Piston Pump - Parts List -	<b>EN</b>	464846A	PA	(317102) or (317107)	<b>End of Support 10/2016</b>
<b>BM 20 EASY</b>	Bulk Melters BM 20 with Piston Pump - EASY Pneumatics -	<b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	397538A* 397539E 397540E 7135230E 397541E 397087E 397542E 397543E 397544E 397545E 397546E	MA	(317102) or (317107)	<b>* = not yet translated</b> <b>End of Support 10/2016</b>
<b>BM 20 EASY</b>	Bulk Melter Series BM 20 with Piston Pump - EASY pneumatic - -Parts List -	<b>EN</b>	397436H	MA	(317102) or (317107)	<b>End of Support 10/2016</b>
<b>BM 20 / BM 200</b>	Bulk Melters BM 20 / BM 200	<b>EN</b> <b>GE</b> <b>FR</b> <b>IT</b> <b>SL</b> <b>SP</b>	7119313B 7119275B 7119314B 7119315B 7135026B 7119316B	OP	(317102) or (317107)	<b>End of Support 10/2016</b>

A-2 - 3 **Nordson Engineering Hot Melt Products (sorted by Model)**

**Bulk Melters - BM 20 Series**

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>BM 20 / BM 200</b>	Control Unit Change-Over for Bulk Melters in the Series BM 20/BM 200	<b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	458475C 458454C 458442C 447748C 458439C 458282C 458469C 464864C* 458459C 213198C 458457C 458450C	MA	(317102) or (317107)	<b>End of Support 10/2016</b>          <b>* available at Nordson K.K.</b>
<b>BM 20 / BM 200</b>	Control Unit Change-Over II for Bulk Melters BM 20/BM 200	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	397910A 397891A 397886A 397875A 397904A 397929A 397906A 397884A 397912A	MA	(317102) or (317107)	<b>End of Support 10/2016</b>
<b>BM 20 / BM 200</b>	Pressure Control for Bulk Melters Series BM 20 / BM200	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PO</b> <b>SP</b> <b>SW</b>	458455A 458356A 458406A 458283A 458474A 464863A* 213171A 447711A 458466A	MA	(317102) or (317107)	<b>End of Support 10/2016</b>          <b>* available at Nordson K.K.</b>

A-2 - 4

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Bulk Melters - BM 20 Series*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>BM 20 / BM 200</b>	Aeration, Pneumatic Assembly P/N 394049 for Bulk Melters BM 20 with Gear/Gerotor Pump Assembly P/N 729174 for Bulk Melters BM 20 / BM 200 with Piston Pump Assembly P/N 394575 for Bulk Melters BM 200 with Gear/Gerotor Pump	<b>EN GE</b>	397039C	IN	(317102) or (317107)	<b><i>Bilingual</i> document, therefore one P/N only End of Support 10/2016</b>
<b>BM 20 / BM 200</b>	Retrofit Kit Bulk Melters BM 20 / BM 200	<b>EN/GE/ FR/SP</b>	213146A	IN	(317102) or (317107)	<b><i>Multilingual</i> document, therefore one P/N only End of Support 10/2016</b>
<b>BM 20 / BM 200</b>	Replacing Aeration Valve on Bulk Melters BM 20, BM 200	<b>EN</b>	213774A	IN	(317102) or (317107)	<b>End of Support 10/2016</b>
<b>BM 20 / BM 200 EASY</b>	Instructions for retrofit Kit 729121	<b>EN/GE/ FR/IT/ SP</b>	397598A	IN	(317102) or (317107)	<b><i>Multilingual</i> document, therefore one P/N only End of Support 10/2016</b>

A-2 - 5

## Nordson Engineering Hot Melt Products (sorted by Model)

### Bulk Melters - BM 200 Series

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>BM 200</b>	Bulk Melters BM 200 with Gear/Gerotor Pump for 200 l Drums	<b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	213403C 213030C 464958C 213027C 447681C 464956C 213033C 213166C 213032C 213031C	MA	(317102) or (317107)	<b>End of Support 10/2016</b>
<b>BM 200</b>	BM 200 with Gear Pump - Parts List -	<b>EN</b>	213003_06	PA	(317102) or (317107)	<b>End of Support 10/2016</b>
<b>BM 200 EASY</b>	Bulk Melters BM 200 with Gear Pump - EASY Pneumatics -	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7119700E 397268E 397212E 397189E 397858E 397220E 397084E 397195E 397248E 7146329E 397244E 7135691E 397233E 397260E	MA	(317102) or (317107)	<b>End of Support 10/2016</b>
<b>BM 200 EASY</b>	Bulk Melters BM 200 with Gear Pump - EASY-pneumatic - - Parts List -	<b>EN</b>	397176J	PA	(317102) or (317107)	<b>End of Support 10/2016</b>

A-2 - 6

## Nordson Engineering Hot Melt Products (sorted by Model)

### Bulk Melters - BM 200 Series

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>BM 200</b>	Bulk Melter BM 200 with Piston Pump for 200l Drums	<b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	213058B 464952B 464937B 464936B 447682B 464931B 464964B 213164B 464940B 213006B	MA	(317102) or (317107)	<b>End of Support 10/2016</b>
<b>BM 200</b>	BM 200 with Piston Pump - Parts List -	<b>EN</b>	213004B	PA	(317102) or (317107)	<b>End of Support 10/2016</b>
<b>BM 200 EASY</b>	Bulk Melters BM 200 with Piston Pump - EASY Pneumatics -	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>SP</b> <b>SW</b>	7105110E 397440E 397270E 397249E 397271E 397085E 397299E 397300E 7119248E 397269E 397273E 397275E	MA	(317102) or (317107)	<b>End of Support 10/2016</b>
<b>BM 200 EASY</b>	Bulk Melters BM 200 with Piston Pump - EASY-pneumatic - - Parts List -	<b>EN</b>	397437I	PA	(317102) or (317107)	<b>End of Support 10/2016</b>



A-2 - 7

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Bulk Melters - BM 5xxx Lueneburg Rebuilt Units*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>BM 505 PC</b>	Bulk Melter BM 505 PC	<b>EN GE</b>	284119 284067	MA	(317104) or (317105)	<b>Meltex</b>
<b>BM 505 PC/ BM 506 PC/ BM 5506 PC/ BM 5530 PC/ BM 5540 PC/ BM 551 PC/ BM 5550 PC/ BM 5551 PC</b>	Drum Melter BM 505 PC / BM 506 PC BM 5506 PC / BM 5530 PC BM 5540 PC / BM 551 PC BM 5550 PC / BM 5551 PC	<b>DA DU FI FR IT PO SP SW</b>	290860A 290861A 290863A 290864A 290865A 290866A 290867A 290868A	IN	(317102) or (317107)	<b>Meltex</b>
<b>BM 506 PC</b>	Bulk Melter BM 506 PC	<b>EN GE</b>	269809 267962	MA	(317104) or (317105)	<b>Meltex, when ordering, please state Unit Type and Serial Number</b>
<b>BM 506 PC/ BM 5506 PC/ BM 551 PC/ BM 5551 PC</b>	Bulk Melters BM 506 PC / BM 5506 PC/ BM 551 PC / BM 5551 PC	<b>EN GE PL</b>	269826 269825 213255	OP	(317102) or (317107)	<b>Meltex</b>
<b>BM 551 PC</b>	Bulk Melter BM 551 PC	<b>EN GE</b>	284120 267964	MA	(317104) or (317105)	<b>Meltex, when ordering, please state Unit Type and Serial Number</b>
<b>BM 5506 PC</b>	Bulk Melter BM 5506 PC	<b>EN GE</b>	284043 284113	MA	(317104) or (317105)	<b>Meltex, when ordering, please state Unit Type and Serial Number</b>
<b>BM 5530 PC/ BM 5540 PC</b>	BM 5530 PC / BM 5540 PC - Parts List -	<b>EN</b>	317124A	PA	(317102) or (317107)	<b>Meltex, only to be ordered with Instructions and Supplement</b>

A-2 - 8

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Bulk Melters - BM 5xxx Lueneburg Rebuilt Units*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>BM 5550 PC</b>	BM 5550 PC - Parts List -	<b>EN</b>	317125	PA	(317102) or (317107)	<b>Meltex, only to be ordered with Instructions and Supplement</b>
<b>BM 5551 PC</b>	Bulk Melter BM 5551 PC	<b>EN GE SP</b>	284118 267965 403035	MA	(317104) or (317105)	<b>Meltex, when ordering, please state Unit Type and Serial Number</b>

A-2 - 9

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>AltaPail</b>	AltaPail Bulk Melters DP020	<b>EN</b> <b>GE</b>	7169000B 7156963B	MA	(317102) or (317107)	
<b>AltaPail</b>	AltaPail Bulk Melters DP020 - Parts List	<b>EN</b>	7156964A	PA	(317102) or (317107)	
<b>DG 21 / DG 201</b>	Drum Melters DG 21 / DG 201	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	464849A 464839A 213094A 464764A 464842A 464848A	MA	(317104) or (317105)	
<b>DG 22 / DG 25 / DG 26 DG 202 / DG 207 / DG 251</b>	Drum Melters DG 22 / DG 25 / DG 26 DG 202 / DG 207 / DG 251	<b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	458221A 412873A 412976A 412874A 412854A 413013A 458020A	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>
<b>DG 25</b>	Drum Melters DG 25	<b>FR</b> <b>GE</b> <b>SP</b>	458387A 458128A 458388A	MA	(317104) or (317105)	

A-2 - 10

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>DuraDrum</b>	DuraDrum Bulk Melters DD200	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7119475J 7105975J 7105868J 7105731J 7119378J 7105821J 7105721K 7135232K 7105820J 7105881A 7105878J 7119472J 7105873J 7156582K 7105765J 7105872J	MA	(317102) or (317107)	
<b>DuraDrum</b>	DuraDrum Bulk Melters DD200 - Parts List -	<b>EN</b>	7135705_05	PA	(317102) or (317107)	
<b>DuraDrum</b>	DuraDrum Bulk Melters DK200	<b>BU</b> <b>CZ</b> <b>DU</b> <b>EN</b> <b>ES</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7135427H 7135271H 7119505H 7119506I 7146242H 7135052H 7119507H 7119423I 7146214H 7119508H 7119509H 7146399H 7146219H 7119510H 7119511H*	MA	(317103) or (317106)	* = not yet translated

A-2 - 11

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
DuraDrum	DuraDrum Bulk Melters DK200 - Parts List -	EN	7135706_06	PA	(317102) or (317107)	
DuraDrum	DuraDrum Bulk Melter (P/N 8051763)	GE	7105533A	IN	(317102) or (317107)	
DuraDrum	DuraDrum Bulk Melter (P/N 8055277)	EN GE	7105625A 7105623A	IN	(317102) or (317107)	
DuraDrum/ DuraPail	DuraDrum/ DuraPail Bulk Melters User's Guide	EN/ CH/JA	7119560_02	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
DuraDrum/ DuraPail	DuraDrum/ DuraPail Bulk Melters User's Guide	EN/CR/ ES/LA/ LI	7192166B	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
DuraDrum/ DuraPail	DuraDrum/ DuraPail Bulk Melters User's Guide	EN/CZ/ HU/PL/ RU	7119558B	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
DuraDrum/ DuraPail	DuraDrum/ DuraPail Bulk Melters User's Guide	EN/DA/ FI/NO/ SW	7119567B	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
DuraDrum/ DuraPail	DuraDrum/ DuraPail Bulk Melters User's Guide	EN/DU/ PO/SL/ SK	7119568B	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
DuraDrum/ DuraPail	DuraDrum/ DuraPail Bulk Melters User's Guide	EN/ FR/ GE/ IT/ SP	7119276B	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>

A-2 - 12

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>DuraPail</b>	DuraPail Bulk Melters DP020	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>SP</b> <b>SW</b>	7119437K 7105976K 7105367K 397983K 7119377K 397981K 397493L 7146489L 397995K 7105122A 7105406K 7119337K 7105346K 7105018K 7105355K	MA	(317103) or (317106)	
<b>DuraPail</b>	DuraPail Bulk Melters DP020 - Parts List -	<b>EN</b>	7135694E	PA	(317102) or (317107)	
<b>DuraPail</b>	DuraPail Bulk Melters DK020	<b>BU</b> <b>CZ</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SK</b> <b>SP</b> <b>SW</b>	7135426G 7146014G 7119489G 7119488G 7119490H 7119422H 7119491G 7156095G* 7119492G 7119504G 7146576H 7156845H 7146856H 7146164G 7119493G 7119494G	MA	(317103) or (317106)	<b>* available at Nordson K.K.</b>

A-2 - 13

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>DuraPail</b>	DuraPail Bulk Melters DK020 - Parts List -	<b>EN</b>	7135693E	PA	(317102) or (317107)	
<b>DuraPail/ DuraDrum</b>	DuraPail DP020 / DuraDrum DD200 Bulk Melters Generation II	<b>CZ DA DU EN ES FI FR GE GR HU IT JA LA LI NO PL PO RO RU SL SP SW</b>	7156450_07 7156384_07 7156211_09 7156106_09 7179784_07 7156361_07 7156148_09 7146728_09 7156368_09 7156648_09 7156109_09 7156277_09 7593221_09 7560747_09 7156587_07 7156654_09 7156152_09 7560546_08 7169170_09 7580932_09 7156107_09 7156360_09	MA	(317103) or (317106)	
<b>DuraPail/ DuraDrum</b>	DuraPail DP020 Bulk Melters with Gear Pump Generation II - Parts List -	<b>EN</b>	7146729_11	PA	(317102) or (317107)	
<b>DuraPail/ DuraDrum</b>	DuraDrum DD200 Bulk Melters with Gear Pump Generation II - Parts List -	<b>EN</b>	7146730_11	PA	(317102) or (317107)	
<b>DuraPail/ DuraDrum</b>	DuraPail/ DuraDrum Safety and User' s Guide	<b>GE GR</b>	7593477_01 7593483_01	OP	(317102) or (317107)	

A-2 - 14

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>DuraPail/ DuraDrum/ VersaPail/ VersaDrum</b>	DuraPail/ DuraDrum VersaPail/ VersaDrum Bulk Melters Safety	<b>EN/ CH/JA</b>	7119561_02	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>DuraPail/ DuraDrum/ VersaPail/ VersaDrum</b>	DuraPail/ DuraDrum VersaPail/ VersaDrum Bulk Melters Safety	<b>EN/CR/ ES/LA/ LI</b>	7192168C	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>DuraPail/ DuraDrum/ VersaPail/ VersaDrum</b>	DuraPail/ DuraDrum VersaPail/ VersaDrum Bulk Melters Safety	<b>EN/CZ/ HU/PL/ RU</b>	7119559C	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>DuraPail/ DuraDrum/ VersaPail/ VersaDrum</b>	DuraPail/ DuraDrum VersaPail/ VersaDrum Bulk Melters Safety	<b>EN/DA/ FI/NO/ SW</b>	7119569C	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>DuraPail/ DuraDrum/ VersaPail/ VersaDrum</b>	DuraPail/ DuraDrum VersaPail/ VersaDrum Bulk Melters Safety	<b>EN/DU/ PO/SL/ SK</b>	7119570C	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>DuraPail/ DuraDrum/ VersaPail/ VersaDrum</b>	DuraPail/ DuraDrum VersaPail/ VersaDrum Bulk Melters Safety	<b>EN/ FR/ GE/ IT/ SP</b>	7119305C	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaDrum</b>	VersaDrum VD200 Bulk Melters with Gear Pump - Parts List -	<b>EN</b>	7146281_14	PA	(317102) or (317107)	
<b>VersaDrum</b>	VersaDrum VD200 Bulk Melters with Piston Pump - Parts List -	<b>CH EN RU</b>	7169270_08 7146280_12 7169001E	PA	((317102) or (317107)	



A-2 - 15

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>VersaDrum</b>	Bulk Melters VersaDrum VD200 with Allen-Bradley Controller (P/N 7155289,....,7570976)	<b>EN</b> <b>GE</b>	7156136_02 7156128_02	MA	(317103) or (317106)	
<b>VersaDrum</b>	Bulk Melters VersaDrum VD200 with Allen-Bradley Controller (P/N 7161294,....,7564594)	<b>EN</b> <b>GE</b>	7156761_08 7156754_08	MA	(317103) or (317106)	
<b>VersaDrum</b>	Bulk Melters VersaDrum VD200 with Allen-Bradley Controller (P/N 7573575)	<b>EN</b> <b>GE</b> <b>IT</b>	7560923_01 7560922_01 7560924_01	MA	(317103) or (317106)	
<b>VersaDrum</b>	Bulk Melters VersaDrum VD200 with Gear Pump - Model SC	<b>DA</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>RO</b> <b>SP</b> <b>TU</b>	7169313A 7169427_03 7179450A 7169277_03 7192762_03 7560801_02 7169627A 7560656_03	MA	(317103) or (317106)	
<b>VersaDrum</b>	Bulk Melters VersaDrum VD200 with Gear Pump - Model SC - Parts List -	<b>GE</b>	7169278_02	PA	(317103) or (317106)	
<b>VersaDrum</b>	Bulk Melters VersaDrum VD200 (P/N 7184467) with Gear Pump and Siemens Controller	<b>EN</b> <b>GE</b> <b>PL</b>	7179961_01 7179771_01 7179998_01	MA	(317103) or (317106)	
<b>VersaDrum</b>	Bulk Melters VersaDrum VD200 (P/N 7184467) with Gear Pump and Siemens Controller - Parts List -	<b>EN</b> <b>PL</b>	7179981_01 7179997_01	PA	(317103) or (317106)	
<b>VersaDrum</b>	Interface Cable P/N 7153985, 7177902	<b>EN</b> <b>GE</b>	7156286_02 7156155_02	IN	(317102) or (317107)	
<b>VersaDrum</b>	Kit-SVC 7140585, 7140586	<b>EN</b> <b>GE</b>	7593122_01 7593121_01	IN	(317102) or (317107)	

A-2 - 16

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>VersaDrum</b>	Kit-SVC conv. 7186935 (Motor Controller i550 in VersaDrum Melters)	<b>EN GE</b>	7560960_04 7560944_04	IN	(317103) or (317106)	
<b>VersaDrum/ VersaPail</b>	ACO System with Bulk Melters VersaPail/ VersaDrum	<b>EN/ GE</b>	7156074_05	IN	(317102) or (317107)	<b>Bilingual document, therefore one P/N only</b>
<b>VersaDrum/ VersaPail</b>	VersaDrum/ VersaPail Bulk Melters User's Guide	<b>EN/CH/ JA</b>	7169763_02	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaDrum/ VersaPail</b>	VersaDrum/ VersaPail Bulk Melters User's Guide	<b>EN/CR/ ES/LA/ LI</b>	7192167B	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaDrum/ VersaPail</b>	VersaDrum/ VersaPail Bulk Melters User's Guide	<b>EN/CZ/ HU/PL/ RU</b>	7146791B	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaDrum/ VersaPail</b>	VersaDrum/ VersaPail Bulk Melters User's Guide	<b>EN/DA/ FI/NO/ SW</b>	7146790B	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaDrum/ VersaPail</b>	VersaDrum/ VersaPail Bulk Melters User's Guide	<b>EN/DU/ PO/SL/ SK</b>	7146789B	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaDrum/ VersaPail</b>	VersaDrum/ VersaPail Bulk Melters User's Guide	<b>EN/FR/ GE/IT/ SP</b>	7146751B	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>VersaPail/ VersaDrum</b>	VersaPail/ VersaDrum Safety and User' s Guide	<b>GE GR RO TU</b>	7560799_01 7560824_01 7560813_01 7560828_01	OP	(317102) or (317107)	

A-2 - 17

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>VersaPail/ VersaDrum</b>	VersaPail VP020 / VersaDrum VD200 Bulk Melters with Gear Pump and IPC Control Unit	<b>CH</b> <b>CR</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SK</b> <b>SP</b> <b>SW</b> <b>TU</b>	7146594_11 7580036_10 7156944_11 7146982_08 7146172_11 7135406_11 7146496_09 7146126_11 7135377_11 7169304_08 7156458_11 7146591_11 7146328A* 7146715_08 7156468_11 7146745_11 7192769_10 7146389_11 7179505_08 7146485_11 7146499_09 7560789_11	MA	(317103) or (317106)	* available at Nordson K.K.

A-2 - 18

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Bulk Melters - DG / DuraDrum / DuraPail / VersaPail / VersaDrum*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>VersaPail/ VersaDrum</b>	VersaPail VP020 / VersaDrum VD200 Bulk Melters with Piston Pump and IPC Control Unit	<b>CH</b> <b>CZ</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b> <b>TU</b>	7156532_04 7146677_04 7192915_05 7146640_06 7179440_06 7146084_06 7179560_06 7156467_04 7169848_04 7156814_06 7156558_06 7156850_04 7146423_04 7146707_04 7560079_05	MA	(317103) or (317106)	
<b>VersaPail/ VersaDrum</b>	Engineering Update with Bookbinding System Configurations (VP/VD with IPC)	<b>CR</b> <b>CZ</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7580046_01 7192735_01 7192736_01 7192665_01 7192678_01 7192646_01 7192733_01 7192675_01 7192737_01 7192666_01 7192739_01	MA	(317103) or (317106)	
<b>VersaPail</b>	VersaPail VP020 Bulk Melters with Gear Pump - Parts List -	<b>EN</b>	7146098_13	PA	(317103) or (317106)	
<b>VersaPail</b>	VersaPail VP020 Bulk Melters with Piston Pump - Parts List -	<b>EN</b>	7146178_12	PA	(317102) or (317107)	

A-3 - 1

## Nordson Engineering Hot Melt Products (sorted by Model)

### *MC/ (PUR) Units*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>MC 4</b>	Hot Melt Material Applicator MC 4	<b>DU EN GE IT</b>	7105567A 213746A 464771B 213747B	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number End of Support 03/2020</b>
<b>MC 6</b>	Hot Melt Material Applicator MC 6	<b>DU EN FR GE IT PO SP SW</b>	403109D 403022D 403142D 317230D 403043D 405042D 405011D 403126D	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number End of Support 03/2020</b>
<b>MC 7</b>	Hot Melt Material Applicator MC 7	<b>DU EN FI FR GE HU IT NO PL PO RU SK SP SW</b>	7105970C 412892C 458161C 397885C 412855C 7146612C 458170C 458320C 7135116C 213660C 7135995C 7135452C 412910C 397265C	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number  End of Support 10/2015</b>
<b>MC 7</b>	Hot Melt Material Applicator MC 7 - Parts List -	<b>EN</b>	7135003A	PA	(317102) or (317107)	<b>End of Support 10/2015</b>

A-3 - 2 **Nordson Engineering Hot Melt Products (sorted by Model)**

**MC/ (PUR) Units**

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>MC 12/ MC 24</b>	Hot Melt Material Applicator MC 12 / MC 24	<b>CZ DA DU EN FI FR GE GR IT NO PL PO RU SP SW</b>	7105701D 405207D 403119D 403076D 413008D 403102D 317291D 7119832D 403077D 409452D 7105796D 7119416D 7105352D 403112D 403243D	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>  <b>Obsolete!</b>  <b>Replaced by PURBlue 4 and PURBlue EC</b>  <b>End of Support 03/2020</b>
<b>MC 12/ MC 24</b>	Hot Melt Material Applicator MC 12 / MC 24 - Parts List -	<b>EN</b>	7135004A	PA	(317102) or (317107)	<b>End of Support 03/2020</b>
<b>MC 20/ MC 21</b>	Melter MC 20 / MC21 with Foil Bag  ( Title Rev. A - E: Melter MC 20 with Foil Bag )	<b>CZ DU EN FI FR GE HU IT JA PL PO RO RU SK SP SW</b>	7105250F 7119673F 397155F 7105430E 397491F 213642F 7156911F 397480F 7105965D 7119266F 7169394F 7135621F 7135298F 7119924F 7105697F 7105431E	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>  <b>End of Support 03/2020</b>

A-3 - 3

## Nordson Engineering Hot Melt Products (sorted by Model)

### *MC/ (PUR) Units*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>MC21 MOD</b>	Adhesive Melters MC21 MOD for Foil-encased PUR Slugs	<b>CZ DU EN FR GE IT PO SK SP</b>	7169890_02 7179389_02 7169901_03 7179356_02 7169563_03 7179757_03 7179905_03 7179530_02 7179064_03	MA	(317102) or (317107)	<b>End of Support 10/2018</b>
<b>MC21 MOD</b>	Adhesive Melters MC21 MOD for Foil-encased PUR Slugs - Parts List	<b>EN</b>	7179606_01	PA	(317102) or (317107)	<b>End of Support 10/2018</b>
<b>MC 106</b>	MC 106 Hot Melt Material Applicator	<b>DA DU EN FR GE IT NO SW</b>	315709A 292738A 283043A 292793A 269876A 290702A 292854A 284184A	MA	(317103) or (317106)	<b>When ordering, please state Unit Type and Serial Number</b>
<b>MC 201/ MC 203/ MC 204/ MC 210</b>	Hot Melt Material Applicators MC 201 / MC 203 / MC 204 / MC 210	<b>EN GE</b>	412628A 409066A	MA	(317102) or (317107)	<b>When ordering, please state Unit Type and Serial Number</b>
<b>MC 405</b>	Hot Melt Applicator MC 405 for Foil Bags	<b>CZ DU EN FR GE HU IT PL SK SP</b>	7146593G 7105658G 213668G 7105667G 213066G 7119805G 7146647G 7135320G 7119349G 7119033G	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>  <b>End of Support 10/2015</b>

A-3 - 4

## Nordson Engineering Hot Melt Products (sorted by Model)

### *MC/ (PUR) Units*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>MC 4020</b>	MC 4020 Hot Melt Material Applicator	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SW</b>	292716A 284124A 290714A 284125A 290715A 292715A	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number End of Support 03/2020</b>
<b>MC 4420</b>	Hot Melt Material Applicator MC 4420	<b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	409195E 317079E 315915E 405210E 403113E 315858E 315911E 213098E 7119635E 317042E 403248E	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number  Obsolete!  Replaced by PURBlue EC and MC21 MOD End of Support 03/2020</b>
<b>MC 4420</b>	Hot Melt Material Applicator MC 4420 - Parts List -	<b>EN</b>	7135164A	PA	(317102) or (317107)	<b>End of Support 03/2020</b>
<b>PURBlue EC</b>	Adhesive Melters PURBlue EC for Reactive Materials	<b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>LI</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>SP</b> <b>SW</b>	7135268_05 7146601B 7135321A 7135055_06 7135322_05 7135449B 7179996_06 7135661A 7146680B 7156680C 7135262C 7156791_06	MA	(317102) or (317107)	<b>End of Support 10/2018</b>



A-3 - 5

## Nordson Engineering Hot Melt Products (sorted by Model)

### *MC/ (PUR) Units*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
PURBlue EC	PURBlue EC Melters - Safety	EN/ FR/ GE/ IT/ SP	7135243A	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only End of Support 10/2018</b>
PURBlue EC	PURBlue EC Melters - Safety	EN/ DA/ RO / SW/ LI	7156682_02	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only End of Support 10/2018</b>
PURBlue EC	PURBlue EC Melters - User's Guide	EN/ FR/ GE/ IT/ SP	7135242A	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only End of Support 10/2018</b>
PURBlue EC	PURBlue EC Melters - User's Guide	EN/ DA/ RO / SW/ LI	7156681_02	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only End of Support 10/2018</b>
PURBlue RP	Slug Melter PURBlue RP	EN GE IT	7179025D 7156483_05 7169016B	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>
VersaPUR-S	Adhesive Melters VersaPUR-S for Slugs	CH CZ DA DU EN FI FR GE GR IT JA PL PO SK SP SW	7560945_03 7179896_03 7580148_03 7192583_04 7179482_04 7580218_04 7192742_04 7179000_04 7593337_04 7192120_04 7179651_02 7179722_04 7192368_03 7560762_03 7179483_04 7580609_03	MA	(317104) or (317105)	

A-3 - 6

## Nordson Engineering Hot Melt Products (sorted by Model)

### *MC/ (PUR) Units*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>VersaPUR-S</b>	VersaPUR-S Adhesive Melters - Safety and User's Guide	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>PO</b> <b>SK</b> <b>SP</b> <b>SW</b>	7192951_01 7580149_01 7192956_01 7192871_01 7580219_01 7192950_01 7192869_01 7593336_01 7192933_01 7192958_01 7192957_01 7192948_01 7560763_01 7192936_01 7580608_01	OP	(317102) or (317107)	
<b>VersaPUR-T</b>	Adhesive Melters VersaPUR-T Tank Melter for Reactive Materials	<b>BU</b> <b>DU</b> <b>EN</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7560755_03 7560978_03 7192212_06 7179011_06 7192592_05 7192934_02 7593150_05 7580196_04 7192347_03 7192370_05 7192596_03	MA	(317104) or (317105)	

**A-3 - 7 Nordson Engineering Hot Melt Products (sorted by Model)**

***MC/ (PUR) Units***

<b>Model</b>	<b>Product Title</b>	<b>Langs.</b>	<b>P/N</b>	<b>Type</b>	<b>Price Category</b>	<b>Notes</b>
<b>VersaPUR-T</b>	VersaPUR-T Adhesive Melters - Safety and User's Guide	<b>BU</b> <b>DU</b> <b>EN</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7560756_01 7560979_01 7192870_01 7192868_01 7192932_01 7560072_01 7593151_01 7580197_01 7192955_01 7192935_01 7192937_01	OP	(317102) or (317107)	
<b>VersaPUR-S/T</b>	Adhesive Melters VersaPUR-S, VersaPUR-T - Parts List -	<b>EN</b>	7192178_06	PA	(317104) or (317105)	

A-4 - 1

## Nordson Engineering Hot Melt Products (sorted by Model)

### MX Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Kit-SVC conv. 7577674 (Motor Controller i550 in MX 3106 and M 4003)	EN GE	7580099_02 7580096_02	IN	(317103) or (317106)	
	Pressure Control for Applicators MX / MC	DU EN FR GE IT JA PO SP	397211A 213020A 397371A 464861A 213087A 7119723A 213110A 7105221A	MA	(317102) or (317107)	
<b>MX 1500</b>	Lotion Applicators MX 1500	EN FR GE IT SP TU	412990B 447750B 412866B 213224B 413039B 7119675B	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>  <b>End of Support 10/2013</b>
<b>MX 2001/ MX 2001 S/ MX 2001 SD</b>	Hot Melt Material Applicators MX 2001 / MX 2001 S / MX 2001 SD	DU EN FI GE IT SP SW	403233A 403134A 7146251A 403133A 403242A 403249A 405050A	MA	(317103) or (317106)	<b>When ordering, please state Unit Type and Serial Number</b>  <b>End of Support 10/2018</b>
<b>MX 3000/ MX 4000</b>	SERIES MX 3000 / MX 4000 Hot Melt Applicators with DC Drives	DU EN FR GE HU IT SP SW	269830 267808 267809 267810 7119546A 269821 269820 269819	OP	(317102) or (317107)	<b>When ordering, please state Unit Type and Serial Number</b>

A-4 - 2

## Nordson Engineering Hot Melt Products (sorted by Model)

### MX Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>MX 3006</b>	Hot Melt Material Applicators MX 3006	<b>DU</b> <b>EN</b> <b>FI</b> <b>GE</b> <b>PO</b>	317030C 317090C 405003C 269879C 317070C	MA	(317103) or (317106)	<b>When ordering, please state Unit Type and Serial Number</b>
<b>MX 3106/ MX 3106 N MX 3106 IG</b>	Hot Melt Material Applicators MX 3106 / MX 3106 N MX 3106 IG	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>PO</b> <b>JA</b> <b>SK</b> <b>SP</b>	464957_04 464780_04 464779_04 412915_05 7105475B 458319_04 7560506_04 464987B* 7105458_04 213173_04	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>  <b>Product Obsolescence September 1st 2017, replaced by MX 4003 NV Tank Melter</b>  <b>* available at Nordson K.K. End of Support 10/2020</b>
<b>MX 3400/ MX 4400</b>	Hot Melt Material Applicators MX 3400 / MX 4400	<b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b> <b>TU</b>	292850C 290847C 290842C 292851C 290843C 290841C 213836C 290845C 412707C 458269C 403061C 397386C 290846C 290848C 397109C	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>  <b>End of Support 10/2013</b>

A-4 - 3

## Nordson Engineering Hot Melt Products (sorted by Model)

### *MX Units*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>MX 3400/ MX 4400</b>	Hot Melt Material Applicators MX 3400 / MX 4400	<b>CH</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b> <b>TU</b>	412695B 409273B 409202B 409203B 409274B 409204B 409205B 213837B 409206B 447744B 409275B 458262B 409491B 213203B 409207B 409208B 397110B	OP	(317102) or (317107)	<b>End of Support 10/2013</b>
<b>MX 4003/ MX 4003 N/ MX 4003 IG</b>	Hot Melt Material Applicator MX 4003 / MX 4003 N / MX 4003 IG	<b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>PL</b> <b>SK</b> <b>SP</b> <b>SW</b>	447611C 409434C 412614C 412823C 409433C 7156855C 409459C 7105301C 7119810C 458250C 458145C	MA	(317104) or (317105)	
<b>MX 4003 NV</b>	Adhesive Melters Series MX4003NV	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>PL</b>	7593119_05 7169177C 7593180_05 7156020_05 7156015_05 7146334_05 7560625_05	MA	(317104) or (317105)	

A-4 - 4

## Nordson Engineering Hot Melt Products (sorted by Model)

### *MX Units*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>MX 4003 NV</b>	Adhesive Melter Series MX 4003 NV - Parts List	<b>EN</b>	7146357_06	PA	(317104) or (317105)	
<b>MX 4003 N/ MX 3106 N</b>	Hot Melt Material Applicators MX 4003 N / MX3106 N - Parts List -	<b>EN</b>	7135192_04	PA	(317102) or (317107)	
<b>MX 4460</b>	Hot Melt Material Applicators MX 4460 with Rockwell PLC-5 System	<b>EN GE IT SP</b>	409293B 407475B 409390B 458063B	MA	(317103) or (317106)	
<b>MX 4460</b>	Electrical Cabinet for Melt Material Applicators MX 4460 with Rockwell PLC-5 System	<b>EN GE IT SP</b>	409240B 409222B 409470B 458064B	MA	(317103) or (317106)	
<b>MX 4460</b>	Electrical Cabinet for Hot Melt Material Applicators MX4460 with Rockwell PLC-5 System - <i>Appendix</i>	<b>EN GE IT SP</b>	409242B 409241B 409471B 458065B	MA	(317102) or (317107)	
<b>MX 4460/ MX 44110</b>	Hot Melt Material Applicators MX 4460 / MX 44110	<b>EN</b>	412887A	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>
<b>MX 5100/ MX 5200</b>	Hot Melt Material Applicators MX 5100 / MX 5200	<b>DU EN FR GE IT SP SW</b>	213524B 213547B 397948B 213422B 213457B 7119543B 213435B	MA	(317103) or (317106)	

A-4 - 5

## Nordson Engineering Hot Melt Products (sorted by Model)

### MX Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>MX 5100/ MX 5200</b>	Hot Melt Material Applicators MX 5100 / MX 5200 with Control System CS 20	<b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b> <b>SW</b>	458353C 213077C 458235C 213333C 458354C 213429C	MA	(317103) or (317106)	<b>When ordering, please state Unit Type and Serial Number</b>
<b>MX 5100/ MX 5200</b>	Hot Melt Material Applicators MX 5100 / MX 5200 with Siemens PLC  (Version A: Hot Melt Material Applicators MX 5124 / MX 51110 / 5224 with Siemens PLC)	<b>EN</b> <b>FR</b> <b>GE</b>	458130A 213129B 458067B	MA	(317103) or (317106)	
<b>MX 5100/ MX 5200</b>	Operator Panel OP 27 for Hot Melt Applicators MX 5100 / MX 5200	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b>	213521A 458099A 213130A 413078A 7105162A	MA	(317102) or (317107)	
<b>MX 5160</b>	Hot Melt Material Applicators MX 5160 with Control System CS 20	<b>EN</b> <b>GE</b>	458301A 458267A	MA	(317103) or (317106)	
<b>MX 51110/ MX 5224</b>	Hot Melt Material Applicators MX 51110 / MX 5224 with Siemens PLC	<b>GE</b>	413067A	MA	(317103) or (317106)	<b>When ordering, please state Unit Type and Serial Number</b>



A-5 - 1

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Analog Pressure Display	<b>EN</b> <b>GE</b>	397141A 458447A	MA	(317102) or (317107)	
	Communication Data List for Drum Melters DG 202 with Rockwell PLC	<b>EN</b>	458183A	MA	(317102) or (317107)	
	Communication Data List for Application Units MX 5160 with Rockwell PLC	<b>EN</b>	458185A	MA	(317102) or (317107)	
	Communication Data List for PROFIBUS Interface on Drum Melters BM 20 / BM 200	<b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>PO</b>	458432A 458433A 458434A 458435A 458429A 213183A	MA	(317102) or (317107)	
	Communication Data List for PROFIBUS Interface on Drum Melters DG	<b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b>	458273B 413036B 412926B 412944B 412876B	MA	(317102) or (317107)	
	Communication Data List for PROFIBUS Interface on Hot Melt Application Units MX / MC	<b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>SP</b> <b>SW</b>	458402C 413037C 412925C 447745C 412943C 412845C 458403C 458476C 7119269C 213182C 458420C 458445C	MA	(317102) or (317107)	

A-5 - 2

## Nordson Engineering Hot Melt Products (sorted by Model)

### Auxiliary Systems

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Field Bus Interface PROFIBUS DP for Control System CS 20	<b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>SP</b> <b>SW</b>	458272B 413038B 412886B 447746B 412940B 412861B 458426B 447623B 7119270B 213181B 458419B 458446B	MA	(317102) or (317107)	
	Field Bus Interface PROFIBUS DP for Siemens PLC	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b>	213527A 458098A 213134A 458015A 7105161A	MA	(317102) or (317107)	
	Interbus Interface	<b>EN</b> <b>FR</b> <b>GE</b>	458171A 458172A 458167A	MA	(317102) or (317107)	
	Nordson Melters on Field Bus with Siemens (Master) PLC	<b>EN</b> <b>GE</b>	7580295_03 7580294_03	MA	(317102) or (317107)	This document applies to application systems that contain one or more of the following units: <b>Bulk melter VD(VersaDrum)</b> <b>Extruder</b> <b>Foam unit UFM Cube</b> <b>Metering station PS-Midi</b> <b>Applicator VDK (Volume metering head)</b>
	PROFIBUS-DP Interface	<b>EN</b> <b>GE</b>	458103B 458072B	PI	(317102) or (317107)	

A-5 - 3 **Nordson Engineering Hot Melt Products (sorted by Model)**

**Auxiliary Systems**

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Single-Channel Temperature Controller	EN FR GE IT JA SP	409009B 409287B 407452B 409480B 464985B* 409041B	MA	(317102) or (317107)	* = available at Nordson K.K.
	Single-Channel Temperature Controller	DU EN FR GE HU IT JA SK SP SW	269827 267950 269818 267951 7105476A 269828 464981* 7105459A 269817 269829	OP	(317102) or (317107)	* = available at Norson K.K.
<b>BA 9624</b>	Luminous Band Display BA 9624	EN GE IT SW	283019B 283018B 7105057B 7105037B	MA	(317102) or (317107)	
<b>CS 20</b>	Control System CS 20	DA DU EN FI FR GE GR IT NO PO RU SP SW	409186A 409187A 409188A 409332A 409189A 409181A 7119548A 409190A 409479A 409371A 7179611A 409191A 409192A	MA " " " " " OP MA " " " "	(317102) or (317107)	

A-5 - 4 **Nordson Engineering Hot Melt Products (sorted by Model)**

**Auxiliary Systems**

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>CS 20_</b> <b>BM 20 / BM</b> <b>200</b>	Control System CS 20 for Bulk Melters BM 20 / BM 200	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7105111C 458438C 458408C 458374C 213410C 458399C 458280C 458412C 464865A* 447602C 7105210C 213180C 7135722C 458428C 447606C	MA	(317103) or (317106)	* = available at K.K.
<b>CS 20_DG</b>	Control System CS 20 for Drum Melters DG	<b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	458223D 412862D 412811D 412863D 407280D 458082D 458296D 458297D 458062D 458298D	MA	(317103) or (317106)	

A-5 - 5 **Nordson Engineering Hot Melt Products (sorted by Model)**

**Auxiliary Systems**

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>CS 20_MX/MC</b>	Control System CS 20 for MX / MC Hot Melt Material Applicators	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SK</b> <b>SP</b> <b>SW</b> <b>TU</b>	7105251D 458485D 458449D 412960D 213352D 412962D 412908D 213838D 7119806D 458462D 464866D 458495D 213141D 213095D 7135625D 397387D 7119350D 458453D 447625D 397113D	MA	(317103) or (317106)	
<b>DD 77</b>	Pressure Difference Measuring Instrument for Filter Monitoring DD 77	<b>EN</b> <b>GE</b>	315804A 315790A	MA	(317102) or (317107)	
<b>DG 202</b>	Control Device PanelMate for DG 202	<b>EN</b> <b>GE</b>	458231B 458212B	MA	(317102) or (317107)	
<b>E5CN</b>	Single Channel Temperature Controller E5CN	<b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>PL</b> <b>SP</b> <b>SW</b>	7119590A 7119283A 7119606A 7119608A 7119053B 7156854B 7119308A 7119589A 7119591A	IN		

A-5 - 6

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>E 75</b>	Electric Gun Driver E 75	<b>EN GE IT</b>	412834B 409398B 447686B	MA	(317102) or (317107)	
<b>E 75</b>	Electric Gun Driver E 75	<b>EN GE</b>	412859B 412858B	PI	(317102) or (317107)	
<b>E 750</b>	Switching Amplifier E 750	<b>EN FR GE SP</b>	292869A 412966A 292792A 405049A	MA	(317102) or (317107)	
<b>ES 10</b>	Coating Weight Control ES 10	<b>EN GE</b>	412739A 412730A	PI	(317102) or (317107)	
<b>ES 10-I</b>	Coating Weight Control ES 10-I	<b>DU EN FR GE</b>	412893B 412727B 412907B 409294B	MA	(317102) or (317107)	
<b>ES 10-II</b>	Coating Weight Control ES 10-II	<b>DU EN FR GE IT SP SW</b>	458017A 458018A 213034A 413049A 213049A 464949A 458141A	MA	(317102) or (317107)	

A-5 - 7

## Nordson Engineering Hot Melt Products (sorted by Model)

### Auxiliary Systems

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>ES 10-III</b>	Coating Weight Control ES 10-III	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>PL</b> <b>RU</b> <b>SP</b> <b>SW</b>	213372G 213356J 213375G 213225J 7156460H 213363G 7105869G 397389G 213436G 213365G	MA	(317102) or (317107)	
<b>ES 23-xxx</b>	Pressure Monitoring Device ES 23-xxx	<b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b> <b>SW</b>	213395C 213387C 213441C 213389C 213309C 213398C 213408C 213402C	MA	(317102) or (317107)	
<b>ES 64</b>	Pressure Control Unit ES 64	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>SP</b> <b>SW</b>	447783C 284111C 317207C 284110C 458000C 213269C 409094C 317160C	MA	(317102) or (317107)	
<b>ES 80 / ES 90 / ES 90 P</b>	Replacement of Central Unit for ES 80 / ES 90 / ES 90 P	<b>EN</b>	213083A	MA	(317102) or (317107)	

**A-5 - 8 Nordson Engineering Hot Melt Products (sorted by Model)**

***Auxiliary Systems***

<b>Model</b>	<b>Product Title</b>	<b>Langs.</b>	<b>P/N</b>	<b>Type</b>	<b>Price Category</b>	<b>Notes</b>
<b>ES 80</b>	Pressure Control Unit ES 80	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	403268E 284132E 292717E 284150E 458380E 315820B 7179777E 458392E 317019B	MA	(317102) or (317107)	
<b>ES 90</b>	Control Box for ES 90	<b>FR</b> <b>GE</b>	412659A 412615A	MA	(317102) or (317107)	
<b>ES 90</b>	Pattern Control Unit ES 90	<b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>IT</b> <b>PL</b> <b>SK</b> <b>SP</b> <b>SW</b>	412711E 405059E 284144E 412959E 292718E 284138E 7119983E 407012E 7105417E 7105392E 405095E 317276E	MA	(317103) or (317106)	



A-5 - 9

## Nordson Engineering Hot Melt Products (sorted by Model)

### Auxiliary Systems

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>ES 90 P</b>	Pattern / Pressure Control Unit ES 90 P	<b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	405208E 317217E 284126E 412888E 292719E 284127E 407138E 292960A 7179778E 405068E 464810E	MA	(317103) or (317106)	
<b>ETR 104 / ETR 108</b>	Temperature Controller ETR 104 / ETR 108	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>SP</b>	413076A 413058A 413063A 413029A 413075A 213380A 447638A	OP	(317102) or (317107)	
<b>FP 13</b>	Temperature Controller	<b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>LI</b> <b>PL</b> <b>PO</b> <b>SL</b> <b>SP</b>	7169635_01 7179307_01 7169611_01 7169850_01 7560768_01 7593142_01 7169639_01 7560666_01 7179769_01	MA	(317102) or (317107)	
<b>OptiStroke</b>	Optical Needle Stroke Detection System OptiStroke	<b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	213958B 7105038B 213748B 7105008B 7105009B	MA	(317102) or (317107)	<b>Product Obsolescence October 31st 2018, replaced by Gen. II. End of Support effective October 31st 2019.</b>

A-5 - 10

## Nordson Engineering Hot Melt Products (sorted by Model)

### Auxiliary Systems

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>OptiStroke</b>	Optical Needle Stroke Detection System OptiStroke Generation II	<b>CH</b> <b>DU</b> <b>EN</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>SK</b> <b>SP</b>	7560332_04 7560709_05 7192332_05 7192103_05 7192843_05 7560897_03* 7560054_02 7580146_05 7560331_05	MA	(317102) or (317107)	* available at Nordson K.K.
<b>OptiStroke</b>	Adapter Bushing for OptiStroke-Sensors	<b>EN/ GE</b>	7105403A	IN	(317102) or (317107)	<b>Bilingual</b> document, therefore one P/N only
<b>PC 6/ PC 9/ PC 12</b>	Temperature Controllers PC 6 / PC 9 / PC 12	<b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	290921A 290922A 290938A 290923A 290940A 290939A 290924A 290925A 290926A 290920A 290927A	IN	(317102) or (317107)	

A-5 - 11

## Nordson Engineering Hot Melt Products (sorted by Model)

### Auxiliary Systems

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
PC 6/ PC 9/ PC 12	Temperature Controllers PC 6 / PC 9 / PC 12	CH CZ DA DU EN FI FR GE HU IT NO PL PO RU SK SP SW	412917B 464928B 447666B 317051B 317050B 403069B 317052B 317032B 7146613B 317053B 317054B 7146010B 317055B 7135996B 7135453B 317056B 317057B	MA	(317102) or (317107)	
TR 35... / TR 36... / TR 36...Z	Temperature Control Boxes TR 35 ... / TR 36 ... / TR 36 ... Z	DU EN FR GE	403232B 213504B 464917B 403144B	MA	(317102) or (317107)	
TR 37... / TR 38... / TR 38...Z	Temperature Control Boxes TR 37 ... / TR 38 ... / TR 38 ... Z	EN FI GE	213505B 7146252B 403146B	MA	(317102) or (317107)	
	Bead Gap Detector II Item Nos. 1160.0443 1160.0449	EN FR GE SW	317199A 403247A 317120A 315786A	MA	(317102) or (317107)	

A-5 - 12

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Digital Display with Limit Monitoring	<b>CZ</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b> <b>SW</b>	464926C 464744C 407455C 409413C 407454C 409004C 458417C 413073C	MA	(317102) or (317107)	
	Digital Display with Limit Monitoring (Type 2300)	<b>CZ</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>SP</b> <b>SW</b>	7105113C 213396C 213388C 213442C 213390C 213308C 213397C 7119265C 213407C 213401C	MA	(317102) or (317107)	
	Feed System for Hot Melt Material Applicators FILLMASTER I	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>SP</b> <b>SW</b>	458328B 458264B 458316B 413083B 458329B 464939B 458330B 458467B	MA	(317102) or (317107)	

A-6 - 1

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Field Bus on Nordson Applicators with IPC	EN FR GE IT LI PL RU SW	7169718_10 7560479_08 7169180_10 7169515_09 7580904_09 7179215_08 7593612_10 7593204_09	MA	(317102) or (317107)	
	Inside Coating Nozzle IBD, IBD-T	DU EN FR GE	7593400D 213759C 412708C 412617D	MA	(317102) or (317107)	
	Material Guide for Applicators (Titel version B: Material Guide for Hot Melt Application Head PF...V)	DU EN FI FR GE	397927B 397964B 397980B 7560659_03 397888_03	IN	(317102) or (317107)	
	Outside Coating Nozzle	EN GE SP	397481B 458302B 458383A	MA	(317102) or (317107)	
	Recirculation Control Module RV45, CC, MG	EN GE	7135366A 7135337A	MA	(317101)	
	Retrofitting Kit Spinner Roll	EN/FR/ GE	409427A	MA	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>AD 24</b>	Hot Melt Application Head AD 24	EN GE	412762A 405111A	MA	(317102) or (317107)	<b>End of Support 10/2015</b>
<b>AG 900</b>	Control Modules Series AG 900	CZ EN GE	7105114B 397773B 458114B	MA	(317102) or (317107)	

A-6 - 2 **Nordson Engineering Hot Melt Products (sorted by Model)**

**Applicators (Guns)**

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>AltaSlot-c</b>	Hot Melt Adhesive Applicator AltaSlot-c	<b>EN GE</b>	7146313_03 7146404_03	MA	(317102) or (317107)	
<b>AltaSlot-i</b>	Hot Melt Adhesive Applicator AltaSlot-i	<b>EN GE</b>	7119466_04 7119456_04	MA	(317102) or (317107)	
<b>AN240</b>	AN240 Applicators	<b>EN GE SW</b>	7192572_03 7560691_03 7580715_03	MA	(317102) or (317107)	
<b>BC</b>	Trolley for Application Heads BC	<b>FR GE</b>	458209A 458196A	MA	(317102) or (317107)	
<b>BC 31</b>	Surface Coating Applicator BC 31 (Title version H: Surface Coating Head BC 31)	<b>CH DU EN FR GE IT JA PO SP</b>	7560882_09 447704G 317096H 405005H 317080_10 317110G 464853H 7119273G 317200G	MA	(317102) or (317107)	
<b>BC 35</b>	Surface Coating Head BC 35	<b>DU EN FR GE IT JA</b>	464923F 458451F 464934F 317098_07 7135176F 464854D*	MA	(317102) or (317107)	<b>* available at Nordson K.K.</b>
<b>BC 40</b>	Surface Coating Application Head BC 40	<b>EN FR GE PO SP</b>	317015C 458142B 315879C 7105106B 7135819B	MA	(317102) or (317107)	

A-6 - 3 **Nordson Engineering Hot Melt Products (sorted by Model)**  
**Applicators (Guns)**

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>BC 40-1620</b>	Surface Application Head BC 40-1620	<b>EN</b> <b>GE</b>	7156122A 7156091A	MA	(317102) or (317107)	
<b>BC 60</b>	Surface Coating Head BC 60	<b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	412827E 7119987E 409387E 7105181E 409140C	MA	(317102) or (317107)	
<b>BC 62</b>	Surface Coating Head BC 62	<b>CH</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>TU</b>	7119922F 317297F 403044F 403040F 317209F 409289F 7105130F 7156510F 7119550F 7560657F	MA	(317102) or (317107)	
<b>BC 70</b>	Surface Coating Head BC 70	<b>FR</b> <b>GE</b> <b>JA</b>	397190G 447604G 7119627D*	MA	(317102) or (317107)	<b>* available at Nordson K.K.</b>
<b>BC 70</b>	Surface Coating Head BC 70 with Gear Pumps	<b>GE</b>	7105789A	MA	(317102) or (317107)	
<b>CA 410/ 420</b>	Cable Applicators	<b>EN</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>PL</b> <b>SP</b> <b>SW</b>	7560254_01 7179883_01 7169990_01 7560815_01 7560624_01 7560509_01 7192989_01	MA	(317102) or (317107)	

A-6 - 4 **Nordson Engineering Hot Melt Products (sorted by Model)**

**Applicators (Guns)**

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
CA 410/ 420	Cable Applicators - Parts List -	EN	7179185_01	PA	(317102) or (317107)	
CC ../ ..C	Hot Melt Material Application Heads for continuous surface coating Control Coat CC ../ ..C	DU EN GE IT SP	409213D 315788D 292963D 213453D 317097D	MA	(317102) or (317107)	<b>End of Support effective November 1st 2017</b>
CC ../ ..I	Hot Melt Material Application Heads for intermittent surface coating Control Coat CC ../ ..I	DA DU EN FR GE IT SP SW	409142D 403031D 292930D 405206D 292878D 213310D 317109D 403054D	MA	(317102) or (317107)	<b>End of Support effective November 1st 2017</b>
CC ../ ..I GP	Hot Melt Material Application Heads with gear pump for intermittent surface coating Control Coat CC ../ ..I GP	EN GE	292856E 292861E	MA	(317102) or (317107)	<b>End of support effective November 1st 2017</b>
CCQE	Hot Melt Applicators Control Coat CCQE	DU EN FR GE IT PL SK SL SP SW TU	7105513_03 397986_05 7135446_05 397836_05 7105014_05 7169616_05 7192986_03 7560866_05 7560088_05 397985_03 7192924_05	MA	(317102) or (317107)	
CC MF	Hot Melt Applicator Control Coat CC MF	EN GE IT	7156197_02 7156183_02 7560077_02	MA	(317102) or (317107)	



A-6 - 5 **Nordson Engineering Hot Melt Products (sorted by Model)**

***Applicators (Guns)***

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
CC 10	Hot Melt Application Head CC 10	EN GE	458131B 458093B	MA	(317102) or (317107)	End of Support effective November 1st 2017
CC 18 / 322 I	Hot Melt Application Head CC 18 / 322 I	EN GE	458342B 458326B	MA	(317102) or (317107)	End of Support effective November 1st 2017
CC 201	Hot Melt Application Head CC 201	FR GE	213135B 458373B	MA	(317102) or (317107)	End of Support effective November 1st 2017
CF 04	Application Head CF 04	EN GE	458168A 458126A	MA	(317102) or (317107)	
CF 04	Retrofitting Kit Application Head CF 04	EN GE	458422A 458398A	MA	(317102) or (317107)	
CF 04	Retrofitting Kit Application Head CF 04	EN GE	447620A 458498A	MA	(317102) or (317107)	
CF 200	Hot Melt Application Heads CF 200	DA DU EN FI FR GE IT PL PO SP SW	213188A 213105A 213125A 213359A 213108A 213014A 213097A 213434A 213167A 213197A 213322A	OP	(317102) or (317107)	
CF 200	Hot Melt Material Application Head CF 200	DA EN GE	7105996C 447653B 458236C	MA	(317102) or (317107)	

A-6 - 6

## Nordson Engineering Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>CF 216</b>	Hot Melt Application Head CF 216	<b>EN GE</b>	213213A 213186A	MA	(317102) or (317107)	
<b>CH26</b>	Application Head Precision Holder CH26	<b>EN FR GE IT</b>	317034A 317131A 317033A 403033A	MA	(317102) or (317107)	
<b>COBRA</b>	Application Nozzle COBRA	<b>EN FR GE IT SP SW</b>	464995A 464994A 464919A 464996A 464992A 464993A	MA	(317102) or (317107)	<b>End of Support 09/2017</b>
<b>CONTOUR COAT</b>	Contour Coat Applicator	<b>EN GE</b>	7105874B 7105345B	MA	(317102) or (317107)	<b>End of Support 06/2016</b>
<b>CURTAIN COAT BC 70</b>	Curtain Coat BC 70 Surface Coating Applicator (Title version H: Application Head Curtain Coat BC 70)	<b>EN GE IT JA PL</b>	7135511_09 7119301_09 7135179H 7119628A* 7146513_09	MA	(317102) or (317107)	<b>* available at Nordson K.K.</b>
<b>DA 34</b>	Application Head Series DA 34	<b>EN GE</b>	403030B 317282B	MA	(317102) or (317107)	<b>End of Support 10/2014</b>
<b>DN 50</b>	Metering Application Head DN 50	<b>EN FR GE SP SW</b>	413054B 407494B 403003B 403052B 413051B	MA	(317102) or (317107)	<b>End of Support 12/2013</b>

A-6 - 7

## Nordson Engineering Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>DPW</b>	Application Heads DPW, DPW-J	<b>CZ</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>PO</b> <b>SP</b> <b>SW</b>	7179897J 7119613I 7105670J 7156799J 7105661J 7119417I 7135450F* 7146415J 7119646G 7119071J 7135780I	MA	(317102) or (317107)	<b>Product Obsolescence September 1st 2017</b>  * available at Nordson K.K.
<b>DPW-HC</b>	Application Heads DPW-HC	<b>EN</b> <b>GE</b> <b>IT</b> <b>SP</b> <b>SW</b>	7119754C 7119704C 7135143C 7119748B 7156321C	MA	(317102) or (317107)	<b>Product Obsolescence September 1st 2017</b>
<b>e-slot</b>	e-slot Applicator	<b>EN</b> <b>IT</b>	7146358A0 7146398A0	MA	(317102) or (317107)	<b>Product Obsolescence September 1st 2013</b> <b>End of Support September 1st 2018</b>
<b>Easy PW</b>	Application Heads Easy PW ... with Swivel Device	<b>CZ</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>SW</b>	7146540E 7105109E 7156910E 397532E 7179785E 7119261E 7156626E	MA	(317102) or (317107)	
<b>EB</b>	Hot Melt Application Heads Series EB	<b>EN</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>SP</b> <b>SW</b>	409496E 409401E 409497E 412624E 464976E 412623E	MA	(317102) or (317107)	

A-6 - 8

## Nordson Engineering Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>EB Flex</b>	Hot Melt Applicators EB Flex (Title - version_05: EB60 Flex)	<b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>PO</b> <b>SP</b>	7560040_07 7179567_08 7580161_07 7560041_07 7179534_08 7179566_03 7560766_04* 7179587_07 7560516_07 7192845_07	MA	(317102) or (317107)	* available at Nordson K.K.
<b>EB Flex</b>	Hot Melt Applicators EB Flex- Parts List -	<b>EN</b>	7192555_07	PA	(317102) or (317107)	
<b>EB Flex</b>	EB Flex OEM Integration Handout	<b>EN</b>	7560692_03	IN	(317102) or (317107)	<b>Created by Application Development, Andrea Poggi</b>
<b>EB Flex</b>	EB Flex OEM Integration IMA Machines Handout	<b>EN</b>	7580977_01	IN	(317102) or (317107)	<b>Created by Application Development, Andrea Poggi</b>
<b>EB ... V</b> <b>EB ... V-M</b>	Hot Melt Application Heads EB ... V EB ... V-M	<b>DA</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>SW</b>	458243I 458009_11 458244I 447671_11 413074_11 7192546I 458245_11 464969F 458246I 7560537_11 7580340_11 7169225I 7135317_11 447724I 458247I	MA	(317102) or (317107)	

A-6 - 9

## Nordson Engineering Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
EF60 V	Applicator with Diamant Nozzle	EN GE RU	7179900_01 7179811_01 7580675_01	MA	(317102) or (317107)	
EF60 V	Applicator with Diamant Nozzle - Parts List -	EN	7179656_01	PA	(317102) or (317107)	
EF60 V	EF60V OEM Integration Handout	EN	7580979_01	IN	(317102) or (317107)	<b>Created by Application Development, Andrea Poggi</b>
EP 10 / EP 10 FL / EP 10 D / EP 10D-FL	Suction Stem Control Module EP 10 / EP 10 FL EP 10 D / EP 10 D-FL	BU CZ DA DU EN FI FR GE HU IT NO PL PO SP SW TU	7135432D 464741D 464747D 412767D 412768D 464841D 458012D 412747D 7105615D 412769D 464761D 7156350D 464890D 458010D 412905D 397127B	MA	(317102) or (317107)	
EP 10	Repair Kit Control Module EP 10	EN GE	447730_06 447729_06	MA	(317102) or (317107)	
EP 11	Application Head	EN GE	7156157A 7156151A	MA	(317102) or (317107)	<b>Only available for special EP 11 P/N 7153753</b>

A-6 - 10

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
EP 11/ EP 11 N/ EP 12 V/ EP 12 L/ EP 12 RV	Hot Melt Applicators EP 11 / EP 11 N EP 12 V / EP 12 L / EP 12 RV	BU CZ DA DU EN FI FR GE GR HU IT NO RU PL PO SP SW TU	7135431G 7560289G 464762G 403265G 317091G 213076G 403082G 317092G 7580553G 7105613G 407470G 464796G 7146738G 7156349G 405051G 403251G 447755G 397126G	MA	(317102) or (317107)	
EP 15	Lotion Application Head EP 15	CZ EN FR GE IT SK SP	464740A 412935A 458011A 412867A 213007A 7105624A 413040A	MA	(317102) or (317107)	
EP 23/ EP 23T	Electropneumatic Hot Melt Application Heads EP 23 / EP 23T	GE	405018A	MA	(317102) or (317107)	<b>End of support 04/2016</b>

A-6 - 11

## Nordson Engineering Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>EP 25/ EP 25 S/ EP 25 SD</b>	Electropneumatic Hot Melt Application Heads EP 25 / EP 25 S / EP 25 SD	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>PO</b> <b>SK</b> <b>SL</b> <b>SP</b> <b>SW</b>	7105253A 409141A 409174A 409017A 409069A 409122A 405019A 7105439A 7105485A 409134A 213124A* 7156365A 464782A 7105467A 7560665A 409217A 397037A	MA	(317102) or (317107)	* available at Nordson K.K.
<b>EP 26 SD</b>	Electropneumatic Hot Melt Application Head EP 26 SD	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>SP</b> <b>SW</b>	213466A 409097A 409098A 405020A 409099A 7119260A 213285A 7105556A	MA	(317102) or (317107)	
<b>EP 26-8 SD</b>	Electropneumatic Hot Melt Application Head EP 26-8 SD	<b>GE</b> <b>IT</b>	7135166A 7135177A	MA	(317102) or (317107)	
<b>EP 30</b>	Hot Melt Application Head EP 30	<b>EN</b> <b>GE</b> <b>IT</b>	397191B 397140B 397219B	MA	(317102) or (317107)	

A-6 - 12

## Nordson Engineering Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
EP 34/ EP 34 S/ EP 34 SD	Electropneumatic Hot Melt Application Heads EP 34 / EP 34 S / EP 34 SD	DU EN FI FR GE IT NO PL RU SP SW	213212A 409090A 7146327A 409091A 405021A 409092A 7593335A 7156143A 7580166A 7146085A 7179316A	MA	(317102) or (317107)	
EP 45	Electropneumatic Hot Melt Application Head EP 45	CZ DU EN FI FR GE GR HU IT JA PL PO RU SP TU	7119713B 409013B 403228C 397523B 409121C 315705C 213840B 7105411B 315808C 464868B* 458270B 315706A 7105351B 213386C 397124B	MA	(317102) or (317107)	<b>End of Support effective November 1st 2017. For diverse replacement products depending on specific applications please refer to the End of Support Notice on ADHinfo.com</b>  * available at Nordson K.K.
EP 45	Control Module EP 45	DU EN FR GE IT SP	7105704A 7105703A 7105705A 7105702A 7105706A 7105707A	MA	(317102) or (317107)	<b>End of Support effective November 1st 2017. For diverse replacement products depending on specific applications please refer to the End of Support Notice on ADHinfo.com</b>



A-6 - 13

## Nordson Engineering Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
EP 45	Feed Valve EP 45	DU FR GE	409170A 409185A 409105A	MA	(317102) or (317107)	<b>End of Support effective November 1st 2017. For diverse replacement products depending on specific applications please refer to the End of Support Notice on ADHinfo.com</b>
EP 48-BoD	Hot Melt Applicators Series EP 48-BoD	EN FR GE	7169856_02 7169862_02 7169838_04	MA	(317102) or (317107)	
EP 48-BoD	Hot Melt Applicators Series EP 48-BoD - Parts List -	EN	7179006_04	PA	(317102) or (317107)	
EP 48 Pro	Hot Melt Applicators Series EP48 Pro	EN FR GE	7560606_02 7560773_02 7560542_03	MA	(317102) or (317107)	
EP 48 Pro	Hot Melt Applicators Series EP48 Pro - Parts List -	EN	7560880_01	PA	(317102) or (317107)	
EP 48 Pro	Instructions for EP 48 Pro Transport Frame (P/N 7561630 „EP48 Pro-angled“, P/N 7561631 „EP48-Pro-straight“)	EN GE	7560871_02 7560827_02	IN	(317102) or (317107)	
EP 48 Pro / VersaPail	EP48 Pro - System Layout and Interface	EN	7580414_01	IN	(317102) or (317107)	
EP 48-V/ EP 48 Pro	Trolleys for EP 48-V/ EP48 Pro (Title Version G: Trolleys for EP 48-V)	BU DU EN FR GE HU IT PL SP	7135435E 7179231G 7119707_09 7135152_08 7119703_09 7156649E 7156202G 7179802G 7135045G	IN	(317102) or (317107)	

A-6 - 14

## Nordson Engineering Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>EP 48-V</b> <b>EP 48-VL</b>	Hot Melt Application Head EP 48-V/ EP 48-VL	<b>BU</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>SK</b> <b>SP</b>	7135429M 7135525M 213399M 213362M 458361M 7135150M 213364M 407307M 213373M 464869I* 213355M 213254M 213109M 7146165M 213315M	MA	(317102) or (317107)	<b>Replaced by UL Models</b>            <b>* available at Nordson K.K.</b>
<b>EP 48-VM</b>	Hot Melt Application Head EP 48-VM	<b>DU</b> <b>EN</b> <b>GE</b>	7156806C 7146651D 7146083D	MA	(317102) or (317107)	<b>Replaced by UL Models</b>
<b>EP 48-VSB</b>	Hot Melt Appilcation Head EP 48-VSB	<b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>SP</b>	7135899B 7135898B 7135820B 7146535B 7146681B* 7146732B	MA	(317102) or (317107)	<b>Replaced by UL Models</b>      <b>* available at Nordson K.K.</b>
<b>EP 48-VSB</b>	Extension Side Gluing for EP 48-VSB ( P/N 7133305 for EP48-VSB, P/N 7173132 for EP48-BoD)	<b>EN/GE</b>	7156055_03	IN	(317102) or (317107)	<b>Replaced by UL Models</b> <b>Bilingual document, therefore one P/N only</b>
<b>EP 48-V (UL Models)</b>	Hot Melt Applicators Series EP 48-V ( UL Models)	<b>CZ</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>JA</b> <b>PO</b>	7156476_06 7156402_06 7156473_08 7156569_08 7156348_08 7169423D* 7560804_08	MA	(317102) or (317107)	            <b>* available at Nordson K.K.</b>

A-6 - 15

## Nordson Engineering Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>EP 48-V (UL Models)</b>	Hot Melt Application Head EP 48-V (UL Design) - Parts List -	<b>EN JA</b>	7156338_08 7169424C*	PA	(317102) or (317107)	<b>* available at Nordson K.K.</b>
<b>EP 51</b>	Electropneumatic Hot Melt Application Head EP 51	<b>DA DU EN FR GE IT JA PO SP SW</b>	7105709B 409283B 409282B 409284B 315703B 315753B 464870B* 315704B 409285B 409286B	MA	(317102) or (317107)	<b>End of Support 07/2016</b>  <b>* available at Nordson K.K.</b>
<b>EP 51</b>	Electro-pneumatic Unheated Coating Head	<b>EN GE SP</b>	7135555A 7135522A 7135620A	MA	(317102) or (317107)	<b>End of Support 07/2016</b>
<b>EP51-01</b>	Application Heads EP51-01 for Edge Banding	<b>GE</b>	397823B	MA	(317102) or (317107)	<b>End of Support 07/2016</b>
<b>EP 51 PW</b>	Electropneumatic Hot Melt Application Head EP 51 PW	<b>EN FR GE SP SW</b>	412734A 397428A 412712A 412743A 413043A	MA	(317102) or (317107)	
<b>EP 52</b>	Hot Melt Application Head Series EP 52	<b>EN FR GE IT JA SP SW</b>	403021B 407468B 317212B 397255B 464871A* 464783B 397264B	MA	(317102) or (317107)	<b>End of Support 07/2016</b>  <b>* available at Nordson K.K.</b>

A-6 - 16

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>EP 310 / EP 310P</b>	Small Metering Unit for PUR Cartridges EP 310 / EP 310 P	<b>EN</b> <b>GE</b> <b>SP</b>	409042A 407453A 409065A	MA	(317102) or (317107)	
<b>GMG</b>	Volume Metering Head GMG	<b>CH</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SK</b> <b>SL</b> <b>SP</b> <b>SW</b>	7560946J 464929J 7156422H 7146227J 405103J 213376J 405027J 405025J 407043J 7146534H 7119267J 7119420J 7179543J 7119351E 7135027E 458414J 413047E	MA	(317102) or (317107)	<b>Former product title VDK</b>
<b>GMG</b>	Electrical Cabinet for Volume Metering Head GMG	<b>CZ</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>SP</b> <b>SW</b>	7105112F 405065F 213377F 405028F 405026F 407499F 7119268F 458415F 413048F	MA	(317102) or (317107)	<b>Former product title VDK</b>

A-6 - 17

## Nordson Engineering Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>GMG</b>	Electrical Cabinet for Volume Metering Head GMG - Model with PLC -	<b>CZ</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>PL</b> <b>PO</b> <b>SK</b> <b>SL</b>	7119289D 7105929D 7135194D 7119192D 7105669D 7135257D 7119421B 7119352B 7135028C	MA	(317102) or (317107)	
<b>GMG</b>	Electrical Cabinet for Volume Metering Head GMG - Model with Volume Display -	<b>CZ</b> <b>EN</b> <b>FR</b> <b>GE</b>	7135648F 7135818F 7135605E 7135147F	MA	(317102) or (317107)	
<b>GMG</b>	Electrical Cabinet for Volume Metering Head GMG - Model April 2008 and later -	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>SP</b>	7146282E 7156423D 7146397E 7146393D 7146607D 7146904E 7146204E 7146537D 7156789E 7156557E 7146267D	MA	(317102) or (317107)	<b>Obsolete!</b> <b>End of Support 04/2013</b>

A-6 - 18

## Nordson Engineering Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>GMS</b>	Electrical Cabinet GMS - Generation II for Volume Metering Head GMG	<b>CH</b> <b>CZ</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b>	7560947_05 7179344_05 7192426_05 7179354_05 7192787_03 7179368_05 7179325_05 7560372_04 7192676_05 7560604_05 7179544_03 7560371_05	MA	(317102) or (317107)	<b>Obsolete!</b> <b>End of Support 04/2021</b>
<b>GMS</b>	Electrical Cabinet GMS - Generation III for Volume Metering Head GMG	<b>CZ</b> <b>GE</b> <b>IT</b>	7593436_01 7593378_01 7593490_01	MA	(317102) or (317107)	
<b>Harmony</b>	Hot Melt Applicators Harmony	<b>GE</b>	7593242_01	MA	(317102) or (317107)	
<b>Harmony</b>	Hot Melt Applicators Harmony - Parts List -	<b>GE</b>	7593243_01	PA	(317102) or (317107)	
<b>LabelCoat</b>	LabelCoat Slot Gun	<b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b>	7105502B 7135061B 7105449B 7135476B	MA	(317102) or (317107)	
<b>LabelCoat MB II</b>	LabelCoat MB II Horizontal Slot Applicator	<b>GE</b>	7560661_01	MA	(317102) or (317107)	
<b>LabelCoat MB II</b>	LabelCoat MB II Horizontal Slot Applicator - Parts List -	<b>GE</b>	7560662_01	PA	(317102) or (317107)	

A-6 - 19

## Nordson Engineering Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LPW	Application Heads LPW	GE	7119868A_01	MA	(317102) or (317107)	<b>Preliminary version ! End of support 10/2013</b>
MG 11	Hot Melt Application Head MG 11	DU EN GE IT SW	412784B 412785B 412715B 412786B 412901B	MA	(317102) or (317107)	<b>End of Support 12/2013</b>
MG 11	Electrical Cabinet	DU EN GE IT SW	412736B 412735B 412716B 412737B 412902B	MA	(317102) or (317107)	<b>End of Support 12/2013</b>
MG 95	Applicator	FR GE	7192573_01 7192493_01	MA	(317102) or (317107)	
MMG	Melt Metering Gun MMG	GE	7135153D	MA	(317102) or (317107)	
MP 16 / MP 16S / MP 16 SD	Assembly Handgun MP 16 / MP 16 S / MP 16 SD	EN FR GE	409143A 409173A 405014A	MA	(317102) or (317107)	<b>End of Support 10/2013</b>
MP 17 / MP 17 S / MP 17 SD	Assembly Handgun MP 17 / MP 17 S / MP 17 SD	EN FR GE	412608A 7119339A 405015A	MA	(317102) or (317107)	<b>End of Support 10/2013</b>
MP 18 / MP 18S / MP 18 SD	Assembly Handgun MP 18 / MP 18 S / MP 18 SD	GE	405016A	MA	(317102) or (317107)	<b>End of Support 10/2013</b>

A-6 - 20

## Nordson Engineering Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>MP 300, MP 300 S, MP 300 P, MP 350, MP 350 S</b>	Assembly Handguns MP 300, MP 300 S, MP 300 P MP 350, MP 350 S	<b>EN FR GE SP</b>	213151C 464918C 405017C 7105695C	MA	(317102) or (317107)	<b>End of Support 10/2013</b>
<b>PatternCoat</b>	Applicators Series PatternCoat (PCT)	<b>DU EN FR GE IT PL SP</b>	7560302_10 7135308_10 7135590_08 7135247_10 7560967_10 7192361_08 7560708_10	MA	(317102) or (317107)	
<b>PatternCoat</b>	Applicators Series PatternCoat (PCT) - Parts List -	<b>EN</b>	7593401_01	PA	(317102) or (317107)	
<b>PF...V PV...V-HT</b>	Hot Melt Application Head PF...V/ PF...V-HT	<b>DU EN FI GE IT JA</b>	397926D 397949_05 397979D 397889_05 7135324D 7119307A*	MA	(317102) or (317107)	<b>* available at Nordson K.K.</b>
<b>PN 18</b>	Electropneumatic Hot Melt Application Heads PN 18	<b>EN FR GE</b>	213558A no P/N 213541A	MA	(317102) or (317107)	<b>End of Support 10/2014</b>
<b>PU...</b>	Application Heads PU...	<b>EN GE PL RU</b>	7135888A 7135460A 7135946A 7146646A	MA	(317102) or (317107)	<b>Product Obsolescence September 1st 2017</b>



A-6 - 21

## Nordson Engineering Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
PW ...	Hot Melt Application Head Series PW...	CZ DA DU EN FI FR GE IT PL RU SP SW	7156142I 458437I 458016I 458013I 458022I 213008I 412882I 464909I 397231I 397388I 464811I 458014I	MA	(317103) or (317106)	<b>Product Obsolescence September 1st 2017</b>
PW ...	Retrofitting Right/Left of Hot Melt Application Heads PW 200 PW 350 PW 500 PW 800	EN GE	213048A 213041A	MA	(317102) or (317107)	<b>Product Obsolescence September 1st 2017</b>
PWII-...	PWII... Applicators	CH EN FR GE HU IT LI PL RO RU SP	7179319_10 7135328_10 7135704_10 7119937_10 7156459B 7135788B 7560769_10 7135747B 7169224_10 7135677B 7135676_10	MA	(317102) or (317107)	<b>Product Obsolescence September 1st 2017</b>
PWII-...	PWII... Applicators P/N 7407037, 7407038 - Parts List -	EN	7179725_01	PA	(317102) or (317107)	<b>Product Obsolescence September 1st 2017</b>
PWII-...HC	PWII-...HC Applicator P/N 7165538	EN GE	7169267A 7169266A	MA	(317102) or (317107)	<b>Product Obsolescence September 1st 2017</b>

A-6 - 22

## Nordson Engineering Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
PWIII	PWIII Applicator P/N 7161049	GE	7156456A	MA	(317102) or (317107)	
PWIII	PWIII Applicator - Model with Adjustable Application Width	DA EN GE IT	7169356C 7169355C 7156701_04 7169514C	MA	(317102) or (317107)	
PWIII	PWIII Applicator - Model with Shim Plate (P/N 7165227)	GE SW	7169127_03 7169171_03	MA	(317102) or (317107)	
PWIII	PWIII Applicator - Parts List -	EN	7156755A	PA	(317102) or (317107)	
PW-S	PW-S Applicators	EN GE GR PO	7169663A1 7169245_03 7169262A0 7169403A1	MA	(317102) or (317107)	
PW-S	PW-S Parts List	EN	7169987_01	PA	(317102) or (317107)	
RA 80	Coating Wheel RA 80	GE	213378A	MA	(317102) or (317107)	
RA 80	Coating Whee RA 80 Double-sided Bearing	DU EN GE IT PL SW	403266C 403108C 315826C 405041C 7119870C 409079C	MA	(317102) or (317107)	

A-6 - 23

## Nordson Engineering Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
RA 80	Coating Wheel RA 80 Single-sided Bearing	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>SW</b>	7135156C 7105506C 407461C 405054C 405105C 317165C 405006C	MA	(317102) or (317107)	
RA 80	Coating Wheel RA 80 Single-sided Bearing With Spinner Rotating Bar	<b>EN</b> <b>GE</b> <b>IT</b> <b>SP</b>	409281C 409234C 7135154C 447708C	MA	(317102) or (317107)	
RA 80	RA 80 Wheel Applicator Station with Additional Tank for Bag Application	<b>EN</b> <b>GE</b>	407042A 407041A	MA	(317102) or (317107)	
RA 80	Maintenance of Wheel Applicator RA 80	<b>GE</b> <b>SW</b>	409199A 409201A	OP	(317102) or (317107)	
ROC	Applicator ROC	<b>GE</b>	7179980_01	MA	(317102) or (317107)	
SB60 - BoD	Hot Melt Applicators SB60 - BoD	<b>EN</b> <b>FR</b> <b>GE</b> <b>JA</b> <b>NO</b> <b>SP</b> <b>SW</b>	7179925_05 7179982_05 7179789_05 7192216_05 7192232_05 7192205_05 7192206_05	MA	(317102) or (317107)	
SB60 - BoD	Hot Melt Applicators SB60 - BoD - Parts List -	<b>EN</b>	7179970_07	PA	(317102) or (317107)	

A-6 - 24

## Nordson Engineering Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>SB60V-BoD</b>	PUReOne OEM Integration Handout	<b>EN</b>	7580978_05	IN	(317102) or (317107)	<b>Created by Application Development, Andrea Poggi</b>
<b>SN 30</b>	Screen Printer Application Head SN 30	<b>EN GE</b>	412978A 412932A	MA	(317102) or (317107)	<b>End of Support 02/2014</b>
<b>SPEED-COAT</b>	Hot Melt Applicators SPEED-COAT	<b>CZ DA DU EN FR GE GR HU IT JA NO PL PO RU SK SL SP SW TU</b>	7169875_08 7560510_08 397351_08 213980_08 7105287_08 213470_08 7146142_06 7560797_08 7105074_08 7156733_05* 7560388_08 7105416_08 7560397_08 7135948_08 7105391_08 7146515C 213978_08 7135227_08 7192922_08	MA	(317102) or (317107)	<b>* available at Nordson K.K.</b>
<b>SPEED-COAT</b>	Hot Melt Applicators Speed-Coat - Parts List -	<b>EN JA</b>	7156778_04 7179148_02*	PA	(317102) or (317107)	<b>* available at Nordson K.K.</b>

A-6 - 25

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>SPEED-COAT</b>	Suction Stem Control Module Speed-Coat	<b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>SP</b> <b>SW</b>	213689_06 213680_06 213686_06 213896A 213685_06 213482_06 213693_06 7179147_05* 213667_06 7169617_06 213661_06 213674_06 213699_06	MA	(317102) or (317107)	<b>End of Support 12/2013 (Generation I only)</b>          <b>* available at Nordson K.K.</b>
<b>SPEED-COAT</b>	Installation Notes Speed-Coat Solenoid Valves	<b>EN/ FR/ GE/ IT/ SP</b>	397072_03	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>TRANSFER DISK</b>	Transfer Disk	<b>EN</b> <b>GE</b> <b>SP</b>	7119617D 7119123D 7135134C	IN	(317102) or (317107)	<b>End of Support 10/2013</b>
<b>TRANSFER DISK</b>	System Description Application System with Transfer Disk	<b>EN</b> <b>GE</b> <b>SP</b>	7119616F 7119124F 7135133F	MA	(317102) or (317107)	<b>End of Support 10/2013</b>

A-6 - 26

## Nordson Engineering Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>TRIO</b>	Trio Hot Melt Applicators	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SK</b> <b>SP</b> <b>SW</b>	7580626_04 7560412_04 7560846_04 7560027_04 7560809_04 7192645_04 7192969_04 7560963_04 7560823_04 7560676_04 7560874_04 7560089_04 7580940_04	MA	(317102) or (317107)	
<b>TRUECOAT</b>	Hot Melt Applicators TrueCoat	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SK</b> <b>SL</b> <b>SP</b> <b>SW</b> <b>TU</b>	7560291_11 7156826_11 7135075_11 7119681_11 7146799_11 7119680_11 7105415_11 7146143_11 7119688_11 7135031A* 7192249_11 7146903_11 7156376_11 7135949_11 7135501_11 7146516_11 7119682_11 7580942_11 7192923_11	MA	(317102) or (317107)	* available at Nordson K.K.

A-6 - 27

## Nordson Engineering Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
TRUECOAT	Hot Melt Applicators TrueCoat HP	CH EN FI GE IT PO RU SP	7560898_04 7179962_04 7580045_04 7179781_04 7593399_04 7192891_04 7593611_04 7192285_04	MA	(317102) or (317107)	
TRUECOAT	Hot Melt Applicators TrueCoat HP with Adjustable Application Width	EN FR GE IT PL PO	7169655_05 7593605_05 7169607_05 7179195_05 7179213_05 7192830_05	MA	(317102) or (317107)	
TRUECOAT	Hot Melt Adhesive Applicators TrueCoat - Parts List -	EN	7146948_09	MA	(317102) or (317107)	
TRUECOAT	Hot Melt Applicator TrueCoat (7144549, 7153564)	EN FR GE IT	7146787A 7146766B 7146762B 7146905B	MA	(317102) or (317107)	
TRUECOAT	Hot Melt Applicator TrueCoat with Throttle Screw	EN GE	7156487B 7156373B	MA	(317102) or (317107)	
TRUECOAT	Applicators in the Series TC-FS Applicators	GE	7169281_02	MA	(317102) or (317107)	
TRUECOAT	Applicators in the Series TC-FS - Parts List -	EN	7179219_01 <sub>a</sub>	PA	(317102) or (317107)	<b>Preliminary Version!</b>

A-6 - 28

## Nordson Engineering Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>TRUECOAT</b>	Applicators in the Series TC-FS Generation II with Motor-driven Application Width Adjustment and Grammage Control (Option)  (Title version_02+03: Applicators in the Series TC-FS Generation II with Grammage Control (Option) (Title version_01: Models RET, EVA/PO, PUR)	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>LI</b> <b>RU</b> <b>SP</b> <b>SW</b>	7179881_01 7179884_09 7560478_07 7179813_09 7179885_09 7580906_08 7593326_09 7560242_08 7192861_09	MA	(317102) or (317107)	
<b>TRUECOAT</b>	Applicators in the Series TC-FS Generation II with Motor-driven Application Width Adjustment and Grammage Control (Option) - Parts List -	<b>EN</b>	7192556_06	PA	(317102) or (317107)	
<b>TRUECOAT</b>	Applicators in the Series TC-FS Generation II with Hand Wheel	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>SP</b>	7192875_01 7192854_03 7560990_03 7192851_03 7560988_03 7560008_03 7560989_03	MA	(317102) or (317107)	
<b>TRUECOAT</b>	Applicators in the Series TC-FS Generation II with Hand Wheel - Parts List -	<b>EN</b>	7560667_01	PA	(317102) or (317107)	
<b>TRUECOAT</b>	TrueCoat HP - Against back up roll OEM Integration Handout	<b>EN</b>	7593214_01	IN	(317102) or (317107)	<b>Created by Application Development, Gerd Ostermann</b>
<b>TRUECOAT</b>	TrueCoat HP - Against web tension OEM Integration Handout	<b>EN</b>	7593281_01	IN	(317102) or (317107)	<b>Created by Application Development, Gerd Ostermann</b>
<b>TRUECOAT</b>	Window of Operation for TrueCoat Applicator TCHP and TCHP-RB	<b>EN</b>	7593277_01	IN	(317102) or (317107)	<b>Created by Application Development, Gerd Ostermann</b>



A-6 - 29

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>TRUECOAT</b>	TrueCoat FS-FL OEM Integration Handout	<b>EN</b>	7580572_02	IN	(317102) or (317107)	<b>Created by Application Development, Ralf Dittmann</b>
<b>TRUECOAT</b>	TrueCoat FS-HG OEM Integration Handout	<b>EN</b>	7580571_01	IN	(317102) or (317107)	<b>Created by Application Development, Ralf Dittmann</b>
<b>TRUECOAT</b>	TrueCoat FS-PW OEM Integration Handout	<b>EN</b>	7580160_02	IN	(317102) or (317107)	<b>Created by Application Development, Ralf Dittmann</b>
<b>TRUFLOW</b>	TruFlow Applikator UTA... Flow Divider and Flow Meter (Title version A: TruFlow Applikator UTA...)	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SK</b> <b>SP</b> <b>SW</b> <b>TU</b>	7146854_02 7156643_02 7169106_02 7146808_02 7169545_02 7146417_02 7169377_02 7560512_02 7156499_02 7179697_02 7560674_02 7179350_02 7169133_02 7560930_02 7560259_02	MA	(317102) or (317107)	

A-6 - 30

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>TRUFLOW</b>	TruFlow Flow Detection System	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SK</b> <b>SP</b> <b>SW</b>	7593153_02 7560273_02 7560336_02 7179720_02 7192260_02 7179933_02 7192290_02 7560513_02 7580249_02 7580169_02 7560899_02 7192987_02 7192104_02 7560931_02	MA	(317102) or (317107)	
<b>TRUFLOW</b>	Electrical Cabinet for TruFlow Application System	<b>CZ</b> <b>EN</b> <b>GE</b>	7146855A_1 7146809A_1 7146416A_1	MA	(317102) or (317107)	
<b>TRUFLOW</b>	Electrical Cabinet for TruFlow Application System Generation II	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>SK</b> <b>SP</b>	7169350_03 7156642_03 7169076_03 7156170_03 7169546_03 7156096_03 7179234_03 7156500_03 7179698_03 7192130_03 7169882_03	MA	(317102) or (317107)	
<b>UM</b>	Universal Application Head UME... and UMU...	<b>EN</b> <b>FR</b> <b>GE</b> <b>RU</b>	7105687A 7119381A 7105558A 7192814A	MA	(317102) or (317107)	

A-6 - 31

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>VDK</b>	VDK-MAXI Applicator	<b>EN</b> <b>FR</b> <b>GE</b> <b>PL</b>	7593515_01 7593407_01 7560229_01 7560237_01	MA	(317102) or (317107)	
<b>VDK</b>	VDK-MIDI Applicator	<b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>IT</b>	7179780_01 7192333_01 7580453_01 7179773_01 7593376_01 7560411_01	MA	(317102) or (317107)	
<b>VDK</b>	VDK-MIDI Applicator (P/N 7185070)	<b>CH</b> <b>EN</b>	7179496_01 7179506_01	MA	(317102) or (317107)	
<b>VDK</b>	VDK-MIDI Volume Metering Head (P/N 7552265)	<b>JA</b>	7169614_01	MA	(317102) or (317107)	

A-7 - 1

## Nordson Engineering Hot Melt Products (sorted by Model)

### Systems - Automotive

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Heated Pro-Meter IV System	CH EN	412919A 413041A	MA	(317102) or (317107)	
	Heated Pro-Meter IV System - System Description	EN	412849A	MA	(317102) or (317107)	
	FlowCoat Pressure Controller	GE	213090E	IN	(317102) or (317107)	
<b>Pro-Flo</b>	Pro-Flo Controller	DU FR GE IT SP SW	292873A 292875A 292872A 292877A 292874A 292896A	OP	(317102) or (317107)	<b>EDB 25-11</b>
<b>Pro-Flo</b>	Pro-Flo Controller (European Version)	DU FR GE SP SW	315859A 315830A 315831A 315861A 315833A	MA	(317102) or (317107)	<b>EDB 25-13</b>
<b>Pro-Flo</b>	Pro-Flo System	DU	292870	IN	(317102) or (317107)	
<b>Pro-Flo</b>	Pro-Flo System	EN FR GE IT SP SW	269847 269848 269849 269850 269852 269851	OP	(317102) or (317107)	
<b>Pro-Flo</b>	Pro-Flo System Dispensing Gun	FR SP	315860B 403062C	MA	(317102) or (317107)	<b>EDB 26-9</b>

A-7 - 2

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Systems - Bookbinding*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Instructions for Kit-EP48-V light barrier P/N 7147780	EN/ GE	7156332B	IN	(317102) or (317107)	<b>Bilingual document, therefore one P/N only</b>
	Spine Gluing with Application Head EP 48-V and PUR Hot Melt Adhesive	BU CZ DA DU EN FI FR GE IT JA NO PL PO SK SP	7135428C 7146013C 213873B 213813B 213574C 7135151C 213787B 213671C 213801B 397987C* 213898B 397213C 213811C 7135408C 213825C	IN	(317102) or (317107)	<b>* available at Nordson K.K.</b>
	Bookbinding System with Bulk Melter BM 20 / BM 200 - Initial Startup -	EN GE JA SP	213416B 213337B 397988A* 7105562B	IN	(317102) or (317107)	<b>* available at Nordson K.K.</b>
	Bookbinding System with Bulk Melter BM 20 / BM200 - System Description -	EN GE JA SP	213417B 213338B 397989B* 7105563B	OP	(317102) or (317107)	<b>* available at Nordson K.K.</b>

A-7 - 3 **Nordson Engineering Hot Melt Products (sorted by Model)**

***Systems - Bookbinding***

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Bookbinding System with Bulk Melter DuraPail / DuraDrum - Initial Startup -	<b>BU</b> <b>CZ</b> <b>DU</b> <b>EN</b> <b>ES</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>SK</b> <b>SP</b>	7135424B 7146011D 7146111D 7119592D 7146244D 7135053D 7119988D 7119824D 7146216D 7119985D 7156607D 7135345D 7146400D 7146166D 7119968D	IN	(317102) or (317107)	
	Book Spine Gluing with Bulk Melter DuraPail / DuraDrum - System Description -	<b>BU</b> <b>CZ</b> <b>DU</b> <b>EN</b> <b>ES</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>SK</b> <b>SP</b>	7135425B 7146012B 7146112B 7119593B 7146243B 7135054B 7119989B 7119823B 7146215B 7119986B 7156606B 7135346B 7146401B 7135407B 7119969B	OP	(317102) or (317107)	

A-7 - 4

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Systems - Bookbinding*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Book Binding System with Melter MC 20 or MC 4420 - Initial Startup -	DA DU EN FR GE IT JA NO PO SP	213512F 213431F 458358F 213424F 458195F 213405F 7119721F 213426F 213112F 213313F	IN	(317102) or (317107)	
	Book Binding System with Melter MC 20 or MC 4420 - System Description -	DA DU EN FR GE IT JA NO PO SP	213513F 213432F 447764F 213425F 447664F 213406F 7119722F 213427F 213113F 213314F	OP	(317102) or (317107)	
	Book Binding System with ProBlue - Initial Startup -	EN GE NO	7146019A 7135931A 7146099A	IN	(317102) or (317107)	
<b>EP 48 PRO</b>	EP 48 PRO Spine Gluing Applicator - System operation card -	EN GE	7560864_01 7580443_01	OP	(317102) or (317107)	
<b>EP 48 PRO</b>	EP 48 PRO Spine Gluing Applicator (KM200) - System operation card -	EN	7560865_01	OP	(317102) or (317107)	
<b>PB 90</b>	Book Binding System PB 90 - System Description -	EN GE	317187A 315924A	MA	(317102) or (317107)	<b>When ordering, please state Unit Type and Serial Number</b>

A-7 - 5

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Systems - Bookbinding*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
PB 90	PB 90 - Operating Console	EN GE	317188A 315925A	MA	(317102) or (317107)	<b>When ordering, please state Unit Type and Serial Number</b>
PB 90	Bulk Melter BM 506 for PB 90	EN GE	317189A 315926A	MA	(317103) or (317106)	<b>When ordering, please state Unit Type and Serial Number</b>
PB 90	Bulk Melter BM 5506 for PB 90	EN	407324A	MA	(317103) or (317106)	<b>When ordering, please state Unit Type and Serial Number</b>
PB 90	Wheel Applicator Station	EN GE	317190B 315927B	MA	(317102) or (317107)	<b>When ordering, please state Unit Type and Serial Number</b>
PB 90	Microset <sup>®</sup> MultiScan Control System	EN GE	317191A 315928A	MA	(317102) or (317107)	<b>When ordering, please state Unit Type and Serial Number</b>
PB 90	PB 90 Trolley Starbinder	EN FR GE	317157A 317174A 315936A	MA	(317102) or (317107)	<b>When ordering, please state Unit Type and Serial Number</b>
PB 90	PB 90 Trolley Normbinder	EN FR GE	317158A 317175A 315937A	MA	(317102) or (317107)	<b>When ordering, please state Unit Type and Serial Number</b>
PB 90	PB 90 Trolley Universal	EN FR GE	403100A 403101A 403099A	MA	(317102) or (317107)	<b>When ordering, please state Unit Type and Serial Number</b>
PB 90	PB 90 Trolley Universal with Eccentric Vertical Adjustment	EN FR GE	317159A 317176A 315938A	MA	(317102) or (317107)	<b>When ordering, please state Unit Type and Serial Number</b>



A-7 - 6

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Systems - Bookbinding*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
SDS	Spindle Metering Device Series SDS	EN FL GE	412911C 412912A 412846C	MA	(317102) or (317107)	
SDS	Spindle Metering System SDS - System Description -	EN FL GE	412913B 412914A 412847B	MA	(317102) or (317107)	

A-7 - 7

## Nordson Engineering Hot Melt Products (sorted by Model)

### Systems - Gasketing

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Foam Mix</b>	System Description FoamMix / BM Gasketing System AGT Standard System	<b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	317253B 315931B 315836B 315923B 403053B	MA	(317103) or (317106)	
<b>Foam Mix</b>	FoamMix / BM Gasketing Unit	<b>GE</b>	458219A	SU	(317102) or (317107)	<b>Addition to P/N 315836B</b>
<b>Foam Mix</b>	System Description FoamMix / BM-Gasketing Unit Tandem System	<b>FR</b> <b>GE</b> <b>IT</b>	315710A 292948A 315922A	MA	(317103) or (317106)	
<b>Foam Mix</b>	Foam Mix System	<b>IT</b>	292789A	IN	(317102) or (317107)	
<b>Foam Mix</b>	FoamMix / Gasketing Unit - Cold - System Description	<b>GE</b> <b>IT</b>	407230A 407231A	MA	(317103) or (317106)	
<b>Foam Mix</b>	FoamMix / BM Gasketing Unit - System Description	<b>GE</b>	458211A	MA	(317102) or (317107)	
<b>Foam Mix</b> <b>9400 Series</b>	Foam Mix 9400 Systems	<b>EN</b> <b>GE</b>	284066 284065	OP	(317102) or (317107)	

A-7 - 8 **Nordson Engineering Hot Melt Products (sorted by Model)**

***Systems - Moulding***

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>WS 100 Series</b> <b>WS 101/</b> <b>WS 102/</b> <b>WS 103/</b> <b>WS 104</b>	Casting System Series WS 100 with Control Module easy	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>PO</b> <b>SP</b>	464812 I 315853 I 317099 I 317017 I 409475 I 213265 I* 7105308I 464813 I 464798 I	MA	(317102) or (317107)	<b>When ordering, please state                      Unit Type and Serial Number</b>  * available at Nordson K.K.
<b>WS 200 Series</b> <b>WS 201/</b> <b>WS 202</b>	Casting System Series WS 200	<b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>SP</b>	317290B 403042B 317179B 412975B 464781B 317246B	MA	(317102) or (317107)	<b>When ordering, please state                      Unit Type and Serial Number</b>

A-8 - 1

## Nordson Engineering (Meltex) Product Line (sorted by Model)

### Coating Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Roll Coater	EN FR GE	412709A 407451A 458325A	MA	(317102) or (317107)	Italian source - P/N 290936
	Self-carrying Swivel Inlet Deublin	DU EN FR GE IT SW	409333A 409318A 409334A 409179A 409319A 409346A	MA	(317102) or (317107)	
	Self-carrying Swivel Inlet Maier	DU EN FR GE IT JA PL PO SP SW	409335C 409320C 409336C 409180C 409321C 7119929C 7146581C 7105198C 464977C 409345C	MA	(317102) or (317107)	
<b>CL 2018/ CL 2018S</b>	Hot Melt Laboratory Coater CL 2018 / CL 2018 S	EN FR GE IT PL SW	317184D 317195D 317172D 403058D 7105714D 458041D	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>
<b>CLG 05</b>	Electrical Cabinet CLG 05	EN GE	407449A 407448A	MA	(317102) or (317107)	<b>When ordering, please state Unit Type and Serial Number</b>
<b>CLG 05/ CLG 05P</b>	Electrical Cabinet CLG 05 / CLG 05 P	GE	458382A	MA	(317102) or (317107)	<b>When ordering, please state Unit Type and Serial Number</b>

A-8 - 2

## Nordson Engineering (Meltex) Product Line (sorted by Model)

### Coating Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>CLG 05/ CLG 05P</b>	Lab Melter CLG 05 / CLG 05 P	<b>DU EN GE</b>	317211A 407473B 315771B	MA	(317102) or (317107)	<b>When ordering, please state Unit Type and Serial Number</b>
<b>CLG 05P</b>	Laboratory Coater CLG 05 P	<b>GE</b>	458335A	MA	(317102) or (317107)	<b>When ordering, please state Unit Type and Serial Number</b>
<b>CLG 05</b>	Laboratory Melter CLG 05	<b>EN FR GE SP</b>	7146638A 7119822A 7119799A 7135940A	MA	(317102) or (317107)	<b>When ordering, please state Unit Type and Serial Number</b>
<b>NT 1027</b>	Hot Melt Coating Module NT 1027	<b>FR GE</b>	409048A 409119A	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>
<b>NT 1035</b>	Hot Melt Coating Module NT 1035	<b>EN GE</b>	7119612B 7119540B	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>
<b>NT 1041</b>	Hot Melt Coating Module NT 1041	<b>FR GE</b>	464935A 464772A	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>
<b>NT 1045</b>	Hot Melt Coating Modules NT 1045	<b>EN GE</b>	7105823A 7105686A	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>
<b>NT 1050</b>	Hot Melt Coating Module NT 1050	<b>FR GE</b>	7135445A 7135340A	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>
<b>NT 1050</b>	Hot Melt Coating Module NT 1050	<b>GE</b>	405193A	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>
<b>NT 1050</b>	Hot Melt Coating Module NT 1050	<b>EN GE</b>	458027A 413086A	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>

A-8 - 3

## Nordson Engineering (Meltex) Product Line (sorted by Model)

### Coating Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
NT 1050	Hot Melt Coating Module NT 1050	EN GE	213750B 213698B	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>
NT 1050	Hot Melt Coating Module NT 1050	GE PO	397424A 397516A	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>
NT 1050	Hot Melt Coating Module NT 1050	EN GE	397550B 397534B	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>
NT 1050	Hot Melt Coating Module NT 1050	EN GE	7119358A 7119300A	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>
NT 1055	Hot Melt Coating Module NT 1055	EN GE PL	7146510A 7146467A 7146579A	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>
NT 1070	Hot Melt Coating Module NT 1070	EN GE	397367A 397078A	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>
NT 1075	Hot Melt Coating Module NT 1075	EN GE	7192177_01 7192149_01	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>
NT 1085	Hot Melt Coating Module NT 1085	GE	447645A	MA	(317104) or (317105)	<b>When ordering, please state Unit Type and Serial Number</b>
NT 4035	Hot Melt Coating Module NT 4035	GE	7119090A	MA	(317104)	<b>When ordering, please state Unit Type and Serial Number</b>
SD01	Swivel Device	EN FR GE SP SW	405092B 405093B 405094B 447624B 405124B	MA	(317102) or (317107)	

A-8 - 4

## Nordson Engineering (Meltex) Product Line (sorted by Model)

### Coating Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
SD02	Swivel Device	EN FR GE IT RU SP SW	317186B 407469B 317185B 397347B 7179744B 7135631B 458042B	MA	(317102) or (317107)	
SD03	Swivel Device with horizontal swivel path for surface coating heads	DU EN FR GE IT PO SP	405229C 405190C 405191C 405192C 458001C 7119274C 7119551C	MA	(317102) or (317107)	
SD04	Swivel Device with possibility for 3D adjustment	GE	317229A	MA	(317102) or (317107)	
SD05	Swivel Device with horizontal adjustment for application heads EP...	FR GE	464803A 464794A	MA	(317102) or (317107)	
SD06	Swivel Device for surface coating heads BC 40 with application widths up to 350mm	GE	412797A	MA	(317102) or (317107)	
SD08	Swivel Device for Hot Melt Application Head Control Coat	DU GE	409232A 409221A	MA	(317102) or (317107)	
SD09	Swivel Device for CT 4000 and CL 2018	EN GE	409474A 409454A	MA	(317102) or (317107)	
SD10	Swivel Device with two mounting positions	GE	409473A	MA	(317102) or (317107)	

A-8 - 5

## Nordson Engineering (Meltex) Product Line (sorted by Model)

### Coating Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
SD11	Swivel Device with Height Adjustment for Hot Melt Application Head Control Coat	EN GE	412704A 412687A	MA	(317102) or (317107)	
SD12	Swivel Device for three Hot Melt Application Heads EP	GE	412701A	MA	(317102) or (317107)	
SD13	Swivel Device for Hot Melt Application Heads EP 51	GE	412722A	MA	(317102) or (317107)	
SD14	Swivel Device for Application Head BC 40 with Adapter for Application Head EP	EN GE	458032B 458004B	MA	(317102) or (317107)	
SD15	Swivel Device with Horizontal Swivel Path for Application Heads EP	EN GE	458102A 458095A	MA	(317102) or (317107)	
SD16	Swivel Device on Coating System CT 4400 for Application Heads EP...	EN GE	447794A 447731A	MA	(317102) or (317107)	
SD17	Swivel Device CT / SB	EN GE SP	447799A 447782A 464777A	MA	(317102) or (317107)	
SD18	Swivel Device	FR GE	7119184A 213028A	MA	(317102) or (317107)	
SD19	Swivel Device with Maintenance Position	FR GE	213086A 213065A	MA	(317102) or (317107)	
SD20	Swivel Device with Coating Roll for Application Heads EP...	EN FR GE	213752B 213733B 213713B	MA	(317 101)	



A-8 - 6

## Nordson Engineering (Meltex) Product Line (sorted by Model)

### Coating Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>SD21</b>	Swivel Device with Sensor for Druckmarkenerkennung	<b>FR</b> <b>GE</b>	397045A 213974A	MA	(317102) or (317107)	
<b>SD22</b>	Swivel Device on CT 4435 for Application Head EP 51	<b>FR</b> <b>GE</b>	397239A 397196A	MA	(317102) or (317107)	
<b>SD23</b>	Swivel Device on CT 4400	<b>EN</b> <b>FR</b> <b>GE</b>	7105769A 397263A 397223A	MA	(317102) or (317107)	
<b>SD24</b>	Adjusting Device for Applicator (Title Version C: Adjusting Device for Application Head)	<b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7156827C 7105951C 397672_04 7105944_04 397453_04 7146698C 7146582C 397475A 7146690C 7146163C 7135757C	MA	(317102) or (317107)	
<b>SD25</b>	Swivel Device for Vertical Coating Position	<b>CH</b> <b>EN</b> <b>GE</b> <b>RU</b>	7156633A 397937A 397892A 7156511A	MA	(317102) or (317107)	
<b>SD26</b>	Adjusting Device for Application Heads EP 51	<b>FR</b> <b>GE</b>	7105867A 7105307A	MA	(317102) or (317107)	
<b>SD27</b>	Adjusting Device for Surface Coating Head	<b>EN</b> <b>FR</b> <b>GE</b> <b>JA</b>	7119821A 7135482A 7119749A 7119932A	MA	(317102) or (317107)	

A-8 - 7

## Nordson Engineering (Meltex) Product Line (sorted by Model)

### Coating Units

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>SD28</b>	Adjusting Device for Application Head Curtain Coat BC70	<b>EN</b> <b>GE</b> <b>IT</b> <b>PL</b>	7135512A 7135326A 7135332A 7146514A	MA	(317102) or (317107)	
<b>SD29</b>	Adjusting Device for Application Head	<b>FR</b> <b>GE</b>	7146071A 7146056A	MA	(317102) or (317107)	
<b>SD30</b>	Adjusting Device	<b>DA</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>SP</b>	7169283D 7146763_05 7146673C 7146659_05 7179196_05 7179214D 7192829_05 7169629_05	MA	(317102) or (317107)	
<b>SD31</b>	Adjusting Device Cart for BC40	<b>EN</b> <b>GE</b>	7156212B 7156207B	MA	(317102) or (317107)	
<b>SD32</b>	Adjusting Device with Motor-driven Angle Adjustment	<b>EN</b> <b>FI</b> <b>GE</b>	7169154A 7169167A 7169103A	MA	(317102) or (317107)	
<b>SD33</b>	Adjusting Device for Applicator EP11	<b>GE</b>	7560337_01	MA	(317102) or (317107)	

A-9 - 1

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Other Hot Melt Units*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>EEX</b>	Extruder Economic Series	<b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>LI</b> <b>PL</b> <b>PO</b> <b>SL</b> <b>SP</b>	7169667_06 7179306_05 7169615_06 7169849_06 7560767_06 7179198_06 7169666_03 7560664_04 7179768_06	MA	(317102) or (317107)	
<b>EX/ EX...UFM</b>	Extruder	<b>CZ</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>PL</b>	7179814_03 7179048_03 7179136_04 7169915_04 7593398_04 7560821_03	MA	(317102) or (317107)	
<b>GR 22</b>	Retrofitting Kit GR 22	<b>GE</b>	409068A	MA	(317102) or (317107)	
<b>HM 4500/ HM 4200</b>	SERIES HM 4500 / HM 4200 Hot Melt Applicator	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b>  <b>SP</b>  <b>SW</b>	290820A 264236B 264238B 264240B 264242B 290822A 264244B 290823A 290821A	SA MA MA MA MA SA MA SA SA	(317104) or (317105)	
<b>HM 4500/ HM 4200</b>	SERIES HM 4500 / HM 4200 Hot Melt Applicator	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b> <b>SW</b>	269823 264237 264239 264241 264243 264245 269824	OP	(317102) or (317107)	

A-9 - 2

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Other Hot Melt Units*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>KBV 400</b>	Cartridge Filling Device KBV 400	<b>FR</b> <b>GE</b>	213499A 213336A	MA	(317102) or (317107)	
<b>PH</b>	PH and PH.. UFM Adhesive Melters	<b>EN</b> <b>GE</b> <b>SW</b>	7179598_02 7179431_02 7179615_02	MA	(317103) or (317106)	
<b>PM 350</b>	Hot Melt Material Premelter PM-350	<b>EN</b>	315789B	MA	(317103) or (317106)	<b>When ordering, please state Unit Type and Serial Number</b>
<b>PS 352/ PS 752</b>	Hot Melt Metering Unit PS 352 / PS 752 with Siemens Controller	<b>EN</b> <b>GE</b>	7146788A 7146717A	MA	(317103) or (317106)	<b>End of Support 03/2018</b>
<b>PS 352/ PS 752/ PS 1502</b>	Hot Melt Metering Unit PS 352 / PS 752 / PS 1502	<b>CH</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>SP</b> <b>SW</b> <b>TU</b>	7119920 <b>B</b> 458207 <b>B</b> 7135508 <b>B</b> 458149 <b>B</b> 409130 <b>B</b> 458050 <b>B</b> 7135518 <b>B</b> 7105518A 7105033A 7135926 <b>B</b>	MA	(317103) or (317106)	<b>End of Support 03/2018</b>
<b>PS 352/ PS 752/ PS 1502</b>	Hot Melt Metering Unit PS 352 / PS 752 / PS 1502 with Control System CS 20	<b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>IT</b> <b>PL</b> <b>RU</b> <b>SP</b> <b>SW</b> <b>TU</b>	397021A 7135509A 213571A 213485A 213522A 213767A 7135519A 7119694A 7105519A 7105034A 7135927A	OP	(317102) or (317107)	<b>End of Support 03/2018</b>

**A-9 - 3 Nordson Engineering Hot Melt Products (sorted by Model)**

***Other Hot Melt Units***

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>PS 352-1S/ PS 352-4S</b>	Hot Melt Metering Unit with Agitator PS 352-1S / PS352-4S	<b>GE IT</b>	7105067A 7105136A	MA	(317103) or (317106)	<b>End of Support 03/2018</b>
<b>PS 752</b>	Hot Melt Metering Unit PS 752-1	<b>GE</b>	409026A	MA	(317103) or (317106)	<b>End of Support 03/2018</b>
<b>UFM</b>	Ultra Foam Mix Cube C4_Type 10	<b>EN</b>	7169638_02	MA	(317102) or (317107)	
<b>UFM</b>	Foam Units Ultra Foam Mix Cube	<b>CH CZ EN FI FR GE IT JA PL SP SW</b>	7593338_06 7179964_05 7179183_06 7192580_03 7593485_06 7169660_06 7179772_03 7560390_03 7179988_04 7179499_05 7179145_01	MA	(317102) or (317107)	
<b>UFM</b>	Touchpanel on Foam Units Ultra Foam Mix Cube	<b>CH CZ EN FI FR GE IT JA PL SP</b>	7593339_06 7179653_06 7179572_06 7192581_03 7593446_07 7179131_07 7560529_03 7560505_03 7179699_06 7192976_06	MA	(317102) or (317107)	
<b>XP 5 / XP 10</b>	Extruder XP 5 XP 10	<b>FR GE IT</b>	213696B 213244B 213656B	MA	(317102) or (317107)	

A-9 - 4

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Other Hot Melt Units*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
XP 5 / XP 10	Extruder XP 5 XP 10	FR GE	213946A 213922A	MA	(317102) or (317107)	
XP 10	Extruder XP 10	GE	458306B	MA	(317102) or (317107)	
XP 22	Extruder XP 22	EN GE PO SP	409107E 409106E 213382E 409108A	MA	(317103) or (317106)	<b>When ordering, please state Unit Type and Serial Number</b>
XP 22	Extruder XP 22	FR GE	409391A 409027A	MA	(317103) or (317106)	<b>When ordering, please state Unit Type and Serial Number</b>
XP 41	Extruder XP 41	EN GE	413097A 413093A	MA	(317103) or (317106)	<b>When ordering, please state Unit Type and Serial Number</b>
XP 81	Extruder XP 81	EN GE	458477A 458436A	MA	(317102) or (317107)	
XP 81	Extruder Item No. 8018770	DU GE	213277A 213258A	MA	(317102) or (317107)	
XP 81	Extruder XP 81	FR GE IT	412802A 412744A 412806A	MA	(317102) or (317107)	
XP 225	Extruder XP 225	EN GE	407127A 405296A	MA	(317104) or (317105)	

A-10 - 1

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Drives*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Air Motor with Piston Pump for Bulk Melters BM	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	464960 <b>C</b> 447698 <b>C</b> 447601 <b>C</b> 458479 <b>C</b> 397982 <b>C</b> 458488 <b>C</b> 458127 <b>C</b> 447654 <b>C</b> 464855 <b>A</b> * 397879 <b>C</b> 213168 <b>C</b> 458489 <b>C</b> 447650 <b>C</b>	MA	(317102) or (317107)	* available at Nordson K.K.
	Servo Converter	<b>GE</b>	458024A	MA	(317102) or (317107)	
	Motor Controller and Servomotor	<b>DU</b> <b>EN</b> <b>GE</b> <b>IT</b> <b>SW</b>	412775B 412776B 412746B 412777B 412903B	MA	(317102) or (317107)	

A-10 - 2

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Drives*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Speed Compiler (RPM)	DA DU EN FI FR GE GR IT JA NO PL PO RU SP SW TU	409374B 405117B 405066B 405204B 405067B 405008B 213845B 405126B 7146027B 409451B 7105755B 405230B 397394B 405292B 405106B 397117B	MA	(317102) or (317107)	(PS03)
	Speed Compiler (RPM)	DA DU EN FI FR GE IT NO PO SP SW	407271A 407272A 407273A 407274A 407275A 409437A 407276A 412686A 407277A 407278A 407279A	MA	(317102) or (317107)	(PS04)
	Three-phase AC Motor with Worm Gear	EN GE SW	412961B 409123B 458046B	MA	(317102) or (317107)	(DR05)



A-10 - 3

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Drives*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>BG</b>	Gear Motor BG	<b>CH</b> <b>EN</b> <b>GE</b> <b>JA</b> <b>PL</b> <b>PO</b>	7135018A 7119597B 7119585B 7146026B 7156351B 7192889B	MA	(317102) or (317107)	
<b>DM 200</b>	Gear Torque Motor DM 200	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>SP</b> <b>SW</b>	405194A 405195A 405196A 405116A 405197A 412705A 405289A 405198A	MA	(317102) or (317107)	
<b>ECC</b>	Overload Coupling Series ECC	<b>CZ</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>SP</b>	464721D 213465E 403039E 403048E 317263E 403047E 7105193E 213251E	MA	(317102) or (317107)	(CL02)
<b>GL 02</b>	D.C. Gear Motor Series GL ...02	<b>EN</b> <b>GE</b> <b>IT</b>	409425A 409422A 409426A	MA	(317102) or (317107)	

A-10 - 4

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Drives*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>GL 03</b>	D.C. Gear Motor Series GL ...03	<b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	317288A 317219A 317220A 403057A 317245A 317206A 317226A 317228A 317223A 317221A 317227A	MA	(317102) or (317107)	
<b>GL 550</b>	D.C. Gear Motor GL 550	<b>EN</b> <b>GE</b> <b>IT</b>	409444A 409421A 409445A	MA	(317102) or (317107)	(DR06)

A-10 - 5

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Drives*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>LM 20/ LM 40</b>	Air Gear Motors LM 20 / LM 40	<b>DU EN GE</b>	409343A 409405A 403103A	MA	(317102) or (317107)	
<b>WS Series</b>	A.C. Gear Motors Series WS ...	<b>CZ DA DU EN FI FR GE GR HU IT JA NO PL PO RU SK SP SW TU</b>	447775C 405231C 407051C 317277D 407410C 407040C 317271D 407153C 7105480C 407039C 405172C 407329C 7105212C 407317C 407018D 7105463C 317278C 405202C 397116C	MA	(317102) or (317107)	(DR03)

A-11 - 1

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Mechanical & Hydraulic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Bypass Plate with Safety Valve	<b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	317299A 403014A 403027A 403041A 317284A 403006A 403001A 403011A 403005A 403019A	MA	(317102) or (317107)	(SV07)
	Cascade Filter	<b>EN</b> <b>GE</b> <b>IT</b> <b>PL</b>	7105511B 7105510B 7156576B 7156354B	MA	(317102) or (317107)	(FC07)
	Feed Valve	<b>CZ</b> <b>EN</b> <b>GE</b>	464725A 464724A 464714A	MA	(317102) or (317107)	
	Feed Valve	<b>EN</b> <b>GE</b>	397497A 397464A	MA	(317102) or (317107)	
	Feed Valve	<b>EN</b> <b>GE</b>	213970A 213954A	MA	(317102) or (317107)	
	Filter Block with Safety Valve	<b>EN</b> <b>GE</b> <b>IT</b>	409464A 409457A 409465A	MA	(317102) or (317107)	



A-11 - 3

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Mechanical & Hydraulic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Filter Unit in Hot Melt Metering Units PS...	CH EN FR GE IT SP SW	7135019B 458234C 458156A 409389C 458151A 7105521A 7105036A	MA	(317102) or (317107)	(FC04)
	Gear Pumps Series Mahr / Feinprüf	CZ DA DU EN FI FR GE GR IT JA NO PO RU SP SW	447774A 407289D 407327D 403038E 409016D 407297D 317247E 407152A 403245E 405171A* 407320D 407316D 407017A 407171D 407172D	MA	(317102) or (317107)	(GP07)  * = available at K.K.
	Gerotor Pump	DA DU EN FR GE IT NO PO SP SW	464746A 464750A 447795A 464709A 458456A 447793A 464703A 213169A 464704A 464705A	MA	(317102) or (317107)	
	Gerotor Pump with Manifold Block	EN FR GE	412936A 412937A 409277A	MA	(317102) or (317107)	

A-11 - 4

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Mechanical & Hydraulic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Mechanical Safety Valve	<b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>SW</b> <b>TU</b>	409160A 409161A 409162A 409163A 409164A 405298A 409165A 464880A* 409166A 7105211A 409167A 7135548A 397391A 409168A 409169A 397118A	MA	(317102) or (317107)	(SV04)          * = available at Nordson K.K.
	Mechanical Safety Valve with Pressure Display	<b>EN</b> <b>FR</b> <b>GE</b>	409363A 409372A 409364A	MA	(317102) or (317107)	(SV02)

## **Nordson Engineering Hot Melt Products (sorted by Model)**

A-11 - 5

### ***Mechanical & Hydraulic Components***

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Pneumatic Safety Valve	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>SK</b> <b>SP</b> <b>SW</b>	447776G 409151G 409152G 405189G 409153G 409154G 317222G 213842F 7105481G 409155G 464986G 409156G 7105303G 409157G 7105464G 409158G 409159G	MA	(317102) or (317107)	(SV05)
	Pneumatic Safety Valve with Reed Switch	<b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b> <b>TU</b>	403012H 317269H 317268_09 409015H 317294H 317135_09 407154B 317281H 405173B* 317270H 317266H 407019B 317256H 403016H 397119F	MA	(317102) or (317107)	(SV06)             * = available at Nordson K.K.



A-11 - 6

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Mechanical & Hydraulic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Sevice Kit 7109870: Pneumatic Safety Valve and Pressure Restrictor Valve (3 bar) Sevice Kit 7109871: Pneumatic Safety Valve and Pressure Restrictor Valve (5 bar)	<b>EN/FR/ GE/IT/ SP</b>	7105860A	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
	Retrofitting Kit PR Pump - Feinprüf Pump	<b>EN GE</b>	412819A 412665A	MA	(317102) or (317107)	
<b>DR 145</b>	Constant Pressure Controller DR 145	<b>EN FR GE IT SW</b>	317181C 409369B 317173C 7135226C 7135224C	MA	(317102) or (317107)	
<b>DR 330</b>	Constant Pressure Controller DR 330	<b>EN GE PL RU SW</b>	317170C 315835C 7146008C 7146003C 447722C	MA	(317102) or (317107)	
<b>DR 900/1300</b>	Constant Pressure Controller DR 900 / DR 1300	<b>GE EN SP</b>	315832B 315946B 403056B	MA	(317102) or (317107)	
<b>GB 04</b>	Pressure Compensating Module	<b>EN GE</b>	407478A 407408A	MA	(317102) or (317107)	

A-11 - 7

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Mechanical & Hydraulic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>KF 25</b>	Nozzle Filter KF 25	<b>BU</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>HU</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b> <b>TU</b>	7135433F 464722D 409136F 409019F 403023F 447691F 413021F 403024F 213843D 7105614F 409018F 464804F 7119263F 464805F 397392F 464806F 403059F 397125D	MA	(317102) or (317107)	<b>When ordering, please state Product Part Number</b>
<b>KF 25</b>	Filter Cartridge KF 25	<b>EN</b> <b>GE</b>	409220A 407487A	MA	(317102) or (317107)	(FC03)
<b>PF...</b>	Active Pressure Accumulator Series PF	<b>EN</b> <b>FR</b> <b>GE</b> <b>SP</b>	403074D 403256D 317296D 403037D	MA	(317102) or (317107)	



A-11 - 9

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Mechanical & Hydraulic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Pump Feed Capacity PR 6 Module 2	EN	407032A			
	Pump Feed Capacity PR 12 Module1	EN	407023A			
	Pump Feed Capacity PR 12 Module 2	EN	407024A			
	Pump Feed Capacity PR 18 Module 2	EN	409064A			
	Pump Feed Capacity PR 25 Module 2	EN	407025A			
	Pump Feed Capacity PR 100 Module 3	EN	407022A			
<b>PU Series</b>	Multiple Current Gear Pump Series PU □-□m□	<b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	405078B 405079B 403220B 405080B 405081B 403132B 405082B 407285B 405083B 405130B 405084B	MA	(317102) or (317107)	(GP09)

A-11 - 10

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Mechanical & Hydraulic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>PU Series</b>	Single Stream Gear Pump Series PU □/85 and PU 700	<b>CH</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	7135016C 464743B 405085C 405086C 403221E 405087C 405088C 403222E 405089C 7146025E 407286C 405090C 405129C 405091C	MA	(317102) or (317107)	(GP10)
<b>PUR_PR_EP48</b>	Pressure Regulator CPR	<b>EN</b> <b>GE</b> <b>IT</b>	7179678_03 7179677_03 7560105_02			
	Pump Feed Capacity PU 2-2 Module 1	<b>EN</b>	409239A			
	Pump Feed Capacity PU 2-4 Module 1	<b>EN</b>	397130A			
	Pump Feed Capacity PU 2-6 Module 1	<b>EN</b>	397131A			
	Pump Feed Capacity PU 2-8 Module 1	<b>EN</b>	213286A			
	Pump Feed Capacity PU 3-2 Module 1	<b>EN</b>	407048A			
	Pump Feed Capacity PU 3-4 Module 1	<b>EN</b>	397314A			
	Pump Feed Capacity PU 4-2 Module 1	<b>EN</b>	407049A			

A-11 - 11

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Mechanical & Hydraulic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Pump Feed Capacity PU 4-4 Module 1	EN	397132A			
	Pump Feed Capacity PU 4-6 Module 1	EN	409145A			
	Pump Feed Capacity PU 6-2 Module 1	EN	409243A			
	Pump Feed Capacity PU 6-4 Module 1	EN	407036A			
	Pump Feed Capacity PU 12-2 Module 1	EN	407050A			
	Pump Feed Capacity PU 12-2 Module 2	EN	412758A			
	Pump Feed Capacity PU 12-4 Module 1	EN	458106A			
	Pump Feed Capacity PU 15/85 Module 2.5	EN	464948A			
	Pump Feed Capacity PU 18-2 Module 1	EN	407438A			
	Pump Feed Capacity PU 25/85 Module 2.5	EN	407033A			
	Pump Feed Capacity PU 25-2 Module 2	EN	213298A			
	Pump Feed Capacity PU 35/85 Module 2.5	EN	407034A			
	Pump Feed Capacity PU 50/85 Module 2.5	EN	407035A			
	Pump Feed Capacity PU 700	EN	407037A			

A-12 - 1

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Pneumatic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Air Heater LH03, LH04, LH05	<b>EN</b> <b>GE</b> <b>PL</b>	7156284A 7156279A 7179170A	MA	(317102) or (317107)	
	Air Manifold Bar	<b>DA</b> <b>EN</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>SP</b> <b>SW</b>	464915A 405052A 405053A 405127A 213022A 213057A 464954A	MA	(317102) or (317107)	
	Air Manifold Bar with Pressure Accumulator for Hot Melt Application Heads	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>PO</b> <b>SP</b>	458355B 458351B 458343B 458315B 7105616B 458393B 213023B 458491B	MA	(317102) or (317107)	
	Air Manifold Bar	<b>EN</b> <b>GE</b>	7105657A 7105626A	MA	(317102) or (317107)	
	Clean Air Flow Kit	<b>DA</b> <b>EN</b>	409139A 403261A	MA	(317102) or (317107)	
	Clean Air Flow Kit (Compact)	<b>EN</b> <b>SW</b>	405109B 405203B	MA	(317102) or (317107)	





A-12 - 3

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Pneumatic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Control Unit for Pneumatic Safety Valves	<b>CZ</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b> <b>SW</b>	7105414B 213764B 213312B 7105722B 213757B 213301B 213317B 213763B 213709B	MA	(317102) or (317107)	(SVC03)
<b>HI 10</b>	Heated Air Assembly HI 10	<b>EN</b> <b>FR</b> <b>GE</b>	409184A 213821A 409085A	MA	(317102) or (317107)	
<b>HI 11</b>	Heated Air Assembly HI 11	<b>EN</b> <b>FR</b> <b>GE</b>	403262A 403263A 403264A	MA	(317102) or (317107)	
<b>HI 14</b>	Heated Air Assembly HI 14	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>RU</b> <b>SP</b>	7580194B 213736B 7179026B 292943B 292944B 292879B 407303B 7179169B 7192815B 213917B	MA	(317102) or (317107)	<b>Obsolete!</b> <b>Replaced by PN 7593622_01</b>
<b>HI 15</b>	Heated Air Assembly HI 15	<b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>SP</b> <b>SW</b>	409137C 317295C 315944C 315947C 315824C 317289C 7146658C 407328C 403055C	MA	(317102) or (317107)	<b>Obsolete!</b> <b>Replaced by PN 7593622_01</b>

A-12 - 4

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Pneumatic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
HI 16	Heated Air Assembly HI 16	EN FR GE IT PL SP SW	315945B 315948B 315827B 213420B 7156355B 213340B 464801B	MA	(317102) or (317107)	<b>Obsolete!</b> <b>Replaced by PN 7593622_01</b>
HI 17	Heated Air Assembly HI 17	EN FR GE	407006A 407007A 407005A	MA	(317102) or (317107)	
HI 14, 15, 16	Spray Air Control Unit HI14, 15, 16	GE PL	7593622_01 7593628_01	MA	(317102) or (317107)	
IG 24	Inert Gas Equipment IG 24	DU EN FI FR GE HU IT JA NO PO SK SP SW	292797E 292796E 292798E 292799E 292778E 7105477E 292909E 464983D* 292910E 292911E 7105460E 292912E 292800E	MA	(317102) or (317107)	<b>When ordering, please state Product Part Number</b>  <b>* available at Nordson K.K.</b>

A-12 - 5

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Pneumatic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>IG 24 V</b>	Inert Gas Equipment IG 24 with Vacuum Pump	<b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	407232A 407233A 407234A 407235A 407236A 407125A 407237A 407238A 407239A 407240A 407241A	MA	(317102) or (317107)	
<b>IG 25</b>	Inert Gas Equipment IG 25	<b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	407242B 407243B 407244B 407245B 407246B 407126B 407247B 407248B 7105737B 407249B 7135997B 407250B 407251B	IN	(317102) or (317107)	

A-12 - 6

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Pneumatic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>IG 25 V</b>	Inert Gas Equipment IG 25 with Vacuum Pump	<b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>SP</b> <b>SW</b>	409362B 407263B 407262B 407264B 407265B 409329B 407266B 407267B 7119892B 407268B 407269B 407270B	IN	(317102) or (317107)	
<b>IG 25 / IG 25 V</b>	Notes on Inert Gas Equipment IG 25 / IG 25V	<b>EN/ FR/</b> <b>GE/ IT/</b> <b>SP</b>	397853A	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>MBT</b>	Membrane Compressed Air Dryer	<b>DU</b> <b>EN</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>RU</b> <b>SP</b>	397857B 458252B 412860B 447707B 458321B 213111B 7105349B 213235B	MA	(317102) or (317107)	
<b>OR ...</b>	Air Conditioning Unit	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b> <b>SW</b>	317060A 317061A 317059A 315918A 317062A 317065A 317074A	MA	(317102) or (317107)	

A-13 - 1

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Electrical & Electronic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Capacitive Evaluation Unit - Data Sheet (LC 24)	EN	407399D	MA	(317102) or (317107)	
	Capacitive Evaluation Unit - Data Sheet (LC 25)	EN	458277B	MA	(317102) or (317107)	
	Capacitive Level Sensor - Data Sheet (IP 68)	EN	407400C	MA	(317102) or (317107)	
	Capacitive Level Sensor - Data Sheet (IP 68)	EN	458278B	MA	(317102) or (317107)	
	Connection Box with Indicator Signal Distributor 2:1	DU EN GE SP	315916A 315910A 315862A 317043A	MA	(317102) or (317107)	
	Encoder	DU EN FI FR GE IT PL PO SK SP SW	317254C 292785C 412889C 292786C 290719C 317279C 7105418C 315701C 7105393C 405048C 317285C	MA	(317102) or (317107)	

A-13 - 2

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Electrical & Electronic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Frequency Converters Series 82xx E and 8200 vector	<b>CH</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7135020A 7119060A 7119006A 7119002A 7119195A 7119005A 7105653A 7105998A 7146030A 7119079A 7146007A 7119007A 7135547A 7146000A 7119034A 7119035A	MA	(317102) or (317107)	
	Heat Exchanger for Electrical Cabinets (RITTAL_SK)	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>SP</b> <b>SW</b>	447732A 464884C 405255C 405264C 464840C 405265C 409044C 464814C 213128C 405266C	SU MA	(317102) or (317107)	CZ = Supplement (Title: Rittal_SK_CZ_A-0396)
	Inductive Proximity Switch	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SW</b>	317248B 292787B 292788B 290819B 317292B 317286B	MA	(317102) or (317107)	(PS01)

A-13 - 3

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Electrical & Electronic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Inductive Proximity Switch Item No. 2614.0387	DA DU EN FI FR GE IT PL PO SK SP SW	413014A 413015A 403105A 412890A 413016A 403104A 413017A 7105419A 413018A 7105394A 413019A 405200A	MA	(317102) or (317107)	(PS02)
	Inductive Proximity Switch	CZ EN FR GE IT PO SP	464706B 464700B 213243B 447798B 213248B 7105194B 213252B	MA	(317102) or (317107)	(PS05)
	BANNER OMNI-BEAM Sensor Heads	EN GE	213072A 213071A	IN	(317102) or (317107)	
	Pressure Sensor	DU EN FR GE IT	409326C 403110C 409327C 403111C 409328C	MA	(317102) or (317107)	(SP83)

A-13 - 4

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Electrical & Electronic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Pressure Sensor	DA DU EN FI FR GE IT JA NO PO SP SW	407443_08 403065_08 317258_08 407444_08 405046_08 317257_08 405097_08 409379G 407445_08 407446_08 407447_08 405201_08	MA	(317102) or (317107)	(SP85)
	Pressure Sensor	EN FR GE	292781A 292782A 290717A	MAN	(317102) or (317107)	
	Pressure Sensor EPXO-...	EN/FR/ GE/SP  EN/CH  EN/CZ  EN/RU	447785_06  7169274_06  7169290_06  7156956_06	IN	(317102) or (317107)	<b>Multilingual documents, therefore one P/N only</b>
	Pressure Sensor Series W / Series K With and Without Safety Switch Contact	CZ DU EN FR GE JA PL PO RU	7169876_11 7156672_11 7119609_13 7156598_12 7119581_13 7146028C 7156353_11 7192888_11 7169147G	MA	(317102) or (317107)	
	Retrofit Kit Solid State Relais	EN/ FR/ GE/ SP	7105876A	IN		<b>Multilingual document, therefore one P/N only</b>



A-13 - 5

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Electrical & Electronic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Retrofitting Kit Encoder	EN/FR/ GE	409428B	MA	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>DMU 04</b>	Pressure Transducer DMU 04	EN/FR/ GE	458037B 458038B 458030B	MA	(317102) or (317107)	
<b>DR 130</b>	Retrofitting Instructions RPM Monitoring DR 130	EN FR GE	403114C	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
<b>GDS 200</b>	Pressure Sensors with Limiting Value Switch Function GDS 200	DU EN FR GE IT	315828B 292783B 292784B 290718B 409300B	MA	(317102) or (317107)	
<b>KTD 3</b>	Tach Generator KTD 3	EN GE SP	464820A 464786A 464860A	MA	(317102) or (317107)	
<b>LG 9</b>	Tach Generator LG 9	DA DU EN FI FR GE IT NO PO SP SW	292903A 292802A 292801A 292803A 292804A 292726A 292904A 292905A 292906A 292907A 292805A	MA	(317102) or (317107)	
<b>NV 01</b>	Level Adaptation Amplifier NV 01	EN GE IT	397153A 458043A 458047A	MA	(317102) or (317107)	

A-13 - 6

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Electrical & Electronic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>P605</b>	Pressure Switch P605	<b>EN</b> <b>GE</b>	7105578A 7105577A	MA	(317102) or (317107)	
<b>PDM 03</b>	Torque Controller for Torque Motors PDM 03	<b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	317298B 403015B 403026B 403049B 317287B 403007B 403000B 403010B 403032B 403020B	MA	(317102) or (317107)	
<b>PY 9450/ PY 9451/ PY 9452/ PY 9453</b>	Pressure Sensors with Limit Value Switch Function PY 9450 PY 9451 PY 9452 PY 9453	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b> <b>SW</b>	409233A 317260A 403299A 317259B 409295A 407282A 409231A	MA	(317102) or (317107)	
<b>TLB-KSR</b>	Signal Amplifier TLB-KSR with Level Sensor	<b>EN</b> <b>GE</b> <b>SP</b>	413022A 412998A 413023A	MA	(317102) or (317107)	
<b>TT 61</b>	Isolating Amplifier TT 61	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PO</b> <b>SP</b> <b>SW</b>	412673A 409383A 412631A 409382A 458023A 7146029A 7105107A 447637A 447727A	MA	(317102) or (317107)	

A-13 - 7

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Electrical & Electronic Components*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>WZ 201/ WZ 202</b>	Week Timer WZ 201, WZ 202	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	213044A 403238B 403244B 403117B 405205B 403235B 403107B 403250B 464883A* 403225B 403227B 403241B 403237B	MA	(317102) or (317107)	* available at Nordson K.K.
<b>WZ 202</b>	WZ 202 Programmable Week Timer	<b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	292892A 292893A 292894A 292895A 292777A 292900A 292897A 292898A 292901A 292902A	MA	(317102) or (317107)	

A-14 - 1

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Level Controls*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Connector Bracket P/N 447 197	EN	464784A	IN	(317102) or (317107)	
	Evaluation unit for capacitive proximity switch	EN GE	409197A 409196A	MA	(317102) or (317107)	
	Level Control Drexelbrook	CZ EN GE	447733A 458190A 458186A	MA	(317102) or (317107)	
	Plotting Unit KFA-1-... for Rod Probe KFS-1-...	DU EN FI FR GE IT PO SP SW	213019A 458430A 447689A 458440A 458379A 447749A 7105108A 458431A 213701A	MA	(317102) or (317107)	
	Plotting Unit KFA-4-... for 3-Point Rod Probe KFS-4-...	DU EN FR GE IT NO SP SW	447762A 447763A 447779A 447673A 213321A 447769A 213127A 447725A	MA	(317102) or (317107)	
	Plotting Unit KFA-5-... for 3-Point Rod Probe KFS-5-...	CH DU EN FR GE PO SP	7135021C 213509C 464795C 458233C 458204C 7105199C 7119552C	MA	(317102) or (317107)	

A-14 - 2

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Level Controls*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Evaluator KFA-5-/ 1-5... for 5-point Level Sensors KFS-5-5... in VersaBlue Melters	EN GE	7119855A 7119820A	MA	(317102) or (317107)	
	Evaluator KFA-5-... for Overfill Sensor	EN GE	7146741B 7146733B	MA	(317102) or (317107)	
	Evaluator KFA for Capacitive Level Sensor KFS-5-4 (in MX 4003 NV Melters)	EN FR GE	7560647_02 7560653_02 7169867_02	MA	(317102) or (317107)	
	Switching Amplifier CSV with Level Sensor	DA DU EN FI FR GE IT JA NO PO SP SW	409093B 409055B 407498B 409078B 409056B 407465B 409057B 409378B* 409063B 409237B 409046B 409045B	MA	(317102) or (317107)	* available at Nordson K.K.
<b>Captron CCT</b>	Captron Rod Probe CCT and Probe Amplifier VC 11-A	EN FR GE	317078A 403137A 317076A	MA	(317102) or (317107)	
<b>LC 18</b>	Weighing Cells LC 18 / LC18-2 / LC18-2 PS	EN GE	283017A 283016A	MA	(317102) or (317107)	

A-14 - 3

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Level Controls*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LC 19	Weighing Cell LC 19-1 / LC 19-2 / LC 19-2 PS	CH DA DU EN FI FR GE IT NO PO SP SW	7135022C 403017C 292932C 292933C 292934C 292935C 292795C 292936C 292937C 292938C 292939C 292940C	MA	(317102) or (317107)	
LC 20	Level Controller LC 20	EN GE	317020A 315940A	MA	(317102) or (317107)	
LC 22	Changing Level Control Sensitivity	EN/FR/ GE	405023A	--	(317102) or (317107)	<b>Multilingual document, therefore one P/N only</b>
LC 23	Electronic Level Control LC 23	DA DU EN FI FR GE IT NO PO SP SW	317164E 315758E 292949E 315759E 315760E 292950E 315761E 315762E 315763E 315764E 315731E	MA	(317102) or (317107)	

A-14 - 4

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Level Controls*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>LC 24</b>	Electronic Level Control LC 24	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b> <b>SW</b>	409053F 409043F 409054F 407288F 409080F 409212F 409047F	MA	(317102) or (317107)	
<b>LC 24</b>	LC 24 Calibration	<b>EN</b>	397406A	OP	(317102) or (317107)	
<b>LC 25</b>	Electronic Level Control LC 25, LC 25-2	<b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>SP</b> <b>SW</b>	7105505D 458287D 458288G 458289D 458276G 458290E 458291D 458292D 458293G	MA	(317102) or (317107)	

A-14 - 5

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Level Controls*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>LC 26</b>	Electronic Level Control LC 26	<b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>SP</b> <b>SW</b>	213311A 213296A 213288A 213294A 213263A 213297A 213292A 213328A 213289A	MA	(317102) or (317107)	
<b>LC_201458</b>	Level Monitoring with Rod Probe	<b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b> <b>SW</b>	213669 <b>B</b> 213895A 213688 <b>B</b> 213639 <b>B</b> 213708 <b>B</b> 397038 <b>B</b> 213702 <b>B</b>	IN	(317102) or (317107)	



A-15 - 1

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Miscellaneous*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Assembly Tools 7136915, 7136918 and 7157121 for Sealing Kits with Variseal Seals	<b>EN/GE</b>	7146229_07	IN	(317102) or (317107)	<b>Bilingual document, therefore one P/N only</b>
	Cartridge Preheater for Hot Melt Cartridges	<b>FR GE SP</b>	213084A 405022A 7105696A	MA	(317102) or (317107)	
	Constant Pressure Controller (P/N 7183101)	<b>EN GE</b>	7560365_02 7560303_02	MA	(317102) or (317107)	
	Elastics Positioning Unit	<b>DA EN FR GE IT</b>	213754C 213556C 213572C 213497C 213552C	MA	(317102) or (317107)	

A-15 - 2

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Miscellaneous*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Glossary	<b>CH</b> <b>CR</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SK</b> <b>SP</b> <b>SW</b> <b>TU</b>	7119980B 7580039B 447718B 407128B 407129B 407130B 407131B 407132B 407020B 213835B* 7105473B 407133B 409386B 407134B 7105207B 407135B 7135552B 7156949B 7105456B 407136B 407137B 397107B	MA	(317102) or (317107)	* = SAP P/N 231835!

A-15 - 3

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Miscellaneous*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	General Application Materials Processing Instructions	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SK</b> <b>SP</b> <b>SW</b> <b>TU</b>	464718A 405144A 405145A 405146A 405147A 405148A 405149A 407300A 7105470A 405150A 405167A* 405151A 7105299A 405152A 407301A 7105453A 405153A 405154A 397104A	MA	(317102) or (317107)	<b>* available at Nordson K.K.</b>

A-15 - 4

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Miscellaneous*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	General Application Materials Processing Instructions (With instructions regarding PUR application materials)	<b>CH</b> <b>CR</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7119977B 7580043_03 447716B 405155B 405156B 405157_03 405158B 405159B 405160_03 407290B 405161B 7146140B 405162B 7105205B 405163B 7135551B 407293B 405164B 405165B	MA	(317102) or (317107)	

A-15 - 5

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Miscellaneous*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Safety Instructions (for Hot Melt Application Systems)	<b>BU</b> <b>CH</b> <b>CR</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>ES</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>LA</b> <b>LI</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SK</b> <b>SL</b> <b>SP</b> <b>SW</b> <b>TU</b>	7560793_02 7119981_02 7580044_02 7105758_02 7105749_02 7105750_02 7105744_02 7146248_02 7105752_02 7105745_02 7105743_02 7105759_02 7105760_02 7105746_02 7146141_02 7593220_02 7560792_02 7105751_02 7105761_02 7105748_02 7135615_02 7105762_02 7105763_02 7105792_02 7105747_02 7105753_02 7119676_02	MA	(317102) or (317107)	
	Safety Instructions for Adhesive and Sealing Material Application Systems	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>SP</b> <b>SW</b>	407382A 407383A 407384A 407385A 407386A 407387A 407388A 407389A	MA	(317102) or (317107)	

A-15 - 6

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Miscellaneous*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Safety Instructions for Adhesive and Sealing Material Application Systems (PUR)	CH DU EN FR GE IT PO SK SP SW	412918A 407390A 407391A 407392A 407393A 407394A 407395A 213601A 407396A 407397A	MA	(317102) or (317107)	
	Test Bench (P) and Test Bench Classic (P)	EN GE HU IT PL	7146589D 7146406D 7179990D 7156745D 7560085D	MA	(317102) or (317107)	
<b>508</b>	Water Recooler 508	EN FI FR GE IT JA PO SP	403063D 409020D 403071D 403036D 464844D 464984D* 464788D 403070D	MA	(317102) or (317107)	<b>* available at Nordson K.K.</b>
<b>GF 200</b>	Metering Pump Flange Station GF 200	EN FR GE IT PO SP	409087D 409351D 315739E 397218E 213381D 409088D	MA	(317102) or (317107)	
<b>GP ...</b>	Metering Pump Station GP...	FR GE IT	412804A 412770A 412808A	MA	(317103) or (317106)	

A-15 - 7

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Miscellaneous*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>GP 200</b>	Metering Pump Station GP 200	<b>CH</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>SP</b> <b>TU</b>	7119921E 213498E 405125_07 403298F 403116_07 409230_07 7105135D 213234F 7560658_07	MA	(317103) or (317106)	<b>When ordering, please state Unit Type and Serial Number</b>
<b>GP 200 (Mini)</b>	Gear Metering Pump Station GP 200 (Mini)	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SK</b> <b>SL</b> <b>SP</b> <b>SW</b> <b>TU</b>	7580142_05 7580093_04 7119286_05 7105523_05 7146258_05 7105509_05 7560685_04 7105526_05 7169359C* 7119094_05 7560380_04 7560675_04 7105595_05 7146610_04 7119599_05 7105525_05 7192926_05	MA	(317102) or (317107)	<b>* available at Nordson K.K.</b>
<b>GP 200 BC 62</b>	SERIES GP 200 / BC 62 Hot Melt Metering and Application System	<b>EN</b> <b>GE</b>	267966 267953	OP	(317102) or (317107)	<b>When ordering, please state Unit Type and Serial Number</b>
<b>P 103</b>	Metering Pump Station P 103	<b>EN</b> <b>GE</b> <b>IT</b>	403050A 403051A 403064A	MA	(317102) or (317107)	<b>When ordering, please state Unit Type and Serial Number</b>

A-15 - 8

## Nordson Engineering Hot Melt Products (sorted by Model)

### *Miscellaneous*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>PS Midi</b>	Pump Station	<b>CZ</b> <b>DU</b> <b>EN</b> <b>GE</b> <b>IT</b> <b>PL</b>	7179965_04 7179882_01 7179718_04 7169754_04 7179774_01 7179989_04	MA	(317103) or (317106)	
<b>PG...</b>	Heated Hoses PG ...	<b>EN</b> <b>GE</b>	317163B 315825B	MA	(317102) or (317107)	
<b>TC..</b>	Heated Hoses TC ...	<b>CH</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SK</b> <b>SL</b> <b>SP</b> <b>SW</b> <b>TU</b>	7119853_09 464742_09 405232_09 317046_09 317044_09 403072_09 317045_09 267969_09 213839_09 7105484_09 315909_09 7119930G 317058_09 7105306_09 317047_09 7146001_09 7105390_09 7146517_09 317075_09 317048_09 397123_09	MA	(317102) or (317107)	



## Nordson US Hot Melt Products (sorted by Model)

B-1 - 1

### Blue Series Melters

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Fulfill Retrofit Kits for Non-ProBlue Melters	GE PL	7560726_02 7560712_02	MA	(317102) or (317107)	EN - 1124683_03 - Issued 01/17
	ATS Retrofit Kit for Hot Melt Adhesive Systems	FR GE IT JA RU SP	7580114_04 7580115_04 7580116_04 7580595_01 7593331_04 7580117_04	MA	(317102) or (317107)	EN - 1125511_04 - Issued 10/18
	ATS Retrofit Manifold Service Kit - P/Ns 1125966 (12-pin cordset), 1125967 (6-pin cordset), and 1125968 (water-wash cordset)	JA	7580596_01*	IN	(317102) or (317107)	EN - 1125969_01 - Issued 05/17 * = available at Nordson K.K
<b>AltaBlue</b>	AltaBlue Adhesive Melters - Models 15, 30, 50, and 100	CH DU FR GE HU IT JA PO RU SP	7401317_04 7179004A07 7135269A03 7135253A07 7135270A03 7135306A03 7135385A 7135266A03 7146335A03 7135331A03	MA	(317103) or (317106)	EN - 1072086A07 - Issued 03/14 <b>Product Discontinued November 1st 2017, Product Obsolescence November 1st 2018.</b> <b>Replacement by EZ Melt™ Melters.</b>
<b>AltaBlue</b>	AltaBlue™ Low Pressure Molding Adhesive Melter	JA	1125976_01*	MA	(317102) or (317107)	EN - 1125976_01 - Issued 04/17 * = available at Nordson K.K
<b>AltaBlue PLC</b>	AltaBlue PLC Series Adhesive Melters - Safety	EN/FR/ GE/IT/ PO/SP/ CH/JA	1125535_01	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only Issued 12/16</b>

## Nordson US Hot Melt Products (sorted by Model)

B-1 - 2

### *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>AltaBlue Touch</b>	AltaBlue Touch Adhesive Melters	CH CZ FR GE IT JA PL PO SK SP	7403725A_01 7593320_04 7179029_04 7179017_04 7179022_04 7179015_01 7192767_04 7179024_04 7580168_04 7179023_04	MA	(317103) or (317106)	<b>EN - 1120350_05 - Issued 04/18</b>
<b>AltaBlue Touch</b>	AltaBlue Touch Series Quick Reference Card	FR GE IT JA PO SP	7169920_01 7169928_01 7169945_01 7169953_01 7169961_01 7169936_01	OP	(317102) or (317107)	<b>EN - 1120352_01 - Issued 02/12</b>
<b>AltaBlue Touch</b>	External Pressure Transducer Kit	FR GE IT JA PO SP	7169925_01 7169933_01 7169950_01 7169958_01 7169966_01 7169941_01	IN	(317102) or (317107)	<b>EN - 1120582_01 - Issued 04/12</b>
<b>AltaBlue Touch</b>	Flow Meter and Encoder Kits	FR GE IT JA PO SP	7169923_01 7169931_01 7169948_01 7169956_01 7169964_01 7169939_01	IN	(317102) or (317107)	<b>EN - 1120580_01 - Issued 04/12</b>
<b>AltaBlue Touch</b>	Flow/Pressure Control and Monitoring	CH GE JA PO SP	7403723_01 7169934_02 7169960_02 7169969_01 7169944_02	MA	(317102) or (317107)	<b>EN - 1120351_02 - Issued 05/12</b>

## Nordson US Hot Melt Products (sorted by Model)

B-1 - 3

### *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>AltaBlue Touch</b>	Flow/Pressure Option Board for Control and/or Monitoring - P/Ns 7403137 and 7403138	<b>FR GE IT JA PO SP</b>	7169924_01 7169932_01 7169949_01 7169957_01 7169965_01 7169940_01	IN	(317102) or (317107)	<b>EN - 1120581_01 - Issued 04/12</b>
<b>AltaBlue Touch</b>	Remote Visual System for 1 AltaTouch Melter - P/N 7403151 (24 ft cable)	<b>FR GE IT JA PO SP</b>	7169921_01 7169929_01 7169946_01 7169954_01 7169962_01 7169937_01	IN	(317102) or (317107)	<b>EN - 1120586_01 - Issued 04/12</b>
<b>AltaBlue Touch</b>	Remote Visual System for 1-5 AltaTouch Melter - P/N 7403152 (50 ft cable) and P/N 7403153 (100 ft cable)	<b>FR GE IT JA PO SP</b>	7169922_01 7169930_01 7169947_01 7169955_01 7169963_01 7169938_01	IN	(317102) or (317107)	<b>EN - 1120393_01 - Issued 04/12</b>
<b>AltaBlue TT</b>	AltaBlue TT Adhesive Melters - Models A4, A10, and A16	<b>CH CZ DU FR GE HU IT JA PL RO RU SP</b>	7401336 7156544A04 7156545A 7156546A 7156474A04 7156540A 7156547A04 7156552A 7156541A 7580256A04 7156542A 7156543A04	MA	(317103) or (317106)	<b>EN - 1095085A04 - Issued 03/14</b>

## Nordson US Hot Melt Products (sorted by Model)

B-1 - 4

### *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>AltaBlue TT QR</b>	AltaBlue TT Quick Reference Guide	<b>EN/CZ DUI/FR/ /GE/HU /IT/PL/ RU/SP/ CH/JA</b>	1124571_01	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only Issued 07/15</b>
<b>AltaBlue/ DuraBlue</b>	Fulfill Retrofit Kit for AltaBlue TT and DuraBlue D10/ D16 Melters	<b>FR GE IT JA SP</b>	7156839A 7156837A 7156843A 7169644A* 7156841A	MA	(317102) or (317107)	<b>EN - 1102240A - Issued 01/13 -&gt; Replaced by P/N 1121940_01  * available at Nordson K.K.</b>
<b>AltaBlue/ DuraBlue</b>	Fulfill Retrofit Kit for AltaBlue TT and DuraBlue D10/ D16 Melters	<b>FR GE IT SP</b>	7179753_01 7179754_01 7179755_01 7179756_01	MA	(317102) or (317107)	<b>EN - 1121940_02 - Issued 5/13</b>
<b>DuraBlue</b>	DuraBlue Adhesive Melters - Models D10 and D16	<b>CH DA DU FI FR GE IT JA NO PL PO SP SW</b>	7119827A 397774B 397778B 397509B 213729B 213717B 213727B 7119828A 397869B 7105855B 397482B 213715B 397674B	MA	(317103) or (317106)	<b>EN - 1028347B - Issued 07/03</b>

## Nordson US Hot Melt Products (sorted by Model)

B-1 - 5

### Blue Series Melters

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>DuraBlue</b>	DuraBlue Adhesive Melters - Models D4L, D10L, and D16L (Gerotor)	<b>CH</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7401350 397994 <b>A05</b> 397775B 397779B 397510B 213730B 213718 <b>A05</b> 7146346A02 213728B 7105883A 397870B 7105969 <b>A05</b> 397483B 7560786 <b>A05</b> 7105350A 213716B 397675B	MA	(317103) or (317106)	<b>EN - 1032059B</b> <b>-&gt; Replaced by P/N 1073401A05</b> <b>Issued 03/14</b>
<b>DuraBlue</b>	DuraBlue Adhesive Melters D4F	<b>GE</b> <b>SP</b>	7119864A03 7119865A03	MA	(317103) or (317106)	<b>EN - 1065648A09 - Issued 03/14</b>
<b>DuraBlue</b>	Pedestal for DuraBlue™ 4F	<b>EN</b> <b>GE</b>	7146384A 7146383A	MA	(317102) or (317107)	<b>N - Benelux BV</b> <b>Issued 01/08</b>
<b>DuraBlue II</b>	DuraBlue II Adhesive Melters Models 20 and 45	<b>CZ</b> <b>FR</b> <b>GE</b> <b>PL</b> <b>SW</b>	7580930_01 7580929_01 7580926_01 7580927_01 7580928_01	MA	(317102) or (317107)	<b>EN - 1126931_01 - Issued 08/18</b>
<b>DuraBlue/ VersaBlue</b>	Fulfill Retrofit Kit - DuraBlue/VersaBlue 25L and 50L Melters	<b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	7169241A 7169246A 7169252A 7169257A	MA	(317102) or (317107)	<b>EN - 1105309A - Issued 02/11</b>

## Nordson US Hot Melt Products (sorted by Model)

B-1 - 6

### *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>DuraBlue/ VersaBlue</b>	Fulfill Retrofit Kit for 100-Liter DuraBlue and VersaBlue Adhesive Melters	<b>FR GE IT SP</b>	7169201A 7169220A 7169214A 7169218A	MA	(317102) or (317107)	<b>EN - 1106395A - Issued 02/11</b>
<b>DuraBlue/ VersaBlue</b>	DB/VB 25 and 50 Fulfill- Lid Replacement - P/N 1123139 and 1123140	<b>PL RU</b>	7560539_01 1123432_01	IN	(317102) or (317107)	<b>EN - 1123432_01 - Issued 02/14</b>
<b>DeviceNet</b>	Profibus-DP, DeviceNet, and ControlNet Fieldbus Interface Cards	<b>FR GE IT JA PO SP</b>	7169926_04 7119831_04 7169951_04 7119808_04 7169967_04 7169942_04	MA	(317102) or (317107)	<b>EN - 1052255_08 - Issued 07/17</b>
<b>Ethernet</b>	Ethernet/IP Network Interface Card	<b>CZ FR GE IT JA PO SP</b>	7580908_09 7169927_04 7119340_04 7119739_04 7119807_04 7169968_04 7169943_04	MA	(317102) or (317107)	<b>EN - 1054600_09 - Issued 07/17</b>
<b>ProBlue</b>	ProBlue Fulfill Integrated Fill System (Generation III)	<b>CZ DU FI FR GE IT RU SP</b>	7179580_02 7179586_02 7179595_02 7179603_02 7179578_02 7179588_02 7179590_02 7179593_02	MA	(317102) or (317107)	<b>EN - 1121787_02 - Issued 5/13</b>

## Nordson US Hot Melt Products (sorted by Model)

B-1 - 7

### *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
ProBlue	ProBlue Fulfill Integrated Fill System (Generation IV)	CH FR GE IT JA SP	7192528_01 7192483_01 7192446_01 7192451_01 7192427_01 7192442_01	MA	(317102) or (317107)	EN - 1123107_01 - Issued 4/15 Issue date of translations 03/14
ProBlue	FulFill Retrofit Kit ProBlue Melters	CZ FR GE IT PL SK SP SW	7593217_05 7560636_02 7560637_02 7560638_02 7580266_03 7593218_05 7560639_02 7580084_03	MA	(317102) or (317107)	EN - 1124682_05 - Issued 4/18
ProBlue	ProBlue Adhesive Melter Pump Replacement Kit P/N 1028303, 1058305, and 1058306 (Title version A: Pump Service Kit - P/N 1028303)	DA DU FI FR GE IT JA NO PO SL SP SW	397600A 397581A 397806A 397780A 397562A 397683A 7580409B* 397654A 397617A 7105834A 397700A 397636A	IN	(317102) or (317107)	EN - 1029711B - Issued 02/05  * available at Nordson K.K.

## Nordson US Hot Melt Products (sorted by Model)

B-1 - 8

### *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>ProBlue</b>	ProBlue Pneumatic Panel Assembly Service Kit - P/N 1028307, 1058380, 1058383, or 1058385  (Title version A : Pneumatic Panel Assembly Service Kit - P/N 1028307)	<b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PO</b> <b>SL</b> <b>SP</b> <b>SW</b>	397601A 397582A 397807A 397781A 397563A 397684A 7580408B* 397655A 397618A 7105835A 397701A 397637A	IN	(317102) or (317107)	<b>EN - 1029713B - Issued 02/05</b>          <b>* available at Nordson K.K.</b>
<b>ProBlue</b>	ProBlue Pressure Discharge Valve Service Kit - P/N 1028308	<b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SL</b> <b>SP</b> <b>SW</b>	397602A 397583A 397808A 397782A 397564A 397685A 397656A 397619A 7105836A 397702A 397638A	IN	(317102) or (317107)	<b>EN - 1029714B02 - Issued 07/10</b>
<b>ProBlue</b>	ProBlue Manifold Service Kit - P/N 1028309	<b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SL</b> <b>SP</b> <b>SW</b>	397603A 397584A 397809A 397783A 397565A 397686A 397657A 397620A 7105837A 397703A 397639A	IN	(317102) or (317107)	<b>EN - 1029715_02 - Issued 08/11</b>



## Nordson US Hot Melt Products (sorted by Model)

B-1 - 9

### *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
ProBlue	RTD Service Kit - P/N 1028320	DA DU FI FR GE IT JA NO PO SL SP SW	397604A 397585A 397810A 397784A 397566A 397687A 7580410B02* 397658A 397621A 7105838A 397704A 397640A	IN	(317102) or (317107)	EN - 1029716_03 - Issued 09/18  * available at Nordson K.K
ProBlue	ProBlue Melter Main Circuit Board Service Kit - P/N 1028322	DA DU FI FR GE IT NO PO SL SP SW	397606A 397587A 397812A 397786A 397568A 397689A 397660A 397623A 7105840A 397706A 397642A	IN	(317102) or (317107)	EN - 1029718A - Issued 2002
ProBlue	ProBlue 10 Main Circuit Board Service Kit - P/N 1028323	DA DU FI FR GE IT NO PO SL SP SW	397607A 397588A 397813A 397787A 397569A 397690A 397661A 397624A 7105841A 397707A 397643A	IN	(317102) or (317107)	EN - 1029719A - Issued 2002

## Nordson US Hot Melt Products (sorted by Model)

B-1 - 10

### *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
ProBlue	6-Hose Extension Board Kit - P/N 1028324	DA DU FI FR GE IT NO PO SL SP SW	397608A 397589A 397814A 397788A 397570A 397691A 397662A 397625A 7105842A 397708A 397644A	IN	(317102) or (317107)	EN - 1029720A - Issued 2002
ProBlue	Operator's Panel/Enclosure Service Kit - P/N 1028326	DA DU FI FR GE IT NO PO SL SP SW	397610A 397591A 397816A 397790A 397572A 397693A 397664A 397627A 7105844A 397710A 397646A	IN	(317102) or (317107)	EN - 1029722A - Issued 2002
ProBlue	ProBlue P10/P15/P30 and P50 Operator's Panel Service Kit - P/N 1028327  (Title version A: Operator's Panel/Enclosure Service Kit - P/N 1028327)	DA DU FI FR GE IT NO PO SL SP SW	397611A 397592A 397817A 397791A 397573A 397694A 397665A 397628A 7105845A 397711A 397647A	IN	(317102) or (317107)	EN - 1029723B - Issued 02/05

## Nordson US Hot Melt Products (sorted by Model)

B-1 - 11

### Blue Series Melters

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>ProBlue</b>	Hose/Gun Module Service Kit - P/N 1028328	<b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SL</b> <b>SP</b> <b>SW</b>	397612A 397593A 397818A 397792A 397574A 397695A 397666A 397629A 7105846A 397712A 397648A	IN	(317102) or (317107)	<b>EN - 1029724A - Issued 2002</b>
<b>ProBlue</b>	Level Switch Service Kit, ProBlue - P/N 1038971, 1038972, 1060329, 1059911, 1060362, 1097366, and 1099690  (Title version A: Level Switch Service Kit, ProBlue - P/N 1038971 and 1038972)	<b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SL</b> <b>SP</b> <b>SW</b>	397615A 397596A 397821A 397795A 397577A 397698A 397669A 397632A 7105849A 397715A 397651A	IN	(317102) or (317107)	<b>EN - 1038989B02 - Issued 01/10</b>
<b>ProBlue</b>	6-Hose Manifold Guard Kit - P/N 1031871	<b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SL</b> <b>SP</b> <b>SW</b>	397616A 397597A 397822A 397796A 397578A 397699A 397670A 397633A 7105850A 397716A 397652A	IN	(317102) or (317107)	<b>EN - 1055774A - Issued 2003</b>

## Nordson US Hot Melt Products (sorted by Model)

B-1 - 12

### Blue Series Melters

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>ProBlue</b>	Manifold Service Kit P/Ns 1064651, 1064652, 1064653, 1064654, 1125302, 1125303, 1125308, 1125309  (Title Version B: Manifold Replacement Kit - P/Ns 1064651, 1064652, 1064653, and 1064654)	<b>JA</b>	7135023B	IN	(317102) or (317107)	<b>EN - 1049668_04 - Issued 09/16</b>
<b>ProBlue</b>	ProBlue Heater Block Kit - PN 1064649 and 1064650	<b>JA</b>	7580411_04*	IN	(317102) or (317107)	<b>EN - 1063729_04 - Issued 04/16</b> <b>* available at Nordson K.K.</b>
<b>ProBlue P4/ P7/ P10</b>	ProBlue Adhesive Melters Model P4, P7, and P10	<b>CH CR/SE CZ DA DU FI FR GE GR HU IT JA KO LA LI NO PL PO RO RU SK SL SP SW</b>	7119829_05 7179355_05 7119036_05 397262_05 397022_05 213918_05 213533_07 213544_08 397183B 7105608A* 213548_08 7119830_07 1024496A** 7192984_06 7560036_06 397281_05 397443_07 397257_05 7135063_07 7105117_07 7146687_07 7105833_05 213570_07 397258_07	MA	(317103) or (317106)	<b>EN - 1024496_08 - Issued 09/18</b>  <b>* = Abridged edition, document and translation is NOT issued by TDLL !</b> <b>** = Abridged edition, document and translation is NOT issued by TDLL !</b>

## Nordson US Hot Melt Products (sorted by Model)

B-1 - 13

### *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Pro Blue P4 /P7/ P10</b>	FulFill Retrofit Kit ProBlue 4/7/10 Melters (Generation II)	<b>CZ</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>RU</b> <b>SP</b>	7169405A 7169301A 7156550A 7156537A 7156538A 7169175A* 7169244A 7169711A 7156539A	MA	(317102) or (317107)	<b>EN - 1098477A - Issued 1/10</b>  <b>* available at Nordson K.K.</b>
<b>ProBlue P10/ P15</b>	ProBlue P10 and P15 8-Hose/Gun Expansion Base	<b>FR</b> <b>GE</b> <b>JA</b> <b>SP</b>	7119691A 7119698A 7119715A* 7119695A	MA	(317102) or (317107)	<b>EN - 1063727B - Issued 04/06</b>  <b>* available at Nordson K.K</b>
<b>ProBlue P15/ 30/ 50</b>	ProBlue Adhesive Melter Model P15, P30, and P50	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>LA</b> <b>LI</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SK</b> <b>SP</b> <b>SW</b>	7146688B02 7105904B 7105903B 7105988B 7105899B 7105913_07 7105901B 7105882_05 7192746_06 7169829_05 7105908B 7156734_07 7105914B 7169842_07 7169365_05 7156929_05 7105922B 7105905B	MA	(317103) or (317106)	<b>EN - 1058683_08 - Issued 09/18</b>

## Nordson US Hot Melt Products (sorted by Model)

B-1 - 14

### *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>ProBlue P15/ 30/ 50</b>	Fulfill Retrofit ProBlue 15 and 30/50 Melters (Generation II)	<b>CZ FR GE IT JA SP</b>	7169406A 7156838A 7156836A 7156842A 7169643A* 7156840A	MA	(317103) or (317106)	<b>EN - 1102228A - Issued 01/13</b> <b>Issue date of translations 08/10</b>  <b>* available at Nordson K.K</b>
<b>ProBlue QR</b>	ProBlue Series Quick Reference Guide	<b>EN/DA/ FI/FR// GE/IT/ NO/PO/ SP/SW/ CH/JA</b>	1124526_02	-	(317102) or (317107)	<b>Multilingual document,</b> <b>therefore one P/N only</b> <b>Issued 02/16</b>
<b>ProBlue ATS</b>	ProBlue ATS and ProBlue Liberty ATS Hot Melt Adhesive Systems	<b>CZ FR GE HU IT JA PL RO RU SK SP</b>	7580265_04 7560847_07 7560848_07 7593136_07 7560849_07 7580167_03 7580102_03 7560941_03 7593330_07 7593187_07 7560850_07	MA	(317103) or (317106)	<b>EN - 1125291_07 - Issued 10/18</b>
<b>ProBlue ATS</b>	ATS Conversion Kit - P/Ns 1125304, 1125305, 1125310, 1125311, and 1125996	<b>JA</b>	7580594_02*	IN	(317102) or (317107)	<b>EN - 1125369_02 - Issued 05/17</b> <b>* available at Nordson K.K</b>
<b>ProBlue ATS</b>	ATS Power Harness Service Kit - P/N 1125300 (1.8 m/6 ft harness) and 1125656 (6 m/20 ft harness)	<b>FR GE IT SP</b>	7593137_03 7593138_03 7593139_03 7593140_03	IN	(317102) or (317107)	<b>EN - 1125345_03 - Issued 10/18</b>

## Nordson US Hot Melt Products (sorted by Model)

B-1 - 15

### *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>ProBlue/ DuraBlue</b>	Software Service Kit - P/N 1018817	<b>DA DU FI FR GE IT NO PO SL SP SW</b>	397613A 397594A 397819A 397793A 397575A 397696A 397667A 397630A 7105847A 397713A 397649A	IN	(317102) or (317107)	<b>EN - 1029725A - Issued 2002</b>
<b>ProBlue/ DuraBlue/ AltaBlue/ DuraPail/Drum /Mesa/ AltaTouch</b>	Input/Output Expansion Card Kit - P/N 1036607	<b>DA DU FI FR GE IT JA NO PO SL SP SW</b>	397614A 397595A 397820A 397794_05 397576_05 397697_05 7169959_05 397668A 397631_05 7105848A 397714_05 397650A	IN	(317102) or (317107)	<b>EN - 1036221_05 - Issued 05/12</b>
<b>ProBlue/ DuraBlue/ DuraPail/ Mesa</b>	Display/CPU Board Service Kit - P/Ns 1028325 and 1104492 (Title version B: CPU Board Service Kit - P/N 1028325)	<b>DA DU FI FR GE IT NO PO SL SP SW</b>	397609B 397590B 397815B 397789B 397571B 397692B 397663B 397626B 7105843B 397709B 397645B	IN	(317102) or (317107)	<b>EN - 1029721C03 - Issued 10/10</b>

## Nordson US Hot Melt Products (sorted by Model)

B-1 - 16

### *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>ProBlue/ ProBlue Liberty/ DuraBlue Mesa</b>	ProBlue, ProBlue Liberty, DuraBlue, or Mesa Thermostat Service Kit - P/N 1028321  (Title version B: ProBlue and DuraBlue Thermostat Service Kit - P/N 1028321)	<b>DA DU FI FR GE IT NO PO SL SP SW</b>	397605B 397586B 397811B 397785B 397567B 397688B 397659B 397622B 7105839B 397705B 397641B	IN	(317102) or (317107)	<b>EN - 1029717_06 - Issued 05/14</b>
<b>ProBlue/ DuraBlue/ DuraDrum/ DuraPail</b>	Instructions for adapter cable (P/N 7114262)	<b>EN/ FR/ GE/ IT</b>	7119096G	IN	(317102) or (317107)	<b>Multilingual document, therefore one P/N only Issued 10/09</b>
<b>ProBlue/ DuraBlue/ AltaBlue TT</b>	ProBlue DuraBlue AltaBlue TT Adhesive Melters - User's Guide	<b>CH/DA/ EN/FI/ FR/GE/ IT/JA/ NO/SP/ SW</b>	1024497B02	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only Issued 10/08</b>
<b>ProBlue/ DuraBlue/ AltaBlue TT</b>	ProBlue DuraBlue AltaBlue TT Adhesive Melters - User's Guide	<b>BU/CZ/ EN/GE/ GR/HU/ PL/RO/ RU/TU/ CR</b>	1091164_03	OP	(317102) or (317107)	<b>Multilingual document, therefore one P/N only Issued 12/12</b>



## Nordson US Hot Melt Products (sorted by Model)

B-1 - 17

### Blue Series Melters

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>ProBlue Flex</b>	ProBlue Flex Adhesive Melter Using the OLED User Interface	<b>CH</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PO</b> <b>RU</b> <b>SP</b>	7593530_01 7593531_01 7593532_01 7593533_01 7593534_01 7593535_01 7593536_01 7593649_01* 7593537_01	MA	(317102) or (317107)	<b>EN - 1128351_01 - Issued 09/19</b>  * = not yet released
<b>ProBlue Flex</b>	ProBlue Flex with BBconn Controls Adhesive Melter	<b>CH</b> <b>CZ</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PO</b> <b>RU</b> <b>SP</b>	7593522_01 7593602_01 7593523_01 7593524_01 7593525_01 7593526_01 7593527_01 7593528_01 7593648_01* 7593529_01	MA	(317102) or (317107)	<b>EN - 1128350_01 - Issued 09/19</b>  * = not yet released
<b>ProBlue Flex</b>	ProBlue Flex with BBconn Controls Hot Melt Adhesive Melter - Installation Guide -	<b>CH</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PO</b> <b>SP</b>	7593462_01 7593463_01 7593464_01 7593465_01 7593482_01 7593475_01 7593466_01 7593467_01	OP	(317102) or (317107)	<b>EN - 1128353_01 - Issued 09/19</b>
<b>ProBlue Flex</b>	ProBlue Flex with BBconn Controls - Safety Guide -	<b>CH</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PO</b> <b>SP</b>	7593448_01 7593449_01 7593450_01 7593451_01 7593452_01 7593473_01 7593453_01 7593454_01	OP	(317102) or (317107)	<b>EN - 1128391_01 - Issued 09/19</b>

## Nordson US Hot Melt Products (sorted by Model)

B-1 - 18

### *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>ProBlue Flex</b>	ProBlue Flex with BBconn Controls - User Interface Quick Reference Guide -	<b>CH</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PO</b> <b>SP</b>	7593455_01 7593456_01 7593457_01 7593458_01 7593459_01 7593474_01 7593460_01 7593461_01	OP	(317102) or (317107)	<b>EN - 1128354_01 - Issued 09/19</b>
<b>ProBlue Flex</b>	Electrical Service Door Kit - OEM P/N 1128356 / OLED P/N 1128094	<b>CH</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PO</b> <b>SP</b>	7593554_01 7593555_01 7593556_01 7593557_01 7593558_01 7593559_01 7593560_01 7593561_01	IN	(317102) or (317107)	<b>EN - 1128378_01 - Issued 07/19</b>
<b>ProBlue Flex</b>	Fill Upgrade Kit - P/N 1127696/1128271	<b>CH</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PO</b> <b>SP</b>	7593538_01 7593539_01 7593540_01 7593541_01 7593542_01 7593543_01 7593544_01 7593545_01	IN	(317102) or (317107)	<b>EN - 1127707_02 - Issued 07/19</b>
<b>ProBlue Flex</b>	Legacy Input/Output (I/O) Kit - P/N 1127717	<b>CH</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PO</b> <b>SP</b>	7593546_01 7593547_01 7593548_01 7593549_01 7593550_01 7593551_01 7593552_01 7593553_01	IN	(317102) or (317107)	<b>EN - 1127718_01 - Issued 04/19</b>

## Nordson US Hot Melt Products (sorted by Model)

B-1 - 19

### *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>ProBlue Flex</b>	Lid Switch Service Kit - P/N 1128173	CH DU FR GE IT JA PO SP	7593562_01 7593563_01 7593564_01 7593565_01 7593566_01 7593567_01 7593568_01 7593569_01	IN	(317102) or (317107)	<b>EN - 1128379_01 - Issued 07/19</b>
<b>ProBlue Liberty</b>	ProBlue Liberty Hot Melt Adhesive System	CH CZ DU FR GE IT JA PL RU SP SW	7192585_01 7192899_01 7560094_01 7192593_01 7192589_01 7192588_01 7192586_01 7192833_01 7560029_01 7192636_01 7560605_01	MA	(317102) or (317107)	<b>EN - 1123388_01 - Issued 07/15</b> <b>Issue date of translations 05/14</b> <b>Obsolete!</b> <b>Replaced by P/N 1124685_02</b>
<b>ProBlue Liberty</b>	ProBlue Liberty Hot Melt Adhesive System	GE KO PO RO SK	7593182_03 7580649_02 7580938_02 7580120_02 7593186_03	MA	(317102) or (317107)	<b>EN - 1124685_03 - Issued 09/18</b>
<b>ProBlue Liberty</b>	ProBlue Liberty System Calibration Warning	EN/CZ DU/FR/ GE/IT/ PL/SP/ CH/JA	1124822_01	-	(317102) or (317107)	<b>Multilingual document,</b> <b>therefore one P/N only</b> <b>Issued 12/15</b>

## Nordson US Hot Melt Products (sorted by Model)

B-1 - 20

### Blue Series Melters

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
ProBlue Liberty QR	ProBlue Liberty System Quick Reference	EN/CZ DU//FR/ GE/IT/ PL/RU/ SP/CH/ JA/KO	1124779_01	-	(317102) or (317107)	<b>Multilingual document, therefore one P/N only Issued 12/15</b>
ProBlue Liberty QR	ProBlue Liberty System Quick Reference	EN/CR/ HU/SE/ SK/SL	7560985_01	-	(317102) or (317107)	<b>EN - 1124779_01 Multilingual document, therefore one P/N only Issued 12/15</b>
Profinet	Profinet IO Network Interface Interface Card	CZ	7580910_03	MA	(317102) or (317107)	<b>EN - 1125091_03 - Issued 07/17</b>
Profinet	Profinet IO Network Starter Kit	CZ	7580909_03	MA	(317102) or (317107)	<b>EN - 1124961_03 - Issued 03/18</b>
PURBlue	PURBlue 4 Adhesive Melter	CZ DA DU FR GE HU IT PL PO RU SL SP SW	7169674_03 7169746_03 7156412_04 7156403A 7156404_04 7580246_04 7156401_04 7156708A03 7156421A 7179571_03 7169631_03 7156408A 7156405A	MA	(317102) or (317107)	<b>EN - 1098452_04 - Issued 11/13 Product Discontinued 30 March 2018, Product Obsolescence 31 October 2018. Replacement by AltaPUR™ Slug Melter.</b>

## Nordson US Hot Melt Products (sorted by Model)

B-1 - 21

### *Blue Series Melters*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
PURBlue	PURBlue 4 Adhesive Melter Upgrade Kit - P/N 1120270	CZ FR GE IT PL PO SP	7169879_01 7169881_01 7169872_01 7169870_01 7169886_01 7169861_01 7169859_01	IN	(317102) or (317107)	EN - 1120277_01 - Issued 03/12 Product Discontinued 30 March 2018, Product Obsolescence 31 October 2018. Replacement by AltaPUR™ Slug Melter.
PURBlue	PURBlue 4 High-Output Adhesive Melter	CZ FR GE IT PL PO SP	7169878_01 7169880_01 7169871_01 7169869_01 7169885_01 7169860_01 7169858_01	MA	(317102) or (317107)	EN - 1120255_01 - Issued 01/13 Issue date of translations 02/12 Product Discontinued 30 March 2018, Product Obsolescence 31 October 2018. Replacement by AltaPUR™ Slug Melter.

B-2 - 1

## Nordson US Hot Melt Products (sorted by Model)

### Series 3000V (Vista)

Model	Product Title	CE	Langs.	P/N	Type	Price Category	Notes
Series 3000V	Series 3000V Low Level Indicator		GE	213634A	IN	(317102) or (317107)	<b>Source:</b> <b>EN:</b> 237473A
Series 3000V	Series 3000 V Input/Output Board		GE	405199K	IN	(317102) or (317107)	<b>Source</b> <b>EN:</b> 229823K
Series 3000V	Pressure Dump Valve Service Kit for Series 3000 Vista Units		GE	409325A	IN	(317102) or (317107)	<b>Source</b> <b>EN:</b> 237479A
Series 3000V	Vista Control Guide		FR	458162B	OP	(317102) or (317107)	<b>Source</b> <b>EN:</b> 321213B
Series 3000V	Vista Profibus Gateway Interface User's Guide		GE	397917A_02	MAN	(317102) or (317107)	<b>Source</b> <b>EN:</b> 321288A_02 - Issued 03/02

B-2 - 2

## Nordson US Hot Melt Products (sorted by Model)

### Series 3000V (Vista)

Model	Product Title	CE	Langs.	P/N	Type	Price Category	Notes
<b>Series 3100V-PC</b>	SERIES 3100V Hot Melt Material Applicator with 6:1 / 14:1 SP30 Piston Pump and Pattern Controller	Y	DA DU FI FR GE IT NO PL PO SP SW	403170E 403171E 403172A 403173E 403174E 403175E 403176E 458299E 403177A 403178E 403179E	MA Part O and Part A	(317103) or (317106)	<b>Source</b> <i>Manual Config. Codes</i> <b>EN:</b> 248449    3100V-XEAPXX/X <b>EN:</b> 248450    3100V-XGAPXX/X  Appropriate OP card included
<b>Series 3100V-TC (Tetra)</b>	SERIES 3100V Hot Melt Material Applicator with 14:1 SP Piston Pump and VistaTemperature Controller	Y	DA DU FI FR GE GR IT NO PL PO SP SW	409264E 403127E 409265E 409266E 409267E 213450G02 409268E 409269E 7119851H 409270E 409271E 409272E	MA Part O and Part A	(317103) or (317106)	<b>Source</b> <i>Manual Config. Codes</i> <b>EN:</b> 272381H    3100V-XEATXX/4  Appropriate OP card included

B-2 - 3

## Nordson US Hot Melt Products (sorted by Model)

### Series 3000V (Vista)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Series 3100V-VC</b>	SERIES 3100V Hot Melt Material Applicator with 6:1 / 14:1 SP30 Piston Pump and Vista Controller	DA DU FI FR GE IT NO PL PO SP SW	403160E 403169E 403161E 403162E 403163E 403164E 403165E 412793E 403166A 403167E 403168E	MA Part O and Part A	(317103) or (317106)	<b>Source</b> <i>Manual Config. Codes</i> <b>EN:</b> 237346      3100V-XEAVXX/X <b>EN:</b> 244943      3100V-XGAVXX/X  Appropriate OP card included
<b>Series 3100V-PC / 3400V-PC</b>	Series 3100V/3400V Hot Melt Material Applicator with AC Constant-Speed Gear Pump, Standard Filter, Pattern Control	DA DU FI FR GE IT NO PO SP SW	407352A 407353A 407354A 407355A 407356A 407357A 407358A 407359A 407360A 407361A	OP	(317102) or (317107)	<b>Source</b> <b>EN:</b> 237532A
<b>Series 3100V-VC / 3400V-VC</b>	Series 3100V/3400V Hot Melt Material Applicator with AC Constant-Speed Gear Pump, Standard Filter, Standard Control	DA DU FI FR GE IT NO PO SP SW	407342A 407343A 407344A 407345A 407346A 407347A 407348A 407349A 407350A 407351A	OP	(317102) or (317107)	<b>Source</b> <b>EN:</b> 237531A



B-2 - 4

## Nordson US Hot Melt Products (sorted by Model)

### Series 3000V (Vista)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Series 3100V-TC / 3400V-TC / 3500V-TC</b>	Series 3100V/3400V/3500V Hot Melt Material Applicator with Piston Pump, Standard Filter, Temperature Control (TC)	DA DU FI FR GE GR IT NO PL PO SP SW	407075B 407076B 407077B 407078B 407079B 213451B 407080B 407081B 458341B 407082B 407083B 407084B	OP	(317102) or (317107)	<b>Source</b> EN: 237518B
<b>Series 3100V-TC / 3400V-TC / 3500V-TC (TCGM)</b>	SERIES 3100V, 3400V, 3500V Hot Melt Material Applicator with 6:1 / 14:1 SP30 Piston Pump and Temperature Controller	DA DU FI FR GE IT NO PO SP SW	409254E 409255E 409256E 409257E 409258E 409259E 409260E 409261E 409262E 409263E	MA Part O and Part A	(317103) or (317106)	<b>Source</b> <i>Manual Config. Codes</i> EN: 309734      3100V-XEATXX/X EN: 310647      3400V-XEATXX/X EN: 310713      3500V-XEATXX/X EN: 273193      3100V-XGATXX/X EN: 248451      3400V-XGATXX/X EN: 309662      3500V-XGATXX/X  Appropriate OP card included
<b>Series 3100V-PC / 3400V-PC / 3500V-PC / 3700V-PC</b>	Series 3100V/3400V/3500V/3700V Hot Melt Material Applicator with Piston Pump, Standard Filter, Pattern Control	DA DU FI FR GE IT NO PL PO SP SW	403151C 403224C 403152C 403153C 403154C 403155C 403156C 412787C 403157C 403158C 403159C	OP	(317102) or (317107)	<b>Source</b> EN: 237379C

B-2 - 5

## Nordson US Hot Melt Products (sorted by Model)

### Series 3000V (Vista)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Series 3100V-VC / 3400V-VC / 3500V-VC / 3700V-VC</b>	Series 3100V/3400V/3500V/3700V Hot Melt Material Applicator with Piston Pump, Standard Filter, Standard Control	DA DU FI FR GE GR IT NO PL PO RU SP SW	403147C 403223C 403148C 403124C 403118C 213419C 403136C 403149C 412788C 403129C 409176C 403121C 403150C	OP	(317102) or (317107)	<b>Source</b> <b>EN:</b> 229777C
<b>Series 3400V-PC</b>	SERIES 3400V Hot Melt Material Applicator with 6:1 / 14:1 SP30 Piston Pump and Pattern Controller	DA DU FI FR GE IT NO PO SP SW	403190E 403191E 403192A 403193E 403194E 403195E 403196E 403197A 403198E 403199E	MA Part O and Part A	(317103) or (317106)	<b>Source</b> <i>Manual Config. Codes</i> <b>EN:</b> 248446      3400V-XEAPXX/X <b>EN:</b> 248447      3400V-XGAPXX/X  Appropriate OP card included
<b>Series 3400V-VC</b>	SERIES 3400V Hot Melt Material Applicator - with AC Constant-Speed Gear Pump and Vista Controller	GE	447639E	MA Part O and Part A	(317103) or (317106)	<b>Source</b> <i>Manual Config. Codes</i> <b>EN:</b> 237681E      3400V-XKJVXX/X <b>EN:</b> 273280E      3400V-XLJVXX/X

B-2 - 6

## Nordson US Hot Melt Products (sorted by Model)

### Series 3000V (Vista)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Series 3400V-VC</b>	SERIES 3400V Hot Melt Material Applicator with 6:1 / 14:1 SP30 Piston Pump and Vista Controller	DA DU FI FR GE IT NO PL PO SP SW	403180E 403181E 403182A 403183E 403184E 403185E 403186E 458338E 403187A 403188E 403189E	MA Part O and Part A	(317103) or (317106)	<b>Source</b> <i>Manual Config. Codes</i> EN: 237347      3400V-XEAVXX/X EN: 243590      3400V-XGAVXX/X  Appropriate OP card included
<b>Series 3500V-PC</b>	SERIES 3500V Hot Melt Material Applicator with 6:1 / 10:1 / 14:1 / 21:1 SP30 Piston Pump and Pattern Controller	DA DU FI FR GE IT NO PO SP SW	403210E 403211E 403212A 403213E 403214E 403215E 403216E 403217A 403218E 403219E	MA Part O and Part A	(317103) or (317106)	<b>Source</b> <i>Manual Config. Codes</i> EN: 331237      3500V-XDAPXX/X EN: 272412      3500V-XEAPXX/X EN: 276140      3500V-XFAPXX/X EN: 288000      3500V-XGAPXX/X  Appropriate OP card included
<b>Series 3500V-VC</b>	SERIES 3500V Hot Melt Material Applicator with 6:1 / 10:1 / 14:1 / 21:1 SP30 Piston Pump and Vista Controller	GE PL	213566E 464809E	MA Part O and Part A	(317103) or (317106)	<b>Source</b> <i>Manual Config. Codes</i> EN: 331245E      3500V-XDBVXX/X EN: 331203E      3500V-XEBVXX/X EN: 331206E      3500V-XFBVXX/X EN: 331208E      3500V-XGBVXX/X  Appropriate OP card included

B-2 - 7

## Nordson US Hot Melt Products (sorted by Model)

### Series 3000V (Vista)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Series 3500V-VC</b>	SERIES 3500V Hot Melt Material Applicator with 6:1 / 10:1 / 14:1 / 21:1 SP30 Piston Pump and Vista Controller	DA DU FI FR GE IT NO PL PO SP SW	403200E 403201E 403202A 403203E 403204E 403205E 403206E 458339E 403207A 403208E 403209E	MA Part O and Part A	(317103) or (317106)	<b>Source</b> <i>Manual Config. Codes</i> <b>EN:</b> 331236      3500V-XDAVXX/X <b>EN:</b> 237348      3500V-XEAVXX/X <b>EN:</b> 240813      3500V-XFAVXX/X <b>EN:</b> 248432      3500V-XGAVXX/X  Appropriate OP card included
<b>Series 3500V-PC / 3700V-PC</b>	Series 3500V/3700V Hot Melt Material Applicator with Piston Pump, Reverse-Flush Filter, Pattern Control	DA DU FI FR GE IT NO PO SP SW	407065B 407066B 407067B 407068B 407069B 407070B 407071B 407072B 407073B 407074B	OP	(317102) or (317107)	<b>Source</b> <b>EN:</b> 237506B
<b>Series 3500V-VC / 3700V-VC</b>	Series 3500V/3700V Hot Melt Material Applicator with Piston Pump, Reverse-Flush Filter, Standard Control	DA DU FI FR GE IT NO PO SP SW	407055B 407056B 407057B 407058B 407059B 407060B 407061B 407062B 407063B 407064B	OP	(317102) or (317107)	<b>Source</b> <b>EN:</b> 237505B

## Nordson US Hot Melt Products (sorted by Model)

### Series 3000V (Vista)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Series 3700V-VC</b>	SERIES 3700V Hot Melt Material Applicator with 6:1 / 10:1 / 14:1 / 21:1 SP30 Piston Pump and Vista Controller	DA DU FI FR GE IT NO PO SP SW	409244E 409245E 409246E 409247E 409248E 409249E 409250E 409251E 409252E 409253E	MA Part O and Part A	(317103) or (317106)	<b>Source</b> <i>Manual Config. Codes</i> <b>EN:</b> 331260      3700V-XDBVXX/X <b>EN:</b> 304985G02 3700V-XEBVXX/X <b>EN:</b> 309663      3700V-XFBVXX/X <b>EN:</b> 237634      3700V-XGBVXX/X  Appropriate OP card included
<b>Series 3800V-VC</b>	SERIES 3800V Hot Melt Material Applicator with AC Constant-Speed Gear Pump and Vista Controller	GE IT	213449E 213347E	MA Part O and Part A	(317103) or (317106)	<b>Source</b> <i>Manual Config. Codes</i> <b>EN:</b> 237655E      3830V-XKJVXX/X <b>EN:</b> 237653E      3830V-XLJVXX/X
<b>Series 3800V-PC / 3900V-PC</b>	Series 3800V/3900V Hot Melt Material Applicator with AC Constant-Speed Gear Pump, Standard Filter, Pattern Control	DA DU FI FR GE IT NO PO SP SW	407372A 407373A 407374A 407375A 407376A 407377A 407378A 407379A 407380A 407381A	OP	(317102) or (317107)	<b>Source</b> <b>EN:</b> 237534A
<b>Series 3800V-PC / 3900V-PC</b>	Series 3800V/3900V Hot Melt Material Applicator with Piston Pump, Reverse-Flush Filter, Pattern Control	DA DU FI FR GE IT NO PO SP SW	407115B 407116B 407117B 407118B 407119B 407120B 407121B 407122B 407123B 407124B	OP	(317102) or (317107)	<b>Source</b> <b>EN:</b> 237528B

B-2 - 9

## Nordson US Hot Melt Products (sorted by Model)

### Series 3000V (Vista)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Series 3800V-PC / 3900V-PC</b>	Series 3800V/3900V Hot Melt Material Applicator with Piston Pump, Standard Filter, Pattern Control	DA DU FI FR GE IT NO PO SP SW	407095B 407096B 407097B 407098B 407099B 407100B 407101B 407102B 407103B 407104B	OP	(317102) or (317107)	<b>Source</b> <b>EN: 237526B</b>
<b>Series 3800V-VC / 3900V-VC</b>	Series 3800V/3900V Hot Melt Material Applicator with AC Constant-Speed Gear Pump, Standard Filter, Standard Control	DA DU FI FR GE IT NO PO SP SW	407362A 407363A 407364A 407365A 407366A 407367A 407368A 407369A 407370A 407371A	OP	(317102) or (317107)	<b>Source</b> <b>EN: 237533A</b>
<b>Series 3800V-VC / 3900V-VC</b>	Series 3800V/3900V Hot Melt Material Applicator with Piston Pump, Reverse-Flush Filter, Standard Control	DA DU FI FR GE IT NO PO SP SW	407105B 407106B 407107B 407108B 407109B 407110B 407111B 407112B 407113B 407114B	OP	(317102) or (317107)	<b>Source</b> <b>EN: 237527B</b>

B-2 - 10

## Nordson US Hot Melt Products (sorted by Model)

### Series 3000V (Vista)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Series 3800V-VC / 3900V-VC</b>	Series 3800V/3900V Hot Melt Material Applicator with Piston Pump, Standard Filter, Standard Control	DA DU FI FR GE IT NO PO SP SW	407085B 407086B 407087B 407088B 407089B 407090B 407091B 407092B 407093B 407094B	OP	(317102) or (317107)	<b>Source</b> <b>EN:</b> 237525B
<b>Series 3860V-VC / 3890V-VC</b>	SERIES 3800V Hot Melt Material Applicator with AC Constant-Speed Gear Pump and Vista Controller	FI GE IT SP	464903E 413035E 464778E 458191E	MA Part O and Part A	(317103) or (317106)	<b>Source</b> <i>Manual Config. Codes</i> <b>EN:</b> 237663E    3860V-XKJVXX/X <b>EN:</b> 237661E    3860V-XLJVXX/X <b>EN:</b> 237671E    3890V-XKJVXX/X <b>EN:</b> 237669E    3890V-XLJVXX/X  Appropriate OP card included
<b>Series 3860V-VC / 3890V-VC</b>	SERIES 3800V Hot Melt Material Applicator with 21:1 SP30 Piston Pump and Vista Controller	DU FI FR GE	213519E 213302E 458200E 213064E	MA Part O and Part A	(317103) or (317106)	<b>Source</b> <i>Manual Config. Codes</i> <b>EN:</b> 309856E    3860V-XFAVXX/X <b>EN:</b> 310299E    3890V-XFAVXX/X  Appropriate OP card included
<b>Series 3860V-VC / 3890V-VC</b>	SERIES 3800V Hot Melt Material Applicator with 21:1 SP30 Piston Pump and Vista Controller	FI FR SW	213229E 458169E 213304E	MA Part O and Part A	(317103) or (317106)	<b>Source</b> <i>Manual Config. Codes</i> <b>EN:</b> 237519E    3860V-XFBVXX/X <b>EN:</b> 323994E    3890V-XFBVXX/X  Appropriate OP card included
<b>Series 3900V-VC</b>	SERIES 3900V Hot Melt Material Applicator with 21:1 SP30 Piston Pump and Vista Controller	FI FR GE	213303E 447770E 213184E	MA	(317103) or (317106)	<b>Source</b> <i>Manual Config. Codes</i> <b>EN:</b> 310301E    3960V-XFBVXX/X  Appropriate OP card included

B-3 - 1

## Nordson US Hot Melt Products (sorted by Model)

### Series 2000 / Series 3000 / Series 5000 / Series 6000

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Series 2300</b>	SERIES 2300 Hot Melt Applicators	<b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b> <b>SW</b>	292732A 292731A 292735A 292733A 292734A 292736A 292737A 292776A	IN	(317102) or (317107)	
<b>Series 2300</b>	Fulfill Retrofit Kit Series 2300 Melters	<b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	7169243A 7169248A 7169254A 7169259A	MA	(317102) or (317107)	<b>EN - 1104162A - Issued 01/13 Obsolete!</b>
<b>Series 3000</b>	Pressure Dump Valve Service Kit for Series 3000 Units	<b>GE</b>	409324B	IN	(317102) or (317107)	<b>EN - 108838B</b>
<b>Series 3000</b>	Fulfill Retrofit 3000 Series Melters	<b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>SP</b>	7179622_01 7179623_01 7179624_01 7179626_01 7179628_01	MA	(317102) or (317107)	<b>EN - 1121935_01 - Issued 04/13 Obsolete!</b>
<b>Series 3000 ACMs</b>	Series 3000 ACMs	<b>FR</b> <b>GE</b>	447713A 447685A	MA	(317104) or (317105)	<b>EN - 1001762A</b>
<b>Series 3100</b>	SERIES 3100 Hot Melt Applicator with Gear Pump  Each manual (MA) is composed of several parts, these have been listed under Notes.	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	290956 290957 290958 290959 290960	MA	(317103) or (317106)	<b>DU</b> = 269831 OP, 284173 IN, RTD, H200 <b>FR</b> = 106531 OP, 284175 IN, RTD, H200 <b>GE</b> = 106532 OP, 284176 IN, RTD; H200 <b>IT</b> = 106533 OP, 284177 IN, RTD, H200 <b>SP</b> = 106534 OP, 284180 IN, RTD, H200
<b>Series 3100</b>	SERIES 3100 Hot Melt Applicator with Piston Pump / MultiScan	<b>DU</b> <b>GE</b> <b>IT</b> <b>SP</b>	269895 269894 269898 269899	MA	(317103) or (317106)	



B-3 - 2

## Nordson US Hot Melt Products (sorted by Model)

### *Series 2000 / Series 3000 / Series 5000 / Series 6000*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Series 3100</b>	SERIES 3100 Hot Melt Material Applicator with 14:1 SP Piston Pump, A Manifold, and MultiScan Controller	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>SP</b>	284092 269897 284091 284094 412765C 284095	MA	(317103) or (317106)	<b>EN - 106687C</b>
<b>Series 3100</b>	SERIES 3100 Hot Melt Applicator with Piston Pump SP 30 14:1 / MultiScan  Each manual (MA) is composed of several parts, these have been listed under Notes.	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	290946 290947 290948 290949 290950	MA	(317103) or (317106)	<b>DU</b> = 269831 OP, 284173 IN, 284092 MA, RTD, H200 <b>FR</b> = 106531 OP, 284175 IN, 269897 MA, RTD, H200 <b>GE</b> = 106532 OP, 284176 IN, 284091 MA, RTD; H200 <b>IT</b> = 106533 OP, 284177 IN, 284094 MA, RTD, H200 <b>SP</b> = 106534 OP, 284180 IN, 284095 MA, RTD, H200
<b>Series 3100</b>	SERIES 3100 Hot Melt Applicator with Piston Pump SP 30 14:1 / UniScan	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b>	283009 283011 283008 283012	MA	(317103) or (317106)	
<b>Series 3100</b>	SERIES 3100 Hot Melt Applicator with Piston Pump SP 30 14:1 / UniScan  Each manual (MA) is composed of several parts, these have been listed under Notes.	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	290951 290952 290953 290954 290955	MA	(317103) or (317106)	<b>DU</b> = 269831 OP, 284173 IN, 283009 MA, RTD, H200 <b>FR</b> = 106531 OP, 284175 IN, 283011 MA, RTD, H200 <b>GE</b> = 106532 OP, 284176 IN, 283008 MA, RTD; H200 <b>IT</b> = 106533 OP, 284177 IN, 283012 MA, RTD, H200 <b>SP</b> = 106534 OP, 284180 IN, RTD, H200

B-3 - 3

## Nordson US Hot Melt Products (sorted by Model)

### Series 2000 / Series 3000 / Series 5000 / Series 6000

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Series 3100</b> <b>Series 3400</b> <b>Series 3500</b> <b>Series 3700</b>	SERIES 3100/ 3400/ 3500/ 3700 Hot Melt Material Applicators	<b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	284172A 284173A 284171A 284174A 284175A 284176A 292868A 284177A 284178A 284179A 284180A 284181A	IN	(317102) or (317107)	
<b>Series 3100</b> <b>Series 3400</b> <b>Series 3500</b> <b>Series 3700</b>	SERIES 3100/3400/3500/3700 Hot Melt Material Applicator with Piston Pump, MultiScan Controller and Manifolds A, B, or S	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>SP</b> <b>SW</b>	458258A* 269816 269831 106530A 269815 106531 106532 7119545A 106533 413034A 269814 106534 269832	OP	(317102) or (317107)	<b>* = Document and translation is NOT issued by TDLL !</b>
<b>Series 3400</b>	SERIES 3400 Hot Melt Applicator with Gear Pump  Each manual (MA) is composed of several parts, these have been listed under Notes.	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	290971 290972 290973 290974 290975	MA	(317103) or (317106)	<b>DU</b> = 269831 OP, 284173 IN, RTD, H200 <b>FR</b> = 106531 OP, 284175 IN, RTD, H200 <b>GE</b> = 106532 OP, 284176 IN, RTD; H200 <b>IT</b> = 106533 OP, 284177 IN, RTD, H200 <b>SP</b> = 106534 OP, 284180 IN, RTD, H200

B-3 - 4

## Nordson US Hot Melt Products (sorted by Model)

### Series 2000 / Series 3000 / Series 5000 / Series 6000

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Series 3400</b>	SERIES 3400 Hot Melt Applicator with Piston Pump / MultiScan	<b>CZ</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	7135296A* 269841 106689E 283006 269842 269840 269810	MA	(317103) or (317106)	<b>* = Document and translation is NOT issued by TDLL !</b>
<b>Series 3400</b>	SERIES 3400 Hot Melt Applicator with Piston Pump SP 30 14:1 / MultiScan	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	284104 284105 284103 284106 284107	MA	(317103) or (317106)	
<b>Series 3400</b>	SERIES 3400 Hot Melt Applicator with Piston Pump SP 30 14:1 / MultiScan  Each manual (MA) is composed of several parts, these have been listed under Notes.	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b> <b>SW</b>	290961 290962 290963 290964 290965 290391	MA	(317103) or (317106)	<b>DU</b> = 269831 OP, 284173 IN, 284104 MA, RTD, H200 <b>FR</b> = 106531 OP, 284175 IN, 284105 MA, RTD, H200 <b>GE</b> = 106532 OP, 284176 IN, 284103 MA, RTD, H200 <b>IT</b> = 106533 OP, 284177 IN, 284106 MA, RTD, H200 <b>SP</b> = 106534 OP, 284180 IN, 284107 MA, RTD, H200
<b>Series 3400</b>	SERIES 3400 Hot Melt Applicator with Piston Pump / UniScan	<b>DU</b> <b>GE</b> <b>IT</b> <b>SP</b>	283001 283000 283004 283005	MA	(317103) or (317106)	
<b>Series 3400</b>	SERIES 3400 Hot Melt Applicator with Piston Pump SP 30 14:1 / UniScan	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	284098 283003 284097 284100 284101	MA	(317103) or (317106)	

B-3 - 5

## Nordson US Hot Melt Products (sorted by Model)

### Series 2000 / Series 3000 / Series 5000 / Series 6000

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Series 3400</b>	SERIES 3400 Hot Melt Applicator with Piston Pump SP 30 14:1 / UniScan  Each manual (MA) is composed of several parts, these have been listed under Notes.	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	290966 290967 290968 290969 290970	MA	(317103) or (317106)	<b>DU</b> = 269831 OP, 284173 IN, 284098 MA, RTD, H200 <b>FR</b> = 106531 OP, 284175 IN, 283003 MA, RTD, H200 <b>GE</b> = 106532 OP, 284176 IN, 284097 MA, RTD; H200 <b>IT</b> = 106533 OP, 284177 IN, 284100 MA, RTD, H200 <b>SP</b> = 106534 OP, 284101 MA, RTD, H200
<b>Series 3500</b>	SERIES 3500 Hot Melt Applicator with Gear Pump  Each manual (MA) is composed of several parts, these have been listed under Notes.	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	290986 290987 290988 290989 290990	MA	(317103) or (317106)	<b>DU</b> = 269831 OP, 284173 IN, RTD, H200 <b>FR</b> = 106531 OP, 284175 IN, RTD, H200 <b>GE</b> = 106532 OP, 284176 IN, RTD; H200 <b>IT</b> = 106533 OP, 284177 IN, RTD, H200 <b>SP</b> = 106534 OP, 284180 IN, RTD, H200
<b>Series 3500</b>	SERIES 3500 Hot Melt Applicator with Piston Pump SP 30 14:1 / MultiScan / UniScan  Each manual (MA) is composed of several parts, these have been listed under Notes.	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	290976 290977 290978 290979 290980	MA	(317103) or (317106)	<b>DU</b> = 269831 OP, 284173 IN, 284038 MA, RTD, H200 <b>FR</b> = 106531 OP, 284175 IN, 284039 MA, RTD, H200 <b>GE</b> = 106532 OP, 284176 IN, 284037 MA, RTD; H200 <b>IT</b> = 106533 OP, 284177 IN, 284040 MA, RTD, H200 <b>SP</b> = 106534 OP, 284180 IN, 284041 MA, RTD, H200
<b>Series 3500</b>	SERIES 3500 Hot Melt Applicator with Piston Pump SP 30 21:1/ MultiScan / UniScan  Each manual (MA) is composed of several parts, these have been listed under Notes.	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	290981 290982 290983 290984 290985	MA	(317103) or (317106)	<b>DU</b> = 269831 OP, 284173 IN, 284050 MA, RTD, H200 <b>FR</b> = 106531 OP, 284175 IN, 284051 MA, RTD, H200 <b>GE</b> = 106532 OP, 284176 IN, 284049 MA, RTD; H200 <b>IT</b> = 106533 OP, 284177 IN, 284052 MA, RTD, H200 <b>SP</b> = 106534 OP, 284180 IN, 284053 MA, RTD, H200
<b>Series 3700</b>	SERIES 3700 Hot Melt Applicator with Gear Pump  Each manual (MA) is composed of several parts, these have been listed under Notes.	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	292701 292702 292703 292704 292705	MA	(317103) or (317106)	<b>DU</b> = 269831 OP, 284173 IN, RTD, H200 <b>FR</b> = 106531 OP, 284175 IN, RTD, H200 <b>GE</b> = 106532 OP, 284176 IN, RTD; H200 <b>IT</b> = 106533 OP, 284177 IN, RTD, H200 <b>SP</b> = 106534 OP, 284180 IN, RTD, H200

B-3 - 6

## Nordson US Hot Melt Products (sorted by Model)

### Series 2000 / Series 3000 / Series 5000 / Series 6000

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Series 3700</b>	SERIES 3700 Hot Melt Applicator with Piston Pump SP 30 14:1 / MultiScan  Each manual (MA) is composed of several parts, these have been listed under Notes.	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	290991 290992 290993 290994 290995	MA	(317103) or (317106)	<b>DU</b> = 269831 OP, 284173 IN, 284038 MA, RTD, H200 <b>FR</b> = 106531 OP, 284175 IN, 284039 MA, RTD, H200 <b>GE</b> = 106532 OP, 284176 IN, 284037 MA, RTD; H200 <b>IT</b> = 106533 OP, 284177 IN, 284040 MA, RTD, H200 <b>SP</b> = 106534 OP, 284180 IN, 284041 MA, RTD, H200
<b>Series 3700</b>	SERIES 3700 Hot Melt Applicator with Piston Pump SP 30 21:1 / MultiScan  Each manual (MA) is composed of several parts, these have been listed under Notes.	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	290996 290997 290998 290999 292700	MA	(317103) or (317106)	<b>DU</b> = 269831 OP, 284173 IN, 284050 MA, RTD, H200 <b>FR</b> = 106531 OP, 284175 IN, 284051 MA, RTD, H200 <b>GE</b> = 106532 OP, 284176 IN, 284049 MA, RTD; H200 <b>IT</b> = 106533 OP, 284177 IN, 284052 MA, RTD, H200 <b>SP</b> = 106534 OP, 284180 IN, 284053 MA, RTD, H200
<b>Series 3800</b> <b>Series 3900</b>	SERIES 3800/ 3900 Hot Melt Material Applicators	<b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	290740A 290741A 290739A 290742A 290743A 290744A 290745A 290747A	IN	(317102) or (317107)	
<b>Series 3800</b> <b>Series 3900</b>	SERIES 3800/ 3900 Hot Melt Applicator SP 21:1  Each manual (MA) is composed of several parts, these have been listed under Notes.	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	292706 292707 292708 292709 292710	MA	(317103) or (317106)	<b>DU</b> = 290741 IN, 284050 MA, RTD, H200 <b>FR</b> = 290743 IN, 284051 MA, RTD H200 <b>GE</b> = 290744 IN, 284049 MA, RTD, H200 <b>IT</b> = 290745 IN, 284052 MA, RTD, H200 <b>SP</b> = 290747 IN, 284053 MA, RTD, H200
<b>Series 3860</b>	SERIES 3860 Hot Melt Material Applicator with DC Pump, K or L Manifold, M.P.C. and Multiscan Controller	<b>PO</b>	397530B	MA	(317103) or (317106)	<b>EN - 334583B</b>

B-3 - 7

## Nordson US Hot Melt Products (sorted by Model)

### *Series 2000 / Series 3000 / Series 5000 / Series 6000*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Series 3860/ 3960</b>	Fulfill Retrofit Series 3860 and 3960 Melters	<b>FR GE IT SP</b>	7179749_01 7179750_01 7179751_01 7179752_01	MA	(317103) or (317106)	<b>EN - 1121936_01 - Issued 04/13</b>
<b>Series 5625P</b>	Series 5625P Melt-On-Demand Application System	<b>FR</b>	405294C	OP	(317102) or (317107)	
<b>Series 5625P</b>	Series 5625P Melt-On-Demand Application System Precision Control Reference Guide	<b>FR</b>	405295C	IN	(317102) or (317107)	
<b>Series 5625P</b>	Series 5625P Melt-On-Demand Application System Single-Drive Dispensing System with Transfer Pump	<b>FR</b>	405293A	MA	(317103) or (317106)	
<b>Series 6000</b>	SERIES 6000	<b>SP</b>	458049A	MA	(317104) or (317105)	<b>Section:      Models covered:</b> <b>1 - 6            6120C</b> <b>7                6120A + 6065C</b> <b>8                6120A + 6120C</b> <b>9                6120C</b> <b>10               6065C</b>
<b>Series 6000 6065</b>	SERIES 6000 Model 6065	<b>GE</b>	269883	MA	(317104) or (317105)	
<b>Series 6000 (6065, 6120, 6220)</b>	SERIES 6000 (6065, 6120, 6220) Hot Melt Material Applicator	<b>DU EN FR GE IT SP</b>	269863 269862 269864 269865 269866 269868	OP	(317102) or (317107)	
<b>Series 6000 6120A</b>	SERIES 6000 Model 6120A	<b>GE IT</b>	104767A 269843	MA	(317104) or (317105)	

B-3 - 8

## Nordson US Hot Melt Products (sorted by Model)

### *Series 2000 / Series 3000 / Series 5000 / Series 6000*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Series 6000 6120C</b>	SERIES 6000 Model 6120C	<b>IT</b>	269844	MA	(317104) or (317105)	
<b>Series OS6000</b>	SERIES OS6000 Hot Melt Material Applicators	<b>DU EN SP</b>	292947A 292855A 292871A	IN	(317102) or (317107)	
<b>SP30 6:1</b>	SP30 6:1 Piston Pump Installation and Maintenance	<b>GE</b>	284185	MA	(317102) or (317107)	
<b>SP30 14:1</b>	SP30 14:1 Piston Pump  Installation and Maintenance Instructions	<b>DU EN FI FR GE IT SP</b>	284038 108715B 397419B 284039 284037 284040 284041	MA	(317102) or (317107)	<b>Issued 10/95</b>
<b>SP30 21:1</b>	SP30 21:1 Piston Pump  Installation and Maintenance Instructions	<b>DU EN FR GE IT SP</b>	284050 108720D 284051 284049 284052 284053	MA	(317102) or (317107)	<b>Issued 02/01</b>
<b>UMI</b>	UNIVERSAL MACHINE INTERFACE FOR SERIES 6000 APPLICATORS	<b>GE</b>	267968	MA	(317102) or (317107)	

B-4 - 1

## Nordson US Hot Melt Products (sorted by Model)

### *Other Melters and Diverse Equipment, Hoses*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Best Hose Routing Practices	<b>CR</b> <b>CZ</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>LI</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SL</b> <b>SP</b>	7580034_04 7580286_04 7560752_04 7192982_04 7192993_04 7580013_04 7192686_04 7560771_04 7192996_04 7192997_04 7580250_04 7580456_04 7580935_04 7192992_04	IN	(317102) or (317107)	<b>EN - 1078079_04 - Issued 09/13</b>
	Elastic Attachement Applications - Quick Reference -	<b>SP</b>	7119155B	IN	(317102) or (317107)	<b>EN - 1046122B - Issued 06/04</b>
	Electrical Cabinet for Label Adhesive System	<b>IT</b>	7560968_01	MA	(317102) or (317107)	<b>EN - 1124934_01 - Issued 03/16</b>
	Melter Flushing Kit - P/N 1072368 Melter Flushing Kit - P/N 1126060	<b>EN</b> <b>FR</b>	1054223A03 7119607_03	IN	(317102) or (317107)	<b>Issued 09/06</b> <b>Issued 07/17</b>
	Three-Way Dispensing Modules	<b>GE</b>	7119611B	IN	(317102) or (317107)	<b>EN - 321551B - Issued 11/02</b>
	Remote Metering Station	<b>IT</b>	7146833B03	MA	(317102) or (317107)	<b>EN - 1041397B03 - Issued 08/06</b>



B-4 - 2

## Nordson US Hot Melt Products (sorted by Model)

### *Other Melters and Diverse Equipment, Hoses*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Capacitive Level Sensor with Amplifier (User's Guide) (Title version_01: Stand-alone Level Sensor) (User's Guide)	FR GE IT SP	7560906_01 7560904_02 7560907_01 7560905_01	MA	(317102) or (317107)	EN - 1125417_02 - Issued 12/17
<b>AltaPUR</b>	AltaPUR Slug Melter	CH GE FR HU IT JA KO PO RU SP	7580627_01 7580612_01 7580630_01 7593120_01 7580613_01 7580628_01 7580632_01 7580631_01 7593329_01 7580629_01	MA	(317103) or (317106)	EN - 1126381_01 - Issued 03/18
<b>Blue Series</b>	Blue Series Hot Melt Hose with RediFlex II Hanger System	CZ DA DU FI FR GE HU IT JA KO PL PO RO RU SP SW	7580428_01 7580429_01 7580430_01 7580431_01 7580432_01 7580433_01 7580434_01 7580435_01 7580436_01 7580437_01 7580438_01 7580439_01 7580476_01 7580440_01 7580441_01 7580442_01	IN	(317102) or (317107)	EN - 1125981_01 - Issued 03/17

B-4 - 3

## Nordson US Hot Melt Products (sorted by Model)

### *Other Melters and Diverse Equipment, Hoses*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Bravura</b>	Bravura Adhesive Melters	<b>DA</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>EN/PL</b> <b>SP</b>	7135103D02* 7119435D02 7105580D02 7105598D02 7105585D02 7119074C** 7105592D02	MA	(317103) or (317106)	<b>EN - 1052743D03 - Issued 02/10</b> <b>* = Only section 2-5 !</b> <b>** = only section INS in Polish !</b>  <b>- OBSOLETE -</b>
<b>Bravura</b>	Bravura Adhesive Melters	<b>DA</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>SP</b>	7135104A 7119436A 7105559A 7105571A 7105535A 7119054A 7105566A	OP	(317102) or (317107)	<b>EN - 1053810A02 - Issued 08/04</b> <b>- OBSOLETE -</b>
<b>C9/ C15</b>	C9 and C15 Adhesive Melters	<b>DU</b> <b>FR</b> <b>GE</b> <b>PO</b> <b>SP</b>	7179527_02 7179525_02 7179526_02 7179529_02 7179528_02	MA	(317102) or (317107)	<b>EN - 1121010_02 - Issued 01/13</b>
<b>Classic Series</b>	Classic Series Melters	<b>FR</b> <b>SP</b>	7169314_02 7169319_02	MA	(317102) or (317107)	<b>EN - 1108226_02 - Issued 02/12</b>
<b>EZ</b>	EZ Adhesive Melters Models 20 and 45	<b>CH</b>	7560918_01	MA	(317102) or (317107)	<b>EN - 1125336_01 - Issued 08/16</b>

B-4 - 4

## Nordson US Hot Melt Products (sorted by Model)

### *Other Melters and Diverse Equipment, Hoses*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Freedom</b>	Freedom Hot Melt Adhesive System	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>PO</b> <b>SP</b> <b>SW</b>	7179694_02 7179648_02 7179995_02 7179649_02 7179994_02 7192323_02 7179670_02 7179654_02 7179668_02	MA	(317102) or (317107)	<b>EN - 1121631_02 - Issued 7/13</b> <b>OLD!</b>
<b>Freedom</b>	Freedom Hot Melt Adhesive System	<b>CZ</b>	7192494_02	MA	(317102) or (317107)	<b>EN - 1123087_02 - Issued 3/14</b> <b>OLD!</b>
<b>Freedom</b>	Freedom Hot Melt Adhesive System	-	-	MA	(317102) or (317107)	<b>EN - 1125366_01 - Issued 12/17</b> <b>NEW!</b>
<b>Freedom</b>	Freedom Hot Melt Adhesive System - Quick Reference -	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>KO</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7179809_01 7179931_01 7179550_01 7179864_01 7179547_01 7179501_01 7179903_01 7179553_01 7179532_01 7179861_01 7560119_01 7179830_01 7179575_01 7179828_01 7179549_01 7179608_01	IN	(317102) or (317107)	<b>EN - 1121655_02 - Issued 10/16</b>

B-4 - 5

## Nordson US Hot Melt Products (sorted by Model)

### *Other Melters and Diverse Equipment, Hoses*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Freedom</b>	Freedom Hot Melt Hose	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>KO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7179810_01 7179932_01 7179551_01 7179865_01 7179546_01 7179500_01 7179904_01 7179552_01 7179531_01 7179862_01 7179831_01 7179576_01 7179829_01 7179548_01 7179609_01	IN	(317102) or (317107)	<b>EN - 1121628_01 - Issued 02/13</b>
<b>Freedom</b>	Freedom Hot Melt Hose with RediFlex II Hanger System	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>KO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7560206_01 7560203_01 7560207_01 7560198_01 7560204_01 7560208_01 7560199_01 7560200_01 7560209_01 7560210_01 7560197_01 7560202_01 7560201_01 7560205_01 7560211_01	IN	(317102) or (317107)	<b>EN - 1124593_01 - Issued 06/15</b>

B-4 - 6

## Nordson US Hot Melt Products (sorted by Model)

### *Other Melters and Diverse Equipment, Hoses*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>GD-200</b>	GD-200S and GD-200F Sensors Customer Product Manual  ( Title version A: GD-200 Sensor )	<b>CH</b> <b>CZ</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>SP</b> <b>SW</b>	7135382_04 7192557_04 7135526_04 7135524_04 7135443_04 7135423_04 7135462_04 7156371_04 7135420_04 7135527_04 7135417_04	MA	(317102) or (317107)	<b>EN - 1074512_04 - Issued 07/14</b>
<b>GD-500</b>	Bead Detection System	<b>IT</b> <b>PL</b>	7156046A 7192155A	MA	(317102) or (317107)	<b>EN - 1085946A - Issued 04/08</b>
<b>GD-500</b>	Smart Sensor	<b>CH</b> <b>CZ</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>RU</b> <b>SP</b> <b>SW</b>	7156123A 7192558A 7156127A 7156137A 7156124A 7156111A 7156140A 7156130A 7580666A 7156139A 7156103A	MA	(317102) or (317107)	<b>EN - 1094263A - Issued 06/09</b>
<b>GP200</b>	GP200 Metering Station	<b>GE</b> <b>IT</b> <b>JA</b> <b>RU</b> <b>SP</b> <b>SW</b>	7146133A04 7135881_07 7169360_07 7146739A04 7135136A 7179508A06	MA	(317102) or (317107)	<b>EN - 1072082_07 - Issued 02/16</b>
<b>GP200</b>	GP200 Metering Station Equipment Part Number 1075167	<b>SP</b>	7135137A	MA	(317102) or (317107)	<b>EN - 1075820A - Issued 01/07</b>

B-4 - 7

## Nordson US Hot Melt Products (sorted by Model)

### *Other Melters and Diverse Equipment, Hoses*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>GP200</b>	GP200 Metering Station	<b>DU</b> <b>RU</b>	7156667A 7169136A	MA	(317102) or (317107)	<b>EN - 1083573A - Issued 03/08</b>
<b>HD-70</b>	Hot Melt Sensor	<b>GE</b>	7179353A	MA	(317102) or (317107)	<b>EN - 1091995A - Issued 10/08</b>
<b>HD-100</b>	Hot Melt Sensor	<b>CH</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>SP</b>	7192128_01 7192165_01 7192160_01 7192139_01 7192140_01 7192129_01 7192150_01	MA	(317102) or (317107)	<b>EN - 1122177_01 - Issued 08/13</b>
<b>LP90</b>	LP90 Fluid Application System	<b>CZ</b> <b>DU</b> <b>GE</b> <b>GR</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SK</b> <b>SP</b>	7192781B03 7192499_04 7179542_04 7580473_04 7105675_04 7192858B03 397405A 7560669_04 7105699_04 397420_04	MA	(317102) or (317107)	<b>EN - 1041182_04 - Issued 06/12</b>
<b>LP 100</b>	LP100 Fluid Application System	<b>FR</b> <b>GE</b> <b>IT</b>	464962B 458405B 458391B	MA	(317102) or (317107)	<b>EN - 1002288B - Issued 03/01</b>

B-4 - 8

## Nordson US Hot Melt Products (sorted by Model)

### *Other Melters and Diverse Equipment, Hoses*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>M2019</b>	M2019 Adhesive Melter (Nordson Corporation Users Only)	<b>CH</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PO</b> <b>SP</b>	7593294_01 7593295_01 7593297_01 7593296_01 7593299_01 7593301_01 7593300_01 7593298_01	MA	(317102) or (317107)	<b>EN - 1127667_01 - Issued 04/19</b>
<b>M2019</b>	M2019 Hot Melt Adhesive Melter -Installation Guide-	<b>CH</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PO</b> <b>SP</b>	7593302_01 7593303_01 7593305_01 7593304_01 7593307_01 7593309_01 7593308_01 7593306_01	OP	(317102) or (317107)	<b>EN - 1127705_01 - Issued 04/19</b>
<b>M2019</b>	M2019 Hot Melt Adhesive Melter -Quick Reference Guide-	<b>CH</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PO</b> <b>SP</b>	7593310_01 7593311_01 7593313_01 7593312_01 7593315_01 7593317_01 7593316_01 7593314_01	OP	(317102) or (317107)	<b>EN - 1127706_01 - Issued 04/19</b>
<b>Mesa</b>	Mesa Adhesive Melters Model M4, M6, M9, and M14	<b>CZ</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>RU</b> <b>SP</b>	7169300A03 7192369_04 7156188_04 7156166_04 7156146_04 7156156_04 7156556_04 7156158_04 7156141_04	MA	(317102) or (317107)	<b>EN - 1089887_05 - Issued 10/15</b>

B-4 - 9

## Nordson US Hot Melt Products (sorted by Model)

### *Other Melters and Diverse Equipment, Hoses*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Mesa	FulFill Retrofit for Mesa Melters	FR GE IT SP	7169200A 7169219A 7169213A 7169217A	MA	(317102) or (317107)	<b>EN - 1103525A - Issued 01/13</b> <b>Issue date of translations 09/10</b> <b>OLD!</b> <b>- &gt; Replaced by P/N 1121938_01</b>
Mesa	FulFill Retrofit for Mesa Melters	FR GE IT SP	7179745_01 7179746_01 7179747_01 7179748_01	MA	(317102) or (317107)	<b>EN - 1121938_02 - Issued 05/13</b> <b>Obsolete!</b>
Mesa	Mesa Adhesive Melters - User' s Guide	EN/CH/ DA/FI/ FR/GE/ IT/JA/ NO/SP/ SW	1096980A	OP	(317102) or (317107)	<b>Issued 06/09</b>
Mesa	Mesa Adhesive Melters - User' s Guide	EN/DU	7192313_01	OP	(317102) or (317107)	<b>Issued 01/14</b>
MiniPUR	MiniPUR Adhesive Melter	FR	7179658A03	MA	(317102) or (317107)	<b>EN - 1093491A03 - Issued 01/13</b>
MiniPUR Plus	MiniPUR Plus Adhesive Melter	CZ FR GE HU JA NO SP SW	7560723_02 7192214_02 7192176_02 7580247_02 7192211_02 7192162_02 7192172_02 7192215_02	MA	(317102) or (317107)	<b>EN - 1122803_02 - Issued 06/14</b>
PM-150/250	PM-150/250 Premelter Manual	DU FR GE IT	413071A 413060A 413059A 413061A	MA	(317102) or (317107)	<b>EN - 321224A (EDB 41-710)</b>



B-4 - 10

## Nordson US Hot Melt Products (sorted by Model)

### *Other Melters and Diverse Equipment, Hoses*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Pro-Meter</b>	Pro-Meter VDK Dispensing System	<b>DA GE IT JA SP</b>	7119346C 397893C 7105096C 7119302C* 7119630C	MA	(317102) or (317107)	<b>EN - 321208C - Issued 3/05 OLD!</b>  * = available at Nordson K.K
<b>Pro-Meter</b>	Pro-Meter VDK Dispensing System	<b>IT JA PL</b>	7560679_07 7169753_07* 7192994_07	MA	(317102) or (317107)	<b>EN - 10692041_07 - Issued 01/12 * = available at Nordson K.K OLD!</b>
<b>Pro-Meter</b>	Pro-Meter VDK Dispensing System	<b>CZ JA</b>	7560836_01 7580591_01*	MA	(317102) or (317107)	<b>EN - 1123462_02 - Issued 07/18 * = available at Nordson K.K NEW!</b>
<b>PS40</b>	PS40 Power Supply	<b>DU GE GR HU PL</b>	7179193 <b>B02</b> 213009 <b>B02</b> 7119834B 7156462 <b>B02</b> 7169216 <b>B02</b>	IN	(317102) or (317107)	<b>EN - 1011339_04 - Issued 08/11 Obsolete!</b>

B-4 - 11

## Nordson US Hot Melt Products (sorted by Model)

### *Other Melters and Diverse Equipment, Hoses*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
RTD	RTD-Style Hot Melt Hose	<b>BU</b> <b>CH</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>ES</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SK</b> <b>SP</b> <b>SW</b>	7135437E 7169269E 7105115E 447643E 284190E 7146247E 458480E 284191E 284192E 7146218E 284193E 447631E 7105754E 403296E 7192771E 7135330E 7156926E 284194E 284195E	MA	(317102) or (317107)	<b>EN - 108232E - Issued 01/00</b>

B-4 - 12

## Nordson US Hot Melt Products (sorted by Model)

### *Other Melters and Diverse Equipment, Hoses*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
RTD	RTD-Style Hot Melt Hoses User' s Guide	BU CH CR CZ DU FR GE HU IT JA LI PL PO RO RU SK SL SP	7580229_01 7580230_01 7580231_01 7580232_01 7580233_01 7580234_01 7580235_01 7580236_01 7580237_01 7580238_01 7580239_01 7580240_01 7580241_01 7580242_01 7580243_01 7580244_01 7580934_01 7580245_01	IN	(317102) or (317107)	EN - 1125982_01 - Issued 03/17
RTD	RTD-Style Hot Melt FoamMix Hoses for Bulk Melter Systems	CH FR GE IT	7179630_01 7560231_01 7560032_01 7560507_01	OP	(317102) or (317107)	EN - 1121861_01 - Issued 06/13
RTD	RTD-Style e. dot Hot Melt Hoses	GE PL SW	7560808B03 7560298B03 7179032B03	IN	(317102) or (317107)	EN - 1032556B03 - Issued 11/07
RTD	RTD Style High Temperature Hot Melt Hoses	GE IT	7146506B03 7192685B04	IN	(317102) or (317107)	EN - 1044182B04 - Issued 10/08
Select Series	Select Series Advanced Technology RTD Style Hoses	GE IT	213478D 213445D	OP	(317102) or (317107)	EN - 321197F04 - Issued 07/09

B-4 - 13

## Nordson US Hot Melt Products (sorted by Model)

### *Other Melters and Diverse Equipment, Hoses*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>TruFlow</b>	TruFlow Meter	<b>CZ DU GE IT PL SK</b>	7560890_03 7593342_03 7580156_03 7560006_03 7560538_03 7560875_03	IN	(317102) or (317107)	<b>EN - 1121840_03 - Issued 07/14</b>
<b>VL200</b>	VL200 Melter	<b>IT</b>	7105607B	MA	(317103) or (317106)	<b>EN - 779639C - Issued 08/05 Obsolete!</b>
<b>VL300</b>	VL300 Melters	<b>GE IT</b>	213123B 213050B	MA	(317103) or (317106)	<b>EN - 1004923D - Issued 10/02 Obsolete!</b>
<b>VL300</b>	VL300 Melters	<b>FR GE</b>	397368C 213080A	OP	(317103) or (317106)	<b>EN - 1004924C - Issued 01/02 Obsolete!</b>
<b>VL400</b>	VL400 Melters	<b>GE IT</b>	7105530A 7105503A	MA	(317103) or (317106)	<b>EN - 1052643B - Issued 08/05 Obsolete!</b>

B-5 - 1

## Nordson US Hot Melt Products (sorted by Model)

### *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Accubar</b>	Accubar Bar Code Verifier	<b>FR</b> <b>IT</b> <b>PL</b>	7119993D02 7119631D 7119154D	MA	(317102) or (317107)	<b>EN - 321356D02 - Issued 02/10</b>
<b>Braille</b>	Braille Pattern Controller	<b>EN</b> <b>IT</b>	7135662A 7135781A	MA	(317102) or (317107)	<b>Application Development Word .doc</b>
<b>Concert</b>	Concert Series Basic Standalone Temperature Controller	<b>FR</b> <b>GE</b> <b>IT</b>	7192853_01 7192883_01 7560048_01	MA	(317102) or (317107)	<b>EN - 1123727_01 - Issued 06/14</b>
<b>Concert</b>	Concert Series Basic Standalone Temperature Controller with Flow Monitor and Control	<b>CZ</b> <b>PL</b> <b>SK</b>	7580068_01 7580075_01 7580069_01	MA	(317102) or (317107)	<b>EN - 1121717_01 - Issued 06/14</b>
<b>Concert</b>	Concert Series Expanded Standalone Temperature Controller	<b>PO</b>	7560394_01	MA	(317102) or (317107)	<b>EN - 1123728_01 - Issued 09/14</b>
<b>Concert</b>	Concert Series Expanded Standalone Temperature Controller with Flow Monitor and Control	<b>CZ</b> <b>PL</b> <b>SK</b>	7580070_01 7580076_01 7580071_01	MA	(317102) or (317107)	<b>EN - 11263730_01 - Issued 09/14</b>
<b>Concert</b>	Concert Series Standalone Temperature Controller - User's Guide -	<b>IT</b>	7560049_01	OP	(317102) or (317107)	<b>EN - 1122802_01 - Issued 06/14</b>
<b>EcoBead</b>	EcoBead Inline Pattern Generator	<b>CH</b> <b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>SP</b>	7179204_01 7179314_01 7179205_01 7179206_01 7179207_01 7179208_01 7560170_01 7179209_01	MA	(317102) or (317107)	<b>EN - 1120911_01 - Issued 09/12</b>

B-5 - 2

## Nordson US Hot Melt Products (sorted by Model)

### *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>EcoBead</b>	EcoBead II Inline Pattern Generator	CH FR GE IT JA SP	7580579_02 7580580_02 7580581_02 7580582_02 7580583_02 7580584_02	MA	(317102) or (317107)	<b>EN - 1124128_02 - Issued 03/18</b>
<b>EcoBead Inspect</b>	Ecobead Inspect	DU FR GE IT PO SP	7593369_01 7593370_01 7593371_01 7593372_01 7593373_01 7593374_01	MA	(317102) or (317107)	<b>EN - 1127083_01 - Issued 05/19</b>
<b>EPC-15</b>	Eclipse Series EPC-15 Pattern Control	DU FI FR GE IT JA PL SP SW	464999A 213249A 447759D02 447760D02 464990D02 447781A* 7119513D 464726D02 213115A	MA	(317103) or (317106)	<b>EN - 321352D02 - Issued 02/10</b> <b>Product Obsolescence October 31, 2014, replaced by Spectra 30 Controller</b>  <b>* available at Nordson K.K</b>
<b>EPC-15</b>	Eclipse Series EPC-15 User's Guide	DA HU JA RU SL	213117C 7146262A** 464873A* 7156923C 7146407C	OP	(317102) or (317107)	<b>EN - 321287C</b> <b>Product Obsolescence October 31, 2014, replaced by Spectra 30 Controller</b>  <b>* available at Nordson K.K</b> <b>** = Abridged edition, document and translation is NOT issued by TDLL !</b>

B-5 - 3

## Nordson US Hot Melt Products (sorted by Model)

### Auxiliary Systems

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>EPC-30</b>	Eclipse Series EPC-30 Pattern Control	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7119051C* 412851B 412985B 412852B 412853B 412680D 412842B 412850B 458274B 458424B 7179129D 412718B 412719C	MA	(317103) or (317106)	<b>EN - 237514D - Issued 02/10</b> <b>Product Obsolescence January 31, 2016, replaced by Spectra 30 Controller</b>  <b>* = Abridged edition, document and translation is NOT issued by TDLL !</b>
<b>EPC-30</b>	Series EPC-30 Current-to-Pressure (I/P) Transducer	<b>GE</b>	213026A	IN	(317102) or (317107)	<b>EN - 331276B02 - Issued 08/10</b> <b>Product Obsolescence January 31, 2016, replaced by Spectra 30 Controller</b>
<b>EPC-30</b>	Eclipse Series EPC-30 User's Guide	<b>FR</b> <b>GE</b> <b>GR</b> <b>HU</b> <b>PL</b> <b>RU</b> <b>SK</b>	447709A 447703A 7119833C 7146265C02 7169183C02 213201A 7119229A	OP	(317102) or (317107)	<b>EN - 331180C02 - Issued 2007</b> <b>Product Obsolescence January 31, 2016, replaced by Spectra 30 Controller</b>
<b>FillEasy II</b>	FillEasy II Adhesive Feed System	<b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PO</b> <b>SP</b> <b>SW</b>	7119961A 7146580A 7135604A 7146260A 7119974A 7119996A 7119992A	MA	(317102) or (317107)	<b>EN - 1073536A - Issued 10/06</b> <b>OBSOLETE!</b>
<b>FillEasy II</b>	FillEasy II Cone and Level Sensor Assembly Installation - P/N 1071613	<b>FR</b>	7135149A	IN	(317102) or (317107)	<b>EN - 1071702A - Issued 1006</b> <b>OBSOLETE!</b>

B-5 - 4

## Nordson US Hot Melt Products (sorted by Model)

### *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Fillmaster</b>	Fillmaster Adhesive Feed System	<b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	213650B 397002B 213677B 213663B 213648B 397047B 213645B 213673B 213719B	MA	(317102) or (317107)	<b>EN - 1030629C - Issued 07/04</b> <b>OBSOLETE!</b>
<b>Fillmaster</b>	Level Sensor	<b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	213651A 397003A 213679A 213664A 213649A 397048A 213646A 213676A 213720A	IN	(317102) or (317107)	<b>EN - 1029200A - Issued 07/02</b> <b>OBSOLETE!</b>
<b>LogiCOMM</b>	LogiCOMM Control System Control Module Manual	<b>CH</b> <b>CZ</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SK</b> <b>SP</b> <b>SW</b>	7135046A** 7146512A 7105862A 7135071B 7105822A 7105812A 7135654A 7105794A 7135341A* 7119148B 7146465A 7146502A 7156930A 7105808A 7105791A	MA	(317102) or (317107)	<b>EN - 1049054A02 - Issued 2010</b> <b>** = Document and translation is</b> <b>NOT issued by TDLL!*</b>  <b>available at Nordson K.K</b>



B-5 - 5

## Nordson US Hot Melt Products (sorted by Model)

### *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>LogiComm</b>	LogiComm Control System with Combination Configuration	<b>CH</b> <b>CZ</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>SP</b> <b>SW</b>	7169758_01 7169152_01 7169723_01 7169693_01 7169682_01 7169701_01 7169816_01 7169707_01 7169679_01 7169698_01	MA	(317102) or (317107)	<b>EN - 1105135_01 - Issued 11/11</b>
<b>LogiComm</b>	LogiComm Control System for Pattern Generation	<b>CH</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>SP</b> <b>SW</b>	7169756_01 7169721_01 7169691_01 7169680_01 7169699_01 7169814_01 7169705_01 7169677_01 7169696_01	MA	(317102) or (317107)	<b>EN - 1120173_01 - Issued 12/11</b> <b>Issue date of translations 11/11</b>
<b>LogiComm</b>	LogiComm Control System for Product Verification	<b>CH</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>SP</b> <b>SW</b>	7169757_01 7169722_01 7169692_01 7169681_01 7169700_01 7169815_01 7169706_01 7169678_01 7169697_01	MA	(317102) or (317107)	<b>EN - 1120174_01 - Issued 12/11</b> <b>Issue date of translations 11/11</b>

B-5 - 6

## Nordson US Hot Melt Products (sorted by Model)

### *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>LogiComm</b>	LogiComm Control System User's Guide	<b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7169470 7169471 7169472 7169473 7169474 7169475 7169476 7169477 7169478 7169479 7169480 7169481 7169482	OP	(317102) or (317107)	<b>EN - 1105134 - Issued 04/11</b>
<b>LogiComm</b>	LogiComm Gun Driver	<b>CZ</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>RU</b> <b>SP</b> <b>SW</b>	7156951 <b>A02</b> 7146391A 7146369A 7146340A 7146360 <b>A02</b> 7146375A 7146396 <b>A02</b> 7146355A 7146605 <b>A02</b> 7560672 <b>A02</b> 7146368 <b>A02</b> 7146577A	MA	(317102) or (317107)	<b>EN - 1087837A02 - Issued 03/10</b>

B-5 - 7

## Nordson US Hot Melt Products (sorted by Model)

### *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>LogiComm</b>	LogiComm Gun Driver User's Guide	<b>CZ DA DU FR GE HU IT NO PL PO RU SK SP SW</b>	7192775A 7146316A 7146317A 7146318A 7146319A 7146320A 7146321A 7146322A 7146323A 7146324A 7560673A 7580000A 7146325A 7146326A	OP	(317102) or (317107)	<b>EN - 1087838A - Issued 05/08</b>
<b>LogiComm</b>	LogiComm OEM Applicator Driver Board	<b>CH DU FR GE IT SP SW</b>	7156173A02 7156189A02 7156195A02 7156206A02 7156182A02 7156222A02 7179030A02	MA	(317102) or (317107)	<b>EN - 1097242A02 - Issued 04/10</b>
<b>LogiComm</b>	LogiComm OEM Applicator Driver Board Wiring Diagram	<b>CH DU FR GE IT SP</b>	7156664A02 7156683A02 7156684A02 7156678A02 7156677A02 7156679A02	IN	(317102) or (317107)	<b>EN - 1098142A02 - Issued 04/10</b>

B-5 - 8

## Nordson US Hot Melt Products (sorted by Model)

### Auxiliary Systems

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>LogiComm</b>	Trigger I/O Board for the LogiComm Gun Driver	<b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>SP</b> <b>SW</b>	7146409A 7146539A 7146411A 7146412A 7146419A 7146464A 7146424A 7146606A 7146413A 7146578A	IN	(317102) or (317107)	<b>EN - 1084488A - Issued 02/06</b>
<b>LogiComm</b>	LogiComm Touch-screen Panel Installation for Basic and Expanded Systems	<b>DA</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>SP</b> <b>SW</b>	7105924A 7105953A 7105916A 7105985A 7135879B 7105921A 7135375A 7105947A 7119150A 7105938A 7105934A 7105918A	IN	(317102) or (317107)	<b>EN - 1060849B - Issued 03/06</b>
<b>LogiComm</b>	LogiComm: Change Encoder from Quadrature to Single Phase	<b>EN/ GE</b>	7169790_01	IN	(317102) or (317107)	<b>Bilingual document, therefore one P/N only</b> <b>Created by Nordson Engineering GmbH</b>
<b>Nitrogen</b>	Generation System	<b>FR</b> <b>PL</b>	7179660_02 7179423A	MA	(317102) or (317107)	<b>EN - 1107704_02 - Issued 06/13</b>
<b>PACK</b>	Pattern Air Control Kit (PACK)	<b>DU</b> <b>FR</b> <b>PL</b> <b>RU</b>	7156669B02 7593216B02 7156358B02 7169143B02	IN	(317102) or (317107)	<b>EN - 1044445B02 - Issued 01/08</b> <b>Obsolete!</b>

B-5 - 9

## Nordson US Hot Melt Products (sorted by Model)

### *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Seal Sentry	Seal Sentry Series 10 Bead Detection System	FR GE NO SP SW	464910A 213015A 213418B 7119137C02 213412B	MA	(317103) or (317106)	EN - 321289D02 - Issued 02/10 <b>Obsolete!</b>
Spectra 30	Pattern Controller <b>-OLD!-</b>	CH CZ DU FR GE IT JA PL PO RU SP	7192744_01 7560062_01 7192788_01 7192786_01 7192782_01 7192779_01 7192745_01 7560146_01 7192774_01 7560339_01 7192800_01	MA	(317103) or (317106)	EN - 1123406_01 - Issued 8/14
Spectra 30	Pattern Controller <b>-NEW!-</b>	CH DU FR GE IT JA PL PO SP	7560423_01 7560421_01 7560418_01 7560417_01 7560419_01 7560424_01 7560425_01 7560422_01 7560420_01	MA	(317103) or (317106)	EN - 1124631_01 - Issued 10/15
Spectra 30	Pattern Controller -Installation Guide- <b>-OLD!-</b>	CH DU FR GE IT JA PL PO SP	7192703_01 7192704_01 7192705_01 7192706_01 7192707_01 7192708_01 7560256_01 7192709_01 7192710_01	OP	(317102) or (317107)	EN - 1123405_01 - Issued 07/14

B-5 - 10

## Nordson US Hot Melt Products (sorted by Model)

### *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Spectra 30</b>	Control System -Installation Guide- <b>-NEW!-</b>	<b>CH</b> <b>CR</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>PO</b> <b>RO</b> <b>SE</b> <b>SL</b> <b>SP</b>	1124780_01 7560973_01 1124781_01 1124782_01 1124783_01 7560974_01 1124784_01 1124785_01 1124786_01 7560745_01 7560975_01 7560976_01 1124787_01	OP	(317102) or (317107)	<b>EN - 1124634_01 - Issued 09/15</b>
<b>Spectra 30</b>	Pattern Controller -Quick Reference Guide- <b>-OLD!-</b>	<b>CH</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>PO</b> <b>SP</b>	7192699_01 7192700_01 7192562_01 7192563_01 7192564_01 7192701_01 7560257_01 7192702_01 7192565_01	OP	(317102) or (317107)	<b>EN - 1122901_01 - Issued 2014</b>

B-5 - 11

## Nordson US Hot Melt Products (sorted by Model)

### Auxiliary Systems

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Spectra 30</b>	Control System -Quick Reference Guide- <b>-NEW!-</b>	<b>CH</b> <b>CR</b> <b>CZ</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>PO</b> <b>RO</b> <b>SE</b> <b>SL</b> <b>SP</b>	1124727_01 7560969_01 7560781_01 1124728_01 1124729_01 1124730_01 7560970_01 1124731_01 1124732_01 1124733_01 7560746_01 7560971_01 7560972_01 1124734_01	OP	(317102) or (317107)	<b>EN - 1124633_01 - Issued 2015</b>
<b>Spectra 30</b>	Control System -Safety Instructions-	<b>CH</b> <b>CR</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>PL</b>  <b>PO</b> <b>RO</b> <b>SE</b> <b>SL</b> <b>SP</b>	7192711_01 7560981_01 7192712_01 7192713_01 7192714_01 7560982_01 7192715_01 7192716_01 1124796_01* <del>7560143_01</del> 7192717_01 7560764_01 7560983_01 7560984_01 7192718_01	IN	(317102) or (317107)	<b>EN - 1123841_01 - Issued 08/14</b>  <b>* PL = US P/N !</b>
<b>Unity</b>	Unity IC30/ IC300 Dispensing System	<b>JA</b>	7156685A*	MA	(317102) or (317107)	<b>EN - 1092353_05 - Issued 06/16</b> <b>* available at Nordson K.K</b>
<b>Unity</b>	Unity IC30/ IC300 PLUS Dispensing System	<b>CH</b>	7580118_01	MA	(317102) or (317107)	<b>EN - 1126102_01 - Issued 06/17</b>

B-5 - 12

## Nordson US Hot Melt Products (sorted by Model)

### *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
Unity	Unity IC30-2HC/ IC300 PLUS Dispensing System	CH	7593244_01	MA	(317102) or (317107)	EN - 1127443_01 - Issued 12/18
Unity	Unity PURJet 30 Dispensing System	HU	7169794A	MA	(317102) or (317107)	EN - 1104545_06 - Issued 12/13
Unity	Unity PURJet 300 Dispensing System	GE	7580897_01	MA	(317102) or (317107)	EN - 1124248_01 - Issued 07/16
Unity	Unity PURJet 30XT/ 300XT Dispensing System	CH JA KO	7593487_01 7593488_01 7593489_01	MA	(317102) or (317107)	EN - 1128349_01 . Issued 08/19
Unity	Unity-C Controller	CH JA	7580059_01 7580592_01*	MA	(317102) or (317107)	EN - 1125640_01 - Issued 06/17 * = available at Nordson K.K
Unity	Unity Series Automated Dispensing Systems	GE JA	7580898_01 7580598_01*	MA	(317102) or (317107)	EN - 1124479_01 - Issued 05/15 * = available at Nordson K.K
Unity	Unity Touch Controller	CH GE JA	7580060_01 7580899_02 7580593_01*	MA	(317102) or (317107)	EN - 1125641_02 - Issued 02/18 * = available at Nordson K.K
Unity	Unity Touch S Controller	CH	7593245_01	MA	(317102) or (317107)	EN - 1127417_01 - Issued 03/19 (Chinese translation issued 12/18)
Vulcan Jet	Vulcan Jet Dispensing Controller	CH FR GE IT JA KO PO SP	7580343_02 7580349_02 7580346_02 7580350_02 7580345_02 7580344_02 7580348_02 7580347_02	MA	(317102) or (317107)	EN - 1126187_02 - Issued 01/19



B-5 - 13

## Nordson US Hot Melt Products (sorted by Model)

### *Auxiliary Systems*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Vulcan Jet</b>	Vulcan Jet Quick Reference Card	<b>CH</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>KO</b> <b>PO</b> <b>SP</b>	7580351_01 7580357_01 7580354_01 7580358_01 7580353_01 7580352_01 7580356_01 7580355_01	IN	(317102) or (317107)	<b>EN - 1126188_01 - Issued 09/17</b>
<b>Vulcan Jet</b>	Vulcan Jet Replacement Kits P/N 1126063, 1126064, 1126065, 1126066, 1126067, 1126068, 1126069, 1126070, 1126071, 1126072, 1126073	<b>CH</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>KO</b> <b>PO</b> <b>SP</b>	7580359_01 7580365_01 7580362_01 7580366_01 7580361_01 7580360_01 7580364_01 7580363_01	IN	(317102) or (317107)	<b>EN - 1126189_01 - Issued 11/17</b>

B-6 - 1

## Nordson US Hot Melt Products (sorted by Model)

### Applicators (Guns)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Cleaning Nozzles	JA	7156562B*	IN	(317102) or (317107)	EN - 1053027 - Issued 2004 * available at Nordson K.K
AD 31	Series AD-31 Swirl and Wide-Pattern Swirl Hand-held Applicators	GE PL RO SK	7580668_03 7580491_03 7560814_03 7580669_03	MA	(317102) or (317107)	EN - 107111_03 - Issued 10/15
AD 31	Series AD-31 and Series L4 Extrusion Hand-held Applicators ( Title version B: Series AD-31 Extrusion Handgun ) ( Title version C: Series AD-31 and Series L4 Extrusion Handguns )	FR GE SK	409229B 397245_05 7580671_05	MA	(317102) or (317107)	EN - 107105_05 - Issued 08/15
AD 41	Series AD-41, L5, and L7 Extrusion Handguns ( Title version B: AD-41 Handgun )	CZ FI FR GE IT JA PL RO	7105254B 7135231G 7135474G 412629G02 7135472G 464852B* 7560455G02 7560785G02	MA	(317102) or (317107)	EN - 237567G02 - Issued 06/10  * available at Nordson K.K
AltaSpray	AltaSpray Applicators	FR GE IT JA SP	7135777A04 7135769A04 7135836A04 7169646A05* 7135778A02	MA	(317102) or (317107)	EN - 1081984A05 - Issued 11/10  * available at Nordson K.K
AltaSpray	AltaSpray Applicator Insulating Jacket Installation	JA	7169645A*	IN	(317102) or (317107)	EN/CH - 1097095A - Issued 09/09 * available at Nordson K.K
AltaSpray Intermittent	AltaSpray Intermittent Applicators	CH GE IT JA	7593503_01 7593505_01 7593506_01 7593504_01	MA	(317102) or (317107)	EN - 1128081_01 - Issued 09/19

B-6 - 2

## Nordson US Hot Melt Products (sorted by Model)

### *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>AltaSpray Plus</b>	AltaSpray Plus Applicators	<b>CH FR GE IT JA PO SP</b>	7593502_01 7192161_01 7192164_01 7192171_01 7192210_01 7192170_01 7192163_01	MA	(317102) or (317107)	<b>EN - 1121844_01 - Issued 05/13</b>
<b>Blue Series</b>	Blue Series Pneumatic Applicators	<b>CZ DA DU FI FR GE IT JA NO PL PO RU SK SP SW</b>	7105736_08 7105733A 7105729A 7105732A 7105831_08 7105735_09 7105829_08 7105793A 7105734A 7105897_09 7105809A 7146767A04 7156927A04 7105851_09 7105727A	MA	(317102) or (317107)	<b>EN - 1054960_09 - Issued 01/19</b>
<b>Blue Series</b>	Blue Series Low Profile Pneumatic Guns	<b>RU</b>	7146768A03	MA	(317102) or (317107)	<b>EN - 1074086A03 - Issued 09/08</b>
<b>CC 200</b>	Control Coat (CC200) Applicators	<b>CZ DA DU FR GE IT PL SP SW</b>	213853B 213932B 213905B 213940B 213892B 213914B 213996B 213965B 213885B	OP	(317102) or (317107)	<b>EN - 237562C - Issued 12/04</b>

B-6 - 3

## Nordson US Hot Melt Products (sorted by Model)

### *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>CF 200</b>	HMS Applicators (CF200) (Title version A: Controlled Fiberization (CF200) Applicators)	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FR</b> <b>HU</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>SK</b> <b>SP</b> <b>SW</b>	213848A 213927A 213900A 213935A 7105617A 213887A 213909A 213991A 7105676A 213960A 213880A	OP	(317102) or (317107)	<b>EN - 1029961C02 - Issued 01/07</b>
<b>CF 200</b>	Universal Applicators (CF200)	<b>IT</b> <b>JA</b>	7135835_04 7119451A*	OP	(317102) or (317107)	<b>EN - 1063322_04 - Issued 08/11</b> <b>*available at Nordson K.K</b>
<b>CF 400</b>	Controlled Fiberization (CF400) Applicators	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>SP</b> <b>SW</b>	213852A 213931A 213904A 213939A 213891A 213913A 213995A 213964A 213884A	OP	(317102) or (317107)	<b>EN - 1029965B - Issued 12/04</b>
<b>Control Coat</b>	Control Coat Applicators Base applicator parts 1066085 and 1065853, grade plate 1065814, and return plate 753367	<b>SP</b>	7119579A	MAN	(317102) or (317107)	<b>EN - 1066099A - Issued 02/06</b>

B-6 - 4

## Nordson US Hot Melt Products (sorted by Model)

### *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>CW 200</b>	Control Weave (CW200) Applicators	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>SP</b> <b>SW</b>	213854B 213933B 213906B 213941B 213893B 213915B 213997B 213966B 213886B	OP	(317102) or (317107)	<b>EN - 303861C - Issued 12/04</b>
<b>e24</b>	e24 Electric Applicator	<b>CH</b> <b>GE</b>	7593470_01 7593471_01	MA	(317102) or (317107)	<b>EN - 1128082_01 - Issued 08/19</b>
<b>e.dot</b>	e.dot Gun	<b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b>	7119109D 7105139B 7119697D 7105119B*	MA	(317102) or (317107)	<b>EN - 1041250E02 - Issued 09/06</b>  * available at Nordson K.K
<b>e.dot+</b>	e.dot+ Electric Applicator (Title A02: e.dot+ Electric Gun)	<b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>SK</b> <b>SW</b>	7156952A02 7169434A02 7156425_03 7156520A02 7156451A02 7560299_03 7580147_03 7179031A02	MA	(317102) or (317107)	<b>EN - 1079033_03 - Issued 11/16</b>  <b>PL translation issued 09/12</b>
<b>e.dot+</b>	e.dot+ Module Replacement Kit - P/N 7301602, 7301603, and 7301604	<b>GE</b>	7156427A	IN	(317102) or (317107)	<b>EN - 1082903A - Issued 0607</b>
<b>e.dot+</b>	e.dot+ Module Seal Service Kit - P/N 7302201	<b>GE</b>	7156426_01	IN	(317102) or (317107)	<b>EN - 1079052_01 - Issued 07/17</b>
<b>e.dot+</b>	e.dot+ Armature-Spring-Nozzle Replacement Kit - P/N 7302202 (.25 mm), 7302203 (.3 mm), and 7302204 (.35 mm)	<b>GE</b>	7156428A	IN	(317102) or (317107)	<b>EN - 1079051A - issued 06/07</b>

B-6 - 5

## Nordson US Hot Melt Products (sorted by Model)

### *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
e driver	e driver	FR GE IT JA SK	7119119B 7105140A 7146341B 7105121A* 7146723B	MA	(317102) or (317107)	EN - 1044198B - Issued 05/05  * available at Nordson K.K
e driver 2, 3, 4	e driver2, e driver3, e driver4	FR JA	7119120C 7105120A*	MA	(317102) or (317107)	EN - 1032560C - Issued 05/05 * available at Nordson K.K
E400	E400 Driver	GE IT PL	7105712B 7119990B 7105296B	MA	(317102) or (317107)	EN - 1037528B02 - Issued 02/10
E400	E400 Hot Melt Electric Gun	GE IT SP	7105764A 7119991B 7105672A	MA	(317102) or (317107)	EN - 1048256B - Issued 12/05
E400B	E400B Rebuildable Hot Melt Electric Applicator	DU	7560271A02	MA	(317102) or (317107)	EN - 1085353A02 - Issued 05/15
E400NP	E400NP Driver	DU GE IT PL SK	7192497C 7146748C 7146351C 7560084C 7146734C	MA	317102) or (317107))	EN - 1038035C02 - Issued 02/10
E401	E401 Electric Applicator	GE SK	7105711C 7146735C	MA	(317102) or (317107)	EN - 1045491C - Issued 07/05
ES400	ES400 Driver	GE SP	397054B 7105832B	MA	(317102) or (317107)	EN - 1015800B - Issued 06/02
ES400	ES400 Electric Applicator	IT PL SK	7146342B 7105297B 7146722B	MA	(317102) or (317107))	EN - 1007312B - issued 06/02

B-6 - 6

## Nordson US Hot Melt Products (sorted by Model)

### *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
FP-200	FP-200 Multi-Swirl Hand-Held Applicator (Title version C: FP-200 Gun System)	IT	413042C	MA	(317102) or (317107)	EN - 108391_04 - Issued 02/16
FP-200	FP-200 Guns	JA PL	464876C* 7179577_03	MA	(317102) or (317107)	EN - 237478_03 - Issued 10/12 * available at Nordson K.K
H-20	Series H-20 Automatic Applicators	CZ FR GE IT PL RO RU	7105866G02 7560042G02 213575G02 7580198G02 7156917G02 7192770G02 7146208G02	MA	(317102) or (317107)	EN - 104449G02 - Issued 04/15 Issue date of translation FR: 01/15 Issue date of translations CZ, PL, RO, RU: 07/04
H-200	Series H-200 Guns	CZ DA DU FI FR GE IT NO PL SP SW	7135297D* 412828G 284196K 412670G 284197G 284198J 284199G 409302G 458144G 284200G 290700G	MA	(317102) or (317107)	EN - 104457K - Issued 08/05 <b>OBSOLETE!</b> * = Document and translation is NOT issued by TDLL !
H-200	Series H-200 Mini-Bead Guns	JA RU	7119718B 7146979B	MA	(317102) or (317107)	EN - 107075B - Issued 09/15 Issue date of translations 04/04 <b>OBSOLETE!!</b>

B-6 - 7

## Nordson US Hot Melt Products (sorted by Model)

### *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>H-400</b>	Series H-400 Guns	<b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>SP</b> <b>SW</b>	213013C 213394C 458060C 412635C 458074C 213264C* 458279C 458239C 213116C	MA	(317102) or (317107)	<b>EN - 331170D - Issued 08/05 OBSOLETE!</b>  * available at Nordson K.K
<b>H-440</b>	Series H-440 Guns	<b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>SP</b> <b>SW</b>	213016C 213404C 458061C 412993C 458029C 213460C* 213323C 458240C 458217C	MA	(317102) or (317107)	<b>EN - 237564C02 - Issued 03/02 OBSOLETE!</b>  * available at Nordson K.K
<b>HMS</b>	HMS Series Applicators (Titel version C: Spray Applicators)	<b>DU</b> <b>SP</b>	7156688F 213501C	MA	(317103) or (317106)	<b>EN -106926F - Issued 09/05 OBSOLETE!</b>
<b>HMS</b>	Section 10 Filter	<b>DU</b>	7156696E02	MA	(317102) or (317107)	<b>EN - 106935E02 - Issued 01/07 Section applies to applicators with an in-out filter OBSOLETE!</b>
<b>HMS</b>	Section 11 Electrical System	<b>DU</b>	7156697D	MA	(317102) or (317107)	<b>EN - 106938D - Issued 12/04 Section applies to applicators with M-style cordsets OBSOLETE!</b>



B-6 - 8

## Nordson US Hot Melt Products (sorted by Model)

### *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>MB 200</b>	Meltblown (MB200) Applicators	<b>CZ DA DU FR GE IT PL SP SW</b>	213849A 213928A 213901A 213936A 213888A 213910A 213992A 213961A 213881A	OP	(317102) or (317107)	<b>EN - 1029962B - Issued 12/04 OBSOLETE!</b>
<b>MiniBlue</b>	MiniBlue	<b>FR GE IT JA RU SP</b>	7105639A 7105630A 7105673A 7105813A* 7135976A 7105651A	MA	(317102) or (317107)	<b>EN - 1013124A02 - Issued 01/08</b>  * available at Nordson K.K
<b>MiniBlue II</b>	MiniBlue II Pneumatic Applicators	<b>CZ DA DU FI FR GE HU IT JA KO LA PL PO RU SK SP SW</b>	7169407_06 7179930_06 7156902_06 7179863_06 7156666_06 7156674_06 7179902_06 7156673_06 7156656_06 7179860_06 7192985_06 7156735_06 7179574_06 7156665_06 7156928_06 7156670_06 7179607_06	MA	(317102) or (317107)	<b>EN - 1096215_08 - Issued 06/17</b>
<b>MiniBlue II</b>	MiniBlue II Low Profile Ball and Seat Pneumatic Applicators	<b>FR</b>	7192723_02	MA	(317102) or (317107)	<b>EN - 1120707_03 - Issued 06/17</b>

B-6 - 9

## Nordson US Hot Melt Products (sorted by Model)

### *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>MiniBlue II</b>	Plastic Cover Kit P/N 1103018	<b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>RU</b> <b>SP</b>	7156969A 7156975A 7156972A 7156970A 7169101A 7156976A	IN	(317102) or (317107)	<b>EN - 1104548A - Issued 11/10</b>
<b>PatternJet</b>	PatternJet Adhesive Dispensing Gun	<b>JA</b>	7119716A	MA	(317102) or (317107)	<b>EN - 1063110A - Issued 03/10</b>
<b>PatternJet</b>	PatternJet Applicators (Title version A02: PatternJet Adhesive Dispensing Gun)	<b>IT</b>	7135799A02	MA	(317102) or (317107)	<b>EN - 1071823_05 - Issued 04/15</b>
<b>PatternJet</b>	Cordset Replacement Kit	<b>JA</b>	7119717A	IN	(317102) or (317107)	<b>EN - 1068356A02 - Issued 06/06</b>
<b>PatternJet Plus</b>	PatternJet Plus Applicators	<b>GE</b> <b>IT</b> <b>PL</b>	7169501_02 7169496_02 7192362_02	MA	(317102) or (317107)	<b>EN - 1095295_03 - Issued 04/16</b>
<b>PatternPro</b>	PatternPro Variable Pitch Applicators (Title Version B: PatternPro Variable Pitch Guns)	<b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>SP</b>	7119471_03 7119467_03 7119468_03 7105877_03 7119469_03	MA	(317102) or (317107)	<b>EN - 1048257_03 - Issued 02/18</b> <b>Created by Nordson Benelux, Maastricht</b>
<b>Sapphire</b>	Sapphire Applicator with Hyper Dispense Technology	<b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>SP</b>	7580310_01 7580311_01 7580312_01 7580313_01 7580314_01	MA	(317102) or (317107)	<b>EN - 1125439_01 - Issued 09/17</b>

B-6 - 10

## Nordson US Hot Melt Products (sorted by Model)

### *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Sapphire</b>	Driver Board - P/N 1126152	<b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>SP</b>	7580315_01 7580316_01 7580317_01 7580318_01 7580319_01	IN	(317102) or (317107)	<b>EN - 1126173_01 - Issued 09/17</b>
<b>Sapphire</b>	Interface Board - P/N 1126154	<b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>SP</b>	7580320_01 7580321_01 7580322_01 7580323_01 7580324_01	IN	(317102) or (317107)	<b>EN - 1126174_01 - Issued 09/17</b>
<b>Sapphire</b>	Sapphire Driver Upgrade Kit - P/N 1126153	<b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>SP</b>	7580325_01 7580326_01 7580327_01 7580328_01 7580329_01	IN	(317102) or (317107)	<b>EN - 1126175_01_01 - Issued 09/17</b>
<b>SD Series</b>	SD Series Electric Gun Driver	<b>CZ</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b> <b>SW</b>	7156026D 458181B 458036A 412632A 409359A 412927A 412723A	MA	(317102) or (317107)	<b>EN - 229766D - Issued 05/05 Replaces E26 Electric Gun Driver (see Section G - Walcom)</b>





B-6 - 13

## Nordson US Hot Melt Products (sorted by Model)

### *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>UM50</b>	Universal Applicators (UM50)	<b>CZ</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>IT</b> <b>RU</b> <b>SP</b>	7593162_04 7560075_04 7135530_04 7146145A 7135531_04 7560916_04 7169467_04	OP	(317102) or (317107)	<b>EN - 1072064_04 - Issued 08/11</b>
<b>UM50</b>	Section 9 Module	<b>SP</b>	7169464_06	MAN	(317102) or (317107)	<b>EN - 1069046_06 - Issued 07/11</b> <b>Section applies to applicators with UM50 modules</b>
<b>Universal</b>	Universal Applicators (Bead /Slot)	<b>IT</b> <b>RU</b> <b>SP</b>	7135951_02 7146980A 7560477_02	OP	(317102) or (317107)	<b>EN - 1084530_02 - Issued 08/11</b>
<b>Universal</b>	High-Speed Universal Series Applicators	<b>FR</b> <b>GE</b> <b>PL</b>	7169156A03 7169161A03 7560053A03	MA	(317103) or (317106)	<b>EN - 1079832_04 - Issued 04/15</b>
<b>Universal</b>	Universal Series Spray Applicators	<b>CZ</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b>	7146718_05 7169430_05 7192974_05 7119449C* 7156896_05 7560693_05 7169137_05 7169463_05	MA	(317103) or (317106)	<b>EN - 1050063_05 - Issued 07/11</b>  * = available at Nordson K.K
<b>Universal</b>	Universal Slice Applicator	<b>GE</b>	7119610B	MA	(317103) or (317106)	<b>EN - 1031709B02 - Issued 03/11</b>
<b>Universal</b>	Universal Slice Applicator	<b>IT</b> <b>SW</b>	7179422A02 7156527A02	MA	(317103) or (317106)	<b>EN - 1072085A02 - Issued 03/09</b>

B-6 - 14

## Nordson US Hot Melt Products (sorted by Model)

### *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Universal</b>	Section 10 Filter (in-out)	<b>CZ</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b>	7146720 <b>A02</b> 7169432 <b>A02</b> 7560698 <b>A02</b> 7119457 <b>A*</b> 7156898 <b>A02</b> 7560699 <b>A02</b> 7169140 <b>A02</b> 7169465 <b>A02</b>	MA	(317102) or (317107)	<b>EN - 1050065A02 - Issued 01/07</b> <b>Section applies to applicators with a Universal in-out filter</b> <b>* available at Nordson K.K</b>
<b>Universal</b>	Section 10 Filter (Threaded)	<b>CZ</b>	7560681_03	MA	(317102) or (317107)	<b>EN - 1096214_03 - Issued 07/11</b> <b>Section applies to applicators with a threaded filter</b>
<b>Universal</b>	Section 11 Electrical System (M-style)	<b>CZ</b> <b>DU</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b>	7146721B03 7156698B03 7169433_04 7560700_04 7156899_04 7560701_04 7169141_04 7169466_04	MA	(317102) or (317107)	<b>EN - 1050067_04 - Issued 07/11</b> <b>Section applies to applicators with Universal M-style cordsets</b>
<b>Universal</b>	Section 11 Electrical System (T-style)	<b>CZ</b>	7560682B03	MA	(317102) or (317107)	<b>EN - 1050066B03 - Issued 01/08</b> <b>Section applies to applicators with Universal T-style cordsets</b>
<b>Universal</b>	Universal Allegro Elastic Coating Nozzles	<b>FR</b> <b>GE</b> <b>SP</b>	7593231_01 7593233_01 7593232_01	MA	(317103) or (317106)	<b>EN - 1120705_01 - Issued 02/15</b>
<b>Universal</b>	Universal Control Coat Nozzles	<b>FR</b> <b>GE</b> <b>SP</b>	7593234_01 7593236_01 7593235_01	MA	(317103) or (317106)	<b>EN - 1120869_01 - Issued 09/12</b>
<b>Universal</b>	Universal Controlled Fiberization (CF) Spray Nozzles (Title version A: Controlled Fiberization (CF) Lamination Application )	<b>FR</b> <b>GE</b> <b>SP</b>	7593240_02 7169575_02 7156218_02	MA  IN	(317103) or (317106)	<b>EN - 1072379_02 - Issued 07/11</b>

B-6 - 15

## Nordson US Hot Melt Products (sorted by Model)

### *Applicators (Guns)*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Universal</b>	Universal Minibead Nozzles	<b>FR</b> <b>GE</b> <b>SP</b>	7593226_01 7593228_01 7593227_01	MA	(317103) or (317106)	<b>EN - 1126825_01 - Issued 12/185</b>
<b>Universal</b>	Universal Signature Spray Nozzles (Continuous Applications) (Title version A02: Signature Lamination Applications)	<b>FR</b> <b>GE</b> <b>SP</b>	7593238_04 7169576_04 7156216_04	MA  IN	(317103) or (317106)	<b>EN - 1076139_04 - Issued 10/11</b>
<b>Universal</b>	Universal Signature Spray Nozzles (Intermittend Applications) (Title version A: Signature Lamination Applications (Intermittend))	<b>FR</b> <b>GE</b> <b>SP</b>	7593239_02 7169577_02 7156217_02	MA  IN	(317103) or (317106)	<b>EN - 1090174_02 - Issued 07/11</b>
<b>Universal</b>	Universal Summit Spray Nozzles	<b>CZ</b> <b>FR</b> <b>GE</b> <b>SP</b>	7560683_02 7593237_02 7169579_02 7156215_02	MA	(317103) or (317106)	<b>EN - 1072400_02 - Issued 07/11</b>
<b>Universal</b>	Universal SureWrap Spray Nozzles	<b>FR</b> <b>GE</b> <b>SP</b>	7593229_01 7169578_01 7593230_01	MA	(317103) or (317106)	<b>EN - 1103674_01 - Issued 07/11</b>
<b>World Gun Series</b>	World Gun Series	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>SP</b> <b>SW</b>	213788A 213908A 213869A 397147A 213830A 213819A 213899A 213897A 213916A 213824A 213818A 213826A	MA	(317103) or (317106)	<b>EN - 1027562C - Issued 11/03</b>



B-7 - 1

## Nordson US Hot Melt Products (sorted by Model)

### *Foam*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
FM 200	FoamMelt 200 Processor	DU FR GE IT PL RU SP	213492B 213503B 213474D02 7135744D 7119786D 7560775_06 213981C	MA	(317102) or (317107)	EN - 321222_06 - Issued 02/19
FM 200	FoamMelt 200 Processor	DA DU FI FR GE IT JA NO PL PO RO SP SW	447735A 447752A 464748A 447771A 447761B 447751A 447697A* 464702A 7119290A 464787A 7580936B 447773A 447792A	OP	(317102) or (317107)	EN - 321380B - Issued 03/01  * available at Nordson K.K
Foam Mix AG-900 Series	Foam Mix AG-900 Series Dispensing Gun	FR GE IT PL SP	292876A 292728A 292729A 7119198B 317283A	MA	(317102) or (317107)	EN - 108168A - Issued 09/91 108168B - Issued 01/97
Foam Mix AG-900 Series	AG900+ Applicators	JA	7169251A*	MA	(317102) or (317107)	EN - 1063320A - Issued 04/07 * available at Nordson K.K

B-7 - 2

## Nordson US Hot Melt Products (sorted by Model)

### *Foam*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Foam Mix AG-900+ Series</b>	AG900+ and AG900+ S Applicators	<b>GE</b>	7156452A	MA	(317102) or (317107)	<b>EN - 1098464A - Issued 09/09</b>
<b>SureFoam</b>	SureFoam Foam Dispensing System	<b>FR GE IT JA PO SP</b>	7146091A 7146092A 7146130A 7580600A <sub>05</sub> * 7146082A 7146068A	MA	(317102) or (317107)	<b>EN - 1079037A05 - Issued 03/14</b>  * = available at Nordson K.K.

## Nordson Finishing Products (sorted by Product Title)

C-1 - 1

*Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	0-8 CC Accu-Drop Ejector Gun	<b>GE</b> <b>IT</b>	7192283A_03 7192224A_03	MA	(317102) or (317107)	<b>EN - 1090618A_03 - Issued 02/10</b>
--	0-900 psi Pressure Reducing Diaphragm Regulator (Title - version_06: 0-900 psi Diaphragm Regulator)	<b>FR</b> <b>IT</b> <b>PL</b> <b>RU</b> <b>SE</b> <b>SP</b>	7146597D03 7192760_05 7146481D02 7169037D03 7560382_06 7146631D03	IN	(317102) or (317107)	<b>EN - 1009506_07 - Issued 01/16</b>
--	0-1000 PSI Pressure Transducer and Amplifier	<b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SE</b> <b>SP</b>	7560489_01* 7560185_01 7560184_01 7560186_01 7560187_01 7560188_01 7580090_01 7560780_01 7560189_01	IN	(317102) or (317107)	<b>EN - 1602989_01- Issued 02/13</b>  * = not yet translated
--	2-8 CC Ejector Gun	<b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>RU</b> <b>SP</b> <b>TU</b>	7179948B_02 7179866B_02 7179816B_02 7179833B_02 7179681B_02 7179909B_02 7179845B_02 7179632B_02	MA	(317102) or (317107)	<b>EN - 1040029_03 - 03/14</b>
--	2-8 CC Ejector Gun Fluid Cartridge Kit	<b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>RU</b> <b>SP</b> <b>TU</b>	7179949B 7179867B 7179817B 7179834B 7179682B 7179910B 7179846B 7179633B	IN	(317102) or (317107)	<b>EN - 1040851B02 - Issued 11/04</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 2

### *Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
23-17	7- and 10-Inch Air Motors with Air Valve	<b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	7192248 <b>C</b> 7105583B 458463 <b>C</b> 7119928 <b>C</b> 7146254 <b>C</b>	MA	(317102) or (317107)	<b>EN - 334607C - Issued 03/05</b>
1-8	25B 2:1 Plated Steel Pump (Title version E-H: 25B Pumps - Obsolete!)	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>SP</b> <b>SW</b>	292973E 292974E 292975E 292976 <b>P02</b> 412606E 317162E 317177E 458109H	MA	(317102) or (317107)	<b>EN - 104330P02 - Issued 05/07</b>
--	24B 4:1 Plated Steel Pump	<b>IT</b>	7192749F02	MA	(317102) or (317107)	<b>EN - 1044131F02 - Issued 05/07</b>
--	25B 16:1 Aluminium Pump	<b>FR</b> <b>IT</b> <b>RU</b>	7105396B 7192747 <b>E02</b> 7169036 <b>E02</b>	MA	(317102) or (317107)	<b>EN - 1044132E02 - Issued 05/07</b>
--	25B 16:1 Stainless Steel Pump	<b>FR</b> <b>GE</b> <b>IT</b>	7105397B 7580158_03 7192748_03	MA	(317102) or (317107)	<b>EN - 1044133_03 - Issued 11/12</b>
--	25B 27:1 Aluminium Pump	<b>FR</b>	7105398B	MA	(317102) or (317107)	<b>EN - 1044134_03 - Issued 11/12</b>
--	25B 27:1 Stainless Steel Pump	<b>FR</b>	7105399B	MA	(317102) or (317107)	<b>EN - 1044135_03 - Issued 11/12</b>
--	55-Gallon Powder Drum Truck for Bulk-Feed Powder Transfer Systems	<b>FR</b> <b>RU</b>	7169980A03 7156610A03	IN	(317102) or (317107)	<b>EN - 1062573_04 - Issued 04/15</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 3

### *Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
1-5	64B Pump 15:1 Aluminium	<b>DU</b> <b>GE</b> <b>IT</b> <b>SP</b>	7179360_05 7179298_05 458241_05 458331_05	MA	(317102) or (317107)	<b>EN - 104321_05 - Issued 06/19</b>
1-5A	Pressure Housing Retainer Service Kit 64B Stainless Steel Pumps (Title version B: <b>64B</b> Housing Retainer Service Kit)	<b>FR</b> <b>GE</b> <b>IT</b>	292811B 292812B 292813B	IN	(317102) or (317107)	<b>EN - 108695C - Issued 01/96</b>
--	90 Degree Cable Routing Fitting Kit	<b>GE</b>	7560779_01	IN	(317102) or (317107)	<b>EN - 1609315_01 - Issued 05/16</b>
4-2	A4B Airless Manual Spray Gun (Title version E: A4B Airless Handgun)	<b>GE</b> <b>PL</b>	107973E 409482E*	MA	(317102) or (317107)	<b>EN - 107973J02 - Issued 05/08</b> <b>* = not yet translated</b>
--	A7A Lancing Spray Guns	<b>GE</b> <b>PL</b> <b>SP</b>	7593143_05 7560852_05 7192793_05	MA	(317102) or (317107)	<b>EN - 107009_05 - Issued 08/18</b>
4-6	A7A Single and Dual Automatic Airless Spray Guns (Title version D - J: A7A Airless Spray Gun)	<b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>RU</b> <b>SP</b>	7105283J 317117D 292915D 409484D 397506L 458333E	MA	(317102) or (317107)	<b>EN - 107966L - Issued 03/06</b> <b>OLD!</b>
--	A7A Single and Dual Automatic Airless Spray Guns	<b>GE</b>	7169042A	MA	(317102) or (317107)	<b>EN - 1072640A - Issued 08/06</b> <b>NEW!</b>
--	A7A Single and Dual Modular Automatic Airless Spray Guns	<b>CZ</b> <b>GE</b> <b>IT</b> <b>RU</b> <b>SP</b> <b>SW</b>	7146615A 7169669A 7192753A 7169035A 7560446A 7169231A	MA	(317102) or (317107)	<b>EN - 1072609A - Issued 08/06</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 4

### *Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	A7A Application Head for Liquid Foil	GE	213274C	IN	(317102) or (317107)	<b>Created by Nordson Engineering GmbH Issued 01/03</b>
4-22	A20A Electric Airless Spray Gun (Title version E: A20A Electric Spray Gun)	FR GE IT PO RU SP	292916E 292917E 292918E 317143E 403096E 317140E	MA	(317102) or (317107)	<b>EN - 108182G02 - Issued 06/08</b>
4-13	A11A Compound Gun	GE	317197D	MA	(317102) or (317107)	<b>EN - 107977E - Issued 09/03</b>
--	Adjustable Mounting Assembly for Automatic Guns	GE	7169557B	IN	(317102) or (317107)	<b>EN - 104618B - Issued 03/98</b>
19-6	Air Lubricator Adjustments and Oils (Title version D: Adjusting Air Line Lubricators)	DU FR GE IT PL PO SP SW TU	292985D 292986E 292987D 292808E 412601E 317114D 317152D 458112D 7560858E	IN	(317102) or (317107)	<b>EN - 108152E - Issued 01/04</b>
--	Air Operated Color Change Valve	PL	7179705A	IN	(317102) or (317107)	<b>EN - 334619A - Issued 10/99</b>
-	Airless Material Pressure Controller	GE	213236D	IN	(317102) or (317107)	<b>Created by Nordson Engineering GmbH Issued 11/02</b>
26-21	Auto-Flo Automatic Dispensing Valve	GE	405069E	MA	(317102) or (317107)	<b>EN - 229798E - Issued 03/06</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 5

***Automotive / Container / Electronics / Liquid***

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Auto-Flo Zero-Cavity Automatic Dispensing Valve	FR	7179171D02	MA	(317102) or (317107)	<b>EN - 303796D02 - Issued 06/03</b>
--	Auto-Flo II Anti-Drool Dispense Valves	CZ FR GE IT RU PL SP TU	7179950_01 7179868_01 7179818_01 7179835_01 7179911_01 7179683_01 7179847_01 7179634_01	MA	(317102) or (317107)	<b>EN - 1104014_01 - Issued 05/12</b>
--	Auto-Flo II Automatic Dispense Valves	CZ FR GE IT PL RU SP TU	7179951_01 7179869_01 7179819_01 7179836_01 7179684_01 7179912_01 7179848_01 7179635_01	MA	(317102) or (317107)	<b>EN - 1104010_01 - Issued 05/12</b>
--	Auto-Flo II CP Dispense Valves	CZ FR GE IT PL RU SP TU	7179952_01 7179870_01 7179820_01 7179837_01 7179685_01 7179913_01 7179849_01 7179636_01	MA	(317102) or (317107)	<b>EN - 1104015_01 - Issued 05/12</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 6

***Automotive / Container / Electronics / Liquid***

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Auto-Flo II Dispense Valves for Pro-Meter-S and -S2K Applications	<b>CH</b> <b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>RU</b> <b>SP</b> <b>TU</b>	7593191_01 7179953_01 7179871_01 7179821_01 7179838_01 7179686_01 7179914_01 7179850_01 7179637_01	MA	(317102) or (317107)	<b>EN - 1104225_01 - Issued 01/13</b>
--	Auto-Flo II Spring-Close Standalone Dispense Valve Cleaning	<b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>TU</b>	7179954A 7179872A 7169209A 7179839A 7179687A 7169197A 7179915A 7179851A 7179638A	IN	(317102) or (317107)	<b>EN - 1105175A - Issued 02/11</b>
--	Auto-Flo II Zero Cavity Dispense Valves	<b>CH</b> <b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>TU</b>	7560456_03 7179955_02 7179873_02 7156914_02 7179840_02 7179266_02 7179138_03 7156922A 7179916_03 7169534_02 7179639_02	MA	(317102) or (317107)	<b>EN - 1103506_03 - Issued 03/14</b>
--	Automatic Iso-Flo Voltage-Block System	<b>PL</b>	7179700C	MA	(317102) or (317107)	<b>EN - 106589C - Issued 10/96</b>



## Nordson Finishing Products (sorted by Product Title)

C-1 - 7

***Automotive / Container / Electronics / Liquid***

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
10-21	Automatic Iso-Flo HD Voltage Block System	DU FR GE IT PL SP	7156396G02 7119161F 213475G02 409117G02 7179701G02 447670G02	MA	(317102) or (317107)	EN - 107158G02 - Issued 05/08
--	Automatic Iso-Flo HD Voltage Block System	CZ	7593408_03	MA	(317102) or (317107)	EN - 1606053_03 - Issued 03/18
10-22	Automatic Iso-Flo HD Voltage Block System	CZ DU FR GE IT PL SP	7593409B02 7156397B 7119163B 7156383B 7156387B 7179702B02 213282B	OP	(317102) or (317107)	EN - 107159B02 - Issued 10/
--	Back Pressure Diaphragm Regulator	FI GE PO SP	7560490A* 7119940A 7135812A 7146632A	IN	(317102) or (317107)	EN - 1060626A - Issued 03/05 * = not yet translated
--	BR-1 Induction Temperature Controller	DU GE SP	7169789_02 7179573_02 7169745_02	MA	(317102) or (317107)	EN - 1106132_04 - Issued 01/16
--	Bubble Detect Calibration Kit	GE IT	7192278B 7192222B	IN	(317102) or (317107)	EN - 1055813B - Issued 11/04
--	Bubble Detection System for the Pro-Meter Controller with Process Sentry	GE IT	7192241B 7192187B	IN	(317102) or (317107)	EN - 1010995B - Issued 02/01
14-5	CanWorks Display Module	GE	315747A	MA	(317102) or (317107)	EN - 106697B - Issued 09/03

## Nordson Finishing Products (sorted by Product Title)

C-1 - 8

### *Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	CanWorks SM-1 Spray Monitor	GE	7105092B	MA	(317102) or (317107)	EN - 106698B - Issued 09/03
--	CE20 Gun Air Injector Manifold Assembly Kit	GE IT	7192277C 7192193C	IN	(317102) or (317107)	EN - 1055812C - Issued 12/04
--	CE20 Gun	GE IT	7135986A03 7135975A03	MA	(317102) or (317107)	EN - 334678A03 - Issued 07/12
--	CE20 2K Large Cycle Dispense Gun	GE IT	7192287 7192198	MA	(317102) or (317107)	EN - 1107352 - Issued 09/11
12-48	Century C-708 and C-718 Workcell	DU FR GE	409005A 409006A 409003A	OP	(317102) or (317107)	EN - 303847A - Issued 05/98
-	Circulation Kit for 180D / 360D Pumps	RU	397508B	IN	(317102) or (317107)	EN - 1006454B - Issued 09/02
6-15	Circulation Kits for CP Pumps (Title version B: Circulation Valve Kit)	DU FR GE SP	292970B 292971B 292972B 409315B	IN	(317102) or (317107)	EN - 108000C - Issued 11/02
--	Clear and Black Primer Five-Gallon Pressure Pot	GE IT	7192279A02 7192194A02	IN	(317102) or (317107)	EN - 1066149A02 - Issued 10/07
12-40	Clean Coat Workcell	SP	403257A	MA	(317102) or (317107)	EN - 229801A - 02/97
17-22	CleanSpray Controller	GE PO SP	403143B 317141B 317137B	MA	(317102) or (317107)	EN - 108330E - Issued 05/04

## Nordson Finishing Products (sorted by Product Title)

C-1 - 9

### *Automotive / Container / Electronics / Liquid*

<b>EDB</b>	<b>Product Title</b>	<b>Langs.</b>	<b>P/N</b>	<b>Type</b>	<b>Price Category</b>	<b>Notes</b>
<b>4-46</b>	CleanSpray II Extension Assembly	<b>SP</b>	213620B	IN	(317102) or (317107)	<b>EN - 331286C - Issued 06/03</b>
<b>14-2</b>	CleanSpray System Operation	<b>PO SP</b>	317168C 317155C	OP	(317102) or (317107)	<b>EN - 108684C - Issued 10/03</b> <b>Date of translations 10/96</b>
--	CleanSpray XT Spray Gun	<b>GE</b>	7119997A02	MA	(317102) or (317107)	<b>EN - 1067500A02 - Issued 07/06</b>
--	Compact Manual Iso-Flo Voltage Block System	<b>PL</b>	7179704B	MA	(317102) or (317107)	<b>EN - 108390B - Issued 07/96</b>
<b>26-26</b>	Controlled Pressure (CP) Gun	<b>GE</b>	409394C	MA	(317102) or (317107)	<b>EN - 303788C - Issued 04/02</b>
<b>12-43</b>	Conveyorized Century Workcell	<b>FR GE IT</b>	412941A 412942A 413052A	MA	(317102) or (317107)	<b>EN - 303778A - Issued 06/99</b>
<b>1-9</b>	CP Pump	<b>DU FR GE PL SP</b>	292964E 292965E 292966E 7560822_03 409312H	MA	(317102) or (317107)	<b>EN - 104373_03 - Issued 10/15</b>
--	CP II Inline Regulator	<b>CZ FR GE IT PL RU SP TU</b>	7179956A 7179874A 7179823A 7179841A 7179688A 7179917A 7179853A 7179640A	MA	(317102) or (317107)	<b>EN - 1097151_02 - Issued 06/13</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 10

*Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	CP II Regulator	<b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>RU</b> <b>SP</b> <b>TU</b>	7179957A_04 7179875A_04 7179824A_04 7179842A_04 7179689A_04 7179918A_04 7179854A_04 7179641A_04	MA	(317102) or (317107)	<b>EN - 1075654A_05 - Issued 06/13</b>
--	CWS 100 - Cable Wet Coating System	<b>EN</b> <b>GE</b>	213391A 464925A	MA	(317102) or (317107)	<b>Created by Nordson Engineering GmbH Issued 08/01</b>
--	DR-1676 Pump	<b>CZ</b> <b>FR</b> <b>TU</b>	7560093_03 7580074_07 7560856_05	MA	(317102) or (317107)	<b>EN - 237432_07 - Issued 04/17</b>
<b>28-13</b>	Drip and Drag Applicator Tool with Felt Wick Dispenser	<b>GE</b>	447610A	MA	(317102) or (317107)	<b>EN - 331287A - Issued 12/99</b>
--	Dual-Pump Primer Delivery Stand	<b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>SP</b>	7146710A-02 7192286A-02 7156056A-02 7560449A-02 7560561A-02	MA	(317102) or (317107)	<b>EN - 1065659A-02 - Issued 11/05</b>
--	Dual Pro-Meter S-Series PCI Controller	<b>CH</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b>	7560457A 7156921A 7146277A 7146949A 7156940A 7560262A 7169522A	MA	(317102) or (317107)	<b>EN - 1083956A - Issued 01/08</b>
--	Dual-Zone Temperature Control Unit	<b>FR</b> <b>PL</b>	7192896A 7169280A	MA	(317102) or (317107)	<b>EN - 1107681_04 - Issued 05/16</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 11

*Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	EcoLiner Compound Gun	<b>FR</b> <b>GE</b>	7146114A 7179517A	MA	(317102) or (317107)	<b>EN - 1069243A - Issued 03/06</b>
<b>0-9</b>	Electrostatic Cable Care and Installation	<b>GE</b> <b>IT</b> <b>SW</b>	409102C 412636C 458120C	MA	(317102) or (317107)	<b>EN - 107913C - Issued 02/04</b>
<b>0-8</b>	Electrostatic System Checks	<b>GE</b> <b>IT</b> <b>SW</b>	409101B 412630B 458119B	IN	(317102) or (317107)	<b>EN - 107964B - Issued 04/96</b>
--	EP2 Pump System	<b>FI</b> <b>PL</b> <b>PO</b> <b>RU</b>	7560491A02* 7146478 <b>A02</b> 7135806A 7169039 <b>A02</b>	MA	(317102) or (317107)	<b>EN - 1072608A02 - Issued 05/08</b> <b>= not yet translated</b>
--	EP-2 Three-Piston Pump	<b>FI</b> <b>GE</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b>	7560492_03* 7119183A 7560190_03 7135807A 7169040A 7119201A	MA	(317102) or (317107)	<b>EN - 1049229_03 - Issued 04/15</b> <b>* = not yet translated</b>
--	EP-2 Three Piston Pump (QRG)	<b>PL</b>	7560191_01	IN	(317102) or (317107)	<b>1607026_01 - Issued 2015</b>
<b>9-15</b>	EPS6 Electrostatic Power Supply	<b>CZ</b> <b>DU</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>SP</b> <b>SW</b>	7156774 <b>D</b> 7179418 <b>D</b> 397478 <b>D</b> 409385 <b>D</b> 7192509 <b>D</b> 7119066 <b>D</b> 458122 <b>C</b>	MA	(317102) or (317107)	<b>EN - 237381D - Issued 11/01</b>
<b>9-13</b>	EPS-8 and EPS-9 Electrostatic Power Supplies	<b>IT</b>	409384B	MA	(317102) or (317107)	<b>EN - 107068C - Issued 11/01</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 12

***Automotive / Container / Electronics / Liquid***

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
17-23	Extended Watchdog Pulse Timer	GE PO SP	403145A 317142A 317138A	IN	(317102) or (317107)	EN - 108821B - Issued 02/01
--	Felt Installation for Flow-Through-Felt Applicators	GE IT SP	7192234A 7192192A 7560562A	IN	(317102) or (317107)	EN - 1043852A - Issued 04/04
--	Five-Gallon Black Primer T-Handle Assemblies	GE IT	7192226B 7192186B	MA	(317102) or (317107)	EN - 343559B - Issued 05/04
--	Flo-Brush PDMP Applicator Tool	GE IT PL	7192284A 7192217A 7560448A	MA	(317102) or (317107)	EN 1091853A - Issued 04/09
--	Flowmeter with Encoder Assembly	GE IT SP TU	7192242E 7192188E 7560722E 7560014E	MA	(317102) or (317107)	EN - 1016731E - Issued 03/05
--	Flowmeter Service Kits	GE IT SP TU	7192225C02 7192219C02 7560721_04 7560013_03	IN	(317102) or (317107)	EN - 334679_04 - Issued 2015
--	Flow-Through-Felt Gravity Feed Applicator Tool	GE IT	7192288_01 7192218_01	MA	(317102) or (317107)	EN - 1108200_01 - Issued 10/11
--	Flow-Through-Felt PDMP Applicator Tool	FR GE IT SP	7146709B02 7192356_04 7156057_04 7560563_05	MA	(317102) or (317107)	EN - 1065657_05 - Issued 11/15
--	Flow-Through-Felt Primer Dispensing System	SP	7560565A	MA	(317102) or (317107)	EN - 1009200A - Issued 02/02

## Nordson Finishing Products (sorted by Product Title)

C-1 - 13

### *Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Flow-Through-Felt Rub Block Maintenance	<b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	7146711B 7192233B 7156058B 7560566B	IN	(317102) or (317107)	<b>EN - 1045635B - Issued 06/05</b>
--	Flow-Through-Felt System Operator's Card	<b>GE</b> <b>IT</b> <b>SP</b>	7192275A 7192220A 7560567A	OP	(317102) or (317107)	<b>EN - 1045721A - Issued 03/04</b>
--	Flow-Through-Felt Troubleshooting Guide	<b>FR</b> <b>IT</b> <b>SP</b>	7156084A 7156083_02 7560568_02	IN	(317102) or (317107)	<b>EN - 1063663_02 - Issued 09/13</b>
<b>6-16</b>	Hard Seat Fluid Pressure Regulator	<b>GE</b> <b>RU</b> <b>SP</b>	458158E 7119602H 412726H	IN	(317102) or (317107)	<b>EN - 104742H - Issued 11/03</b>
--	HD Cable and Retrofit Cable Care and Installation	<b>PL</b>	7192510B	IN	(317102) or (317107)	<b>EN - 229802B - Issued 01/06</b>
--	Helical Flowmeter	<b>GE</b> <b>IT</b>	7192276B 7192221B	IN	(317102) or (317107)	<b>EN - 1050114B - Issued 02/05</b>
<b>5-2</b>	High Pressure Fluid Hoses	<b>IT</b> <b>SW</b>	458242C 458113C	IN	(317102) or (317107)	<b>EN - 108145_04 - Issued 08/13</b>
<b>26-14</b>	HIVISC Gun Manual	<b>SP</b>	409408A	MA	(317102) or (317107)	<b>EN - 107001B - Issued 10/98</b>
--	Ink-Dot Controller	<b>FI</b> <b>GE</b> <b>PL</b> <b>PO</b> <b>SP</b>	7560493C02* 7560398C02 7156529C02 7135802C02 7146636C02	MA	(317102) or (317107)	<b>EN - 106605C02 - Issued 09/03</b> <b>* = not yet translated</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 14

### *Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
4-33	Ink-Dot Electric Spray Gun	PL PO SP	7156528D 7135803D 7146635D	MA	(317102) or (317107)	EN - 229727D - Issued 01/01
--	Ink-Dot Electric Spray Gun	FI FR GE	75604934_02* 7169600A 7560399_02	MA	(317102) or (317107)	EN - 1103065_02 - Issued 10/11 * = not yet translated
--	Ink-Dot Hydraulic System	PL PO SP	7156530A02 7135804B 7146633B	MA	(317102) or (317107)	EN - 237436B and EN - 237436A02, both Issued 09/03
--	Ink-Dot Hydraulic System	FI GE	7560495A* 7560400A	MA	(317102) or (317107)	EN - 1103066A - Issued 7/10 * = not yet translated
--	Ink-Dot Hydraulic System with Reservoir Manifold	FR GE	7169601A 7560476A	MA	(317102) or (317107)	EN - 1103067A - Issued 07/10
	Ink-Dot System with Reservoir Manifold	FR	7169602A	OP	(317102) or (317107)	EN - 1100472A - Issued 06/12
14-18	Ink-Dot System	DU GE IT PO SP	397055B 447720B 407433A 317169A 317156A	OP	(317102) or (317107)	EN - 229726B02 - Issued 10/03
--	Ink-Dot Series II Driver	PO SP	7135808B02 7146634B02	IN	(317102) or (317107)	EN - 237466B02 - Issued 09/03



## Nordson Finishing Products (sorted by Product Title)

C-1 - 15

### *Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
3-54	Inverted Dual High Pressure Fluid Filters Assemblies (Title Versions A-C: Inverted Dual High Pressure Fluid Filters)	<b>CZ</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b>	7146617C02 7179361 <b>C03</b> 7156879 <b>C03</b> 7179299 <b>C03</b> 464946 <b>C03</b> 7146480C02 7135810C 7119603C 7146627 <b>C03</b>	IN	(317102) or (317107)	<b>EN - 334621C03 - Issued 02/09</b>
3-53	Inverted High Pressure Fluid Filters	<b>DU</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>RU</b> <b>SE</b> <b>SP</b> <b>SW</b>	7179362B 213100_03 464891B 7146479B 397505B 7560378B 213148B 7169233B	IN	(317102) or (317107)	<b>EN - 331290_03 - Issued 01/17</b> <b>( B version issued 04/04)</b>
--	IPS-20 Automatic Electrostatic System Controller	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	7179373A 7156465A 7169413A 7179376A 7179332A	MA	(317102) or (317107)	<b>EN - 1084168A - Issued 06/08</b>
--	IPS-20 Manual Electrostatic System Controller	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	7179372A 7156466A 7169414A 7179375A 7179331A	MA	(317102) or (317107)	<b>EN - 1084167A - Issued 06/08</b>
10-26	Iso-Flo Coupling Repair	<b>IT</b>	213735C	IN	(317102) or (317107)	<b>EN- 229782C - Issued 01/02</b>
10-24	Dump Shuttle Kit for the HD Manual Iso-Flo	<b>IT</b>	213734B	IN	(317102) or (317107)	<b>EN - 229771B - Issued 11/97</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 16

***Automotive / Container / Electronics / Liquid***

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
10-25	Dump Shuttle Kit for the HD Automatic Iso-Flo	GE	7119447C	IN	(317102) or (317107)	EN - 229772C - Issued 02/01
10-5	Iso-Flo Supply Pump	FR	269873	IN	(317102) or (317107)	EN - 108621B - Issued 12/96
--	iTrax Electronic Pressure Regulator	FI GE	7560499_03* 7560401_03	MA	(317102) or (317107)	EN - 1604922_03 - Issued 01/16 * = not yet translated
--	iTrax PRx Module	SP	7169511A04	MA	(317102) or (317107)	EN - 1078355_08 - Issued 04/15
--	iTrax PRx II Module	FI GE PO	7560498_02* 7560402_02 7580618_02	MA	(317102) or (317107)	EN - 1604923_02 - Issued 03/15 * = not yet translated
--	iTrax Spray Controller	FI GE PO SP	7560497_06* 7560286_06 7580616_08 7169512A04	MA	(317102) or (317107)	EN - 1079459_08 - Issued 02/18 * = not yet translated
--	iTrax Spray Monitor with Can-in-Pocket Feature	FI GE PL PO SP	7560496_04* 7560287_04 7146477A02 7580617_06 7169513A03	MA	(317102) or (317107)	EN - 1066206_06 - Issued 06/16 * = not yet translated
--	iTrax System Operator Interface User' s Guide	FI	7560500_01*	OP	(317102) or (317107)	EN - 1604854_01 - Issued 02/14 * = not yet translated
21-56	Kinetix Electrostatic Spray Gun Automatic Version 60kV Airspray and KVLP Waterborne	FR GE IT	7105187F 213172C 464885B	MA	(317102) or (317107)	EN - 334609H04 - Issued 08/08

## Nordson Finishing Products (sorted by Product Title)

C-1 - 17

### *Automotive / Container / Electronics / Liquid*

<b>EDB</b>	<b>Product Title</b>	<b>Langs.</b>	<b>P/N</b>	<b>Type</b>	<b>Price Category</b>	<b>Notes</b>
<b>8-8</b>	Kinetix Electrostatic Spray Gun Automatic Air-Assisted Airless	<b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	7105239E 213160B 464739A 213284B	MA	(317102) or (317107)	<b>EN - 334593F03 - Issued 08/08</b>
<b>8-13</b>	Kinetix Electrostatic Spray Gun Manual Air-Assisted Airless	<b>FR</b> <b>GE</b> <b>IT</b>	7105041E 213161D 447784C	MA	(317102) or (317107)	<b>EN - 334591F03 - Issued 08/08</b>
<b>8-7</b>	Kinetix Electrostatic Spray Gun Automatic Airless	<b>FR</b> <b>GE</b> <b>IT</b>	7105238E 213191B 464765A	MA	(317102) or (317107)	<b>EN - 334592F03 - Issued 08/08</b>
<b>8-11</b>	Kinetix Electrostatic Spray Gun Manual Version Airless	<b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b>	7105242C 213192D 464749C 7105817G	MA	(317102) or (317107)	<b>EN - 334598G03 - Issued 08/08</b>
<b>17-24</b>	Level Detector	<b>PO</b> <b>SP</b>	317132A 317139A	MA	(317102) or (317107)	<b>EN - 106988A - Issued 07/95</b>
<b>6-31</b>	Low-Pressure Color Change Manifold	<b>GE</b>	397528B	MA	(317102) or (317107)	<b>EN - 331151C - Issued 10/03</b>
<b>1-34</b>	Low-Pressure Diaphragm Pump	<b>GE</b>	7156308A	IN	(317102) or (317107)	<b>EN - 1013754A - Issued 11/01</b>
<b>5-3</b>	Low Pressure Hoses and Connectors	<b>IT</b>	412661B	IN	(317102) or (317107)	<b>EN - 104598B - Issued 07/97</b>
-	Magnetic Separator Adjustments	<b>FR</b> <b>GE</b>	7105715A 7119858A	IN	(317102) or (317107)	<b>EN - 1040053A Issued 03/03</b>
<b>28-7</b>	Manual Black Primer Application System	<b>GE</b> <b>IT</b> <b>SP</b>	7192208C 7192174C 409410A	MA	(317102) or (317107)	<b>EN - 107003C - Issued 04/02</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 18

***Automotive / Container / Electronics / Liquid***

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
28-6	Manual Clear Primer Application System	GE IT SP	7192207B 7192173B 409409A	MA	(317102) or (317107)	EN - 107002B - Issued 02/06
10-20	Manual Iso-Flo HD Voltage Block System	CZ DU FR GE IT PL SP SW	7119876G 7179370G02 7119160G 458193G02 407427G02 7179703_03 7179320G02 458117C	MA	(317102) or (317107)	EN - 107157_03 - Issued 0713
10-19	Manual Iso-Flo HD Voltage Block System	DU FR GE IT SP	7179371B 7119162B 458194B 407432B 7179321B	OP	(317102) or (317107)	EN - 187695B02 - Issued 10/03
-	Manual Pressure Regulator - Stainless Seat	GE	213237D	IN	(317102) or (317107)	Created by Nordson Engineering GmbH Issued 11/02
--	Mastic Gun	GE IT	7192236A 7192191A	MA	(317102) or (317107)	EN - 1040769A - Issued 02/04
17-26	MEG Driver	GE PL SP	7105093B 7146475B 458322A	MA	(317102) or (317107)	EN - 229776B - Issued 10/14
--	MEG Inside Stripe Applicator	GE IT SP	7179352_04 7192754_04 7192839_04	MA	(317102) or (317107)	EN - 1084632_04 - Issued 07/16

## Nordson Finishing Products (sorted by Product Title)

C-1 - 19

***Automotive / Container / Electronics / Liquid***

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	MEG II Airless Spray Guns ( Reduced Cavity and Extended Tip )	FR GE IT PL PO SP	7192971_09 7105094_09 7192755_09 7146476_09 7135805_09 7146622_09	MA	(317102) or (317107)	<b>EN - 334669_09 - Issued 07/16</b>
--	MEG II Airless Spray Guns with 10 ft Cable	FI FR GE IT PL PO RU SE SP	7560501_02* 7560174_04 7560173_04 7560175_04 7560176_04 7560177_04 7580088_04 7560384_04 7560178_04	MA	(317102) or (317107)	<b>EN - 1602990_04 - Issued 07/16</b>  * = not yet translated
--	MEG II Armature Spring Kit	PO SP	7135815B 7146623B	IN	(317102) or (317107)	<b>EN - 1046764_02 - Issued 09/14</b>
--	MEG II Spray Gun (QRG)	FR GE IT PL PO RU SE SP	7192995_01 7560179_01 7560180_01 7560181_01 7560182_01 7580089_01 7560389_01 7560183_01	IN	(317102) or (317107)	<b>EN - 1606179_01 - Issued 09/14</b>
--	Mini Regenerative Air Dryer	GE IT	7192281A03 7192196A03	IN	(317102) or (317107)	<b>EN - 1066461A_03 - Issued 01/07</b>
--	MSP3 Filter Element Change	GE PO RU SP	7580678_02 7560472_02 7560263_02 7580267_02	IN	(317102) or (317107)	<b>EN - 1083734_02 - Issued 11/14</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 20

*Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	NC-1 Spray Gun Driver	<b>GE</b> <b>IT</b> <b>SE</b> <b>SP</b>	7169624A 7192759A 7560385A 7560660A	IN	(317102) or (317107)	<b>EN - 1101142A - Issued 04/10</b>
--	NH-4 Heaters	<b>DA</b> <b>GE</b>	7560111_01 7580159_02	MA	(317102) or (317107)	<b>EN - 1602369_02 - Issued 03/17</b>
--	Nine-Station Valve Pack	<b>GE</b> <b>IT</b> <b>SP</b>	7192280A 7192195A 7560569A	IN	(317102) or (317107)	<b>EN - 1066460A - Issued 2005</b>
--	Nordson Airless Nozzle Tester	<b>FR</b>	7192972A	OP	(317102) or (317107)	<b>EN - 187681A -Issued 11/95</b>
--	Nordson Mastic Regulator	<b>GE</b> <b>IT</b>	7192238B 7192189B	IN	(317102) or (317107)	<b>EN - 1017656B - Issued 04/03</b>
<b>2-0</b>	Paint Heater Calculations	<b>PL</b>	7119197A	IN	(317102) or (317107)	<b>EN - 334624A - Issued 11/99</b>
--	Pattern Control Kit	<b>PL</b>	7192511A	IN	(317102) or (317107)	<b>EN - 1023432A - Issued 02/02</b>
--	PDMP Purge Gland Greasing	<b>GE</b> <b>IT</b> <b>SP</b>	7192289_01 7192199_01 7560564_01	IN	(317102) or (317107)	<b>EN - 1601202_01 - Issued 02/12</b>
<b>PermaFlo</b>	Circulation Kit for PermaFlo Pumps	<b>CZ</b> <b>GE</b> <b>IT</b>	7156051A 7105191A 7192752A	IN	(317102) or (317107)	<b>EN - 1029315A - Issued 11/02</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 21

### *Automotive / Container / Electronics / Liquid*

<b>EDB</b>	<b>Product Title</b>	<b>Langs.</b>	<b>P/N</b>	<b>Type</b>	<b>Price Category</b>	<b>Notes</b>
<b>PermaFlo</b>	PermaFlo 815 Pump	<b>GE</b> <b>IT</b> <b>PL</b> <b>RU</b> <b>SP</b> <b>SW</b> <b>TU</b>	7179202_02 7192750_02 7560853_02 7179421_02 7560308_03 7169260A 7169518A	MA	(317102) or (317107)	<b>EN - 1102698_03 - Issued 10/16</b>
<b>PermaFlo</b>	PermaFlo 815 Pump Service Kits Quick Reference Guide	<b>FR</b>	7156480 -QR02	IN	(317102) or (317107)	<b>EN - 1085470-QR03 - Issued 2008</b>
<b>PermaFlo</b>	PermaFlo 830 Pump	<b>DA</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>TU</b>	7560110_03 7156481A02 7179203_03 7192751_03 7169519A02	MA	(317102) or (317107)	<b>EN - 1085458_03 - Issued 07/12</b>
<b>PermaFlo</b>	PermaFlo 830 Pump Service Kits Quick Reference Guide	<b>FR</b>	7156481 -QR02	IN	(317102) or (317107)	<b>EN - 1085458-QR03 - Issued 2008</b>
<b>Permaflo</b>	PermaFlo Pump Packing Kits	<b>FR</b>	7156491A02	IN	317102) or (317107)	<b>EN - 1087851A02 - Issued 09/08</b>
-	Pressure Transducer and Amplifier Assembly	<b>GE</b>	7105095D	IN	(317102) or (317107)	<b>EN - 331233D - Issued 12/03</b>
<b>21-51</b>	Prism Automatic Low-Pressure Spray Guns (Airspray and HVLP)	<b>GE</b> <b>IT</b> <b>SP</b>	7105010C 458188C 397832C	MA	(317102) or (317107)	<b>EN - 303869C02 - Issued 08/08</b>
<b>25-18</b>	Process Sentry Controller (Body Shop Version)	<b>GE</b>	412809A	MA	(317102) or (317107)	<b>EN - 331162C - Issued 07/02</b>
--	Pro-Meter Controller with Process Sentry (AC Motor Version)	<b>GE</b> <b>IT</b>	7192209A 7192175A	MA	(317102) or (317107)	<b>EN - 334623A - Issued 04/00</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 22

### *Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Pro-Meter Controller with Process Sentry (DC Motor Version)	<b>GE</b> <b>IT</b>	7192239B 7192231B	MA	(317102) or (317107)	<b>EN - 1007773B - Issued 11/03</b>
--	Pro-Meter Gear Metering Pump	<b>CH</b> <b>GE</b> <b>IT</b>	7580058E03 7135988E03 7135913E03	MA	(317102) or (317107)	<b>EN - 303808E03 - Issued 04/16</b>
--	Pro-Meter S-Series Dispensers	<b>CH</b> <b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>TU</b>	7560458_08 7179959_06 7179173_06 7156932_07 7146276_07 7179691_06 7146946_09 7156924A04 7179920_07 7169521A05 7179643_06	MA	(317102) or (317107)	<b>EN - 1075653_09 - Issued 07/16</b>
--	Pro-Meter S2K-Series Dispensers	<b>CH</b> <b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>RU</b> <b>SP</b> <b>TU</b>	7593192_09 7179958_07 7179876_07 7179825_07 7179843_07 7179690_07 7179919_07 7179855_07 7179642_07	MA	(317102) or (317107)	<b>EN - 1089138_09 - Issued 03/18</b>
--	Pro-Meter II 14-Zone Heated Controller with PROFIBUS	<b>IT</b>	7146461A	MA	(317102) or (317107)	<b>EN - 1086500A - Issued 04/08</b>
--	Pro-Swirl Applicator and Controller	<b>GE</b> <b>IT</b>	7192240C02 7192223C02	MA	(317102) or (317107)	<b>EN - 1009910_03 - Issued 08/15</b>



## Nordson Finishing Products (sorted by Product Title)

C-1 - 23

### *Automotive / Container / Electronics / Liquid*

<b>EDB</b>	<b>Product Title</b>	<b>Langs.</b>	<b>P/N</b>	<b>Type</b>	<b>Price Category</b>	<b>Notes</b>
--	Pro-Swirl Motor Rotor Replacement	<b>GE</b> <b>IT</b>	7192235B 7192200B	IN	(317102) or (317107)	<b>EN - 1041592B - Issued 06/05</b>
--	Pro-Swirl Teach Tip Installation	<b>GE</b> <b>IT</b>	7192237A 7192190A	IN	(317102) or (317107)	<b>EN - 1024900A - Issued 02/02</b>
--	PS3 Controller General Operation Guide with Optional Controller Configurations	<b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>RU</b> <b>SP</b> <b>TU</b>	7179960_01 7179877_01 7179826_01 7179844_01 7179692_01 7179921_01 7179856_01 7179644_01	MA	(317102) or (317107)	<b>EN - 1602964_01 - Issued 12/12</b>
--	RA-20 Paint/ Solvent/ Dump Valve	<b>PL</b> <b>PO</b>	7192515B02 7179696B02	IN	(317102) or (317107)	<b>EN - 237431B02 - Issued 09/07</b>
<b>21-47</b>	RA-20 Rotary Atomizer	<b>CZ</b> <b>IT</b> <b>PL</b> <b>SP</b>	7156772 <b>J02</b> 409468C 7192512 <b>J02</b> 412897F	MA	(317102) or (317107)	<b>EN - 237366J02 - Issued 10/07</b>
<b>21-48</b>	RA-20 Rotary Atomizer	<b>CZ</b> <b>DU</b> <b>PL</b> <b>SP</b>	7156773 <b>B02</b> 213950B 7192513 <b>B02</b> 412974B	OP	(317102) or (317107)	<b>EN - 237367B02 - Issued 10/03</b>
--	RA-20 Rotary Atomizer Nozzle Kit	<b>PL</b>	7192514A	IN	(317102) or (317107)	<b>EN - 1065516A - Issued 10/05</b>
--	RPM Indicator	<b>PL</b>	7192516_03	MA	(317102) or (317107)	<b>EN - 108103_03 - Issued 07/13</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 24

***Automotive / Container / Electronics / Liquid***

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
Rhino	Standard A- and B-Unit Rhino Bulk Unloader Controls	<b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>RU</b> <b>SP</b>	7192244 <b>C</b> 405004 <b>C</b> 409416 <b>C</b> 407283 <b>C</b> 7135342 <b>C</b> * 7119370 <b>C</b> 7179555 <b>C</b> 405007 <b>B</b>	MA	(317103) or (317106)	<b>EN - 187688_02 - Issued 06/15</b>  <b>Version C Issued 02/03</b>  <b>* available at Nordson K.K.</b>
--	Rhino AB 5-Gallon Container Change	<b>CH</b> <b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>SP</b>	7580718_01 7580723_01 7580721_01 7580719_01 7580724_01 7580722_01 7580720_01	OP	(317102) or (317107)	<b>EN - 1612497_01 - Issued 05/18</b>
--	Rhino AB Lower Check Repacement	<b>CH</b> <b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>SP</b>	7580725_01 7580730_01 7580728_01 7580726_01 7580731_01 7580729_01 7580727_01	IN	(317102) or (317107)	<b>EN - 1613134_01 - Issued 06/18</b>
--	Rhino AB Packing Gland Replacement	<b>CH</b> <b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>SP</b>	7580732_01 7580737_01 7580735_01 7580733_01 7580738_01 7580736_01 7580734_01	IN	(317102) or (317107)	<b>EN - 1613099_01 - Issued 06/18</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 25

***Automotive / Container / Electronics / Liquid***

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino AB Soft Goods Replacement Kit	CH CZ FR GE IT JA SP	7580739_01 7580744_01 7580742_01 7580740_01 7580745_01 7580743_01 7580741_01	IN	(317102) or (317107)	EN - 1613476_01 - Issued 06/18
--	Rhino AB Upper Check Valve Replacement	CH CZ FR GE IT JA SP	7580746_01 7580751_01 7580749_01 7580747_01 7580752_01 7580750_01 7580748_01	IN	(317102) or (317107)	EN - 1613133_01 - Issued 06/18
--	Rhino AB and AC Unloaders	CH CZ FR GE IT JA SP	7580767_01 7580772_01 7580770_01 7580768_01 7580773_01 7580771_01 7580769_01	MA	(317102) or (317107)	EN - 1609834_01 - Issued 05/18
--	Rhino ACO Conversion Kit	CH CZ FR GE IT JA SP	7580753_02 7580758_02 7580756_02 7580754_02 7580759_02 7580757_02 7580755_02	IN	(317102) or (317107)	EN - 1610315_02 - Issued 02/18
--	Rhino Bleed Valve	CH CZ FR GE IT JA SP	7580760_01 7580765_01 7580763_01 7580761_01 7580766_01 7580764_01 7580762_01	IN	(317102) or (317107)	EN - 1612230_01 - Issued 10/17

## Nordson Finishing Products (sorted by Product Title)

C-1 - 26

### *Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
27-53	Rhino Bulk Unloader Container Change	<b>CZ</b> <b>FR</b> <b>GE</b> <b>NO</b> <b>PL</b> <b>RU</b> <b>SP</b> <b>SW</b>	7146645C 7146834C 7146871C 7146536C 7119371C 7179554C 7146256C 213120C	OP	(317102) or (317107)	<b>EN - 107172C - Issued 12/00</b>
23-18	Rhino Bulk Unloader Frames	<b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b>	7192245B 7105582B 447609B 7119927B	MA	(317102) or (317107)	<b>EN - 334608B - Issued 10/00</b>
--	Rhino Heated Bulk Unloader Drum Position Sensor	<b>IT</b>	7146454A	IN	(317102) or (317107)	<b>EN - 1085713A-02 - Issued 09/08</b>
--	Rhino Power Train Cell Pail Hold Down	<b>GE</b> <b>RO</b>	7169202A 7169190A	IN	(317102) or (317107)	<b>EN - 1105525A - Issued 01/11</b>
--	Rhino Power Train Cell Drum Position Switch	<b>GE</b> <b>RO</b>	7169203A 7169191A	IN	(317102) or (317107)	<b>EN - 1105526A - Issued 01/11</b>
--	Rhino Power Train Cell Ram Control and Blow-Off Module	<b>GE</b> <b>RO</b>	7169204A 7169192A	IN	(317102) or (317107)	<b>EN - 1105544A - Issued 01/11</b>
--	Rhino Power Train Cell Follower Module	<b>GE</b> <b>RO</b>	7169205A 7169193A	IN	(317102) or (317107)	<b>EN - 1105591A - Issued 01/11</b>
--	Rhino Power Train Cell Pail Change	<b>GE</b> <b>RO</b>	7169206A 7169194A	IN	(317102) or (317107)	<b>EN - 1106431A - Issued 01/11</b>
--	Rhino Power Train Cell Pail Level Detect Module	<b>GE</b> <b>RO</b>	7169207A 7169195A	IN	(317102) or (317107)	<b>EN - 1106360A - Issued 01/11</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 27

*Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino Power Train Cell Pneumatic Crossover Control Module	<b>GE</b> <b>RO</b>	7169208A 7169196A	IN	(317102) or (317107)	<b>EN - 1106561A - Issued 01/11</b>
<b>27-64</b>	Rhino Pump Service Kits	<b>CZ</b> <b>SW</b>	7192246B 213118B	IN	(317102) or (317107)	<b>EN - 303801B - Issued 04/00</b>
<b>23-16</b>	Rhino Screw Together 24:1 / 48:1 & 32:1 / 65:1 Pumps	<b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b>	7192247C 7105584C 458461C 7119926C	MA	(317102) or (317107)	<b>EN - 334606C - Issued 09/01</b>
--	Rhino SD/SD2/XD/XD2 ¾- and 1¼ -Inch Ball Check Valves	<b>CH</b> <b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PO</b> <b>RO</b> <b>SP</b>	7560459_03 7580127_03 7179177A02 7156918_03 7192259_02 7119724A* 7146965_03 7156939A02 7169529A02	IN	(317102) or (317107)	<b>EN - 1043115_04 - Issued 07/18</b>  <b>* available at Nordson K.K</b>
--	Rhino SD Bleed Valves	<b>CH</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PO</b> <b>RO</b> <b>SP</b>	7560460 <b>A03</b> 7156919 <b>A03</b> 7179888 <b>A03</b> 7119725A* 7146966 <b>A03</b> 7156938 <b>A03</b> 7169530 <b>A03</b>	IN	(317102) or (317107)	<b>EN - 1047087A03 - Issued 07/08</b>  <b>* available at Nordson K.K</b>
--	Rhino SD Interconnect Hose Modules	<b>JA</b>	7119727A*	IN	(317102) or (317107)	<b>EN - 1047086A - Issued 02/04</b> <b>* available at Nordson K.K</b>
--	Rhino SD Packing Gland Replacement	<b>JA</b>	7119728A*	IN	(317102) or (317107)	<b>EN - 1033035A - Issued 11/03</b> <b>* available at Nordson K.K</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 28

### *Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino SD Switch for Glass Application	<b>JA</b>	7119730A*	IN	(317102) or (317107)	<b>EN - 1047117A - Issued 03/04</b> * available at Nordson K.K
--	Rhino SD Purge Buttons for Electric Changeover Controls	<b>CH</b> <b>GE</b> <b>JA</b> <b>PO</b>	7560461A02 7580681_03 7119732A* 7146967A02	IN	(317102) or (317107)	<b>EN - 1047104_03 - Issued 06/18</b> * available at Nordson K.K
--	Rhino SD Runaway Sensors	<b>JA</b>	7119733A*	IN	(317102) or (317107)	<b>EN - 1047108B - Issued 03/06</b> * available at Nordson K.K
--	Rhino SD Single Red Lens 24 VDC Light Towers for Electric Changeover Controls	<b>JA</b>	7119734A*	IN	(317102) or (317107)	<b>EN - 1047115A - Issued 02/04</b> * available at Nordson K.K
--	Rhino SD Single Amber Lens 24 VDC Light Tower for Electric Changeover Controls	<b>JA</b>	7119735A*	IN	(317102) or (317107)	<b>EN - 1047114A - Issued 02/04</b> * available at Nordson K.K
--	Rhino SD/XD 125- or 160-mm Frames	<b>CH</b> <b>CZ</b> <b>GE</b> <b>PO</b> <b>SP</b>	7593154_05 7593507_05 7580679_02 7560956_01 7580268_02	MA	(317102) or (317107)	<b>EN - 1607593_05 - Issued 08/18</b>
--	Rhino SD / XD Container Change	<b>FR</b> <b>JA</b> <b>PL</b> <b>PO</b> <b>SP</b>	7179178B 7119726A* 7179264B 7146962B 7169533B	OP	(317102) or (317107)	<b>EN - 1045988B - Issued 02/06</b> * available at Nordson K.K
--	Rhino SD / XD PCI and PLC/DeviceNet Filter Stand Cable Module	<b>CH</b> <b>GE</b> <b>PO</b> <b>SP</b>	7560462A 7580682A 7560957A 7580269A	IN	(317102) or (317107)	<b>EN - 1047120A - Issued 04/06</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 29

### *Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino SD / XD Pressure Switches for PCI/PLC and DeviceNet Applications	<b>CH</b> <b>GE</b> <b>JA</b> <b>PO</b> <b>RU</b>	7593158 <b>B</b> 7580680 <b>B</b> 7119731A 7560473 <b>B</b> 7560264 <b>B</b>	IN	(317102) or (317107)	<b>EN - 1047116B - Issued 02/05</b>
--	Rhino SD / XD Pump Air Valve Rebuild Kit	<b>JA</b>	7119737A*	IN	(317102) or (317107)	<b>EN - 1062535A - Issued 05/05</b> <b>* available at Nordson K.K</b>
--	Rhino SD / XD Type-F Electric Control Module Pneumatic Purge Button (Title version A: Rhino SD Ford Electrical ChangeOver Control)	<b>JA</b>	7119729A*	IN	(317102) or (317107)	<b>EN - 1047105B-01 - Issued 07/06</b> <b>* available at Nordson K.K</b>
--	Rhino SD / XD Type-G/D 24 Vdc ISO Electric Control Module	<b>CH</b> <b>GE</b> <b>PO</b>	7560463A02 7580683A02 7146968A02	IN	(317102) or (317107)	<b>EN - 1047125A02 - Issued 08/06</b>
--	Rhino SD / XD Type-G/D Pneumatic Control Module	<b>SP</b>	7169524A02	IN	(317102) or (317107)	<b>EN - 1047102A02 - Issued 08/06</b>
--	Rhino SD2 / XD2 and VE Hose Support Module	<b>CH</b> <b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>SP</b>	7560468_02 7179414_02 7179404_02 7192311_02 7146453_02 7179395_02 7179141_02 7169528A	IN	(317102) or (317107)	<b>EN - 1085711_02 - Issued 12/12</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 30

### *Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino SD2 / XD2 and VE Interconnect Hose Modules	<b>CH</b> <b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>SP</b>	7560467A_03 7179415_03 7179405_03 7192282A_03 7192197A_03 7179396_03 7146970A_03 7169527A_03	IN	(317102) or (317107)	<b>EN - 1077748A_03 - Issued 12/12</b>
--	Rhino SD2 / XD2 ARW Air Circuit Module	<b>GE</b> <b>IT</b>	7192309A 7192269A	IN	(317102) or (317107)	<b>EN - 1077884A - Issued 08/07</b>
--	Rhino SD2 / XD2 Centering Pad Module	<b>CH</b>	7593155A	IN	(317102) or (317107)	<b>EN - 1096811A - Issued 06/09</b>
--	Rhino SD2 / XD2 Container Change for Two-Hand Controls with Blow-Off Circuit	<b>TU</b>	7560023A	IN	(317102) or (317107)	<b>EN - 1094288A - Issued 06/09</b>
--	Rhino SD2 / XD2 DeciceNet I/O Modules	<b>GE</b> <b>IT</b> <b>PO</b> <b>SP</b>	7192306A 7192266A 7146971A 7580270A	IN	(317102) or (317107)	<b>EN - 1077749A - Issued 08/07</b>
--	Rhino SD2 / XD2 Drive Train Shroud	<b>CZ</b>	7580128A	IN	(317102) or (317107)	<b>EN - 1087764A - Issued 2008</b>
--	Rhino SD2 / XD2 Drum-Centering Shoes	<b>CH</b> <b>CZ</b>	7593156A 7580129A	IN	(317102) or (317107)	<b>EN - 1096813A - Issued 06/09</b>
--	Rhino SD2 / XD2 Electric Drum/Pail Level Indicators	<b>CH</b> <b>GE</b> <b>IT</b> <b>PO</b>	7560464A 7192304A 7192263A 7146969A	IN	(317102) or (317107)	<b>EN - 1077746A - Issued 07/07</b>



## Nordson Finishing Products (sorted by Product Title)

C-1 - 31

### *Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino SD2 / XD2 Follower Modules	<b>CH</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>SP</b> <b>TU</b>	7560466 <b>A04</b> 7192308A03 7192268A03 7146972 <b>A04</b> 7169525A03 7560016 <b>A04</b>	IN	(317102) or (317107)	<b>EN - 1077883A04 - Issued 06/09</b>
--	Rhino SD2 / XD2 Frames	<b>CH</b> <b>CZ</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>RO</b> <b>SP</b>	7560465_05 7179020_05 7156920_05 7146447_05 7146964_05 7156933_05 7169531_05	MA	(317102) or (317107)	<b>EN - 1073086_05 - Issued 03/18</b>
--	Rhino SD2 / XD2 NAP Frames	<b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>RU</b>	7179021A02 7179176A02 7192312A02 7192271A02 7179262A02 7560265A02	MA	(317102) or (317107)	<b>EN - 1077149A02 - Issued 06/09</b>
--	Rhino SD2/XD2 NPN Runaway Sensor	<b>CH</b> <b>GE</b> <b>PO</b>	7593157A 7580684A 7560958A	IN	(317102) or (317107)	<b>EN - 1096335A - Issued 06/09</b>
--	Rhino SD2 / XD2 Packing Gland Replacement	<b>CH</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>RO</b> <b>SP</b> <b>TU</b>	7560469A 7156916A 7192261A 7146963_02 7156937A 7169532A 7560015A	OP	(317102) or (317107)	<b>EN - 1075674_02 - Issued 2016</b>
--	Rhino SD2 / XD2 Pneumatic Drum/Pail Level Indicators	<b>GE</b> <b>IT</b> <b>SP</b>	7192305A02 7192264A02 7169526A02	IN	(317102) or (317107)	<b>EN - 1077747A02 - Issued 06/09</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 32

***Automotive / Container / Electronics / Liquid***

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino SD2 / XD2 Pressure Relief Valves	<b>GE</b> <b>IT</b> <b>PO</b>	7192307A 7192267A 7560474A	IN	(317102) or (317107)	<b>EN - 1077882A - Issued 07/07</b>
--	Rhino SD2 / XD2 Pumps (Title -A08 :Rhino SD2 / XD2 / XD2H Pumps)	<b>CH</b> <b>CZ</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>SP</b>	7560470_13 7179019_15 7192795_12 7179179A11 7135989A11 7146275A11 7179261A11 7146959_15 7156931A10 7169523A11	MA	(317102) or (317107)	<b>EN - 1073520_15 - Issued 03/18</b>
--	Rhino SD2 / XD2 Runaway Sensors	<b>CH</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>SP</b>	7560471A02 7179180A02 7192303A02 7192262A02 7179140A02 7580271A02	IN	(317102) or (317107)	<b>EN - 1075675A02 - Issued 01/10</b>
--	Rhino SD2 / XD2 CE Two-Hand Operation Control Module	<b>TU</b>	7560021A	IN	(317102) or (317107)	<b>EN - 1087765A - Issued 05/08</b>
--	Rhino SD2 / XD2 / XD2H Customer-Specific Pumps	<b>IT</b> <b>TU</b>	7179889A03 7560024A03	MA	(317102) or (317107)	<b>EN - 1096339A03 - Issued 11/10</b>
--	Rhino SD2CE / XD2H Drum Level Detect Module	<b>IT</b> <b>TU</b>	7146448A 7560017A	MA	(317102) or (317107)	<b>EN - 1085716A - Issued 02/08</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 33

### *Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino SD3 / XD3 5-Gallon Dual Post Container Hold-Down	CH CZ FR GE IT JA SP	7580781_01 7580786_01 7580784_01 7580782_01 7580787_01 7580785_01 7580783_01	IN	(317102) or (317107)	EN - 1613100_01 - Issued 06/18
--	Rhino SD3 / XD3 5-Gallon Follower Modules	CH CZ FR GE IT JA SP	7580788_03 7580790_03 7580495_03 7580496_03 7580791_03 7580789_03 7580497_03	MA03	(317102) or (317107)	EN - 1610313_03 - Issued 06/18
--	Rhino SD3 / XD3 55-Gallon Pneumatic Unloader Container Change	CH CZ FR GE IT JA SP	7580792_01 7580797_01 7580795_01 7580793_01 7580798_01 7580796_01 7580794_01	OP	(317102) or (317107)	EN - 1612498_01 - Issued 05/18
--	Rhino SD3 / XD3 190 cc ARW Packing Gland Replacement	CH CZ FR GE IT JA SP	7580774_01 7580779_01 7580777_01 7580775_01 7580780_01 7580778_01 7580776_01	IN	(317102) or (317107)	EN - 1613686_01 - Issued 06/18
--	Rhino SD3 / XD3 Air Motor	CH CZ FR GE IT JA SP	7580799_03 7580801_03 7580492_03 7580493_03 7580802_03 7580800_03 7580494_03	MA	(317102) or (317107)	EN - 1610312_03 - Issued 06/18

## Nordson Finishing Products (sorted by Product Title)

C-1 - 34

### *Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino SD3 / XD3 Automatic Crossover (ACO) to Automatic Shutdown (ASD) Conversion Kit	CH CZ FR GE IT JA SP	7580803_01 7580808_01 7580806_01 7580804_01 7580809_01 7580807_01 7580805_01	IN	(317102) or (317107)	EN - 1613844_01 - Issued 06/18
--	Rhino SD3 / XD3 Container Hold-Down	CH CZ FR GE IT JA SP	7580810_02 7580815_02 7580813_02 7580811_02 7580816_02 7580814_02 7580812_02	IN	(317102) or (317107)	EN - 1610314_02 - Issued 06/18
--	Rhino SD3 / XD3 Container Level Light Tower	CH CZ FR GE IT JA SP	7580817_01 7580822_01 7580820_01 7580818_01 7580823_01 7580821_01 7580819_01	IN	(317102) or (317107)	EN - 1610316_01 - Issued 06/18
--	Rhino SD3 / XD3 Dual-Post Frame	CH CZ FR GE IT JA SP	7580824_01 7580829_01 7580827_01 7580825_01 7580830_01 7580828_01 7580826_01	MA	(317102) or (317107)	EN - 1613098_01 - Issued 06/18
--	Rhino SD3 / XD3 Hose Support Module for Pneumatic Controls	CH CZ FR GE IT JA SP	7580831_01 7580836_01 7580834_01 7580832_01 7580837_01 7580835_01 7580833_01	IN	(317102) or (317107)	EN - 1613386_01 - Issued 06/18

## Nordson Finishing Products (sorted by Product Title)

C-1 - 35

### *Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino SD3 / XD3 Hydraulic Section	CH CZ FR GE IT JA SP	7580838_04 7580840_04 7580504_04 7580505_04 7580841_04 7580839_04 7580506_04	MA	(317102) or (317107)	EN - 1611632_04 - Issued 06/18
--	Rhino SD3 / XD3 Hydraulic Section Pump Outlet Manifold	CH CZ FR GE IT JA SP	7580842_02 7580844_02 7580513_02 7580514_02 7580845_02 7580843_02 7580515_02	IN	(317102) or (317107)	EN - 1611641_02 - Issued 06/18
--	Rhino SD3 / XD3 Material Container Blow-Off Check Valve	CH CZ FR GE IT JA SP	7580846_02 7580848_02 7580498_02 7580499_02 7580849_02 7580847_02 7580500_02	IN	(317102) or (317107)	EN - 1610317_02 - Issued 06/18
--	Rhino SD3 / XD3 Packing Gland Replacement	CH CZ FR GE IT JA SP	7580850_01 7580852_01 7580510_01 7580511_01 7580853_01 7580851_01 7580512_01	IN	(317102) or (317107)	EN - 1611640_01 - Issued 07/17
--	Rhino SD3 / XD3 Pneumatic Container Level Detectors	CH CZ FR GE IT JA SP	7580854_01 7580859_01 7580857_01 7580855_01 7580860_01 7580858_01 7580856_01	IN	(317102) or (317107)	EN - 1613339_01 - Issued 06/18

## Nordson Finishing Products (sorted by Product Title)

C-1 - 36

*Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino SD3 / XD3 Pneumatic Controls	<b>CH</b> <b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>SP</b>	7580861_02 7580863_02 7580507_02 7580508_02 7580864_02 7580862_02 7580509_02	MA	(317102) or (317107)	<b>EN - 1611639_02 - Issued 06/18</b>
--	Rhino (SD3 / XD3) Single-Post Container Change	<b>CH</b> <b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>SP</b>	7580865_01 7580870_01 7580868_01 7580866_01 7580871_01 7580869_01 7580867_01	OP	(317102) or (317107)	<b>EN - 1607399_01 - Issued 05/17</b>
--	Rhino SD3 / XD3 Single-Post Frame	<b>CH</b> <b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>SP</b>	7580872_03 7580874_03 7580501_03 7580502_03 7580875_03 7580873_03 7580503_03	MA	(317102) or (317107)	<b>EN - 1610311_03 - Issued 06/18</b>
--	Rhino SD3 / XD3 Single-Post Unloaders	<b>CH</b> <b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>SP</b>	7580876_01 7580881_01 7580879_01 7580877_01 7580882_01 7580880_01 7580878_01	MA	(317102) or (317107)	<b>EN - 1610310_02 - Issued 06/18</b>
<b>23-15</b>	Rhino Stainless Steel 24:1 / 48:1 Single-Acting Bolt Together Pumps	<b>GE</b>	447613A	MA	(317102) or (317107)	<b>EN - 334605B - Issued 01/04</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 37

### *Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
27-49	Rhino Unloader Packing Gland Replacement	<b>CZ</b> <b>FR</b> <b>GE</b> <b>PL</b> <b>RU</b> <b>SP</b>	7192243A 7146835A 7146872A 7119372A 7179556A 7146255A	OP	(317102) or (317107)	<b>EN - 187674A - Issued 09/96</b>
27-59	GMT Rhino Unloader Packing Gland Replacement - Updated Pump Design (Title version B: Rhino Unloader Packing Gland Replacement - Updated Pump Design)	<b>SW</b>	213119B	OP	(317102) or (317107)	<b>EN - 229760C - Issued 07/03</b>
--	Rhino VE Bulk Unloaders, 125-mm Frame	<b>CZ</b>	7580130_04	MA	(317102) or (317107)	<b>EN - 1608271_04 - Issued 09/19</b>
--	Rhino VE Bleed Valve	<b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>RU</b>	7179018A 7179174A 7192295A 7146455A 7179265A 7560267A	IN	(317102) or (317107)	<b>EN - 1080105A - Issued 07/07</b> <b>Obsolete!</b> <b>-&gt; Replaced by 1608273_01</b>
--	Rhino VE/CE 24 Vdc Light Tower for Pneumatic Control Modules	<b>CZ</b> <b>GE</b> <b>IT</b>	7580132_01 7192298_01 7192253_01	IN	(317102) or (317107)	<b>EN - 1602148_01 - Issued 2013</b>
--	Rhino VE/CE Bulk Unloader OP Card	<b>CZ</b> <b>FR</b> <b>GE</b> <b>PL</b> <b>RU</b>	7179410_01 7179401_01 7192302_01 7179392_01 7560269_01	OP	(317102) or (317107)	<b>EN - 1602948_01 - Issued 12/12</b>
--	Rhino VE/CE Pneumatic Level Detect Modules	<b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>RU</b>	7179413_01 7179403_01 7192299_01 7192254_01 7179394_01 7560270_01	IN	(317102) or (317107)	<b>EN - 1603025_01 - Issued 12/12</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 38

### *Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino VE Follower Modules	<b>CZ</b> <b>FR</b> <b>SP</b>	7580131_01 7580958_01 7580297_01	IN	(317102) or (317107)	<b>EN - 1608275_01 - Issued 11/15</b>
--	Rhino VE Pneumatic Drum Level Modules	<b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b>	7179412_01 7179402_01 7192296_01 7192251_01 7179393_01	IN	(317102) or (317107)	<b>EN - 1602963_01 - Issued 12/12</b>
--	Rhino VE Pop-Off Valve	<b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b>	7179417_01 7179407_01 7192300_01 7192255_01 7179398_01	IN	(317102) or (317107)	<b>EN - 1097674_01 - Issued 12/12</b>
--	Rhino VE Relief Valves	<b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b>	7179416_01 7179406_01 7192301_01 7192256_01 7179397_01	IN	(317102) or (317107)	<b>EN - 1098016_01 - Issued 03/12</b>
--	Rhino VE Standard Bulk Unloader OP Card	<b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b>	7179409_01 7179400_01 7192294_01 7192258_01 7179391_01	OP	(317102) or (317107)	<b>EN - 1600110_01 - Issued 12/12</b>
--	Rhino XD2 Stainless Steel Packing Gland Replacement	<b>GE</b> <b>IT</b>	7192310A 7192270A	IN	(317102) or (317107)	<b>EN - 1081653A - Issued 10/07</b>
--	Rhino XD2H Container Change for Two-Hand Control Urethane Systems	<b>IT</b>	7179890A	OP	(317102) or (317107)	<b>EN - 1087958A - Issued 06/09</b>
--	Rhino XD2H Heated Control Modules	<b>IT</b> <b>TU</b>	7146450A 7560019A02	MA	(317102) or (317107)	<b>EN - 1087552A_02 - Issued 09/08</b>



## Nordson Finishing Products (sorted by Product Title)

C-1 - 39

***Automotive / Container / Electronics / Liquid***

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Rhino XD2H Heated Follower Module with Steel Ring	<b>IT</b> <b>TU</b>	7146451A 7560018A	MA	(317102) or (317107)	<b>EN - 1085717_02 - Issued 11/15</b>
--	Rhino XD2H Interconnect Hose Module	<b>IT</b> <b>TU</b>	7146452A 7560020A	MA	(317102) or (317107)	<b>EN - 1087763A - Issued 05/08</b>
--	Rhino XD2H Platen/ J-Box Harness Assembly	<b>IT</b> <b>TU</b>	7146449A 7560022A	MA	(317102) or (317107)	<b>EN - 1087784A - Issued 05/08</b>
--	Saturn Solenoid Valves	<b>JA</b>	7119801A*	IN	(317102) or (317107)	<b>EN - 1059638B - Issued 05/05</b> <b>* available at Nordson K.K</b>
--	Small Cv Saturn Solenoid Valves	<b>JA</b>	7119802A*	IN	(317102) or (317107)	<b>EN - 1069640A -Issued 04/06</b> <b>* available at Nordson K.K</b>
--	SDS Single-PCI Controller	<b>FR</b> <b>PO</b>	7179172A02 7179139A02	MA	(317102) or (317107)	<b>EN - 1062961A_02 - Issued 11/07</b>
--	Self-Venting Pressure Regulator	<b>IT</b>	7192756A	IN	(317102) or (317107)	<b>EN - 1105708A - Issued 08/13</b>
<b>3-5</b>	Siphon Strainer Assemblies	<b>GE</b>	7156307D	IN	(317102) or (317107)	<b>EN - 108466D - Issued 07/99</b>
<b>6-14</b>	Soft Seat Fluid Pressure Regulator	<b>GE</b> <b>IT</b> <b>PO</b> <b>SP</b>	447767E 213870E 317178C 317154C	IN	(317102) or (317107)	<b>EN - 104622F - Issued 11/03</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 40

### *Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
19-5	Pump Packing and Solvent Chamber Fluid Guide (Title version F: Solvent Chamber Fluids)	DU FR GE IT NO PL PO SP SW TU	292981F 292982G 292983F 292984G 292962F 412603G 317113F 317151F 458111F 7560857G	IN	(317102) or (317107)	EN - 108044G - Issued 10/03
26-15	Spray Automatic Dispensing Valves	GE SP	405070A 403013A	MA	(317102) or (317107)	EN - 107023A - Issued 06/95
6-13	Spray Pressure Control Manifold	DU FI FR GE IT PO RU SE SP	7179363G02 7560502_03* 7156881G02 317161G02 7179317G02 7135811G 7169038G02 7560383_03 7146629G02	IN	(317102) or (317107)	EN - 108730_03 - Issued 04/15 * = not yet translated
22-1	Standard and Conical AN Series Air Spray Nozzles) (Title version D: Standard and Conical Air Spray Nozzles)	GE IT SW	409103D 412640D 458116D	IN	(317102) or (317107)	EN - 107967E - Issued 08/01
--	Standard and Stainless Steel Circulation Valves	IT	7192758A	IN	(317102) or (317107)	EN - 1033690A - Issued 11/02
---	Standard and Stainless Steel Single and Dual Circulation Kits	GE IT RU	397903D 7192757D 7119604D	IN	(317102) or (317107)	EN - 104625D - Issued 11/02

## Nordson Finishing Products (sorted by Product Title)

C-1 - 41

***Automotive / Container / Electronics / Liquid***

<b>EDB</b>	<b>Product Title</b>	<b>Langs.</b>	<b>P/N</b>	<b>Type</b>	<b>Price Category</b>	<b>Notes</b>
<b>StediFlo</b>	StediFlow 3:1 and 6:1 Low Pressure Pumps	<b>CZ PL</b>	7179519_01 7179510_01	MA	(317102) or (317107)	<b>EN - 1601877_01 - Issued 07/12</b>
<b>StediFlo</b>	StediFlow 8:1 Low Pressure Pump	<b>CZ PL RO</b>	7179520_01 7179511_01 7560045_01	MA	(317102) or (317107)	<b>EN - 1601878_01 - Issued 07/12</b>
<b>StediFlo</b>	StediFlow 10:1 Pump	<b>CZ PL</b>	7179521_01 7179512_01	MA	(317102) or (317107)	<b>EN - 1601879_01 - Issued 07/12</b>
<b>StediFlo</b>	StediFlow 12:1 Pump	<b>CZ PL</b>	7179522_01 7179513_01	MA	(317102) or (317107)	<b>EN - 1601880_01 - Issued 07/12</b>
<b>StediFlo</b>	StediFlow 18:1/ 32:1Pumps	<b>CZ PL SP</b>	7179523_01 7179514_01 7560447_01	MA	(317102) or (317107)	<b>EN - 1601881_01 - Issued 07/12</b>
<b>StediFlo</b>	StediFlow High Pressure 57:1 Pump	<b>CZ PL</b>	7179524_01 7179515_01	MA	(317102) or (317107)	<b>EN - 1601882_01 - Issued 07/12</b>
--	T-Filters	<b>PO SP</b>	7135809A 7146628A04	IN	(317102) or (317107)	<b>EN - 303843A04 - Issued 05/08</b>
--	Temperature Control System	<b>CZ FI FR GE</b>	7560196_02 7560503_02* 7580073_04 7135536_05	MA	(317102) or (317107)	<b>EN - 1075456_05 - Issued 05/17</b> * = not yet translated

## Nordson Finishing Products (sorted by Product Title)

C-1 - 42

*Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Trilogy Air Assisted Airless Manual Spray Gun	CH CZ DA FR GE IT JA KO PL SP SW	7179056_01 7179467_01 7560112_01 7179057_01 7179058_01 7179059_01 7179060_01 7179061_01 7179458_01 7179062_01 7179063_01	MA	(317102) or (317107)	<b>EN - 1601051_02 - Issued 12/15</b>
--	Trilogy Air Assisted Airless LT Manual Spray Gun	CH CZ FR GE IT JA KO PL SP SW	7179065_01 7179468_01 7179066_01 7179067_01 7179068_01 7179069_01 7179070_01 7179459_01 7179071_01 7179072_01	MA	(317102) or (317107)	<b>EN - 1601052_03 - Issued 02/16</b>
--	Trilogy GP Air Spray and LVLP Gravity Fed Manual Spray Guns	CH CZ FR GE IT JA KO PL SP SW	7179073_01 7179469_01 7179074_01 7179075_01 7179076_01 7179077_01 7179078_01 7179460_01 7179079_01 7179080_01	MA	(317102) or (317107)	<b>EN - 1601053_02 - Issued 07/13</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 43

***Automotive / Container / Electronics / Liquid***

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Trilogy AC Air Spray and LVLP Gravity Fed Manual Spray Guns	CH CZ FR GE IT JA KO PL SP SW	7179081_01 7179470_01 7179082_01 7179083_01 7179084_01 7179085_01 7179086_01 7179461_01 7179087_01 7179088_01	MA	(317102) or (317107)	EN - 1601054_02 - Issued 07/13
	Trilogy Air Spray and LVLP Gravity Fed Manual Spray Guns	CH CZ FR GE IT JA KO PL SP SW	7179089_01 7179471_01 7179090_01 7179091_01 7179092_01 7179093_01 7179094_01 7179462_01 7179095_01 7179096_01	MA	(317102) or (317107)	EN - 1601055_03 - Issued 02/16
--	Trilogy Air Spray and LVLP Siphon Fed Manual Spray Guns	CH CZ FR GE IT JA KO PL SP SW	7179097_01 7179472_01 7179098_01 7179099_01 7179100_01 7179101_01 7179102_01 7179463_01 7179103_01 7179104_01	MA	(317102) or (317107)	EN - 1601056_03 - Issued 02/16

## Nordson Finishing Products (sorted by Product Title)

C-1 - 44

*Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Trilogy Air-Assisted Airless Automatic Spray Guns	CH CZ FR GE IT JA KO PL SP SW	7179105_01 7179473_01 7179106_01 7179107_01 7179108_01 7179109_01 7179110_01 7179464_01 7179111_01 7179112_01	MA	(317102) or (317107)	EN - 1601057_01 - Issued 06/12
--	Trilogy Air Spray and LVLP Automatic Spray Guns  (Title version _01: Trilogy Automatic AS and LP Guns)	CH CZ FR GE IT JA KO PL PO SP SW	7179113_01 7179474_01 7179114_01 7179115_01 7179168_01 7179117_01 7179118_01 7179465_01 7179695_01 7179119_01 7179120_01	MA	(317102) or (317107)	EN - 1601058_03 - Issued 03/14
--	Trilogy LP Quick Change Automatic Spray Guns	CH CZ FR GE IT JA KO PL SP SW	7179121_01 7179475_01 7179122_01 7179123_01 7179124_01 7179125_01 7179126_01 7179466_01 7179127_01 7179128_01	MA	(317102) or (317107)	EN - 1601059_01 - Issued 06/12
--	Trilogy Manual Electrostatic Air Spray/HVLP Solventborne Spray Gun	DU FR GE IT SP	7179425A 7156877A 7169317A 7179433A 7169293A	MA	(317102) or (317107)	EN - 1093591A - Issued 06/09

## Nordson Finishing Products (sorted by Product Title)

C-1 - 45

***Automotive / Container / Electronics / Liquid***

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Trilogy Manual Electrostatic Air Spray/HVLP Waterborne Spray Gun	<b>DU</b> <b>GE</b> <b>IT</b> <b>SP</b>	7179428A 7179313A 7179436A 7179327A	MA	(317102) or (317107)	<b>EN - 1093558A - Issued 06/09</b>
--	Trilogy Solventborne Electrostatic HVLP and Air Spray Automatic Gun	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	7179427A 7156878A 7179303A 7179435A 7179326A	MA	(317102) or (317107)	<b>EN - 1093593A - Issued 04/09</b>
--	Trilogy Waterborne Electrostatic HVLP and Air Spray Automatic Gun	<b>CZ</b> <b>DU</b> <b>GE</b> <b>IT</b> <b>SP</b>	7593411A 7179426A 7179312A 7179434A 7169250A	MA	(317102) or (317107)	<b>EN - 1093592A - Issued 04/09</b>
<b>26-19</b>	Two Component Dispensing Gun	<b>GE</b>	409393A	MA	(317102) or (317107)	<b>EN - 107063C_04 - Issued 08/10</b>
<b>28-12</b>	Two Component Meter	<b>GE</b>	412794A	MA	(317102) or (317107)	<b>EN - 331161A - Issued 04/99</b>
--	Two-Way Ball Valves and Ball Valve Manifolds	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>SP</b>	7179364D02 7156880D02 7179300D02 7179318D02 7135813D02 7146625D02	IN	(317102) or (317107)	<b>EN - 104667D02 - Issued 03/07</b>
--	Universal Automatic Non-Conductive Fluid Regulator	<b>GE</b> <b>PL</b> <b>SP</b>	397902 <b>F03</b> 7179706 <b>F03</b> 7169249A	MA	(317102) or (317107)	<b>EN - 1017527F03 - Issued 04/08</b>

## Nordson Finishing Products (sorted by Product Title)

C-1 - 46

*Automotive / Container / Electronics / Liquid*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Welded Can Coating System (System Training Guide)	PL	7119962A	MA	(317102) or (317107)	EN - C0057 - Issued 11/06
--	XPS 60 Power Supply	CZ DU	7593410_02 7580011_02	MA	(317102) or (317107)	EN - 1606291_02 - Issued 07/16



## Nordson Finishing Products (sorted by Product Title)

C-2 - 1

### U.S. Powder

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Antistatic Powder Feed Tubing	<b>DU</b>	7135922A	IN	(317102) or (317107)	<b>EN - 1070652A - Issued 06/06</b>
--	ColorMax 2 Powder Coating System with Encore Feed Center) (Title version_01: ColorMax 2 E/Cubed Powder Coating System with Encore Feed Center)	<b>SP</b>	7192606_01	MA	(317102) or (317107)	<b>EN - 1605397_04 - Issued 10/15</b>
--	ColorMax 2 Powder Coating System with Encore® Venturi Feed Center - Color Change Procedure .ppt	<b>SP</b>	7560076_02	IN	(317102) or (317107)	<b>EN - 1605545_03 - Issued 06/15</b>
--	ColorMax Powder Coating System	<b>PO SP</b>	7169279C02 7169354C02	MA	(317102) or (317107)	<b>EN - 1012899C02 - Issued 06/09</b> <b>Title on emanuals: ColorMax Powder Coating System with Spectrum Feed Center and Sure-Max Transfer System</b>
--	ColorMax Powder Coating Booth Installation Guide	<b>PO SP</b>	7169285A 7169353A	MA	(317102) or (317107)	<b>EN - 1099290A - Issued 02/10</b>
--	Container Inside Powder Coating Equipment	<b>GE</b>	7156409A	IN	(317102) or (317107)	<b>EN - 1092529A - Issued 12/08</b>
<b>38-10</b>	Econo-Coat Series II Powder Coating System	<b>SP</b>	412692B	MA	(317102) or (317107)	<b>EN - 106712C02 - Issued 1010</b>
<b>31-0</b>	Electrostatic System Installation, Checks and Troubleshooting	<b>SP</b>	213353A	MA	(317102) or (317107)	<b>EN - 334632A - Issued 04/03</b> <b>Issue date of SP translation : 02/00</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 2

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Encore Angled Spray Extensions	<b>CZ</b> <b>GE</b> <b>FR</b> <b>RU</b> <b>SP</b>	7580992_02 7580663_02 7580122_02 7580969_02 7580998_02	IN	(317102) or (317107)	<b>EN - 1605615_02 - Issued 02/16</b>
--	Encore Automatic Powder Spray Guns	<b>CH</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>LI</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>SW</b> <b>TU</b>	7593211_16 7169910_16 7179583A03 7169784A02 7169443A02 7169771_16 7169338_16 7169807A02 7179380A04 7169555A03 7169767A02 7169452A02 7169777_16 7169436_16 7169819A02 7192597_07	MA	(317102) or (317107)	<b>EN - 1098185_17 - Issued 03/19</b>
	Encore Engage External Controller	<b>GE</b>	7593572_01	MA	(317102) or (317107)	<b>EN - 1615897_01 - Issued 05/19</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 3

### U.S. Powder

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Encore Generation II Powder Feed Pumps	CH CZ DA DU ES FI FR GE IT LI PL PO RU SP SW TU	7593212_02 7169911A 7179584A 7169783A 7179618A 7169188A 7169734A 7169199A 7169806A 7179386A 7156808A 7156968A 7156613A 7169107A 7156818A 7192598_02	IN	(317102) or (317107)	EN - 1095927_02 - Issued 01/14
--	Encore Inline Powder Feed Pump	CZ DU FI FR GE IT LI PL PO RO RU SP SW	7580337_02 7169785A 7169801A 7169772A 7169798A 7169808A 7179385A 7169553A 7169768A 7169455A 7169778A 7169437A 7169820A	IN	(317102) or (317107)	EN - 1095928_02 - Issued 01/14
--	Encore Lance Extensions	DU FR GE IT PL RU SP	7593588_01 7593589_01 7593590_01 7593591_01 7593592_01 7593593_01 7593594_01	IN	(317102) or (317107)	EN - 1609894_01 - Issued 10/16

## Nordson Finishing Products (sorted by Product Title)

C-2 - 4

### U.S. Powder

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Encore Manual Powder Spray System	CH CZ CR DA DU FI FR GE HU IT LI PL PO RU SP SW	7156064A* 7146813A 7146726A 7146899A 7146841A 7146891A 7146837A 7146851A 7146868A 7146826A 7192126A02 7146847A 7156967A02 7146822A 7146930A 7146830A	OP	(317102) or (317107)	<b>EN - 1088668A02 - Issued 04/09</b>  * = Document and translation is NOT issued by TDLL !
--	Encore Pattern Adjuster Kit	FR SP	7169733A 7169690A	IN	(317102) or (317107)	<b>EN - 1098440A - Issued 11/09</b>
--	Encore Powder Feed Center	SP	7192607_01	MA	(317102) or (317107)	<b>EN - 1602966_05 - Issued 10/15</b>
--	Ion Collector Kit for Encore Automatic Guns	CZ DA DU FI FR GE IT PO RO RU SP SW TU	7169912_06 7179275A02 7179311A02 7179245A02 7169919_06 7179223_06 7179248A02 7179343A02 7179367A02 7169907_06 7169896_06 7179324A02 7179379A02	IN	(317102) or (317107)	<b>EN - 1098186_06 - Issued 09/16</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 5

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Encore HD</b>	Encore HD Automatic Powder Spray Guns	<b>CZ</b>	7192398_13	MA	(317102) or (317107)	<b>EN - 1602018_13 - Issued 02/19</b>
		<b>DA</b>	7192432_08			
		<b>DU</b>	7192105_08			
		<b>FI</b>	7192410_08			
		<b>FR</b>	7192503_13			
		<b>GE</b>	7192132_13			
		<b>HU</b>	7580394_08			
		<b>IT</b>	7192404_08			
		<b>PL</b>	7192470_08			
		<b>PO</b>	7192538_08			
		<b>RO</b>	7192142_08			
		<b>RU</b>	7192229_13			
		<b>SL</b>	7192463_08			
		<b>SP</b>	7192121_13			
<b>SW</b>	7192420_08					
<b>TU</b>	7192476_08					
<b>Encore HD</b>	Encore HD Automatic System Pump Panel	<b>CH</b>	7580687_01	MA	(317102) or (317107)	<b>EN - 1612312_01 - Issued 10/17</b>
		<b>CZ</b>	7580688_01			
		<b>DA</b>	7580689_01			
		<b>DU</b>	7580690_01			
		<b>FI</b>	7580691_01			
		<b>FR</b>	7580692_01			
		<b>GE</b>	7580693_01			
		<b>HU</b>	7593165_01			
		<b>IT</b>	7580694_01			
		<b>JA</b>	7580695_01			
		<b>PL</b>	7580696_01			
		<b>PO</b>	7580697_01			
		<b>RO</b>	7580698_01			
		<b>RU</b>	7580699_01			
		<b>SL</b>	7580700_01			
		<b>SP</b>	7580701_01			
		<b>SW</b>	7580702_01			
<b>TU</b>	7580685_01					

## Nordson Finishing Products (sorted by Product Title)

C-2 - 6

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Encore HD</b>	Encore HD Color-on-Demand System	<b>CZ</b>	7593413_03	MA	(317102) or (317107)	<b>EN - 1612313_03 - Issued 12/18</b>
<b>Encore HD</b>	Encore HD Manual Powder Spray Gun	<b>CH CR CZ DA DU FI FR GE HU IT JA PL PO RO RU SL SP SW TU</b>	7560450_07 7580008_09 7192399_13 7192433_07 7192458_13 7192411_07 7192504_13 7192377_13 7580460_09 7192405_07 7560451_09 7192471_07 7192539_07 7192382_07 7192371_13 7192464_07 7192387_07 7192421_08 7192477_01	MA	(317102) or (317107)	<b>EN - 1604869_13 - Issued 07/18</b>
<b>Encore HD</b>	Encore HD Manual Powder Spray Guns - Lance Extensions -	<b>CZ FR GE RU SP</b>	7580989_01 7593106_01 7580990_01 7580973_01 7593107_01	IN	(317102) or (317107)	<b>EN - 1604971_01 - Issued 12/13</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 7

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Encore HD</b>	Encore HD Manual Powder Spray System	<b>CH</b>	7560431_01	MA	(317102) or (317107)	<b>EN - 1605707_04 - Issued 07/18</b>
		<b>CZ</b>	7560544_01			
		<b>DA</b>	7560586_01			
		<b>DU</b>	7560587_01			
		<b>FI</b>	7560588_01			
		<b>FR</b>	7560589_01			
		<b>GE</b>	7560429_01			
		<b>HU</b>	7580459_01			
		<b>IT</b>	7560547_01			
		<b>JA</b>	7560432_01			
		<b>PL</b>	7560428_01			
		<b>PO</b>	7560594_01			
		<b>RO</b>	7560590_01			
		<b>RU</b>	7560591_01			
<b>SL</b>	7560592_01					
<b>SP</b>	7560430_01					
<b>SW</b>	7560593_01					
<b>Encore HD</b>	Encore HD Mobile Powder Coating System - Quick Start Guide -	<b>CH</b>	7560441_01	OP	(317102) or (317107)	<b>EN - 1608259_02 - Issued 02/16</b>
		<b>CZ</b>	7560731_02			
		<b>DA</b>	7560732_02			
		<b>DU</b>	7560733_02			
		<b>FI</b>	7560734_02			
		<b>FR</b>	7560735_02			
		<b>GE</b>	7560439_02			
		<b>HU</b>	7580463_02			
		<b>IT</b>	7560736_02			
		<b>JA</b>	7560442_01			
		<b>PL</b>	7560438_02			
		<b>PO</b>	7560737_02			
		<b>RO</b>	7560738_02			
		<b>RU</b>	7560739_02			
<b>SL</b>	7560740_02					
<b>SP</b>	7560440_02					
<b>SW</b>	7560741_02					

## Nordson Finishing Products (sorted by Product Title)

C-2 - 8

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Encore HD</b>	Encore HD Powder Spray System with Prodigy Color-on-Demand	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SL</b> <b>SP</b> <b>SW</b> <b>TU</b>	7192614_04 7192615_01 7192616_01 7192617_01 7192638_04 7192618_04 7192695_01 7192619_01 7192620_01 7192621_01 7192622_04 7192623_01 7192659_04 7192634_01 7192656_01	MA	(317102) or (317107)	<b>EN - 1605396_04 - Issued 05/18</b>
<b>Encore HD</b>	Encore HD Powder Spray System with Prodigy Color-on-Demand - OP Card	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SL</b> <b>SP</b> <b>SW</b> <b>TU</b>	7192624_01 7192625_01 7192626_01 7192627_01 7192639_01 7192628_01 7192696_01 7192629_01 7192630_01 7192631_01 7192632_01 7192633_01 7192660_01 7192635_01 7192657_01	OP	(317102) or (317107)	<b>EN - 1605548_01 - Issued 03/14</b>



## Nordson Finishing Products (sorted by Product Title)

C-2 - 9

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Encore HD</b>	Encore HD Powder Spray System with Prodigy Pump Cabinet	<b>CZ DA DU FI FR GE IT PL PO RO RU SL SP SW TU</b>	7192401_02 7192435_02 7192460_02 7192413_02 7192506_02 7192379_02 7192407_02 7192473_02 7192541_02 7192384_02 7192373_02 7192466_02 7192389_02 7192423_02 7192479_02	MA	(317102) or (317107)	<b>EN - 1604979_02 - Issued 02/14</b>
<b>Encore HD</b>	Encore HD Powder Spray System with Prodigy Pump Cabinet - OP Card	<b>CZ DA DU FI FR GE IT PL PO RO RU SL SP SW TU</b>	7192402_01 7192436_01 7192461_01 7192414_01 7192507_01 7192380_01 7192408_01 7192474_01 7192542_01 7192385_01 7192374_01 7192467_01 7192390_01 7192424_01 7192480_01	OP	(317102) or (317107)	<b>EN - 1604871_01 - Issued 01/14</b>
<b>Encore HD</b>	Encore HD Powder Spray System with Pump Cabinet	<b>CZ DU</b>	7580951_02 7593415_03	MA	(317102) or (317107)	<b>EN - 1612632_03 - Issued 12/18</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 10

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Encore HD</b>	Encore HD Pump	<b>CH</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SL</b> <b>SP</b> <b>SW</b> <b>TU</b>	7580518_01 7580519_02 7580520_01 7580521_02 7580522_01 7580523_01 7580524_01 7593164_02 7580525_02 7580526_01 7580527_01 7580528_01 7580529_01 7580530_01 7580531_01 7580532_01 7580533_01 7580686_02	MA	(317102) or (317107)	<b>EN - 1605708_03 - Issued 06/19</b>
<b>Encore HD</b>	Encore HD Pump Cabinet	<b>GE</b>	7593573_01	MA	(317102) or (317107)	<b>EN - 1614813_01 - Issued 03/19</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 11

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Encore HD</b>	Encore HD Pump Control Unit and Power Supply	<b>CH</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SL</b> <b>SP</b> <b>SW</b> <b>TU</b>	7560436_01 7560545_01 7560595_01 7560577_06 7560596_01 7560578_01 7560434_02 7580461_02 7560548_01 7560437_02 7560433_01 7560599_01 7560579_01 7560580_01 7560597_01 7560435_01 7560598_01 7560581_01	MA	(317102) or (317107)	<b>EN - 1606783_06 - Issued 06/19</b>
<b>Encore HD</b>	Encore HD Pump - Parts Poster	<b>CH</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SL</b> <b>SP</b> <b>SW</b>	7580534_01 7580535_01 7580536_01 7580537_01 7580538_01 7580539_01 7580540_01 7580541_01 7580542_01 7580543_01 7580544_01 7580545_01 7580546_01 7580547_01 7580548_01 7580549_01	IN	(317102) or (317107)	<b>EN - 1605710_01 - Issued 05/18</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 12

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Encore HD</b>	External Diffuser for Encore HD Automatic Spray Guns	<b>CZ</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>RU</b> <b>SP</b> <b>SW</b>	7580987_03 7593102_03 7580988_03 7580395_01 7560550_01 7580971_03 7593103_03 7560678_01	IN	(317102) or (317107)	<b>EN - 1606973_03 - Issued 07/17</b>
<b>Encore HD/ XT</b>	Encore HD and XT Manual Powder Spray System Controller  (Titel version_01: Encore HD Manual Powder Spray System Controller)	<b>CH</b> <b>CR</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>LI</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SL</b> <b>SP</b> <b>SW</b> <b>TU</b>	7560452_04 7580009_04 7192400_05 7192434_04 7192459_05 7192412_04 7192505_05 7192378_05 7580462_04 7192406_04 7560453_04 7580890_04 7192472_04 7192540_04 7192383_04 7192372_05 7192465_04 7192388_05 7192422_04 7192478_01	MA	(317102) or (317107)	<b>EN - 1604870_05 - Issued 04/18</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 13

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Encore HD/ iControl</b>	Encore HD iControl System Hardware Manual ( Installation, Troubleshooting, Repair, Parts )	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>SW</b> <b>TU</b>	7192649_02 7560403_02 7179665_02 7560405_02 7560404_02 7192133_02 7560171_02 7560406_02 7560407_02 7192143_02 7192228_02 7192122_02 7560408_02 7560409_02	MA	(317102) or (317107)	<b>EN - 1603054_02 - Issued 04/15</b>
<b>Encore HD/ iControl</b>	Encore HD iControl 2 Integrated Control System (Installation, Troubleshooting, Repair)	<b>IT</b> <b>SP</b>	7593190_02 7580949_01	MA	(317102) or (317107)	<b>EN - 1609758_02 - Issued 08/18</b>
<b>Encore/ iControl</b>	Standard Encore iControl Console Hardware Manual	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7169909A02 7179582A02 7179798A02 7179937A02 7169973A02 7179488A02 7179942A02 7169554A02 7179341A02 7169520A02 7169795A02 7169435A02 7179807A02	MA	(317102) or (317107)	<b>EN - 1105821_04 - Issued 05/15</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 14

### U.S. Powder

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Encore/ iControl</b>	Encore iControl 2 Integrated Control System (Installation, Troubleshooting, Repair)	<b>CZ DU FR GE IT PL RO RU SP SW</b>	7560321_12 7560324_12 7560326_12 7560322_12 7560320_12 7560325_12 7192946_12 7192953_12 7560323_12 7593135_12	MA	(317102) or (317107)	<b>EN - 1603638_13 - Issued 07/19</b>
<b>Encore LT</b>	Encore LT Air Filter Kit	<b>FR SP</b>	7169728_01 7169685_01	IN	(317102) or (317107)	<b>EN - 1600565_01 - Issued 09/11</b>
<b>Encore LT</b>	Encore LT Automatic Powder Spray Controllers	<b>CZ FI FR GE IT PL RU SP TU</b>	7580993_01 7560940_01 7192689_01 7192852_01 7593145_01 7580370_01 7580091_01 7580999_01 7192599_01	MA	(317102) or (317107)	<b>EN - 1604858_01 - Issued 11/13</b>
<b>Encore LT</b>	Encore LT Automatic Powder Spray Systems	<b>CZ FR GE RU SP TU</b>	7580985_01 7593100_01 7580986_01 7580970_01 7593101_01 7192600_01	OP	(317102) or (317107)	<b>EN - 1604860_01 - Issued 11/13</b>
<b>Encore LT</b>	Encore LT Main Control Board Replacement	<b>FR IT PL SP</b>	7169729 7593146 7169865 7169686	IN	(317102) or (317107)	<b>EN - 1108327 - Issued 06/11</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 15

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Encore LT</b>	Encore LT Manual Powder Spray Systems	<b>CH</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>ES</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>LI</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SL</b> <b>SP</b> <b>SW</b> <b>TU</b>	7593213_16 7580171_16 7580172_11 7580173_11 7580174_11 7580175_11 7580176_16 7580177_16 7580588_11 7580178_11 7580179_11 7580180_11 7580181_11 7580182_11 7580183_16 7192801_11 7580184_16 7580185_11 7192601_11	MA	(317102) or (317107)	<b>EN - 1604857_16 - Issued 07/18</b>
<b>Encore LT</b>	Encore LT Manual Powder Spray Systems	<b>HU</b> <b>SL</b> <b>TU</b>	7580589_01 7192802_01 7192602_01	OP	(317102) or (317107)	<b>EN - 1604859_01 - Issued 11/13</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 16

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Encore LT</b>	Encore LT Manual Powder Spray Systems Quick Start Guide	<b>CZ</b>	7580199_03	OP	(317102) or (317107)	<b>EN - 1601161_03 - Issued 05/17</b>
		<b>DA</b>	7580200_03			
		<b>DU</b>	7580201_03			
		<b>ES</b>	7580202_0			
		<b>FI</b>	7580203_03			
		<b>FR</b>	7580204_03			
		<b>GE</b>	7580205_03			
		<b>HU</b>	7580590_03*			
		<b>IT</b>	7580206_03			
		<b>LI</b>	7580207_03			
		<b>PL</b>	7580208_03			
		<b>PO</b>	7580209_03			
		<b>RO</b>	7580210_03			
		<b>RU</b>	7580211_03			
		<b>SL</b>	7192820_03			
<b>SP</b>	7580212_03					
<b>SW</b>	7580213_03					
<b>TU</b>	7580214_03					
<b>Encore PE</b>	Encore Automatic Porcelain Enamel Powder Spray Gun	<b>CZ</b>	7179893_04	MA	(317102) or (317107)	<b>EN - 1601753_05 - Issued 08/16</b>
		<b>DA</b>	7179985_01			
		<b>DU</b>	7179795_01			
		<b>FI</b>	7179934_05			
		<b>FR</b>	7192692_05			
		<b>GE</b>	7179485_05			
		<b>IT</b>	7179939_05			
		<b>PL</b>	7179792_05			
		<b>RO</b>	7560341_04			
		<b>RU</b>	7179799_04			
		<b>SL</b>	7179735_01			
		<b>SP</b>	7179822_04			
		<b>SW</b>	7179804_01			
		<b>TU</b>	7560340_04			



## Nordson Finishing Products (sorted by Product Title)

C-2 - 17

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Encore PE</b>	Encore Automatic Porcelain Enamel Powder Spray Gun - Parts Poster	<b>CZ</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>TU</b>	7560349_03 7560350_04 7560351_03 7593185_04 7580369_04 7560355_03 7560352_03 7560353_03 7560354_03	IN	(317102) or (317107)	<b>EN - 1602223_04 - Issued 08/16</b>
<b>Encore PE</b>	Encore Manual Porcelain Enamel Powder Spray Gun and Controller	<b>GE</b>	7192349_01	MA	(317102) or (317107)	<b>EN - 1602221_01 - Issued 10/12</b>
<b>Encore PE</b>	Encore Manual Porcelain Enamel Powder Spray Systems	<b>IT</b>	7593402_02	MA	(317102) or (317107)	<b>EN - 1612500_02 - Issued 07/18</b>
<b>Encore PE</b>	Encore Porcelain Enamel Powder Pump	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>RU</b> <b>SP</b> <b>SW</b>	7179894_01 7179986_01 7179796_01 7179935_01 7192691_01 7179486_01 7179940_01 7179793_01 7179800_01 7179852_01 7179805_01	IN	(317102) or (317107)	<b>EN - 1602273_01 - Issued 09/12</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 18

### U.S. Powder

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Encore PE</b>	Ion Collector Kit - Encore Automatic PE Gun	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>RU</b> <b>SP</b> <b>SW</b>	7179895_01 7179987_01 7179797_01 7179936_01 7179487_01 7179941_01 7179794_01 7179801_01 7179879_01 7179806_01	IN	(317102) or (317107)	<b>EN - 1602228_01 - Issued 09/12</b>
<b>Encore PE/HD</b>	Encore Automatic Porcelain Enamel HD Powder Spray Gun	<b>CZ</b> <b>FR</b> <b>GE</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>TU</b>	7560342_03 7560343_03 7560344_03 7560348_03 7560345_03 7560346_03 7560347_03	MA	(317102) or (317107)	<b>EN - 1605438_04 - Issued 08/16</b>
<b>Encore PE/HD</b>	Encore Automatic Porcelain Enamel HD Powder Spray Gun - Parts Poster	<b>CZ</b> <b>FR</b> <b>GE</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>TU</b>	7560356_02 7560357_02 7560358_02 7560362_02 7560359_02 7560360_02 7560361_02	IN	(317102) or (317107)	<b>EN - 1605678_03 - Issued 08/16</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 19

### U.S. Powder

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Encore XT</b>	Encore XT Manual Powder Spray Systems	<b>CZ</b> <b>DU</b> <b>DA</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b> <b>TU</b>	7192319_03 7192327_03 7192330_03 7192325_03 7192334_03 7179731_01 7192326_03 7192351_03 7192324_03 7192265_03 7192328_03 7192329_03 7192355_03	MA	(317102) or (317107)	<b>EN - 1603227_17 - Issued 07/18</b>
--	ESD Grounding Block Kit Installation	<b>CZ</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b> <b>TU</b>	7560530A 7169780A 7169802A 7169773A 7146573A 7593168A 7169809A 7169813A 7169769A 7169776A 7169748A 7169821A 7560787A	IN	(317102) or (317107)	<b>EN - 1069022A - Issued 03/06</b>
<b>38-4</b>	Excel 2000 Series Powder Coating System	<b>SP</b>	317133G	MA	(317102) or (317107)	<b>EN - 106641H03 - Issued 04/09</b>
<b>33-13</b>	EXP-100 Electrostatic Power Unit	<b>CZ</b> <b>GE</b> <b>HU</b>	7179599E 405118C 7119741E	MA	(317102) or (317107)	<b>EN - 108242_03 - Issued 05/16</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 20

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	External Gun Blow Off Kit	<b>CZ</b> <b>FR</b> <b>GE</b> <b>RU</b> <b>SP</b> <b>TU</b>	7580655_02 7593104_02 7580991_02 7580972_02 7593105_02 7560788_02	IN	(317102) or (317107)	<b>EN - 1603264_02 - Issued 04/15</b>
--	Global Oscillator	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7169694_01 7169764_01 7169738_01 7169708_01 7169740_01 7169688_01 7169714_01 7169761_03 7169715_01 7169703_01 7169702_01 7169710_03 7169720_01		(317102) or (317107)	<b>EN - 1106313_03 - Issued 04/12</b>
--	HDLV 55-Gallon Powder Drum Unloader  (Title version A02: HDLV 55-Gallon Powder Drum Dolly)	<b>CZ</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b> <b>TU</b>	7156725_05 7169781A04 7169803A04 7169223_05 7169230_05 7169810A04 7146996A02 7169770A04 7135937_05 7169747_05 7169822A04 7192825A04	IN	(317102) or (317107)	<b>EN - 1073133_05 - Issued 04/15</b>
<b>32-15</b>	High Flow and 100 PLUS FB Powder Pumps	<b>GE</b> <b>HU</b>	464817C 7119743C	IN	(317102) or (317107)	<b>EN - 107987C - Issued 02/97</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 21

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>38-11</b>	Horizon 200/400 Powder Coating System	<b>IT</b> <b>PO</b> <b>RU</b>	407426A 213357D 403 246A	MA	(317102) or (317107)	<b>EN - 106913_04 - Issued 04/19</b>
<b>iControl</b>	iControl Integrated Control System OP	<b>BU</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>HU</b> <b>IT</b> <b>LI</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SE</b> <b>SP</b> <b>SW</b> <b>TU</b>	7105628D 7105145_04 7105146_04 7105147_04 7156521_04 7105148_04 7105149_04 7105627D 7119642E 7105150_04 7156873F 7105512_04 7179330_04 7179707_04 7105154_04 7146583F 397851_04 7105151_04 7560410_04	OP	(317102) or (317107)	<b>EN - 1024758_04 - Issued 04/13</b>
<b>iControl</b>	iControl Standard Console Hardware Manual ( Installation, Troubleshooting, Repair, Parts )	<b>GE</b> <b>PO</b> <b>SP</b>	7580157_04 7169298A 7169367A	MA	317103) or (317106)	<b>EN - 1105779_04 - Issued 09/14</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 22

### U.S. Powder

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>iControl</b>	iControl Operator Interface (Configuration, Preset Setup, Operation)	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>GE</b> <b>IT</b> <b>LI</b> <b>PL</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7146203C03 7135495C02 7135463C02 7156522C03 7146674C02 7119519C03 7156872C05 7146656C02 7146054C02 7135801_06 7135484C02 7146315C02	MA	(317102) or (317107)	<b>EN - 1056418_06 - Issued 04/13</b>
<b>iControl</b>	iControl Configuration Guide	<b>CZ</b> <b>FI</b> <b>GE</b> <b>IT</b> <b>LI</b> <b>SP</b> <b>SW</b>	7146203-CG 7156522-CG 7146674-CG 7119519-CG 7156872-CG 7135484-CG 7146315-CG	MA	(317102) or (317107)	<b>EN - 1056418-CG06 - Issued 04/13</b>
<b>iControl</b>	Standard iControl Power Supply Kit	<b>CZ</b> <b>GE</b> <b>RU</b> <b>SP</b>	7192834A 7192823A 7192827A 7192842A	IN	(317102) or (317107)	<b>EN - 1107150A - Issued 06/11</b>
<b>iControl/ Prodigy</b>	iControl Prodigy Console Hardware Manual ( Installation, Troubleshooting, Repair, Parts )	<b>PO</b>	7179437A02	MA	(317103) or (317106)	<b>EN - 1105820A02 - Issued 09/14</b>
<b>31-31B</b>	Ion Collector Kits for Automatic Guns (Versa-Spray + Versa-Spray II)	<b>IT</b>	407430A	IN	(317102) or (317107)	<b>EN - 108887B - Issued 03/03</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 23

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Manual Horizontal In/Out Positioner	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7169441A 7169509A 7169458A 7169589A 7169491A 7169488A 7169461A 7169348A 7169451A 7169506A 7169411A 7169448A 7169446A	IN	(317102) or (317107)	<b>EN - 1104688A - Issued 01/11</b>
<b>32-35</b>	Metric Porcelain Enamel Powder Pump	<b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>RU</b> <b>SP</b> <b>SW</b> <b>TU</b>	7119815 <b>D</b> 412613 <b>B</b> 409116 <b>B</b> 458006 <b>D</b> 458401 <b>D</b> 7135185 <b>D</b> 412647 <b>B</b> 7105132 <b>D</b> 7135713 <b>D</b>	IN	(317102) or (317107)	<b>EN - 106813D - Issued 04/99</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 24

### U.S. Powder

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
32-14	Metric Powder Transfer Pump	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>LI</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>SW</b> <b>TU</b>	7560033C 7105421C 7179664C 7156584C 7169905C 412612C 407425C 7169113C 7156196C 213241C 7169453C 7105363C 412646C 7146531C 7192944C	IN	(317102) or (317107)	<b>EN - 106702C - Issued 03/03</b>
32-12	Metric Standard and Low-Flow Powder Feed Pumps	<b>DA</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>GR</b> <b>PO</b> <b>RU</b> <b>SK</b> <b>SP</b> <b>SW</b>	7192783E 7156604E 7135613E 412717B 409298A 7146761E 7105994D 7105364E 7156506E 412690E 7146253E	IN	(317102) or (317107)	<b>EN - 106699E - Issued 08/05</b>
32-38	Modular Powder Feed Pumps	<b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>SP</b> <b>SW</b>	409115B 213596E 213630H 213025H 409010H 409341H 409435H 7105806H 458324H 213617E	IN MA IN IN IN IN IN IN IN MA	(317102) or (317107)	<b>EN - 107128H - Issued 05/04</b> <b>Rev. E = Manual</b> <b>Rev. H = Instructions</b>



## Nordson Finishing Products (sorted by Product Title)

C-2 - 25

### U.S. Powder

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	NHR-X-X Encore Feed Hoppers	<b>CZ</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>RU</b> <b>SP</b>	7580994_01 7593416_01 7593108_01 7580221_01 7580974_01 7593109_01	IN	(317102) or (317107)	<b>EN - 1609826_01 - Issued 10/16</b>
--	NHR-X-X Feed Hoppers	<b>CZ</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7135751A 7156605A 7169979A 7135882A 7146562A 7156807A 7135489A 7192144A 7146866A 7135494A 7146530A	IN	(317102) or (317107)	<b>EN - 1062942_04 - Issued 10/16</b>
--	NHR-18-150 Powder Feed Hopper	<b>FR</b> <b>HU</b> <b>SP</b> <b>TU</b>	7192690A03 7156524A03 7560618A03 7192603A03	IN	(317102) or (317107)	<b>EN - 1080413A03 - Issued 02/09</b>
--	NHR-25 Feed Hopper with Agitator	<b>GE</b>	7156410A	IN	(317102) or (317107)	<b>EN - 1092140_02 - Issued 02/16</b>
<b>34-36</b>	Non-Loading kV Meter Kit	<b>IT</b> <b>SP</b>	315751A 7135910 <b>E02</b>	IN	(317102) or (317107)	<b>EN - 107004E02 - Issued 07/07</b>
--	Nordson Automatic Spray Gun Support Kits	<b>CZ</b> <b>FR</b> <b>GE</b> <b>RU</b> <b>SP</b>	7580995A02 7593110A02 7169344A02 7580975A02 7593111A02	MA	(317102) or (317107)	<b>EN - 1104183A02 - Issued 01/11</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 26

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Nordson Belt-Drive Horizontal In/Out Positioner	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7169440_02 7169508_02 7169457_02 7169588_02 7169490_02 7169345_02 7169460_02 7169418_02 7169450_02 7169502_02 7169484_02 7169447_02 7169445_02	MA	(317102) or (317107)	<b>EN - 7750171_03 - Issued 10/12</b>
--	Nordson Extruded Automatic Spray Gun Support Kits	<b>SP</b>	7192608_01	MA	(317102) or (317107)	<b>EN - 1604216_02 - Issued 08/14</b>
--	Nordson NIO2 In/Out Positioner	<b>SP</b>	7192609_01	MA	(317102) or (317107)	<b>EN - 1603770_02 - Issued 05/16</b>
<b>31-29D</b>	Nozzle Extension Installation for Versa-Spray and Versa-Spray II Manual Guns used with Versa-Spray II Control Units	<b>GE</b> <b>IT</b>	315757B 315752B	IN	(317102) or (317107)	<b>EN - 108861B - Issued 10/95</b>
<b>31-18</b>	NPE-LF10 and NPE-HF10 Powder Spray Guns	<b>CZ</b> <b>FR</b> <b>GE</b> <b>HU</b>	7179600C 213814C 317196C 7119742C	MA	(317102) or (317107)	<b>EN - 108191C - Issued 06/03</b>
--	NV02 Oscillator	<b>SP</b>	7192610_01	MA	(317102) or (317107)	<b>EN - 1602413_02 - Issued 06/18</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 27

### U.S. Powder

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	NVR-Series Vertical Reciprocators	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7169337_02 7169507_02 7169456_02 7169613_02 7169332_02 7169343_02 7169459_02 7169318_02 7169449_02 7169469_02 7169331_02 7169330_02 7169444_02	MA	(317102) or (317107)	<b>EN - 1098602_02 - Issued 06/11</b>
--	Optional Nozzles for Versa-Spray and Versa-Spray II Guns	<b>FI</b> <b>HU</b> <b>IT</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SK</b>	7156740A 7105816A 397936A 7560912A 7119573A 7105508A 7156512A	IN	(317102) or (317107)	<b>EN - 1037936A - Issued 03/03</b>
--	Pattern Adjuster for Encore Lance Assemblies	<b>FR</b> <b>SP</b>	7169732A 7169689A	IN	(317102) or (317107)	<b>EN - 1100013A - Issued 01/10</b>
<b>32-39</b>	Porcelain Powder Transfer Pump with Stainless Steel Tube Adapter	<b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>RU</b> <b>SW</b> <b>TU</b>	7119816E 409299A 458473C 458005C 7135184E 7105133E 7135714E	IN	(317102) or (317107)	<b>EN - 229784E - Issued 05/02</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 28

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>32-17</b>	Powder Transfer Pump	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	397341B 315934B 213591B 290839B 397008B 409485B 412604B 458045B 7105362 <b>C</b> 397676 <b>C</b> 213879B	IN	(317102) or (317107)	<b>EN - 108117C - Issued 03/03</b>
<b>34-25</b>	Powder Tubings, Fittings and Miscellaneous Accessories	<b>SP</b>	213344D	IN	(317102) or (317107)	<b>EN - 108662D - Issued 10/99</b>
<b>Prodigy</b>	Prodigy Automatic Tube-Mount Gun Clap	<b>FI</b>	7156776A02	IN	(317102) or (317107)	<b>EN - 1054549A02 - Issued 06/10</b>
<b>Prodigy</b>	Prodigy Automatic Powder Spray Guns	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>LI</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7146755B05 7135497B04 7135467B04 7156777B05 7135795B04 7146004B04 7146569B04 7169115B05 7146642B05 7179349 <b>B07</b> 7146055B04 7135889B04 7135642B04 7146468B04	MA	(317102) or (317107)	<b>EN - 1054075B07 - Issued 09/10</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 29

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Prodigy</b>	Prodigy Powder Port Feed Center ( Title version A: Prodigy Powder Port )	<b>CZ</b> <b>DA</b> <b>DU</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>RU</b> <b>SP</b> <b>SW</b>	7146753A03 7135498A 7135379A 7146776A03 7146563A03 7146655A03 7135891A03 7146170A03 7146456A03	MA	(317102) or (317107)	<b>EN - 1056625_07 - Issued 12/11 (US-Version)</b>  <b>(European version: see U. K. Powder)</b>
<b>Prodigy</b>	Prodigy Nozzle Disassembly and Cleaning	<b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SL</b> <b>SP</b> <b>SW</b>	7135469A01 7169029A01 7156988A01 7146783A01 7146570A01 7169095A01 7169007A01 7169072A01 7135671A01 7169086A01 7146528A01	IN	(317102) or (317107)	<b>EN - 1073708A01 - Issued 11/06</b>
<b>Prodigy</b>	Prodigy Spray Gun Nozzles (Parts Poster)	<b>GE</b>	7156593A	IN	(317102) or (317107)	<b>EN - 1079431A - Issued 05/07</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 30

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Prodigy</b>	Prodigy to Encore HD Manual Powder Spray System Upgrade Kit	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SL</b> <b>SP</b> <b>SW</b> <b>TU</b>	7192403_01 7192437_01 7192462_01 7192415_01 7192508_01 7192381_01 7192409_01 7192475_01 7192543_01 7192386_01 7192375_01 7192468_01 7192391_01 7192425_01 7192481_01	IN	(317102) or (317107)	<b>EN - 1604780_03 - Issued 07/15</b>
<b>Prodigy</b>	Prodigy Mobile Manual Powder Spray System	<b>GE</b>	7156971A	IN	(317102) or (317107)	<b>EN - 1081310A- Issued 03/08</b>
<b>Prodigy</b>	Prodigy Lance Assembly	<b>CZ</b> <b>DU</b> <b>GE</b> <b>FI</b> <b>FR</b> <b>HU</b> <b>IT</b> <b>LI</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SL</b> <b>SP</b> <b>SW</b> <b>TU</b>	7146754A 7169063A 7146781A 7156781A 7146772A 7580399A 7146564A 7169120A 7169093A 7169005A 7169070A 7179734A 7169085A 7146524A 7192826A	IN	(317102) or (317107)	<b>EN - 1084294A - Issued 05/08</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 31

### U.S. Powder

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
Prodigy	Prodigy Mobile Box Unloader System	<b>CZ</b> <b>DU</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>PL</b> <b>RU</b> <b>SP</b>	7580997A 7593418A 7169981A 7156411A 7593169A 7593147A 7169650A 7169796A 7192611A	IN	(317102) or (317107)	<b>EN - 1091202A - Issued 10/08</b>
Prodigy	Prodigy Porcelain Enamel Manual Powder Spray Gun	<b>SL</b>	7169642A	MA	(317102) or (317107)	<b>EN - 1093482_02 - Issued 04/12</b>
Prodigy	Prodigy/ Sure Coat Nozzle Extension	<b>LI</b>	7169117A02	IN	(317102) or (317107)	<b>EN - 1097315A02 - Issued 01/10</b>
Prodigy	Prodigy Robot Gun	<b>GE</b>	7169315A	MA	(317102) or (317107)	<b>EN - 1105518_02 - Issued 03/14</b>
Prodigy	Prodigy Generation II Manual Powder Spray Gun	<b>CZ</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>LI</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7135764A 7169054A04 7156779A04 7156979A04 7146779A02 7146994A02 7169116A04 7146471A02 7156993_06 7146060A02 7135893A 7156341A04 7146459A02	MA	(317102) or (317107)	<b>EN - 1077434_09 - Issued 06/15</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 32

### *U.S. Powder*

<b>EDB</b>	<b>Product Title</b>	<b>Langs.</b>	<b>P/N</b>	<b>Type</b>	<b>Price Category</b>	<b>Notes</b>
<b>Prodigy</b>	Prodigy Generation II Manual Powder Spray Gun - Resistor Replacement Kit -	<b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7169055A 7169018A 7156980A 7156857A 7156890A 7169087A 7156994A 7135903A 7169078A 7146523A	IN	(317102) or (317107)	<b>EN - 1081072A - Issued 09/07</b>
<b>Prodigy</b>	Prodigy Generation II Manual Powder Spray Gun - Lance Extensions -	<b>RO</b>	7192148_01	IN	(317102) or (317107)	<b>EN - 1603191_01 - Issued 02/13</b>
<b>Prodigy</b>	Prodigy Generation III Color-on-Demand System	<b>GE</b>	7169382A02	MA	(317102) or (317107)	<b>EN - 1102101_04 - Issued 05/13</b>
<b>Prodigy</b>	Prodigy Generation III Color-on-Demand System OP Card	<b>GE</b>	7169383A04	OP	(317102) or (317107)	<b>EN - 1081751_06 - Issued 05/13</b>
<b>Prodigy</b>	Prodigy HDLV Pump Fluidizing Tube Replacement	<b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SL</b> <b>SP</b> <b>SW</b>	7135595A 7169059 <b>A02</b> 7169022 <b>A02</b> 7119047A 7119106A 7119321A 7119086A 7169089 <b>A02</b> 7169012 <b>A02</b> 7135900A 7135665 <b>A02</b> 7119213A 7146526A02	IN	(317102) or (317107)	<b>EN - 1058016A02 - Issued 09/07</b>



## Nordson Finishing Products (sorted by Product Title)

C-2 - 33

### U.S. Powder

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Prodigy</b>	Prodigy HDLV Pump Pinch Valve Replacement	<b>DA</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>RU</b> <b>SL</b> <b>SP</b> <b>SW</b>	7135596A 7119048A 7119107A 7119322A 7119087A02 7135901A 7135666A03 7119214A 7146527A02	IN	(317102) or (317107)	<b>EN - 1053279A03 - Issued 08/09</b>
<b>Prodigy</b>	Prodigy HDLV Pump Circuit Board Replacement	<b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>RU</b> <b>SL</b> <b>SP</b> <b>SW</b>	7135597B 7169058B02 7169021B02 7156983B02 7156859B02 7156885B02 7156997B02 7135909B 7135664B 7169081B02 7169046B02	IN	(317102) or (317107)	<b>EN - 1058046B02 - Issued 11/08</b>
<b>Prodigy</b>	Prodigy High-Capacity HDLV Pump Fluidizing Tube Replacement	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>IT</b> <b>LI</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b> <b>TU</b>	7156724A02 7135598A 7135924A 7169026A02 7156986A02 7146784A02 7146760A02 7146567A02 7169123A02 7169091A02 7169003A02 7135908A 7169083A02 7146525A02 7192674A02	IN	(317102) or (317107)	<b>EN - 1063413_03 - Issued 09/16</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 34

### U.S. Powder

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Prodigy</b>	Prodigy High-Capacity HDLV Pump Pinch Valve Replacement	<b>CZ DA DU FI FR GE GR IT LI PL PO RU SP SW TU</b>	7156723 <b>A02</b> 7135599A 7135923A 7169027 <b>A02</b> 7156987 <b>A02</b> 7146785A 7146759A 7146568A 7169124 <b>A02</b> 7169092 <b>A02</b> 7169004 <b>A02</b> 7135907A 7169084 <b>A02</b> 7146529A 7192673 <b>A02</b>	IN	(317102) or (317107)	<b>EN - 1063437A02 - Issued 08/09</b>
<b>Prodigy</b>	Prodigy HDLV Pump Lance Powder Tube Fitting Kit	<b>CZ DU FI FR GE IT PL PO RU SP SW</b>	7156087A 7169060A 7169023A 7156984A 7156860A 7156886A 7169090A 7156998A 7169069A 7169082A 7169047A	IN	(317102) or (317107)	<b>EN - 1071378A - Issued 06/06</b>
<b>Prodigy</b>	Prodigy HDLV Transfer Pump Station	<b>CZ FR GE IT RU SP TU</b>	7580996A03 7593112A03 7192134A03 7560172A03 7580976A03 7593113A03 7192671A03	IN	(317102) or (317107)	<b>EN - 1073134A03 - Issued 08/09</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 35

### U.S. Powder

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Prodigy</b>	Prodigy Generation II HDLV Manual System Installation Instructions	<b>CZ</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7135762A 7169056A 7169019A 7156981A 7156858A 7156894A 7169088A 7156995A 7135904A 7169079A 7169044A	IN	(317102) or (317107)	<b>EN - 1081707A - Issued 09/07</b>
<b>Prodigy</b>	Prodigy Generation II High-Capacity HDLV Powder Transfer Pump	<b>CH</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>LI</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SL</b> <b>SP</b> <b>SW</b> <b>TU</b>	7169398A04 7156722_08 7560536A04 7179661A04 7156586A03 7169904_08 7169346_08 7169537_08 7560576A04 7169122A03 7156775A03 7156846A04 7169454A04 7169075_08 7179732A04 7156340_08 7156809A04 7192672A04	MA	(317102) or (317107)	<b>EN - 1092270_08 - Issued 04/18</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 36

### U.S. Powder

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Prodigy</b>	Prodigy HDLV System Troubleshooting - Generation III (Rev. A - A03: Generation II)	<b>CZ</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7135776A 7156847A03 7156848A03 7156864A03 7146672A 7146671A 7146621A 7156865A04 7156863A04 7156849A03 7146519A	IN	(317102) or (317107)	<b>EN - 1081071_05 - Issued 03/16</b>
<b>Prodigy</b>	Prodigy Generation II HDLV Pump, Pump Manifold and Circuit Board  (Title 08 -10: Prodigy Generation III HDLV Pump, Pump Manifold and Circuit Board)  (Title - A06: Prodigy HDLV Pump Generation II, Pump Manifold and Circuit Board)  (Title A - A04: Prodigy HDLV Pump Generation 2)	<b>CR</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>LI</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SL</b> <b>SP</b> <b>SW</b> <b>TU</b>	7580007_10 7135752_11 7192438_08 7169061_08 7169024_08 7135797_11 7146158_11 7580398_10 7146566_08 7169119A06 7146998_08 7156999_08 7146062_08 7135894_11 7169641_08 7156342_11 7146458_08 7192482_08	MA	(317102) or (317107)	<b>EN - 1081195_11 - Issued 10/18</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 37

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Prodigy</b>	Prodigy Generation III Manual Powder Spray System (Title version A: Prodigy HDLV Manual System Generation III)	<b>CZ DU FI FR GE PL PO RO RU SL SP SW</b>	7179154_02 7179042_02 7179187_02 7179164_02 7179035_02 7179052_02 7179049_02 7192145_03 7179151_02 7169640A 7179161_02 7179157_02	MA	(317102) or (317107)	<b>EN - 1102106_03 - Issued 11/12</b>
<b>Prodigy</b>	Prodigy PLC Gateway Generation III	<b>CZ DU GE IT</b>	7593414_02 7593417_02 7169606A 7560870_02	MA	(317102) or (317107)	<b>EN - 1102107_02 - Issued 12/14</b>
<b>Prodigy</b>	Prodigy Generation III HDLV Manual System Operator's Card	<b>CZ DU FI FR GE PL PO RO RU SP SW</b>	7179155A 7179043A 7179188A 71791655A 7179036A 7179053A 7179050A 7192146A 7179152A 7179162A 7179158A	OP	(317102) or (317107)	<b>EN - 1102109A - Issued 07/10</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 38

### U.S. Powder

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Prodigy</b>	Prodigy Generation III Automatic System HDLV Pump Panel	<b>CZ</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SL</b> <b>SP</b> <b>SW</b> <b>TU</b>	7179156A 7179044A 7179189A 7179166A 7179037A 7580464A 7179054A 7179051A 7192147A 7179153A 7179733A 7179163A 7179159A 7192824A	MAN	(317102) or (317107)	<b>EN - 1102110A - Issued 11/10</b>
--	Pulse Valve Diaphragm Kit	<b>PL</b>	7105782A	IN	(317102) or (317107)	<b>EN - 1038550_02 - Issued 02/13</b>
--	Spectrum Powder Feed Center	<b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b>	7169552A 7169287A 7169505A 7192392_03 7169363A	MA	(317102) or (317107)	<b>EN - 1103292_04 - Issued 04/15</b>
--	Spectrum VT Inline Powder Feed Pump	<b>PO</b> <b>SP</b>	7580948_01 7593582_01	IN	(317102) or (317107)	<b>EN - 1609219_01 - Issued 07/16</b>
--	Spectrum VT Pump Manifold Siphon Block Assembly	<b>SP</b>	7593583_01	IN	(317102) or (317107)	<b>EN - 1609210_01 - Issued 07/16</b>
--	Standard Powder Transfer Pump Kit	<b>RU</b>	7156611C	IN	317102) or (317107)	<b>EN - 108655C - Issued 09/02</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 39

### U.S. Powder

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
31-46	Sure Coat Automatic Powder Spray Gun	CH CZ DA DU FI FR GE GR HU IT PL PO RU SP SW	7169399J03 397423F 397334F 397343F 213798D 397282F 464967J 7105865G 7119643J 464922J 7105249F 397357J03 7105343F 213067J03 213691D	MA	(317102) or (317107)	EN - 334627_05 - Issued 04/16
--	Sure Coat and Prodigy Manual Gun Cable Replacement ( Title Rev. B: Sure Coat Manual Gun Cable Replacement )	DU FI FR GE IT PL PO RU SL SP SW	7169066C03 7169031C03 7156990C03 7146786C03 7156892C03 7169097C03 7169009C03 7135906C03 7135670C03 213342B 7146522C03	IN	(317102) or (317107)	EN - 237393C03 - Issued 09/07
34-40	Sure Coat Manual Gun Lance Extensions	DU FI FR GE IT PL PO RU SP SW	7169067B 7169032B 7156991B 7156862B 7156893B 7169098B 7169010B 7169074B 213343B 7169052B	IN	(317102) or (317107)	EN - 303814B - Issued 03/13

## Nordson Finishing Products (sorted by Product Title)

C-2 - 40

### U.S. Powder

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
37-31	Tribomatic 500 Manual Powder Spray Gun	FI GE IT NO PL SP SW	458101B 412611B 7119782D 409029B 7169215D02 412645B 7105192C	MA	(317102) or (317107)	EN - 237467D02 - Issued 11/07
--	Tribomatic Optional Sprayheads and Nozzles	DA FR IT PL PO SP	7105405A 7135682A 7105730A 7169222A 7105807A 397992A	IN	(317102) or (317107)	EN - 1040999A - Issued 04/03
37-20	Tribomatic II Automatic Powder Spray Gun	CZ FR GE IT PL PO RU SP	7156721F 213339F 412651D 407422C 409483C* 407492E 7105974F 213327E	MA	(317102) or (317107)	EN - 106571F - Issued 10/02 * = not yet translated
--	Tribomatic II Manual Powder Spray Gun	IT	7560141A	MA	(317102) or (317107)	EN - 1098020A - Issued 06/09
37-19	Tribomatic II Powder Pump	CZ DA DU GE IT PO RU SP	7146162B 7105422B 7135925B 7119145B 412843A 458048A 7119849B 458334A	IN IN IN IN MA MA IN MA	(317102) or (317107)	EN - 106570B - Issued 05/01 Rev. A = Manual Rev. B = Instructions



## Nordson Finishing Products (sorted by Product Title)

C-2 - 41

### U.S. Powder

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
37-34	Tribomatic II Extended Automatic Powder Spray Gun	DA FI GE IT SP	7105404B 7105427B 213866B 7105717B 7146156B03	MA	(317102) or (317107)	EN - 334691B03 - Issued 07/06
37-38	Tribomatic II Purgeable Automatic Powder Spray Gun	FR GE IT PL PO SP	7135681A02 213856A 7105718A02 7169221A02 7105805A02 397991A02	MA	(317102) or (317107)	EN - 1014255A02 - Issued 04/03
--	Vantage FCM Booth	SP	7179973A	MA	(317102) or (317107)	EN - 1102582A - Issued 05/11
--	Vantage Individual Powder Spray Gun Controller	CH CZ DA DU ES FI FR GE IT PL PO RO RU SK SP SW	7169400C 7105341A 7105267C 7105288A 7169375C 7105516C 7105356C 7105269C 7105265C 7105575A 7105262C 7135708C 7105488A 7156505C 7105294C 7105291C	MA	(317102) or (317107)	EN - 1044199_04 - Issued 04/15
--	Vantage Manual Electrostatic Porcelain Enamel Powder Spray Gun	RU	7146865A	MA	(317102) or (317107)	EN - 1075735_02 - Issued 04/16

## Nordson Finishing Products (sorted by Product Title)

C-2 - 42

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Vantage Manual Powder Spray Gun	<b>CZ</b> <b>FI</b> <b>FR</b> <b>IT</b> <b>PO</b> <b>RU</b> <b>SP</b>	7135981A 7135760A 7135611A 7135600A 7156433A02 7135826A 7135534A	MA	(317102) or (317107)	<b>EN - 1070278_04 - Issued 04/16</b>
--	Vantage Manual Spray Gun Control Unit	<b>CZ</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PO</b> <b>RU</b> <b>SP</b>	7135982A02 7135761A02 7135612A02 7135539A02 7135601A02 7156434A02 7135827A02 7135535A02	MA	(317102) or (317107)	<b>EN - 1066850_03 - Issued 04/16</b>
--	Vantage Modular Gun Control System	<b>CZ</b> <b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>HU</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>SW</b>	7105342A 7105268A 7105289A 7105517A 7105357A 7105270C 7105950C 7105814B 7105266A 7105576A 7105263A 7119576C 7105489A 7105295C 7105292A	MA	(317102) or (317107)	<b>EN - 1046736_05 - Issued 04/15</b>
--	Vantage RCM Powder Coating Booth	<b>SP</b>	7179974A	MA	(317102) or (317107)	<b>EN - 1030157A - Issued 10/02</b>

## Nordson Finishing Products (sorted by Product Title)

C-2 - 43

### U.S. Powder

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Vantage RCM Powder Coating Booth Installation Instructions	SP	7179975A	In	(317102) or (317107)	EN - 1032841A - Issued 10/02
35-11	Versa-Coat Batch and Conveyor Booths	SP	412817B	MA	(317102) or (317107)	EN - 106535E - Issued 06/01
31-23	Versa-Spray IPS Automatic Electrostatic Porcelain Enamel Powder Spray Gun	DA ES FR GE IT NO PL RU SP SW TU	7192784F02 7169372F02 292920C 292919F02 407479C 413003C 7560641F02 7135182F02 7560144F02 7105131F02 7135690F02	MA	(317102) or (317107)	EN - 106584_03 - Issued 05/16
31-26	Versa-Spray II IPS Automatic Powder Spray Gun	DA DU FI FR GE HU IT PL PO RO RU SK SP SW	315766D 412820E 397970H 213010G 292925D 7105815G 292926G 7119240G 7135505_02 7119572H 7105490H 7156507H 397868G 213618E	MA	(317102) or (317107)	EN - 107016_02 - Issued 05/16

## Nordson Finishing Products (sorted by Product Title)

C-2 - 44

### *U.S. Powder*

EDB	Product Title	Langs.	P/N	Type	Price Category	Notes
33-19	Versa-Spray II IPS 2-Gauge Control Unit	<b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>SP</b> <b>SW</b>	213633C 397968 <b>D</b> 292834C 292835A 292836C 413001B 7119239 <b>D</b> 7119165 <b>D</b> 397860C 213587C	MA	(317102) or (317107)	<b>EN - 106991D - Issued 07/05</b>
--	Vibratory Deck Sieves - 15 in. (380 mm)	<b>RO</b> <b>RU</b> <b>SP</b>	7192947_01 7192954_01 7192291_01	IN	(317102) or (317107)	<b>EN - 1604433_01 - Issued 07/13</b>
--	VO618N Belt-Drive Horizontal In/Out Positioner	<b>PO</b> <b>SP</b>	7169276A 7169342A	IN	(317102) or (317107)	<b>EN - 1058080A - Issued 02/05</b>

## Nordson Finishing Products (sorted by Product Title)

C-3 - 1

### *U.K. / Europe Powder*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	A300 Ultrasonic Sieve	EN	7593637_01	MA	(317102) or (317107)	Is currently being created by Nordson (U.K.) Ltd.
	Afterfilter Generation 5	CZ DA DU EN FI FR GE HU IT LI PL PO RO RU SP SW TU	7146918_05 7560532_05 7179662_05 7146911_05 7156577_05 7156513_05 7146914_05 7593248_05 7146912A 7169110A 7146915A 7179347_05 7169504_05 7146916_05 7146917_05 7146913_05 7192942_05	MA	(317102) or (317107)	Issued 03/18

## Nordson Finishing Products (sorted by Product Title)

C-3 - 2

### *U.K. / Europe Powder*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Afterfilter Generation 5 - Total Control Board	CH CR CZ DA DU EN FI FR GE HU IT LI PL PO RO RU SP SW TU	7593207C 7580010C 7146926A 7560533C 7179663C 7146919_05 7156583C 7156514A 7146922C 7593249C 7146920A 7169111A 7146923A 7179348C 7169503C 7146924A 7146925C 7146921A 7192943C	MA	(317102) or (317107)	<b>Issued 2018</b>
	Big Bag Unloader	CZ DU EN FI FR GE IT PL RU SP SW	7580288_03 7593429_03 7580188_03 7580336_03 7580289_03 7580290_03 7580291_03 7580292_03 7580957_03 7580293_03 7593170_03	MA	(317102) or (317107)	<b>Issued 11/18</b>

## Nordson Finishing Products (sorted by Product Title)

C-3 - 3

### *U.K. / Europe Powder*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	ColorMax Engineered Booth	CH CZ EN FR GE HU PO RO RU SP TU	7593166B 7192648B 7156925_04 7169906B 7169226B 7593167B 7179340B 7192141B 7169826B 7580984B 7593206B	MA	(317102) or (317107)	Issued 09/19
	ColorMax <sup>3</sup>	CH CR CZ DA DU EN FI FR GE HU IT LI PL PO RO RU SP SW TU	7156424A 7580006D 7135647_07 7135632C 7146574C 7135457_07 7135603C 7169977_07 7146708_07 7593250_06 7146746C 7169109A 7146575A 7179345C 7135943A 7135646_07 7135672_07 7146333C 7192941C	MA	(317102) or (317107)	Issued 09/19

## Nordson Finishing Products (sorted by Product Title)

C-3 - 4

### U.K. / Europe Powder

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	ColorMax <sup>3</sup> Colour Change Procedure - Prodigy	EN FI FR GE PO RU SP	7169100A 7169442A 7169983A 7179296A 7179346A 7192230A 7179452A	OP	(317102) or (317107)	<b>Issued 11/10</b>
	Detecting Module MRT 116	EN RU	7156271A 7156272A	MA	(317102) or (317107)	<b>Issued 2008 (Word .docs)</b>
	ECC 701 Electrostatic Cable Coater	CZ DA EN ES FI FR GE IT PL PO RU SK SP SW	7146388C 7192768_04 7146059_06 7169371C 7146175C 7146202_05 7135786_06 7146157_05 7169587_05 7156763_06 7179269_04 7156503B 7146999_04 7146159_04	MA	(317102) or (317107)	<b>Issued 08/16</b> <b>Created by Nordson Engineering GmbH</b> <b>End of Support 10/2020</b>
	ECC 701 Electrostatic Cable Coater - Parts List-	EN	7135883_06	PA	(317102) or (317107)	<b>Issued 12/16</b> <b>Created by Nordson Engineering GmbH</b> <b>End of Support 10/2020</b>



## Nordson Finishing Products (sorted by Product Title)

C-3 - 5

### U.K. / Europe Powder

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	ECC 701 Operator's Card	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>ES</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SK</b> <b>SP</b> <b>SW</b>	7146881A 7146882A 7146880A 7146860A 7169374A 7146883A 7146884A 7146859A 7146885A 7146886A 7146887A 7146879A 7146888A 7156504A 7146878A 7146889A	OP	(317102) or (317107)	<b>Issued 02/09</b> <b>Created by Nordson Engineering GmbH</b> <b>End of Support 10/2020</b>
	ECC 702 Electrostatic Cable Coater	<b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b>	7580223_02 7580227_01 7560959_02 7593183_01 7580367_01	MA	(317102) or (317107)	<b>Issued 05/19</b> <b>Created by Nordson Engineering GmbH</b>
	ECC 702 Electrostatic Cable Coater - Parts List-	<b>EN</b>	7580107_02	PA	(317102) or (317107)	<b>Issued 05/19</b> <b>Created by Nordson Engineering GmbH</b>
	ECC 702 Operator's Card	<b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b>	7580101_01 7580228_01 7580100_01 7593184_01 7580368_01	OP	(317102) or (317107)	<b>Created by Nordson Engineering GmbH</b>

## Nordson Finishing Products (sorted by Product Title)

C-3 - 6

### U.K. / Europe Powder

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	ECC-Compact Electrostatic Cable Coater	EN GE HU IT LA RU	7593223_02 7192931_02 7580967_02 7580925_02 7580135_02 7560807_02	MA	(317102) or (317107)	<b>Issued 05/17</b> <b>Created by Nordson Engineering GmbH</b>
	ECC-Compact Electrostatic Cable Coater - Parts List-	EN	7593625_01	PA	(317102) or (317107)	<b>Issued 12/19</b> <b>Created by Nordson Engineering GmbH</b>
	EcoMax	EN GE	7593428_01 7593476_01	MA	(317102) or (317107)	<b>Issued 07/19</b>
	HDLV Standalone Pump Panel - Encore ( Title Version C: HDLV Standalone Pump Panel Gen III )	CZ EN FI FR GE HU IT PL PO RU SP SW TU	7192117C 7169013_04 7179938C 7169982_04 7169229_04 7580397_04 7179971C 7179444C 7192124C 7192118C 7179892C 7192119C 7593255_04	IN	(317102) or (317107)	<b>Issued 02/18</b>
	Motorized Base Control HQ-612	EN SP	7156273A 7156274A	MA	(317102) or (317107)	<b>Issued 2009 - Word .docs</b>

## Nordson Finishing Products (sorted by Product Title)

C-3 - 7

### *U.K. / Europe Powder*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Nordson MicroMax Booth (Manual Spray Booth)	<b>CZ</b> <b>CR</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>PO</b> <b>RU</b> <b>SL</b> <b>SP</b> <b>SW</b>	7156050J * 7146769_11 7135592_11 213114D 768635_11 213291E 7119293_11 458238A 7119323_11 458261E 7105023_11 447739C 7169550_11 464767_11 213967I	MA	(317102) or (317107)	<b>* = Document and translation is NOT issued by TDLL ! Issued 11/17</b>
	NQCB / NCB Booth Systems	<b>CZ</b> <b>DA</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>LI</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b> <b>TU</b>	7156186C 7135593C 768636E 7119814C 7146685E 7156193E 7192127E 7119196C 7105992C 7105586C 7135674C 7135716C	MA	(317102) or (317107)	<b>Issued 01/13</b>

## Nordson Finishing Products (sorted by Product Title)

C-3 - 8

### *U.K. / Europe Powder*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Oscillator HOF/50	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>PL</b> <b>RU</b> <b>SP</b> <b>SW</b> <b>TU</b>	7560034_02 7560277_02 7560282_02 7192822_02 7560275_02 7560278_02 7560281_02 7560276_02 7560280_02 7560279_02 7560283_02 7560284_02	MA	(317102) or (317107)	<b>Issued 05/16</b>
	PowderPilot HD	<b>CZ</b> <b>DA</b> <b>EN</b> <b>GE</b> <b>HU</b> <b>PL</b> <b>SP</b> <b>TU</b>	7593512D 7593514D 7156953D 7169227D 7593510D 7593616D 7593511D 7593513D	MA	(317102) or (317107)	<b>Issued 03/19</b>
	PowderPilot HD Controls Manual ( Title version _01: PowderPilot HD System Manual )	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>LI</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>SW</b> <b>TU</b>	7192740_01 7560535_01 7580604_02 7192721_02 7192863_01 7560152_01 7192776_01 7580481_02 7593433_02 7580888_02 7560261_01 7192777_02 7192743_01 7560877_01 7192938_01	MA	(317102) or (317107)	<b>Issued 09/17</b>

## Nordson Finishing Products (sorted by Product Title)

C-3 - 9

### *U.K. / Europe Powder*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Reciprocator HF30 V4 / HF80 V4	CH CZ DA DU EN FI FR GE HU IT PL PO RO RU SP SW TU	7593209_04 7179858_04 7192111_02 7192100_02 7179770_04 7179719_02 7192116_04 7192101_04 7580396_04 7593431_04 7192135_0 7580945_04 7192967_02 7179788_04 7179999_04 7192110_02 7192109_02	MA	(317102) or (317107)	<b>Issued 04/16</b>
	Reciprocator Control HQF-02	CZ DU EN FR GE PL RO RU SP	7179859_01 7192272_01 7179783_01 7192227_01 7192315_01 7192322_01 7192318_01 7192316_01 7179657_01	OP	(317102) or (317107)	<b>Issued 06/13</b>
	Rotary Sieve 360 + Hopper	EN FR GE	7580607_01 7593377_01 7593283_01	MA	(317102) or (317107)	<b>Issued 10/18</b>
	Spectrum COD System	EN	7580641_01	MA	(317102) or (317107)	<b>Issued 06/18</b>

## Nordson Finishing Products (sorted by Product Title)

C-3 - 10

### *U.K. / Europe Powder*

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Spectrum HD Powder Feed Center - Generation II -	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>LI</b> <b>PL</b> <b>RO</b> <b>RU</b> <b>SP</b> <b>SW</b> <b>TU</b>	7192917_02 7560534_02 7192914_02 7192568_02 7192898_02 7560151_02 7192913_02 7580400_02 7593434_02 7580889_02 7593617_02 7560260_02 7192912_02 7192910_02 7560878_02 7192940_02	MA	(317102) or (317107)	<b>Issued 05/17</b>
	Spectrum VT Feed Center (EU)	<b>CZ</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>PO</b> <b>RO</b> <b>RU</b> <b>SP</b>	7580980_01 7580470_01 7580982_01 7580981_01 7580599_01 7580947_01 7580562_01 7580968_01 7580983_01	MA	(317102) or (317107)	<b>Issued 01/18</b>
	Tilt Table	<b>EN</b>	7560626_01	MA	(317102) or (317107)	<b>Is currently beeing created by Nordson (U.K.) Ltd.</b>
	Trio Application Control System	<b>CZ</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>RU</b> <b>SP</b>	7580959_01 7580708_01 7580960_01 7580961_01 7580962_01 7580963_01	MA	(317102) or (317107)	<b>Issued 09/18</b>

## Nordson Finishing Products (sorted by Product Title)

C-3 - 11

### U.K. / Europe Powder

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Twin Cyclone	CH CZ DA DU EN FI FR GE HU IT LI PO RU SP SW TU	7593210_08 397894_08 7135349_08 213812_08 768641_08 7156533_08 213987_08 464727_08 7593251_08 464738_08 7169112_08 213975_08 7105590_08 397006_08 213920_08 7192939_08	MA	(317102) or (317107)	<b>Issued 07/19</b>
	Venturi & HDLV - 150L Powder Feed Hopper	EN	7560761_01	MA	(317102) or (317107)	<b>Is currently beeing created by Nordson (U.K.) Ltd.</b>
	Z-Axis HBF	CH CZ DA DU EN FI FR GE HU IT PL PO RO RU SP SW TU	7593208_01 7192548_01 7192519_01 7192525_01 7179832_01 7192532_01 7192526_01 7192492_01 7580401_01 7593432_01 7192522_01 7580946_01 7192968_01 7192450_01 7179629_01 7192524_01 7192521_01	MA	(317102) or (317107)	<b>Issued 05/16</b>

## Nordson UV Products (sorted by Product Title)

D-1-1

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>U.K. Products</b>						
--	6kW Mini Cooler	<b>FR EN GE</b>	7156813A 7119934A 7135790A	IN	(317102) or (317107)	
--	Accelerated Drying System (Sheetcure)	<b>DU</b>	no P/N	MA	(317102) or (317107)	
--	Digital Power Supply DPS 5-U	<b>EN</b>	7135100A	MA	(317102) or (317107)	
--	DropCure UV Lamp Head	<b>FR EN GE</b>	7156812C 7119747C 7135789C	MA	(317102) or (317107)	
--	e-Series	<b>EN FR GE</b>	7146507A 7146771A 7156622A	MA	(317102) or (317107)	
--	ew-Series System	<b>EN GE</b>	7156018A 7156208A	MA	(317102) or (317107)	
--	Ink Mist Extraction Hood	<b>DU NO</b>	no P/N no P/N	MA	(317102) or (317107)	<b>EN source - IM-C01-A</b>
--	MiniCure	<b>EN NO SW</b>	7119745C 7135932C 7135638C	MA	(317102) or (317107)	
--	MaxiCure	<b>EN</b>	7119746A	MA	(317102) or (317107)	



## Nordson UV Products (sorted by Product Title)

D-1-2

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Nordson Cooler Unit	EN GE IT FR PO SP	213000D 213001D 397908C 213711C 397859C 7105487D	MA	(317102) or (317107)	
--	Nordson Drying System	CH DU EN FI FR GE GR IT JA PL PO RO RU SP SW TU	7119406G 7105939G 464978G 7146271G 213710G 464979G 7135272G 397909G 7119401G 7146987G 397855G 7119947G 7119886G 7105486G 7146088G 7105824G	MA	(317102) or (317107)	
<b>Parts Drawings</b>	LS29 I/C	EN	7156414A	PA	(317102) or (317107)	
<b>Parts Drawings</b>	LSX29 I/C	EN	7156415A	PA	(317102) or (317107)	
<b>Parts Drawings</b>	LSX29 EOP-DU	EN	7156416A	PA	(317102) or (317107)	
<b>Parts Drawings</b>	LSX40 I/C	EN	7156417A	PA	(317102) or (317107)	

## Nordson UV Products (sorted by Product Title)

D-1-3

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Parts Drawings</b>	LS40 EOP (Upsweep)	<b>EN</b>	7156418A	PA	(317102) or (317107)	
<b>Parts Drawings</b>	LS40 DU-EOP	<b>EN</b>	7156419A	PA	(317102) or (317107)	
<b>Parts Drawings</b>	LS40 I/C	<b>EN</b>	7156420A	PA	(317102) or (317107)	
--	PU System	<b>EN</b> <b>FR</b> <b>GE</b>	7135102A 7156811A 7135791A	MA	(317102) or (317107)	
--	Spectral Drying Systems - Operating Manual	<b>SP</b>	no P/N	MA	(317102) or (317107)	<b>EN source - Manual 2.1</b>
--	Spectronic NT20 Monochrome Display	<b>DU</b> <b>FR</b> <b>GE</b> <b>SP</b>	no P/N no P/N no P/N no P/N	MA	(317102) or (317107)	<b>EN source - D 122135D</b>
--	Spectronic NT 31 Colour Display	<b>DU</b> <b>FR</b> <b>GE</b> <b>SW</b>	no P/N no P/N no P/N no P/N	MA	(317102) or (317107)	<b>EN source - 12NT31 C</b>
--	Spectronic Operating / Alarm Instructions	<b>FR</b> <b>GE</b>	no P/N no P/N	MA	(317102) or (317107)	<b>EN source - D 0600000</b>
--	Spectronic Operating / Alarm Instructions	<b>FR</b>	no P/N	MA	(317102) or (317107)	<b>EN source - D 122135A</b>

## Nordson UV Products (sorted by Product Title)

D-1-4

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
--	Spectronic 3 Operating Manual for Nordson Dryer	CH DU EN FR GE GR IT JA PO RO RU SP TU	7119407B 7105940B 397431B 397553B 397677B 7135273B 397933B 7119402B 397801B 7119948B 7119887B 7105445B 7105825B	MA	(317102) or (317107)	
--	Spectronic 4 Manual	CH DU EN FI FR GE GR IT JA PL PO RO RU SP SW TU	7135844F 7135845F 7135629F 7146272E 7135846E 7135847E 7135630E 7135842E 7146874C 7146988F 7135848E 7135849E 7135850E 7135851E 7135843E 7135852E	MA	(317102) or (317107)	
--	Ultra-Violet Curing System	PO SP	no P/N 409030A	MA	(317102) or (317107)	<b>EN source - 407467A (av. in EDC)</b>
--	UVED UV Light Emitting Diode	EN	7156629A	MA	(317102) or (317107)	

## Nordson UV Products (sorted by Product Title)

D-1-5

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>U.S. Products</b>						
--	CoolWave Ultraviolet Microwave Applied Curing System with Six-Inch Lamphead	<b>SW</b>	7105076B	MA	(317102) or (317107)	<b>EN - 775361B - Issued 6/03</b>
--	CW306 Lamphead with Unicable	<b>FR GE IT</b>	7119952B 7105088A 7119398B	MA	(317102) or (317107)	<b>EN - 775567B - Issued 5/05</b>
--	Coolwave 306 Lamphead with Unicable	<b>PL PO SP</b>	7179927A03 7169131A03 7169370A03	MA	(317102) or (317107)	<b>EN - 1074167A03 - Issued 11/10</b>
--	CW410 Lamphead with Unicable	<b>FR</b>	7119954A	MA	(317102) or (317107)	<b>EN - 775555A - Issued 5/05</b>
--	CW610 Lamphead	<b>GE</b>	7105087A	MA	(317102) or (317107)	<b>EN - 775560A - Issued 2/04</b>
--	CW610 Lamphead with Unicable	<b>FR GE PL SW</b>	7119480B 7119347A 7119482B 7119356A	MA	(317102) or (317107)	<b>EN - 1061255B - Issued 1/06</b>
--	CW610 Lamphead with Unicable	<b>FR</b>	7560724A02	MA	(317102) or (317107)	<b>EN - 1074165A02 - Issued 11/10</b>
--	CoolWave 2 610 UV Curing System	<b>FR GE IT SK</b>	7593141_01 7593131_01 7593132_01 7593133_01	MA	(317102) or (317107)	<b>EN - 1612563_01 - Issued 12/17</b>
--	MPS306F Power Supply with Unicable	<b>FR GE IT</b>	7119953C 7105086A 7119399C	MA	(3171012)	<b>EN - 775569C - Issued 7/05</b>

## Nordson UV Products (sorted by Product Title)

D-1-6

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
--	MPS306F Power Supply with Unicable	<b>PL</b> <b>PO</b> <b>SP</b>	7179926A 7169132A 7169369A	MA	(3171012)	<b>EN - 1074166A - Issued 06/07</b>
--	MPS610D Power Supply with Dual Cables	<b>GE</b>	7105085A	MA	(317102) or (317107)	<b>EN - 775564B - Issued 02/04</b>
--	MPS610V Power Supply with Unicable	<b>FR</b> <b>GE</b> <b>PL</b> <b>SW</b>	7119481B 7119348B 7119483B 7119357A	MA	(317102) or (317107)	<b>EN - 1061254B - Issued 1/06</b>
--	MPS610V Power Supply with Unicable	<b>FR</b>	7560725A	MA	(317102) or (317107)	<b>EN - 1074164A - Issued 1/07</b>
--	MPS610V Power Supply with Dual Cables	<b>GE</b>	7105084A	MA	(317102) or (317107)	<b>EN - 775562B - Issued 2/04</b>

## Paper and Paperboard Converting

E-1-1

### Nordson Benelux Products ( former Walcom ) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>BRACKETS</b>	Brackets	<b>EN GE</b>	213017A 464847A	MA	(317102) or (317107)	<b>For Nordson internal use ONLY</b>
<b>BRACKETS</b>	Core Winding Bracket 120	<b>EN GE</b>	7179249_01 7179182_01	MA	(317102) or (317107)	
<b>BC 5100</b>	BC 5100 Bar Code Scanner	<b>HU PL</b>	7560488A 7156844A	MA	(317102) or (317107)	<b>EN - 1076483A</b>
<b>CBC 5100</b>	Color Barcode Scanner CBC 5100	<b>CZ DU EN FR GE IT PL RU SP</b>	7169309D 7135444D 7135357D 7135418D 7135024D 7135360D 7169306D 7580667D 7135368D	MA	(317102) or (317107)	
<b>CHAMELEON</b>	Application Head System	<b>CZ DU EN FI FR GE IT JA SP SW</b>	7560663C 458076C 409216C 213177C 447630C 409215C 213233C 7119846C* 213231C 213238C	MA	(317102) or (317107)	<b>* available at Nordson K.K</b>

## Paper and Paperboard Converting

E-1-2

### Nordson Benelux Products ( former Walcom ) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>E 26</b>	Electric Gun Driver	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b> <b>SW</b>	317127A 317128A 317129A 317134A 317144A 317130A	MA	(317102) or (317107)	<b>EN - 187728A (EDB 42-81)</b> <b>No longer valid - replaced by SD Series Electric Gun Driver (see Section B - Hot Melt)</b>
<b>EP48</b>	Spine Gluing with EP 48 and LogiComm - OPERATION	<b>EN</b> <b>GE</b>	7192179_01 7192180_01	IN	(317102) or (317107)	
<b>EP48</b>	Spine Gluing with EP 48 and LogiComm - SETTINGS	<b>EN</b> <b>GE</b>	7192181_01 7192182_01	IN	(317102) or (317107)	
<b>EP48</b>	Spine Gluing with EP 48 (Integrated Systems) - OPERATION	<b>EN</b> <b>GE</b> <b>IT</b>	7192201_01 7192202_01 7560107_01	IN	(317102) or (317107)	
<b>EP48</b>	Spine Gluing with EP 48 (Integrated Systems) - SETTINGS	<b>EN</b> <b>GE</b> <b>IT</b>	7192203_01 7192204_01 7560108_01	IN	(317102) or (317107)	
<b>G-NET</b>	G-NET Verification System	<b>DA</b> <b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>SP</b> <b>SW</b>	464728A 464729A 464730A 464731A 464732A 464733A 464734A 464736A 464737A	MA	(317102) or (317107)	<b>EN - 321226D (56-GNET-MA-01)</b>
<b>LA 22/ LA 44</b>	Glue Guns	<b>GE</b>	397019A	MA	(317102) or (317107)	<b>EN - 321344A</b>

## Paper and Paperboard Converting

E-1-3

### Nordson Benelux Products ( former Walcom ) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LA 100	Level Monitor	CZ EN FR GE IT SP	7169320A 7156393A 7156388A 7156078A 7156389A 7156382A	MA	(317102) or (317107)	
LA 100-C	Level Detection	EN FR GE IT PL SP	7169652_02 7169742_01 7169595_03 7169735_01 7192340_02 7169675_01	MA	(317102) or (317107)	
LA105	Pressurized Adhesive Container	EN	7119459A	MA	(317102) or (317107)	
LA120	Pressurized Adhesive Container	EN	7119460A	MA	(317102) or (317107)	
LA 105/ LA 120/ LA 140	Pressurized Adhesive Container	CZ DU	7169321B 213270A	MA	(317102) or (317107)	<b>Issued 12/04 - OLD!</b>
LA 105/ LA 120/	Pressurized Adhesive Container	EN FR GE IT PL SP	213261_03 213647_03 213207_03 213627_03 7179438_03 213652_03	MA	(317102) or (317107)	<b>Issued 08/18 - NEW!</b>  <b>PL - Issued 01/12</b>



## Paper and Paperboard Converting

E-1-4

### Nordson Benelux Products ( former Walcom ) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LA 300	Piston Pump	CZ DA DU EN FI FR GE GR HU IT JA NO PL PO RU SP SW	7105336_05 7105329_05 7105327_06 7105256_06 7105330_05 7105324_06 7105255_06 7105334_05 7105335_05 7105326_06 7105963A* 7105333_05 7105331_06 7105332_05 7146365_06 7105325_06 7105328_06	MA	(317102) or (317107)	* available at Nordson K.K
LA 302	Pressure Controller	EN GE FI FR	7119797A 7119689A 7135479A 7169376A	MA	(317102) or (317107)	

## Paper and Paperboard Converting

E-1-5

### Nordson Benelux Products ( former Walcom ) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LA 310	Piston Pump	CZ DA DU EN FI FR GE GR HU IT NO PL PO RU SP SW	7156309_04 7156336_04 7156312_05 7156289_05 7156318_04 7156331_05 7156068_05 7156322_04 7156323_04 7156311_05 7156324_04 7156317_05 7156315_04 7156314_05 7156310_05 7156316_05	MA	(317102) or (317107)	Issued 09/2017
LA 320/ LA 320M	Pneumatic Diaphragm Pump	CZ DU FI FR EN GE HU PL	7156758_02 7156756_02 7156782_02 7192350_02 7156751_02 7156689_02 7192545_02 7156771_02	MA	(317102) or (317107)	Issued 09/2017
LA 330	Constant Pressure Controller	DA DU EN FR GE IT NO PO SP	213400A 213360A 213329A 213371A 213306A 213383A 213354A 213346A 213324A	MA	(317102) or (317107)	

E-1-6

## Paper and Paperboard Converting

### Nordson Benelux Products ( former Walcom ) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LA 330-II	Constant Pressure Controller	BU DU EN GE PO SP	7135430C 7156805C 7105264C 397831C 7146392C 7105564C	MA	(317102) or (317107)	<b>Product Obsolescence 22 September 2014, replaced by CPR Pressure Regulator . End of Support effective 30 November 2018.</b>
LA 38X	Pressure Regulators	CZ DU EN FR GE IT JA PL RU SP SW	7146498C 397470C 397377_04 397467C 397376_04 397468C 7105962A* 7119151C 7146366C 397469C 397471C	MA	(317102) or (317107)	<b>Issued 12/2019</b>  * available at Nordson K.K
LA 404	Pattern Control System	CZ DU FR GE IT JA SP	7105819A 397441A 397401A 397463A 397400A 7119847B 397484A	MA	(317102) or (317107)	<b>EN - 1037527B</b>

E-1-7

## Paper and Paperboard Converting

### Nordson Benelux Products ( former Walcom ) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>LA 404-2</b>	Pattern Controller	<b>BU</b> <b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>GR</b> <b>HU</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SK</b> <b>SL</b> <b>SP</b> <b>SW</b> <b>TU</b>	7135434A 7146017A 7146132A 7135120A 7119995A 7146072A 7135076A 7119877A 7146155A 7146080A 7135125A 7135155A 7146100A 7135344A 7146169A 7146131A 7146168A 7146073A 7135128A 7135130A 7146032A	MA	(317102) or (317107)	
<b>LA 600PE</b>	Product Ejection System	<b>CZ</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>SP</b>	7169310A 213816A 213433A 213796A 213443A 213804A 7119152A 213820A	MA	(317102) or (317107)	<b>Product Discontinuation March 6 2018, Product Obsolescence September 1st 2018. No Replacement.</b>

E-1-8

## Paper and Paperboard Converting

### Nordson Benelux Products ( former Walcom ) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LA 725/ LA 725-S	Applicators	DU EN FR GE IT JA PL SP	7192844_02 7179424_02 7179490_02 7179276_02 7179491_02 7192416_01* 7192698_02 7179448_02	MA	(317102) or (317107)	* available at Nordson K.K
LA 820/ LA 820 RC	Liquid Adhesive Guns	CZ DU EN FR GE IT PL SP	7105766B 7105977B 7105681B 7105927B 7105680B 7105931B 7119153B 7105928B	MA	(317102) or (317107)	<b>Product Obsolescence January 1st 2018, replaced by LA 825/ LA 825 RC Applicators.</b>  <b>End of Support effective February 1st 2018. For diverse replacement products depending on specific applications please refer to the End of Support Notice on ADHinfo.com</b>
LA 825/ LA 825 RC	Applicators (Version A: Liquid Adhesive Guns)	CZ DU EN FR GE IT PL RU SP	7156031_02 7156032_02 7156011_02 7156027_02 7156001_02 7156029_02 7156033_02 7156028_02 7156030_02	MA	317102) or (317107)	
LA 844M	LA 844M Electric Applicator	CZ DU GE IT PL RU SK SP	7192780A 7192498A 7179541A02 7146352A02 7192857A02 7560671A02 7560998A02 7192790A02	MA	(317102) or (317107)	EN - 1062950A02

## Paper and Paperboard Converting

E-1-9

### Nordson Benelux Products ( former Walcom ) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
LA 901	Hot Melt Application Head	EN GE	7135939B 7135721B	MA	(317102) or (317107)	
LA 4100	User Interface Specification	DU FR GE IT SP SW	213530A 213605A 213529A 213531A 213528A 213532A	MA	(317102) or (317107)	EN source no P/N (Rev. F 4/02/01)
LA 4100	Pattern Control System	DU FR GE IT SP	213573A 213604A 213584A 213553A 213817A	MA	(317102) or (317107)	EN -1006817A
LA 4400	Pattern Control System	DU FR GE IT SP	213805A 213773A 213770A 213858A 213971A	MA	(317102) or (317107)	EN - 321232D
LA 5091	Hot Melt Glue Sensor	-	-	OP	(317102) or (317107)	EN - 377023A
Labeling	Multi e. dot+ Gun	EN GE	7169558B 7146700B	MA	(317102) or (317107)	
Labeling	Bracket for Multi e. dot+ Guns	GE	7146703A	MA	(317102) or (317107)	
Labeling	Electrical Cabinet Label Application System for Multi e. dot+ or MiniBlue II Guns	EN GE	7169559B 7146701B	MA	(317102) or (317107)	

E-1-10

## Paper and Paperboard Converting

### Nordson Benelux Products ( former Walcom ) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Labeling</b>	Electrical Cabinet Label Gluing System	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>SP</b>	7156330A 7146179A 7156559A 7135653A 7135775A 7192213A 7156329A	MA	(317102) or (317107)	
<b>Labeling</b>	Electrical Cabinet Label Gluing System without Pneumatics	<b>EN</b> <b>GE</b>	7156012A 7156006A	MA	(317102) or (317107)	
<b>Labeling</b>	System Manual e.dot+ Roll Fed Labeling (RFL)	<b>EN</b> <b>GE</b>	7169564B 7146705B	MA	(317102) or (317107)	
<b>LB 101</b>	Pressurized Adhesive Container	<b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>NO</b> <b>PO</b> <b>SP</b> <b>SW</b>	292759D 292758D 315717D 292761D 292760D 292762D 315740D 315718D 292763D 315719D	MA	(317102) or (317107)	
<b>LB 120</b>	Pressurized Adhesive Container	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	292765_05 292764_05 292767_05 292766_05 292768_05 292769_05	MA	(317102) or (317107)	

## Paper and Paperboard Converting

E-1-11

### Nordson Benelux Products ( former Walcom ) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>LB 140</b>	Pressurized Adhesive Container	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	292771_06 292770_06 292773_06 292772_06 292774_06 292775_06	MA	(317102) or (317107)	
<b>LEP 34 S</b>	Electropneumatic Hot Melt Applicators LEP 34 S	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b>	7560307_03 397963_03 7135060B 397416_03 7135477B 7156144B	MA	(317102) or (317107)	
<b>LS 373</b>	Liquid Adhesive Gun	<b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>SP</b>	292753E 292752E 315729E 292755E 292754E 7192547E 292756E 315743E 7146960E 315730E 292757E	MA	(317102) or (317107)	<b>Issued 09/2017</b>
<b>LS-T 373</b>	Liquid Adhesive Gun	<b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	7135973B 7135977B 7135929B 7135983B 7135985B	MA	(317102) or (317107)	<b>Issued 09/2017</b>



## Paper and Paperboard Converting

E-1-12

### Nordson Benelux Products ( former Walcom ) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>LV 227</b>	Applicator (Title version B + C: Liquid Adhesive Gun)	<b>CZ</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>NO</b> <b>PL</b> <b>PO</b> <b>SP</b> <b>SW</b>	7169322B 405029C 405030_05 405031C 405032_05 405033_05 405034_05 464878B* 405035C 7135115C 405036C 405037_05 405038C	MA	(317102) or (317107)	<b>Issued 09/2017</b>          <b>* available at Nordson K.K</b>
<b>VarioCoat-S/ VarioCoat-M</b>	Applicators	<b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>SP</b>	7560317_02 7560327_02 7179993_02 7560328_02 7560330_02 7560329_02	MA	(317102) or (317107)	<b>Issued 09/2017</b>
<b>WM 100 CS</b>	Pattern Control Unit for Corrugated Cardboard	<b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>SP</b> <b>SW</b>	317202C 317149C 7119343C 317205C 7135361C 317166C 7119975C 317167C 405211C	MA	(317102) or (317107)	<b>Obsolete!</b>
<b>WM 302</b>	Pressure Control Unit	<b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	317145B 317146B 317147B 317108B 317171B 317148B	MA	(317102) or (317107)	

E-1-13

## Paper and Paperboard Converting

### Nordson Benelux Products ( former Walcom ) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>WM 315&amp; WM 315M &amp; WM 325</b>	Pneumatic Diaphragm Pump	<b>DU EN FR GE IT SP</b>	315855B 315814B 315856B 315837B 315857B 317087B	MA	(317102) or (317107)	<b>Replaced by WM320/320M!</b>
<b>WM 315 H</b>	High Pressure Pneumatic Diaphragm Pump	<b>DU EN FR GE IT SP</b>	317272A 317218A 403086A 317210A 403002A 317273A	MA	(317102) or (317107)	<b>Obsolete!</b>
<b>WM 320/ WM 320M</b>	Pneumatic Diaphragm Pump (see also LA320 / LA320M - revision B)	<b>DU EN FR GE IT SP</b>	409147B 407442B 409148A 407441B 409149A 409150A	MA	(317102) or (317107)	
<b>WM 325</b>	Pneumatic Membrane Pump	<b>EN GE</b>	458285A 458286A	MA	(317102) or (317107)	
<b>WM 351/352</b>	Pressure Regulator for Liquid Adhesives - Pump Mounted	<b>DU EN FI FR GE IT SW</b>	315905A 315841A 315906A 315907A 315842A 317182A 315908A	MA	(317102) or (317107)	
<b>WM 353/354</b>	Pressure Regulators for Liquid Adhesives - Wall Mounted	<b>DU EN FR GE IT</b>	315913A 315843A 315914A 315844A 317183A	MA	(317102) or (317107)	<b>Replaced by LA38x series!</b>

## Paper and Paperboard Converting

E-1-14

### Nordson Benelux Products ( former Walcom ) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>WM 360</b>	Pneumatic Piston Pump for Liquid Adhesives - Lid Mounted	<b>CZ</b> <b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>PL</b> <b>SP</b> <b>SW</b>	7105365C* 315888C* 315889C* 315819C* 315890C* 315891C* 315838C* 403078B* 315892C* 397000C* 317049C* 315893C*	MA	(317102) or (317107)	<b>* = supplement included - correction to parts list, page 8-7</b>
<b>WM 360 WM</b>	Pneumatic Piston Pump for Liquid Adhesives - Wall Mounted	<b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	403125A 403081A 213626A 409182A 403080A 409183A 403236A	MA	(317102) or (317107)	
<b>WM 370</b>	Pressure Regulators for Liquid Adhesives	<b>DA</b> <b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	315896A 315897A 315839A 315898A 315899A 315840A 317180A 315917A	MA	(317102) or (317107)	
<b>WM 408</b>	OP - special corrugated	<b>EN</b> <b>FR</b>	213704A 213706A	OP	(317102) or (317107)	

E-1-15

## Paper and Paperboard Converting

### Nordson Benelux Products ( former Walcom ) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>WM 408</b>	Pattern Control Unit	DA DU EN FI FR GE IT PL RU SP SW	413009E 317068E 317063E 403085E 317069E 315866E 317111E 464774E 7135172E 317071E 405212E	MA	(317102) or (317107)	
<b>WM 408</b>	Pattern Control Unit	CH DA DU EN FI FR GE IT NO PL SW	213876A 458225A 213988A 374360A 458314A 375364A 458386A 458094A 458226A 458378A 458227A	OP	(317102) or (317107)	
<b>WM 408</b>	PCA 408 Electric Gun Driver Board (7 languages: DU / EN / FR / GE / IT / SP / SW)	--	331182B	IN	(317102) or (317107)	<b>EDB No. 4-44</b>
<b>WM 416</b>	Pattern Control Unit	DU EN FR GE IT SP SW	405043A 317262A 407054A 317261A 405044A 403045A 407287A	MA	(317102) or (317107)	

E-1-16

## Paper and Paperboard Converting

### Nordson Benelux Products ( former Walcom ) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>WM 500</b>	Liquid Adhesive Detection System	<b>DA</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>RU</b> <b>SP</b> <b>SW</b>	447663B 315864B 315815B 315865B 315816B 317225B 7135173B 317064B 407011B	MA	(317102) or (317107)	
<b>WM 500</b>	Liquid Adhesive Detection System	<b>CH</b> <b>DA</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>NO</b> <b>SW</b>	213877A 458311A 374361A 458313A 375425A 464953A 458312A 458310A	OP	(317102) or (317107)	
<b>WM 500</b>	OP - special corrugated	<b>EN</b> <b>FR</b>	213705A 213707A	OP	(317102) or (317107)	
<b>WM 710</b>	Liquid Adhesive Gun	<b>DU</b> <b>EN</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>JA</b> <b>PL</b> <b>SP</b>	405062B 403270B 213208B 407008B 403271B 407009B 464881B* 7179439B 407010B	MA	(317102) or (317107)	<b>* available at Nordson K.K</b>

E-1-17

## Paper and Paperboard Converting

### Nordson Benelux Products ( former Walcom ) (sorted by Model)

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>WM 801 P/Q</b>	Liquid Adhesive Gun	<b>CZ DU EN FI FR GE IT JA PL SP SW</b>	7105366B 403229B 403123B 213502B 409096B 403122B 409104B 464882B* 397001B 403230B 409493B	MA	(317102) or (317107)	* available at Nordson K.K
<b>WM 801 S/Q</b>	Liquid Adhesive Gun	<b>DU EN FI FR GE IT SP SW</b>	7105725A 7105606A 7105799A 7105716A 7105605A 7105726A 7105728A 7105724A	MA	(317102) or (317107)	
<b>WM 83X &amp; WM 88X</b>	Liquid Adhesive Guns	<b>DA DU EN FI FR GE IT SP SW</b>	315845A 315846A 315812A 315847A 315848A 315813A 315849A 317037A 315850A	MA	(317102) or (317107)	

Issued by Technical Documentation Local Languages (TDLL) Department, Nordson Engineering, Lüneburg  
Status : December 2019

## Asymtek (sorted by Product Title)

F-1 -1

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Free-Standing Loaders	IT	409323A	MA		EN source - 76-UYO3-0C ( Obsolete !!! )
	Millenium Series	FI FR GE	409342A 409449A 409322A	MA		EN source - 76-UML1-0C ( Obsolete !!! )

Other translated Asymtek manuals are available on <<http://www.asymtek.com>> by clicking on Tech Support, then Manuals.

## EFD (sorted by Product Title)

F-2 -1

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
EFD	740V Series Dispense Valve Operating Manual	FR GE PL SK	7105999A 7105879A 7105800A 7119226A	MAN	(317102) or (317107)	EN - 7105955A
EFD	741V Series Dispense Valve Installation Guide	DU FR GE PL SP	7179190A 7135455A 7135058A 7119879A 7135117A	IN	(317102) or (317107)	EN - No P/N
EFD	741V Series Dispense Valve Maintenance and Parts Guide	DU FR GE PL SP	7179191A 7135456A 7135059A 7119880A 7135118A	IN	(317102) or (317107)	EN - No P/N
EFD	Float Level Switch Installation for 600D5 Series Tank Reservoirs	DU FR GE PL SK	7179192A 7119000A 7105880A 7105801A 7119227A	IN	(317102) or (317107)	EN - 7105956A



## JM Laboratories (sorted by Product Title)

F-3 -1

Model/Edition	Product Title	Langs.	P/N	Type	Price Category	Notes
	<b><i>ORDER DIRECTLY VIA JML !</i></b>					
	Durafiber II Modular Application System	<b>GE SP SW</b>	412857A 458317A 412878A	MA	(317102) or (317107)	<b>EN source - no P/N</b>
	Durafiber III Modular Adhesive Applicator	<b>FR GE IT SP SW</b>	412970B 412971A 458300B 458265B 458205B	MA	(317102) or (317107)	<b>EN source - no P/N</b>
	Duraheater Modular Air Heating System	<b>FR GE IT SP SW</b>	458034A 412856A 458303A 458318A 412877A	MA	(317102) or (317107)	<b>EN source - no P/N</b>
	Duramelt DX-902 Expansion Melt Delivery System	<b>IT</b>	458305A	MA	(317102) or (317107)	<b>EN source - no P/N (10171)</b>
	Duramelt DX-902 Expansion Melt Delivery System	<b>IT</b>	447626A	MA	(317102) or (317107)	<b>EN source - no P/N (11399)</b>
	Duramelt DX-902 Melt Delivery System	<b>PL SP</b>	458371A 413050A	MA	(317102) or (317107)	<b>EN source - no P/N</b>
	Duramelt DX-902 Melt Delivery Unit - Ply Bonding System plus comprehensive Training material as .ppt file	<b>IT</b>	464908A	MA	(317102) or (317107)	<b>EN source - no P/N</b>
	Duramelt DX-2002 Melt Delivery System	<b>GE IT SP</b>	413066A 213012A 458039A	MA	(317102) or (317107)	<b>EN source - no P/N</b>
	Duramelt DX-2002 Melt Delivery System - HMI texts complete .xls file only, including screen .bmp files	<b>EN/GE</b>	-	-	-	

## JM Laboratories (sorted by Product Title)

F-3 -2

Model/Edition	Product Title	Langs.	P/N	Type	Price Category	Notes
	Duraremove Metering Unit DRM 448	<b>FR SP</b>	458201A 458266A	MA	(317102) or (317107)	<b>EN source - no P/N</b>
	DX Remote HMI texts complete .xls file only ( by Keith Mulkey )	<b>EN/IT</b>	-	-	-	
	MeltBlown Fiber System comprehensive manual ( sections 1 - 6 ) (JM Job # 18685)	<b>GE</b>	-	MA	(317103) or (317106)	<b>EN source - no P/N</b>
	MonoComponent MeltBlown HMI texts complete .xls file only (JM Job # 18685)	<b>EN/GE/ PO</b>	-	-	-	
	MonoComponent MeltBlown Installation, Operation, Maintenance, Operation Fitesa	<b>PO</b>	-	-	-	<b>EN source - no P/N</b>
	Ply Bonding Applicator ( Rev. 0005, Jan 2000 )	<b>IT</b>	458304A	MA	(317102) or (317107)	<b>EN source - no P/N</b>
	Ply Bonding Applicator ( Dec 99 ), incl. Charts	<b>FR</b>	458071A	MA	(317102) or (317107)	<b>EN source - no P/N</b>
	Ply Bonding Applicator (JM Job # 398834), including Warranty document	<b>SW</b>	-	MA	(317102) or (317107)	<b>EN source - no P/N</b>
	Polymer Meltblown (JM Job # 8996), plus System Screens, .ppt files	<b>IT</b>	458123A	MA	(317102) or (317107)	<b>EN source - no P/N</b>
	Remote Metering Station ( Ref. D12340 )	<b>SP</b>	447607A	MA	(317102) or (317107)	<b>EN source - no P/N</b>
	Spunbond Fiber System comprehensive manual ( sections 1 - 9 )	<b>TU</b>	-	MA	(317103) or (317106)	<b>EN source - no P/N</b>

Issued by Technical Documentation Local Languages (TDLL) Department, Nordson Engineering, Lüneburg  
Status : December 2019

## JM Laboratories (sorted by Product Title)

F-3 -3

Model/Edition	Product Title	Langs.	P/N	Type	Price Category	Notes
	Universal Slice Applicator	SP	213483A	MA	(317102) or (317107)	EN source - no P/N
	Universal Slice Applicator, Betrieb u Wartung, .ppt	GE	-	MA	(317102) or (317107)	EN source - no P/N

## March Plasma (sorted by Product Title)

F-4 -1

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
AP-1000	AP-1000 Plasma System - Operation and Maintenance Manual	GE	397378A	MA	(317103) or (317106)	EN - 021-000137
XTRAK	XTRAK System - Operation and Maintenance Manual	GE	213749A	MA	(317103) or (317106)	EN - 021-000140 rev.1.0

## Mountaingate (sorted by Product Title)

F-5 -1

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Mountaingate Heat and Hold Induction System	EN PL	1041928A 7105857A	MA	(317102) or (317107)	
ICD	Series Induction Dryer	EN GE SP	75-3000-02 292958A 317216A	MA	(317102) or (317107)	
ICD	Series Induction Dryers	EN FR PO	1018438A 397091A 397088A	MA	(317102) or (317107)	
ISC2	Series Induction Dryers	EN FR SP	1606739_01 7192945_01 7560607_01	MA	(317102) or (317107)	
EcoDry	Series Induction Dryers	DU EN FR GE SP	7146532A02 1045354A02 7105554A 7119856A 7105560A	MA	(317102) or (317107)	Issued 02/04
EcoDry	Nordson EcoDry Series Induction Dryers with Touch Screen Controls	DU EN FR GE IT SP	7169793_02 1601306_02 7192654_02 7169824_02 7560078_02 7179714_02	MA	(317102) or (317107)	Issued 3/14

## Mountaingate (sorted by Product Title)

F-5 -2

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>EcoDry</b>	Series Induction Dryers	<b>EN</b> <b>FR</b> <b>GE</b> <b>SP</b>	1045825A 7105555A 7119857A 7105561A	OP	(317102) or (317107)	
<b>iDry</b>	Nordson iDry Series Induction Dryers	<b>CZ</b> <b>DU</b> <b>EN</b> <b>FR</b> <b>GE</b> <b>HU</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>RU</b> <b>SP</b>	7580941_04 7179374A02 1075452_04 7135912_04 7179419_04 7560774_04 7179441_04 7192961A02 7580145_04 7179645A02 7135884_04	MA	(317102) or (317107)	

## Nordson Sealant Equipment (sorted by Product Title)

F-6 -1

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
--	2200-245-Series Kiss Valves	FR PL RU SP SW	7593395_01 7580065_01 7580900_01 7580257_01 7593265_01	MAN	(317102) or (317107)	EN - 7439854_01 - Issued 08/16
<b>PRO-METER A2K/ D2K/ H2K</b>	PRO-METER A2K/ D2K/ H2K Series Dispense System	GE	7580953	MAN	(317102) or (317107)	EN - 7439855 - Issued 06/17
<b>PRO-METER A2K/ D2K/ H2K</b>	PRO-METER A2K/ D2K/ H2K Operator's Card	GE	7580954	OP	(317102) or (317107)	EN - 7443491 - Issued 06/17
<b>PRO-METER A2K/ D2K/ H2K</b>	PRO-METER A2K/ D2K/ H2K Quick Start Guide	GE	7580955	IN	(317102) or (317107)	EN - 7443490 - Issued 06/17
<b>PRO-METER V2K</b>	PRO-METER V2K	CZ FR GE IT SP	7580298(06/17) 7580299(06/17) 7580300(06/17) 7580467(12/17) 7580301(06/17)	MAN	(317102) or (317107)	EN - 7440274 - Issued 06/17 and 12/17
<b>PRO-METER V2K</b>	PRO-METER V2K Operator's Card	CZ FR GE IT SP	7580302 7580303 7580304 7580468 7580305	OP	(317102) or (317107)	EN - 7440262 - Issued 06/17
<b>PRO-METER V2K</b>	PRO-METER V2K Quick Start Guide	CZ FR GE IT SP	7580306 7580307 7580308 7580469 7580309	IN	(317102) or (317107)	EN - 7440272 - Issued 05/17

Issued by Technical Documentation Local Languages (TDLL) Department, Nordson Engineering, Lüneburg  
Status : December 2019

## Nordson Sealant Equipment (sorted by Product Title)

F-6 -2

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Steady-Mix 2K</b>	Steady-Mix 2K	<b>CH</b> <b>GE</b> <b>JA</b>	7593356 7593383 7593358	MA	(317102) or (317107)	<b>EN - 7444434 - Issued 2019</b>
<b>Steady-Mix 2K</b>	Steady-Mix 2K Quick Start Guide	<b>CH</b> <b>GE</b> <b>JA</b>	7593357 7593384 7593359	IN	(317102) or (317107)	<b>EN - 7444435 - Issued 2019</b>



## PICODOSTEC (sorted by Product Title)

F-7-1

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Micrometering System PICODOSTEC SV 60 Piezoelectric Metering Valve with Slide Technology, Type SV with Control Unit Type CON SV	EN GE	7135378A 7135350A	MA	(317102) or (317107)	
	Micrometering System PICODOSTEC DS100/DS200 Micrometering Valve Type DV with Control Unit Type CON	FR GE	7156293A 7156292A	MA	(317102) or (317107)	
	DCON Aixtron	EN GE	7156295A 7156294A	MA	(317102) or (317107)	
	Cleaning Instructions How to Clean PICO Piezoelectric Metering Valves	EN FR GE	7156297A 7156298A 7156296A	MA	(317102) or (317107)	
	Manual for Pressure Tank DT-FP	EN GE	7156502A 7156501A	MA	(317102) or (317107)	
	Operating Manual Pulse Generator DPA2 <sup>+2</sup> for Triggering the Control Unit Type CON/DCON	EN GE	7156508A 7156509A	MA	(317102) or (317107)	

## Nordson Puffe Hot Melt (sorted by Product Title)

F-8 -1

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
	Extruder EX 03-PS01	<b>CZ</b>	7119187A	MA	(317102) or (317107)	<b>GE source - no P/N</b>
	Heated Hoses Serie PC	<b>CZ</b>	7119188A	MA	(317102) or (317107)	<b>GE source - no P/N</b>
	Pressure Sensor	<b>CZ</b>	7119189A	MA	(317102) or (317107)	<b>GE source - no P/N</b>
	Bead Application Head AN 26 T	<b>CZ</b>	7119190A	MA	(317102) or (317107)	<b>GE source - no P/N</b>

## Slutterback (sorted by Product Title)

F-9 -1

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>Autotech AT 8</b>	Hotmelt Unit	<b>DU</b> <b>FR</b> <b>GE</b>	458376A 447615A 458377A	MA	(317102) or (317107)	<b>EN - 19600-221D</b>
<b>Autotech AT 15</b>	Hotmelt Unit	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>PL</b> <b>PO</b> <b>SP</b>	412898C 412674C 412681C 412761C 397251C 464838C 412728C	MA	(317102) or (317107)	<b>EN - 19600-184H (US-version)</b> <b>EN - 19600-216C (European)</b>
<b>Autotech AT 30 / 40 / 60</b>	Melt Unit Series with T500 Temperature Controller	<b>DU</b> <b>FR</b>	458069B 458070B	MA	(317102) or (317107)	<b>EN - 19600-146C</b>
<b>CH22-TR</b>	Pattern Controller	<b>FR</b>	315933A	MA	(317102) or (317107)	<b>EN - 19600-113B</b>
<b>Data Beam Sensor</b>	Controller	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	290904A 290905A 290906A 290907A 290908A	MA	(317102) or (317107)	<b>EN - 19600 124A</b>
<b>DC Driver</b>	DC Driver - Single Output	<b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	405047F 405010F 405104F 405057F	MA	(317102) or (317107)	<b>EN - 19600-76F</b>
<b>DX5 / DX3A</b>	Temperature Controllers	<b>JA</b>	464867A	MA	(317102) or (317107)	<b>EN - 19600-210A</b>
<b>E100XT</b>	Applicator	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	290713G 292890G 292891G 290808G 290809G	MA	(317102) or (317107)	<b>EN - 19600-17XTH</b>

## Slutterback (sorted by Product Title)

F-9 -2

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>E900</b>	Modular Applicators 3-Pin Coil	<b>FR</b> <b>GE</b> <b>IT</b>	405055A 405009A 405096A	MA	(317102) or (317107)	<b>EN - 19600-154A</b> <b>End of Support 04/2018</b>
<b>ET2-TR</b>	Pattern Controller	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	290886B 290887B 290817B 290888B 290889B	MA	(317102) or (317107)	<b>EN - 19600-131B</b>
<b>ET4</b>	Pattern Controller	<b>DU</b> <b>GE</b> <b>IT</b> <b>SP</b>	290855A 290857A 290858A 290859A	MA	(317102) or (317107)	<b>EN - 19600-129A</b> <b>(latest EN revision -</b> <b>19600-129C)</b>
<b>ET4-T</b>	Pattern Controller	<b>DU</b> <b>GE</b> <b>IT</b> <b>SP</b>	315799B 315796B 315800B 290885B	MA	(317102) or (317107)	<b>EN - 19600-130B</b> <b>(latest EN revision -19600-130C)</b>
<b>HC/HS/OP/ 501 Style</b>	Heated Supply Hoses (Automatic Application)	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	290712 I 290767 I 290768 I 290769 I 290770 I	MA	(317102) or (317107)	<b>EN - 19600-24I</b> <b>(latest EN revision - 19600-24K)</b>
<b>HD2</b>	Head Driver	<b>DU</b>  <b>FR</b>  <b>GE</b>  <b>IT</b> <b>SP</b>	290890A* 292841A 290891A* 292842A 290892A* 292843A 290893A 290894A	MA	(317102) or (317107)	<b>EN - 19600-126A</b> <b>* = old version</b>
<b>HD2A</b>	Head Driver	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	290895A 290896A 292844A 290897A 290898A	MA	(317102) or (317107)	<b>EN - 19600-127A</b>

## Slutterback (sorted by Product Title)

F-9 -3

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
HD4A	Head Driver	DU FR GE  IT SP	290899A 290900A 290901A* 292845A 290902A 290903A	MA	(317102) or (317107)	EN - 19600-128A * = old version
JR1	Hotmelt System	DU FR SP	413089B 413090B 464965B	MA	(317102) or (317107)	EN - 19600-191B
JR5	Hot Melt Applicator	DA DU FI FR GE NO SP SW	407416D 407491D 407440D 407417D 407421D 407419D 407450D 407439D	OP	(317102) or (317107)	EN - 19600-195D
JR5 / JR6 / JR7 / JR8	JR Series Hotmelt System Product Manual	DA DU FI FR GE IT NO SP SW	409070A* 409071A 409072B 409073A 409074A 413070A 409075A* 409076A 409077A*	MA	(317102) or (317107)	EN - 19600-190-2A * = not yet translated
KB 10/20E/ T150	Melt Unit	DU FR GE IT SP	315781C 315782C 315783C 315784C 315785C	MA	(317102) or (317107)	EN - 19600-144A

## Slutterback (sorted by Product Title)

F-9 -4

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>KB 10/20E/ Thermostat</b>	Melt Unit	<b>DU FR GE IT SP</b>	315776A 315778A 315779A 315780A 315777A	MA	(317102) or (317107)	<b>EN - 19600-143A</b>
<b>KS 10/20E/ T150</b>	Melt Unit	<b>DA DU FI FR GE IT NO SP SW</b>	317066C 315770C 315821C 315772C 315773C 315774C 315809C 315775C 315794C	MA	(317102) or (317107)	<b>EN - 19600-145A</b>
<b>L4</b>	Handgun	<b>DA DU FI FR GE IT NO SP SW</b>	315943C 292951C 292952C 292953C 292954C 292955C 315810C 292956C 292957C	MA	(317102) or (317107)	<b>EN - 19600-110B</b>
<b>L5</b>	Handgun - Manual Extrusion and Swirl Applicator	<b>DU FR GE IT SP</b>	458059E 403073C 403079C 403089C 403091C	MA	(317102) or (317107)	<b>EN - 19600-147E</b>
<b>LR 10</b>	Low Profile Hot Melt Unit	<b>JA</b>	464877B*	MA	(317102) or (317107)	<b>EN - 19600-158B</b> * = available at Nordson K.K.

## Slutterback (sorted by Product Title)

F-9 -5

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
<b>LS 10/20E</b>	Melt Unit	<b>DU</b> <b>FI</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b> <b>SW</b>	292880A 292945A 292881A 292882A 292883A 292884A 292946A	MA	(317102) or (317107)	<b>EN - 19600-137A</b> <b>No longer distributed</b>
<b>Mini Squirt II</b>	Hot Melt Adhesive Applicator	<b>FR</b> <b>IT</b> <b>SP</b>	403087F 403088F 403090F	MA	(317102) or (317107)	<b>EN - 19600-03MSII - revision F</b>
<b>MiniSquirt III</b>	MiniSquirt III Hand-held Applicator	<b>PL</b> <b>PO</b>	7179518 <b>D02</b> 7135170D	MA	(317102) or (317107)	<b>EN - 1018551D02 - Issued 12/15</b> <b>Date of Polish translation 01/09</b> <b>Obsolete!</b>
<b>SW4</b>	Swirl Handgun	<b>FR</b> <b>GE</b>	407493A 315930A	MA	(317102) or (317107)	<b>EN - 19600-125A</b>
<b>T150</b>	Temperature Controller	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	290824C 290721C 290722C 290723C 290724C	MA	(317102) or (317107)	<b>EN - 19600-116C</b>
<b>T500</b>	Temperature Controller	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	290916B 283048B 290917B 283050B 283049B	MA	(317102) or (317107)	
<b>T1000</b>	Temperature Controller	<b>DU</b> <b>FR</b> <b>GE</b> <b>IT</b> <b>SP</b>	290918 I 283045 I 290919 I 283047 I 283046 I	MA	(317102) or (317107)	<b>No longer marketed in EU</b>

Issued by Technical Documentation Local Languages (TDLL) Department, Nordson Engineering, Lüneburg  
Status : December 2019

## Watlow (sorted by Product Title)

F-10 -1

Model	Product Title	Langs.	P/N	Type	Price Category	Notes
TDM4	Thermo-Ducer	EN GE	no P/N 292959	MA	(317102) or (317107)	