


Popis

Pozri obr. 1. Rhino SD3/XD3 Moduly prepojovacích hadíc sú určené na použitie na rámoch vykladača s dvomi stĺpmi nakonfigurovanými s 5- a 55-galónovými doskami sledovača. Moduly sú k dispozícii aj ako hromadné vykladače nakonfigurované s možnosťou odtlakovania. Každý modul pozostáva z hadice, trubíc a káblov vedených cez káblovú trasu. Pre verzie 24 V DC je zahrnutá aj káblová pumpa pre snímanie zdvihov.



Obr. 1 Typický modul prepojovacích hadíc

Údržba


Reťazová trasa

Spôsob vybratia a výmeny článku(-ov) v reťazovej trase pozri na obrázku 2-3 a v tabuľke 1.

Tabuľka 1 Spotrebné položky


Položka	Použitie
Plochý skrutkovač	Odstránenie článku(-ov).

1. Plochý skrutkovač zasuňte do plôšky na článku a vypáčte nahor, aby vyskočil mostík (1). Pozri obr. 2.



Obr. 2 Reťazová trasa

2. Článok zaistíte na svojom mieste tak, že nainštalujete mostík (1) a potom mostík (1) zatlačíte, až kým nezacvakne na svojom mieste v článku. Pozri obr. 3.




Obr. 3 Refazová trasa

Náhradné diely

Ak chcete objednať diely, zavolajte zákaznícke a servisné stredisko spoločnosti Nordson, alebo sa obráťte na miestneho zástupcu Nordson. Zoznamy náhradných dielov modulu prepojovacej hadice sú zoradené podľa veľkosti rámu.


Modul hadice s rámom DP so vzduchovým motorom SD3, 24 V DC

Pozri obrázok 4-5 a nasledujúci zoznam náhradných dielov.



Obr. 4 Modul hadice s rámom DP so vzduchovým motorom SD3, 24 V DC (1 z 2)

Položka	P/N	Popis	Množstvo	Poznámka
1	1615644	TUBE, 16 mm-OD, polyurethane, fire resistant, black	8 ft	
	1615652	TUBE, 16 mm-OD, polyurethane, fire resistant, blue	8 ft	
2	1100040	CONNECTOR, male, elbow, 16 mm T x ½ RPT, with seal	1	
3	-----	BUSHING, BSPT pipe, hydraulic, ¾ x ½, steel, zinc	1	
4	1616611	TUBE, 8 mm-OD, polyurethane, fire resistant, black	8 ft	
	1615652	TUBE, 8 mm-OD, polyurethane, fire resistant, blue	8 ft	
5	1615824	CABLE, 4-pin micro, 4 M, male/female	1	
6	1045605	HOSE, -06, low pressure, synthetic, fiber, M2 black	9.5 ft	
	1045606	HOSE, -06, low pressure, synthetic, fiber, M1 blue	9.5 ft	
7	1045647	CONNECTOR, female, barbed, ¾ T x 9/16-18, brass	1	
8	1615608	CONNECTOR, male, 37, ¾ T x R ¼, steel	1	




Obr. 5 Modul hadice s rámom DP so vzduchovým motorom SD3, 24 V DC (2 z 2)

Položka	P/N	Popis	Množstvo	Poznámka
1	-----	NUT, lock, nylon, M6, steel, zinc, class 8, per ISO 7040	4	
2	-----	WASHER, flat, M, regular, M6, steel, zinc, per ISO 7089	8	
3	-----	SCREW, socket, M6 x 16, zinc, class 12.9, per ISO 4762	4	
4	1616841	CHAIN, cable, 3.43 x 1.02, 18 links	1	
5	-----	SCREW, socket, M6 x 65, zinc, class 12.9, per ISO 4762	2	
6	1615643	TUBE, 6 mm-OD, polyurethane, fire resistant, black	17 ft	A
	1615651	TUBE, 6 mm-OD, polyurethane, fire resistant, blue	17 ft	
7	324046	HANGER, hose	1	
8	-----	COUPLER, disconnect, barb, pushlock, 3/8 tube	1	
9	1045605	HOSE, -06, low pressure, synthetic, fiber, M2 black	9.5 ft	
	1045606	HOSE, -06, low pressure, synthetic, fiber, M1 blue	9.5 ft	
10	1073257	NIPPLE, disconnect, 1/4 T, 3/8 NPT female	1	
11	973084	BUSHING, pipe, hydraulic, 1/2 x 3/8, steel, zinc	1	
12	1073896	NIPPLE, pipe, schedule, 40, 3/8 NPT, 18 in., galvanized	1	
POZNÁMKA A: Len pre moduly s odtlakovaním a/alebo ARW.				


Modul hadice s rámom DP so vzduchovým motorom SD2, 24 V DC

Pozri obrázok 6-7 a zoznam náhradných dielov.



Obr. 6 Modul hadice s rámom DP so vzduchovým motorom SD2, 24 V DC (1 z 2)

Položka	P/N	Popis	Množstvo	Poznámka
1	1615608	CONNECTOR, male, 37, $\frac{3}{8}$ T x R $\frac{1}{4}$, steel	1	
2	1045647	CONNECTOR, female, barbed, $\frac{3}{8}$ T x 9/16-18, brass	1	
3	1045605	HOSE, -06, low pressure, synthetic, fiber, M2 black	9.5 ft	
	1045606	HOSE, -06, low pressure, synthetic, fiber, M1 blue	9.5 ft	
4	1616841	CHAIN, cable, 3.43 x 1.02, 18 links	1	
5	1615824	CABLE, 4-pin micro, 4 M, male/female	1	
6	1616611	TUBE, 8 mm-OD, polyurethane, fire resistant, black	8 ft	
	1615652	TUBE, 8 mm-OD, polyurethane, fire resistant, blue	8 ft	
7	-----	BUSHING, BSPT pipe, hydraulic, $\frac{3}{4}$ x $\frac{1}{2}$, steel, zinc	1	
8	1100040	CONNECTOR, male, elbow, 16 mm T x $\frac{1}{2}$ RPT, with seal	1	
9	1615644	TUBE, 16 mm-OD, polyurethane, fire resistant, black	8 ft	
	1615652	TUBE, 16 mm-OD, polyurethane, fire resistant, blue	8 ft	
10	1615643	TUBE, 6 mm-OD, polyurethane, fire resistant, black	17 ft	A
	1615652	TUBE, 6 mm-OD, polyurethane, fire resistant, blue	17 ft	
11	324046	HANGER, hose	1	
12	-----	COUPLER, disconnect, barb, pushlock, $\frac{3}{8}$ tube	1	
13	1073257	NIPPLE, disconnect, $\frac{1}{4}$ T, $\frac{3}{8}$ NPT female	1	
14	1073896	NIPPLE, pipe, schedule, 40, $\frac{3}{8}$ NPT, 18 in., galvanized	1	
15	973084	BUSHING, pipe, hydraulic, $\frac{1}{2}$ x $\frac{3}{8}$, steel, zinc	1	
POZNÁMKA A: Len pre moduly s odtlakovaním a/alebo ARW.				
AR: As Required (Podľa potreby)				




Obr. 7 Modul hadice s rámom DP so vzduchovým motorom SD2, 24 V DC (2 z 2)

Položka	P/N	Popis	Množstvo	Poznámka
1	-----	NUT, lock, nylon, M6, steel, zinc, class 8, per ISO 7040	4	
2	-----	WASHER, flat, M, regular, M6, steel, zinc, per ISO 7089	8	
3	-----	SCREW, socket, M6 x 16, zinc, class 12.9, per ISO 4762	4	
4	1616841	CHAIN, cable, 3.43 x 1.02, 18 links	1	
5	-----	SCREW, socket, M6 x 65, zinc, class 12.9, per ISO 4762	2	

Táto strana je prázdna zámerne


Modul hadice s malým/velkým rámom so vzduchovým motorom SD3, 24 V DC

Pozri obrázok 8-10 a nasledujúci zoznam náhradných dielov.




Obr. 8 Modul hadice s malým/velkým rámom so vzduchovým motorom SD3, 24 V DC (1 z 3)

Položka	P/N	Popis	Množstvo	Poznámka
1	-----	NUT, lock, nylon, M6, steel, zinc, class 8, per ISO 7040	4	
2	-----	WASHER, flat, M, regular, M6, steel, zinc, per ISO 7089	8	
3	-----	SCREW, socket, M6 x 16, zinc, class 12.9, per ISO 4762	4	
4	-----	SCREW, socket, M6 x 65, zinc, class 12.9, per ISO 4762	2	
5	1615647	CHAIN, cable, 3.43 x 1.02, 27 links	1	



Obr. 9 Modul hadice s malým/veľkým rámom so vzduchovým motorom SD3, 24 V DC (2 z 3)

Položka	P/N	Popis	Množstvo	Poznámka
1	1615643	TUBE, 6 mm-OD, polyurethane, fire resistant, black	17 ft	A
	1615651	TUBE, 6 mm-OD, polyurethane, fire resistant, blue	17 ft	
2	1615644	TUBE, 16 mm-OD, polyurethane, fire resistant, black	8 ft	
	1615653	TUBE, 16 mm-OD, polyurethane, fire resistant, blue	8 ft	
3	1100040	CONNECTOR, male, elbow, 16 mm T x 1/2 RPT, with seal	1	
4	-----	BUSHING, BSPT pip, hydraulic, 3/4 x 1/2, steel, zinc	1	
5	1616611	TUBE, 8 mm-OD, polyurethane, fire resistant, black	8 ft	
	1615652	TUBE, 8 mm-OD, polyurethane, fire resistant, blue	8 ft	
6	1045605	HOSE, -06, low pressure, synthetic, fiber, M2 black	9.5 ft	
	1045606	HOSE, -06, low pressure, synthetic, fiber, M1 blue	9.5 ft	
7	1045647	CONNECTOR, female, barbed, 3/8 T, 9/16-18, brass	1	
8	1615608	CONNECTOR, male, 3/8 T x R 1/4, steel	1	
POZNÁMKA A: Len pre moduly s odtlakovaním a/alebo ARW.				




Obr. 10 Modul hadice s malým/veľkým rámom so vzduchovým motorom SD3, 24 V DC (3 z 3)

Položka	P/N	Popis	Množstvo	Poznámka
1	324046	HANGER, hose	1	
2	-----	COUPLER, disconnect, barb, pushlock, 3/8 tube	1	
3	1045605	HOSE, -06, low pressure, synthetic, fiber, M2 black	9.5 ft	
	1045606	HOSE, -06, low pressure, synthetic, fiber, M1 blue	9.5 ft	
4	1073257	NIPPLE, disconnect, 1/4 T, 3/8 NPT, female	1	
5	1073896	NIPPLE, pipe, schedule 40, 3/8 NPT, 18 in., galvanized	1	
6	-----	SCREW, socket, M6 x 45, zinc, class 12.9, per ISO 4762	2	
7	983029	WASHER, flat, M, regular, M6, steel, zinc, per ISO 7089	8	
8	1615824	CABLE, 4-pin micro, 4 m, male/female	1	


Modul hadice s malým/velkým rámom so vzduchovým motorom SD2, 24 V DC

Pozri obrázok 11-13 a nasledujúci zoznam náhradných dielov.




Obr. 11 Modul hadice s malým/velkým rámom so vzduchovým motorom SD2, 24 V DC (1 z 3)

Položka	P/N	Popis	Množstvo	Poznámka
1	-----	SCREW, socket, M6 x 65, zinc, class 12.9, per ISO 4762	2	
2	-----	WASHER, flat, M, regular, M6, steel, zinc, per ISO 7089	8	
3	-----	SCREW, socket, M6 x 16, zinc, class 12.9, per ISO 4762	4	
4	-----	NUT, lock, nylon, M6, steel, zinc, class 8, per ISO 7040	4	
5	1615647	CHAIN, cable, 3.43 x 1.02, 27 links	1	



Obr. 12 Modul hadice s malým/veľkým rámom so vzduchovým motorom SD2, 24 V DC (2 z 3)

Položka	P/N	Popis	Množstvo	Poznámka
1	1615643	TUBE, 6 mm-OD, polyurethane, fire resistant, black	17 ft	A
	1615651	TUBE, 6 mm-OD, polyurethane, fire resistant, blue	17 ft	
2	1615644	TUBE, 16 mm-OD, polyurethane, fire resistant, black	8 ft	
	1615653	TUBE, 16 mm-OD, polyurethane, fire resistant, blue	8 ft	
3	1100040	CONNECTOR, male, elbow, 16 mm T x 1/2 RPT, with seal	1	
4	-----	BUSHING, BSPT pipe, hydraulic, 3/4 x 1/2, steel, zinc	1	
5	1616611	TUBE, 8 mm-OD, polyurethane, fire resistant, black	8 ft	
	1615652	TUBE, 8 mm-OD, polyurethane, fire resistant, blue	8 ft	
POZNAMKA A: Len pre moduly s odtlakovaním a/alebo ARW.				




Obr. 13 Modul hadice s malým/veľkým rámom so vzduchovým motorom SD2, 24 V DC (3 z 3)

Položka	P/N	Popis	Množstvo	Poznámka
1	1615824	CABLE, 4-pin micro, 4 M, male/female	1	
2	1615608	CONENCTOR, male, 37, ⅜ T x R ¼, steel	1	
3	1045647	CONNECTOR, female, barbed, ⅜ T, 9/16-18, brass	1	
4	1045605	HOSE, -06, low pressure, synthetic, fiber, M2 black	9.5 ft	
	1045606	HOSE, -06, low pressure, synthetic, fiber, M1 blue	9.5 ft	
5	1616611	TUBE, 8 mm-OD, polyurethane, fire resistant, black	8 ft	
	1615652	TUBE, 8 mm-OD, polyurethane, fire resistant, blue	8 ft	
6	-----	BUSHING, BSPT pipe, hydraulic, ¾ x ½, steel, zinc	1	
7	1100040	CONNECTOR, male, 16 mm T x ½ RPT, with seal	1	
8	1615644	TUBE, 16 mm-OD, polyurethane, fire resistant, black	8 ft	
	1615653	TUBE, 16 mm-OD, polyurethane, fire resistant, blue	8 ft	
9	324046	HANGER, hose	1	
10	-----	COUPLER, disconnect, barbed, pushlock, ⅜ tube	1	
11	1073257	NIPPLE, disconnect, ¼ T, ⅜ NPT, female	1	
12	1073896	NIPPLE, pipe, schedule 40, ⅜ NPT, 18 in., galvanized	1	
13	-----	SCREW, socket, M6 x 45, zinc, class 12.9, per ISO 4762	2	
14	-----	WASHER, flat, M, regular, M6, steel, zinc, per ISO 7089	8	
15	1615643	TUBE, 6 mm-OD, polyurethane, fire resistant, black	17 ft	A
	1615651	TUBE, 6 mm-OD, polyurethane, fire resistant, blue	17 ft	
POZNÁMKA A: Len pre moduly s odtlakovaním a/alebo ARW.				


Modul hadice s malým/velkým rámom so vzduchovým motorom SD3, MT, 24 V DC

Pozri obrázok 14-15 a nasledujúci zoznam náhradných dielov.



Obr. 14 Modul hadice s malým/velkým rámom so vzduchovým motorom SD3, MT, 24 V DC (1 z 2)

Položka	P/N	Popis	Množstvo	Poznámka
1	-----	NUT, lock, nylon, M6, steel, zinc, class 8, per ISO 7040	4	
2	-----	WASHER, flat, M, regular, M6, steel, zinc, per ISO 7089	8	
3	-----	SCREW, socket, M6 x 16, zinc, class 12.9, per ISO 4762	4	
4	-----	SCREW, socket, M6 x 65, zinc, class 12.9, per ISO 4762	2	
5	1615647	CHAIN, cable, 3.43 x 1.02, 27 links	1	




Obr. 15 Modul hadice s malým/veľkým rámom so vzduchovým motorom SD3, MT, 24 V DC (2 z 2)

Položka	P/N	Popis	Množstvo	Poznámka
1	1615643	TUBE, 6 mm-OD, polyurethane, fire resistant, black	17 ft	A
	1615651	TUBE, 6 mm-OD, polyurethane, fire resistant, blue	17 ft	
2	1615644	TUBE, 16 mm-OD, polyurethane, fire resistant, black	8 ft	
	1615653	TUBE, 16 mm-OD, polyurethane, fire resistant, blue	8 ft	
3	1100040	CONNECTOR, male, elbow, 16 mm T x 1/2 RPT, with seal	1	
4	-----	BUSHING, BSPT pipe, hydraulic, 3/4 x 1/2, steel, zinc	1	
5	1616611	TUBE, 8 mm-OD, polyurethane, fire resistant, black	8 ft	
	1615652	TUBE, 8 mm-OD, polyurethane, fire resistant, blue	8 ft	
6	1615824	CABLE, 4-pin micro, 4 M, male/female	1	
POZNAMKA A: Len pre moduly s odtlakovaním a/alebo ARW.				


Modul hadice s malým/velkým rámom so vzduchovým motorom SD2, MT, 24 V DC

Pozri obrázok 16-17 a nasledujúci zoznam náhradných dielov.



Obr. 16 Modul hadice s malým/velkým rámom so vzduchovým motorom SD2, MT, 24 V DC (1 z 2)

Položka	P/N	Popis	Množstvo	Poznámka
1	-----	SCREW, socket, M6 x 65, zinc, class 12.9, per ISO 4762	2	
2	-----	WASHER, flat, M, regular, M6, steel, zinc, per ISO 7089	8	
3	-----	SCREW, socket, M6 x 16, zinc, class 12.9, per ISO 4762	4	
4	-----	NUT, lock, nylon, M6, steel, zinc, class 8, per ISO 7040	4	
5	1615647	CHAIN, cable, 3.43 x 1.02, 27 links	1	




Obr. 17 Modul hadice s malým/veľkým rámom so vzduchovým motorom SD2, MT, 24 V DC (2 z 2)

Položka	P/N	Popis	Množstvo	Poznámka
1	1615643	TUBE, 6 mm-OD, polyurethane, fire resistant, black	17 ft	A
	1615651	TUBE, 6 mm-OD, polyurethane, fire resistant, blue	17 ft	
2	1615824	CABLE, 4-pin micro, 4 M, male/female	1	
3	1615644	TUBE, 16 mm-OD, polyurethane, fire resistant, black	8 ft	
	1615653	TUBE, 16 mm-OD, polyurethane, fire resistant, blue	8 ft	
4	1100040	CONNECTOR, male, elbow, 16 mm T x ½ RPT, with seal	1	
5	-----	BUSHING, BSPT pip, hydraulic, ¾ x ½, steel, zinc	1	
6	1616611	TUBE, 8 mm-OD, polyurethane, fire resistant, black	8 ft	
	1615652	TUBE, 8 mm-OD, polyurethane, fire resistant, blue	8 ft	
POZNÁMKA A: Len pre moduly s odtlakovaním a/alebo ARW.				


Modul hadice s rámom DP so vzduchovým motorom SD3, pneumatický

Pozri obrázok 18-19 a nasledujúci zoznam náhradných dielov.



Obr. 18 Modul hadice s rámom DP so vzduchovým motorom SD3, pneumatický (1 z 2)

Položka	P/N	Popis	Množstvo	Poznámka
1	1045605	HOSE, -06, low pressure, synthetic, fiber, M2 black	6 ft	
2	-----	COUPLER, disconnect, barbed, pushlock, 3/8 tube	1	
3	-----	NIPPLE, disconnect, 1/4 T, 3/8 NPT female	1	
4	-----	BUSHING, pipe, hydraulic, 1/2 x 3/8, steel, zinc	1	
5	-----	NIPPLE, pipe, schedule 40, 3/8 NPT, 18 in., galvanized	1	
6	-----	SCREW, socket, M6 x 45, class 12.9, per ISO 4762	4	
7	-----	WASHER, flat, M, regular, M6, steel, zinc, per ISO 7089	8	
8	1616841	CHAIN, cable, 3.43 x 1.02, 18 links	1	
9	-----	SCREW, socket, M6 x 16, zinc, class 12.9, per ISO 4762	4	
10	-----	NUT, lock, nylon, M6, steel, zinc, class 8, per ISO 7040	4	




Obr. 19 Modul hadice s rámom DP so vzduchovým motorom SD3, pneumatický (2 z 2)

Položka	P/N	Popis	Množstvo	Poznámka
1	1616612	TUBE, 10 mm-OD, polyurethane, fire resistant, black	8 ft	
	1616613	TUBE, 12 mm-OD, polyurethane, fire resistant, black		
	1615644	TUBE, 16 mm-OD, polyurethane, fire resistant, black		
2	1612106	ELBOW, male, 10 mm T x R 1/4, with seal, fire resistant	2	
	1612107	ELBOW, male, 10 mm T x R 3/8, with seal, fire resistant		
	1612109	ELBOW, male, 12 mm T x R 1/2, with seal, fire resistant		
	1100040	CONNECTOR, male, elbow, 16 mm T x 1/2 RPT, with seal		
3	-----	BUSHING, BSPT pipe, hydraulic, 3/4 x 1/2, steel, zinc	1	
4	1616611	TUBE, 8 mm-OD, polyurethane, fire resistant, black	8 ft	
5	1613369	BUSHING, red, R 1/4 x RC 1/8, BRS, NP	1	
6	1613372	ELBOW, male, restrict-flow, 8 mm T x R 1/8, 1.7 diameter	1	
7	-----	ADAPTER, 8 mm T x 1/4 RPT	1	
8	1616813	CONNECTOR, male, 37, 3/8 T x G 1/4 female, steel	1	
9	-----	CONNECTOR, male, restrict-flow, 8 mm T x R 1/8, 1.1 diameter	1	


Modul hadice s rámom DP so vzduchovým motorom SD2, pneumatický

Pozri obrázok 20-21 a nasledujúci zoznam náhradných dielov.



Obr. 20 Modul hadice s rámom DP so vzduchovým motorom SD2, pneumatický (1 z 2)

Položka	P/N	Popis	Množstvo	Poznámka
1	1045605	HOSE, -06, low pressure, synthetic, fiber, M2	6 ft	
2	-----	COUPLER, disconnect, barbed, pushlock, 3/8 tube	1	
3	-----	NIPPLE, disconnect, 1/4 T, 3/8 NPT female	1	
4	-----	BUSHING, pipe, hydraulic, 1/2 x 3/8, steel, zinc	1	
5	-----	NIPPLE, pipe, schedule 40, 3/8 NPT, 18 in., galvanized	1	
6	-----	SCREW, socket, M6 x 45, class 12.9, per ISO 4762	4	
7	-----	WASHER, flat, M, regular, M6, steel, zinc, per ISO 7089	8	
8	1616841	CHAIN, cable, 3.43 x 1.02, 18 links	1	
9	-----	SCREW, socket, M6 x 16, zinc, class 12.9, per ISO 4762	4	
10	-----	NUT, lock, nylon, M6, steel, zinc, class 8, per ISO 7040	4	




Obr. 21 Modul hadice s rámom DP so vzduchovým motorom SD2, pneumatický (2 z 2)

Položka	P/N	Popis	Množstvo	Poznámka
1	1616611	TUBE, 8 mm-OD, polyurethane, fire resistant, black	8 ft	
2	-----	BUSHING, BSPT pipe, hydraulic, $\frac{3}{4}$ x $\frac{1}{2}$, steel, zinc	1	
3	1612106	ELBOW, male, 10 mm T x R $\frac{1}{4}$, with seal, fire resistant	2	
	1612107	ELBOW, male, 10 mm T x R $\frac{3}{8}$, with seal, fire resistant		
	1612109	ELBOW, male, 12 mm T x R $\frac{1}{2}$, with seal, fire resistant		
	1100040	CONNECTOR, male, elbow, 16 mm T x $\frac{1}{2}$ RPT, with seal		
4	1616612	TUBE, 10 mm-OD, polyurethane, fire resistant, black	8 ft	
	1616613	TUBE, 12 mm-OD, polyurethane, fire resistant, black		
	1615644	TUBE, 16 mm-OD, polyurethane, fire resistant, black		
5	1613369	BUSHING, red, R $\frac{1}{4}$ x RC $\frac{1}{8}$, BRS, NP	1	
6	1613372	ELBOW, male, restrict-flow, 8 mm T x R $\frac{1}{8}$, 1.7 diameter	1	
7	-----	ADAPTER, 8 mm T x $\frac{1}{4}$ RPT	1	
8	1616813	CONNECTOR, male, 37, $\frac{3}{8}$ T x G $\frac{1}{4}$ female, steel	1	
9	-----	CONNECTOR, male, restrict-flow, 8 mm T x R $\frac{1}{8}$, 1.1 diameter	1	


Modul hadice s malým/velkým rámom so vzduchovým motorom SD3, 55-gal., pneumatický

Pozri obrázok 22-23 a nasledujúci zoznam náhradných dielov.



Obr. 22 Modul hadice s malým/velkým rámom so vzduchovým motorom SD3, 55-gal., pneumatický (1 z 2)

Položka	P/N	Popis	Množstvo	Poznámka
1	-----	NUT, lock, nylon, M6 steel, zinc, class 8, per ISO 7040	4	
2	-----	WASHER, flat, M, regular, M6, steel, zinc, per ISO 7089	8	
3	-----	SCREW, socket, M6 x 16, zinc, class 12.9, per ISO 4762	4	
4	-----	SCREW, socket, M6 x 65, zinc, class 12.9, per ISO 4762	2	
5	1615647	CHAIN, cable, 3.43 x 1.02, 27 links	1	
6	-----	COUPLER, disconnect, barb, pushlock, 3/8 tube	1	
7	1616612	HANGER, hose	1	
8	-----	HOSE, -06, low pressure, synthetic, fiber, M2B	9.5 ft	
9	-----	NIPPLE, disconnect, 1/4 T, 3/8 NPT female	1	
10	-----	NIPPLE, pipe, schedule 40, 3/8 NPT, 18 in., galvanized	1	
11	-----	SCREW, socket, M6 x 45, zinc, class 12.9, per ISO 4762	2	
12	-----	BUSHING, pipe, hydraulic, 1/2 x 3/8, steel, zinc	1	




Obr. 23 Modul hadice s malým/veľkým rámom so vzduchovým motorom SD3, 55-gal., pneumatický (2 z 2)

Položka	P/N	Popis	Množstvo	Poznámka
1	1616612	TUBE, 10 mm-OD, polyurethane, fire resistant, black	9 ft	
	1616613	TUBE, 12 mm-OD, polyurethane, fire resistant, black		
	1615644	TUBE, 16 mm-OD, polyurethane, fire resistant, black		
2	1612106	ELBOW, male, 10 mm T x R ¼, with seal, fire resistant	1	
	1100040	CONNECTOR, male, elbow, 16 mm T x ½ RPT, with seal		
3	1612505	BUSHING, BSPT, pipe, hydraulic, ¾ x ½, steel, zinc	1	
4	1616611	TUBE, 8 mm-OD, polyurethane, fire resistant, black	9 ft	
	1612108	ELBOW, male, 10 mm T x ½, with seal, fire resistant		
5	1612109	ELBOW, male, 12 mm T x ½, with seal, fire resistant	1	
	1100040	CONNECTOR, male, elbow, 16 mm T x ½ RPT, with seal		
6	-----	BUSHING, pipe, hydraulic, ½ x ¾, steel, zinc	1	
7	-----	ELBOW, male, 8 mm T x ¼ RPT	1	
8	-----	ADAPTER, 8 mm T x ¼ RPT	1	
9	1616813	CONNECTOR, male, 37, ¾ T x G ¼ female, steel	1	
10	1610709	CONNECTOR, male, restrict-flow, 8 mm T x R ½, 1.4 diameter	1	


Modul hadice s malým/velkým rámom so vzduchovým motorom SD2, 5-gal. A 55-gal., pneumatický

Pozri obrázok 24-25 a nasledujúci zoznam náhradných dielov.



Obr. 24 Modul hadice s malým/velkým rámom so vzduchovým motorom SD2, 5-gal. A 55-gal., pneumatický (1 z 2)

Položka	P/N	Popis	Množstvo	Poznámka
1	-----	NUT, lock, nylon, M6 steel, zinc, class 8, per ISO 7040	4	
2	-----	WASHER, flat, M, regular, M6, steel, zinc, per ISO 7089	8	
3	-----	SCREW, socket, M6 x 16, zinc, class 12.9, per ISO 4762	4	
4	-----	SCREW, socket, M6 x 65, zinc, class 12.9, per ISO 4762	2	
5	1615647	CHAIN, cable, 3.43 x 1.02, 27 links	1	
6	-----	COUPLER, disconnect, barb, pushlock, 3/8 tube	1	
7	1616612	HANGER, hose	1	
8	-----	HOSE, -06, low pressure, synthetic, fiber, M2B	9.5 ft	
9	-----	NIPPLE, disconnect, 1/4 T, 3/8 NPT female	1	
10	-----	NIPPLE, pipe, schedule 40, 3/8 NPT, 18 in., galvanized	1	
11	-----	SCREW, socket, M6 x 45, zinc, class 12.9, per ISO 4762	2	
12	-----	BUSHING, pipe, hydraulic, 1/2 x 3/8, steel, zinc	1	



Obr. 25 Modul hadice s malým/veľkým rámom so vzduchovým motorom SD2, 5-gal. A 55-gal., pneumatický (2 z 2)

Položka	P/N	Popis	Množstvo	Poznámka
1	1616611	TUBE, 8 mm-OD, polyurethane, fire resistant, black	9 ft	
2	1612505	BUSHING, BSPT, pipe, hydraulic, 3/4 x 1/2, steel, zinc	1	
3	1612106	ELBOW, male, 10 mm T x R 1/4, with seal, fire resistant	1	
	1100040	CONNECTOR, male, elbow, 16 mm T x 1/2 RPT, with seal		
4	1616612	TUBE, 10 mm-OD, polyurethane, fire resistant, black	9 ft	
	1616613	TUBE, 12 mm-OD, polyurethane, fire resistant, black		
	1615644	TUBE, 16 mm-OD, polyurethane, fire resistant, black		
	1612108	ELBOW, male, 10 mm T x 1/2, with seal, fire resistant		
5	1612109	ELBOW, male, 12 mm T x 1/2, with seal, fire resistant	1	
	1100040	CONNECTOR, male, elbow, 16 mm T x 1/2 RPT, with seal		
6	-----	BUSHING, pipe, hydraulic, 1/2 x 3/8, steel, zinc	1	
7	-----	ELBOW, male, 8 mm T x 1/4 RPT	1	A
	-----	ELBOW, male, restrict-flow, 8 mm T x R 1/8, 1.7 diameter		B
8	-----	ADAPTER, 8 mm T x 1/4 RPT	1	
9	1616813	CONNECTOR, male, 37, 3/8 T x G 1/4 female, steel	1	
10	1610709	CONNECTOR, male, restrict-flow, 8 mm T x R 1/8, 1.4 diameter	1	
POZNÁMKA A: Iba 55-galónový modul. B: Iba 5-galónový modul.				

Spotrebný materiál

Lepidlá na použitie podľa pokynov na moduloch hadíc.

P/N	Popis
900481	ADHESIVE, pipe/thread/hydraulic sealant (PST)
900439	ADHESIVE, Loctite [®] , 271, Red, Hi-Strength, 50 ml