

Rhino[®] XD2H Interconnect Hose Modules

Description

See Figure 1. The Rhino XD2H Interconnect Hose Module consists of a hose, tubing, and the hardware necessary to connect the pneumatic control components from the bulk unloader control module to the pump and follower plate.




Figure 1 Interconnect Hose Module

Parts

To order parts, call the Nordson Industrial Coating Systems Customer Support Center at (800) 433-9319 or contact your local Nordson representative.

XD2H Standard Hose Module

See Figure 2 and the following parts list.




Figure 2 XD2H Standard Hose Module Parts

Item	Part	Description	Quantity
—	1082633	MODULE, Interconnect hose, large frame, Rhino XD2, Heated	1
1	972024	• CONNECTOR, female, 1/2 hose, 3/4-16, barbed	1
2	281858	• HOSE, 1/2 ID, Push-Lok	5 ft
3	1082635	• CONNECTOR, barbed, 1/2 BSPT x 1/2 hose, brass	1
4	1082731	• TUBING, 6 mm, Nylon, blue, flame resistant	9 ft
5	324289	• STRAP, cable, 0.06–4.00, black	10
6	972304	• FITTING, tube, 1 1/16–12 x 3/4	1
7	972837	• ELBOW, male, 6 mm tube x 1/8 BSPT	1
8	900481	• ADHESIVE, pipe thread	AR
AR: As Required			

XD2H Hose Module with Depressurization

See Figure 3 and the parts list that begins on page 4.




Figure 3 XD2H Hose Module with Depressurization Parts

4 Rhino XD2H Interconnect Hose Modules

Item	Part	Description	Quantity
—	1614608	MODULE, hose, XD2H, 2-post with depressurization	1
1	1045605	• HOSE, -06, low pressure, synthetic, fiber braid, M2 series, blue	5.5 ft
2	-----	• SCREW, socket, 1/4-20 x 0.750, zinc, Grade 8	2
3	-----	• WASHER, lock, E, SPT, 1/4, steel, zinc, 14451-GA	4
4	-----	• WASHER, flat, regular, 1/4, zinc, per ISO 7090	2
5	-----	• NUT, hex, regular, 1/4-20, steel, zinc, 14441-GA, per ISO 4034	2
6	324046	• HANGER, hose	1
7	124795	• FITTING, hose, 3/4 barbed x 1 1/16	2
8	124792	• HOSE, -12, low pressure, synthetic, fiber braid, M2 series, blue	5.1 ft
9	972119	• ELBOW, male, 1/4 tube x 1/8 NPT	1
10	-----	• TUBING, 1/4 OD Polyethylene, flame resistant	7 ft
11	1073257	• NIPPLE, disconnect, 1/4 T, 3/8 NPT	1
12	1073896	• NIPPLE, pipe, schedule 40, 3/8 NPT, 18 in., galvanized	1
13	973084	• BUSHING, pipe, hydraulic, 1/2 x 3/8, steel, zinc	1
14	973562	• BUSHING, pipe, hydraulic, 3/8 x 1/4, steel, zinc	2
15	-----	• CONNECTOR, 37 degree flare, 5/16 T x 1/4 NPT	1
16	972000	• CONNECTOR, 37 degree, 7/16-20 x 1/4, steel, male	1
17	329829	• CONNECTOR, female, 1/4 hose, 7/16-20 barbed	2
18	329830	• CONNECTOR, female, 1/4 hose, 1/2-20 barbed	2
19	1004375	• CLAMP, hose, 9/16, crimp, double ear	4
20	805652	• HOSE -04, low pressure, synthetic, fiber braid, M2 series, blue	1 ft
21	282785	• CLAMPS, 1 1/2 ID	1
22	-----	• SCREW, socket, 1/4-20 x 2.500, zinc, Grade 8, per ISO 4762	2
23	-----	• WASHER, lock, E, INT, 1/4, steel, zinc	2
24	-----	• CONNECTOR, male, 3/8 hose, 1/4 NPT, barbed	1
25	900439	• ADHESIVE, Loctite® 271, red, high strength, 50 ml	AR
26	900481	• ADHESIVE, pipe thread	AR

Issued 6/19

Original copyright date 2008. Nordson, the Nordson logo, and Rhino are registered trademarks of Nordson Corporation.
All other trademarks are the property of their respective owners.