



Nordson 10-inch Wheel Dolly



Figure 1 - Nordson 10-inch
Wheel Dolly




Figure 2 - Nordson 10-inch
Wheel Dolly Mount Kit

The Nordson 10-inch wheel dolly is furnished with the dolly mount kit installed. The dolly and mount kit are designed to mount either the Model 25B or Model 64B airless pumps, the NH-4 Heater, fluid filter, and necessary hoses. Welded mounting blocks, located on the dolly uprights, provide for installation of the Model EPU-8 Power Unit.

The dolly mount kit is available (less dolly), to facilitate use of customer's present installation. The mount kit is designed to accommodate a complete Nordson Airless System. Equipment may be installed to the mount plate in a number of arrangements. Refer to Figures 3 through 10.

SPECIFICATIONS

(Dolly)	<u>U.S.A.</u>	<u>Metric</u>
Height	41.5 inch	1054 mm
Width	19.75 inch	502 mm
Depth	22.0 inch	559 mm
Wheel Diameter	10.0 inch	254 mm

Nordson Dolly Mounting
Model 25B System Equipment




Figure 3 - Model 25B, NH-4 Heater, Filter, and EPU-8 Power Unit, Front View



Figure 4 - Model 25B, NH-4 Heater, Filter, and EPU-8 Power Unit, Rear View



Figure 5 - Model 25B, NH-4 Heater, and Filter, Front View



Figure 6 - Model 25B, NH-4 Heater, and Filter, Rear View



The above equipment mounting arrangements are shown and suggested because of equipment weight, and for adequate dolly stability during system operation.

NOTE:

Figures 5, 6, 9, and 10, illustrate the pump and heater mounted back-to-back. This arrangement is accomplished by using the four (4) long hex screws (5/16-18 x 1-3/4), lockwashers, and nuts.



Nordson Dolly Mounting
Model 64B System Equipment



Figure 7 - Model 64B, NH-4 Heater, Filter, and EPU-8 Power Unit, Front View



Figure 8 - Model 64B, NH-4 Heater, Filter, and EPU-8 Power Unit, Rear View



Figure 9 - Model 64B, NH-4 Heater and Filter, Front View



Figure 10 - Model 64B, NH-4 Heater and Filter, Rear View



The above equipment mounting arrangements are shown and suggested because of equipment weight, and for adequate dolly stability during system operation.




Figure 11 - Dolly with Mount

PARTS LIST

Key	Kit No.	Part No.	Description	Req'd.
		245 859	Dolly, Wet System, w/Mount	1
3		800 000	. Hose, Rubber, 3/8 I.D., Air	1
4		245 864	. Plate, Mount	1
5		981 264	. Screw, Flt. Hd., 1/4-20 x 3/4	4
6		820 024	. Hose, Nylon, 1/4" x 24" (1/2-20 Fittings)	1
7		983 150	. Lockwasher, .313	8
8		981 309	. Screw, Hex, 5/16-18 x 3/4	8
9		981 312	. Screw, Hex, 5/16-18 x 1-3/4	4
10		984 140	. Nut, Hex, 5/16	4
11		972 180	. Elbow, Male, 1/2-20 x 3/8 NPT	1
12		972 255	. Elbow, Male, 3/4-16 x 3/8 NPT	1
13		972 555	. Fitting, Barbed	1
14		820 036	. Hose, Nylon, 1/4" x 36" (1/2-20 Fittings)	1
NS		972 598	. Connector, Elbow, Male 3/4 x 7/8	1