

# Gun Mounting Bar

---

## **1. Introduction**

---

The gun mounting bar is adjustable for a variety of angles and booth depths. It also provides a stable and versatile system for gun mounting.

---

## **2. Specifications**

---

To follow are the specifications for the gun mounting bar.

Rod length: 914 mm (36 in.)

Clamp capacity: 25.4 mm (1 in.)

Gun mounting  
rod diameter: 12.7 mm ( $\frac{1}{2}$  in.)

### 3. Parts

**NOTE:** Parts included in an assembly are indented to each assembly.

See Figure 1.

Item	Part	Description	Quantity	Note
—	249 160	Bar, gun mounting	1	
1	981 430	• Screw, hex, $\frac{7}{16}$ -14 x 1.0, cap, black	1	
2	247 839	• Rod, gun mounting	1	
3	981 763	• Screw, socket set, $\frac{3}{8}$ -16 x 0.375, flat, zinc	1	
4	248 964	• Rod, adjusting, 3 ft	1	
5	247 844	• Sleeve, locking	1	
6	248 668	• Body, locking	1	
7	248 669	• Body, adjust mounting	1	
8	983 061	• Washer, flat, E, 0.406 x 0.812 x 0.065, zinc	1	
9	249 074	• Handle, adjustable, $\frac{3}{8}$ -16 x 2.75	1	
10	248 957	• Handle, adjustable, $\frac{3}{8}$ -16 x 1.77	1	
11	247 838	• Sleeve, gun end mounting	1	
NS	630 111	Mount, gun, Tribomatic	1	A

**NOTE A:** When using the gun mounting bar with the Tribomatic automatic powder spray gun, discard item 2 and order the Tribomatic gun mount.

NS: Not Shown




Fig. 1 Gun Mounting Bar

Original copyright date 1988. Nordson, the Nordson logo, and Tribomatic are registered trademarks of Nordson Corporation.