


Side-Mount Pump Mounting Kit

Installation

Use this kit to side-mount Nordson 100 Plus and Modular powder pumps.

NOTE: Cut the pickup hose so the end is at least 25 mm (1 in.) above the fluidizing plate. If it is too close, air bubbles and unfluidized powder could be pulled into the pump, resulting in uneven powder flow to the spray guns.



1401388A

Figure 1 Side Mount Pump Mounting Kit Installation

- | | | |
|---------------|---------------|----------------|
| 1. Pump mount | 3. O-ring | 5. Pickup tube |
| 2. O-rings | 4. Ground nut | 6. Hose clamp |

Note: O-rings (item 2) are conductive silicone. Do not replace them with non-conductive O-rings.

Parts

To order parts, call the Nordson Finishing Customer Support Center at (800) 433-9319 or your local Nordson representative.

See Figure 1.

Item	Part	Description	Quantity	Note
-	1051479	KIT, pump mount w/90-degree angled pickup tube	1	
1	114225	• MOUNT, pump	1	
2	941185	• O-RING, silicone, conductive, 0.875 x 1.062 in.	2	
3	942161	• O-RING, silicone, 1.125 x 1.375 x 0.125 in.	1	
4	142382	• NUT, ground, pump mount	1	
5	1051448	• TUBE, pickup, angled, 90 degrees	1	
6	939247	• CLAMP, hose, snap-it	1	

Issued 4/04

Original copyright date 2004. Nordson and the Nordson logo are registered trademarks of Nordson Corporation.