


HRM-1 Mounting Instructions

1. Description

The Nordson HRM-1 mounting kit is used to mount the Model HRM-1 Mini Hopper on the Versa-Spray Dolly System and the Manual Product Line. This kit can also be used to wall-mount the mini-hopper, using items 1, 2 and 4, from the kit and customer supplied fasteners.



3222004B

Fig. 1 Mounting Kit

2. Parts

Item	Part	Description	Quantity	Note
—	141 047	Installation kit, hopper, HRM-1	1	
1	246 749	• Strap, cinching	1	
2	246 747	• Washer, mount strap	1	
3	982 244	• Scr, pan, slt, M5 x 35, zn	2	
4	166 777	• Bracket, mounting, hopper	1	
5	983 127	• Lockwasher, int, M5, zn	2	
6	984 706	• Nut, hex, M5, stl, zn	2	

Original copyright date 1991. Nordson, the Nordson logo, and Versa-Spray are registered trademarks of Nordson Corporation.