

Encore® Generation II
Powder Feed Pump

1095922 Corona Pump

For Complete parts and service information, scan the QR code or go to manuals.nordson.com for instruction sheet 1095927.



NOTE: Two O-rings (item 5) are shipped loose with pump for use with lance assemblies.

1625717
Nozzle Couplings Kit

Elbows

Coupling, Nipple End

Coupling, Socket End

Coupling, Socket End

Nozzle

4 -008, Conductive O-Ring

NOTE: Nozzle Coupling Kit includes items which support Tribo pump assemblies.

Optional Pump Mounts

1082204
Pump Coupling

1085679
Pump Adapter Kit

3 (-114, Conductive O-Ring)

1625718
Pump Body Kit

Body

2 -113, Conductive O-Rings

5

Pump Throat Kits - 10 Pack

1625721
Throat Tivar® Assembly (10 Pack)

1625722
Throat PTFE Assembly (10 Pack)

Standard Tivar Throat

Optional PTFE Throat

1625719
Throat Holder Kit

1 -014, Conductive O-Rings

Throat Holder

Nut

O-Ring Kit 1623816	
1	x20
2	x20
3	x10
4	x20
5	x20

O-Ring Reference Chart
(Use this chart to help in the identification of O-rings.)
(Print requirements for proper sizing: 11x17, landscape)

(-014, Conductive) (-113, Conductive) (-114, Conductive) (-008) (Conductive)

1 2 3 4 5

NOTE: Item 5 (Conductive O-Ring) is not shown in assembly.

Encore® Generation II
Powder Feed Pump

1095924 Tribomatic® Pump

For Complete parts and service information, scan the QR code or go to emanuals.nordson.com for instruction sheet 1095927.



NOTE: Two O-rings (item 5) are shipped loose with pump for use with lance assemblies.

1625717
Nozzle Couplings Kit

NOTE: Nozzle Coupling Kit includes items which support Corona pump assemblies.

Optional Pump Mounts

3 (-114, Conductive O-Ring)

1625718
Pump Body Kit

Pump Throat Kits - 10 Pack

1625721
Throat Tivar Assembly (10 Pack)

1625722
Throat PTFE Assembly (10 Pack)

1625719
Throat Holder Kit

O-Ring Kit 1623816	
1	x20
2	x20
3	x10
4	x20
5	x20

O-Ring Reference Chart (Use this chart to help in the identification of O-rings.) (Print requirements for proper sizing: 11x17, landscape)				
1	2	3	4	5
NOTE: Item 5 (Conductive O-Ring) is not shown in assembly.				