

Gun Mounting Bar

Introduction

The gun mounting bar is adjustable for a variety of angles and booth depths. It also provides a stable and versatile system for gun mounting. Two bar lengths are available:

- 18-inches
- 36-inches

Specifications

To follow are the specifications for the gun mounting bar.

	36-inch Kit	18-inch Kit
Rod length	914-mm (36-in.)	457-mm (18-in.)
Clamp capacity	25.4-mm (1-in.)	25.4-mm (1-in.)
Gun Mounting rod diameter	12.7-mm (¹ / ₂ -in.)	12.7-mm (1/2-in.)

Parts

For parts and technical support, contact Nordson Industrial Coating Systems at (800) 433-9319 or contact your local Nordson representative. Parts can also be ordered from the Internet at <http://www.enordson.com>.

See Figure 1.

Item	Part	Description	Quantity	Note
–	249160	Bar, gun mounting, 36-in.	1	
–	1602271	Bar, gun mounting, 18-in.	1	
1	981430	• Screw, hex, $\frac{7}{16}$ -14 x 1.0, cap, black	1	
2	247839	• Rod, gun mounting	1	
3	981763	• Screw, socket set, $\frac{3}{8}$ -16 x 0.375, flat, zinc	1	
4	248964	• Rod, adjusting, 3 ft	1	B
4	1602272	• Rod, adjusting, 18-in.	1	C
5	247844	• Sleeve, locking	1	
6	248668	• Body, locking	1	
7	248669	• Body, adjust mounting	1	
8	983061	• Washer, flat, E, 0.406 x 0.812 x 0.065, zinc	1	
9	249074	• Handle, adjustable, $\frac{3}{8}$ -16 x 2.75	1	
10	248957	• Handle, adjustable, $\frac{3}{8}$ -16 x 1.77	1	
11	247838	• Sleeve, gun end mounting	1	
NS	630111	• Mount, gun, Tribomatic	1	A

NOTE A: When using the gun mounting bar with the Tribomatic® automatic powder spray gun, discard item 2 and order the Tribomatic gun mount.

B: 36-in. adjusting rod only used with 36-in gun mounting bar (part number 249160).

C: 18-in adjusting rod only used with 18-in gun mounting bar (part number 1602271).

NS: Not Shown




Figure 1 Gun Mounting Bar

Issued 10/12

Original copyright date 2012. Nordson, the Nordson logo, and Tribomatic are registered trademarks of Nordson Corporation.