

NIO2 Automatic In/Out Positioner

For Complete parts and service information, scan the QR code or go to manuals.nordson.com for manual 1603770.



In/Out Positioner Full Assembly
1603758: 0.6 M, 230/460 Vac, 60 Hz 1603759: 0.6 M, 575/600 Vac, 60 Hz 1603766: 1.0 M, 230/460 Vac, 60 Hz 1603767: 1.0 M, 575/600 Vac, 60 Hz 1603762: 1.5 M, 230/460 Vac, 60 Hz 1603763: 1.5 M, 575/600 Vac, 60 Hz
Gearmotors
1602508: 230/460 V, 60 Hz 1602639: 575 V, 60 Hz
Chains
1602631: 87.5 in. (0.6 m stroke) 1602681: 158.5 in. (1.5 m stroke) 1602513: 119.5 in. (1.0 m stroke)
Sensors and Encoder
1108645*: Inductive proximity sensor 7750042: Proximity sensor 1602597: Encoder *Item not shown.
Additional Hardware (Not available for purchase)
Screw, button head, socket, M8 x 14, zinc Washer, flat, M, regular, M8, steel, zinc
NOTE: To set side cover and bumper wheel and other maintenance, refer to the manual.

