

# Excel and CK-SL Hose Routing Tray

---

## 1. Introduction

---

The Nordson hose routing tray is mounted to the Excel and CK-SL powder coating booth. The hose routing tray supports up to 20 hoses, and/or electronic cables.

To obtain part numbers and ordering information about the service kit, refer to the *Parts* section.

**NOTE:** It is not necessary for the hoses to lay side by side. Routing the hoses horizontally through the tray improves the powder flow quality.

---

## 2. Installation

---



**WARNING:** Allow only qualified personnel to perform the following tasks. Observe and follow the safety instructions in this document and all other related documentation.

See Figure 1. Using the provided carriage bolts (2), lock washers (3), and nuts (4), mount the hose routing tray (1) to the Excel or CK-SL powder-coating booth.

## Extension

The hose routing tray can be extended from 1524 mm (60.0 in.) to 1828 mm (72.0 in.).

1. Loosen the carriage bolts (2).
2. Remove the carriage bolts (2), lock washers (3), and hex nuts (4).
3. Extend the tray until the mounting holes are aligned.
4. Insert the carriage bolts (2) into the aligned holes, add the lock washers (3), and tighten the nuts (4).

## Dimensions

See Figure 1.

### 3. Parts

---

The following parts list provides ordering information for the Excel and CK-SL hose routing tray. If you need assistance in ordering parts, contact your Nordson Corporation representative.

Item	Part	Description	Quantity	Note
1	332 769	Tray, hose assembly	1	
2	-----	1/2-13 x 1 LG round head carriage bolt	8	
3	-----	1/2 in. lock washer	8	
4	-----	Nut, hex 1/2-13	8	




Fig. 1 Excel and CK-SL Hose Routing Tray

Original copyright date 1998. Nordson and the Nordson logo are registered trademarks of Nordson Corporation.